



Reliable and Energy saving LED Floodlight

Essential LED Flood BVP152/153 Gen 3

Essential LED MiniFlood Gen 3 comes with a compact and sturdy design. It has a high-quality housing and corrosion-proof powder coating, suitable for general outdoor application. High efficiency designed with latest LED technology, achieves substantial energy savings comparing to conventional floodlights.

Benefits

- Ideal replacement for conventional halogen floodlights with substantial energy savings
- Sturdy design for unique design and feel of luminaire
- Reliable quality and brand promise guarantee hassle free operations for outdoor application

Features

- CCTs: 3000K (WW), 6500K (CW)
- Power: 10W/20W/30W/50W/100W/150W/200W
- Input voltage: 110-277V~ 50/60Hz
- 100 lm/W system efficacy
- 30k hours lifetime (3 years warranty)
- Breather (water stop valve)
- Operating temperature: -40°C to 50°C

Application

- Security Lighting, Landscape, Arena and Sports, Architectural light, Parking area lighting, Amenity

Essential LED Flood BVP152/153 Gen 3

Warnings and Safety

- The luminaire shall be installed or maintained by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements
- The external flexible cable or cord of this luminaire cannot be replaced; if the cord is damaged, the luminaire shall be destroyed.
- The light source of this luminaire is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced

Versions



Essential LED Flood BVP152/153 Gen 3

Essential LED Flood BVP152/153 Gen 3

Essential LED Flood BVP152/153 Gen 3

General Information	
Driver included	Yes
Lamp family code	-
Light source replaceable	No
Light Technical	
Luminaire light beam spread	120°
Color rendering index (CRI)	≥80
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Black
Mech. impact protection code	IK06
Ingress protection code	IP65
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Approval and Application	
Ambient temperature range	-40 °C to 50 °C

Light Technical

		Correlated Color	Luminous Efficacy	Luminous Flux
Order Code	Full Product Name	Temperature (Nom)	(rated) (Nom)	
911401817586	BVP153 G3 LED141/WW 150W 110-277V SWB	3000 K	94 lm/W	14,100 lm
911401837586	BVP153 G3 LED150/CW 150W 110-277V SWB	6500 K	100 lm/W	15,000 lm
911401812586	BVP152 G3 LED18/WW 20W 110-277V SWB	3000 K	94 lm/W	1,880 lm
911401832586	BVP152 G3 LED20/CW 20W 110-277V SWB	6500 K	100 lm/W	2,000 lm
911401811586	BVP152 G3 LED9/WW 10W 110-277V SWB	3000 K	99 lm/W	985 lm
911401831586	BVP152 G3 LED10/CW 10W 110-277V SWB	6500 K	105 lm/W	1,050 lm
911401814586	BVP152 G3 LED47/WW 50W 110-277V SWB	3000 K	94 lm/W	4,700 lm
911401834586	BVP152 G3 LED50/CW 50W 110-277V SWB	6500 K	100 lm/W	5,000 lm
911401818586	BVP153 G3 LED188/WW 200W 110-277V SWB	3000 K	94 lm/W	18,800 lm
911401838586	BVP153 G3 LED200/CW 200W 110-277V SWB	6500 K	100 lm/W	20,000 lm
911401816586	BVP153 G3 LED94/WW 100W 110-277V SWB	3000 K	94 lm/W	9,400 lm
911401836586	BVP153 G3 LED100/CW 100W 110-277V SWB	6500 K	100 lm/W	10,000 lm
911401813586	BVP152 G3 LED28/WW 30W 110-277V SWB	3000 K	94 lm/W	2,820 lm

Essential LED Flood BVP152/153 Gen 3

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401833586	BVP152 G3 LED30/CW 30W 110-277V SWB	6500 K	100 lm/W	3,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
911401817586	BVP153 G3 LED141/WW 150W 110-277V SWB	150 W	Surge protection level until 4 kV
911401837586	BVP153 G3 LED150/CW 150W 110-277V SWB	150 W	Surge protection level until 4 kV
911401812586	BVP152 G3 LED18/WW 20W 110-277V SWB	20 W	Surge protection level until 2 kV
911401832586	BVP152 G3 LED20/CW 20W 110-277V SWB	20 W	Surge protection level until 2 kV
911401811586	BVP152 G3 LED9/WW 10W 110-277V SWB	10 W	Surge protection level until 2 kV
911401831586	BVP152 G3 LED10/CW 10W 110-277V SWB	10 W	Surge protection level until 2 kV
911401814586	BVP152 G3 LED47/WW 50W 110-277V SWB	50 W	Surge protection level until 2 kV

Order Code	Full Product Name	Power Consumption	Surge Protection (Common/Differential)
911401834586	BVP152 G3 LED50/CW 50W 110-277V SWB	50 W	Surge protection level until 2 kV
911401818586	BVP153 G3 LED188/WW 200W 110-277V SWB	200 W	Surge protection level until 4 kV
911401838586	BVP153 G3 LED200/CW 200W 110-277V SWB	200 W	Surge protection level until 4 kV
911401816586	BVP153 G3 LED94/WW 100W 110-277V SWB	100 W	Surge protection level until 4 kV
911401836586	BVP153 G3 LED100/CW 100W 110-277V SWB	100 W	Surge protection level until 4 kV
911401813586	BVP152 G3 LED28/WW 30W 110-277V SWB	30 W	Surge protection level until 2 kV
911401833586	BVP152 G3 LED30/CW 30W 110-277V SWB	30 W	Surge protection level until 2 kV

Mechanical and Housing

Order Code	Full Product Name	Overall height
911401817586	BVP153 G3 LED141/WW 150W 110-277V SWB	316 mm
911401837586	BVP153 G3 LED150/CW 150W 110-277V SWB	316 mm
911401812586	BVP152 G3 LED18/WW 20W 110-277V SWB	122 mm
911401832586	BVP152 G3 LED20/CW 20W 110-277V SWB	122 mm
911401811586	BVP152 G3 LED9/WW 10W 110-277V SWB	105 mm
911401831586	BVP152 G3 LED10/CW 10W 110-277V SWB	105 mm
911401814586	BVP152 G3 LED47/WW 50W 110-277V SWB	176 mm

Order Code	Full Product Name	Overall height
911401834586	BVP152 G3 LED50/CW 50W 110-277V SWB	176 mm
911401818586	BVP153 G3 LED188/WW 200W 110-277V SWB	356 mm
911401838586	BVP153 G3 LED200/CW 200W 110-277V SWB	356 mm
911401816586	BVP153 G3 LED94/WW 100W 110-277V SWB	254 mm
911401836586	BVP153 G3 LED100/CW 100W 110-277V SWB	254 mm
911401813586	BVP152 G3 LED28/WW 30W 110-277V SWB	156 mm
911401833586	BVP152 G3 LED30/CW 30W 110-277V SWB	156 mm

