



Classic heritage design

Classic LEDspotMV

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.

Benefits

- Long lifetime
- Huge energy savings
- Low heat generation.

Features

- Classic heritage design
- Easy retrofit
- Energy-efficient

Application


- Operating temperature range is between -20 °C and 45 °C ambient
- Only to be used in dry indoor environments; can be used in most open fixtures with GU10 lamp holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency lighting fixtures or exit lights

Versions



LED 40W G9 WW 230V Dim SRT6

Dimensional drawing



Product	D	C
LED 40W G9 WW 230V Dim SRT6	18 mm	59 mm

