



T12 Linear fluorescent lighting

T12 Standard

Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Benefits

- Provides highly reliable and high-quality lighting solution at low cost
- Standard colors with moderate color rendering

Features

- Standard colors with moderate color rendering (Ra 50 - 75)
- Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Application

- Mostly used in applications where continuous light output is required and color rendering is not an important factor.


Versions



LPPR TL-RS G13

T12 Standard

Dimensional drawing



General Information	
Cap-Base	G13

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
928003505415	F20T12/D-765 25 PK	Cool Daylight	6200 K	72	975 lm
928006005401	F40T12/54-765 1SL/25	6500 Kelvin	6500 K	72	2,500 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928003505415	F20T12/D-765 25 PK	59 V	19.3 W
928006005401	F40T12/54-765 1SL/25	107 V	40 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
928003505415	F20T12/D-765 25 PK	Yes
928006005401	F40T12/54-765 1SL/25	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928003505415	F20T12/D-765 25 PK	T12
928006005401	F40T12/54-765 1SL/25	T-12

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928003505415	F20T12/D-765 25 PK	8.0 mg
928006005401	F40T12/54-765 1SL/25	8 mg

Product	D (max)	A (max)	B (max)	B (min)	C (max)
F20T12/D-765 25 PK	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
F40T12/54-765 1SL/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
F40T12/D-765 25 PK	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
928006405415	F40T12/D-765 25 PK	Cool Daylight	6200 K	75	2,500 lm

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928006405415	F40T12/D-765 25 PK	107 V	39.5 W

Order Code	Full Product Name	Dimmable
928006405415	F40T12/D-765 25 PK	Yes

Order Code	Full Product Name	Bulb Shape
928006405415	F40T12/D-765 25 PK	T12

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928006405415	F40T12/D-765 25 PK	10.5 mg

