



Maxos LED inserts for TTX400 – efficiency champion with great payback

Maxos LED inserts for TTX400

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED inserts for TTX400 a truly future-proof solution.

Benefits

- Substantial energy savings for a limited investment
- Comfortable light, long lifetime
- Compatibility with proven TTX400 trunking system

Maxos LED inserts for TTX400


Features

- Mid-power LED boards; exchangeable LED unit
- Up to 169 lm/W efficiency
- LED gear trays for T5 and TL-D-length trunkings (high lumen output); replacement LED gear trays with same lumen packages as installed T5 and TL-D solutions (lower wattage)
- Choice of medium, wide and double asymmetric beam lenses
- Compatible with our standard TTX400 rails for TL5 49 W and TL-D 58 W lengths


Application

- Industry
- Warehouses
- Supermarkets, DIY stores, electronics retailers, showrooms

Dimensional drawing



Product details



IPDP_4MX400i_0003-Detail
photo



IPDP_4MX400i_0005-Detail
photo

Maxos LED inserts for TTX400

General Information	
Driver included	Yes
Gear	-
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Controls and Dimming	
Dimmable	Yes
Maximum dim level	1%
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	LED66S
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	LED55S
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	LED80S
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	LED66S
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	LED66S
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	LED66S
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	LED80S
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	LED80S
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	LED80S
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	LED66S
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	LED80S
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	LED55S
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	LED55S
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	LED66S
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	LED66S
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	LED66S
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	LED55S
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	LED55S
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	LED55S
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	LED66S
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	LED66S
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	LED66S
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	LED55S
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	LED55S
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	LED66S
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	LED66S
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	LED66S
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	LED55S
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	LED55S
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	LED55S
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	LED66S
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	LED66S
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	LED66S
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	-
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	-
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	-
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	-
910500460579	4MX400 491 LED55S/840 PSD VWB WH	LED55S
910629123226	4MX400 491 LED40S/830 PSD NB WH	LED40S
910629123326	4MX400 491 LED40S/830 PSD WB WH	LED40S
910629123426	4MX400 491 LED40S/840 PSD NB WH	LED40S
910629123526	4MX400 491 LED40S/840 PSD WB WH	LED40S
910629123626	4MX400 491 LED55S/830 PSD NB WH	LED55S
910629123726	4MX400 491 LED55S/830 PSD WB WH	LED55S
910629123826	4MX400 491 LED55S/840 PSD NB WH	LED55S
910629123926	4MX400 491 LED55S/840 PSD WB WH	LED55S
910629124026	4MX400 581 LED40S/830 PSD NB WH	LED40S
910629124326	4MX400 581 LED40S/840 PSD WB WH	LED40S
910629124626	4MX400 581 LED55S/840 PSD NB WH	LED55S
910629124726	4MX400 581 LED55S/840 PSD WB WH	LED55S
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	LED40S

Maxos LED inserts for TTX400

Order Code	Full Product Name	Lamp family code
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	LED40S
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	LED55S
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	LED55S
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	LED40S
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	LED55S
910629158826	4MX400 581 LED66S/840 PSD WB WH	LED66S
910629158926	4MX400 581 LED66S/840 PSD NB WH	LED66S
910629162326	4MX400 491 LED40S/830 PSD A20 WH	LED40S
910629162426	4MX400 491 LED40S/840 PSD A20 WH	LED40S
910629162526	4MX400 491 LED55S/830 PSD A20 WH	LED55S
910629162626	4MX400 491 LED55S/840 PSD A20 WH	LED55S
910629162726	4MX400 491 LED66S/840 PSD NB WH	LED66S
910629162826	4MX400 491 LED66S/840 PSD WB WH	LED66S
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	LED66S
910629163126	4MX400 581 LED55S/840 PSD A20 WH	LED55S
910629167126	4MX400 491 LED80S/840 PSD WB WH	LED80S
910500460045	4MX400 581 LED80S/840 PSD VWB WH	LED80S
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	LED55S
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	LED80S
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	LED66S
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	LED66S
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	LED80S
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	LED80S
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	LED80S
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	LED66S
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	LED80S
910629124126	4MX400 581 LED40S/830 PSD WB WH	LED40S
910629124226	4MX400 581 LED40S/840 PSD NB WH	LED40S
910629124426	4MX400 581 LED55S/830 PSD NB WH	LED55S
910629124526	4MX400 581 LED55S/830 PSD WB WH	LED55S
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	LED40S
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	LED55S
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	LED66S
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	LED66S
910629166826	4MX400 581 LED80S/840 PSD NB WH	LED80S
910629167326	4MX400 581 LED80S/840 PSD WB WH	LED80S

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	4000 K	169 lm/W	6,600 lm	1
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	4000 K	150 lm/W	5,500 lm	1
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	4000 K	166 lm/W	8,000 lm	1

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	4000 K	169 lm/W	6,600 lm	1
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	4000 K	169 lm/W	6,600 lm	1
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	4000 K	169 lm/W	6,600 lm	1

Maxos LED inserts for TTX400

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	4000 K	166 lm/W	8,000 lm	1
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	4000 K	166 lm/W	8,000 lm	1
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	4000 K	166 lm/W	8,000 lm	1
910500460113	4MX400 491 LED66S/840 PSD- CLO DA20 WH	4000 K	169 lm/W	6,600 lm	1
910500460114	4MX400 491 LED80S/840 PSD- CLO DA20 WH	4000 K	166 lm/W	8,000 lm	1
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	4000 K	150 lm/W	5,500 lm	1
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	4000 K	150 lm/W	5,500 lm	1
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	4000 K	151 lm/W	6,600 lm	1
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	4000 K	151 lm/W	6,600 lm	1
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	4000 K	151 lm/W	6,600 lm	1
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	4000 K	150 lm/W	5,500 lm	1
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	4000 K	150 lm/W	5,500 lm	1
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	4000 K	150 lm/W	5,500 lm	1
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	4000 K	151 lm/W	6,600 lm	1
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	4000 K	151 lm/W	6,600 lm	1
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	4000 K	151 lm/W	6,600 lm	1

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	4000 K	150 lm/W	5,500 lm	1
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	4000 K	150 lm/W	5,500 lm	1
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	4000 K	151 lm/W	6,600 lm	1
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	4000 K	151 lm/W	6,600 lm	1
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	4000 K	151 lm/W	6,600 lm	1
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	4000 K	150 lm/W	5,500 lm	1
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	4000 K	150 lm/W	5,500 lm	1
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	4000 K	150 lm/W	5,500 lm	1
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	4000 K	151 lm/W	6,600 lm	1
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	4000 K	151 lm/W	6,600 lm	1
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	4000 K	151 lm/W	6,600 lm	1
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	4000 K	151 lm/W	6,600 lm	-
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	4000 K	151 lm/W	6,600 lm	-
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	4000 K	151 lm/W	6,600 lm	-
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	4000 K	151 lm/W	6,600 lm	-
910500460579	4MX400 491 LED55S/840 PSD VWB WH	4000 K	169 lm/W	5,500 lm	1

Maxos LED inserts for TTX400

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
910629123226	4MX400 491 LED40S/830 PSD NB WH	3000 K	166 lm/W	4,000 lm	1
910629123326	4MX400 491 LED40S/830 PSD WB WH	3000 K	166 lm/W	4,000 lm	1
910629123426	4MX400 491 LED40S/840 PSD NB WH	4000 K	166 lm/W	4,000 lm	1
910629123526	4MX400 491 LED40S/840 PSD WB WH	4000 K	166 lm/W	4,000 lm	1
910629123626	4MX400 491 LED55S/830 PSD NB WH	3000 K	169 lm/W	5,200 lm	1
910629123726	4MX400 491 LED55S/830 PSD WB WH	3000 K	169 lm/W	5,200 lm	1
910629123826	4MX400 491 LED55S/840 PSD NB WH	4000 K	169 lm/W	5,500 lm	1
910629123926	4MX400 491 LED55S/840 PSD WB WH	4000 K	169 lm/W	5,500 lm	1
910629124026	4MX400 581 LED40S/830 PSD NB WH	3000 K	166 lm/W	4,000 lm	1
910629124326	4MX400 581 LED40S/840 PSD WB WH	4000 K	166 lm/W	4,000 lm	1
910629124626	4MX400 581 LED55S/840 PSD NB WH	4000 K	169 lm/W	5,500 lm	1
910629124726	4MX400 581 LED55S/840 PSD WB WH	4000 K	169 lm/W	5,500 lm	1
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	3000 K	166 lm/W	4,000 lm	1
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	4000 K	166 lm/W	4,000 lm	1
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	3000 K	169 lm/W	5,500 lm	1
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	4000 K	169 lm/W	5,500 lm	1

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	4000 K	166 lm/W	4,000 lm	1
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	3000 K	169 lm/W	5,500 lm	1
910629158826	4MX400 581 LED66S/840 PSD WB WH	4000 K	169 lm/W	6,600 lm	1
910629158926	4MX400 581 LED66S/840 PSD NB WH	4000 K	169 lm/W	6,600 lm	1
910629162326	4MX400 491 LED40S/830 PSD A20 WH	3000 K	166 lm/W	4,000 lm	1
910629162426	4MX400 491 LED40S/840 PSD A20 WH	4000 K	166 lm/W	4,000 lm	1
910629162526	4MX400 491 LED55S/830 PSD A20 WH	3000 K	169 lm/W	5,500 lm	1
910629162626	4MX400 491 LED55S/840 PSD A20 WH	4000 K	169 lm/W	5,500 lm	1
910629162726	4MX400 491 LED66S/840 PSD NB WH	4000 K	169 lm/W	6,600 lm	1
910629162826	4MX400 491 LED66S/840 PSD WB WH	4000 K	169 lm/W	6,600 lm	1
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	4000 K	169 lm/W	6,600 lm	1
910629163126	4MX400 581 LED55S/840 PSD A20 WH	4000 K	169 lm/W	5,500 lm	1
910629167126	4MX400 491 LED80S/840 PSD WB WH	4000 K	166 lm/W	8,000 lm	1
910500460045	4MX400 581 LED80S/840 PSD VWB WH	4000 K	166 lm/W	8,000 lm	1
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	4000 K	169 lm/W	5,500 lm	1
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	4000 K	166 lm/W	8,000 lm	1

Maxos LED inserts for TTX400

Order Code	Full Product Name	Correlated	Luminous	Number
		Color Temperature (Nom)	Efficacy (rated) (Nom) Luminous Flux	
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	4000 K	169 lm/W 6,600 lm	1
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	4000 K	169 lm/W 6,600 lm	1
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	4000 K	166 lm/W 8,000 lm	1
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	4000 K	166 lm/W 8,000 lm	1
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	4000 K	166 lm/W 8,000 lm	1
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	4000 K	169 lm/W 6,600 lm	1
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	4000 K	166 lm/W 8,000 lm	1
910629124126	4MX400 581 LED40S/830 PSD WB WH	3000 K	166 lm/W 4,000 lm	1
910629124226	4MX400 581 LED40S/840 PSD NB WH	4000 K	166 lm/W 4,000 lm	1

Light Technical (2/2)

Order Code	Full Product Name	Optic type
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	Wide beam
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	Narrow beam
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	Double asymmetric optic 20°
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	Double asymmetric optic 20°
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	Narrow beam
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	Wide beam
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	Double asymmetric optic 20°
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	Narrow beam
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	Wide beam
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	Double asymmetric optic 20°
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	Double asymmetric optic 20°
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	Double asymmetric optic 20°

Order Code	Full Product Name	Correlated	Luminous	Number
		Color Temperature (Nom)	Efficacy (rated) (Nom) Luminous Flux	
910629124426	4MX400 581 LED55S/830 PSD NB WH	3000 K	169 lm/W 5,500 lm	1
910629124526	4MX400 581 LED55S/830 PSD WB WH	3000 K	169 lm/W 5,500 lm	1
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	3000 K	166 lm/W 4,000 lm	1
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	4000 K	169 lm/W 5,500 lm	1
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	4000 K	169 lm/W 6,600 lm	1
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	4000 K	169 lm/W 6,600 lm	1
910629166826	4MX400 581 LED80S/840 PSD NB WH	4000 K	166 lm/W 8,000 lm	1
910629167326	4MX400 581 LED80S/840 PSD WB WH	4000 K	166 lm/W 8,000 lm	1

Order Code	Full Product Name	Optic type
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	Wide beam
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	Double asymmetric optic 20°
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	Narrow beam
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	Wide beam
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	Double asymmetric optic 20°
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	Narrow beam
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	Wide beam
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	Double asymmetric optic 20°
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	Narrow beam
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	Wide beam

Maxos LED inserts for TTX400

Order Code	Full Product Name	Optic type
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	Double asymmetric optic 20°
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	Narrow beam
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	Double asymmetric optic 20°
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	Narrow beam
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	Wide beam
910500460180	4MX433 581 LED55S/840 PSD DA20WHEELB3C-2R	Double asymmetric optic 20°
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	Narrow beam
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	Wide beam
910500460183	4MX433 581 LED66S/840 PSD DA20WHEELB3C-2R	Double asymmetric optic 20°
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	Narrow beam
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	Wide beam
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	Wide beam
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	Wide beam
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	Wide beam
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	Wide beam
910500460579	4MX400 491 LED55S/840 PSD VWB WH	Very wide beam
910629123226	4MX400 491 LED40S/830 PSD NB WH	Narrow beam
910629123326	4MX400 491 LED40S/830 PSD WB WH	Wide beam
910629123426	4MX400 491 LED40S/840 PSD NB WH	Narrow beam
910629123526	4MX400 491 LED40S/840 PSD WB WH	Wide beam
910629123626	4MX400 491 LED55S/830 PSD NB WH	Narrow beam
910629123726	4MX400 491 LED55S/830 PSD WB WH	Wide beam
910629123826	4MX400 491 LED55S/840 PSD NB WH	Narrow beam
910629123926	4MX400 491 LED55S/840 PSD WB WH	Wide beam
910629124026	4MX400 581 LED40S/830 PSD NB WH	Narrow beam
910629124326	4MX400 581 LED40S/840 PSD WB WH	Wide beam
910629124626	4MX400 581 LED55S/840 PSD NB WH	Narrow beam
910629124726	4MX400 581 LED55S/840 PSD WB WH	Wide beam
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	Double asymmetric optic 20°
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	Double asymmetric optic 20°
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	Double asymmetric optic 20°
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	Double asymmetric optic 20°
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	Double asymmetric optic 20°
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	Double asymmetric optic 20°

Order Code	Full Product Name	Optic type
910629158826	4MX400 581 LED66S/840 PSD WB WH	Wide beam
910629158926	4MX400 581 LED66S/840 PSD NB WH	Narrow beam
910629162326	4MX400 491 LED40S/830 PSD A20 WH	Asymmetrical mirror axis angle 20°
910629162426	4MX400 491 LED40S/840 PSD A20 WH	Asymmetrical mirror axis angle 20°
910629162526	4MX400 491 LED55S/830 PSD A20 WH	Asymmetrical mirror axis angle 20°
910629162626	4MX400 491 LED55S/840 PSD A20 WH	Asymmetrical mirror axis angle 20°
910629162726	4MX400 491 LED66S/840 PSD NB WH	Narrow beam
910629162826	4MX400 491 LED66S/840 PSD WB WH	Wide beam
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	Double asymmetric optic 20°
910629163126	4MX400 581 LED55S/840 PSD A20 WH	Asymmetrical mirror axis angle 20°
910629167126	4MX400 491 LED80S/840 PSD WB WH	Wide beam
910500460045	4MX400 581 LED80S/840 PSD VWB WH	Very wide beam
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	Very wide beam
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	Double asymmetric optic 20°
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	Double asymmetric optic 20°
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	Narrow beam
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	Double asymmetric optic 20°
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	Narrow beam
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	Wide beam
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	Double asymmetric optic 20°
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	Double asymmetric optic 20°
910629124126	4MX400 581 LED40S/830 PSD WB WH	Wide beam
910629124226	4MX400 581 LED40S/840 PSD NB WH	Narrow beam
910629124426	4MX400 581 LED55S/830 PSD NB WH	Narrow beam
910629124526	4MX400 581 LED55S/830 PSD WB WH	Wide beam
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	Double asymmetric optic 20°
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	Double asymmetric optic 20°
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	Double asymmetric optic 20°
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	Wide beam
910629166826	4MX400 581 LED80S/840 PSD NB WH	Narrow beam
910629167326	4MX400 581 LED80S/840 PSD WB WH	Wide beam

Operating and Electrical

Maxos LED inserts for TTX400

Order Code	Full Product Name	Power Consumption
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	39 W
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	36.5 W
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	48 W
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	39 W
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	39 W
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	39 W
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	48 W
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	48 W
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	48 W
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	39 W
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	48 W
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	36.5 W
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	36.5 W
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	43.5 W
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	43.5 W
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	43.5 W
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	36.5 W
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	36.5 W
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	36.5 W
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	43.5 W
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	43.5 W
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	43.5 W
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	36.5 W
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	36.5 W
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	43.5 W
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	43.5 W
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	43.5 W
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	36.5 W
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	36.5 W
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	36.5 W
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	43.5 W
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	43.5 W
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	43.5 W
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	43.5 W
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	43.5 W
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	43.5 W
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	43.5 W
910500460579	4MX400 491 LED55S/840 PSD VWB WH	32.5 W

Order Code	Full Product Name	Power Consumption
910629123226	4MX400 491 LED40S/830 PSD NB WH	24 W
910629123326	4MX400 491 LED40S/830 PSD WB WH	24 W
910629123426	4MX400 491 LED40S/840 PSD NB WH	24 W
910629123526	4MX400 491 LED40S/840 PSD WB WH	24 W
910629123626	4MX400 491 LED55S/830 PSD NB WH	32.5 W
910629123726	4MX400 491 LED55S/830 PSD WB WH	32.5 W
910629123826	4MX400 491 LED55S/840 PSD NB WH	32.5 W
910629123926	4MX400 491 LED55S/840 PSD WB WH	32.5 W
910629124026	4MX400 581 LED40S/830 PSD NB WH	24 W
910629124326	4MX400 581 LED40S/840 PSD WB WH	24 W
910629124626	4MX400 581 LED55S/840 PSD NB WH	32.5 W
910629124726	4MX400 581 LED55S/840 PSD WB WH	32.5 W
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	24 W
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	24 W
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	32.5 W
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	32.5 W
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	24 W
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	32.5 W
910629158826	4MX400 581 LED66S/840 PSD WB WH	39 W
910629158926	4MX400 581 LED66S/840 PSD NB WH	39 W
910629162326	4MX400 491 LED40S/830 PSD A20 WH	24 W
910629162426	4MX400 491 LED40S/840 PSD A20 WH	24 W
910629162526	4MX400 491 LED55S/830 PSD A20 WH	32.5 W
910629162626	4MX400 491 LED55S/840 PSD A20 WH	32.5 W
910629162726	4MX400 491 LED66S/840 PSD NB WH	39 W
910629162826	4MX400 491 LED66S/840 PSD WB WH	39 W
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	39 W
910629163126	4MX400 581 LED55S/840 PSD A20 WH	32.5 W
910629167126	4MX400 491 LED80S/840 PSD WB WH	48 W
910500460045	4MX400 581 LED80S/840 PSD VWB WH	48 W
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	32.5 W
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	48 W
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	39 W
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	39 W
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	48 W
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	48 W
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	48 W
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	39 W
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	48 W
910629124126	4MX400 581 LED40S/830 PSD WB WH	24 W
910629124226	4MX400 581 LED40S/840 PSD NB WH	24 W
910629124426	4MX400 581 LED55S/830 PSD NB WH	32.5 W
910629124526	4MX400 581 LED55S/830 PSD WB WH	32.5 W
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	24 W
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	32.5 W
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	39 W
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	39 W
910629166826	4MX400 581 LED80S/840 PSD NB WH	48 W
910629167326	4MX400 581 LED80S/840 PSD WB WH	48 W

Controls and Dimming

Maxos LED inserts for TTX400

Order Code	Full Product Name	Embedded control
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	Constant light output
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	-
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	-
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	-
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	-
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	-
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	-
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	-
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	-
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	-
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	-
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	-
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	-
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	-
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	-
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	-
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	-
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	-
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	-
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	-
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	-
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	-
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	-
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	-
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	-
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	-
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	-
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	-
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	-
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	-
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	-
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	-
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	-
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	-
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	-
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	-
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	-
910500460579	4MX400 491 LED55S/840 PSD VWB WH	-
910629123226	4MX400 491 LED40S/830 PSD NB WH	-
910629123326	4MX400 491 LED40S/830 PSD WB WH	-
910629123426	4MX400 491 LED40S/840 PSD NB WH	-
910629123526	4MX400 491 LED40S/840 PSD WB WH	-
910629123626	4MX400 491 LED55S/830 PSD NB WH	-

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	Polymethyl methacrylate bowl/cover

Order Code	Full Product Name	Embedded control
910629123726	4MX400 491 LED55S/830 PSD WB WH	-
910629123826	4MX400 491 LED55S/840 PSD NB WH	-
910629123926	4MX400 491 LED55S/840 PSD WB WH	-
910629124026	4MX400 581 LED40S/830 PSD NB WH	-
910629124326	4MX400 581 LED40S/840 PSD WB WH	-
910629124626	4MX400 581 LED55S/840 PSD NB WH	-
910629124726	4MX400 581 LED55S/840 PSD WB WH	-
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	-
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	-
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	-
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	-
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	-
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	-
910629158826	4MX400 581 LED66S/840 PSD WB WH	-
910629158926	4MX400 581 LED66S/840 PSD NB WH	-
910629162326	4MX400 491 LED40S/830 PSD A20 WH	-
910629162426	4MX400 491 LED40S/840 PSD A20 WH	-
910629162526	4MX400 491 LED55S/830 PSD A20 WH	-
910629162626	4MX400 491 LED55S/840 PSD A20 WH	-
910629162726	4MX400 491 LED66S/840 PSD NB WH	-
910629162826	4MX400 491 LED66S/840 PSD WB WH	-
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	-
910629163126	4MX400 581 LED55S/840 PSD A20 WH	-
910629167126	4MX400 491 LED80S/840 PSD WB WH	-
910500460045	4MX400 581 LED80S/840 PSD VWB WH	-
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	-
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	-
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	-
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	-
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	-
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	-
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	-
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	-
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	-
910629124126	4MX400 581 LED40S/830 PSD WB WH	-
910629124226	4MX400 581 LED40S/840 PSD NB WH	-
910629124426	4MX400 581 LED55S/830 PSD NB WH	-
910629124526	4MX400 581 LED55S/830 PSD WB WH	-
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	-
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	-
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	-
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	-
910629166826	4MX400 581 LED80S/840 PSD NB WH	-
910629167326	4MX400 581 LED80S/840 PSD WB WH	-

Order Code	Full Product Name	Optical cover type
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	Polymethyl methacrylate bowl/cover

Maxos LED inserts for TTX400

Order Code	Full Product Name	Optical cover type
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	Polymethyl methacrylate bowl/cover
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/cover
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/cover
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	Polymethyl methacrylate bowl/cover
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/cover
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/cover
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	Polymethyl methacrylate bowl/cover
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	Polymethyl methacrylate bowl/cover
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	Polymethyl methacrylate bowl/cover
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	Polymethyl methacrylate bowl/cover
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	Polymethyl methacrylate bowl/cover
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	Polymethyl methacrylate bowl/cover
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	Polymethyl methacrylate bowl/cover
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	Polymethyl methacrylate bowl/cover
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/cover
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/cover
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	Polymethyl methacrylate bowl/cover
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/cover
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/cover
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	Polymethyl methacrylate bowl/cover
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	Polymethyl methacrylate bowl/cover
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	Polymethyl methacrylate bowl/cover
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	Polymethyl methacrylate bowl/cover
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	Polymethyl methacrylate bowl/cover
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	Polymethyl methacrylate bowl/cover

Order Code	Full Product Name	Optical cover type
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/cover
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/cover
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	Polymethyl methacrylate bowl/cover
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/cover
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/cover
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	-
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	-
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	-
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	-
910500460579	4MX400 491 LED55S/840 PSD VWB WH	Polymethyl methacrylate bowl/cover
910629123226	4MX400 491 LED40S/830 PSD NB WH	Polymethyl methacrylate bowl/cover
910629123326	4MX400 491 LED40S/830 PSD WB WH	Polymethyl methacrylate bowl/cover
910629123426	4MX400 491 LED40S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
910629123526	4MX400 491 LED40S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
910629123626	4MX400 491 LED55S/830 PSD NB WH	Polymethyl methacrylate bowl/cover
910629123726	4MX400 491 LED55S/830 PSD WB WH	Polymethyl methacrylate bowl/cover
910629123826	4MX400 491 LED55S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
910629123926	4MX400 491 LED55S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
910629124026	4MX400 581 LED40S/830 PSD NB WH	Polymethyl methacrylate bowl/cover
910629124326	4MX400 581 LED40S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
910629124626	4MX400 581 LED55S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
910629124726	4MX400 581 LED55S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover

Maxos LED inserts for TTX400

Order Code	Full Product Name	Optical cover type
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910629158826	4MX400 581 LED66S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
910629158926	4MX400 581 LED66S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
910629162326	4MX400 491 LED40S/830 PSD A20 WH	Polymethyl methacrylate bowl/cover
910629162426	4MX400 491 LED40S/840 PSD A20 WH	Polymethyl methacrylate bowl/cover
910629162526	4MX400 491 LED55S/830 PSD A20 WH	Polymethyl methacrylate bowl/cover
910629162626	4MX400 491 LED55S/840 PSD A20 WH	Polymethyl methacrylate bowl/cover
910629162726	4MX400 491 LED66S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
910629162826	4MX400 491 LED66S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910629163126	4MX400 581 LED55S/840 PSD A20 WH	Polymethyl methacrylate bowl/cover
910629167126	4MX400 491 LED80S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
910500460045	4MX400 581 LED80S/840 PSD VWB WH	Polymethyl methacrylate bowl/cover
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	Polymethyl methacrylate bowl/cover
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	Polymethyl methacrylate bowl/cover

Order Code	Full Product Name	Optical cover type
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/cover
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	Polymethyl methacrylate bowl/cover
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/cover
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/cover
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	Polymethyl methacrylate bowl/cover
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	Polymethyl methacrylate bowl/cover
910629124126	4MX400 581 LED40S/830 PSD WB WH	Polymethyl methacrylate bowl/cover
910629124226	4MX400 581 LED40S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
910629124426	4MX400 581 LED55S/830 PSD NB WH	Polymethyl methacrylate bowl/cover
910629124526	4MX400 581 LED55S/830 PSD WB WH	Polymethyl methacrylate bowl/cover
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/cover
910629166826	4MX400 581 LED80S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
910629167326	4MX400 581 LED80S/840 PSD WB WH	Polymethyl methacrylate bowl/cover

Emergency Operation

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	-	-
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	-	-
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	-	-
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	-	-
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	-	-

Maxos LED inserts for TTX400

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	-	-
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	-	-
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	-	-
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	-	-
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours	3 hour(s)

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
		duration basic version	
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)

Maxos LED inserts for TTX400

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910500460579	4MX400 491 LED55S/840 PSD VWB WH	-	-
910629123226	4MX400 491 LED40S/830 PSD NB WH	-	-
910629123326	4MX400 491 LED40S/830 PSD WB WH	-	-
910629123426	4MX400 491 LED40S/840 PSD NB WH	-	-
910629123526	4MX400 491 LED40S/840 PSD WB WH	-	-
910629123626	4MX400 491 LED55S/830 PSD NB WH	-	-
910629123726	4MX400 491 LED55S/830 PSD WB WH	-	-
910629123826	4MX400 491 LED55S/840 PSD NB WH	-	-
910629123926	4MX400 491 LED55S/840 PSD WB WH	-	-
910629124026	4MX400 581 LED40S/830 PSD NB WH	-	-
910629124326	4MX400 581 LED40S/840 PSD WB WH	-	-
910629124626	4MX400 581 LED55S/840 PSD NB WH	-	-
910629124726	4MX400 581 LED55S/840 PSD WB WH	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	-	-
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	-	-
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	-	-
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	-	-
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	-	-
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	-	-
910629158826	4MX400 581 LED66S/840 PSD WB WH	-	-
910629158926	4MX400 581 LED66S/840 PSD NB WH	-	-
910629162326	4MX400 491 LED40S/830 PSD A20 WH	-	-
910629162426	4MX400 491 LED40S/840 PSD A20 WH	-	-
910629162526	4MX400 491 LED55S/830 PSD A20 WH	-	-
910629162626	4MX400 491 LED55S/840 PSD A20 WH	-	-
910629162726	4MX400 491 LED66S/840 PSD NB WH	-	-
910629162826	4MX400 491 LED66S/840 PSD WB WH	-	-
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	-	-
910629163126	4MX400 581 LED55S/840 PSD A20 WH	-	-
910629167126	4MX400 491 LED80S/840 PSD WB WH	-	-
910500460045	4MX400 581 LED80S/840 PSD VWB WH	-	-
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	-	-
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	-	-
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	-	-
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	-	-
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	-	-

Maxos LED inserts for TTX400

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	-	-
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	-	-
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	-	-
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	-	-
910629124126	4MX400 581 LED40S/830 PSD WB WH	-	-
910629124226	4MX400 581 LED40S/840 PSD NB WH	-	-
910629124426	4MX400 581 LED55S/830 PSD NB WH	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910629124526	4MX400 581 LED55S/830 PSD WB WH	-	-
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	-	-
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	-	-
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	-	-
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	-	-
910629166826	4MX400 581 LED80S/840 PSD NB WH	-	-
910629167326	4MX400 581 LED80S/840 PSD WB WH	-	-

Order Code	Full Product Name	Initial chromaticity
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	(0.38, 0.38) SDCM <3.5
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	(0.38, 0.38) SDCM <3.5
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	(0.38, 0.38) SDCM <3.5
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	(0.38, 0.38) SDCM <3.5
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	(0.38, 0.38) SDCM <3.5

Maxos LED inserts for TTX400

Order Code	Full Product Name	Initial chromaticity
910500460579	4MX400 491 LED55S/840 PSD VWB WH	(0.38, 0.38) SDCM <3.5
910629123226	4MX400 491 LED40S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
910629123326	4MX400 491 LED40S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
910629123426	4MX400 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629123526	4MX400 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629123626	4MX400 491 LED55S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
910629123726	4MX400 491 LED55S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
910629123826	4MX400 491 LED55S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629123926	4MX400 491 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629124026	4MX400 581 LED40S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
910629124326	4MX400 581 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629124626	4MX400 581 LED55S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629124726	4MX400 581 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
910629158826	4MX400 581 LED66S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629158926	4MX400 581 LED66S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629162326	4MX400 491 LED40S/830 PSD A20 WH	(0.43, 0.40) SDCM <3.5
910629162426	4MX400 491 LED40S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5
910629162526	4MX400 491 LED55S/830 PSD A20 WH	(0.43, 0.40) SDCM <3.5
910629162626	4MX400 491 LED55S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5
910629162726	4MX400 491 LED66S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629162826	4MX400 491 LED66S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Initial chromaticity
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629163126	4MX400 581 LED55S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5
910629167126	4MX400 491 LED80S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910500460045	4MX400 581 LED80S/840 PSD VWB WH	(0.38, 0.38) SDCM <3.5
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5
910629124126	4MX400 581 LED40S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
910629124226	4MX400 581 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629124426	4MX400 581 LED55S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
910629124526	4MX400 581 LED55S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910629166826	4MX400 581 LED80S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629167326	4MX400 581 LED80S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5

Product Data

Order Code	Full Product Name	Product family code
910500460028	4MX400 491 LED66S/840 PSD-CLO WB WH	4MX400
910500460061	4MX433 491 LED55S/840 PSD NB WH ELB3	4MX433
910500460099	4MX400 491 LED80S/840 PSD DA20 WH	4MX400
910500460101	4MX400 491 LED66S/840 PSD DA20 WH C-2R	4MX400
910500460102	4MX400 491 LED66S/840 PSD NB WH C-2R	4MX400
910500460103	4MX400 491 LED66S/840 PSD WB WH C-2R	4MX400
910500460104	4MX400 491 LED80S/840 PSD DA20 WH C-2R	4MX400
910500460105	4MX400 491 LED80S/840 PSD NB WH C-2R	4MX400
910500460106	4MX400 491 LED80S/840 PSD WB WH C-2R	4MX400
910500460113	4MX400 491 LED66S/840 PSD-CLO DA20 WH	4MX400
910500460114	4MX400 491 LED80S/840 PSD-CLO DA20 WH	4MX400
910500460154	4MX433 491 LED55S/840 PSD DA20 WH ELB3	4MX433
910500460155	4MX433 491 LED55S/840 PSD WB WH ELB3	4MX433
910500460159	4MX433 491 LED66S/840 PSD DA20 WH ELB3	4MX433
910500460160	4MX433 491 LED66S/840 PSD NB WH ELB3	4MX433
910500460161	4MX433 491 LED66S/840 PSD WB WH ELB3	4MX433
910500460162	4MX433 491 LED55S/840 PSD DA20WHELB3C-2R	4MX433
910500460163	4MX433 491 LED55S/840 PSD NB WH ELB3C-2R	4MX433
910500460164	4MX433 491 LED55S/840 PSD WB WH ELB3C-2R	4MX433
910500460165	4MX433 491 LED66S/840 PSD DA20WHELB3C-2R	4MX433


Order Code	Full Product Name	Product family code
910500460166	4MX433 491 LED66S/840 PSD NB WH ELB3C-2R	4MX433
910500460167	4MX433 491 LED66S/840 PSD WB WH ELB3C-2R	4MX433
910500460171	4MX433 581 LED55S/840 PSD DA20 WH ELB3	4MX433
910500460172	4MX433 581 LED55S/840 PSD NB WH ELB3	4MX433
910500460177	4MX433 581 LED66S/840 PSD DA20 WH ELB3	4MX433
910500460178	4MX433 581 LED66S/840 PSD NB ELB3 WH	4MX433
910500460179	4MX433 581 LED66S/840 PSD WB WH ELB3	4MX433
910500460180	4MX433 581 LED55S/840 PSD DA20WHELB3C-2R	4MX433
910500460181	4MX433 581 LED55S/840 PSD NB WH ELB3C-2R	4MX433
910500460182	4MX433 581 LED55S/840 PSD WB WH ELB3C-2R	4MX433
910500460183	4MX433 581 LED66S/840 PSD DA20WHELB3C-2R	4MX433
910500460184	4MX433 581 LED66S/840 PSD NB WH ELB3C-2R	4MX433
910500460185	4MX433 581 LED66S/840 PSD WB WH ELB3C-2R	4MX433
910500460495	4MX433 491 LED66S/840 PSD WB WH ELP3	4MX433
910500460496	4MX433 581 LED66S/840 PSD WB WH ELP3	4MX433
910500460499	4MX433 491 LED66S/840 PSD WB WH ELD3	4MX433
910500460501	4MX433 581 LED66S/840 PSD WB WH ELD3	4MX433
910500460579	4MX400 491 LED55S/840 PSD VWB WH	4MX400
910629123226	4MX400 491 LED40S/830 PSD NB WH	4MX400
910629123326	4MX400 491 LED40S/830 PSD WB WH	4MX400

Maxos LED inserts for TTX400


Order Code	Full Product Name	Product family code
910629123426	4MX400 491 LED40S/840 PSD NB WH	4MX400
910629123526	4MX400 491 LED40S/840 PSD WB WH	4MX400
910629123626	4MX400 491 LED55S/830 PSD NB WH	4MX400
910629123726	4MX400 491 LED55S/830 PSD WB WH	4MX400
910629123826	4MX400 491 LED55S/840 PSD NB WH	4MX400
910629123926	4MX400 491 LED55S/840 PSD WB WH	4MX400
910629124026	4MX400 581 LED40S/830 PSD NB WH	4MX400
910629124326	4MX400 581 LED40S/840 PSD WB WH	4MX400
910629124626	4MX400 581 LED55S/840 PSD NB WH	4MX400
910629124726	4MX400 581 LED55S/840 PSD WB WH	4MX400
910629128226	4MX400 491 LED40S/830 PSD DA20 WH	4MX400
910629128326	4MX400 491 LED40S/840 PSD DA20 WH	4MX400
910629128426	4MX400 491 LED55S/830 PSD DA20 WH	4MX400
910629128526	4MX400 491 LED55S/840 PSD DA20 WH	4MX400
910629128726	4MX400 581 LED40S/840 PSD DA20 WH	4MX400
910629128826	4MX400 581 LED55S/830 PSD DA20 WH	4MX400
910629158826	4MX400 581 LED66S/840 PSD WB WH	4MX400
910629158926	4MX400 581 LED66S/840 PSD NB WH	4MX400
910629162326	4MX400 491 LED40S/830 PSD A20 WH	4MX400
910629162426	4MX400 491 LED40S/840 PSD A20 WH	4MX400
910629162526	4MX400 491 LED55S/830 PSD A20 WH	4MX400
910629162626	4MX400 491 LED55S/840 PSD A20 WH	4MX400
910629162726	4MX400 491 LED66S/840 PSD NB WH	4MX400
910629162826	4MX400 491 LED66S/840 PSD WB WH	4MX400

Order Code	Full Product Name	Product family code
910629162926	4MX400 491 LED66S/840 PSD DA20 WH	4MX400
910629163126	4MX400 581 LED55S/840 PSD A20 WH	4MX400
910629167126	4MX400 491 LED80S/840 PSD WB WH	4MX400
910500460045	4MX400 581 LED80S/840 PSD VWB WH	4MX400
910500460047	4MX400 581 LED55S/840 PSD VWB WH C-2R	4MX400
910500460107	4MX400 581 LED80S/840 PSD DA20 WH	4MX400
910500460108	4MX400 581 LED66S/840 PSD DA20 WH C-2R	4MX400
910500460109	4MX400 581 LED66S/840 PSD NB WH C-2R	4MX400
910500460110	4MX400 581 LED80S/840 PSD DA20 WH C-2R	4MX400
910500460111	4MX400 581 LED80S/840 PSD NB WH C-2R	4MX400
910500460112	4MX400 581 LED80S/840 PSD WB WH C-2R	4MX400
910500460115	4MX400 581 LED66S/840 PSD-CLO DA20 WH	4MX400
910500460116	4MX400 581 LED80S/840 PSD-CLO DA20 WH	4MX400
910629124126	4MX400 581 LED40S/830 PSD WB WH	4MX400
910629124226	4MX400 581 LED40S/840 PSD NB WH	4MX400
910629124426	4MX400 581 LED55S/830 PSD NB WH	4MX400
910629124526	4MX400 581 LED55S/830 PSD WB WH	4MX400
910629128626	4MX400 581 LED40S/830 PSD DA20 WH	4MX400
910629128926	4MX400 581 LED55S/840 PSD DA20 WH	4MX400
910629158726	4MX400 581 LED66S/840 PSD DA20 WH	4MX400
910629165526	4MX400 581 LED66S/840 PSD WB WH C-2R	4MX400
910629166826	4MX400 581 LED80S/840 PSD NB WH	4MX400
910629167326	4MX400 581 LED80S/840 PSD WB WH	4MX400


Polar Wide Diagrams



Polar Normal (separate) - 4MX400I - 910500460105




Polar Normal (separate) - 4MX400I - 910500460109




Polar Normal (separate) - 4MX400I - 910500460112

Maxos LED inserts for TTX400


Polar Wide Diagrams




Polar Normal (separate) - 4MX400I - 910629123726




Polar Normal (separate) - 4MX400I - 910629165526




Polar Normal (separate) - 4MX400I - 910629124026




Polar Normal (separate) - 4MX400I - 910629123326




Polar Normal (separate) - 4MX400I - 910629124326




Polar Normal (separate) - 4MX400I - 910629124426



Polar Normal (separate) - 4MX400I - 910629123926




Polar Normal (separate) - 4MX400I - 910629158926



Polar Normal (separate) - 4MX400I - 910629124126

Maxos LED inserts for TTX400


Polar Wide Diagrams



Polar Normal (separate) - 4MX400I - 910629167326

Polar Normal (separate) - 4MX400I - 910629124726


Polar Normal (separate) - 4MX400I - 910629124626



Polar Normal (separate) - 4MX400I - 910629123626

Polar Normal (separate) - 4MX400I - 910629123526

Polar Normal (separate) - 4MX400I - 910629124226




Polar Normal (separate) - 4MX400I - 910629123426

Polar Normal (separate) - 4MX400I - 910629162826


Polar Normal (separate) - 4MX400I - 910629124526

Maxos LED inserts for TTX400


Polar Wide Diagrams




Polar Normal (separate) - 4MX400I - 910629123826




Polar Normal (separate) - 4MX400I - 910629158826




Polar Normal (separate) - 4MX400I - 910629123226




Polar Normal (separate) - 4MX400I - 910629162326




Polar Normal (separate) - 4MX400I - 910629162426




Polar Normal (separate) - 4MX400I - 910629162526



Polar Normal (separate) - 4MX400I - 910629162626






Polar Normal (separate) - 4MX400I - 910629162726



Polar Normal (separate) - 4MX400I - 910629163126

Maxos LED inserts for TTX400




Polar Wide Diagrams



Polar Normal (separate) - 4MX400I - 910629166826

Polar Normal (separate) - 4MX400I - 910500460579


Polar Normal (separate) - 4MX400I - 910500460045



Polar Normal (separate) - 4MX400I - 910500460047

Polar Normal (separate) - 4MX400I - 910500460103

Polar Normal (separate) - 4MX400I - 910500460111



Polar Normal (separate) - 4MX400I - 910500460102

Maxos LED inserts for TTX400

