



Maxos LED inserts for TTX400 – efficiency champion with great payback

Maxos LED inserts for TTX400

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED inserts for TTX400 a truly future-proof solution.

Benefits

- Substantial energy savings for a limited investment
- Comfortable light, long lifetime
- Compatibility with proven TTX400 trunking system

Maxos LED inserts for TTX400


Features

- Mid-power LED boards; exchangeable LED unit
- Up to 138 lm/W efficiency
- LED gear trays for T5 and TL-D-length trunkings (high lumen output); replacement LED gear trays with same lumen packages as installed T5 and TL-D solutions (lower wattage)
- Choice of medium, wide and double asymmetric beam lenses
- Compatible with our standard TTX400 rails for TL5 49 W and TL-D 58 W lengths


Application

- Industry
- Warehouses
- Supermarkets, DIY stores, electronics retailers, showrooms

Dimensional drawing



Product details



IPDP_4MX400i_0003-Detail
photo



IPDP_4MX400i_0005-Detail
photo

Maxos LED inserts for TTX400

General Information	
Driver included	Yes
Gear	-
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Controls and Dimming	
Dimmable	Yes
Maximum dim level	1%
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code
97010299	4MX400 491 LED80S/840 PSD NB WH C-2R	LED80S
97011999	4MX400 491 LED80S/840 PSD WB WH C-2R	LED80S
07995699	4MX433 581 LED66S/840 PSD WB WH ELP3	-
66241899	4MX400 491 LED40S/830 PSD NB WH	LED40S
66242599	4MX400 491 LED40S/830 PSD WB WH	LED40S
66243299	4MX400 491 LED40S/840 PSD NB WH	LED40S
66244999	4MX400 491 LED40S/840 PSD WB WH	LED40S
66245699	4MX400 491 LED55S/830 PSD NB WH	LED55S
66246399	4MX400 491 LED55S/830 PSD WB WH	LED55S
66247099	4MX400 491 LED55S/840 PSD NB WH	LED55S
66248799	4MX400 491 LED55S/840 PSD WB WH	LED55S
66249499	4MX400 581 LED40S/830 PSD NB WH	LED40S
66252499	4MX400 581 LED40S/840 PSD WB WH	LED40S
66255599	4MX400 581 LED55S/840 PSD NB WH	LED55S
66256299	4MX400 581 LED55S/840 PSD WB WH	LED55S
66317099	4MX400 491 LED40S/830 PSD DA20 WH	LED40S
66318799	4MX400 491 LED40S/840 PSD DA20 WH	LED40S
66319499	4MX400 491 LED55S/830 PSD DA20 WH	LED55S
66320099	4MX400 491 LED55S/840 PSD DA20 WH	LED55S
66322499	4MX400 581 LED40S/840 PSD DA20 WH	LED40S
66323199	4MX400 581 LED55S/830 PSD DA20 WH	LED55S
66661499	4MX400 581 LED66S/840 PSD WB WH	LED66S
66662199	4MX400 581 LED66S/840 PSD NB WH	LED66S
67278399	4MX400 491 LED80S/840 PSD WB WH	LED80S
66250099	4MX400 581 LED40S/830 PSD WB WH	LED40S
66251799	4MX400 581 LED40S/840 PSD NB WH	LED40S
66253199	4MX400 581 LED55S/830 PSD NB WH	LED55S
66254899	4MX400 581 LED55S/830 PSD WB WH	LED55S
66321799	4MX400 581 LED40S/830 PSD DA20 WH	LED40S
66324899	4MX400 581 LED55S/840 PSD DA20 WH	LED55S
66660799	4MX400 581 LED66S/840 PSD DA20 WH	LED66S

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
97010299	4MX400 491 LED80S/840 PSD NB WH C-2R	4000 K	166 lm/W	8,000 lm	1
97011999	4MX400 491 LED80S/840 PSD WB WH C-2R	4000 K	166 lm/W	8,000 lm	1
07995699	4MX433 581 LED66S/840 PSD WB WH ELP3	4000 K	151 lm/W	6,600 lm	-
66241899	4MX400 491 LED40S/830 PSD NB WH	3000 K	166 lm/W	4,000 lm	1
66242599	4MX400 491 LED40S/830 PSD WB WH	3000 K	166 lm/W	4,000 lm	1
66243299	4MX400 491 LED40S/840 PSD NB WH	4000 K	166 lm/W	4,000 lm	1

Maxos LED inserts for TTX400

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
66244999	4MX400 491 LED40S/840 PSD WB WH	4000 K	166 lm/W	4,000 lm	1
66245699	4MX400 491 LED55S/830 PSD NB WH	3000 K	169 lm/W	5,200 lm	1
66246399	4MX400 491 LED55S/830 PSD WB WH	3000 K	169 lm/W	5,200 lm	1
66247099	4MX400 491 LED55S/840 PSD NB WH	4000 K	169 lm/W	5,500 lm	1
66248799	4MX400 491 LED55S/840 PSD WB WH	4000 K	169 lm/W	5,500 lm	1
66249499	4MX400 581 LED40S/830 PSD NB WH	3000 K	166 lm/W	4,000 lm	1
66252499	4MX400 581 LED40S/840 PSD WB WH	4000 K	166 lm/W	4,000 lm	1
66255599	4MX400 581 LED55S/840 PSD NB WH	4000 K	169 lm/W	5,500 lm	1
66256299	4MX400 581 LED55S/840 PSD WB WH	4000 K	169 lm/W	5,500 lm	1
66317099	4MX400 491 LED40S/830 PSD DA20 WH	3000 K	166 lm/W	4,000 lm	1
66318799	4MX400 491 LED40S/840 PSD DA20 WH	4000 K	166 lm/W	4,000 lm	1
66319499	4MX400 491 LED55S/830 PSD DA20 WH	3000 K	169 lm/W	5,500 lm	1
66320099	4MX400 491 LED55S/840 PSD DA20 WH	4000 K	169 lm/W	5,500 lm	1

Light Technical (2/2)

Order Code	Full Product Name	Optic type
97010299	4MX400 491 LED80S/840 PSD NB WH C-2R	Narrow beam
97011999	4MX400 491 LED80S/840 PSD WB WH C-2R	Wide beam
07995699	4MX433 581 LED66S/840 PSD WB WH ELP3	Wide beam
66241899	4MX400 491 LED40S/830 PSD NB WH	Narrow beam
66242599	4MX400 491 LED40S/830 PSD WB WH	Wide beam
66243299	4MX400 491 LED40S/840 PSD NB WH	Narrow beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
66322499	4MX400 581 LED40S/840 PSD DA20 WH	4000 K	166 lm/W	4,000 lm	1
66323199	4MX400 581 LED55S/830 PSD DA20 WH	3000 K	169 lm/W	5,500 lm	1
66661499	4MX400 581 LED66S/840 PSD WB WH	4000 K	169 lm/W	6,600 lm	1
66662199	4MX400 581 LED66S/840 PSD NB WH	4000 K	169 lm/W	6,600 lm	1
67278399	4MX400 491 LED80S/840 PSD WB WH	4000 K	166 lm/W	8,000 lm	1
66250099	4MX400 581 LED40S/830 PSD WB WH	3000 K	166 lm/W	4,000 lm	1
66251799	4MX400 581 LED40S/840 PSD NB WH	4000 K	166 lm/W	4,000 lm	1
66253199	4MX400 581 LED55S/830 PSD NB WH	3000 K	169 lm/W	5,500 lm	1
66254899	4MX400 581 LED55S/830 PSD WB WH	3000 K	169 lm/W	5,500 lm	1
66321799	4MX400 581 LED40S/830 PSD DA20 WH	3000 K	166 lm/W	4,000 lm	1
66324899	4MX400 581 LED55S/840 PSD DA20 WH	4000 K	169 lm/W	5,500 lm	1
66660799	4MX400 581 LED66S/840 PSD DA20 WH	4000 K	169 lm/W	6,600 lm	1

Order Code	Full Product Name	Optic type
66244999	4MX400 491 LED40S/840 PSD WB WH	Wide beam
66245699	4MX400 491 LED55S/830 PSD NB WH	Narrow beam
66246399	4MX400 491 LED55S/830 PSD WB WH	Wide beam
66247099	4MX400 491 LED55S/840 PSD NB WH	Narrow beam
66248799	4MX400 491 LED55S/840 PSD WB WH	Wide beam
66249499	4MX400 581 LED40S/830 PSD NB WH	Narrow beam

Maxos LED inserts for TTX400

Order Code	Full Product Name	Optic type
66252499	4MX400 581 LED40S/840 PSD WB WH	Wide beam
66255599	4MX400 581 LED55S/840 PSD NB WH	Narrow beam
66256299	4MX400 581 LED55S/840 PSD WB WH	Wide beam
66317099	4MX400 491 LED40S/830 PSD DA20 WH	Double asymmetric optic 20°
66318799	4MX400 491 LED40S/840 PSD DA20 WH	Double asymmetric optic 20°
66319499	4MX400 491 LED55S/830 PSD DA20 WH	Double asymmetric optic 20°
66320099	4MX400 491 LED55S/840 PSD DA20 WH	Double asymmetric optic 20°
66322499	4MX400 581 LED40S/840 PSD DA20 WH	Double asymmetric optic 20°
66323199	4MX400 581 LED55S/830 PSD DA20 WH	Double asymmetric optic 20°

Operating and Electrical

Order Code	Full Product Name	Power Consumption
97010299	4MX400 491 LED80S/840 PSD NB WH C-2R	48 W
97011999	4MX400 491 LED80S/840 PSD WB WH C-2R	48 W
07995699	4MX433 581 LED66S/840 PSD WB WH ELP3	43.5 W
66241899	4MX400 491 LED40S/830 PSD NB WH	24 W
66242599	4MX400 491 LED40S/830 PSD WB WH	24 W
66243299	4MX400 491 LED40S/840 PSD NB WH	24 W
66244999	4MX400 491 LED40S/840 PSD WB WH	24 W
66245699	4MX400 491 LED55S/830 PSD NB WH	32.5 W
66246399	4MX400 491 LED55S/830 PSD WB WH	32.5 W
66247099	4MX400 491 LED55S/840 PSD NB WH	32.5 W
66248799	4MX400 491 LED55S/840 PSD WB WH	32.5 W
66249499	4MX400 581 LED40S/830 PSD NB WH	24 W
66252499	4MX400 581 LED40S/840 PSD WB WH	24 W
66255599	4MX400 581 LED55S/840 PSD NB WH	32.5 W
66256299	4MX400 581 LED55S/840 PSD WB WH	32.5 W
66317099	4MX400 491 LED40S/830 PSD DA20 WH	24 W

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
97010299	4MX400 491 LED80S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/cover
97011999	4MX400 491 LED80S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/cover
07995699	4MX433 581 LED66S/840 PSD WB WH ELP3	-
66241899	4MX400 491 LED40S/830 PSD NB WH	Polymethyl methacrylate bowl/cover
66242599	4MX400 491 LED40S/830 PSD WB WH	Polymethyl methacrylate bowl/cover
66243299	4MX400 491 LED40S/840 PSD NB WH	Polymethyl methacrylate bowl/cover

Order Code	Full Product Name	Optic type
66661499	4MX400 581 LED66S/840 PSD WB WH	Wide beam
66662199	4MX400 581 LED66S/840 PSD NB WH	Narrow beam
67278399	4MX400 491 LED80S/840 PSD WB WH	Wide beam
66250099	4MX400 581 LED40S/830 PSD WB WH	Wide beam
66251799	4MX400 581 LED40S/840 PSD NB WH	Narrow beam
66253199	4MX400 581 LED55S/830 PSD NB WH	Narrow beam
66254899	4MX400 581 LED55S/830 PSD WB WH	Wide beam
66321799	4MX400 581 LED40S/830 PSD DA20 WH	Double asymmetric optic 20°
66324899	4MX400 581 LED55S/840 PSD DA20 WH	Double asymmetric optic 20°
66660799	4MX400 581 LED66S/840 PSD DA20 WH	Double asymmetric optic 20°

Order Code	Full Product Name	Power Consumption
66318799	4MX400 491 LED40S/840 PSD DA20 WH	24 W
66319499	4MX400 491 LED55S/830 PSD DA20 WH	32.5 W
66320099	4MX400 491 LED55S/840 PSD DA20 WH	32.5 W
66322499	4MX400 581 LED40S/840 PSD DA20 WH	24 W
66323199	4MX400 581 LED55S/830 PSD DA20 WH	32.5 W
66661499	4MX400 581 LED66S/840 PSD WB WH	39 W
66662199	4MX400 581 LED66S/840 PSD NB WH	39 W
67278399	4MX400 491 LED80S/840 PSD WB WH	48 W
66250099	4MX400 581 LED40S/830 PSD WB WH	24 W
66251799	4MX400 581 LED40S/840 PSD NB WH	24 W
66253199	4MX400 581 LED55S/830 PSD NB WH	32.5 W
66254899	4MX400 581 LED55S/830 PSD WB WH	32.5 W
66321799	4MX400 581 LED40S/830 PSD DA20 WH	24 W
66324899	4MX400 581 LED55S/840 PSD DA20 WH	32.5 W
66660799	4MX400 581 LED66S/840 PSD DA20 WH	39 W

Order Code	Full Product Name	Optical cover type
66244999	4MX400 491 LED40S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
66245699	4MX400 491 LED55S/830 PSD NB WH	Polymethyl methacrylate bowl/cover
66246399	4MX400 491 LED55S/830 PSD WB WH	Polymethyl methacrylate bowl/cover
66247099	4MX400 491 LED55S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
66248799	4MX400 491 LED55S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
66249499	4MX400 581 LED40S/830 PSD NB WH	Polymethyl methacrylate bowl/cover

Maxos LED inserts for TTX400

Order Code	Full Product Name	Optical cover type
66252499	4MX400 581 LED40S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
66255599	4MX400 581 LED55S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
66256299	4MX400 581 LED55S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
66317099	4MX400 491 LED40S/830 PSD DA20 WH	Polymethyl methacrylate bowl/cover
66318799	4MX400 491 LED40S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
66319499	4MX400 491 LED55S/830 PSD DA20 WH	Polymethyl methacrylate bowl/cover
66320099	4MX400 491 LED55S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
66322499	4MX400 581 LED40S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
66323199	4MX400 581 LED55S/830 PSD DA20 WH	Polymethyl methacrylate bowl/cover
66661499	4MX400 581 LED66S/840 PSD WB WH	Polymethyl methacrylate bowl/cover

Order Code	Full Product Name	Optical cover type
66662199	4MX400 581 LED66S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
67278399	4MX400 491 LED80S/840 PSD WB WH	Polymethyl methacrylate bowl/cover
66250099	4MX400 581 LED40S/830 PSD WB WH	Polymethyl methacrylate bowl/cover
66251799	4MX400 581 LED40S/840 PSD NB WH	Polymethyl methacrylate bowl/cover
66253199	4MX400 581 LED55S/830 PSD NB WH	Polymethyl methacrylate bowl/cover
66254899	4MX400 581 LED55S/830 PSD WB WH	Polymethyl methacrylate bowl/cover
66321799	4MX400 581 LED40S/830 PSD DA20 WH	Polymethyl methacrylate bowl/cover
66324899	4MX400 581 LED55S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover
66660799	4MX400 581 LED66S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover

Emergency Operation

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
97010299	4MX400 491 LED80S/840 PSD NB WH C-2R	-	-
97011999	4MX400 491 LED80S/840 PSD WB WH C-2R	-	-
07995699	4MX433 581 LED66S/840 PSD WB WH ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
66241899	4MX400 491 LED40S/830 PSD NB WH	-	-
66242599	4MX400 491 LED40S/830 PSD WB WH	-	-
66243299	4MX400 491 LED40S/840 PSD NB WH	-	-
66244999	4MX400 491 LED40S/840 PSD WB WH	-	-
66245699	4MX400 491 LED55S/830 PSD NB WH	-	-
66246399	4MX400 491 LED55S/830 PSD WB WH	-	-
66247099	4MX400 491 LED55S/840 PSD NB WH	-	-
66248799	4MX400 491 LED55S/840 PSD WB WH	-	-
66249499	4MX400 581 LED40S/830 PSD NB WH	-	-
66252499	4MX400 581 LED40S/840 PSD WB WH	-	-
66255599	4MX400 581 LED55S/840 PSD NB WH	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
66256299	4MX400 581 LED55S/840 PSD WB WH	-	-
66317099	4MX400 491 LED40S/830 PSD DA20 WH	-	-
66318799	4MX400 491 LED40S/840 PSD DA20 WH	-	-
66319499	4MX400 491 LED55S/830 PSD DA20 WH	-	-
66320099	4MX400 491 LED55S/840 PSD DA20 WH	-	-
66322499	4MX400 581 LED40S/840 PSD DA20 WH	-	-
66323199	4MX400 581 LED55S/830 PSD DA20 WH	-	-
66661499	4MX400 581 LED66S/840 PSD WB WH	-	-
66662199	4MX400 581 LED66S/840 PSD NB WH	-	-
67278399	4MX400 491 LED80S/840 PSD WB WH	-	-
66250099	4MX400 581 LED40S/830 PSD WB WH	-	-
66251799	4MX400 581 LED40S/840 PSD NB WH	-	-
66253199	4MX400 581 LED55S/830 PSD NB WH	-	-
66254899	4MX400 581 LED55S/830 PSD WB WH	-	-

Maxos LED inserts for TTX400

Order Code	Full Product Name	Emergency lighting		Rated duration of the emergency lighting (when fully charged)
66321799	4MX400 581 LED40S/830 PSD DA20 WH	-	-	-
66324899	4MX400 581 LED55S/840 PSD DA20 WH	-	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
97010299	4MX400 491 LED80S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
97011999	4MX400 491 LED80S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
07995699	4MX433 581 LED66S/840 PSD WB WH ELP3	(0.38, 0.38) SDCM <3.5
66241899	4MX400 491 LED40S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
66242599	4MX400 491 LED40S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
66243299	4MX400 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66244999	4MX400 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66245699	4MX400 491 LED55S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
66246399	4MX400 491 LED55S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
66247099	4MX400 491 LED55S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66248799	4MX400 491 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66249499	4MX400 581 LED40S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
66252499	4MX400 581 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66255599	4MX400 581 LED55S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66256299	4MX400 581 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66317099	4MX400 491 LED40S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5

Product Data

Order Code	Full Product Name	Product family code
97010299	4MX400 491 LED80S/840 PSD NB WH C-2R	4MX400
97011999	4MX400 491 LED80S/840 PSD WB WH C-2R	4MX400
07995699	4MX433 581 LED66S/840 PSD WB WH ELP3	4MX433
66241899	4MX400 491 LED40S/830 PSD NB WH	4MX400
66242599	4MX400 491 LED40S/830 PSD WB WH	4MX400
66243299	4MX400 491 LED40S/840 PSD NB WH	4MX400
66244999	4MX400 491 LED40S/840 PSD WB WH	4MX400
66245699	4MX400 491 LED55S/830 PSD NB WH	4MX400
66246399	4MX400 491 LED55S/830 PSD WB WH	4MX400
66247099	4MX400 491 LED55S/840 PSD NB WH	4MX400
66248799	4MX400 491 LED55S/840 PSD WB WH	4MX400
66249499	4MX400 581 LED40S/830 PSD NB WH	4MX400
66252499	4MX400 581 LED40S/840 PSD WB WH	4MX400
66255599	4MX400 581 LED55S/840 PSD NB WH	4MX400
66256299	4MX400 581 LED55S/840 PSD WB WH	4MX400
66317099	4MX400 491 LED40S/830 PSD DA20 WH	4MX400


Order Code	Full Product Name	Emergency lighting		Rated duration of the emergency lighting (when fully charged)
66660799	4MX400 581 LED66S/840 PSD DA20 WH	-	-	-

Order Code	Full Product Name	Initial chromaticity
66318799	4MX400 491 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
66319499	4MX400 491 LED55S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
66320099	4MX400 491 LED55S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
66322499	4MX400 581 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
66323199	4MX400 581 LED55S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
66661499	4MX400 581 LED66S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66662199	4MX400 581 LED66S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
67278399	4MX400 491 LED80S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66250099	4MX400 581 LED40S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
66251799	4MX400 581 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66253199	4MX400 581 LED55S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5
66254899	4MX400 581 LED55S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5
66321799	4MX400 581 LED40S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5
66324899	4MX400 581 LED55S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
66660799	4MX400 581 LED66S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5


Order Code	Full Product Name	Product family code
66318799	4MX400 491 LED40S/840 PSD DA20 WH	4MX400
66319499	4MX400 491 LED55S/830 PSD DA20 WH	4MX400
66320099	4MX400 491 LED55S/840 PSD DA20 WH	4MX400
66322499	4MX400 581 LED40S/840 PSD DA20 WH	4MX400
66323199	4MX400 581 LED55S/830 PSD DA20 WH	4MX400
66661499	4MX400 581 LED66S/840 PSD WB WH	4MX400
66662199	4MX400 581 LED66S/840 PSD NB WH	4MX400
67278399	4MX400 491 LED80S/840 PSD WB WH	4MX400
66250099	4MX400 581 LED40S/830 PSD WB WH	4MX400
66251799	4MX400 581 LED40S/840 PSD NB WH	4MX400
66253199	4MX400 581 LED55S/830 PSD NB WH	4MX400
66254899	4MX400 581 LED55S/830 PSD WB WH	4MX400
66321799	4MX400 581 LED40S/830 PSD DA20 WH	4MX400
66324899	4MX400 581 LED55S/840 PSD DA20 WH	4MX400
66660799	4MX400 581 LED66S/840 PSD DA20 WH	4MX400

Maxos LED inserts for TTX400


Polar Wide Diagrams




Polar Normal (separate) - 4MX400I - 910500460105




Polar Normal (separate) - 4MX400I - 910629123726




Polar Normal (separate) - 4MX400I - 910629124026




Polar Normal (separate) - 4MX400I - 910629123326




Polar Normal (separate) - 4MX400I - 910629124326




Polar Normal (separate) - 4MX400I - 910629124426



Polar Normal (separate) - 4MX400I - 910629123926




Polar Normal (separate) - 4MX400I - 910629158926




Polar Normal (separate) - 4MX400I - 910629124126

Maxos LED inserts for TTX400


Polar Wide Diagrams




Polar Normal (separate) - 4MX400I - 910629124726




Polar Normal (separate) - 4MX400I - 910629124626




Polar Normal (separate) - 4MX400I - 910629123626




Polar Normal (separate) - 4MX400I - 910629123526




Polar Normal (separate) - 4MX400I - 910629124226




Polar Normal (separate) - 4MX400I - 910629123426



Polar Normal (separate) - 4MX400I - 910629124526




Polar Normal (separate) - 4MX400I - 910629123826



Polar Normal (separate) - 4MX400I - 910629158826

Maxos LED inserts for TTX400

Polar Wide Diagrams



Polar Normal (separate) - 4MX400I - 910629123226

