



Maxos LED Industry – innovative, flexible solution delivers ideal light output

Maxos LED

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED Industry offers best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED Industry system comprises exchangeable mid-power LED boards mounted on a standard Maxos trunking rail. A choice of wide and medium-beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: the use of our upgradable LED engine platform makes Maxos LED Industry a truly future-proof solution.

Benefits

- Substantial energy savings for a limited investment
- Comfortable light, long lifetime
- Compatibility with proven Maxos trunking system

Features

- Mid-power LED boards; exchangeable LED unit
- Up to 165 lm/W efficiency
- LED gear trays for T5 and TL-D-length trunkings (high lumen output); replacement LED gear trays with same lumen packages as installed T5 and TL-D solutions (lower wattage)
- Choice of narrow, medium, double asymmetric and asymmetric lenses
- Compatible with our standard Maxos and TTX400 rails for TL5 49 W and TL-D 58 W lengths

Application


- Industry
- Warehouses
- Supermarkets, DIY stores, electronics retailers
- Showrooms

Versions



IPPR 4MX850i 0001

Dimensional drawing



Product details



IPDP_4MX850i_0001-Detail
photo



IPDP_4MX850i_0003-Detail
photo



IPDP_4MX850i_0005-Detail
photo

General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Line Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-

General Information

Order Code	Full Product Name	Lamp family code	Light source	
			replaceable	
910500460502	4MX850 491 LED80S/840 PSD WB SI	LED80S	No	
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	LED66S	No	
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	LED80S	No	
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	LED66S	No	
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	LED80S	No	
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	LED80S	No	
910500460049	4MX850 491 LED80S/840 PSD VWB WH	LED80S	No	
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	LED80S	No	
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	LED80S	No	
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	LED66S	No	
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	LED66S	No	
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	LED66S	No	
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	LED80S	No	
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	LED80S	No	
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	LED80S	No	
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	LED55S	No	
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	LED55S	No	
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	LED55S	No	
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	LED66S	No	
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	LED66S	No	
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	LED66S	No	
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	LED55S	No	
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	LED55S	No	
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	LED55S	No	

Order Code	Full Product Name	Lamp family code	Light source replaceable
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	LED66S	No
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	LED66S	No
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	LED66S	No
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	LED55S	No
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	LED66S	No
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	LED40S	No
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	-	No
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	-	No
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	-	No
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	LED40S	No
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	LED55S	No
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	LED40S	No
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	LED66S	No
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	LED80S	No
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-	-
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-	-
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-	-
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-	-
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-	-
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-	-
910629167426	4MX850 491 LED80S/840 PSD NB WH	LED80S	No
910629167526	4MX850 491 LED80S/840 PSD WB WH	LED80S	No
910500460518	4MX850 581 LED66S/830 PSD WB SI	-	No
910629120826	4MX850 491 LED55S/830 PSD NB SI	LED55S	No
910629120926	4MX850 491 LED55S/840 PSD NB SI	LED55S	No
910629121026	4MX850 491 LED55S/830 PSD WB SI	LED55S	No
910629121126	4MX850 491 LED55S/840 PSD WB SI	LED55S	No
910629121226	4MX850 581 LED55S/830 PSD NB SI	LED55S	No
910629121326	4MX850 581 LED55S/840 PSD NB SI	LED55S	No
910629121426	4MX850 581 LED55S/830 PSD WB SI	LED55S	No
910629121526	4MX850 581 LED55S/840 PSD WB SI	LED55S	No
910629122426	4MX850 491 LED40S/830 PSD NB SI	LED40S	No
910629122526	4MX850 491 LED40S/840 PSD NB SI	LED40S	No
910629122626	4MX850 491 LED40S/830 PSD WB SI	LED40S	No
910629122726	4MX850 491 LED40S/840 PSD WB SI	LED40S	No
910629122826	4MX850 581 LED40S/830 PSD NB SI	LED40S	No
910629122926	4MX850 581 LED40S/840 PSD NB SI	LED40S	No
910629123026	4MX850 581 LED40S/830 PSD WB SI	LED40S	No
910629123126	4MX850 581 LED40S/840 PSD WB SI	LED40S	No
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	LED55S	No
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	LED55S	No
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	LED55S	No
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	LED55S	No
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	LED40S	No
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	LED40S	No
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	LED40S	No
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	LED40S	No
910629160826	4MX850 491 LED55S/830 PSD A20 SI	LED55S	No
910629160926	4MX850 491 LED55S/840 PSD A20 SI	LED55S	No
910629161126	4MX850 491 LED40S/830 PSD A20 SI	LED40S	No
910629161226	4MX850 491 LED40S/840 PSD A20 SI	LED40S	No

Order Code	Full Product Name	Lamp family code	Light source
			replaceable
910629162226	4MX850 491 LED66S/840 PSD A20 SI	LED66S	No
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	LED55S	No
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	LED55S	No
910500457964	4MX850 581 LED80S/840 PSD NB WH	LED80S	No
910500457965	4MX850 581 LED80S/840 PSD WB WH	LED80S	No
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	LED66S	No
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	LED80S	No
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	LED80S	No
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	LED80S	No
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	LED66S	No
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	LED66S	No
910500460048	4MX850 581 LED80S/840 PSD VWB WH	LED80S	No
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	LED40S	No
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	LED66S	No
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	LED80S	No
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	LED66S	No
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	LED80S	No
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	LED66S	No
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	LED80S	No
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	LED55S	No
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	LED55S	No
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	LED55S	No
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	LED66S	No
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	LED66S	No
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	LED55S	No
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	LED55S	No
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	LED55S	No
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	LED66S	No
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	LED66S	No
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	LED55S	No
910500460476	4MX850 581 LED80S/830 PSD VWB WH	-	No
910500460477	4MX850 581 LED80S/830 PSD WB WH	-	No
910500460483	4MX850 581 LED80S/840 PSD A20 WH	LED80S	No
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	-	No
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	-	No
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	LED55S	No
910629120026	4MX850 491 LED55S/830 PSD NB WH	LED55S	No
910629120126	4MX850 491 LED55S/840 PSD NB WH	LED55S	No
910629120226	4MX850 491 LED55S/830 PSD WB WH	LED55S	No
910629120326	4MX850 491 LED55S/840 PSD WB WH	LED55S	No
910629120426	4MX850 581 LED55S/830 PSD NB WH	LED55S	No
910629120526	4MX850 581 LED55S/840 PSD NB WH	LED55S	No
910629120626	4MX850 581 LED55S/830 PSD WB WH	LED55S	No
910629120726	4MX850 581 LED55S/840 PSD WB WH	LED55S	No
910629121626	4MX850 491 LED40S/830 PSD NB WH	LED40S	No
910629121726	4MX850 491 LED40S/840 PSD NB WH	LED40S	No
910629121826	4MX850 491 LED40S/830 PSD WB WH	LED40S	No
910629121926	4MX850 491 LED40S/840 PSD WB WH	LED40S	No
910629122026	4MX850 581 LED40S/830 PSD NB WH	LED40S	No
910629122126	4MX850 581 LED40S/840 PSD NB WH	LED40S	No
910629122226	4MX850 581 LED40S/830 PSD WB WH	LED40S	No

Order Code	Full Product Name	Lamp family code	Light source replaceable
910629122326	4MX850 581 LED40S/840 PSD WB WH	LED40S	No
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	LED55S	No
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	LED55S	No
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	LED55S	No
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	LED55S	No
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	LED40S	No
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	LED40S	No
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	LED40S	No
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	LED40S	No
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	LED66S	No
910629158126	4MX850 491 LED66S/840 PSD WB WH	LED66S	No
910629158226	4MX850 491 LED66S/840 PSD NB WH	LED66S	No
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	LED66S	No
910629160126	4MX850 491 LED66S/830 PSD WB WH	LED66S	No
910629160226	4MX850 491 LED66S/830 PSD NB WH	LED66S	No
910629160326	4MX850 581 LED66S/840 PSD WB WH	LED66S	No
910629160426	4MX850 581 LED66S/840 PSD NB WH	LED66S	No
910629160526	4MX850 491 LED40S/840 PSD A20 WH	LED40S	No
910629160626	4MX850 491 LED55S/840 PSD A20 WH	LED55S	No
910629160726	4MX850 491 LED55S/830 PSD A20 WH	LED55S	No
910629161026	4MX850 491 LED40S/830 PSD A20 WH	LED40S	No
910629162126	4MX850 491 LED66S/840 PSD A20 WH	LED66S	No
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	LED66S	No
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	LED55S	No
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	LED66S	No
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	LED55S	No

Light Technical (1/2)

		Beam	Correlated	Luminous	
	Full Product	angle of	Color	Efficacy	
Order Code	Name	light	Temperature	(rated)	Luminous
		source	(Nom)	(Nom)	Flux
910500460502	4MX850 491	120	4000 K	166 lm/W	8,000 lm
	LED80S/840	degree(s)			
	PSD WB SI				
910500460013	4MX850 491	120	4000 K	169 lm/W	6,600 lm
	LED66S/840	degree(s)			
	PSD-CLO WB				
	WH				
910500460014	4MX850 491	120	4000 K	166 lm/W	8,000 lm
	LED80S/840	degree(s)			
	PSD-CLO WB				
	WH				
910500460016	4MX850 491	120	4000 K	169 lm/W	6,600 lm
	LED66S/840	degree(s)			
	PSD-CLO NB				
	WH				
910500460017	4MX850 491	120	4000 K	166 lm/W	8,000 lm
	LED80S/840	degree(s)			

		Beam	Correlated	Luminous	
	Full Product	angle of	Color	Efficacy	
Order Code	Name	light	Temperature	(rated)	Luminous
		source	(Nom)	(Nom)	Flux
	PSD-CLO NB				
	WH				
910500460023	4MX850 491	120	4000 K	166 lm/W	8,000 lm
	LED80S/840	degree(s)			
	PSD-CLO DA20				
	WH				
910500460049	4MX850 491	120	4000 K	166 lm/W	8,000 lm
	LED80S/840	degree(s)			
	PSD VWB WH				
910500460075	4MX850 491	120	4000 K	166 lm/W	8,000 lm
	LED80S/840	degree(s)			
	PSD VWB WH				
	C-2R				
910500460215	4MX850 491	120	4000 K	166 lm/W	8,000 lm
	LED80S/840	degree(s)			
	PSD DA20 WH				
910500460216	4MX850 491	120	4000 K	169 lm/W	6,600 lm
	LED66S/840	degree(s)			

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSD DA20 WH C-2R				
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	120 degree(s)	4000 K	169 lm/W	6,600 lm
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	120 degree(s)	4000 K	169 lm/W	6,600 lm
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460266	4MX883 491 LED55S/840	120 degree(s)	4000 K	150 lm/W	5,500 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSD DA20 WHELBC-2R				
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	120 degree(s)	4000 K	169 lm/W	5,500 lm
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	120 degree(s)	4000 K	169 lm/W	6,600 lm
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	120 degree(s)	4000 K	166 lm/W	4,000 lm
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	120 degree(s)	3000 K	158 lm/W	3,800 lm
910500460537	4MX850 491 LED40S/840	120 degree(s)	4000 K	166 lm/W	4,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910500460538	PSD NB WH C-2R				
	4MX850 491	120	4000 K	169 lm/W	5,500 lm
910500460560	LED55S/840 PSD NB WH C-2R	degree(s)			
	4MX850 491	120	4000 K	166 lm/W	4,000 lm
910500460561	LED40S/840 PSD A20 WH C-2R	degree(s)			
	4MX850 491	120	4000 K	169 lm/W	6,600 lm
910500460562	LED66S/840 PSD A20 WH C-2R	degree(s)			
	4MX850 491	120	4000 K	166 lm/W	8,000 lm
910505105684	LED80S/840 PSD A20 WH C-2R	degree(s)			
	4MX850 491	-	4000 K	166 lm/W	4,000 lm
910505105685	LED40S/840 DIA NB WH C-2R				
	4MX850 491	-	4000 K	166 lm/W	4,000 lm
910505105686	LED40S/840 DIA WB WH C-2R				
	4MX850 491	-	4000 K	169 lm/W	6,600 lm
910505105687	LED66S/840 DIA NB WH C-2R				
	4MX850 491	-	4000 K	169 lm/W	6,600 lm
910505105688	LED66S/840 DIA WB WH C-2R				
	4MX850 491	-	4000 K	166 lm/W	8,000 lm
910505105689	LED80S/840 DIA NB WH C-2R				
	4MX850 491	-	4000 K	166 lm/W	8,000 lm
910629167426	LED80S/840 PSD NB WH	degree(s)			
	4MX850 491	120	4000 K	166 lm/W	8,000 lm
910629167526	LED80S/840 PSD WB WH	degree(s)			
	4MX850 491	120	4000 K	166 lm/W	8,000 lm
910500460518	LED66S/830 PSD WB SI	degree(s)			
	4MX850 581	120	3000 K	161 lm/W	6,300 lm
910629120826	LED55S/830 PSD NB SI	degree(s)			
	4MX850 491	120	3000 K	160 lm/W	5,200 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910629120926	4MX850 491 LED55S/840 PSD NB SI	120 degree(s)	4000 K	169 lm/W	5,500 lm
	4MX850 491 LED55S/830 PSD WB SI	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629121126	4MX850 491 LED55S/840 PSD WB SI	120 degree(s)	4000 K	169 lm/W	5,500 lm
	4MX850 581 LED55S/830 PSD NB SI	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629121326	4MX850 581 LED55S/840 PSD NB SI	120 degree(s)	4000 K	169 lm/W	5,500 lm
	4MX850 581 LED55S/830 PSD WB SI	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629121426	4MX850 581 LED55S/830 PSD WB SI	120 degree(s)	3000 K	160 lm/W	5,200 lm
	4MX850 581 LED55S/840 PSD WB SI	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629122426	4MX850 491 LED40S/830 PSD NB SI	120 degree(s)	3000 K	158 lm/W	3,800 lm
	4MX850 491 LED40S/840 PSD NB SI	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629122626	4MX850 491 LED40S/830 PSD WB SI	120 degree(s)	3000 K	158 lm/W	3,800 lm
	4MX850 491 LED40S/840 PSD WB SI	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629122826	4MX850 581 LED40S/830 PSD NB SI	120 degree(s)	3000 K	158 lm/W	3,800 lm
	4MX850 581 LED40S/840 PSD NB SI	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629123026	4MX850 581 LED40S/830 PSD WB SI	120 degree(s)	3000 K	158 lm/W	3,800 lm
	4MX850 581 LED40S/840 PSD WB SI	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	120 degree(s)	3000 K	160 lm/W	5,200 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	120 degree(s)	3000 K	158 lm/W	3,800 lm
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	120 degree(s)	3000 K	158 lm/W	3,800 lm
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629160826	4MX850 491 LED55S/830 PSD A20 SI	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629160926	4MX850 491 LED55S/840 PSD A20 SI	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629161126	4MX850 491 LED40S/830 PSD A20 SI	120 degree(s)	3000 K	166 lm/W	4,000 lm
910629161226	4MX850 491 LED40S/840 PSD A20 SI	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629162226	4MX850 491 LED66S/840 PSD A20 SI	120 degree(s)	4000 K	169 lm/W	6,600 lm
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	120 degree(s)	4000 K	169 lm/W	5,500 lm
910500457964	4MX850 581 LED80S/840 PSD NB WH	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500457965	4MX850 581 LED80S/840 PSD WB WH	120 degree(s)	4000 K	166 lm/W	8,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	120 degree(s)	4000 K	169 lm/W	6,600 lm
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	120 degree(s)	4000 K	169 lm/W	6,600 lm
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	120 degree(s)	4000 K	169 lm/W	6,600 lm
910500460048	4MX850 581 LED80S/840 PSD VWB WH	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	120 degree(s)	4000 K	166 lm/W	4,000 lm
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	120 degree(s)	4000 K	169 lm/W	6,600 lm
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	120 degree(s)	4000 K	169 lm/W	6,600 lm
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	120 degree(s)	4000 K	169 lm/W	6,600 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	120 degree(s)	4000 K	150 lm/W	5,500 lm
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	120 degree(s)	4000 K	169 lm/W	5,500 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910500460476	4MX850 581 LED80S/830 PSD VWB WH	120 degree(s)	3000 K	166 lm/W	8,000 lm
910500460477	4MX850 581 LED80S/830 PSD WB WH	120 degree(s)	3000 K	166 lm/W	7,600 lm
910500460483	4MX850 581 LED80S/840 PSD A20 WH	120 degree(s)	4000 K	166 lm/W	8,000 lm
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	120 degree(s)	4000 K	153 lm/W	6,600 lm
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629120026	4MX850 491 LED55S/830 PSD NB WH	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629120126	4MX850 491 LED55S/840 PSD NB WH	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629120226	4MX850 491 LED55S/830 PSD WB WH	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629120326	4MX850 491 LED55S/840 PSD WB WH	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629120426	4MX850 581 LED55S/830 PSD NB WH	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629120526	4MX850 581 LED55S/840 PSD NB WH	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629120626	4MX850 581 LED55S/830 PSD WB WH	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629120726	4MX850 581 LED55S/840 PSD WB WH	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629121626	4MX850 491 LED40S/830 PSD NB WH	120 degree(s)	3000 K	158 lm/W	3,800 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910629121726	4MX850 491 LED40S/840 PSD NB WH	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629121826	4MX850 491 LED40S/830 PSD WB WH	120 degree(s)	3000 K	158 lm/W	3,800 lm
910629121926	4MX850 491 LED40S/840 PSD WB WH	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629122026	4MX850 581 LED40S/830 PSD NB WH	120 degree(s)	3000 K	158 lm/W	3,800 lm
910629122126	4MX850 581 LED40S/840 PSD NB WH	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629122226	4MX850 581 LED40S/830 PSD WB WH	120 degree(s)	3000 K	158 lm/W	3,800 lm
910629122326	4MX850 581 LED40S/840 PSD WB WH	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	120 degree(s)	3000 K	158 lm/W	3,800 lm
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	120 degree(s)	3000 K	158 lm/W	3,800 lm
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	120 degree(s)	4000 K	169 lm/W	6,600 lm
910629158126	4MX850 491 LED66S/840 PSD WB WH	120 degree(s)	4000 K	169 lm/W	6,600 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910629158226	4MX850 491 LED66S/840 PSD NB WH	120 degree(s)	4000 K	169 lm/W	6,600 lm
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	120 degree(s)	3000 K	161 lm/W	6,300 lm
910629160126	4MX850 491 LED66S/830 PSD WB WH	120 degree(s)	3000 K	161 lm/W	6,300 lm
910629160226	4MX850 491 LED66S/830 PSD NB WH	120 degree(s)	3000 K	161 lm/W	6,300 lm
910629160326	4MX850 581 LED66S/840 PSD WB WH	120 degree(s)	4000 K	169 lm/W	6,600 lm
910629160426	4MX850 581 LED66S/840 PSD NB WH	120 degree(s)	4000 K	169 lm/W	6,600 lm
910629160526	4MX850 491 LED40S/840 PSD A20 WH	120 degree(s)	4000 K	166 lm/W	4,000 lm
910629160626	4MX850 491 LED55S/840 PSD A20 WH	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629160726	4MX850 491 LED55S/830 PSD A20 WH	120 degree(s)	3000 K	160 lm/W	5,200 lm
910629161026	4MX850 491 LED40S/830 PSD A20 WH	120 degree(s)	3000 K	166 lm/W	4,000 lm
910629162126	4MX850 491 LED66S/840 PSD A20 WH	120 degree(s)	4000 K	169 lm/W	6,600 lm
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	120 degree(s)	4000 K	153 lm/W	6,600 lm
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	120 degree(s)	4000 K	169 lm/W	5,500 lm
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	120 degree(s)	4000 K	169 lm/W	6,600 lm
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	120 degree(s)	4000 K	169 lm/W	5,500 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of	
		light sources	Optic type
910500460502	4MX850 491 LED80S/840 PSD WB SI	1	Wide beam
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	1	Wide beam
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	1	Wide beam
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	1	Narrow beam
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	1	Narrow beam
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	1	Double asymmetric optic 20°
910500460049	4MX850 491 LED80S/840 PSD VWB WH	1	Very wide beam
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	1	Very wide beam
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	1	Double asymmetric optic 20°
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	1	Narrow beam
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	1	Wide beam
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	1	Double asymmetric optic 20°
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	1	Narrow beam
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	1	Wide beam
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	1	Double asymmetric optic 20°
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	1	Narrow beam
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	1	Wide beam
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	1	Double asymmetric optic 20°
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	1	Narrow beam
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	1	Wide beam
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	1	Double asymmetric optic 20°
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	1	Narrow beam
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	1	Wide beam

Order Code	Full Product Name	Number of	
		light sources	Optic type
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	1	Double asymmetric optic 20°
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	1	Narrow beam
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	1	Wide beam
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	1	Wide beam
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	1	Very wide beam
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	-	Wide beam
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	-	Wide beam
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	-	Wide beam
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	-	Wide beam
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	-	Narrow beam
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	1	Narrow beam
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	-	Asymmetrical mirror axis angle 20°
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	1	Asymmetrical mirror axis angle 20°
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	1	Asymmetrical mirror axis angle 20°
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-	Narrow beam
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-	Wide beam
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-	Narrow beam
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-	Wide beam
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-	Narrow beam
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-	Wide beam
910629167426	4MX850 491 LED80S/840 PSD NB WH	1	Narrow beam
910629167526	4MX850 491 LED80S/840 PSD WB WH	1	Wide beam
910500460518	4MX850 581 LED66S/830 PSD WB SI	-	Wide beam
910629120826	4MX850 491 LED55S/830 PSD NB SI	1	Narrow beam

Order Code	Full Product Name	Number of	
		light sources	Optic type
910629120926	4MX850 491 LED55S/840 PSD NB SI	1	Narrow beam
910629121026	4MX850 491 LED55S/830 PSD WB SI	1	Wide beam
910629121126	4MX850 491 LED55S/840 PSD WB SI	1	Wide beam
910629121226	4MX850 581 LED55S/830 PSD NB SI	1	Narrow beam
910629121326	4MX850 581 LED55S/840 PSD NB SI	1	Narrow beam
910629121426	4MX850 581 LED55S/830 PSD WB SI	1	Wide beam
910629121526	4MX850 581 LED55S/840 PSD WB SI	1	Wide beam
910629122426	4MX850 491 LED40S/830 PSD NB SI	1	Narrow beam
910629122526	4MX850 491 LED40S/840 PSD NB SI	1	Narrow beam
910629122626	4MX850 491 LED40S/830 PSD WB SI	1	Wide beam
910629122726	4MX850 491 LED40S/840 PSD WB SI	1	Wide beam
910629122826	4MX850 581 LED40S/830 PSD NB SI	1	Narrow beam
910629122926	4MX850 581 LED40S/840 PSD NB SI	1	Narrow beam
910629123026	4MX850 581 LED40S/830 PSD WB SI	1	Wide beam
910629123126	4MX850 581 LED40S/840 PSD WB SI	1	Wide beam
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	1	Double asymmetric optic 20°
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	1	Double asymmetric optic 20°
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	1	Double asymmetric optic 20°
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	1	Double asymmetric optic 20°
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	1	Double asymmetric optic 20°
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	1	Double asymmetric optic 20°
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	1	Double asymmetric optic 20°
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	1	Double asymmetric optic 20°
910629160826	4MX850 491 LED55S/830 PSD A20 SI	1	Asymmetrical mirror axis angle 20°
910629160926	4MX850 491 LED55S/840 PSD A20 SI	1	Asymmetrical mirror axis angle 20°

Order Code	Full Product Name	Number of	
		light sources	Optic type
910629161126	4MX850 491 LED40S/830 PSD A20 SI	1	Asymmetrical mirror axis angle 20°
910629161226	4MX850 491 LED40S/840 PSD A20 SI	1	Asymmetrical mirror axis angle 20°
910629162226	4MX850 491 LED66S/840 PSD A20 SI	1	Asymmetrical mirror axis angle 20°
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	1	Double asymmetric optic 35°
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	1	Double asymmetric optic 35°
910500457964	4MX850 581 LED80S/840 PSD NB WH	1	Narrow beam
910500457965	4MX850 581 LED80S/840 PSD WB WH	1	Wide beam
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	1	Wide beam
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	1	Wide beam
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	1	Narrow beam
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	1	Wide beam
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	1	Narrow beam
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	1	Wide beam
910500460048	4MX850 581 LED80S/840 PSD VWB WH	1	Very wide beam
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	-	Wide beam
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	1	Double asymmetric optic 20°
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	1	Double asymmetric optic 20°
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	1	Double asymmetric optic 20°
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	1	Double asymmetric optic 20°
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	1	Double asymmetric optic 20°
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	1	Double asymmetric optic 20°
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	1	Narrow beam
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	1	Wide beam
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	1	Double asymmetric optic 20°

Order Code	Full Product Name	Number of		Optic type
		light	sources	
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	1		Wide beam
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	1		Double asymmetric optic 20°
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	1		Narrow beam
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	1		Wide beam
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	1		Double asymmetric optic 20°
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	1		Narrow beam
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	1		Narrow beam
910500460476	4MX850 581 LED80S/830 PSD VWB WH	-		Very wide beam
910500460477	4MX850 581 LED80S/830 PSD WB WH	-		Wide beam
910500460483	4MX850 581 LED80S/840 PSD A20 WH	1		Asymmetrical mirror axis angle 20°
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	-		Wide beam
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	-		Wide beam
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	1		Wide beam
910629120026	4MX850 491 LED55S/830 PSD NB WH	1		Narrow beam
910629120126	4MX850 491 LED55S/840 PSD NB WH	1		Narrow beam
910629120226	4MX850 491 LED55S/830 PSD WB WH	1		Wide beam
910629120326	4MX850 491 LED55S/840 PSD WB WH	1		Wide beam
910629120426	4MX850 581 LED55S/830 PSD NB WH	1		Narrow beam
910629120526	4MX850 581 LED55S/840 PSD NB WH	1		Narrow beam
910629120626	4MX850 581 LED55S/830 PSD WB WH	1		Wide beam
910629120726	4MX850 581 LED55S/840 PSD WB WH	1		Wide beam
910629121626	4MX850 491 LED40S/830 PSD NB WH	1		Narrow beam
910629121726	4MX850 491 LED40S/840 PSD NB WH	1		Narrow beam
910629121826	4MX850 491 LED40S/830 PSD WB WH	1		Wide beam
910629121926	4MX850 491 LED40S/840 PSD WB WH	1		Wide beam

Order Code	Full Product Name	Number of		Optic type
		light	sources	
910629122026	4MX850 581 LED40S/830 PSD NB WH	1		Narrow beam
910629122126	4MX850 581 LED40S/840 PSD NB WH	1		Narrow beam
910629122226	4MX850 581 LED40S/830 PSD WB WH	1		Wide beam
910629122326	4MX850 581 LED40S/840 PSD WB WH	1		Wide beam
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	1		Double asymmetric optic 20°
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	1		Double asymmetric optic 20°
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	1		Double asymmetric optic 20°
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	1		Double asymmetric optic 20°
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	1		Double asymmetric optic 20°
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	1		Double asymmetric optic 20°
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	1		Double asymmetric optic 20°
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	1		Double asymmetric optic 20°
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	1		Double asymmetric optic 20°
910629158126	4MX850 491 LED66S/840 PSD WB WH	1		Wide beam
910629158226	4MX850 491 LED66S/840 PSD NB WH	1		Narrow beam
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	1		Double asymmetric optic 20°
910629160126	4MX850 491 LED66S/830 PSD WB WH	1		Wide beam
910629160226	4MX850 491 LED66S/830 PSD NB WH	1		Narrow beam
910629160326	4MX850 581 LED66S/840 PSD WB WH	1		Wide beam
910629160426	4MX850 581 LED66S/840 PSD NB WH	1		Narrow beam
910629160526	4MX850 491 LED40S/840 PSD A20 WH	1		Asymmetrical mirror axis angle 20°
910629160626	4MX850 491 LED55S/840 PSD A20 WH	1		Asymmetrical mirror axis angle 20°
910629160726	4MX850 491 LED55S/830 PSD A20 WH	1		Asymmetrical mirror axis angle 20°
910629161026	4MX850 491 LED40S/830 PSD A20 WH	1		Asymmetrical mirror axis angle 20°
910629162126	4MX850 491 LED66S/840 PSD A20 WH	1		Asymmetrical mirror axis angle 20°

Order Code	Full Product Name	Number of	
		light sources	Optic type
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	1	Wide beam
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	1	Double asymmetric optic 35°

Order Code	Full Product Name	Number of	
		light sources	Optic type
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	1	Double asymmetric optic 35°
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	1	Double asymmetric optic 35°

Operating and Electrical

Order Code	Full Product Name	Input		Suitable for random switching
		Voltage	Power Consumption	
910500460502	4MX850 491 LED80S/840 PSD WB SI	220 to 240 V	48 W	Not applicable
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	220-240 V	39 W	Not applicable
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	220-240 V	48 W	Not applicable
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	220-240 V	39 W	Not applicable
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	220-240 V	48 W	Not applicable
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	220-240 V	48 W	Not applicable
910500460049	4MX850 491 LED80S/840 PSD VWB WH	220-240 V	48 W	Not applicable
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	220 to 240 V	48 W	Not applicable
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	220-240 V	48 W	Not applicable
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	220-240 V	39 W	Not applicable
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	220-240 V	39 W	Not applicable
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	220-240 V	39 W	Not applicable
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	220-240 V	48 W	Not applicable

Order Code	Full Product Name	Input		Suitable for random switching
		Voltage	Power Consumption	
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	220-240 V	48 W	Not applicable
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	220-240 V	48 W	Not applicable
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	220-240 V	36.5 W	Not applicable
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	220-240 V	36.5 W	Not applicable
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	220-240 V	36.5 W	Not applicable
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	220-240 V	43 W	Not applicable
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	220-240 V	43 W	Not applicable
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	220-240 V	43 W	Not applicable
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	220-240 V	36.5 W	Not applicable
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	220-240 V	36.5 W	Not applicable
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	220-240 V	36.5 W	Not applicable
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	220-240 V	43 W	Not applicable
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	220-240 V	43 W	Not applicable

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	220-240 V	43 W	Not applicable
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	220-240 V	32.5 W	Not applicable
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	220-240 V	39 W	Not applicable
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	220-240 V	24 W	Not applicable
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	220-240 V	43 W	Not applicable
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	220 to 240 V	43 W	Not applicable
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	220 to 240 V	24 W	Not applicable
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	220-240 V	24 W	Not applicable
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	220-240 V	32.5 W	Not applicable
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	220 to 240 V	24 W	Not applicable
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	220 to 240 V	39 W	Not applicable
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	220 to 240 V	48 W	Not applicable
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	220 to 240 V	24 W	No
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	220 to 240 V	24 W	No
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	220 to 240 V	39 W	No
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	220 to 240 V	39 W	No

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	220 to 240 V	48 W	No
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	220 to 240 V	48 W	No
910629167426	4MX850 491 LED80S/840 PSD NB WH	220-240 V	48 W	Not applicable
910629167526	4MX850 491 LED80S/840 PSD WB WH	220-240 V	48 W	Not applicable
910500460518	4MX850 581 LED66S/830 PSD WB SI	220 to 240 V	39 W	Not applicable
910629120826	4MX850 491 LED55S/830 PSD NB SI	220-240 V	32.5 W	Not applicable
910629120926	4MX850 491 LED55S/840 PSD NB SI	220-240 V	32.5 W	Not applicable
910629121026	4MX850 491 LED55S/830 PSD WB SI	220-240 V	32.5 W	Not applicable
910629121126	4MX850 491 LED55S/840 PSD WB SI	220-240 V	32.5 W	Not applicable
910629121226	4MX850 581 LED55S/830 PSD NB SI	220-240 V	32.5 W	Not applicable
910629121326	4MX850 581 LED55S/840 PSD NB SI	220-240 V	32.5 W	Not applicable
910629121426	4MX850 581 LED55S/830 PSD WB SI	220-240 V	32.5 W	Not applicable
910629121526	4MX850 581 LED55S/840 PSD WB SI	220-240 V	32.5 W	Not applicable
910629122426	4MX850 491 LED40S/830 PSD NB SI	220-240 V	24 W	Not applicable
910629122526	4MX850 491 LED40S/840 PSD NB SI	220-240 V	24 W	Not applicable
910629122626	4MX850 491 LED40S/830 PSD WB SI	220-240 V	24 W	Not applicable
910629122726	4MX850 491 LED40S/840 PSD WB SI	220-240 V	24 W	Not applicable
910629122826	4MX850 581 LED40S/830 PSD NB SI	220-240 V	24 W	Not applicable
910629122926	4MX850 581 LED40S/840 PSD NB SI	220-240 V	24 W	Not applicable
910629123026	4MX850 581 LED40S/830 PSD WB SI	220-240 V	24 W	Not applicable

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910629123126	4MX850 581 LED40S/840 PSD WB SI	220-240 V	24 W	Not applicable
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	220-240 V	32.5 W	Not applicable
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	220-240 V	32.5 W	Not applicable
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	220-240 V	32.5 W	Not applicable
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	220-240 V	32.5 W	Not applicable
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	220-240 V	24 W	Not applicable
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	220-240 V	24 W	Not applicable
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	220-240 V	24 W	Not applicable
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	220-240 V	24 W	Not applicable
910629160826	4MX850 491 LED55S/830 PSD A20 SI	220-240 V	32.5 W	Not applicable
910629160926	4MX850 491 LED55S/840 PSD A20 SI	220-240 V	32.5 W	Not applicable
910629161126	4MX850 491 LED40S/830 PSD A20 SI	220-240 V	24 W	Not applicable
910629161226	4MX850 491 LED40S/840 PSD A20 SI	220-240 V	24 W	Not applicable
910629162226	4MX850 491 LED66S/840 PSD A20 SI	220-240 V	39 W	Not applicable
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	220-240 V	32.5 W	Not applicable
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	220-240 V	32.5 W	Not applicable

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910500457964	4MX850 581 LED80S/840 PSD NB WH	220-240 V	48 W	Not applicable
910500457965	4MX850 581 LED80S/840 PSD WB WH	220-240 V	48 W	Not applicable
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	220-240 V	39 W	Not applicable
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	220-240 V	48 W	Not applicable
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	220-240 V	48 W	Not applicable
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	220-240 V	48 W	Not applicable
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	220-240 V	39 W	Not applicable
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	220-240 V	39 W	Not applicable
910500460048	4MX850 581 LED80S/840 PSD VWB WH	220-240 V	48 W	Not applicable
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	220 to 240 V	24 W	Not applicable
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	220-240 V	39 W	Not applicable
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	220-240 V	48 W	Not applicable
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	220-240 V	39 W	Not applicable
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	220-240 V	48 W	Not applicable
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	220-240 V	39 W	Not applicable
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	220-240 V	48 W	Not applicable

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	220-240 V	36.5 W	Not applicable
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	220-240 V	36.5 W	Not applicable
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	220-240 V	36.5 W	Not applicable
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	220-240 V	43 W	Not applicable
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	220-240 V	43 W	Not applicable
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	220-240 V	36.5 W	Not applicable
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	220-240 V	36.5 W	Not applicable
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	220-240 V	36.5 W	Not applicable
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	220-240 V	43 W	Not applicable
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	220-240 V	43 W	Not applicable
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	220-240 V	32.5 W	Not applicable
910500460476	4MX850 581 LED80S/830 PSD VWB WH	220 to 240 V	48 W	Not applicable
910500460477	4MX850 581 LED80S/830 PSD WB WH	220 to 240 V	48 W	Not applicable
910500460483	4MX850 581 LED80S/840 PSD A20 WH	220 to 240 V	48 W	Not applicable
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	220-240 V	43 W	Not applicable
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	220-240 V	43 W	Not applicable

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	220-240 V	32.5 W	Not applicable
910629120026	4MX850 491 LED55S/830 PSD NB WH	220-240 V	32.5 W	Not applicable
910629120126	4MX850 491 LED55S/840 PSD NB WH	220-240 V	32.5 W	Not applicable
910629120226	4MX850 491 LED55S/830 PSD WB WH	220-240 V	32.5 W	Not applicable
910629120326	4MX850 491 LED55S/840 PSD WB WH	220-240 V	32.5 W	Not applicable
910629120426	4MX850 581 LED55S/830 PSD NB WH	220-240 V	32.5 W	Not applicable
910629120526	4MX850 581 LED55S/840 PSD NB WH	220-240 V	32.5 W	Not applicable
910629120626	4MX850 581 LED55S/830 PSD WB WH	220-240 V	32.5 W	Not applicable
910629120726	4MX850 581 LED55S/840 PSD WB WH	220-240 V	32.5 W	Not applicable
910629121626	4MX850 491 LED40S/830 PSD NB WH	220-240 V	24 W	Not applicable
910629121726	4MX850 491 LED40S/840 PSD NB WH	220-240 V	24 W	Not applicable
910629121826	4MX850 491 LED40S/830 PSD WB WH	220-240 V	24 W	Not applicable
910629121926	4MX850 491 LED40S/840 PSD WB WH	220-240 V	24 W	Not applicable
910629122026	4MX850 581 LED40S/830 PSD NB WH	220-240 V	24 W	Not applicable
910629122126	4MX850 581 LED40S/840 PSD NB WH	220-240 V	24 W	Not applicable
910629122226	4MX850 581 LED40S/830 PSD WB WH	220-240 V	24 W	Not applicable

Maxos LED

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910629122326	4MX850 581 LED40S/840 PSD WB WH	220–240 V	24 W	Not applicable
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	220–240 V	32.5 W	Not applicable
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	220–240 V	32.5 W	Not applicable
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	220–240 V	32.5 W	Not applicable
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	220–240 V	32.5 W	Not applicable
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	220–240 V	24 W	Not applicable
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	220–240 V	24 W	Not applicable
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	220–240 V	24 W	Not applicable
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	220–240 V	24 W	Not applicable
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	220–240 V	39 W	Not applicable
910629158126	4MX850 491 LED66S/840 PSD WB WH	220–240 V	39 W	Not applicable
910629158226	4MX850 491 LED66S/840 PSD NB WH	220–240 V	39 W	Not applicable
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	220–240 V	39 W	Not applicable

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
910629160126	4MX850 491 LED66S/830 PSD WB WH	220–240 V	39 W	Not applicable
910629160226	4MX850 491 LED66S/830 PSD NB WH	220–240 V	39 W	Not applicable
910629160326	4MX850 581 LED66S/840 PSD WB WH	220–240 V	39 W	Not applicable
910629160426	4MX850 581 LED66S/840 PSD NB WH	220–240 V	39 W	Not applicable
910629160526	4MX850 491 LED40S/840 PSD A20 WH	220–240 V	24 W	Not applicable
910629160626	4MX850 491 LED55S/840 PSD A20 WH	220–240 V	32.5 W	Not applicable
910629160726	4MX850 491 LED55S/830 PSD A20 WH	220–240 V	32.5 W	Not applicable
910629161026	4MX850 491 LED40S/830 PSD A20 WH	220–240 V	24 W	Not applicable
910629162126	4MX850 491 LED66S/840 PSD A20 WH	220–240 V	39 W	Not applicable
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C–2R	220–240 V	43 W	Not applicable
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	220–240 V	32.5 W	Not applicable
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	220–240 V	39 W	Not applicable
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	220–240 V	32.5 W	Not applicable

Controls and Dimming

Order Code	Full Product Name	Embedded control	Maximum dim level
910500460502	4MX850 491 LED80S/840 PSD WB SI	–	1%
910500460013	4MX850 491 LED66S/840 PSD–CLO WB WH	Constant light output	1%
910500460014	4MX850 491 LED80S/840 PSD–CLO WB WH	Constant light output	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910500460016	4MX850 491 LED66S/840 PSD–CLO NB WH	Constant light output	1%
910500460017	4MX850 491 LED80S/840 PSD–CLO NB WH	Constant light output	1%
910500460023	4MX850 491 LED80S/840 PSD–CLO DA20 WH	Constant light output	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910500460049	4MX850 491 LED80S/840 PSD VWB WH	-	1%
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	-	1%
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	-	1%
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	-	1%
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	-	1%
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	-	1%
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	-	1%
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	-	1%
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	-	1%
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	-	1%
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	-	1%
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	-	1%
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	-	1%
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	-	1%
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	-	1%
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	-	1%
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	-	1%
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	-	1%
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	-	1%
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	-	1%
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	-	1%
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	-	1%
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	-	1%
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	-	1%
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	-	1%
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	-	1%
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	-	1%
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	-	1%
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	-	1%
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	-	1%
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	-	1%
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-	-
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-	-
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-	-
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-	-
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-	-
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-	-
910629167426	4MX850 491 LED80S/840 PSD NB WH	-	1%
910629167526	4MX850 491 LED80S/840 PSD WB WH	-	1%
910500460518	4MX850 581 LED66S/830 PSD WB SI	-	1%
910629120826	4MX850 491 LED55S/830 PSD NB SI	-	1%
910629120926	4MX850 491 LED55S/840 PSD NB SI	-	1%
910629121026	4MX850 491 LED55S/830 PSD WB SI	-	1%
910629121126	4MX850 491 LED55S/840 PSD WB SI	-	1%
910629121226	4MX850 581 LED55S/830 PSD NB SI	-	1%
910629121326	4MX850 581 LED55S/840 PSD NB SI	-	1%
910629121426	4MX850 581 LED55S/830 PSD WB SI	-	1%
910629121526	4MX850 581 LED55S/840 PSD WB SI	-	1%
910629122426	4MX850 491 LED40S/830 PSD NB SI	-	1%
910629122526	4MX850 491 LED40S/840 PSD NB SI	-	1%
910629122626	4MX850 491 LED40S/830 PSD WB SI	-	1%
910629122726	4MX850 491 LED40S/840 PSD WB SI	-	1%
910629122826	4MX850 581 LED40S/830 PSD NB SI	-	1%
910629122926	4MX850 581 LED40S/840 PSD NB SI	-	1%
910629123026	4MX850 581 LED40S/830 PSD WB SI	-	1%
910629123126	4MX850 581 LED40S/840 PSD WB SI	-	1%
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	-	1%
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	-	1%
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	-	1%
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	-	1%
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	-	1%
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	-	1%
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	-	1%
910629160826	4MX850 491 LED55S/830 PSD A20 SI	-	1%
910629160926	4MX850 491 LED55S/840 PSD A20 SI	-	1%
910629161126	4MX850 491 LED40S/830 PSD A20 SI	-	1%
910629161226	4MX850 491 LED40S/840 PSD A20 SI	-	1%
910629162226	4MX850 491 LED66S/840 PSD A20 SI	-	1%
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	-	1%
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	-	1%
910500457964	4MX850 581 LED80S/840 PSD NB WH	-	1%
910500457965	4MX850 581 LED80S/840 PSD WB WH	-	1%
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	Constant light output	1%
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	Constant light output	1%
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	-	1%
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	-	1%
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	-	1%
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	-	1%
910500460048	4MX850 581 LED80S/840 PSD VWB WH	-	1%
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	-	1%
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	-	1%
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	-	1%
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	-	1%
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	-	1%
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	-	1%
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	-	1%
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	-	1%
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	-	1%
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	-	1%
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	-	1%
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	-	1%
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	-	1%
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	-	1%
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	-	1%
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	-	1%
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	-	1%
910500460476	4MX850 581 LED80S/830 PSD VWB WH	-	1%
910500460477	4MX850 581 LED80S/830 PSD WB WH	-	1%
910500460483	4MX850 581 LED80S/840 PSD A20 WH	-	1%
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	-	1%
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	-	1%
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	-	1%
910629120026	4MX850 491 LED55S/830 PSD NB WH	-	1%
910629120126	4MX850 491 LED55S/840 PSD NB WH	-	1%
910629120226	4MX850 491 LED55S/830 PSD WB WH	-	1%
910629120326	4MX850 491 LED55S/840 PSD WB WH	-	1%
910629120426	4MX850 581 LED55S/830 PSD NB WH	-	1%
910629120526	4MX850 581 LED55S/840 PSD NB WH	-	1%
910629120626	4MX850 581 LED55S/830 PSD WB WH	-	1%
910629120726	4MX850 581 LED55S/840 PSD WB WH	-	1%
910629121626	4MX850 491 LED40S/830 PSD NB WH	-	1%
910629121726	4MX850 491 LED40S/840 PSD NB WH	-	1%
910629121826	4MX850 491 LED40S/830 PSD WB WH	-	1%
910629121926	4MX850 491 LED40S/840 PSD WB WH	-	1%
910629122026	4MX850 581 LED40S/830 PSD NB WH	-	1%
910629122126	4MX850 581 LED40S/840 PSD NB WH	-	1%
910629122226	4MX850 581 LED40S/830 PSD WB WH	-	1%
910629122326	4MX850 581 LED40S/840 PSD WB WH	-	1%
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	-	1%
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	-	1%
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	-	1%
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	-	1%
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	-	1%
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	-	1%
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	-	1%
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	-	1%
910629158126	4MX850 491 LED66S/840 PSD WB WH	-	1%
910629158226	4MX850 491 LED66S/840 PSD NB WH	-	1%
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	-	1%
910629160126	4MX850 491 LED66S/830 PSD WB WH	-	1%
910629160226	4MX850 491 LED66S/830 PSD NB WH	-	1%
910629160326	4MX850 581 LED66S/840 PSD WB WH	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910629160426	4MX850 581 LED66S/840 PSD NB WH	-	1%
910629160526	4MX850 491 LED40S/840 PSD A20 WH	-	1%
910629160626	4MX850 491 LED55S/840 PSD A20 WH	-	1%
910629160726	4MX850 491 LED55S/830 PSD A20 WH	-	1%
910629161026	4MX850 491 LED40S/830 PSD A20 WH	-	1%
910629162126	4MX850 491 LED66S/840 PSD A20 WH	-	1%
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	-	1%
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	-	1%
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	-	1%
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	-	1%

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing Color
910500460502	4MX850 491 LED80S/840 PSD WB SI	Polymethyl methacrylate bowl/cover	Silver
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	Polymethyl methacrylate bowl/cover	White
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	Polymethyl methacrylate bowl/cover	White
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	Polymethyl methacrylate bowl/cover	White
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	Polymethyl methacrylate bowl/cover	White
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	Polymethyl methacrylate bowl/cover	White
910500460049	4MX850 491 LED80S/840 PSD VWB WH	Polymethyl methacrylate bowl/cover	White
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	Polymethyl methacrylate bowl/cover	White
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	Polymethyl methacrylate bowl/cover	White

Order Code	Full Product Name	Optical cover type	Housing Color
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	Polymethyl methacrylate bowl/cover	White
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/cover	White
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/cover	White
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	Polymethyl methacrylate bowl/cover	White
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/cover	White
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/cover	White
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	Polymethyl methacrylate bowl/cover	White
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	Polymethyl methacrylate bowl/cover	White
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	Polymethyl methacrylate bowl/cover	White

Order Code	Full Product Name	Optical cover type	Housing Color
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	Polymethyl methacrylate bowl/ cover	White
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	Polymethyl methacrylate bowl/ cover	White
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	Polymethyl methacrylate bowl/ cover	White
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	Polymethyl methacrylate bowl/ cover	White
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	Polymethyl methacrylate bowl/ cover	White
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	-	White
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	-	White
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	-	White
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	Polymethyl methacrylate bowl/ cover	White

Order Code	Full Product Name	Optical cover type	Housing Color
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	Polymethyl methacrylate bowl/ cover	White
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-	White
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-	White
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-	White
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-	White
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-	White
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-	White
910629167426	4MX850 491 LED80S/840 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629167526	4MX850 491 LED80S/840 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910500460518	4MX850 581 LED66S/830 PSD WB SI	-	Silver
910629120826	4MX850 491 LED55S/830 PSD NB SI	Polymethyl methacrylate bowl/ cover	Silver
910629120926	4MX850 491 LED55S/840 PSD NB SI	Polymethyl methacrylate bowl/ cover	Silver
910629121026	4MX850 491 LED55S/830 PSD WB SI	Polymethyl methacrylate bowl/ cover	Silver
910629121126	4MX850 491 LED55S/840 PSD WB SI	Polymethyl methacrylate bowl/ cover	Silver
910629121226	4MX850 581 LED55S/830 PSD NB SI	Polymethyl methacrylate bowl/ cover	Silver
910629121326	4MX850 581 LED55S/840 PSD NB SI	Polymethyl methacrylate bowl/ cover	Silver
910629121426	4MX850 581 LED55S/830 PSD WB SI	Polymethyl methacrylate bowl/ cover	Silver
910629121526	4MX850 581 LED55S/840 PSD WB SI	Polymethyl methacrylate bowl/ cover	Silver

Maxos LED

Order Code	Full Product Name	Optical cover type	Housing Color
910629122426	4MX850 491 LED40S/830 PSD NB SI	Polymethyl methacrylate bowl/ cover	Silver
910629122526	4MX850 491 LED40S/840 PSD NB SI	Polymethyl methacrylate bowl/ cover	Silver
910629122626	4MX850 491 LED40S/830 PSD WB SI	Polymethyl methacrylate bowl/ cover	Silver
910629122726	4MX850 491 LED40S/840 PSD WB SI	Polymethyl methacrylate bowl/ cover	Silver
910629122826	4MX850 581 LED40S/830 PSD NB SI	Polymethyl methacrylate bowl/ cover	Silver
910629122926	4MX850 581 LED40S/840 PSD NB SI	Polymethyl methacrylate bowl/ cover	Silver
910629123026	4MX850 581 LED40S/830 PSD WB SI	Polymethyl methacrylate bowl/ cover	Silver
910629123126	4MX850 581 LED40S/840 PSD WB SI	Polymethyl methacrylate bowl/ cover	Silver
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629160826	4MX850 491 LED55S/830 PSD A20 SI	Polymethyl methacrylate bowl/ cover	Silver

Order Code	Full Product Name	Optical cover type	Housing Color
910629160926	4MX850 491 LED55S/840 PSD A20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629161126	4MX850 491 LED40S/830 PSD A20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629161226	4MX850 491 LED40S/840 PSD A20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629162226	4MX850 491 LED66S/840 PSD A20 SI	Polymethyl methacrylate bowl/ cover	Silver
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	Polymethyl methacrylate bowl/ cover	Silver
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	Polymethyl methacrylate bowl/ cover	Silver
910500457964	4MX850 581 LED80S/840 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910500457965	4MX850 581 LED80S/840 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910500460003	4MX850 581 LED66S/840 PSD- CLO WB WH	Polymethyl methacrylate bowl/ cover	White
910500460004	4MX850 581 LED80S/840 PSD- CLO WB WH	Polymethyl methacrylate bowl/ cover	White
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460048	4MX850 581 LED80S/840 PSD VWB WH	Polymethyl methacrylate bowl/ cover	White
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White

Maxos LED

Order Code	Full Product Name	Optical cover type	Housing Color
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460226	4MX850 581 LED66S/840 PSD- CLO DA20 WH	Polymethyl methacrylate bowl/ cover	White
910500460227	4MX850 581 LED80S/840 PSD- CLO DA20 WH	Polymethyl methacrylate bowl/ cover	White
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	Polymethyl methacrylate bowl/ cover	White
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	Polymethyl methacrylate bowl/ cover	White
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	Polymethyl methacrylate bowl/ cover	White
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	Polymethyl methacrylate bowl/ cover	White
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	Polymethyl methacrylate bowl/ cover	White
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	Polymethyl methacrylate bowl/ cover	White
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	Polymethyl methacrylate bowl/ cover	White
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910500460476	4MX850 581 LED80S/830 PSD VWB WH	-	White

Order Code	Full Product Name	Optical cover type	Housing Color
910500460477	4MX850 581 LED80S/830 PSD WB WH	-	White
910500460483	4MX850 581 LED80S/840 PSD A20 WH	Polymethyl methacrylate bowl/ cover	White
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	-	White
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	-	White
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/ cover	White
910629120026	4MX850 491 LED55S/830 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629120126	4MX850 491 LED55S/840 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629120226	4MX850 491 LED55S/830 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629120326	4MX850 491 LED55S/840 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629120426	4MX850 581 LED55S/830 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629120526	4MX850 581 LED55S/840 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629120626	4MX850 581 LED55S/830 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629120726	4MX850 581 LED55S/840 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629121626	4MX850 491 LED40S/830 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629121726	4MX850 491 LED40S/840 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629121826	4MX850 491 LED40S/830 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629121926	4MX850 491 LED40S/840 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629122026	4MX850 581 LED40S/830 PSD NB WH	Polymethyl methacrylate bowl/ cover	White

Maxos LED

Order Code	Full Product Name	Optical cover type	Housing Color
910629122126	4MX850 581 LED40S/840 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629122226	4MX850 581 LED40S/830 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629122326	4MX850 581 LED40S/840 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629158126	4MX850 491 LED66S/840 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629158226	4MX850 491 LED66S/840 PSD NB WH	Polymethyl methacrylate bowl/ cover	White

Order Code	Full Product Name	Optical cover type	Housing Color
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	Polymethyl methacrylate bowl/ cover	White
910629160126	4MX850 491 LED66S/830 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629160226	4MX850 491 LED66S/830 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629160326	4MX850 581 LED66S/840 PSD WB WH	Polymethyl methacrylate bowl/ cover	White
910629160426	4MX850 581 LED66S/840 PSD NB WH	Polymethyl methacrylate bowl/ cover	White
910629160526	4MX850 491 LED40S/840 PSD A20 WH	Polymethyl methacrylate bowl/ cover	White
910629160626	4MX850 491 LED55S/840 PSD A20 WH	Polymethyl methacrylate bowl/ cover	White
910629160726	4MX850 491 LED55S/830 PSD A20 WH	Polymethyl methacrylate bowl/ cover	White
910629161026	4MX850 491 LED40S/830 PSD A20 WH	Polymethyl methacrylate bowl/ cover	White
910629162126	4MX850 491 LED66S/840 PSD A20 WH	Polymethyl methacrylate bowl/ cover	White
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	Polymethyl methacrylate bowl/ cover	White
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	Polymethyl methacrylate bowl/ cover	White
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	Polymethyl methacrylate bowl/ cover	White

Emergency Operation

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910500460502	4MX850 491 LED80S/840 PSD WB SI	-	-
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	-	-
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	-	-
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	-	-
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	-	-
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	-	-
910500460049	4MX850 491 LED80S/840 PSD VWB WH	-	-
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	-	-
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	-	-
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	-	-
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	-	-
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	-	-
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	-	-
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	-	-
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	-	-
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	-	-
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	-	-
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	-	-
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	-	-
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	-	-
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	-	-
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	-	-
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	-	-
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	-	-
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-	-
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-	-
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-	-
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-	-
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-	-
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-	-
910629167426	4MX850 491 LED80S/840 PSD NB WH	-	-
910629167526	4MX850 491 LED80S/840 PSD WB WH	-	-
910500460518	4MX850 581 LED66S/830 PSD WB SI	-	-
910629120826	4MX850 491 LED55S/830 PSD NB SI	-	-
910629120926	4MX850 491 LED55S/840 PSD NB SI	-	-
910629121026	4MX850 491 LED55S/830 PSD WB SI	-	-
910629121126	4MX850 491 LED55S/840 PSD WB SI	-	-
910629121226	4MX850 581 LED55S/830 PSD NB SI	-	-
910629121326	4MX850 581 LED55S/840 PSD NB SI	-	-
910629121426	4MX850 581 LED55S/830 PSD WB SI	-	-
910629121526	4MX850 581 LED55S/840 PSD WB SI	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910629122426	4MX850 491 LED40S/830 PSD NB SI	-	-
910629122526	4MX850 491 LED40S/840 PSD NB SI	-	-
910629122626	4MX850 491 LED40S/830 PSD WB SI	-	-
910629122726	4MX850 491 LED40S/840 PSD WB SI	-	-
910629122826	4MX850 581 LED40S/830 PSD NB SI	-	-
910629122926	4MX850 581 LED40S/840 PSD NB SI	-	-
910629123026	4MX850 581 LED40S/830 PSD WB SI	-	-
910629123126	4MX850 581 LED40S/840 PSD WB SI	-	-
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	-	-
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	-	-
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	-	-
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	-	-
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	-	-
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	-	-
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	-	-
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	-	-
910629160826	4MX850 491 LED55S/830 PSD A20 SI	-	-
910629160926	4MX850 491 LED55S/840 PSD A20 SI	-	-
910629161126	4MX850 491 LED40S/830 PSD A20 SI	-	-
910629161226	4MX850 491 LED40S/840 PSD A20 SI	-	-
910629162226	4MX850 491 LED66S/840 PSD A20 SI	-	-
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	-	-
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910500457964	4MX850 581 LED80S/840 PSD NB WH	-	-
910500457965	4MX850 581 LED80S/840 PSD WB WH	-	-
910500460003	4MX850 581 LED66S/840 PSD- CLO WB WH	-	-
910500460004	4MX850 581 LED80S/840 PSD- CLO WB WH	-	-
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	-	-
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	-	-
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	-	-
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	-	-
910500460048	4MX850 581 LED80S/840 PSD VWB WH	-	-
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	-	-
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	-	-
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	-	-
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	-	-
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	-	-
910500460226	4MX850 581 LED66S/840 PSD- CLO DA20 WH	-	-
910500460227	4MX850 581 LED80S/840 PSD- CLO DA20 WH	-	-
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	Emergency lighting 3 hours	3 hour(s)

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
		duration basic version	
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	-	-
910500460476	4MX850 581 LED80S/830 PSD VWB WH	-	-
910500460477	4MX850 581 LED80S/830 PSD WB WH	-	-
910500460483	4MX850 581 LED80S/840 PSD A20 WH	-	-
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	-	-
910629120026	4MX850 491 LED55S/830 PSD NB WH	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910629120126	4MX850 491 LED55S/840 PSD NB WH	-	-
910629120226	4MX850 491 LED55S/830 PSD WB WH	-	-
910629120326	4MX850 491 LED55S/840 PSD WB WH	-	-
910629120426	4MX850 581 LED55S/830 PSD NB WH	-	-
910629120526	4MX850 581 LED55S/840 PSD NB WH	-	-
910629120626	4MX850 581 LED55S/830 PSD WB WH	-	-
910629120726	4MX850 581 LED55S/840 PSD WB WH	-	-
910629121626	4MX850 491 LED40S/830 PSD NB WH	-	-
910629121726	4MX850 491 LED40S/840 PSD NB WH	-	-
910629121826	4MX850 491 LED40S/830 PSD WB WH	-	-
910629121926	4MX850 491 LED40S/840 PSD WB WH	-	-
910629122026	4MX850 581 LED40S/830 PSD NB WH	-	-
910629122126	4MX850 581 LED40S/840 PSD NB WH	-	-
910629122226	4MX850 581 LED40S/830 PSD WB WH	-	-
910629122326	4MX850 581 LED40S/840 PSD WB WH	-	-
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	-	-
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	-	-
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	-	-
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	-	-
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	-	-
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	-	-
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	-	-
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	-	-
910629158126	4MX850 491 LED66S/840 PSD WB WH	-	-
910629158226	4MX850 491 LED66S/840 PSD NB WH	-	-
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	-	-
910629160126	4MX850 491 LED66S/830 PSD WB WH	-	-
910629160226	4MX850 491 LED66S/830 PSD NB WH	-	-
910629160326	4MX850 581 LED66S/840 PSD WB WH	-	-
910629160426	4MX850 581 LED66S/840 PSD NB WH	-	-
910629160526	4MX850 491 LED40S/840 PSD A20 WH	-	-
910629160626	4MX850 491 LED55S/840 PSD A20 WH	-	-
910629160726	4MX850 491 LED55S/830 PSD A20 WH	-	-
910629161026	4MX850 491 LED40S/830 PSD A20 WH	-	-
910629162126	4MX850 491 LED66S/840 PSD A20 WH	-	-
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	Emergency lighting 3 hours duration basic version	3 hour(s)
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	-	-
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	-	-
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	-	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500460502	4MX850 491 LED80S/840 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460049	4MX850 491 LED80S/840 PSD VWB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	-20 to +35 °C	Temperature 850 °C, duration 30 s
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	0 to +35 °C	Temperature 650 °C, duration 30 s
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629167426	4MX850 491 LED80S/840 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629167526	4MX850 491 LED80S/840 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460518	4MX850 581 LED66S/830 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120826	4MX850 491 LED55S/830 PSD NB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120926	4MX850 491 LED55S/840 PSD NB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629121026	4MX850 491 LED55S/830 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629121126	4MX850 491 LED55S/840 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629121226	4MX850 581 LED55S/830 PSD NB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629121326	4MX850 581 LED55S/840 PSD NB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629121426	4MX850 581 LED55S/830 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629121526	4MX850 581 LED55S/840 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629122426	4MX850 491 LED40S/830 PSD NB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629122526	4MX850 491 LED40S/840 PSD NB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629122626	4MX850 491 LED40S/830 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629122726	4MX850 491 LED40S/840 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629122826	4MX850 581 LED40S/830 PSD NB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629122926	4MX850 581 LED40S/840 PSD NB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629123026	4MX850 581 LED40S/830 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629123126	4MX850 581 LED40S/840 PSD WB SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629160826	4MX850 491 LED55S/830 PSD A20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629160926	4MX850 491 LED55S/840 PSD A20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629161126	4MX850 491 LED40S/830 PSD A20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629161226	4MX850 491 LED40S/840 PSD A20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629162226	4MX850 491 LED66S/840 PSD A20 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500457964	4MX850 581 LED80S/840 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500457965	4MX850 581 LED80S/840 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460048	4MX850 581 LED80S/840 PSD VWB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460476	4MX850 581 LED80S/830 PSD VWB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460477	4MX850 581 LED80S/830 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460483	4MX850 581 LED80S/840 PSD A20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	-20 to +35 °C	Temperature 650 °C, duration 30 s
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120026	4MX850 491 LED55S/830 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120126	4MX850 491 LED55S/840 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120226	4MX850 491 LED55S/830 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120326	4MX850 491 LED55S/840 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120426	4MX850 581 LED55S/830 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120526	4MX850 581 LED55S/840 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120626	4MX850 581 LED55S/830 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629120726	4MX850 581 LED55S/840 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629121626	4MX850 491 LED40S/830 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629121726	4MX850 491 LED40S/840 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629121826	4MX850 491 LED40S/830 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629121926	4MX850 491 LED40S/840 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629122026	4MX850 581 LED40S/830 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629122126	4MX850 581 LED40S/840 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629122226	4MX850 581 LED40S/830 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629122326	4MX850 581 LED40S/840 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629158126	4MX850 491 LED66S/840 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629158226	4MX850 491 LED66S/840 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629160126	4MX850 491 LED66S/830 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629160226	4MX850 491 LED66S/830 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629160326	4MX850 581 LED66S/840 PSD WB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629160426	4MX850 581 LED66S/840 PSD NB WH	-20 to +35 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629160526	4MX850 491 LED40S/840 PSD A20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629160626	4MX850 491 LED55S/840 PSD A20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629160726	4MX850 491 LED55S/830 PSD A20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629161026	4MX850 491 LED40S/830 PSD A20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629162126	4MX850 491 LED66S/840 PSD A20 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	-20 to +35 °C	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910500460502	4MX850 491 LED80S/840 PSD WB SI	(0.38, 0.38) SDCM <3.5	+/-10%
910500460013	4MX850 491 LED66S/840 PSD- CLO WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460014	4MX850 491 LED80S/840 PSD- CLO WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460016	4MX850 491 LED66S/840 PSD- CLO NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460017	4MX850 491 LED80S/840 PSD- CLO NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460023	4MX850 491 LED80S/840 PSD- CLO DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460049	4MX850 491 LED80S/840 PSD VWB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	(0.38, 0.38) SDCM <3.5	-10% / +10%
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	(0.38, 0.38) SDCM <3.5	-10% / +10%
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	(0.38, 0.38) SDCM <3.5	-10% / +10%
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	(0.38, 0.38) SDCM <3.5	-10% / +10%
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	(0.38, 0.38) SDCM <3.5	-10% / +10%
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	(0.38, 0.38) SDCM <3.5	-10% / +10%
910629167426	4MX850 491 LED80S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629167526	4MX850 491 LED80S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460518	4MX850 581 LED66S/830 PSD WB SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629120826	4MX850 491 LED55S/830 PSD NB SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629120926	4MX850 491 LED55S/840 PSD NB SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629121026	4MX850 491 LED55S/830 PSD WB SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629121126	4MX850 491 LED55S/840 PSD WB SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629121226	4MX850 581 LED55S/830 PSD NB SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629121326	4MX850 581 LED55S/840 PSD NB SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629121426	4MX850 581 LED55S/830 PSD WB SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629121526	4MX850 581 LED55S/840 PSD WB SI	(0.38, 0.38) SDCM <3.5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910629122426	4MX850 491 LED40S/830 PSD NB SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629122526	4MX850 491 LED40S/840 PSD NB SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629122626	4MX850 491 LED40S/830 PSD WB SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629122726	4MX850 491 LED40S/840 PSD WB SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629122826	4MX850 581 LED40S/830 PSD NB SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629122926	4MX850 581 LED40S/840 PSD NB SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629123026	4MX850 581 LED40S/830 PSD WB SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629123126	4MX850 581 LED40S/840 PSD WB SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629160826	4MX850 491 LED55S/830 PSD A20 SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629160926	4MX850 491 LED55S/840 PSD A20 SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629161126	4MX850 491 LED40S/830 PSD A20 SI	(0.43, 0.40) SDCM <3.5	+/-10%
910629161226	4MX850 491 LED40S/840 PSD A20 SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629162226	4MX850 491 LED66S/840 PSD A20 SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	(0.38, 0.38) SDCM <3.5	+/-10%
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	(0.38, 0.38) SDCM <3.5	+/-10%
910500457964	4MX850 581 LED80S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500457965	4MX850 581 LED80S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910500460003	4MX850 581 LED66S/840 PSD- CLO WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460004	4MX850 581 LED80S/840 PSD- CLO WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460048	4MX850 581 LED80S/840 PSD VWB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460226	4MX850 581 LED66S/840 PSD- CLO DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460227	4MX850 581 LED80S/840 PSD- CLO DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910500460476	4MX850 581 LED80S/830 PSD VWB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460477	4MX850 581 LED80S/830 PSD WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460483	4MX850 581 LED80S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	(0.38, 0.38) SDCM <3.5	+/-10%
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910629120026	4MX850 491 LED55S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629120126	4MX850 491 LED55S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629120226	4MX850 491 LED55S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629120326	4MX850 491 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629120426	4MX850 581 LED55S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629120526	4MX850 581 LED55S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629120626	4MX850 581 LED55S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629120726	4MX850 581 LED55S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629121626	4MX850 491 LED40S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629121726	4MX850 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629121826	4MX850 491 LED40S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629121926	4MX850 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629122026	4MX850 581 LED40S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629122126	4MX850 581 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629122226	4MX850 581 LED40S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629122326	4MX850 581 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629158126	4MX850 491 LED66S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629158226	4MX850 491 LED66S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629160126	4MX850 491 LED66S/830 PSD WB WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629160226	4MX850 491 LED66S/830 PSD NB WH	(0.43, 0.40) SDCM <3.5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910629160326	4MX850 581 LED66S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629160426	4MX850 581 LED66S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629160526	4MX850 491 LED40S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629160626	4MX850 491 LED55S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629160726	4MX850 491 LED55S/830 PSD A20 WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629161026	4MX850 491 LED40S/830 PSD A20 WH	(0.43, 0.40) SDCM <3.5	+/-10%
910629162126	4MX850 491 LED66S/840 PSD A20 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5	+/-10%
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	(0.38, 0.38) SDCM <3.5	+/-10%
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	(0.38, 0.38) SDCM <3.5	+/-10%

Product Data

Order Code	Full Product Name	Product family code
910500460502	4MX850 491 LED80S/840 PSD WB SI	4MX850
910500460013	4MX850 491 LED66S/840 PSD-CLO WB WH	4MX850
910500460014	4MX850 491 LED80S/840 PSD-CLO WB WH	4MX850
910500460016	4MX850 491 LED66S/840 PSD-CLO NB WH	4MX850
910500460017	4MX850 491 LED80S/840 PSD-CLO NB WH	4MX850
910500460023	4MX850 491 LED80S/840 PSD-CLO DA20 WH	4MX850
910500460049	4MX850 491 LED80S/840 PSD VWB WH	4MX850
910500460075	4MX850 491 LED80S/840 PSD VWB WH C-2R	4MX850
910500460215	4MX850 491 LED80S/840 PSD DA20 WH	4MX850
910500460216	4MX850 491 LED66S/840 PSD DA20 WH C-2R	4MX850
910500460217	4MX850 491 LED66S/840 PSD NB WH C-2R	4MX850
910500460218	4MX850 491 LED66S/840 PSD WB WH C-2R	4MX850
910500460219	4MX850 491 LED80S/840 PSD DA20 WH C-2R	4MX850
910500460220	4MX850 491 LED80S/840 PSD NB WH C-2R	4MX850
910500460221	4MX850 491 LED80S/840 PSD WB WH C-2R	4MX850
910500460257	4MX883 491 LED55S/840 PSD DA20 WH ELB3	4MX883
910500460258	4MX883 491 LED55S/840 PSD NB WH ELB3	4MX883
910500460259	4MX883 491 LED55S/840 PSD WB WH ELB3	4MX883
910500460263	4MX883 491 LED66S/840 PSD DA20 WH ELB3	4MX883
910500460264	4MX883 491 LED66S/840 PSD NB WH ELB3	4MX883
910500460265	4MX883 491 LED66S/840 PSD WB WH ELB3	4MX883
910500460266	4MX883 491 LED55S/840 PSD DA20 WHELBC-2R	4MX883
910500460267	4MX883 491 LED55S/840 PSD NB WH ELB3C-2R	4MX883

Order Code	Full Product Name	Product family code
910500460268	4MX883 491 LED55S/840 PSD WB WH ELB3C-2R	4MX883
910500460269	4MX883 491 LED66S/840 PSD DA20 WHELBC-2R	4MX883
910500460270	4MX883 491 LED66S/840 PSD NB WH ELB3C-2R	4MX883
910500460271	4MX883 491 LED66S/840 PSD WB WH ELB3C-2R	4MX883
910500460391	4MX850 491 LED55S/840 PSD WB WH C-2R	4MX850
910500460415	4MX850 491 LED66S/840 PSD VWB WH C-2R	4MX850
910500460420	4MX850 491 LED40S/840 PSD WB WH C-2R	4MX850
910500460487	4MX883 491 LED66S/840 PSD WB WH ELP3	4MX883
910500460491	4MX883 491 LED66S/840 PSD WB WH ELD3	4MX883
910500460531	4MX850 491 LED40S/830 PSD WB WH C-2R	4MX850
910500460537	4MX850 491 LED40S/840 PSD NB WH C-2R	4MX850
910500460538	4MX850 491 LED55S/840 PSD NB WH C-2R	4MX850
910500460560	4MX850 491 LED40S/840 PSD A20 WH C-2R	4MX850
910500460561	4MX850 491 LED66S/840 PSD A20 WH C-2R	4MX850
910500460562	4MX850 491 LED80S/840 PSD A20 WH C-2R	4MX850
910505105684	4MX850 491 LED40S/840 DIA NB WH C-2R	4MX850
910505105685	4MX850 491 LED40S/840 DIA WB WH C-2R	4MX850
910505105686	4MX850 491 LED66S/840 DIA NB WH C-2R	4MX850
910505105687	4MX850 491 LED66S/840 DIA WB WH C-2R	4MX850
910505105688	4MX850 491 LED80S/840 DIA NB WH C-2R	4MX850
910505105689	4MX850 491 LED80S/840 DIA WB WH C-2R	4MX850
910629167426	4MX850 491 LED80S/840 PSD NB WH	4MX850
910629167526	4MX850 491 LED80S/840 PSD WB WH	4MX850




Order Code	Full Product Name	Product family code
910500460518	4MX850 581 LED66S/830 PSD WB SI	4MX850
910629120826	4MX850 491 LED55S/830 PSD NB SI	4MX850
910629120926	4MX850 491 LED55S/840 PSD NB SI	4MX850
910629121026	4MX850 491 LED55S/830 PSD WB SI	4MX850
910629121126	4MX850 491 LED55S/840 PSD WB SI	4MX850
910629121226	4MX850 581 LED55S/830 PSD NB SI	4MX850
910629121326	4MX850 581 LED55S/840 PSD NB SI	4MX850
910629121426	4MX850 581 LED55S/830 PSD WB SI	4MX850
910629121526	4MX850 581 LED55S/840 PSD WB SI	4MX850
910629122426	4MX850 491 LED40S/830 PSD NB SI	4MX850
910629122526	4MX850 491 LED40S/840 PSD NB SI	4MX850
910629122626	4MX850 491 LED40S/830 PSD WB SI	4MX850
910629122726	4MX850 491 LED40S/840 PSD WB SI	4MX850
910629122826	4MX850 581 LED40S/830 PSD NB SI	4MX850
910629122926	4MX850 581 LED40S/840 PSD NB SI	4MX850
910629123026	4MX850 581 LED40S/830 PSD WB SI	4MX850
910629123126	4MX850 581 LED40S/840 PSD WB SI	4MX850
910629125226	4MX850 491 LED55S/830 PSD DA20 SI	4MX850
910629125326	4MX850 491 LED55S/840 PSD DA20 SI	4MX850
910629125426	4MX850 581 LED55S/830 PSD DA20 SI	4MX850
910629125526	4MX850 581 LED55S/840 PSD DA20 SI	4MX850
910629126026	4MX850 491 LED40S/830 PSD DA20 SI	4MX850
910629126126	4MX850 491 LED40S/840 PSD DA20 SI	4MX850
910629126226	4MX850 581 LED40S/830 PSD DA20 SI	4MX850
910629126326	4MX850 581 LED40S/840 PSD DA20 SI	4MX850
910629160826	4MX850 491 LED55S/830 PSD A20 SI	4MX850
910629160926	4MX850 491 LED55S/840 PSD A20 SI	4MX850
910629161126	4MX850 491 LED40S/830 PSD A20 SI	4MX850
910629161226	4MX850 491 LED40S/840 PSD A20 SI	4MX850
910629162226	4MX850 491 LED66S/840 PSD A20 SI	4MX850
910629165626	4MX850 491 LED55S/840 PSD DA35 SI	4MX850
910629165726	4MX850 581 LED55S/840 PSD DA35 SI	4MX850
910500457964	4MX850 581 LED80S/840 PSD NB WH	4MX850
910500457965	4MX850 581 LED80S/840 PSD WB WH	4MX850
910500460003	4MX850 581 LED66S/840 PSD-CLO WB WH	4MX850
910500460004	4MX850 581 LED80S/840 PSD-CLO WB WH	4MX850
910500460007	4MX850 581 LED80S/840 PSD NB WH C-2R	4MX850
910500460008	4MX850 581 LED80S/840 PSD WB WH C-2R	4MX850
910500460009	4MX850 581 LED66S/840 PSD NB WH C-2R	4MX850
910500460010	4MX850 581 LED66S/840 PSD WB WH C-2R	4MX850
910500460048	4MX850 581 LED80S/840 PSD VWB WH	4MX850
910500460070	4MX850 581 LED40S/840 PSD WB WH C-2R	4MX850
910500460222	4MX850 581 LED66S/840 PSD DA20 WH	4MX850
910500460223	4MX850 581 LED80S/840 PSD DA20 WH	4MX850
910500460224	4MX850 581 LED66S/840 PSD DA20 WH C-2R	4MX850
910500460225	4MX850 581 LED80S/840 PSD DA20 WH C-2R	4MX850
910500460226	4MX850 581 LED66S/840 PSD-CLO DA20 WH	4MX850
910500460227	4MX850 581 LED80S/840 PSD-CLO DA20 WH	4MX850
910500460273	4MX883 581 LED55S/840 PSD DA20 WH ELB3	4MX883
910500460274	4MX883 581 LED55S/840 PSD NB WH ELB3	4MX883
910500460275	4MX883 581 LED55S/840 PSD WB WH ELB3	4MX883

Order Code	Full Product Name	Product family code
910500460279	4MX883 581 LED66S/840 PSD DA20 WH ELB3	4MX883
910500460280	4MX883 581 LED66S/840 PSD WB WH ELB3	4MX883
910500460281	4MX883 581 LED55S/840 PSD DA20 WHELBC-2R	4MX883
910500460282	4MX883 581 LED55S/840 PSD NB WH ELB3C-2R	4MX883
910500460283	4MX883 581 LED55S/840 PSD WB WH ELB3C-2R	4MX883
910500460284	4MX883 581 LED66S/840 PSD DA20 WHELBC-2R	4MX883
910500460285	4MX883 581 LED66S/840 PSD NB WH ELB3C-2R	4MX883
910500460393	4MX850 581 LED55S/840 PSD NB WH C-2R	4MX850
910500460476	4MX850 581 LED80S/830 PSD VWB WH	4MX850
910500460477	4MX850 581 LED80S/830 PSD WB WH	4MX850
910500460483	4MX850 581 LED80S/840 PSD A20 WH	4MX850
910500460488	4MX883 581 LED66S/840 PSD WB WH ELP3	4MX883
910500460492	4MX883 581 LED66S/840 PSD WB WH ELD3	4MX883
910500460595	4MX850 581 LED55S/840 PSD WB WH C-2R	4MX850
910629120026	4MX850 491 LED55S/830 PSD NB WH	4MX850
910629120126	4MX850 491 LED55S/840 PSD NB WH	4MX850
910629120226	4MX850 491 LED55S/830 PSD WB WH	4MX850
910629120326	4MX850 491 LED55S/840 PSD WB WH	4MX850
910629120426	4MX850 581 LED55S/830 PSD NB WH	4MX850
910629120526	4MX850 581 LED55S/840 PSD NB WH	4MX850
910629120626	4MX850 581 LED55S/830 PSD WB WH	4MX850
910629120726	4MX850 581 LED55S/840 PSD WB WH	4MX850
910629121626	4MX850 491 LED40S/830 PSD NB WH	4MX850
910629121726	4MX850 491 LED40S/840 PSD NB WH	4MX850
910629121826	4MX850 491 LED40S/830 PSD WB WH	4MX850
910629121926	4MX850 491 LED40S/840 PSD WB WH	4MX850
910629122026	4MX850 581 LED40S/830 PSD NB WH	4MX850
910629122126	4MX850 581 LED40S/840 PSD NB WH	4MX850
910629122226	4MX850 581 LED40S/830 PSD WB WH	4MX850
910629122326	4MX850 581 LED40S/840 PSD WB WH	4MX850
910629124826	4MX850 491 LED55S/830 PSD DA20 WH	4MX850
910629124926	4MX850 491 LED55S/840 PSD DA20 WH	4MX850
910629125026	4MX850 581 LED55S/830 PSD DA20 WH	4MX850
910629125126	4MX850 581 LED55S/840 PSD DA20 WH	4MX850
910629125626	4MX850 491 LED40S/830 PSD DA20 WH	4MX850
910629125726	4MX850 491 LED40S/840 PSD DA20 WH	4MX850
910629125826	4MX850 581 LED40S/830 PSD DA20 WH	4MX850
910629125926	4MX850 581 LED40S/840 PSD DA20 WH	4MX850
910629158026	4MX850 491 LED66S/840 PSD DA20 WH	4MX850
910629158126	4MX850 491 LED66S/840 PSD WB WH	4MX850
910629158226	4MX850 491 LED66S/840 PSD NB WH	4MX850
910629160026	4MX850 491 LED66S/830 PSD DA20 WH	4MX850
910629160126	4MX850 491 LED66S/830 PSD WB WH	4MX850
910629160226	4MX850 491 LED66S/830 PSD NB WH	4MX850
910629160326	4MX850 581 LED66S/840 PSD WB WH	4MX850
910629160426	4MX850 581 LED66S/840 PSD NB WH	4MX850
910629160526	4MX850 491 LED40S/840 PSD A20 WH	4MX850
910629160626	4MX850 491 LED55S/840 PSD A20 WH	4MX850
910629160726	4MX850 491 LED55S/830 PSD A20 WH	4MX850
910629161026	4MX850 491 LED40S/830 PSD A20 WH	4MX850
910629162126	4MX850 491 LED66S/840 PSD A20 WH	4MX850

Order Code	Full Product Name	Product family code
910629165226	4MX883 581 LED66S/840 PSD WB WH ELB3C-2R	4MX883
910629165926	4MX850 491 LED55S/840 PSD DA35 WH	4MX850

Order Code	Full Product Name	Product family code
910629166026	4MX850 491 LED66S/840 PSD DA35 WH	4MX850
910629166126	4MX850 581 LED55S/840 PSD DA35 WH	4MX850




Polar Wide Diagrams



Polar Normal (separate) - 4MX850I - 910500457964

Polar Normal (separate) - 4MX850I - 910500457965




Polar Normal (separate) - 4MX850I - 910500460070



Polar Normal (separate) - 4MX850I - 910500460477

Polar Normal (separate) - 4MX850I - 910500460007

Polar Normal (separate) - 4MX850I - 910500460420




Polar Normal (separate) - 4MX850I - 910500460502


Polar Normal (separate) - 4MX850I - 910500460220

Polar Normal (separate) - 4MX850I - 910629123126


Polar Wide Diagrams




Polar Normal (separate) - 4MX850I - 910629125126




Polar Normal (separate) - 4MX850I - 910629125926




Polar Normal (separate) - 4MX850I - 910629126126




Polar Normal (separate) - 4MX850I - 910629121126




**Polar Normal (separate) - 4MX850I -
910629167526**




Polar Normal (separate) - 4MX850I - 910629121926



Polar Normal (separate) - 4MX850I - 910629120926




Polar Normal (separate) - 4MX850I - 910629158226




Polar Normal (separate) - 4MX850I - 910629121526


Polar Wide Diagrams




Polar Normal (separate) - 4MX850I - 910629167426




Polar Normal (separate) - 4MX850I - 910629160626




Polar Normal (separate) - 4MX850I - 910629162126




Polar Normal (separate) - 4MX850I - 910629121726




Polar Normal (separate) - 4MX850I - 910629125326




Polar Normal (separate) - 4MX850I - 910629160926



Polar Normal (separate) - 4MX850I - 910629160326




Polar Normal (separate) - 4MX850I - 910629122126




Polar Normal (separate) - 4MX850I - 910629122726


Polar Wide Diagrams




Polar Normal (separate) - 4MX850I - 910629161226




Polar Normal (separate) - 4MX850I - 910629122926




Polar Normal (separate) - 4MX850I - 910629125526




Polar Normal (separate) - 4MX850I - 910629120526




Polar Normal (separate) - 4MX850I - 910629122326




Polar Normal (separate) - 4MX850I - 910629122526



Polar Normal (separate) - 4MX850I - 910629120126




Polar Normal (separate) - 4MX850I - 910629121326




Polar Normal (separate) - 4MX850I - 910629126326


Polar Wide Diagrams




Polar Normal (separate) - 4MX850I - 910629120726




Polar Normal (separate) - 4MX850I - 910629120326




Polar Normal (separate) - 4MX850I - 910629124926




Polar Normal (separate) - 4MX850I - 910629125726




Polar Normal (separate) - 4MX850I - 910629158026




Polar Normal (separate) - 4MX850I - 910629160426



Polar Normal (separate) - 4MX850I - 910629160526




Polar Normal (separate) - 4MX850I - 910629162226




Polar Normal (separate) - 4MX850I - 910500460537


Polar Wide Diagrams




Polar Normal (separate) - 4MX850I - 910500460538




Polar Normal (separate) - 4MX850I - 910500460560




Polar Normal (separate) - 4MX850I - 910500460562




Polar Normal (separate) - 4MX850I - 910500460561




Polar Normal (separate) - 4MX850I - 910500460595




Polar Normal (separate) - 4MX850I - 910500460009



Polar Normal (separate) - 4MX850I - 910500460008




Polar Normal (separate) - 4MX850I - 910500460010




Polar Normal (separate) - 4MX850I - 910500460049


Polar Wide Diagrams




Polar Normal (separate) - 4MX850I - 910500460048




Polar Normal (separate) - 4MX850I - 910500460075




Polar Normal (separate) - 4MX850I - 910500460216




Polar Normal (separate) - 4MX850I - 910500460215




Polar Normal (separate) - 4MX850I - 910500460218




Polar Normal (separate) - 4MX850I - 910500460221



Polar Normal (separate) - 4MX850I - 910500460222




Polar Normal (separate) - 4MX850I - 910500460217




Polar Normal (separate) - 4MX850I - 910500460223


Polar Wide Diagrams




Polar Normal (separate) - 4MX850I - 910500460391




Polar Normal (separate) - 4MX850I - 910500460415




Polar Normal (separate) - 4MX850I - 910500460393




Polar Normal (separate) - 4MX850I - 910500460476




Polar Normal (separate) - 4MX850I - 910500460483




Polar Normal (separate) - 4MX850I - 910500460518



Polar Normal (separate) - 4MX850I - 910500460224




Polar Normal (separate) - 4MX850I - 910500460225




Polar Normal (separate) - 4MX850I - 910500460219


Polar Wide Diagrams




Polar Normal (separate) - 4MX850I - 910505105689




Polar Normal (separate) - 4MX850I - 910505105684




Polar Normal (separate) - 4MX850I - 910505105688



Polar Normal (separate) - 4MX850I - 910505105686



Polar Normal (separate) - 4MX850I - 910505105687



Polar Normal (separate) - 4MX850I - 910505105685

