



Maxos LED Performer – efficient and precise line lighting

Maxos LED Performer

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Benefits

- Extremely fast payback
- Breakthrough optical system for precise beam shaping
- Flexible in terms of retrofits, spots, changes, accessories

Features


- Low energy consumption compared to fluorescent
- Excellent beam shaping for less spill light and exact light distribution in horizontal and vertical planes
- Proven Philips LED engines (Fortimo)
- Can be mounted, new or retrofit, onto a Maxos rail

Application

- Supermarkets
- Warehouses
- Production facilities

Maxos LED Performer

Dimensional drawing




Product details

IPDP_4MX900i_0001-Detail
photo



IPDP_4MX900i_0003-Detail
photo



IPDP_4MX900i_0007-Detail
photo



IPDP_4MX900i_0011-Detail
photo



Maxos LED Performer

Product details



IPDP_4MX900i_0013-Detail
photo

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class I
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Mechanical and Housing	
Mech. impact protection code	IK02
Ingress protection code	IP40
Approval and Application	
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	50S
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	50S
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	50S
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	50S
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	50S
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	50S
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	75S
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	75S
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	75S
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	75S
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	75S
910500460309	4MX900 581 LED40S/840 PSD MB WH	40S
910500460310	4MX900 581 LED40S/840 PSD NB WH	40S
910500460311	4MX900 581 LED40S/840 PSD WB WH	40S
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	50S
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	50S
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	50S
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	50S
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	75S
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	75S
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	75S
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	75S
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	50S
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	50S
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	50S
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	50S
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	50S
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	50S
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	75S
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	75S
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	75S
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	50S
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	50S
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	50S
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	50S
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	50S
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	75S

Order Code	Full Product Name	Lamp family code
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	75S
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	75S
910629173126	4MX900 581 LED50S/840 PSD MB WH	LED50S
910629177026	4MX900 581 LED50S/840 PSD WB WH	LED50S
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	75S
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	50S
910629132426	4MX900 LED40S/840 PSD WB WH L1200	LED40S
910629132526	4MX900 LED40S/840 PSD MB WH L1200	LED40S
910629132626	4MX900 LED40S/840 PSD NB WH L1200	LED40S
910629137226	4MX900 LED60S/840 PSD WB WH L1800	LED60S
910629137326	4MX900 LED60S/840 PSD MB WH L1800	LED60S
910629137426	4MX900 LED60S/840 PSD NB WH L1800	LED60S
910629138826	4MX900 LED90S/840 PSD WB WH L1800	LED90S
910629138926	4MX900 LED90S/840 PSD MB WH L1800	LED90S
910629139026	4MX900 LED90S/840 PSD NB WH L1800	LED90S
910629140426	4MX900 581 LED40S/840 PSU WB WH	LED40S
910629140526	4MX900 581 LED40S/840 PSU MB WH	LED40S
910629142026	4MX900 491 LED40S/840 PSU WB WH	LED40S
910629142126	4MX900 491 LED40S/840 PSU MB WH	LED40S
910629143226	4MX900 LED40S/840 PSU WB WH L1200	LED40S
910629144426	4MX900 491 LED40S/840 PSD WB WH	LED40S
910629144526	4MX900 491 LED40S/840 PSD MB WH	LED40S
910629144626	4MX900 491 LED40S/840 PSD NB WH	LED40S
910629144826	4MX900 491 LED50S/840 PSD WB WH	LED50S
910629144926	4MX900 491 LED50S/840 PSD MB WH	LED50S
910629145026	4MX900 491 LED50S/840 PSD NB WH	LED50S
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	LED40S
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	LED60S
910629145626	4MX900 581 LED40S/840 PSU A30 WH	LED40S
910629145726	4MX900 581 LED50S/840 PSU A30 WH	LED50S
910629145826	4MX900 491 LED40S/840 PSU A30 WH	LED40S
910629145926	4MX900 491 LED50S/840 PSU A30 WH	LED50S
910629146026	4MX900 581 LED50S/840 PSU WB WH	LED50S
910629146126	4MX900 581 LED50S/840 PSU MB WH	LED50S
910629146426	4MX900 491 LED50S/840 PSU WB WH	LED50S
910629146526	4MX900 491 LED50S/840 PSU MB WH	LED50S
910629146626	4MX900 491 LED50S/840 PSU NB WH	LED50S
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	LED90S
910629148326	4MX900 581 LED75S/840 PSU A30 WH	LED75S
910629148526	4MX900 491 LED75S/840 PSU A30 WH	LED75S
910629170326	4MX900 491 LED75S/840 PSU WB WH	LED75S
910629170426	4MX900 491 LED75S/840 PSU MB WH	LED75S
910629170826	4MX900 581 LED75S/840 PSU WB WH	LED75S
910629170926	4MX900 581 LED75S/840 PSU MB WH	LED75S
910629171026	4MX900 581 LED75S/840 PSU NB WH	LED75S
910629171326	4MX900 491 LED75S/840 PSD WB WH	LED75S
910629171426	4MX900 491 LED75S/840 PSD MB WH	LED75S
910629171526	4MX900 491 LED75S/840 PSD NB WH	LED75S
910629171826	4MX900 491 LED75S/840 PSD A30 WH	LED75S
910629171926	4MX900 581 LED75S/840 PSD WB WH	LED75S
910629172026	4MX900 581 LED75S/840 PSD MB WH	LED75S
910629172126	4MX900 581 LED75S/840 PSD NB WH	LED75S

Maxos LED Performer

Order Code	Full Product Name	Lamp family code
910629172426	4MX900 581 LED75S/840 PSD A30 WH	LED75S
910629173226	4MX900 581 LED50S/840 PSD A30 WH	LED50S
910629131626	4MX900 LED40S/840 PSD WB SI L1200	LED40S
910629136426	4MX900 LED60S/840 PSD WB SI L1800	LED60S
910629138026	4MX900 LED90S/840 PSD WB SI L1800	LED90S
910629138126	4MX900 LED90S/840 PSD MB SI L1800	LED90S
910629141226	4MX900 491 LED40S/840 PSU WB SI	LED40S
910629141326	4MX900 491 LED40S/840 PSU MB SI	LED40S
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	LED90S
910629172926	4MX900 LED40S/840 PSU WB SI L1200	LED40S
910629177526	4MX900 581 LED50S/840 PSU A30 SI	LED50S

Light Technical (1/2)

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	155 lm/W	5,000 lm	-	Wide beam
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	155 lm/W	5,000 lm	-	Medium beam
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	155 lm/W	5,000 lm	-	Narrow beam
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	155 lm/W	5,000 lm	-	Medium beam
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	155 lm/W	5,000 lm	-	Narrow beam
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	155 lm/W	5,000 lm	-	Wide beam
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	149 lm/W	7,500 lm	-	Narrow beam
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	149 lm/W	7,500 lm	-	Wide beam
910500460305	4MX900 491 LED75S/840	149 lm/W	7,500 lm	-	Medium beam

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
	PSD MB WH C-2R				
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	149 lm/W	7,500 lm	-	Narrow beam
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	149 lm/W	7,500 lm	-	Wide beam
910500460309	4MX900 581 LED40S/840 PSD MB WH	159 lm/W	4,000 lm	-	Medium beam
910500460310	4MX900 581 LED40S/840 PSD NB WH	159 lm/W	4,000 lm	-	Narrow beam
910500460311	4MX900 581 LED40S/840 PSD WB WH	159 lm/W	4,000 lm	-	Wide beam
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	155 lm/W	5,000 lm	-	Medium beam
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	155 lm/W	5,000 lm	-	Narrow beam
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	155 lm/W	5,000 lm	-	Medium beam
910500460318	4MX900 581 LED50S/840	155 lm/W	5,000 lm	-	Narrow beam

Maxos LED Performer

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
	PSD NB WH C-2R				
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	149 lm/W	7,500 lm	-	Narrow beam
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	149 lm/W	7,500 lm	-	Medium beam
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	149 lm/W	7,500 lm	-	Narrow beam
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	149 lm/W	7,500 lm	-	Wide beam
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	155 lm/W	5,000 lm	-	Medium beam
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	155 lm/W	5,000 lm	-	Narrow beam
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	155 lm/W	5,000 lm	-	Wide beam
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	155 lm/W	5,000 lm	-	Medium beam
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	155 lm/W	5,000 lm	-	Narrow beam
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	155 lm/W	5,000 lm	-	Wide beam
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	149 lm/W	7,500 lm	-	Medium beam
910500460372	4MX933 491 LED75S/840	149 lm/W	7,500 lm	-	Narrow beam

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
	PSD NB WH ELB3C-2R				
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	149 lm/W	7,500 lm	-	Wide beam
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	155 lm/W	5,000 lm	-	Medium beam
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	155 lm/W	5,000 lm	-	Wide beam
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	155 lm/W	5,000 lm	-	Medium beam
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	155 lm/W	5,000 lm	-	Narrow beam
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	155 lm/W	5,000 lm	-	Wide beam
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	149 lm/W	7,500 lm	-	Medium beam
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	149 lm/W	7,500 lm	-	Narrow beam
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	149 lm/W	7,500 lm	-	Wide beam
910629173126	4MX900 581 LED50S/840 PSD MB WH	155 lm/W	5,000 lm	-	Medium beam
910629177026	4MX900 581 LED50S/840 PSD WB WH	155 lm/W	5,000 lm	-	Wide beam
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	149 lm/W	7,500 lm	1	Medium beam

Maxos LED Performer

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	155 lm/W	5,000 lm	-	Narrow beam
910629132426	4MX900 LED40S/840 PSD WB WH L1200	154 lm/W	4,000 lm	1	Wide beam
910629132526	4MX900 LED40S/840 PSD MB WH L1200	154 lm/W	4,000 lm	1	Medium beam
910629132626	4MX900 LED40S/840 PSD NB WH L1200	154 lm/W	4,000 lm	1	Narrow beam
910629137226	4MX900 LED60S/840 PSD WB WH L1800	161 lm/W	6,000 lm	1	Wide beam
910629137326	4MX900 LED60S/840 PSD MB WH L1800	161 lm/W	6,000 lm	1	Medium beam
910629137426	4MX900 LED60S/840 PSD NB WH L1800	161 lm/W	6,000 lm	1	Narrow beam
910629138826	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9,000 lm	1	Wide beam
910629138926	4MX900 LED90S/840 PSD MB WH L1800	150 lm/W	9,000 lm	1	Medium beam
910629139026	4MX900 LED90S/840 PSD NB WH L1800	150 lm/W	9,000 lm	1	Narrow beam
910629140426	4MX900 581 LED40S/840 PSU WB WH	159 lm/W	4,000 lm	1	Wide beam
910629140526	4MX900 581 LED40S/840 PSU MB WH	159 lm/W	4,000 lm	1	Medium beam
910629142026	4MX900 491 LED40S/840 PSU WB WH	159 lm/W	4,000 lm	1	Wide beam

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910629142126	4MX900 491 LED40S/840 PSU MB WH	159 lm/W	4,000 lm	1	Medium beam
910629143226	4MX900 LED40S/840 PSU WB WH L1200	154 lm/W	4,000 lm	1	Wide beam
910629144426	4MX900 491 LED40S/840 PSD WB WH	159 lm/W	4,000 lm	1	Wide beam
910629144526	4MX900 491 LED40S/840 PSD MB WH	159 lm/W	4,000 lm	1	Medium beam
910629144626	4MX900 491 LED40S/840 PSD NB WH	159 lm/W	4,000 lm	1	Narrow beam
910629144826	4MX900 491 LED50S/840 PSD WB WH	155 lm/W	5,000 lm	1	Wide beam
910629144926	4MX900 491 LED50S/840 PSD MB WH	155 lm/W	5,000 lm	1	Medium beam
910629145026	4MX900 491 LED50S/840 PSD NB WH	155 lm/W	5,000 lm	1	Narrow beam
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	154 lm/W	4,000 lm	1	Asymmetrical mirror axis angle 30°
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	161 lm/W	6,000 lm	1	Asymmetrical mirror axis angle 30°
910629145626	4MX900 581 LED40S/840 PSU A30 WH	159 lm/W	4,000 lm	1	Asymmetrical mirror axis angle 30°
910629145726	4MX900 581 LED50S/840 PSU A30 WH	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°
910629145826	4MX900 491 LED40S/840 PSU A30 WH	159 lm/W	4,000 lm	1	Asymmetrical mirror axis angle 30°
910629145926	4MX900 491 LED50S/840 PSU A30 WH	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°
910629146026	4MX900 581 LED50S/840 PSU WB WH	155 lm/W	5,000 lm	1	Wide beam

Maxos LED Performer

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910629146126	4MX900 581 LED50S/840 PSU MB WH	155 lm/W	5,000 lm	1	Medium beam
910629146426	4MX900 491 LED50S/840 PSU WB WH	155 lm/W	5,000 lm	1	Wide beam
910629146526	4MX900 491 LED50S/840 PSU MB WH	155 lm/W	5,000 lm	1	Medium beam
910629146626	4MX900 491 LED50S/840 PSU NB WH	155 lm/W	5,000 lm	1	Narrow beam
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	150 lm/W	9,000 lm	1	Asymmetrical mirror axis angle 30°
910629148326	4MX900 581 LED75S/840 PSU A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°
910629148526	4MX900 491 LED75S/840 PSU A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°
910629170326	4MX900 491 LED75S/840 PSU WB WH	149 lm/W	7,500 lm	1	Wide beam
910629170426	4MX900 491 LED75S/840 PSU MB WH	149 lm/W	7,500 lm	1	Medium beam
910629170826	4MX900 581 LED75S/840 PSU WB WH	149 lm/W	7,500 lm	1	Wide beam
910629170926	4MX900 581 LED75S/840 PSU MB WH	149 lm/W	7,500 lm	1	Medium beam
910629171026	4MX900 581 LED75S/840 PSU NB WH	149 lm/W	7,500 lm	1	Narrow beam
910629171326	4MX900 491 LED75S/840 PSD WB WH	149 lm/W	7,500 lm	1	Wide beam
910629171426	4MX900 491 LED75S/840 PSD MB WH	149 lm/W	7,500 lm	1	Medium beam
910629171526	4MX900 491 LED75S/840 PSD NB WH	149 lm/W	7,500 lm	1	Narrow beam
910629171826	4MX900 491 LED75S/840 PSD A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
910629171926	4MX900 581 LED75S/840 PSD WB WH	149 lm/W	7,500 lm	1	Wide beam
910629172026	4MX900 581 LED75S/840 PSD MB WH	149 lm/W	7,500 lm	1	Medium beam
910629172126	4MX900 581 LED75S/840 PSD NB WH	149 lm/W	7,500 lm	1	Narrow beam
910629172426	4MX900 581 LED75S/840 PSD A30 WH	149 lm/W	7,500 lm	1	Asymmetrical mirror axis angle 30°
910629173226	4MX900 581 LED50S/840 PSD A30 WH	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°
910629131626	4MX900 LED40S/840 PSD WB SI L1200	154 lm/W	4,000 lm	1	Wide beam
910629136426	4MX900 LED60S/840 PSD WB SI L1800	161 lm/W	6,000 lm	1	Wide beam
910629138026	4MX900 LED90S/840 PSD WB SI L1800	150 lm/W	9,000 lm	1	Wide beam
910629138126	4MX900 LED90S/840 PSD MB SI L1800	150 lm/W	9,000 lm	1	Medium beam
910629141226	4MX900 491 LED40S/840 PSU WB SI	159 lm/W	4,000 lm	1	Wide beam
910629141326	4MX900 491 LED40S/840 PSU MB SI	159 lm/W	4,000 lm	1	Medium beam
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	150 lm/W	9,000 lm	1	Asymmetrical mirror axis angle 30°
910629172926	4MX900 LED40S/840 PSU WB SI L1200	154 lm/W	4,000 lm	1	Wide beam
910629177526	4MX900 581 LED50S/840 PSU A30 SI	155 lm/W	5,000 lm	1	Asymmetrical mirror axis angle 30°

Light Technical (2/2)

Order Code	Full Product Name	Upward light output ratio
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	0
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	0
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	0
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	0
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	0
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	0
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	0
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	0
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	0
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	0
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	0
910500460309	4MX900 581 LED40S/840 PSD MB WH	0
910500460310	4MX900 581 LED40S/840 PSD NB WH	0
910500460311	4MX900 581 LED40S/840 PSD WB WH	0
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	0
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	0
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	0
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	0
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	0
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	0
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	0
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	0
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	0
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	0
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	0
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	0
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	0
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	0
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	0
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	0
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	0
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	0
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	0
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	0
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	0
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	0
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	0
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	0
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	0
910629173126	4MX900 581 LED50S/840 PSD MB WH	-
910629177026	4MX900 581 LED50S/840 PSD WB WH	-
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	0
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	0
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-
910629132526	4MX900 LED40S/840 PSD MB WH L1200	-
910629132626	4MX900 LED40S/840 PSD NB WH L1200	-
910629137226	4MX900 LED60S/840 PSD WB WH L1800	-
910629137326	4MX900 LED60S/840 PSD MB WH L1800	-
910629137426	4MX900 LED60S/840 PSD NB WH L1800	-
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-

Order Code	Full Product Name	Upward light output ratio
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-
910629139026	4MX900 LED90S/840 PSD NB WH L1800	-
910629140426	4MX900 581 LED40S/840 PSU WB WH	-
910629140526	4MX900 581 LED40S/840 PSU MB WH	-
910629142026	4MX900 491 LED40S/840 PSU WB WH	-
910629142126	4MX900 491 LED40S/840 PSU MB WH	-
910629143226	4MX900 LED40S/840 PSU WB WH L1200	-
910629144426	4MX900 491 LED40S/840 PSD WB WH	-
910629144526	4MX900 491 LED40S/840 PSD MB WH	-
910629144626	4MX900 491 LED40S/840 PSD NB WH	-
910629144826	4MX900 491 LED50S/840 PSD WB WH	-
910629144926	4MX900 491 LED50S/840 PSD MB WH	-
910629145026	4MX900 491 LED50S/840 PSD NB WH	-
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	-
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-
910629145626	4MX900 581 LED40S/840 PSU A30 WH	-
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-
910629146026	4MX900 581 LED50S/840 PSU WB WH	-
910629146126	4MX900 581 LED50S/840 PSU MB WH	-
910629146426	4MX900 491 LED50S/840 PSU WB WH	-
910629146526	4MX900 491 LED50S/840 PSU MB WH	-
910629146626	4MX900 491 LED50S/840 PSU NB WH	-
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-
910629148326	4MX900 581 LED75S/840 PSU A30 WH	-
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-
910629170326	4MX900 491 LED75S/840 PSU WB WH	-
910629170426	4MX900 491 LED75S/840 PSU MB WH	-
910629170826	4MX900 581 LED75S/840 PSU WB WH	-
910629170926	4MX900 581 LED75S/840 PSU MB WH	-
910629171026	4MX900 581 LED75S/840 PSU NB WH	-
910629171326	4MX900 491 LED75S/840 PSD WB WH	-
910629171426	4MX900 491 LED75S/840 PSD MB WH	-
910629171526	4MX900 491 LED75S/840 PSD NB WH	-
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-
910629171926	4MX900 581 LED75S/840 PSD WB WH	-
910629172026	4MX900 581 LED75S/840 PSD MB WH	-
910629172126	4MX900 581 LED75S/840 PSD NB WH	-
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-
910629173226	4MX900 581 LED50S/840 PSD A30 WH	-
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-
910629138126	4MX900 LED90S/840 PSD MB SI L1800	-
910629141226	4MX900 491 LED40S/840 PSU WB SI	-
910629141326	4MX900 491 LED40S/840 PSU MB SI	-
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-
910629172926	4MX900 LED40S/840 PSU WB SI L1200	-
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-

Maxos LED Performer

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power
			Consumption
910500458678	4MX900 491 LED50S/840 PSD- CLO WB WH	220 to 240 V	32.2 W
910500460294	4MX900 491 LED50S/840 PSD- CLO MB WH	220 to 240 V	25.16 W
910500460295	4MX900 491 LED50S/840 PSD- CLO NB WH	220 to 240 V	25.16 W
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	220 to 240 V	32.2 W
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	220 to 240 V	32.2 W
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	220 to 240 V	32.2 W
910500460302	4MX900 491 LED75S/840 PSD- CLO NB WH	220 to 240 V	40.16 W
910500460303	4MX900 491 LED75S/840 PSD- CLO WB WH	220 to 240 V	40.16 W
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	220 to 240 V	50.2 W
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	220 to 240 V	50.2 W
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	220 to 240 V	50.2 W
910500460309	4MX900 581 LED40S/840 PSD MB WH	220 to 240 V	25.2 W
910500460310	4MX900 581 LED40S/840 PSD NB WH	220 to 240 V	25.2 W
910500460311	4MX900 581 LED40S/840 PSD WB WH	220 to 240 V	25.2 W
910500460314	4MX900 581 LED50S/840 PSD- CLO MB WH	220 to 240 V	25.16 W
910500460315	4MX900 581 LED50S/840 PSD- CLO NB WH	220 to 240 V	25.16 W
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	220 to 240 V	32.2 W
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	220 to 240 V	32.2 W
910500460321	4MX900 581 LED75S/840 PSD- CLO NB WH	220 to 240 V	40.16 W
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	220 to 240 V	50.2 W
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	220 to 240 V	50.2 W
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	220 to 240 V	50.2 W
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	220 to 240 V	32.2 W
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	220 to 240 V	32.2 W
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	220 to 240 V	32.2 W

Order Code	Full Product Name	Input Voltage	Power
			Consumption
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	220 to 240 V	32.2 W
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	220 to 240 V	32.2 W
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	220 to 240 V	32.2 W
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	220 to 240 V	50.2 W
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	220 to 240 V	50.2 W
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	220 to 240 V	50.2 W
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	220 to 240 V	32.2 W
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	220 to 240 V	32.2 W
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	220 to 240 V	32.2 W
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	220 to 240 V	32.2 W
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	220 to 240 V	32.2 W
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	220 to 240 V	50.2 W
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	220 to 240 V	50.2 W
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	220 to 240 V	50.2 W
910629173126	4MX900 581 LED50S/840 PSD MB WH	220 to 240 V	32.2 W
910629177026	4MX900 581 LED50S/840 PSD WB WH	220-240 V	32.2 W
910500458125	4MX900 581 LED75S/840 PSD- CLO MB WH	220 to 240 V	50.2 W
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	220 to 240 V	32.2 W
910629132426	4MX900 LED40S/840 PSD WB WH L1200	220 to 240 V	25.9 W
910629132526	4MX900 LED40S/840 PSD MB WH L1200	220 to 240 V	25.9 W
910629132626	4MX900 LED40S/840 PSD NB WH L1200	220 to 240 V	25.9 W
910629137226	4MX900 LED60S/840 PSD WB WH L1800	220 to 240 V	37.3 W
910629137326	4MX900 LED60S/840 PSD MB WH L1800	220 to 240 V	37.3 W
910629137426	4MX900 LED60S/840 PSD NB WH L1800	220 to 240 V	37.3 W
910629138826	4MX900 LED90S/840 PSD WB WH L1800	220 to 240 V	60.1 W

Maxos LED Performer

Order Code	Full Product Name	Input Voltage	Power
			Consumption
910629138926	4MX900 LED90S/840 PSD MB WH L1800	220 to 240 V	60.1 W
910629139026	4MX900 LED90S/840 PSD NB WH L1800	220 to 240 V	60.1 W
910629140426	4MX900 581 LED40S/840 PSU WB WH	220 to 240 V	25.2 W
910629140526	4MX900 581 LED40S/840 PSU MB WH	220 to 240 V	25.2 W
910629142026	4MX900 491 LED40S/840 PSU WB WH	220 to 240 V	25.2 W
910629142126	4MX900 491 LED40S/840 PSU MB WH	220 to 240 V	25.2 W
910629143226	4MX900 LED40S/840 PSU WB WH L1200	220 to 240 V	25.9 W
910629144426	4MX900 491 LED40S/840 PSD WB WH	220 to 240 V	25.2 W
910629144526	4MX900 491 LED40S/840 PSD MB WH	220 to 240 V	25.2 W
910629144626	4MX900 491 LED40S/840 PSD NB WH	220 to 240 V	25.2 W
910629144826	4MX900 491 LED50S/840 PSD WB WH	220 to 240 V	32.2 W
910629144926	4MX900 491 LED50S/840 PSD MB WH	220 to 240 V	32.2 W
910629145026	4MX900 491 LED50S/840 PSD NB WH	220 to 240 V	32.2 W
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	220 to 240 V	25.9 W
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	220 to 240 V	37.3 W
910629145626	4MX900 581 LED40S/840 PSU A30 WH	220 to 240 V	25.2 W
910629145726	4MX900 581 LED50S/840 PSU A30 WH	220 to 240 V	32.2 W
910629145826	4MX900 491 LED40S/840 PSU A30 WH	220 to 240 V	25.2 W
910629145926	4MX900 491 LED50S/840 PSU A30 WH	220 to 240 V	32.2 W
910629146026	4MX900 581 LED50S/840 PSU WB WH	220 to 240 V	32.2 W
910629146126	4MX900 581 LED50S/840 PSU MB WH	220 to 240 V	32.2 W
910629146426	4MX900 491 LED50S/840 PSU WB WH	220 to 240 V	32.2 W
910629146526	4MX900 491 LED50S/840 PSU MB WH	220 to 240 V	32.2 W
910629146626	4MX900 491 LED50S/840 PSU NB WH	220 to 240 V	32.2 W
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	220 to 240 V	60.1 W

Order Code	Full Product Name	Input Voltage	Power
			Consumption
910629148326	4MX900 581 LED75S/840 PSU A30 WH	220 to 240 V	50.2 W
910629148526	4MX900 491 LED75S/840 PSU A30 WH	220 to 240 V	50.2 W
910629170326	4MX900 491 LED75S/840 PSU WB WH	220 to 240 V	50.2 W
910629170426	4MX900 491 LED75S/840 PSU MB WH	220 to 240 V	50.2 W
910629170826	4MX900 581 LED75S/840 PSU WB WH	220 to 240 V	50.2 W
910629170926	4MX900 581 LED75S/840 PSU MB WH	220 to 240 V	50.2 W
910629171026	4MX900 581 LED75S/840 PSU NB WH	220 to 240 V	50.2 W
910629171326	4MX900 491 LED75S/840 PSD WB WH	220 to 240 V	50.2 W
910629171426	4MX900 491 LED75S/840 PSD MB WH	220 to 240 V	50.2 W
910629171526	4MX900 491 LED75S/840 PSD NB WH	220 to 240 V	50.2 W
910629171826	4MX900 491 LED75S/840 PSD A30 WH	220 to 240 V	50.2 W
910629171926	4MX900 581 LED75S/840 PSD WB WH	220 to 240 V	50.2 W
910629172026	4MX900 581 LED75S/840 PSD MB WH	220 to 240 V	50.2 W
910629172126	4MX900 581 LED75S/840 PSD NB WH	220 to 240 V	50.2 W
910629172426	4MX900 581 LED75S/840 PSD A30 WH	220 to 240 V	50.2 W
910629173226	4MX900 581 LED50S/840 PSD A30 WH	220 to 240 V	32.2 W
910629131626	4MX900 LED40S/840 PSD WB SI L1200	220 to 240 V	25.9 W
910629136426	4MX900 LED60S/840 PSD WB SI L1800	220 to 240 V	37.3 W
910629138026	4MX900 LED90S/840 PSD WB SI L1800	220 to 240 V	60.1 W
910629138126	4MX900 LED90S/840 PSD MB SI L1800	220 to 240 V	60.1 W
910629141226	4MX900 491 LED40S/840 PSU WB SI	220 to 240 V	25.2 W
910629141326	4MX900 491 LED40S/840 PSU MB SI	220 to 240 V	25.2 W
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	220 to 240 V	60.1 W
910629172926	4MX900 LED40S/840 PSU WB SI L1200	220 to 240 V	25.9 W
910629177526	4MX900 581 LED50S/840 PSU A30 SI	220 to 240 V	32.2 W

Controls and Dimming

Maxos LED Performer

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	Yes	Constant light output	1%
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	Yes	Constant light output	1%
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	Yes	Constant light output	1%
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	Yes	-	1%
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	Yes	-	1%
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	Yes	-	1%
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	Yes	Constant light output	1%
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	Yes	Constant light output	1%
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	Yes	-	1%
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	Yes	-	1%
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	Yes	-	1%
910500460309	4MX900 581 LED40S/840 PSD MB WH	Yes	-	1%
910500460310	4MX900 581 LED40S/840 PSD NB WH	Yes	-	1%
910500460311	4MX900 581 LED40S/840 PSD WB WH	Yes	-	1%
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	Yes	Constant light output	1%
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	Yes	Constant light output	1%
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	Yes	-	1%
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	Yes	-	1%
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	Yes	Constant light output	1%
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	Yes	-	1%
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	Yes	-	1%
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	Yes	-	1%
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	No	-	Not applicable
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	No	-	Not applicable
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	No	-	Not applicable

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	Yes	-	1%
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	Yes	-	1%
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	Yes	-	1%
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	Yes	-	1%
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	Yes	-	1%
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	Yes	-	1%
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	No	-	Not applicable
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	No	-	Not applicable
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	Yes	-	1%
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	Yes	-	1%
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	Yes	-	1%
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	Yes	-	1%
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	Yes	-	1%
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	Yes	-	1%
910629173126	4MX900 581 LED50S/840 PSD MB WH	Yes	-	1%
910629177026	4MX900 581 LED50S/840 PSD WB WH	Yes	-	1%
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	Yes	Constant light output	1%
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	No	-	Not applicable
910629132426	4MX900 LED40S/840 PSD WB WH L1200	Yes	-	1%
910629132526	4MX900 LED40S/840 PSD MB WH L1200	Yes	-	1%
910629132626	4MX900 LED40S/840 PSD NB WH L1200	Yes	-	1%
910629137226	4MX900 LED60S/840 PSD WB WH L1800	Yes	-	1%
910629137326	4MX900 LED60S/840 PSD MB WH L1800	Yes	-	1%
910629137426	4MX900 LED60S/840 PSD NB WH L1800	Yes	-	1%
910629138826	4MX900 LED90S/840 PSD WB WH L1800	Yes	-	1%

Maxos LED Performer

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910629138926	4MX900 LED90S/840 PSD MB WH L1800	Yes	-	1%
910629139026	4MX900 LED90S/840 PSD NB WH L1800	Yes	-	1%
910629140426	4MX900 581 LED40S/840 PSU WB WH	No	-	Not applicable
910629140526	4MX900 581 LED40S/840 PSU MB WH	No	-	Not applicable
910629142026	4MX900 491 LED40S/840 PSU WB WH	No	-	Not applicable
910629142126	4MX900 491 LED40S/840 PSU MB WH	No	-	Not applicable
910629143226	4MX900 LED40S/840 PSU WB WH L1200	No	-	Not applicable
910629144426	4MX900 491 LED40S/840 PSD WB WH	Yes	-	1%
910629144526	4MX900 491 LED40S/840 PSD MB WH	Yes	-	1%
910629144626	4MX900 491 LED40S/840 PSD NB WH	Yes	-	1%
910629144826	4MX900 491 LED50S/840 PSD WB WH	Yes	-	1%
910629144926	4MX900 491 LED50S/840 PSD MB WH	Yes	-	1%
910629145026	4MX900 491 LED50S/840 PSD NB WH	Yes	-	1%
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	Yes	-	1%
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	Yes	-	1%
910629145626	4MX900 581 LED40S/840 PSU A30 WH	No	-	Not applicable
910629145726	4MX900 581 LED50S/840 PSU A30 WH	No	-	Not applicable
910629145826	4MX900 491 LED40S/840 PSU A30 WH	No	-	Not applicable
910629145926	4MX900 491 LED50S/840 PSU A30 WH	No	-	Not applicable
910629146026	4MX900 581 LED50S/840 PSU WB WH	No	-	Not applicable
910629146126	4MX900 581 LED50S/840 PSU MB WH	No	-	Not applicable
910629146426	4MX900 491 LED50S/840 PSU WB WH	No	-	Not applicable
910629146526	4MX900 491 LED50S/840 PSU MB WH	No	-	Not applicable
910629146626	4MX900 491 LED50S/840 PSU NB WH	No	-	Not applicable
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	Yes	-	1%

Order Code	Full Product Name	Dimmable	Embedded control	Maximum dim level
910629148326	4MX900 581 LED75S/840 PSU A30 WH	No	-	Not applicable
910629148526	4MX900 491 LED75S/840 PSU A30 WH	No	-	Not applicable
910629170326	4MX900 491 LED75S/840 PSU WB WH	No	-	Not applicable
910629170426	4MX900 491 LED75S/840 PSU MB WH	No	-	Not applicable
910629170826	4MX900 581 LED75S/840 PSU WB WH	No	-	Not applicable
910629170926	4MX900 581 LED75S/840 PSU MB WH	No	-	Not applicable
910629171026	4MX900 581 LED75S/840 PSU NB WH	No	-	Not applicable
910629171326	4MX900 491 LED75S/840 PSD WB WH	Yes	-	1%
910629171426	4MX900 491 LED75S/840 PSD MB WH	Yes	-	1%
910629171526	4MX900 491 LED75S/840 PSD NB WH	Yes	-	1%
910629171826	4MX900 491 LED75S/840 PSD A30 WH	Yes	-	1%
910629171926	4MX900 581 LED75S/840 PSD WB WH	Yes	-	1%
910629172026	4MX900 581 LED75S/840 PSD MB WH	Yes	-	1%
910629172126	4MX900 581 LED75S/840 PSD NB WH	Yes	-	1%
910629172426	4MX900 581 LED75S/840 PSD A30 WH	Yes	-	1%
910629173226	4MX900 581 LED50S/840 PSD A30 WH	Yes	-	1%
910629131626	4MX900 LED40S/840 PSD WB SI L1200	Yes	-	1%
910629136426	4MX900 LED60S/840 PSD WB SI L1800	Yes	-	1%
910629138026	4MX900 LED90S/840 PSD WB SI L1800	Yes	-	1%
910629138126	4MX900 LED90S/840 PSD MB SI L1800	Yes	-	1%
910629141226	4MX900 491 LED40S/840 PSU WB SI	No	-	Not applicable
910629141326	4MX900 491 LED40S/840 PSU MB SI	No	-	Not applicable
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	Yes	-	1%
910629172926	4MX900 LED40S/840 PSU WB SI L1200	No	-	Not applicable
910629177526	4MX900 581 LED50S/840 PSU A30 SI	No	-	Not applicable

Mechanical and Housing

Maxos LED Performer

Order Code	Full Product Name	Optical cover type	Housing	
			Color	
910500458678	4MX900 491 LED50S/840 PSD- CLO WB WH	Polymethyl methacrylate bowl/ cover	White	
910500460294	4MX900 491 LED50S/840 PSD- CLO MB WH	Polymethyl methacrylate bowl/ cover	White	
910500460295	4MX900 491 LED50S/840 PSD- CLO NB WH	Polymethyl methacrylate bowl/ cover	White	
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460302	4MX900 491 LED75S/840 PSD- CLO NB WH	Polymethyl methacrylate bowl/ cover	White	
910500460303	4MX900 491 LED75S/840 PSD- CLO WB WH	Polymethyl methacrylate bowl/ cover	White	
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460309	4MX900 581 LED40S/840 PSD MB WH	Polymethyl methacrylate bowl/ cover	White	
910500460310	4MX900 581 LED40S/840 PSD NB WH	Polymethyl methacrylate bowl/ cover	White	
910500460311	4MX900 581 LED40S/840 PSD WB WH	Polymethyl methacrylate bowl/ cover	White	
910500460314	4MX900 581 LED50S/840 PSD- CLO MB WH	Polymethyl methacrylate bowl/ cover	White	
910500460315	4MX900 581 LED50S/840 PSD- CLO NB WH	Polymethyl methacrylate bowl/ cover	White	
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	Polymethyl methacrylate bowl/ cover	White	

Order Code	Full Product Name	Optical cover type	Housing	
			Color	
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460321	4MX900 581 LED75S/840 PSD- CLO NB WH	Polymethyl methacrylate bowl/ cover	White	
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	Polymethyl methacrylate bowl/ cover	White	
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	Polymethyl methacrylate bowl/ cover	White	
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	Polymethyl methacrylate bowl/ cover	White	
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	Polymethyl methacrylate bowl/ cover	White	
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	Polymethyl methacrylate bowl/ cover	White	
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	

Maxos LED Performer

Order Code	Full Product Name	Optical cover type	Housing	
			Color	
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	Polymethyl methacrylate bowl/ cover	White	
910629173126	4MX900 581 LED50S/840 PSD MB WH	-	White	
910629177026	4MX900 581 LED50S/840 PSD WB WH	-	White	
910500458125	4MX900 581 LED75S/840 PSD- CLO MB WH	Polymethyl methacrylate bowl/ cover	White	
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	Polymethyl methacrylate bowl/ cover	White	
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-	White	
910629132526	4MX900 LED40S/840 PSD MB WH L1200	-	White	
910629132626	4MX900 LED40S/840 PSD NB WH L1200	-	White	
910629137226	4MX900 LED60S/840 PSD WB WH L1800	-	White	
910629137326	4MX900 LED60S/840 PSD MB WH L1800	-	White	
910629137426	4MX900 LED60S/840 PSD NB WH L1800	-	White	
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-	White	
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-	White	
910629139026	4MX900 LED90S/840 PSD NB WH L1800	-	White	
910629140426	4MX900 581 LED40S/840 PSU WB WH	-	White	
910629140526	4MX900 581 LED40S/840 PSU MB WH	-	White	
910629142026	4MX900 491 LED40S/840 PSU WB WH	-	White	
910629142126	4MX900 491 LED40S/840 PSU MB WH	-	White	

Order Code	Full Product Name	Optical cover type	Housing	
			Color	
910629143226	4MX900 LED40S/840 PSU WB WH L1200	-	White	
910629144426	4MX900 491 LED40S/840 PSD WB WH	-	White	
910629144526	4MX900 491 LED40S/840 PSD MB WH	-	White	
910629144626	4MX900 491 LED40S/840 PSD NB WH	-	White	
910629144826	4MX900 491 LED50S/840 PSD WB WH	-	White	
910629144926	4MX900 491 LED50S/840 PSD MB WH	-	White	
910629145026	4MX900 491 LED50S/840 PSD NB WH	-	White	
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	-	White	
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-	White	
910629145626	4MX900 581 LED40S/840 PSU A30 WH	-	White	
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-	White	
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-	White	
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-	White	
910629146026	4MX900 581 LED50S/840 PSU WB WH	-	White	
910629146126	4MX900 581 LED50S/840 PSU MB WH	-	White	
910629146426	4MX900 491 LED50S/840 PSU WB WH	-	White	
910629146526	4MX900 491 LED50S/840 PSU MB WH	-	White	
910629146626	4MX900 491 LED50S/840 PSU NB WH	-	White	
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-	White	
910629148326	4MX900 581 LED75S/840 PSU A30 WH	-	White	
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-	White	
910629170326	4MX900 491 LED75S/840 PSU WB WH	-	White	
910629170426	4MX900 491 LED75S/840 PSU MB WH	-	White	
910629170826	4MX900 581 LED75S/840 PSU WB WH	-	White	
910629170926	4MX900 581 LED75S/840 PSU MB WH	-	White	

Maxos LED Performer

Order Code	Full Product Name	Optical cover type	Housing Color
910629171026	4MX900 581 LED75S/840 PSU NB WH	-	White
910629171326	4MX900 491 LED75S/840 PSD WB WH	-	White
910629171426	4MX900 491 LED75S/840 PSD MB WH	-	White
910629171526	4MX900 491 LED75S/840 PSD NB WH	-	White
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-	White
910629171926	4MX900 581 LED75S/840 PSD WB WH	-	White
910629172026	4MX900 581 LED75S/840 PSD MB WH	-	White
910629172126	4MX900 581 LED75S/840 PSD NB WH	-	White
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-	White
910629173226	4MX900 581 LED50S/840 PSD A30 WH	-	White

Order Code	Full Product Name	Optical cover type	Housing Color
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-	Silver
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-	Silver
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-	Silver
910629138126	4MX900 LED90S/840 PSD MB SI L1800	-	Silver
910629141226	4MX900 491 LED40S/840 PSU WB SI	-	Silver
910629141326	4MX900 491 LED40S/840 PSU MB SI	-	Silver
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-	Silver
910629172926	4MX900 LED40S/840 PSU WB SI L1200	-	Silver
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-	Silver

Emergency Operation (1/2)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	No	-	-	-
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	No	-	-	-
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	No	-	-	-
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	No	-	-	-
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	No	-	-	-
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	No	-	-	-
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	No	-	-	-
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	No	-	-	-
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	No	-	-	-
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	No	-	-	-
910500460309	4MX900 581 LED40S/840 PSD MB WH	No	-	-	-

Maxos LED Performer

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910500460310	4MX900 581 LED40S/840 PSD NB WH	No	-	-	-
910500460311	4MX900 581 LED40S/840 PSD WB WH	No	-	-	-
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	No	-	-	-
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	No	-	-	-
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	No	-	-	-
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	No	-	-	-
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	No	-	-	-
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	No	-	-	-
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	No	-	-	-
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	No	-	-	-
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	No	Emergency lighting 3 hours	360 lm	Lithium

Maxos LED Performer

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
			duration basic version		
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910629173126	4MX900 581 LED50S/840 PSD MB WH	-	-	-	-
910629177026	4MX900 581 LED50S/840 PSD WB WH	-	-	-	-
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	No	-	-	-
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	No	Emergency lighting 3 hours duration basic version	360 lm	Lithium
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-	-	-	-
910629132526	4MX900 LED40S/840	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
	PSD MB WH L1200				
910629132626	4MX900 LED40S/840 PSD NB WH L1200	-	-	-	-
910629137226	4MX900 LED60S/840 PSD WB WH L1800	-	-	-	-
910629137326	4MX900 LED60S/840 PSD MB WH L1800	-	-	-	-
910629137426	4MX900 LED60S/840 PSD NB WH L1800	-	-	-	-
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-	-	-	-
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-	-	-	-
910629139026	4MX900 LED90S/840 PSD NB WH L1800	-	-	-	-
910629140426	4MX900 581 LED40S/840 PSU WB WH	-	-	-	-
910629140526	4MX900 581 LED40S/840 PSU MB WH	-	-	-	-
910629142026	4MX900 491 LED40S/840 PSU WB WH	-	-	-	-
910629142126	4MX900 491 LED40S/840 PSU MB WH	-	-	-	-
910629143226	4MX900 LED40S/840 PSU WB WH L1200	-	-	-	-
910629144426	4MX900 491 LED40S/840 PSD WB WH	-	-	-	-

Maxos LED Performer

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910629144526	4MX900 491 LED40S/840 PSD MB WH	-	-	-	-
910629144626	4MX900 491 LED40S/840 PSD NB WH	-	-	-	-
910629144826	4MX900 491 LED50S/840 PSD WB WH	-	-	-	-
910629144926	4MX900 491 LED50S/840 PSD MB WH	-	-	-	-
910629145026	4MX900 491 LED50S/840 PSD NB WH	-	-	-	-
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	-	-	-	-
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-	-	-	-
910629145626	4MX900 581 LED40S/840 PSU A30 WH	-	-	-	-
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-	-	-	-
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-	-	-	-
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-	-	-	-
910629146026	4MX900 581 LED50S/840 PSU WB WH	-	-	-	-
910629146126	4MX900 581 LED50S/840 PSU MB WH	-	-	-	-
910629146426	4MX900 491 LED50S/840 PSU WB WH	-	-	-	-
910629146526	4MX900 491 LED50S/840 PSU MB WH	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910629146626	4MX900 491 LED50S/840 PSU NB WH	-	-	-	-
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-	-	-	-
910629148326	4MX900 581 LED75S/840 PSU A30 WH	-	-	-	-
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-	-	-	-
910629170326	4MX900 491 LED75S/840 PSU WB WH	-	-	-	-
910629170426	4MX900 491 LED75S/840 PSU MB WH	-	-	-	-
910629170826	4MX900 581 LED75S/840 PSU WB WH	-	-	-	-
910629170926	4MX900 581 LED75S/840 PSU MB WH	-	-	-	-
910629171026	4MX900 581 LED75S/840 PSU NB WH	-	-	-	-
910629171326	4MX900 491 LED75S/840 PSD WB WH	-	-	-	-
910629171426	4MX900 491 LED75S/840 PSD MB WH	-	-	-	-
910629171526	4MX900 491 LED75S/840 PSD NB WH	-	-	-	-
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-	-	-	-
910629171926	4MX900 581 LED75S/840 PSD WB WH	-	-	-	-
910629172026	4MX900 581 LED75S/840 PSD MB WH	-	-	-	-
910629172126	4MX900 581 LED75S/840 PSD NB WH	-	-	-	-

Maxos LED Performer

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-	-	-	-
910629173226	4MX900 581 LED50S/840 PSD A30 WH	-	-	-	-
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-	-	-	-
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-	-	-	-
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-	-	-	-
910629138126	4MX900 LED90S/840	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Type of emergency lighting battery
	PSD MB SI L1800				
910629141226	4MX900 491 LED40S/840 PSU WB SI	-	-	-	-
910629141326	4MX900 491 LED40S/840 PSU MB SI	-	-	-	-
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-	-	-	-
910629172926	4MX900 LED40S/840 PSU WB SI L1200	-	-	-	-
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-	-	-	-

Emergency Operation (2/2)

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	-	-
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	-	-
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	-	-
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	-	-
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	-	-
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	-	-
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	-	-
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	-	-
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	-	-
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	-	-

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	-	-
910500460309	4MX900 581 LED40S/840 PSD MB WH	-	-
910500460310	4MX900 581 LED40S/840 PSD NB WH	-	-
910500460311	4MX900 581 LED40S/840 PSD WB WH	-	-
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	-	-
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	-	-
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	-	-
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	-	-
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	-	-
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	-	-

Maxos LED Performer

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	-	-
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	-	-
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	3.4 W	3 hour(s)
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	3.4 W	3 hour(s)
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	3.4 W	3 hour(s)
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	3.4 W	3 hour(s)
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	3.4 W	3 hour(s)
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	3.4 W	3 hour(s)
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	3.4 W	3 hour(s)
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	3.4 W	3 hour(s)
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	3.4 W	3 hour(s)
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	3.4 W	3 hour(s)
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	3.4 W	3 hour(s)
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	3.4 W	3 hour(s)
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	3.4 W	3 hour(s)
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	3.4 W	3 hour(s)
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	3.4 W	3 hour(s)
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	3.4 W	3 hour(s)
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	3.4 W	3 hour(s)
910629173126	4MX900 581 LED50S/840 PSD MB WH	-	-
910629177026	4MX900 581 LED50S/840 PSD WB WH	-	-
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	-	-
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	3.4 W	3 hour(s)
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-	-

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910629132526	4MX900 LED40S/840 PSD MB WH L1200	-	-
910629132626	4MX900 LED40S/840 PSD NB WH L1200	-	-
910629137226	4MX900 LED60S/840 PSD WB WH L1800	-	-
910629137326	4MX900 LED60S/840 PSD MB WH L1800	-	-
910629137426	4MX900 LED60S/840 PSD NB WH L1800	-	-
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-	-
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-	-
910629139026	4MX900 LED90S/840 PSD NB WH L1800	-	-
910629140426	4MX900 581 LED40S/840 PSU WB WH	-	-
910629140526	4MX900 581 LED40S/840 PSU MB WH	-	-
910629142026	4MX900 491 LED40S/840 PSU WB WH	-	-
910629142126	4MX900 491 LED40S/840 PSU MB WH	-	-
910629143226	4MX900 LED40S/840 PSU WB WH L1200	-	-
910629144426	4MX900 491 LED40S/840 PSD WB WH	-	-
910629144526	4MX900 491 LED40S/840 PSD MB WH	-	-
910629144626	4MX900 491 LED40S/840 PSD NB WH	-	-
910629144826	4MX900 491 LED50S/840 PSD WB WH	-	-
910629144926	4MX900 491 LED50S/840 PSD MB WH	-	-
910629145026	4MX900 491 LED50S/840 PSD NB WH	-	-
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	-	-
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-	-
910629145626	4MX900 581 LED40S/840 PSU A30 WH	-	-
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-	-
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-	-

Maxos LED Performer

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-	-
910629146026	4MX900 581 LED50S/840 PSU WB WH	-	-
910629146126	4MX900 581 LED50S/840 PSU MB WH	-	-
910629146426	4MX900 491 LED50S/840 PSU WB WH	-	-
910629146526	4MX900 491 LED50S/840 PSU MB WH	-	-
910629146626	4MX900 491 LED50S/840 PSU NB WH	-	-
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-	-
910629148326	4MX900 581 LED75S/840 PSU A30 WH	-	-
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-	-
910629170326	4MX900 491 LED75S/840 PSU WB WH	-	-
910629170426	4MX900 491 LED75S/840 PSU MB WH	-	-
910629170826	4MX900 581 LED75S/840 PSU WB WH	-	-
910629170926	4MX900 581 LED75S/840 PSU MB WH	-	-
910629171026	4MX900 581 LED75S/840 PSU NB WH	-	-
910629171326	4MX900 491 LED75S/840 PSD WB WH	-	-
910629171426	4MX900 491 LED75S/840 PSD MB WH	-	-

Order Code	Full Product Name	Power consumption during Central DC emergency mode	Rated duration of the emergency lighting (when fully charged)
910629171526	4MX900 491 LED75S/840 PSD NB WH	-	-
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-	-
910629171926	4MX900 581 LED75S/840 PSD WB WH	-	-
910629172026	4MX900 581 LED75S/840 PSD MB WH	-	-
910629172126	4MX900 581 LED75S/840 PSD NB WH	-	-
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-	-
910629173226	4MX900 581 LED50S/840 PSD A30 WH	-	-
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-	-
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-	-
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-	-
910629138126	4MX900 LED90S/840 PSD MB SI L1800	-	-
910629141226	4MX900 491 LED40S/840 PSU WB SI	-	-
910629141326	4MX900 491 LED40S/840 PSU MB SI	-	-
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-	-
910629172926	4MX900 LED40S/840 PSU WB SI L1200	-	-
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	0 to +45 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s

Maxos LED Performer

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460309	4MX900 581 LED40S/840 PSD MB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460310	4MX900 581 LED40S/840 PSD NB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460311	4MX900 581 LED40S/840 PSD WB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	0 °C to 35 °C	Temperature 850 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910629173126	4MX900 581 LED50S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s

Maxos LED Performer

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629177026	4MX900 581 LED50S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	0 to +45 °C	Temperature 650 °C, duration 30 s
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	0 °C to 35 °C	Temperature 850 °C, duration 30 s
910629132426	4MX900 LED40S/840 PSD WB WH L1200	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629132526	4MX900 LED40S/840 PSD MB WH L1200	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629132626	4MX900 LED40S/840 PSD NB WH L1200	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629137226	4MX900 LED60S/840 PSD WB WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629137326	4MX900 LED60S/840 PSD MB WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629137426	4MX900 LED60S/840 PSD NB WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629138826	4MX900 LED90S/840 PSD WB WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629138926	4MX900 LED90S/840 PSD MB WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629139026	4MX900 LED90S/840 PSD NB WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629140426	4MX900 581 LED40S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629140526	4MX900 581 LED40S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629142026	4MX900 491 LED40S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629142126	4MX900 491 LED40S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629143226	4MX900 LED40S/840 PSU WB WH L1200	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629144426	4MX900 491 LED40S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629144526	4MX900 491 LED40S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629144626	4MX900 491 LED40S/840 PSD NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629144826	4MX900 491 LED50S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629144926	4MX900 491 LED50S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145026	4MX900 491 LED50S/840 PSD NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145626	4MX900 581 LED40S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629146026	4MX900 581 LED50S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629146126	4MX900 581 LED50S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629146426	4MX900 491 LED50S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629146526	4MX900 491 LED50S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629146626	4MX900 491 LED50S/840 PSU NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629148326	4MX900 581 LED75S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629170326	4MX900 491 LED75S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s

Maxos LED Performer

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629170426	4MX900 491 LED75S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629170826	4MX900 581 LED75S/840 PSU WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629170926	4MX900 581 LED75S/840 PSU MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171026	4MX900 581 LED75S/840 PSU NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171326	4MX900 491 LED75S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171426	4MX900 491 LED75S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171526	4MX900 491 LED75S/840 PSD NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171826	4MX900 491 LED75S/840 PSD A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629171926	4MX900 581 LED75S/840 PSD WB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629172026	4MX900 581 LED75S/840 PSD MB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	(0.38, 0.38) SDCM <3.5
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	(0.38, 0.38) SDCM <3.5
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460309	4MX900 581 LED40S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910500460310	4MX900 581 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910500460311	4MX900 581 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	(0.38, 0.38) SDCM <3.5
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Ambient temperature range	Glow-wire test
910629172126	4MX900 581 LED75S/840 PSD NB WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629172426	4MX900 581 LED75S/840 PSD A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629173226	4MX900 581 LED50S/840 PSD A30 WH	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629131626	4MX900 LED40S/840 PSD WB SI L1200	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629136426	4MX900 LED60S/840 PSD WB SI L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629138026	4MX900 LED90S/840 PSD WB SI L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629138126	4MX900 LED90S/840 PSD MB SI L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629141226	4MX900 491 LED40S/840 PSU WB SI	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629141326	4MX900 491 LED40S/840 PSU MB SI	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629172926	4MX900 LED40S/840 PSU WB SI L1200	-20 to +40 °C	Temperature 650 °C, duration 30 s
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-20 to +40 °C	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Initial chromaticity
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	(0.38, 0.38) SDCM <3.5
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5

Maxos LED Performer

Order Code	Full Product Name	Initial chromaticity
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	(0.38, 0.38) SDCM <3.5
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	(0.38, 0.38) SDCM <3.5
910629173126	4MX900 581 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629177026	4MX900 581 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	(0.38, 0.38) SDCM <3.5
910629132426	4MX900 LED40S/840 PSD WB WH L1200	(0.38, 0.38) SDCM <3.5
910629132526	4MX900 LED40S/840 PSD MB WH L1200	(0.38, 0.38) SDCM <3.5
910629132626	4MX900 LED40S/840 PSD NB WH L1200	(0.38, 0.38) SDCM <3.5
910629137226	4MX900 LED60S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
910629137326	4MX900 LED60S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
910629137426	4MX900 LED60S/840 PSD NB WH L1800	(0.38, 0.38) SDCM <3.5
910629138826	4MX900 LED90S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
910629138926	4MX900 LED90S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
910629139026	4MX900 LED90S/840 PSD NB WH L1800	(0.38, 0.38) SDCM <3.5
910629140426	4MX900 581 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629140526	4MX900 581 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629142026	4MX900 491 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629142126	4MX900 491 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629143226	4MX900 LED40S/840 PSU WB WH L1200	(0.38, 0.38) SDCM <3.5
910629144426	4MX900 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629144526	4MX900 491 LED40S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629144626	4MX900 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629144826	4MX900 491 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Initial chromaticity
910629144926	4MX900 491 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629145026	4MX900 491 LED50S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	(0.38, 0.38) SDCM <3.5
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5
910629145626	4MX900 581 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629145726	4MX900 581 LED50S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629145826	4MX900 491 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629145926	4MX900 491 LED50S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629146026	4MX900 581 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629146126	4MX900 581 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629146426	4MX900 491 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629146526	4MX900 491 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629146626	4MX900 491 LED50S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5
910629148326	4MX900 581 LED75S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629148526	4MX900 491 LED75S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
910629170326	4MX900 491 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629170426	4MX900 491 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629170826	4MX900 581 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
910629170926	4MX900 581 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
910629171026	4MX900 581 LED75S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
910629171326	4MX900 491 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629171426	4MX900 491 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629171526	4MX900 491 LED75S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629171826	4MX900 491 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
910629171926	4MX900 581 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
910629172026	4MX900 581 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
910629172126	4MX900 581 LED75S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
910629172426	4MX900 581 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
910629173226	4MX900 581 LED50S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
910629131626	4MX900 LED40S/840 PSD WB SI L1200	(0.38, 0.38) SDCM <3.5
910629136426	4MX900 LED60S/840 PSD WB SI L1800	(0.38, 0.38) SDCM <3.5
910629138026	4MX900 LED90S/840 PSD WB SI L1800	(0.38, 0.38) SDCM <3.5
910629138126	4MX900 LED90S/840 PSD MB SI L1800	(0.38, 0.38) SDCM <3.5
910629141226	4MX900 491 LED40S/840 PSU WB SI	(0.38, 0.38) SDCM <3.5
910629141326	4MX900 491 LED40S/840 PSU MB SI	(0.38, 0.38) SDCM <3
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	(0.38, 0.38) SDCM <3.5
910629172926	4MX900 LED40S/840 PSU WB SI L1200	(0.38, 0.38) SDCM <3.5
910629177526	4MX900 581 LED50S/840 PSU A30 SI	(0.38, 0.38) SDCM <3.5

Product Data

Order Code	Full Product Name	Product family code
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	4MX900
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	4MX900
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	4MX900
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	4MX900
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	4MX900
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	4MX900
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	4MX900


Order Code	Full Product Name	Product family code
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	4MX900
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	4MX900
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	4MX900
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	4MX900
910500460309	4MX900 581 LED40S/840 PSD MB WH	4MX900
910500460310	4MX900 581 LED40S/840 PSD NB WH	4MX900
910500460311	4MX900 581 LED40S/840 PSD WB WH	4MX900

Maxos LED Performer


Order Code	Full Product Name	Product family code
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	4MX900
910500460315	4MX900 581 LED50S/840 PSD-CLO NB WH	4MX900
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	4MX900
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	4MX900
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	4MX900
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	4MX900
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	4MX900
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	4MX900
910500460359	4MX933 491 LED50S/840 PSU MB WH ELB3	4MX933
910500460360	4MX933 491 LED50S/840 PSU NB WH ELB3	4MX933
910500460361	4MX933 491 LED50S/840 PSU WB WH ELB3	4MX933
910500460363	4MX933 491 LED50S/840 PSD MB WH ELB3C-2R	4MX933
910500460364	4MX933 491 LED50S/840 PSD NB WH ELB3C-2R	4MX933
910500460365	4MX933 491 LED50S/840 PSD WB WH ELB3C-2R	4MX933
910500460371	4MX933 491 LED75S/840 PSD MB WH ELB3C-2R	4MX933
910500460372	4MX933 491 LED75S/840 PSD NB WH ELB3C-2R	4MX933
910500460373	4MX933 491 LED75S/840 PSD WB WH ELB3C-2R	4MX933
910500460375	4MX933 581 LED50S/840 PSU MB WH ELB3	4MX933
910500460377	4MX933 581 LED50S/840 PSU WB WH ELB3	4MX933
910500460379	4MX933 581 LED50S/840 PSD MB WH ELB3C-2R	4MX933
910500460380	4MX933 581 LED50S/840 PSD NB WH ELB3C-2R	4MX933
910500460381	4MX933 581 LED50S/840 PSD WB WH ELB3C-2R	4MX933
910500460387	4MX933 581 LED75S/840 PSD MB WH ELB3C-2R	4MX933
910500460388	4MX933 581 LED75S/840 PSD NB WH ELB3C-2R	4MX933
910500460389	4MX933 581 LED75S/840 PSD WB WH ELB3C-2R	4MX933
910629173126	4MX900 581 LED50S/840 PSD MB WH	4MX900
910629177026	4MX900 581 LED50S/840 PSD WB WH	4MX900
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	4MX900
910500460376	4MX933 581 LED50S/840 PSU NB WH ELB3	4MX933
910629132426	4MX900 LED40S/840 PSD WB WH L1200	4MX900
910629132526	4MX900 LED40S/840 PSD MB WH L1200	4MX900
910629132626	4MX900 LED40S/840 PSD NB WH L1200	4MX900
910629137226	4MX900 LED60S/840 PSD WB WH L1800	4MX900
910629137326	4MX900 LED60S/840 PSD MB WH L1800	4MX900
910629137426	4MX900 LED60S/840 PSD NB WH L1800	4MX900
910629138826	4MX900 LED90S/840 PSD WB WH L1800	4MX900
910629138926	4MX900 LED90S/840 PSD MB WH L1800	4MX900
910629139026	4MX900 LED90S/840 PSD NB WH L1800	4MX900
910629140426	4MX900 581 LED40S/840 PSU WB WH	4MX900
910629140526	4MX900 581 LED40S/840 PSU MB WH	4MX900
910629142026	4MX900 491 LED40S/840 PSU WB WH	4MX900
910629142126	4MX900 491 LED40S/840 PSU MB WH	4MX900
910629143226	4MX900 LED40S/840 PSU WB WH L1200	4MX900

Order Code	Full Product Name	Product family code
910629144426	4MX900 491 LED40S/840 PSD WB WH	4MX900
910629144526	4MX900 491 LED40S/840 PSD MB WH	4MX900
910629144626	4MX900 491 LED40S/840 PSD NB WH	4MX900
910629144826	4MX900 491 LED50S/840 PSD WB WH	4MX900
910629144926	4MX900 491 LED50S/840 PSD MB WH	4MX900
910629145026	4MX900 491 LED50S/840 PSD NB WH	4MX900
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	4MX900
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	4MX900
910629145626	4MX900 581 LED40S/840 PSU A30 WH	4MX900
910629145726	4MX900 581 LED50S/840 PSU A30 WH	4MX900
910629145826	4MX900 491 LED40S/840 PSU A30 WH	4MX900
910629145926	4MX900 491 LED50S/840 PSU A30 WH	4MX900
910629146026	4MX900 581 LED50S/840 PSU WB WH	4MX900
910629146126	4MX900 581 LED50S/840 PSU MB WH	4MX900
910629146426	4MX900 491 LED50S/840 PSU WB WH	4MX900
910629146526	4MX900 491 LED50S/840 PSU MB WH	4MX900
910629146626	4MX900 491 LED50S/840 PSU NB WH	4MX900
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	4MX900
910629148326	4MX900 581 LED75S/840 PSU A30 WH	4MX900
910629148526	4MX900 491 LED75S/840 PSU A30 WH	4MX900
910629170326	4MX900 491 LED75S/840 PSU WB WH	4MX900
910629170426	4MX900 491 LED75S/840 PSU MB WH	4MX900
910629170826	4MX900 581 LED75S/840 PSU WB WH	4MX900
910629170926	4MX900 581 LED75S/840 PSU MB WH	4MX900
910629171026	4MX900 581 LED75S/840 PSU NB WH	4MX900
910629171326	4MX900 491 LED75S/840 PSD WB WH	4MX900
910629171426	4MX900 491 LED75S/840 PSD MB WH	4MX900
910629171526	4MX900 491 LED75S/840 PSD NB WH	4MX900
910629171826	4MX900 491 LED75S/840 PSD A30 WH	4MX900
910629171926	4MX900 581 LED75S/840 PSD WB WH	4MX900
910629172026	4MX900 581 LED75S/840 PSD MB WH	4MX900
910629172126	4MX900 581 LED75S/840 PSD NB WH	4MX900
910629172426	4MX900 581 LED75S/840 PSD A30 WH	4MX900
910629173226	4MX900 581 LED50S/840 PSD A30 WH	4MX900
910629131626	4MX900 LED40S/840 PSD WB SI L1200	4MX900
910629136426	4MX900 LED60S/840 PSD WB SI L1800	4MX900
910629138026	4MX900 LED90S/840 PSD WB SI L1800	4MX900
910629138126	4MX900 LED90S/840 PSD MB SI L1800	4MX900
910629141226	4MX900 491 LED40S/840 PSU WB SI	4MX900
910629141326	4MX900 491 LED40S/840 PSU MB SI	4MX900
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	4MX900
910629172926	4MX900 LED40S/840 PSU WB SI L1200	4MX900
910629177526	4MX900 581 LED50S/840 PSU A30 SI	4MX900


Polar Wide Diagrams




Polar Normal (separate) - 4MX900I - 910629172026




Polar Normal (separate) - 4MX900I - 910629171926




Polar Normal (separate) - 4MX900I - 910629145626




Polar Normal (separate) - 4MX900I - 910629146026




Polar Normal (separate) - 4MX900I - 910629140426




Polar Normal (separate) - 4MX900I - 910629170926



Polar Normal (separate) - 4MX900I - 910629144926




Polar Normal (separate) - 4MX900I - 910629145726




Polar Normal (separate) - 4MX900I - 910629145826


Polar Wide Diagrams




Polar Normal (separate) - 4MX900I - 910629171326




Polar Normal (separate) - 4MX900I - 910629146126




Polar Normal (separate) - 4MX900I - 910629146626




Polar Normal (separate) - 4MX900I - 910629177026




Polar Normal (separate) - 4MX900I - 910629173126




Polar Normal (separate) - 4MX900I - 910629141226



Polar Normal (separate) - 4MX900I - 910629142126




Polar Normal (separate) - 4MX900I - 910629144426




Polar Normal (separate) - 4MX900I - 910629146426


Polar Wide Diagrams




Polar Normal (separate) - 4MX900I - 910629144626




Polar Normal (separate) - 4MX900I - 910629140526




Polar Normal (separate) - 4MX900I - 910629141326




Polar Normal (separate) - 4MX900I - 910629142026




Polar Normal (separate) - 4MX900I - 910629171826




Polar Normal (separate) - 4MX900I - 910629145926



Polar Normal (separate) - 4MX900I - 910629170426




Polar Normal (separate) - 4MX900I - 910629170326




Polar Normal (separate) - 4MX900I - 910629171526


Polar Wide Diagrams




Polar Normal (separate) - 4MX900I - 910629144826




Polar Normal (separate) - 4MX900I - 910629170826




Polar Normal (separate) - 4MX900I - 910629171426




Polar Normal (separate) - 4MX900I - 910629144526




Polar Normal (separate) - 4MX900I - 910629145026




Polar Normal (separate) - 4MX900I - 910629148526



Polar Normal (separate) - 4MX900I - 910629148326




Polar Normal (separate) - 4MX900I - 910629171026




Polar Normal (separate) - 4MX900I - 910629172126


Polar Wide Diagrams




Polar Normal (separate) - 4MX900I - 910629172426




Polar Normal (separate) - 4MX900I - 910629173226




Polar Normal (separate) - 4MX900I - 910629177526




Polar Normal (separate) - 4MX900I - 910629146526




Polar Normal (separate) - 4MX900I - 910500460299




Polar Normal (separate) - 4MX900I - 910500460311



Polar Normal (separate) - 4MX900I - 910500460307




Polar Normal (separate) - 4MX900I - 910500460298




Polar Normal (separate) - 4MX900I - 910500460297


Polar Wide Diagrams




Polar Normal (separate) - 4MX900I - 910500460305




Polar Normal (separate) - 4MX900I - 910500460306




Polar Normal (separate) - 4MX900I - 910500460309




Polar Normal (separate) - 4MX900I - 910500460317




Polar Normal (separate) - 4MX900I - 910500460310




Polar Normal (separate) - 4MX900I - 910500460318



Polar Normal (separate) - 4MX900I - 910500460323



Polar Normal (separate) - 4MX900I - 910500460325



Polar Normal (separate) - 4MX900I - 910500460324

Maxos LED Performer

