



Mains-voltage linear R7S with very high light output

CorePro LEDlinear MV

CorePro R7S is a retrofit replacement for traditional double-ended linear R7S lamps. Its 'light all around' design delivers light just like a halogen lamp. Within the range you can choose dimmable products which have deep dimming function that enables a cozy ambience when using a dimmable fixture.

Benefits

- Up to 90% energy saving compared to standard halogen lamps
- Lower maintenance costs

Features

- Easy retrofit
- Operates at 220–240 V AC and its form-factor is designed as a direct retrofit into all double ended holders
- Lifetime of 15,000 hours (B50L70)
- UV- and IR-free light
- Free of mercury and hazardous materials – RoHS compliant

Application

- Living rooms, corridors, outdoor luminaires (security lighting), free floor-standing indoor luminaires, construction lighting

CorePro LEDlinear MV


Versions



LED Lamps, CorePro 118 mm R7S



DTE310 3 x 10A Trailing Edge Dimmer Controller



LED 100W R7S 78mm WH ND SRT4




LEDlinear CorePro 7,2W R7S



LEDlinear CorePro 7,2W R7S 1


Dimensional drawing



Product	D	C
CorePro LEDlinear ND 7-60W R7S 78mm830	28 mm	78 mm
CorePro LEDlinear ND 7-60W R7S 78mm840	28 mm	78 mm
CorePro LEDlinearND 11.5-100W R7S78mm830	28 mm	78 mm

CorePro LEDlinear MV

Dimensional drawing



Product	D	C
CorePro LED linear D 14-120W R7S 118 830	29 mm	118 mm
CorePro LED linear D 14-120W R7S 118 840	29 mm	118 mm
CorePro R7S 118mm 14-100W 830 D	29 mm	118 mm
CorePro R7S 118mm 14-100W 840 D	29 mm	118 mm
CoreProLED linearD 17.5-150W R7S 118 830	42 mm	118 mm
CoreProLED linearD 17.5-150W R7S 118 840	42 mm	118 mm
LED 14-120W R7S 118mm 830 D 1pk AU	29 mm	118 mm

Product	D	C
CorePro R7S 118mm 7.2-60W 830	15 mm	118 mm
CorePro R7S 118mm 7.2-60W 840	15 mm	118 mm

General Information	
Cap-Base	R7s
Nominal lifetime	15,000 hour(s)
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

General Information

Order Code	Full Product Name	Rated Lifetime (Hours)	Switching Cycle
929001243702	CorePro R7S 118mm 14-100W 830 D	-	50,000
929001243802	CorePro R7S 118mm 14-100W 840 D	-	50,000
929001353602	CorePro LED linear D 14-120W R7S 118 830	-	50,000
929001353679	LED 14-120W R7S 118mm 830 D 1pk AU	15,000 hour(s)	50,000
929001353702	CorePro LED linear D 14-120W R7S 118 840	-	50,000
929003791502	CorePro LEDlinearND 11.5-100W R7S78mm830	-	50,000

Order Code	Full Product Name	Rated Lifetime (Hours)	Switching Cycle
929002495002	CorePro R7S 118mm 7.2-60W 830	-	8,000
929002016602	CoreProLED linearD 17.5-150W R7S 118 830	-	50,000
929002016702	CoreProLED linearD 17.5-150W R7S 118 840	-	50,000
929003791302	CorePro LEDlinear ND 7-60W R7S 78mm830	-	50,000
929003791402	CorePro LEDlinear ND 7-60W R7S 78mm840	-	50,000

CorePro LEDlinear MV

Order Code	Full Product Name	Rated	Switching
		Lifetime (Hours)	Cycle
929002495102	CorePro R7S 118mm 7.2-60W 840	-	8,000

Light Technical

Order Code	Full Product Name	Beam	Correlated	Color	Luminous
		Angle (Nom)	Color Temperature (Nom)		
929001243702	CorePro R7S 118mm 14-100W 830 D	-	3000 K	830	1,600 lm
929001243802	CorePro R7S 118mm 14-100W 840 D	-	4000 K	840	1,800 lm
929001353602	CorePro LED linear D 14-120W R7S 118 830	-	3000 K	830	2,000 lm
929001353679	LED 14-120W R7S 118mm 830 D 1pk AU	-	3000 K	830	2,000 lm
929001353702	CorePro LED linear D 14-120W R7S 118 840	-	4000 K	840	2,000 lm
929003791502	CorePro LEDlinearND	300 degree(s)	3000 K	830	1,521 lm

Order Code	Full Product Name	Beam	Correlated	Color	Luminous
		Angle (Nom)	Color Temperature (Nom)		
	11.5-100W R7S78mm830				
929002495002	CorePro R7S 118mm 7.2-60W 830	-	3000 K	830	810 lm
929002016602	CoreProLED linearD 17.5-150W R7S 118 830	-	3000 K	830	2,460 lm
929002016702	CoreProLED linearD 17.5-150W R7S 118 840	-	4000 K	840	2,460 lm
929003791302	CorePro LEDlinear ND 7-60W R7S 78mm830	300 degree(s)	3000 K	830	950 lm
929003791402	CorePro LEDlinear ND 7-60W R7S 78mm840	300 degree(s)	4000 K	840	1,000 lm
929002495102	CorePro R7S 118mm 7.2-60W 840	-	4000 K	840	850 lm

Operating and Electrical

Order Code	Full Product Name	Line	Power	Wattage
		Frequency	Consumption	Equivalent
929001243702	CorePro R7S 118mm 14-100W 830 D	50 to 60 Hz	14 W	100 W
929001243802	CorePro R7S 118mm 14-100W 840 D	50 to 60 Hz	14 W	100 W
929001353602	CorePro LED linear D 14-120W R7S 118 830	50 to 60 Hz	14 W	120 W
929001353679	LED 14-120W R7S 118mm 830 D 1pk AU	-	14 W	120 W
929001353702	CorePro LED linear D 14-120W R7S 118 840	50 to 60 Hz	14 W	120 W
929003791502	CorePro LEDlinearND 11.5-100W R7S78mm830	-	11.5 W	100 W
929002495002	CorePro R7S 118mm 7.2-60W 830	50 to 60 Hz	7.2 W	60 W

Order Code	Full Product Name	Line	Power	Wattage
		Frequency	Consumption	Equivalent
929002016602	CoreProLED linearD 17.5-150W R7S 118 830	50 to 60 Hz	17.5 W	150 W
929002016702	CoreProLED linearD 17.5-150W R7S 118 840	50 to 60 Hz	17.5 W	150 W
929003791302	CorePro LEDlinear ND 7-60W R7S 78mm830	-	7 W	60 W
929003791402	CorePro LEDlinear ND 7-60W R7S 78mm840	-	7 W	60 W
929002495102	CorePro R7S 118mm 7.2-60W 840	50 to 60 Hz	7.2 W	60 W

Temperature

CorePro LEDlinear MV

Order Code	Full Product Name	T-Case Maximum (Nom)
929001243702	CorePro R7S 118mm 14-100W 830 D	90 °C
929001243802	CorePro R7S 118mm 14-100W 840 D	90 °C
929001353602	CorePro LED linear D 14-120W R7S 118 830	100 °C
929001353679	LED 14-120W R7S 118mm 830 D 1pk AU	100 °C
929001353702	CorePro LED linear D 14-120W R7S 118 840	100 °C
929003791502	CorePro LEDlinearND 11.5-100W R7S78mm830	104 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929001243702	CorePro R7S 118mm 14-100W 830 D	Only with specific dimmers
929001243802	CorePro R7S 118mm 14-100W 840 D	Only with specific dimmers
929001353602	CorePro LED linear D 14-120W R7S 118 830	Yes
929001353679	LED 14-120W R7S 118mm 830 D 1pk AU	Only with specific dimmers
929001353702	CorePro LED linear D 14-120W R7S 118 840	Yes
929003791502	CorePro LEDlinearND 11.5-100W R7S78mm830	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001243702	CorePro R7S 118mm 14-100W 830 D	-	Linear
929001243802	CorePro R7S 118mm 14-100W 840 D	-	Linear
929001353602	CorePro LED linear D 14-120W R7S 118 830	-	Linear
929001353679	LED 14-120W R7S 118mm 830 D 1pk AU	Clear	Linear
929001353702	CorePro LED linear D 14-120W R7S 118 840	-	Linear
929003791502	CorePro LEDlinearND 11.5-100W R7S78mm830	Clear	R7S

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929001243702	CorePro R7S 118mm 14-100W 830 D	-	14 kWh
929001243802	CorePro R7S 118mm 14-100W 840 D	-	14 kWh
929001353602	CorePro LED linear D 14-120W R7S 118 830	-	14 kWh
929001353679	LED 14-120W R7S 118mm 830 D 1pk AU	-20 to +45 °C	14 kWh
929001353702	CorePro LED linear D 14-120W R7S 118 840	-	14 kWh
929003791502	CorePro LEDlinearND 11.5-100W R7S78mm830	-20 to +45 °C	12 kWh
929002495002	CorePro R7S 118mm 7.2-60W 830	-	8 kWh

Order Code	Full Product Name	T-Case Maximum (Nom)
929002495002	CorePro R7S 118mm 7.2-60W 830	110 °C
929002016602	CoreProLED linearD 17.5-150W R7S 118 830	102 °C
929002016702	CoreProLED linearD 17.5-150W R7S 118 840	102 °C
929003791302	CorePro LEDlinear ND 7-60W R7S 78mm830	88 °C
929003791402	CorePro LEDlinear ND 7-60W R7S 78mm840	88 °C
929002495102	CorePro R7S 118mm 7.2-60W 840	110 °C

Order Code	Full Product Name	Dimmable
929002495002	CorePro R7S 118mm 7.2-60W 830	No
929002016602	CoreProLED linearD 17.5-150W R7S 118 830	Only with specific dimmers
929002016702	CoreProLED linearD 17.5-150W R7S 118 840	Only with specific dimmers
929003791302	CorePro LEDlinear ND 7-60W R7S 78mm830	No
929003791402	CorePro LEDlinear ND 7-60W R7S 78mm840	No
929002495102	CorePro R7S 118mm 7.2-60W 840	No

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002495002	CorePro R7S 118mm 7.2-60W 830	Clear	Linear
929002016602	CoreProLED linearD 17.5-150W R7S 118 830	-	Linear
929002016702	CoreProLED linearD 17.5-150W R7S 118 840	-	Linear
929003791302	CorePro LEDlinear ND 7-60W R7S 78mm830	Clear	R7S
929003791402	CorePro LEDlinear ND 7-60W R7S 78mm840	Clear	R7S
929002495102	CorePro R7S 118mm 7.2-60W 840	Clear	Linear

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002016602	CoreProLED linearD 17.5-150W R7S 118 830	-	18 kWh
929002016702	CoreProLED linearD 17.5-150W R7S 118 840	-	18 kWh
929003791302	CorePro LEDlinear ND 7-60W R7S 78mm830	-20 to +45 °C	7 kWh
929003791402	CorePro LEDlinear ND 7-60W R7S 78mm840	-20 to +45 °C	7 kWh
929002495102	CorePro R7S 118mm 7.2-60W 840	-	8 kWh

