



Apparecchio lineare R7S a tensione di rete con emissione luminosa molto elevata

CorePro LEDlinear MV

CorePro R7S è una sostituzione retrofit per le lampade lineari a terminazione doppia R7S. Il design per una "luce completamente diffusa" offre un'illuminazione analoga a quella delle lampade alogene. All'interno della gamma è possibile scegliere prodotti dimmerabili che hanno la funzione avanzata di regolazione del flusso che consente di creare un'atmosfera accogliente quando si usa un apparecchio regolabile.

Vantaggi

- Risparmio energetico fino all'90% rispetto alle lampade alogene standard
- Minori costi di manutenzione

Caratteristiche

- Facilità di aggiornamento diretto (retrofit)
- Funziona a 220-240 V CA e il suo fattore di forma è progettato come aggiornamento diretto (retrofit) in tutti gli attacchi a terminazione doppia
- Durata di 15.000 ore (B50L70)
- Luce priva di raggi UV e IR
- Priva di mercurio e materiali pericolosi – Conforme alla direttiva RoHS

Applicazione

- Soggiorni, corridoi, illuminazione da esterni (lampade di emergenza), apparecchi a piantana per interni, illuminazioni per cantieri edili

CorePro LEDlinear MV


Versions



LED Lamps, CorePro 118 mm R7S




DTE310 3 x 10A Trailing Edge
Dimmer Controller



LED 100W R7S 78mm WH ND
SRT4



LEDlinear CorePro 7,2W R7S



LEDspot R7S 230V




LED 60W R7S 78mm WH RF ND
SRT4




LEDlinear CorePro 7,2W R7S 1


Disegno tecnico



Product	D	C
CorePro LEDlinear ND 7-60W R7S 78mm830	28 mm	78 mm
CorePro LEDlinear ND 7-60W R7S 78mm840	28 mm	78 mm
CorePro LEDlinearND 11.5-100W R7S78mm830	28 mm	78 mm



Product	D	C
CorePro LED linear D 14-120W R7S 118 830	29 mm	118 mm
CorePro LED linear D 14-120W R7S 118 840	29 mm	118 mm
CorePro R7S 118mm 14-100W 830 D	29 mm	118 mm
CorePro R7S 118mm 14-100W 840 D	29 mm	118 mm
CoreProLED linearD 17.5-150W R7S 118 830	42 mm	118 mm
CoreProLED linearD 17.5-150W R7S 118 840	42 mm	118 mm



Product	D	C
CorePro R7S 118mm 7.2-60W 830	15 mm	118 mm
CorePro R7S 118mm 7.2-60W 840	15 mm	118 mm

Informazioni generali	
Attacco	R7s
Durata nominale	15.000 ore
Dati tecnici di illuminazione	
Indice di resa cromatica (CRI)	80
LLMF a fine durata vita nominale (Nom)	70 %
Funzionamento e parte elettrica	
Frequenza di ingresso	Da 50 a 60 Hz
Tempo di avvio (Nom)	0,5 s

Informazioni generali

CorePro LEDlinear MV

Order Code	Full Product Name	Ciclo di commutazione on/off
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	50.000
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	50.000
71400300	CorePro LED linear D 14-120W R7S 118 830	50.000
71406500	CorePro LED linear D 14-120W R7S 118 840	50.000
30199300	CorePro LEDlinearND 11.5-100W R7S78mm830	50.000
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	8.000

Dati tecnici di illuminazione

Order Code	Full Product Name	Angolo del fascio (Nom)	Temperatura di colore correlata (Nom)	Codice colore	Flusso luminoso
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	-	3000 K	830	1.600 lm
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	-	4000 K	840	1.800 lm
71400300	CorePro LED linear D 14-120W R7S 118 830	-	3000 K	830	2.000 lm
71406500	CorePro LED linear D 14-120W R7S 118 840	-	4000 K	840	2.000 lm
30199300	CorePro LEDlinearND 11.5-100W R7S78mm830	300 °	3000 K	830	1.521 lm
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	-	3000 K	830	810 lm

Funzionamento e parte elettrica

Order Code	Full Product Name	Frequenza di linea	Consumo energetico	Potenza equivalente
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	50 to 60 Hz	14 W	100 W
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	50 to 60 Hz	14 W	100 W
71400300	CorePro LED linear D 14-120W R7S 118 830	50 to 60 Hz	14 W	120 W
71406500	CorePro LED linear D 14-120W R7S 118 840	50 to 60 Hz	14 W	120 W
30199300	CorePro LEDlinearND 11.5-100W R7S78mm830	-	11,5 W	100 W
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	50 to 60 Hz	7,2 W	60 W

Temperatura

Order Code	Full Product Name	Ciclo di commutazione on/off
64673800	CoreProLED linearD 17.5-150W R7S 118 830	50.000
64675200	CoreProLED linearD 17.5-150W R7S 118 840	50.000
30193100	CorePro LEDlinear ND 7-60W R7S 78mm830	50.000
30195500	CorePro LEDlinear ND 7-60W R7S 78mm840	50.000
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	8.000

Order Code	Full Product Name	Angolo del fascio (Nom)	Temperatura di colore correlata (Nom)	Codice colore	Flusso luminoso
64673800	CoreProLED linearD 17.5-150W R7S 118 830	-	3000 K	830	2.460 lm
64675200	CoreProLED linearD 17.5-150W R7S 118 840	-	4000 K	840	2.460 lm
30193100	CorePro LEDlinear ND 7-60W R7S 78mm830	300 °	3000 K	830	950 lm
30195500	CorePro LEDlinear ND 7-60W R7S 78mm840	300 °	4000 K	840	1.000 lm
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	-	4000 K	840	850 lm

Order Code	Full Product Name	Frequenza di linea	Consumo energetico	Potenza equivalente
64673800	CoreProLED linearD 17.5-150W R7S 118 830	50 to 60 Hz	17,5 W	150 W
64675200	CoreProLED linearD 17.5-150W R7S 118 840	50 to 60 Hz	17,5 W	150 W
30193100	CorePro LEDlinear ND 7-60W R7S 78mm830	-	7 W	60 W
30195500	CorePro LEDlinear ND 7-60W R7S 78mm840	-	7 W	60 W
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	50 to 60 Hz	7,2 W	60 W

CorePro LEDlinear MV

Order Code	Full Product Name	Temp. massima involucro (Nom)
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	90 °C
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	90 °C
71400300	CorePro LED linear D 14-120W R7S 118 830	100 °C
71406500	CorePro LED linear D 14-120W R7S 118 840	100 °C
30199300	CorePro LEDlinearND 11.5-100W R7S78mm830	104 °C
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	110 °C

Controlli e dimmerazione

Order Code	Full Product Name	Dimmerabile
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	Solo con dimmer specifici
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	Solo con dimmer specifici
71400300	CorePro LED linear D 14-120W R7S 118 830	Sì
71406500	CorePro LED linear D 14-120W R7S 118 840	Sì
30199300	CorePro LEDlinearND 11.5-100W R7S78mm830	No
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	No

Meccanica e corpo

Order Code	Full Product Name	Finitura lampadina	Forma lampadina
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	-	Lineare
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	-	Lineare
71400300	CorePro LED linear D 14-120W R7S 118 830	-	Lineare
71406500	CorePro LED linear D 14-120W R7S 118 840	-	Lineare
30199300	CorePro LEDlinearND 11.5-100W R7S78mm830	Trasparente	R7S
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	Trasparente	Lineare

Approvazione e applicazione

Order Code	Full Product Name	Intervallo temperatura ambiente	Consumo energetico kWh/1000 h
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	-	14 kWh
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	-	14 kWh
71400300	CorePro LED linear D 14-120W R7S 118 830	-	14 kWh
71406500	CorePro LED linear D 14-120W R7S 118 840	-	14 kWh
30199300	CorePro LEDlinearND 11.5-100W R7S78mm830	Da -20 a +45 °C	12 kWh

Order Code	Full Product Name	Temp. massima involucro (Nom)
64673800	CoreProLED linearD 17.5-150W R7S 118 830	102 °C
64675200	CoreProLED linearD 17.5-150W R7S 118 840	102 °C
30193100	CorePro LEDlinear ND 7-60W R7S 78mm830	88 °C
30195500	CorePro LEDlinear ND 7-60W R7S 78mm840	88 °C
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	110 °C

Order Code	Full Product Name	Dimmerabile
64673800	CoreProLED linearD 17.5-150W R7S 118 830	Solo con dimmer specifici
64675200	CoreProLED linearD 17.5-150W R7S 118 840	Solo con dimmer specifici
30193100	CorePro LEDlinear ND 7-60W R7S 78mm830	No
30195500	CorePro LEDlinear ND 7-60W R7S 78mm840	No
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	No

Order Code	Full Product Name	Finitura lampadina	Forma lampadina
64673800	CoreProLED linearD 17.5-150W R7S 118 830	-	Lineare
64675200	CoreProLED linearD 17.5-150W R7S 118 840	-	Lineare
30193100	CorePro LEDlinear ND 7-60W R7S 78mm830	Trasparente	R7S
30195500	CorePro LEDlinear ND 7-60W R7S 78mm840	Trasparente	R7S
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	Trasparente	Lineare

Order Code	Full Product Name	Intervallo temperatura ambiente	Consumo energetico kWh/1000 h
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	-	8 kWh
64673800	CoreProLED linearD 17.5-150W R7S 118 830	-	18 kWh
64675200	CoreProLED linearD 17.5-150W R7S 118 840	-	18 kWh
30193100	CorePro LEDlinear ND 7-60W R7S 78mm830	Da -20 a +45 °C	7 kWh
30195500	CorePro LEDlinear ND 7-60W R7S 78mm840	Da -20 a +45 °C	7 kWh

CorePro LEDlinear MV

Order Code	Full Product Name	Intervallo temperatura ambiente	Consumo energetico kWh/1000 h
30399700	CorePro LED linear R7S 118mm	-	8 kWh
7.2-60W 840			

