



# The best LED solution for High Intensity Discharge (HID) SOX lamp replacement

## MASTER - LED HID SOX

Philips MASTER LED HID SOX offers an easy and short payback LED solution to replace SOX systems. These lamps bring the LED benefits of energy efficiency and long lifetime to conventional HID SOX replacement. They also come with a low initial investment to ensure instant savings. With the right lamp size, cap and light distribution, you can easily retrofit the traditional SOX system with MASTER LED HID SOX lamp thereby enhancing the light quality with comfort and safety without having to replace the fixtures or sacrifice the light effect

### Benefits

- Cost savings ensure a quick payback
- Low initial investment
- Enhance lighting quality for comfort and safety

### Features

- High Energy efficient lamps
- Long lifetime - 50,000 hrs
- Surge protection 6KV
- Pleasant white light with CRI 70
- Omnidirectional light around lamp
- Right lamp size and lighting distribution with same end cap as conventional SOX
- Additional Energy saving by Direct Mains connection
- IP60 product (IP rated sockets required for outdoor application)

# MASTER - LED HID SOX

## Application

- Road and Street
- Tunnel

## Warnings and Safety

- Please refer to the installation guide or consult a Philips Lighting representative for wiring diagram and instructions.

## Versions




TrueForce LEDHIL SOX 36W B22 740 FR



LEDTForce SOX Tshape B22

## Dimensional drawing



Product	D	C
MAS LED SOX M 2.5Klm 18W 840 B22 FR	52 mm	312 mm
MAS LED SOX M 4Klm 28W 840 B22 FR	52 mm	425 mm
MAS LED SOX M 5Klm 36W 840 B22 FR	52 mm	425 mm

MASTER - LED HID SOX

General Information	
Cap-Base	B22
Switching Cycle	50,000
Nominal lifetime	50,000 hour(s)
Light Technical	
Beam Angle (Nom)	230 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Color Code	840
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	T-shape
Approval and Application	
Ambient temperature range	-30 to +45 °C

Light Technical

Order Code	Full Product Name	Luminous Flux
929002496902	MAS LED SOX M 4Klm 28W 840 B22 FR	4,000 lm
929002497002	MAS LED SOX M 5Klm 36W 840 B22 FR	5,000 lm
929002496802	MAS LED SOX M 2.5Klm 18W 840 B22 FR	2,500 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929002496902	MAS LED SOX M 4Klm 28W 840 B22 FR	28 W
929002497002	MAS LED SOX M 5Klm 36W 840 B22 FR	36 W

Order Code	Full Product Name	Power Consumption
929002496802	MAS LED SOX M 2.5Klm 18W 840 B22 FR	18 W


Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002496902	MAS LED SOX M 4Klm 28W 840 B22 FR	65 °C
929002497002	MAS LED SOX M 5Klm 36W 840 B22 FR	67 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002496802	MAS LED SOX M 2.5Klm 18W 840 B22 FR	63 °C

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002496902	MAS LED SOX M 4Klm 28W 840 B22 FR	28 kWh
929002497002	MAS LED SOX M 5Klm 36W 840 B22 FR	36 kWh
929002496802	MAS LED SOX M 2.5Klm 18W 840 B22 FR	18 kWh



## MASTER - LED HID SOX

