



# The perfect fit LED solution for SOX system retrofit

## TrueForce LED Public (Road/Area – SOX)

Philips TrueForce LED Public (Road/Area – SOX) offers an easy and short payback LED solution to replace SOX systems. These lamps bring the LED benefits of energy efficiency and long lifetime to HID replacement. They also come with a low initial investment to ensure instant savings. With the right lamp size, cap and light distribution, you can easily retrofit the traditional SOX system with TrueForce LED SOX lamp thereby enhancing the light quality with comfort and safety without having to replace the fixtures or sacrifice the light effect.

### Benefits

- Cost savings ensure a quick payback
- Low initial investment
- Enhance lighting quality for comfort and safety

### Features

- High Energy efficient lamps
- Long lifetime – 50,000 hrs
- Surge protection 6KV
- Pleasant white light with CRI 70
- Omnidirectional light around lamp
- Right lamp size and lighting distribution with same end cap as conventional SOX
- Additional energy saving by direct mains connection
- IP60 product (IP rated sockets required for outdoor application)

### Application

- Road and Street
- Tunnel

# TrueForce LED Public (Road/Area – SOX)

## Warnings and Safety


• Please refer to the installation guide or consult a Philips Lighting representative for wiring diagram and instructions.

## Versions



TrueForce LEDHIL SOX 36W B22 740 FR

## Dimensional drawing



Product	D	C
MAS LED SOX M 4Klm 28W 840 B22 FR	52 mm	425 mm
MAS LED SOX M 5Klm 36W 840 B22 FR	52 mm	425 mm

TrueForce LED Public (Road/Area – SOX)

General Information	
Cap base	B22
Switching Cycle	50,000
Nominal lifetime	50,000 h
Light Technical	
Beam angle (nom.)	230 degree(s)
Correlated Colour Temperature (Nom)	4000 K
Colour rendering index (CRI)	80
Colour Code	840
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting time (nom.)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb shape	T-shape
Approval and Application	
Ambient temperature range	-30 to +45 °C

Light Technical

Order Code	Full Product Name	Luminous Flux
929002496902	MAS LED SOX M 4Klm 28W 840 B22 FR	4,000 lm
929002497002	MAS LED SOX M 5Klm 36W 840 B22 FR	5,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929002496902	MAS LED SOX M 4Klm 28W 840 B22 FR	28 W

Order Code	Full Product Name	Power Consumption
929002497002	MAS LED SOX M 5Klm 36W 840 B22 FR	36 W


Temperature

Order Code	Full Product Name	T-Case maximum (nom.)
929002496902	MAS LED SOX M 4Klm 28W 840 B22 FR	65 °C

Order Code	Full Product Name	T-Case maximum (nom.)
929002497002	MAS LED SOX M 5Klm 36W 840 B22 FR	67 °C

Approval and Application

Order Code	Full Product Name	Energy consumption kWh/
		1,000 hours
929002496902	MAS LED SOX M 4Klm 28W 840 B22 FR	28 kWh
929002497002	MAS LED SOX M 5Klm 36W 840 B22 FR	36 kWh



## TrueForce LED Public (Road/Area – SOX)

