



For top performance and sustainability

MASTER LEDspot ExpertColor MV

MASTER LEDspot ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. They offer superior lighting that has a customized spectrum, high CRI, and deep dimming feature. What's more the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, with MASTER LEDspot ExpertColor you can take advantage of the full ExpertColor family, which also includes LEDspot MR16, LEDspot AR111 and LEDspot PAR lamps. MASTER LEDspot ExpertColor delivers huge energy savings and minimizes maintenance costs without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within a short time period.

Benefits

- Create a warm and comfortable ambience with MASTER LED GU10
- Hassle-free retrofit solution for greater energy efficiency and sustainability
- Interior decor, furnishings and fabrics look great

Features

- Customized color spectrum replicates halogen light color
- Best-in-class color realization CRI97, R9>85
- Retrofittable with main-voltage GU10 halogen lamps
- Deep and smooth dimming with broad transformer compatibility

Application

- Hospitality
- Retail
- Residential


MASTER LEDspot ExpertColor MV

Versions



MASTER LEDspot ExpertColor MV
35W GU10 25D

Dimensional drawing



Product	D	C
MAS LED ExpertColor 3.9-35W GU10 927 25D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 927 36D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 930 25D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 930 36D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 940 25D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 940 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 927 24D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 927 25D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 927 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 927 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 930 24D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 930 25D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 930 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 930 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 940 25D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 940 36D	50 mm	54 mm
MASLED ExpertColor5.5-50W GU10 927 25DUK	50 mm	54 mm
MASLED ExpertColor5.5-50W GU10 927 36DUK	50 mm	54 mm
MASLEDExpertColor 5.5-50W GU10 930 36DUK	50 mm	54 mm

MASTER LEDspot ExpertColor MV

General Information	
Cap-Base	GU10
Switching Cycle	50,000
Nominal lifetime	40,000 hour(s)
Light Technical	
Color rendering index (CRI)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Temperature	
T-Case Maximum (Nom)	80 °C
Mechanical and Housing	
Bulb Shape	PAR16

Light Technical (1/2)

		Correlated Color			
Order Code	Full Product Name	Beam Angle (Nom)	Temperature	Color	Luminous
			(Nom)	Code	Flux
929001346402	MAS LED ExpertColor 3.9-35W GU10 927 25D	25 degree(s)	2700 K	927	265 lm
929001346502	MAS LED ExpertColor 3.9-35W GU10 930 25D	25 degree(s)	3000 K	930	280 lm
929001346602	MAS LED ExpertColor 3.9-35W GU10 940 25D	25 degree(s)	4000 K	940	300 lm
929001346702	MAS LED ExpertColor 3.9-35W GU10 927 36D	36 degree(s)	2700 K	927	265 lm
929001346802	MAS LED ExpertColor 3.9-35W GU10 930 36D	36 degree(s)	3000 K	930	280 lm
929001346902	MAS LED ExpertColor 3.9-35W GU10 940 36D	36 degree(s)	4000 K	940	300 lm
929001347002	MAS LED ExpertColor 5.5-50W GU10 927 25D	25 degree(s)	2700 K	927	355 lm
929001347008	MAS LED ExpertColor 5.5-50W GU10 927 24D	24 degree(s)	2700 K	927	385 lm
929001347099	MASLED ExpertColor5.5-50W GU10 927 25DUK	25 degree(s)	2700 K	927	355 lm
929001347102	MAS LED ExpertColor 5.5-50W GU10 930 25D	25 degree(s)	3000 K	930	375 lm
929001347108	MAS LED ExpertColor 5.5-50W GU10 930 24D	24 degree(s)	3000 K	930	405 lm
929001347202	MAS LED ExpertColor 5.5-50W GU10 940 25D	25 degree(s)	4000 K	940	400 lm
929001347302	MAS LED ExpertColor 5.5-50W GU10 927 36D	36 degree(s)	2700 K	927	355 lm
929001347308	MAS LED ExpertColor 5.5-50W GU10 927 36D	36 degree(s)	2700 K	927	385 lm
929001347398	MASLED ExpertColor5.5-50W GU10 927 36DUK	36 degree(s)	2700 K	927	355 lm
929001347402	MAS LED ExpertColor 5.5-50W GU10 930 36D	36 degree(s)	3000 K	930	375 lm
929001347408	MAS LED ExpertColor 5.5-50W GU10 930 36D	36 degree(s)	3000 K	930	405 lm
929001347499	MASLEDExpertColor 5.5-50W GU10 930 36DUK	36 degree(s)	3000 K	930	375 lm
929001347502	MAS LED ExpertColor 5.5-50W GU10 940 36D	36 degree(s)	4000 K	940	400 lm

Light Technical (2/2)

		Luminous Intensity (Nom)
929001346402	MAS LED ExpertColor 3.9-35W GU10 927 25D	700 cd
929001346502	MAS LED ExpertColor 3.9-35W GU10 930 25D	750 cd
929001346602	MAS LED ExpertColor 3.9-35W GU10 940 25D	800 cd
929001346702	MAS LED ExpertColor 3.9-35W GU10 927 36D	540 cd
929001346802	MAS LED ExpertColor 3.9-35W GU10 930 36D	560 cd

		Luminous Intensity (Nom)
929001346902	MAS LED ExpertColor 3.9-35W GU10 940 36D	600 cd
929001347002	MAS LED ExpertColor 5.5-50W GU10 927 25D	1,000 cd
929001347008	MAS LED ExpertColor 5.5-50W GU10 927 24D	1,000 cd
929001347099	MASLED ExpertColor5.5-50W GU10 927 25DUK	1,000 cd
929001347102	MAS LED ExpertColor 5.5-50W GU10 930 25D	1,000 cd

MASTER LEDspot ExpertColor MV

Order Code	Full Product Name	Luminous Intensity (Nom)
929001347108	MAS LED ExpertColor 5.5-50W GU10 930 24D	1,000 cd
929001347202	MAS LED ExpertColor 5.5-50W GU10 940 25D	1,050 cd
929001347302	MAS LED ExpertColor 5.5-50W GU10 927 36D	800 cd
929001347308	MAS LED ExpertColor 5.5-50W GU10 927 36D	800 cd
929001347398	MASLED ExpertColor5.5-50W GU10 927 36DUK	800 cd

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929001346402	MAS LED ExpertColor 3.9-35W GU10 927 25D	3.9 W	35 W
929001346502	MAS LED ExpertColor 3.9-35W GU10 930 25D	3.9 W	35 W
929001346602	MAS LED ExpertColor 3.9-35W GU10 940 25D	3.9 W	35 W
929001346702	MAS LED ExpertColor 3.9-35W GU10 927 36D	3.9 W	35 W
929001346802	MAS LED ExpertColor 3.9-35W GU10 930 36D	3.9 W	35 W
929001346902	MAS LED ExpertColor 3.9-35W GU10 940 36D	3.9 W	35 W
929001347002	MAS LED ExpertColor 5.5-50W GU10 927 25D	5.5 W	50 W
929001347008	MAS LED ExpertColor 5.5-50W GU10 927 24D	5.5 W	50 W
929001347099	MASLED ExpertColor5.5-50W GU10 927 25DUK	5.5 W	50 W
929001347102	MAS LED ExpertColor 5.5-50W GU10 930 25D	5.5 W	50 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
929001346402	MAS LED ExpertColor 3.9-35W GU10 927 25D	Only with specific dimmers
929001346502	MAS LED ExpertColor 3.9-35W GU10 930 25D	Only with specific dimmers
929001346602	MAS LED ExpertColor 3.9-35W GU10 940 25D	Only with specific dimmers
929001346702	MAS LED ExpertColor 3.9-35W GU10 927 36D	Only with specific dimmers
929001346802	MAS LED ExpertColor 3.9-35W GU10 930 36D	Only with specific dimmers
929001346902	MAS LED ExpertColor 3.9-35W GU10 940 36D	Only with specific dimmers
929001347002	MAS LED ExpertColor 5.5-50W GU10 927 25D	Only with specific dimmers
929001347008	MAS LED ExpertColor 5.5-50W GU10 927 24D	Yes

Order Code	Full Product Name	Luminous Intensity (Nom)
929001347402	MAS LED ExpertColor 5.5-50W GU10 930 36D	800 cd
929001347408	MAS LED ExpertColor 5.5-50W GU10 930 36D	800 cd
929001347499	MASLEDExpertColor 5.5-50W GU10 930 36DUK	800 cd
929001347502	MAS LED ExpertColor 5.5-50W GU10 940 36D	800 cd

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929001347108	MAS LED ExpertColor 5.5-50W GU10 930 24D	5.5 W	50 W
929001347202	MAS LED ExpertColor 5.5-50W GU10 940 25D	5.5 W	50 W
929001347302	MAS LED ExpertColor 5.5-50W GU10 927 36D	5.5 W	50 W
929001347308	MAS LED ExpertColor 5.5-50W GU10 927 36D	5.5 W	50 W
929001347398	MASLED ExpertColor5.5-50W GU10 927 36DUK	5.5 W	50 W
929001347402	MAS LED ExpertColor 5.5-50W GU10 930 36D	5.5 W	50 W
929001347408	MAS LED ExpertColor 5.5-50W GU10 930 36D	5.5 W	50 W
929001347499	MASLEDExpertColor 5.5-50W GU10 930 36DUK	5.5 W	50 W
929001347502	MAS LED ExpertColor 5.5-50W GU10 940 36D	5.5 W	50 W

Order Code	Full Product Name	Dimmable
929001347099	MASLED ExpertColor5.5-50W GU10 927 25DUK	Only with specific dimmers
929001347102	MAS LED ExpertColor 5.5-50W GU10 930 25D	Only with specific dimmers
929001347108	MAS LED ExpertColor 5.5-50W GU10 930 24D	Yes
929001347202	MAS LED ExpertColor 5.5-50W GU10 940 25D	Only with specific dimmers
929001347302	MAS LED ExpertColor 5.5-50W GU10 927 36D	Only with specific dimmers
929001347308	MAS LED ExpertColor 5.5-50W GU10 927 36D	Yes
929001347398	MASLED ExpertColor5.5-50W GU10 927 36DUK	Only with specific dimmers
929001347402	MAS LED ExpertColor 5.5-50W GU10 930 36D	Only with specific dimmers
929001347408	MAS LED ExpertColor 5.5-50W GU10 930 36D	Yes

MASTER LEDspot ExpertColor MV

Order Code	Full Product Name	Dimmable
929001347499	MASLEDExpertColor 5.5-50W GU10 930 36DUK	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929001347502	MAS LED ExpertColor 5.5-50W GU10 940 36D	Only with specific dimmers





Mechanical and Housing


Order Code	Full Product Name	Bulb Finish
929001346402	MAS LED ExpertColor 3.9-35W GU10 927 25D	-
929001346502	MAS LED ExpertColor 3.9-35W GU10 930 25D	-
929001346602	MAS LED ExpertColor 3.9-35W GU10 940 25D	-
929001346702	MAS LED ExpertColor 3.9-35W GU10 927 36D	-
929001346802	MAS LED ExpertColor 3.9-35W GU10 930 36D	-
929001346902	MAS LED ExpertColor 3.9-35W GU10 940 36D	Clear
929001347002	MAS LED ExpertColor 5.5-50W GU10 927 25D	Clear
929001347008	MAS LED ExpertColor 5.5-50W GU10 927 24D	-
929001347099	MASLED ExpertColor5.5-50W GU10 927 25DUK	-
929001347102	MAS LED ExpertColor 5.5-50W GU10 930 25D	Clear

Order Code	Full Product Name	Bulb Finish
929001347108	MAS LED ExpertColor 5.5-50W GU10 930 24D	-
929001347202	MAS LED ExpertColor 5.5-50W GU10 940 25D	-
929001347302	MAS LED ExpertColor 5.5-50W GU10 927 36D	-
929001347308	MAS LED ExpertColor 5.5-50W GU10 927 36D	-
929001347398	MASLED ExpertColor5.5-50W GU10 927 36DUK	-
929001347402	MAS LED ExpertColor 5.5-50W GU10 930 36D	-
929001347408	MAS LED ExpertColor 5.5-50W GU10 930 36D	-
929001347499	MASLEDExpertColor 5.5-50W GU10 930 36DUK	-
929001347502	MAS LED ExpertColor 5.5-50W GU10 940 36D	-

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001346402	MAS LED ExpertColor 3.9-35W GU10 927 25D	4 kWh
929001346502	MAS LED ExpertColor 3.9-35W GU10 930 25D	4 kWh
929001346602	MAS LED ExpertColor 3.9-35W GU10 940 25D	4 kWh
929001346702	MAS LED ExpertColor 3.9-35W GU10 927 36D	4 kWh
929001346802	MAS LED ExpertColor 3.9-35W GU10 930 36D	4 kWh
929001346902	MAS LED ExpertColor 3.9-35W GU10 940 36D	4 kWh
929001347002	MAS LED ExpertColor 5.5-50W GU10 927 25D	6 kWh
929001347008	MAS LED ExpertColor 5.5-50W GU10 927 24D	6 kWh
929001347099	MASLED ExpertColor5.5-50W GU10 927 25DUK	6 kWh
929001347102	MAS LED ExpertColor 5.5-50W GU10 930 25D	6 kWh
929001347108	MAS LED ExpertColor 5.5-50W GU10 930 24D	6 kWh
929001347202	MAS LED ExpertColor 5.5-50W GU10 940 25D	6 kWh
929001347302	MAS LED ExpertColor 5.5-50W GU10 927 36D	6 kWh
929001347308	MAS LED ExpertColor 5.5-50W GU10 927 36D	6 kWh
929001347398	MASLED ExpertColor5.5-50W GU10 927 36DUK	6 kWh
929001347402	MAS LED ExpertColor 5.5-50W GU10 930 36D	6 kWh
929001347408	MAS LED ExpertColor 5.5-50W GU10 930 36D	6 kWh
929001347499	MASLEDExpertColor 5.5-50W GU10 930 36DUK	6 kWh
929001347502	MAS LED ExpertColor 5.5-50W GU10 940 36D	6 kWh







120°


90°

60°


MASTER LEDspot ExpertColor MV




Accent Diagrams




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 927 25D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 930 25D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 940 25D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 927 36D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 930 36D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 940 36D



Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 927 25DUK




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 930 24D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 940 25D

MASTER LEDspot ExpertColor MV


Accent Diagrams



Accent Diagram - MASLED ExpertColor5.5-50W
GU10 927 36DUK




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 930 36D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 940 36D


Beam Diagrams




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 927 25D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 930 25D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 940 25D



Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 927 36D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 930 36D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 940 36D


Beam Diagrams




Beam diagram - MASLED ExpertColor5.5-50W GU10 927 25DUK




Beam diagram - MAS LED ExpertColor 5.5-50W GU10 930 24D




Beam diagram - MAS LED ExpertColor 5.5-50W GU10 940 25D



Beam diagram - MASLED ExpertColor5.5-50W GU10 927 36DUK



Beam diagram - MAS LED ExpertColor 5.5-50W GU10 930 36D



Beam diagram - MAS LED ExpertColor 5.5-50W GU10 940 36D

