



For top performance and sustainability

MASTER LEDspot ExpertColor MV

MASTER LEDspot MV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates ambience with superior lighting that has a customised spectrum, high CRI and deep dimming features. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot LV lamps.

Benefits

- Create a warm and comfortable ambience with MASTER LED GU10
- A hassle-free retrofit solution for greater energy efficiency and sustainability
- Interior decor, furnishings and fabrics look great

Features


- Customised colour spectrum replicates halogen light colour
- Best-in-class colour realisation CRI97, R9>85
- Retrofittable with main-voltage GU10 halogen lamps
- Deep and smooth dimming with broad transformer compatibility

Application

- Hospitality
- Retail
- Residential

MASTER LEDspot ExpertColor MV

Dimensional drawing



Product	D	C
MAS LED ExpertColor 3.9-35W GU10 927 25D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 927 36D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 930 25D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 930 36D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 940 25D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 940 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 930 25D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 940 25D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 940 36D	50 mm	54 mm
MASLED ExpertColor5.5-50W GU10 927 25DUK	50 mm	54 mm
MASLED ExpertColor5.5-50W GU10 927 36DUK	50 mm	54 mm
MASLEDExpertColor 5.5-50W GU10 930 36DUK	50 mm	54 mm

General Information	
Cap base	GU10
Switching Cycle	50,000
Nominal lifetime	40,000 h
Light Technical	
Colour rendering index (CRI)	97
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting time (nom.)	0.5 s
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb shape	PAR16

Light Technical (1/2)

		Correlated Colour			
		Beam angle	Temperature	Colour	Luminous
Order Code	Full Product Name	(nom.)	(Nom)	Code	Flux
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	25 degree(s)	2700 K	927	265 lm
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	25 degree(s)	3000 K	930	280 lm
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	25 degree(s)	4000 K	940	300 lm
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	36 degree(s)	2700 K	927	265 lm
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	36 degree(s)	3000 K	930	280 lm
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	36 degree(s)	4000 K	940	300 lm
70761601	MASLED ExpertColor5.5-50W GU10 927 25DUK	25 degree(s)	2700 K	927	355 lm
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	25 degree(s)	3000 K	930	375 lm
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	25 degree(s)	4000 K	940	400 lm
70767801	MASLED ExpertColor5.5-50W GU10 927 36DUK	36 degree(s)	2700 K	927	355 lm
70769201	MASLEDExpertColor 5.5-50W GU10 930 36DUK	36 degree(s)	3000 K	930	375 lm
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	36 degree(s)	4000 K	940	400 lm

Light Technical (2/2)

Order Code	Full Product Name	Luminous intensity (nom.)
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	700 cd
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	750 cd

Order Code	Full Product Name	Luminous intensity (nom.)
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	800 cd
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	540 cd

MASTER LEDspot ExpertColor MV

Order Code	Full Product Name	Luminous intensity (nom.)
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	560 cd
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	600 cd
70761601	MASLED ExpertColor5.5-50W GU10 927 25DUK	1,000 cd
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	1,000 cd

Order Code	Full Product Name	Luminous intensity (nom.)
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	1,050 cd
70767801	MASLED ExpertColor5.5-50W GU10 927 36DUK	800 cd
70769201	MASLEDExpertColor 5.5-50W GU10 930 36DUK	800 cd
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	800 cd

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage equivalent
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	3.9 W	35 W
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	3.9 W	35 W
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	3.9 W	35 W
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	3.9 W	35 W
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	3.9 W	35 W
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	3.9 W	35 W

Order Code	Full Product Name	Power Consumption	Wattage equivalent
70761601	MASLED ExpertColor5.5-50W GU10 927 25DUK	5.5 W	50 W
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	5.5 W	50 W
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	5.5 W	50 W
70767801	MASLED ExpertColor5.5-50W GU10 927 36DUK	5.5 W	50 W
70769201	MASLEDExpertColor 5.5-50W GU10 930 36DUK	5.5 W	50 W
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	5.5 W	50 W


Mechanical and Housing









Order Code	Full Product Name	Lamp Finish
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	-
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	-
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	-
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	-
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	-
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	Clear


Order Code	Full Product Name	Lamp Finish
70761601	MASLED ExpertColor5.5-50W GU10 927 25DUK	-
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	Clear
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	-
70767801	MASLED ExpertColor5.5-50W GU10 927 36DUK	-
70769201	MASLEDExpertColor 5.5-50W GU10 930 36DUK	-
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	-

Approval and Application


Order Code	Full Product Name	Energy consumption kWh/1,000 hours
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	4 kWh
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	4 kWh
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	4 kWh
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	4 kWh
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	4 kWh
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	4 kWh
70761601	MASLED ExpertColor5.5-50W GU10 927 25DUK	6 kWh
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	6 kWh
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	6 kWh
70767801	MASLED ExpertColor5.5-50W GU10 927 36DUK	6 kWh
70769201	MASLEDExpertColor 5.5-50W GU10 930 36DUK	6 kWh
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	6 kWh









Accent Diagrams




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 927 25D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 930 25D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 940 25D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 927 36D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 930 36D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 940 36D



Accent Diagram - MASLED ExpertColor5.5-50W
GU10 927 25DUK




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 930 25D




**Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 940 25D**

MASTER LEDspot ExpertColor MV


Accent Diagrams



Accent Diagram - MASLED ExpertColor5.5-50W
GU10 927 36DUK




Accent Diagram - MASLED ExpertColor 5.5-50W
GU10 930 36DUK




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 940 36D


Beam Diagrams




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 927 25D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 930 25D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 940 25D



Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 927 36D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 930 36D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 940 36D


Beam Diagrams




Beam diagram - MASLED ExpertColor5.5-50W
GU10 927 25DUK




Beam diagram - MAS LED ExpertColor 5.5-50W
GU10 930 25D




Beam diagram - MAS LED ExpertColor 5.5-50W
GU10 940 25D



Beam diagram - MASLED ExpertColor5.5-50W
GU10 927 36DUK



Beam diagram - MASLEDEExpertColor 5.5-50W
GU10 930 36DUK



Beam diagram - MAS LED ExpertColor 5.5-50W
GU10 940 36D

