



Pentru performanță și durabilitate de top

MASTER LEDspot ExpertColor MV

MASTER LEDspot MV ExpertColor creează o ambianță caldă și confortabilă pentru spații hoteliere, locuințe și restaurante. Ele oferă iluminare superioară, care are un spectru personalizat, CRI ridicat și caracteristică de reglare/dimare profundă. În plus, designul inovator, curbat, se va potrivi cu aproape orice decor interior, cu aspectul său curat și îngrijit. În plus, cu MASTER LEDspot ExpertColor poți profita de întreaga familie ExpertColor, care include și lămpi LEDspot MR16, LEDspot AR111 și LEDspot PAR. MASTER LEDspot ExpertColor oferă economii uriașe de energie și minimizează costurile de întreținere fără niciun compromis în ceea ce privește calitatea luminii și durata de viață, permițând proprietarilor rezidențiali și de afaceri să obțină o rentabilitate a investiției într-o perioadă scurtă de timp.

Beneficii

- Creați o ambianță caldă și confortabilă cu MASTER LED GU10
- Soluție de modernizare fără probleme pentru o eficiență energetică și durabilitate mai mare
- Decorul interior, mobilierul și Țesăturile arată grozav

Caracteristici


- Spectrul de culori personalizat reproduce culoarea luminii cu halogen;
- Cel mai bună realizare a culorii din clasă CRI97, R9, >85;
- Permite instalarea retrofit pe vechile instalații cu lămpi cu halogen GU10 alimentate direct la rețea/
- Reglare/dimare profundă și lină cu compatibilitate largă cu diferite drivere

Cerere

- Industria hotelieră
- Retail
- Domeniul rezidențial

MASTER LEDspot ExpertColor MV

Cote



Product	D	C
MAS LED ExpertColor 3.9-35W GU10 927 25D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 927 36D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 930 25D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 930 36D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 940 25D	50 mm	54 mm
MAS LED ExpertColor 3.9-35W GU10 940 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 927 25D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 927 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 930 25D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 930 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 940 25D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 940 36D	50 mm	54 mm

Informații generale	
Baza elementului de fixare	GU10
Ciclu de comutare	50.000
Durată de viață nominală	40.000 ore
Date tehnice lumină	
Indice de redare a culorilor (IRC)	97
Factorul de menținere a fluxului luminos al lămpii la sfârșitul duratei de viață nominale (nom.)	70 %
Funcționare și sistem electric	
Frecvență de intrare	De la 50 până la 60 Hz
Frecvență linie	50 to 60 Hz
Timp de pornire (nom.)	0,5 s
Temperatură	
Maximum T-case (nom.)	80 °C
Sisteme de comandă și reglarea intensității luminoase	
Cu reglarea intensității luminoase	Numai cu anumite variatoare
Sistem mecanic și carcasă	
Formă bec	PAR16

Date tehnice lumină (1/2)

Order Code	Full Product Name	Unghi de distribuție luminoasă (nom.)	Temperatură de culoare corelată (nom.)	Cod culoare	Flux luminos
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	25 °	2700 K	927	265 lm
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	25 °	3000 K	930	280 lm
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	25 °	4000 K	940	300 lm
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	36 °	2700 K	927	265 lm
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	36 °	3000 K	930	280 lm
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	36 °	4000 K	940	300 lm
70761600	MASTER LED ExpertColor 5.5-50W GU10 927 25D	25 °	2700 K	927	355 lm
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	25 °	3000 K	930	375 lm
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	25 °	4000 K	940	400 lm
70767800	MASTER LED ExpertColor 5.5-50W GU10 927 36D	36 °	2700 K	927	355 lm
70769200	MASTER LED ExpertColor 5.5-50W GU10 930 36D	36 °	3000 K	930	375 lm
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	36 °	4000 K	940	400 lm

Date tehnice lumină (2/2)

Order Code	Full Product Name	Intensitate luminoasă (nom.)
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	700 cd

Order Code	Full Product Name	Intensitate luminoasă (nom.)
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	750 cd

MASTER LEDspot ExpertColor MV

Order Code	Full Product Name	Intensitate luminoasă (nom.)
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	800 cd
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	540 cd
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	560 cd
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	600 cd
70761600	MASTER LED ExpertColor 5.5-50W GU10 927 25D	1.000 cd

Order Code	Full Product Name	Intensitate luminoasă (nom.)
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	1.000 cd
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	1.050 cd
70767800	MASTER LED ExpertColor 5.5-50W GU10 927 36D	800 cd
70769200	MASTER LED ExpertColor 5.5-50W GU10 930 36D	800 cd
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	800 cd

Funcționare și sistem electric

Order Code	Full Product Name	Consum de curent	Echivalent putere
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	3,9 W	35 W
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	3,9 W	35 W
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	3,9 W	35 W
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	3,9 W	35 W
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	3,9 W	35 W
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	3,9 W	35 W

Order Code	Full Product Name	Consum de curent	Echivalent putere
70761600	MASTER LED ExpertColor 5.5-50W GU10 927 25D	5,5 W	50 W
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	5,5 W	50 W
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	5,5 W	50 W
70767800	MASTER LED ExpertColor 5.5-50W GU10 927 36D	5,5 W	50 W
70769200	MASTER LED ExpertColor 5.5-50W GU10 930 36D	5,5 W	50 W
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	5,5 W	50 W


Sistem mecanic și carcasă









Order Code	Full Product Name	Finisaj bec
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	-
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	-
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	-
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	-
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	-
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	Transparent


Order Code	Full Product Name	Finisaj bec
70761600	MASTER LED ExpertColor 5.5-50W GU10 927 25D	Transparent
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	Transparent
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	-
70767800	MASTER LED ExpertColor 5.5-50W GU10 927 36D	-
70769200	MASTER LED ExpertColor 5.5-50W GU10 930 36D	-
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	-

Aprobare și aplicație


Order Code	Full Product Name	Consum de energie kWh/1000 h
70749400	MASTER LED ExpertColor 3.9-35W GU10 927 25D	4 kWh
70751700	MASTER LED ExpertColor 3.9-35W GU10 930 25D	4 kWh
70753100	MASTER LED ExpertColor 3.9-35W GU10 940 25D	4 kWh
70755500	MASTER LED ExpertColor 3.9-35W GU10 927 36D	4 kWh
70757900	MASTER LED ExpertColor 3.9-35W GU10 930 36D	4 kWh
70759300	MASTER LED ExpertColor 3.9-35W GU10 940 36D	4 kWh
70761600	MASTER LED ExpertColor 5.5-50W GU10 927 25D	6 kWh
70763000	MASTER LED ExpertColor 5.5-50W GU10 930 25D	6 kWh
70765400	MASTER LED ExpertColor 5.5-50W GU10 940 25D	6 kWh
70767800	MASTER LED ExpertColor 5.5-50W GU10 927 36D	6 kWh
70769200	MASTER LED ExpertColor 5.5-50W GU10 930 36D	6 kWh
70771500	MASTER LED ExpertColor 5.5-50W GU10 940 36D	6 kWh









Accent Diagrams




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 927 25D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 930 25D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 940 25D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 927 36D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 930 36D




Accent Diagram - MAS LED ExpertColor
3.9-35W GU10 940 36D



Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 927 25D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 930 25D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 940 25D

MASTER LEDspot ExpertColor MV


Accent Diagrams



Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 927 36D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 930 36D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 940 36D


Beam Diagrams




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 927 25D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 930 25D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 940 25D



Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 927 36D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 930 36D




Beam diagram - MAS LED ExpertColor 3.9-35W
GU10 940 36D


Beam Diagrams




Beam diagram - MAS LED ExpertColor 5.5-50W
GU10 927 25D




Beam diagram - MAS LED ExpertColor 5.5-50W
GU10 930 25D




Beam diagram - MAS LED ExpertColor 5.5-50W
GU10 940 25D



Beam diagram - MAS LED ExpertColor 5.5-50W
GU10 927 36D



Beam diagram - MAS LED ExpertColor 5.5-50W
GU10 930 36D



Beam diagram - MAS LED ExpertColor 5.5-50W
GU10 940 36D

