



Create a warm, welcoming ambience with superior quality lighting

MASTER LEDspot ExpertColor LV

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Benefits

- Create warm and comfortable ambience
- Interior decor, furnishings and fabrics look great
- Hassle-free retrofit solution for greater energy efficiency and sustainability

Features

- Customized color spectrum replicates halogen light color
- Trimless design with beautiful V-groove lens
- Best-in-class color realization CRI97, R9>85
- Deep and smooth dimming with broad transformer compatibility
- Retrofit with low-voltage MR16 halogen lamps with GU5.3 socket




MASTER LEDspot ExpertColor LV

Application

- Hospitality: hotel guest room, corridors, lobby, reception area, restaurants, bars, cafes
- Home: living room, bedrooms, hall way
- Retail: exhibitions, display cabinets, shops, dressing rooms

MASTER LEDspot ExpertColor LV

Dimensional drawing



| Product | D | C |
|--|---------|-------|
| MAS LED MR16 ExpertColor 6.7-50W 927 10D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 927 24D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 927 24D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 927 36D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 927 36D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 930 10D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 930 24D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 930 24D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 930 36D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 930 36D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 930 36D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 940 36D | 50.5 mm | 46 mm |

| Product | D | C |
|--|---------|-------|
| MAS MR16 ExpertColor6.7-50W 927 24D EZ10 | 50.5 mm | 57 mm |
| MAS MR16 ExpertColor6.7-50W 930 24D EZ10 | 50.5 mm | 57 mm |
| MAS MR16 ExpertColor6.7-50W 930 36D EZ10 | 50.5 mm | 57 mm |

| Product | D | C |
|--|---------|-------|
| MAS LED ExpertColor 6.7-35W MR16 927 36D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 930 36D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 7.5-43W MR16 927 36D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 7.5-43W MR16 930 24D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 7.5-43W MR16 930 36D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 7.5-43W MR16 940 24D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 7.5-43W MR16 940 36D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 927 10D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 927 24D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 927 60D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 930 10D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 930 24D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 930 60D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 940 10D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 940 24D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 940 36D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 6.7-35W MR16 940 60D | 50.5 mm | 46 mm |
| MAS LED ExpertColor 7.5-43W MR16 927 24D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 927 60D | 50.5 mm | 46 mm |
| MAS LED MR16 ExpertColor 6.7-50W 930 60D | 50.5 mm | 46 mm |

MASTER LEDspot ExpertColor LV

| General Information | |
|---------------------------------------|----------------------------|
| Switching Cycle | 50,000 |
| Nominal lifetime | 40,000 hour(s) |
| Light Technical | |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | - Hz |
| Line Frequency | - Hz |
| Starting Time (Nom) | 0.5 s |
| Controls and Dimming | |
| Dimmable | Only with specific dimmers |
| Mechanical and Housing | |
| Bulb Shape | MR16 |

General Information

| Order Code | Full Product Name | Cap-Base |
|--------------|--|----------|
| 929003078802 | MAS LED ExpertColor 6.7-35W MR16 927 10D | GU5.3 |
| 929003078902 | MAS LED ExpertColor 6.7-35W MR16 930 10D | GU5.3 |
| 929003079002 | MAS LED ExpertColor 6.7-35W MR16 940 10D | GU5.3 |
| 929003079702 | MAS LED ExpertColor 7.5-43W MR16 927 24D | GU5.3 |
| 929003079802 | MAS LED ExpertColor 7.5-43W MR16 930 24D | GU5.3 |
| 929003079902 | MAS LED ExpertColor 7.5-43W MR16 940 24D | GU5.3 |
| 929003080002 | MAS LED ExpertColor 7.5-43W MR16 927 36D | GU5.3 |
| 929003080102 | MAS LED ExpertColor 7.5-43W MR16 930 36D | GU5.3 |
| 929003080202 | MAS LED ExpertColor 7.5-43W MR16 940 36D | GU5.3 |
| 929003078502 | MAS LED ExpertColor 6.7-35W MR16 927 60D | GU5.3 |
| 929003078508 | MAS LED MR16 ExpertColor 6.7-50W 927 60D | GU5.3 |
| 929003078602 | MAS LED ExpertColor 6.7-35W MR16 930 60D | GU5.3 |
| 929003078608 | MAS LED MR16 ExpertColor 6.7-50W 930 60D | GU5.3 |
| 929003078702 | MAS LED ExpertColor 6.7-35W MR16 940 60D | GU5.3 |
| 929003079102 | MAS LED ExpertColor 6.7-35W MR16 927 24D | GU5.3 |
| 929003079202 | MAS LED ExpertColor 6.7-35W MR16 930 24D | GU5.3 |
| 929003079302 | MAS LED ExpertColor 6.7-35W MR16 940 24D | GU5.3 |
| 929003079402 | MAS LED ExpertColor 6.7-35W MR16 927 36D | GU5.3 |
| 929003079502 | MAS LED ExpertColor 6.7-35W MR16 930 36D | GU5.3 |
| 929003079602 | MAS LED ExpertColor 6.7-35W MR16 940 36D | GU5.3 |
| 929003077008 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | GU5.3 |
| 929003077010 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | GU5.3 |
| 929003077108 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | GU5.3 |
| 929003077110 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | GU5.3 |
| 929003077308 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | GU5.3 |
| 929003077310 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | GU5.3 |
| 929003077408 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | GU5.3 |
| 929003077410 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | GU5.3 |
| 929003077508 | MAS LED MR16 ExpertColor 6.7-50W 940 36D | GU5.3 |
| 929003077918 | MAS MR16 ExpertColor6.7-50W 927 24D EZ10 | EZ10 |
| 929003078018 | MAS MR16 ExpertColor6.7-50W 930 24D EZ10 | EZ10 |
| 929003078318 | MAS MR16 ExpertColor6.7-50W 930 36D EZ10 | EZ10 |
| 929003076710 | MAS LED MR16 ExpertColor 6.7-50W 927 10D | GU5.3 |
| 929003076808 | MAS LED MR16 ExpertColor 6.7-50W 930 10D | GU5.3 |

Light Technical (1/2)

| Order Code | Full Product Name | Beam | Correlated | Color | |
|--------------|--|--------------|-------------------------|-------------|----------------|
| | | Angle (Nom) | Color Temperature (Nom) | index (CRI) | rendering Code |
| 929003078802 | MAS LED ExpertColor 6.7-35W MR16 927 10D | 10 degree(s) | 2700 K | 97 | 927 |
| 929003078902 | MAS LED ExpertColor 6.7-35W MR16 930 10D | 10 degree(s) | 3000 K | 97 | 930 |
| 929003079002 | MAS LED ExpertColor 6.7-35W MR16 940 10D | 10 degree(s) | 4000 K | 97 | 940 |

| Order Code | Full Product Name | Beam | Correlated | Color | |
|--------------|--|--------------|-------------------------|-------------|----------------|
| | | Angle (Nom) | Color Temperature (Nom) | index (CRI) | rendering Code |
| 929003079702 | MAS LED ExpertColor 7.5-43W MR16 927 24D | 24 degree(s) | 2700 K | 92 | 927 |
| 929003079802 | MAS LED ExpertColor 7.5-43W MR16 930 24D | 24 degree(s) | 3000 K | 92 | 930 |
| 929003079902 | MAS LED ExpertColor 7.5-43W MR16 940 24D | 24 degree(s) | 4000 K | 92 | 940 |
| 929003080002 | MAS LED ExpertColor 7.5-43W MR16 927 36D | 36 degree(s) | 2700 K | 92 | 927 |

MASTER LEDspot ExpertColor LV

| Order Code | Full Product Name | Beam Angle (Nom) | Correlated Color | Color rendering index | Color Code |
|--------------|--|------------------|-------------------|-----------------------|------------|
| | | | Temperature (Nom) | (CRI) | |
| 929003080102 | MAS LED ExpertColor 7.5-43W MR16 930 36D | 36 degree(s) | 3000 K | 92 | 930 |
| 929003080202 | MAS LED ExpertColor 7.5-43W MR16 940 36D | 36 degree(s) | 4000 K | 92 | 940 |
| 929003078502 | MAS LED ExpertColor 6.7-35W MR16 927 60D | 60 degree(s) | 2700 K | 97 | 927 |
| 929003078508 | MAS LED MR16 ExpertColor 6.7-50W 927 60D | 60 degree(s) | 2700 K | 97 | 927 |
| 929003078602 | MAS LED ExpertColor 6.7-35W MR16 930 60D | 60 degree(s) | 3000 K | 97 | 930 |
| 929003078608 | MAS LED MR16 ExpertColor 6.7-50W 930 60D | 60 degree(s) | 3000 K | 97 | 930 |
| 929003078702 | MAS LED ExpertColor 6.7-35W MR16 940 60D | 60 degree(s) | 4000 K | 97 | 940 |
| 929003079102 | MAS LED ExpertColor 6.7-35W MR16 927 24D | 24 degree(s) | 2700 K | 97 | 927 |
| 929003079202 | MAS LED ExpertColor 6.7-35W MR16 930 24D | 24 degree(s) | 3000 K | 97 | 930 |
| 929003079302 | MAS LED ExpertColor 6.7-35W MR16 940 24D | 24 degree(s) | 4000 K | 97 | 940 |
| 929003079402 | MAS LED ExpertColor 6.7-35W MR16 927 36D | 36 degree(s) | 2700 K | 97 | 927 |
| 929003079502 | MAS LED ExpertColor 6.7-35W MR16 930 36D | 36 degree(s) | 3000 K | 97 | 930 |
| 929003079602 | MAS LED ExpertColor 6.7-35W MR16 940 36D | 36 degree(s) | 4000 K | 97 | 940 |
| 929003077008 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | 24 degree(s) | 2700 K | 97 | 927 |
| 929003077010 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | 24 degree(s) | 2700 K | 97 | 927 |

Light Technical (2/2)

| Order Code | Full Product Name | Luminous Intensity (Nom) | |
|--------------|--|--------------------------|----------|
| | | Luminous Flux | (Nom) |
| 929003078802 | MAS LED ExpertColor 6.7-35W MR16 927 10D | 410 lm | 4,600 cd |

| Order Code | Full Product Name | Beam Angle (Nom) | Correlated Color | Color rendering index | Color Code |
|--------------|--|------------------|-------------------|-----------------------|------------|
| | | | Temperature (Nom) | (CRI) | |
| 929003077108 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | 24 degree(s) | 3000 K | 97 | 930 |
| 929003077110 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | 24 degree(s) | 3000 K | 97 | 930 |
| 929003077308 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | 36 degree(s) | 2700 K | 97 | 927 |
| 929003077310 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | 36 degree(s) | 2700 K | 97 | 927 |
| 929003077408 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | 36 degree(s) | 3000 K | 97 | 930 |
| 929003077410 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | 36 degree(s) | 3000 K | 97 | 930 |
| 929003077508 | MAS LED MR16 ExpertColor 6.7-50W 940 36D | 36 degree(s) | 4000 K | 97 | 940 |
| 929003077918 | MAS MR16 ExpertColor6.7-50W 927 24D EZ10 | 24 degree(s) | 2700 K | 97 | 927 |
| 929003078018 | MAS MR16 ExpertColor6.7-50W 930 24D EZ10 | 24 degree(s) | 3000 K | 97 | 930 |
| 929003078318 | MAS MR16 ExpertColor6.7-50W 930 36D EZ10 | 36 degree(s) | 3000 K | 97 | 930 |
| 929003076710 | MAS LED MR16 ExpertColor 6.7-50W 927 10D | 10 degree(s) | 2700 K | 97 | 927 |
| 929003076808 | MAS LED MR16 ExpertColor 6.7-50W 930 10D | 10 degree(s) | 3000 K | 97 | 930 |

| Order Code | Full Product Name | Luminous Intensity (Nom) | |
|--------------|--|--------------------------|----------|
| | | Luminous Flux | (Nom) |
| 929003078902 | MAS LED ExpertColor 6.7-35W MR16 930 10D | 430 lm | 4,800 cd |

MASTER LEDspot ExpertColor LV

| Order Code | Full Product Name | Luminous Flux | Luminous Intensity (Nom) |
|--------------|--|---------------|--------------------------|
| 929003079002 | MAS LED ExpertColor 6.7-35W MR16 940 10D | 440 lm | 4,800 cd |
| 929003079702 | MAS LED ExpertColor 7.5-43W MR16 927 24D | 485 lm | 2,400 cd |
| 929003079802 | MAS LED ExpertColor 7.5-43W MR16 930 24D | 500 lm | 2,600 cd |
| 929003079902 | MAS LED ExpertColor 7.5-43W MR16 940 24D | 520 lm | 2,800 cd |
| 929003080002 | MAS LED ExpertColor 7.5-43W MR16 927 36D | 485 lm | 1,400 cd |
| 929003080102 | MAS LED ExpertColor 7.5-43W MR16 930 36D | 500 lm | 1,550 cd |
| 929003080202 | MAS LED ExpertColor 7.5-43W MR16 940 36D | 520 lm | 1,650 cd |
| 929003078502 | MAS LED ExpertColor 6.7-35W MR16 927 60D | 400 lm | 410 cd |
| 929003078508 | MAS LED MR16 ExpertColor 6.7-50W 927 60D | 450 lm | 410 cd |
| 929003078602 | MAS LED ExpertColor 6.7-35W MR16 930 60D | 440 lm | 440 cd |
| 929003078608 | MAS LED MR16 ExpertColor 6.7-50W 930 60D | 480 lm | 440 cd |
| 929003078702 | MAS LED ExpertColor 6.7-35W MR16 940 60D | 440 lm | 440 cd |
| 929003079102 | MAS LED ExpertColor 6.7-35W MR16 927 24D | 420 lm | 2,100 cd |
| 929003079202 | MAS LED ExpertColor 6.7-35W MR16 930 24D | 440 lm | 2,200 cd |
| 929003079302 | MAS LED ExpertColor 6.7-35W MR16 940 24D | 460 lm | 2,200 cd |
| 929003079402 | MAS LED ExpertColor 6.7-35W MR16 927 36D | 420 lm | 1,300 cd |

| Order Code | Full Product Name | Luminous Flux | Luminous Intensity (Nom) |
|--------------|--|---------------|--------------------------|
| 929003079502 | MAS LED ExpertColor 6.7-35W MR16 930 36D | 440 lm | 1,400 cd |
| 929003079602 | MAS LED ExpertColor 6.7-35W MR16 940 36D | 460 lm | 1,400 cd |
| 929003077008 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | 450 lm | 2,200 cd |
| 929003077010 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | 450 lm | 2,200 cd |
| 929003077108 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | 480 lm | 2,400 cd |
| 929003077110 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | 480 lm | 2,400 cd |
| 929003077308 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | 450 lm | 1,350 cd |
| 929003077310 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | 450 lm | 1,350 cd |
| 929003077408 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | 480 lm | 1,450 cd |
| 929003077410 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | 480 lm | 1,450 cd |
| 929003077508 | MAS LED MR16 ExpertColor 6.7-50W 940 36D | 480 lm | 1,450 cd |
| 929003077918 | MAS MR16 ExpertColor6.7-50W 927 24D EZ10 | 450 lm | 2,200 cd |
| 929003078018 | MAS MR16 ExpertColor6.7-50W 930 24D EZ10 | 480 lm | 2,400 cd |
| 929003078318 | MAS MR16 ExpertColor6.7-50W 930 36D EZ10 | 480 lm | 1,450 cd |
| 929003076710 | MAS LED MR16 ExpertColor 6.7-50W 927 10D | 450 lm | 4,500 cd |
| 929003076808 | MAS LED MR16 ExpertColor 6.7-50W 930 10D | 480 lm | 5,000 cd |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Wattage Equivalent |
|--------------|--|-------------------|--------------------|
| 929003078802 | MAS LED ExpertColor 6.7-35W MR16 927 10D | 6.7 W | 35 W |
| 929003078902 | MAS LED ExpertColor 6.7-35W MR16 930 10D | 6.7 W | 35 W |
| 929003079002 | MAS LED ExpertColor 6.7-35W MR16 940 10D | 6.7 W | 35 W |
| 929003079702 | MAS LED ExpertColor 7.5-43W MR16 927 24D | 7.5 W | 43 W |
| 929003079802 | MAS LED ExpertColor 7.5-43W MR16 930 24D | 7.5 W | 43 W |
| 929003079902 | MAS LED ExpertColor 7.5-43W MR16 940 24D | 7.5 W | 43 W |

| Order Code | Full Product Name | Power Consumption | Wattage Equivalent |
|--------------|--|-------------------|--------------------|
| 929003080002 | MAS LED ExpertColor 7.5-43W MR16 927 36D | 7.5 W | 43 W |
| 929003080102 | MAS LED ExpertColor 7.5-43W MR16 930 36D | 7.5 W | 43 W |
| 929003080202 | MAS LED ExpertColor 7.5-43W MR16 940 36D | 7.5 W | 43 W |
| 929003078502 | MAS LED ExpertColor 6.7-35W MR16 927 60D | 6.7 W | 35 W |
| 929003078508 | MAS LED MR16 ExpertColor 6.7-50W 927 60D | 6.7 W | 50 W |
| 929003078602 | MAS LED ExpertColor 6.7-35W MR16 930 60D | 6.7 W | 35 W |

MASTER LEDspot ExpertColor LV

| Order Code | Full Product Name | Power Consumption | Wattage Equivalent |
|--------------|---|-------------------|--------------------|
| 929003078608 | MAS LED MR16 ExpertColor 6.7-50W 930 60D | 6.7 W | 50 W |
| 929003078702 | MAS LED ExpertColor 6.7-35W MR16 940 60D | 6.7 W | 35 W |
| 929003079102 | MAS LED ExpertColor 6.7-35W MR16 927 24D | 6.7 W | 35 W |
| 929003079202 | MAS LED ExpertColor 6.7-35W MR16 930 24D | 6.7 W | 35 W |
| 929003079302 | MAS LED ExpertColor 6.7-35W MR16 940 24D | 6.7 W | 35 W |
| 929003079402 | MAS LED ExpertColor 6.7-35W MR16 927 36D | 6.7 W | 35 W |
| 929003079502 | MAS LED ExpertColor 6.7-35W MR16 930 36D | 6.7 W | 35 W |
| 929003079602 | MAS LED ExpertColor 6.7-35W MR16 940 36D | 6.7 W | 35 W |
| 929003077008 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | 6.7 W | 50 W |
| 929003077010 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | 6.7 W | 50 W |
| 929003077108 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | 6.7 W | 50 W |

| Order Code | Full Product Name | Power Consumption | Wattage Equivalent |
|--------------|---|-------------------|--------------------|
| 929003077110 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | 6.7 W | 50 W |
| 929003077308 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | 6.7 W | 50 W |
| 929003077310 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | 6.7 W | 50 W |
| 929003077408 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | 6.7 W | 50 W |
| 929003077410 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | 6.7 W | 50 W |
| 929003077508 | MAS LED MR16 ExpertColor 6.7-50W 940 36D | 6.7 W | 50 W |
| 929003077918 | MAS MR16 ExpertColor6.7-50W 927 24D EZ10 | 6.7 W | 50 W |
| 929003078018 | MAS MR16 ExpertColor6.7-50W 930 24D EZ10 | 6.7 W | 50 W |
| 929003078318 | MAS MR16 ExpertColor6.7-50W 930 36D EZ10 | 6.7 W | 50 W |
| 929003076710 | MAS LED MR16 ExpertColor 6.7-50W 927 10D | 6.7 W | 50 W |
| 929003076808 | MAS LED MR16 ExpertColor 6.7-50W 930 10D | 6.7 W | 50 W |

Temperature

| Order Code | Full Product Name | T-Case Maximum (Nom) |
|--------------|--|----------------------|
| 929003078802 | MAS LED ExpertColor 6.7-35W MR16 927 10D | 92 °C |
| 929003078902 | MAS LED ExpertColor 6.7-35W MR16 930 10D | 92 °C |
| 929003079002 | MAS LED ExpertColor 6.7-35W MR16 940 10D | 92 °C |
| 929003079702 | MAS LED ExpertColor 7.5-43W MR16 927 24D | 93 °C |
| 929003079802 | MAS LED ExpertColor 7.5-43W MR16 930 24D | 93 °C |
| 929003079902 | MAS LED ExpertColor 7.5-43W MR16 940 24D | 93 °C |
| 929003080002 | MAS LED ExpertColor 7.5-43W MR16 927 36D | 93 °C |
| 929003080102 | MAS LED ExpertColor 7.5-43W MR16 930 36D | 93 °C |
| 929003080202 | MAS LED ExpertColor 7.5-43W MR16 940 36D | 93 °C |
| 929003078502 | MAS LED ExpertColor 6.7-35W MR16 927 60D | 92 °C |
| 929003078508 | MAS LED MR16 ExpertColor 6.7-50W 927 60D | 92 °C |
| 929003078602 | MAS LED ExpertColor 6.7-35W MR16 930 60D | 92 °C |
| 929003078608 | MAS LED MR16 ExpertColor 6.7-50W 930 60D | 92 °C |
| 929003078702 | MAS LED ExpertColor 6.7-35W MR16 940 60D | 92 °C |
| 929003079102 | MAS LED ExpertColor 6.7-35W MR16 927 24D | 92 °C |
| 929003079202 | MAS LED ExpertColor 6.7-35W MR16 930 24D | 92 °C |
| 929003079302 | MAS LED ExpertColor 6.7-35W MR16 940 24D | 92 °C |

| Order Code | Full Product Name | T-Case Maximum (Nom) |
|--------------|--|----------------------|
| 929003079402 | MAS LED ExpertColor 6.7-35W MR16 927 36D | 92 °C |
| 929003079502 | MAS LED ExpertColor 6.7-35W MR16 930 36D | 92 °C |
| 929003079602 | MAS LED ExpertColor 6.7-35W MR16 940 36D | 92 °C |
| 929003077008 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | 92 °C |
| 929003077010 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | 92 °C |
| 929003077108 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | 92 °C |
| 929003077110 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | 92 °C |
| 929003077308 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | 92 °C |
| 929003077310 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | 92 °C |
| 929003077408 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | 92 °C |
| 929003077410 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | 92 °C |
| 929003077508 | MAS LED MR16 ExpertColor 6.7-50W 940 36D | 92 °C |
| 929003077918 | MAS MR16 ExpertColor6.7-50W 927 24D EZ10 | 92 °C |
| 929003078018 | MAS MR16 ExpertColor6.7-50W 930 24D EZ10 | 92 °C |
| 929003078318 | MAS MR16 ExpertColor6.7-50W 930 36D EZ10 | 92 °C |
| 929003076710 | MAS LED MR16 ExpertColor 6.7-50W 927 10D | 92 °C |
| 929003076808 | MAS LED MR16 ExpertColor 6.7-50W 930 10D | 92 °C |







Approval and Application











| Order Code | Full Product Name | Energy Consumption kWh/1000 h |
|--------------|--|-------------------------------|
| 929003078802 | MAS LED ExpertColor 6.7-35W MR16 927 10D | 7 kWh |

| Order Code | Full Product Name | Energy Consumption kWh/1000 h |
|--------------|--|-------------------------------|
| 929003078902 | MAS LED ExpertColor 6.7-35W MR16 930 10D | 7 kWh |



MASTER LEDspot ExpertColor LV

| Order Code | Full Product Name | Energy Consumption kWh/1000 h |
|--------------|--|----------------------------------|
| 929003079002 | MAS LED ExpertColor 6.7-35W MR16 940 10D | 7 kWh |
| 929003079702 | MAS LED ExpertColor 7.5-43W MR16 927 24D | 8 kWh |
| 929003079802 | MAS LED ExpertColor 7.5-43W MR16 930 24D | 8 kWh |
| 929003079902 | MAS LED ExpertColor 7.5-43W MR16 940 24D | 8 kWh |
| 929003080002 | MAS LED ExpertColor 7.5-43W MR16 927 36D | 8 kWh |
| 929003080102 | MAS LED ExpertColor 7.5-43W MR16 930 36D | 8 kWh |
| 929003080202 | MAS LED ExpertColor 7.5-43W MR16 940 36D | 8 kWh |
| 929003078502 | MAS LED ExpertColor 6.7-35W MR16 927 60D | 7 kWh |
| 929003078508 | MAS LED MR16 ExpertColor 6.7-50W 927 60D | - |
| 929003078602 | MAS LED ExpertColor 6.7-35W MR16 930 60D | 7 kWh |
| 929003078608 | MAS LED MR16 ExpertColor 6.7-50W 930 60D | - |
| 929003078702 | MAS LED ExpertColor 6.7-35W MR16 940 60D | 7 kWh |
| 929003079102 | MAS LED ExpertColor 6.7-35W MR16 927 24D | 7 kWh |
| 929003079202 | MAS LED ExpertColor 6.7-35W MR16 930 24D | 7 kWh |
| 929003079302 | MAS LED ExpertColor 6.7-35W MR16 940 24D | 7 kWh |
| 929003079402 | MAS LED ExpertColor 6.7-35W MR16 927 36D | 7 kWh |
| 929003079502 | MAS LED ExpertColor 6.7-35W MR16 930 36D | 7 kWh |
| 929003079602 | MAS LED ExpertColor 6.7-35W MR16 940 36D | 7 kWh |
| 929003077008 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | - |
| 929003077010 | MAS LED MR16 ExpertColor 6.7-50W 927 24D | - |
| 929003077108 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | - |
| 929003077110 | MAS LED MR16 ExpertColor 6.7-50W 930 24D | - |
| 929003077308 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | - |
| 929003077310 | MAS LED MR16 ExpertColor 6.7-50W 927 36D | - |
| 929003077408 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | - |
| 929003077410 | MAS LED MR16 ExpertColor 6.7-50W 930 36D | - |
| 929003077508 | MAS LED MR16 ExpertColor 6.7-50W 940 36D | - |
| 929003077918 | MAS MR16 ExpertColor6.7-50W 927 24D EZ10 | - |
| 929003078018 | MAS MR16 ExpertColor6.7-50W 930 24D EZ10 | - |
| 929003078318 | MAS MR16 ExpertColor6.7-50W 930 36D EZ10 | - |
| 929003076710 | MAS LED MR16 ExpertColor 6.7-50W 927 10D | - |
| 929003076808 | MAS LED MR16 ExpertColor 6.7-50W 930 10D | - |







MASTER LEDspot ExpertColor LV




Accent Diagrams



Accent Diagram - MAS LED MR16 ExpertColor
6.7-50W 927 36D




Accent Diagram - MAS LED ExpertColor
7.5-43W MR16 930 36D




Accent Diagram - MAS LED
ExpertColor 6.7-35W MR16 927 24D


Accent Diagrams




Accent Diagram - MAS LED ExpertColor
6.7-35W MR16 930 36D




Accent Diagram - MAS LED
ExpertColor 6.7-35W MR16 930 24D




Accent Diagram - MAS LED ExpertColor
7.5-43W MR16 930 24D




Accent Diagram - MAS LED
ExpertColor 6.7-35W MR16 927 10D




Accent Diagram - MAS LED MR16 ExpertColor
6.7-50W 930 10D




Accent Diagram - MAS LED MR16 ExpertColor
6.7-50W 930 60D



Accent Diagram - MAS LED MR16 ExpertColor
6.7-50W 927 24D




Accent Diagram - MAS LED ExpertColor
6.7-35W MR16 927 36D




Accent Diagram - MAS LED
ExpertColor 6.7-35W MR16 940 24D


Accent Diagrams




Accent Diagram - MAS LED MR16 ExpertColor
6.7-50W 940 36D




Accent Diagram - MAS LED MR16 ExpertColor
6.7-50W 927 10D




Accent Diagram - MAS LED ExpertColor
7.5-43W MR16 940 24D




Accent Diagram - MAS LED ExpertColor
7.5-43W MR16 927 36D




Accent Diagram - MAS LED
ExpertColor 7.5-43W MR16 927 24D




Accent Diagram - MAS LED MR16 ExpertColor
6.7-50W 927 60D



Accent Diagram - MAS LED
ExpertColor 6.7-35W MR16 940 36D




Accent Diagram - MAS LED ExpertColor
7.5-43W MR16 940 36D




Accent Diagram - MAS LED
ExpertColor 6.7-35W MR16 930 10D

Accent Diagrams




Accent Diagram - MAS MR16
ExpertColor6.7-50W 930 24D EZ10


Beam Diagrams




Beam diagram - MAS LED ExpertColor 6.7-35W
MR16 930 10D




Beam diagram - MAS MR16
ExpertColor6.7-50W 930 24D EZ10




Beam diagram - MAS LED ExpertColor 6.7-35W
MR16 940 36D



Beam diagram - MAS LED MR16 ExpertColor
6.7-50W 927 60D




Beam diagram - MAS LED ExpertColor 6.7-35W
MR16 930 24D




Beam diagram - MAS LED MR16 ExpertColor
6.7-50W 927 24D


Beam Diagrams




Beam diagram - MAS LED ExpertColor 7.5-43W
MR16 927 36D




Beam diagram - MAS LED ExpertColor 6.7-35W
MR16 930 36D




Beam diagram - MAS LED ExpertColor 6.7-35W
MR16 927 10D




Beam diagram - MAS LED MR16 ExpertColor
6.7-50W 940 36D




Beam diagram - MAS LED ExpertColor 7.5-43W
MR16 930 36D




Beam diagram - MAS LED MR16 ExpertColor
6.7-50W 930 60D



Beam diagram - MAS LED ExpertColor 6.7-35W
MR16 927 24D




Beam diagram - MAS LED MR16 ExpertColor
6.7-50W 927 10D




Beam diagram - MAS LED ExpertColor 7.5-43W
MR16 927 24D


Beam Diagrams




Beam diagram - MAS LED ExpertColor 6.7-35W MR16 940 24D




Beam diagram - MAS LED MR16 ExpertColor 6.7-50W 930 10D




Beam diagram - MAS LED ExpertColor 7.5-43W MR16 930 24D




Beam diagram - MAS LED ExpertColor 6.7-35W MR16 927 36D



Beam diagram - MAS LED ExpertColor 7.5-43W MR16 940 36D



Beam diagram - MAS LED ExpertColor 7.5-43W MR16 940 24D



Beam diagram - MAS LED MR16 ExpertColor 6.7-50W 927 36D

