



Your everyday LEDspot GU10

Essential LEDspot GU10

Essential LEDspots are compatible with most existing fixtures with a GU10 socket and are designed as a retrofit replacement for halogen spots. Essential LEDspots deliver significant energy savings and minimize initial investment.

Benefits

- Up to 90% energy saving compared with traditional halogen lamps
- Lower maintenance costs
- Low initial investment

Features

- Easy retrofit
- Lifetime up to 15,000 hours
- Non-dimmable
- UV- and IR-free light

Application

- Domestic applications

Essential LEDspot GU10

Versions



LEDspot 50W GU10 830 35D



CorePro LEDspot MV 25W GU10 830 36D



LEDspot 50W GU10 PAR16 827-865 36D ND



LEDspot 25W GU10 MR11 827 36D ND




LEDspots LATAM1 AR111 GU10



MZD LED 50W GU10 830 60D ND



LEDspots K R PAR16 GU10




LEDCLA GU10 220-240V 36D ND



LEDspots K S PAR16 GU10





Dimensional drawing



Product	D	C
6W (50W) GU10 Warm white Dimmable Spot	50 mm	53 mm
Corepro LEDspot 4.6-50W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 865 36D	50 mm	54 mm
LEDspot GU10 6-50W D 830 35D 120V 1PF/6	50 mm	53 mm
LEDspot GU10 6-50W D 830 35D 120V 3CT/6	50 mm	53 mm
LEDspot GU10 6-50W D 865 35D 120V 1PF/6	50 mm	54 mm

Essential LEDspot GU10

Dimensional drawing



Product	D	C
ESS LEDspots 50W GU10 827 36D ND TR	50 mm	54 mm
ESS LEDspots 50W GU10 830 36D ND TR	50 mm	54 mm
ESS LEDspots 50W GU10 840 36D ND TR	50 mm	54 mm
ESS LEDspots 50W GU10 865 36D ND TR	50 mm	54 mm





Product	D	C
CorePro LEDspot 4.9-65W GU10 830 36D	50 mm	54 mm
CorePro LEDspot 4.9-65W GU10 865 36D	50 mm	54 mm
LEDspot GU10 6-50W D 850 35D 120V 3CT/6	50 mm	53 mm

Product	D	C
LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	50.5 mm	54.5 mm
LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	50.5 mm	54.5 mm
LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	50.5 mm	54.5 mm
LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	50.5 mm	54.5 mm
LEDClassic 35W GU10 827 100-240V 36D ND	50.5 mm	54.5 mm
LEDClassic 35W GU10 865 100-240V 36D ND	50.5 mm	54.5 mm
LEDClassic 50W GU10 827 100-240V 40D ND	50.5 mm	54.5 mm
LEDClassic 50W GU10 865 100-240V 40D ND	50.5 mm	54.5 mm
LEDspot 4-50W GU10 827 100-240V 36D ND	50.5 mm	54.5 mm
LEDspot 4-50W GU10 865 100-240V 36D ND	50.5 mm	54.5 mm

Product	D	C
LEDspot50W GU10Kit_R 827 100-240V 36D	50 mm	54 mm
LEDspot50W GU10Kit_R 865 100-240V 36D	50 mm	54 mm
LEDspot50W GU10Kit_R 865 100-240V 36D 2P	50 mm	54 mm

Essential LEDspot GU10

Dimensional drawing



Product	D	C
Corepro LEDspot 670lm GU10 830 60D	50 mm	54 mm
Corepro LEDspot 730lm GU10 865 60D	50 mm	54 mm

Product	D	C
LED MR11 GU10 25W 36D 6500K ND	36 mm	50 mm
MR11 3.5W-25W 250lm 36D 2700K GU10 ND	36 mm	50 mm

Product	D	C
LEDspot50W GU10Kit_S 827 100-240V 36D PF	50 mm	54 mm
LEDspot50W GU10Kit_S 865 100-240V 36D PF	50 mm	54 mm

Product	D	C
LEDspot 70W AR111GU10 827 220-240V 30DND	111 mm	65 mm
LEDspot 70W AR111GU10 865 220-240V 30DND	111 mm	65 mm

Essential LEDspot GU10

General Information	
Cap-Base	GU10
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s

General Information

Order Code	Full Product Name	Switching Cycle	Nominal lifetime
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	50,000	25,000 hour(s)
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	50,000	25,000 hour(s)
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	50,000	25,000 hour(s)
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	50,000	25,000 hour(s)
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	50,000	25,000 hour(s)
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	50,000	25,000 hour(s)
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	50,000	25,000 hour(s)
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	50,000	25,000 hour(s)
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	50,000	25,000 hour(s)
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	50,000	25,000 hour(s)
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	50,000	25,000 hour(s)
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	50,000	25,000 hour(s)
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	50,000	15,000 hour(s)
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	50,000	25,000 hour(s)
929002981071	CorePro LEDspot 4.9-65W GU10 830 36D	50,000	15,000 hour(s)
929003739971	CorePro LEDspot 4.9-65W GU10 865 36D	50,000	15,000 hour(s)
929001218182	Corepro LEDspot 4.6-50W GU10 830 36D	50,000	15,000 hour(s)

Order Code	Full Product Name	Switching Cycle	Nominal lifetime
929001218382	Corepro LEDspot 4.6-50W GU10 865 36D	50,000	15,000 hour(s)
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	15,000	15,000 hour(s)
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	15,000	15,000 hour(s)
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	15,000	15,000 hour(s)
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	50,000	25,000 hour(s)
929001912141	LED MR11 GU10 25W 36D 6500K ND	50,000	25,000 hour(s)
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	50,000	25,000 hour(s)
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	50,000	25,000 hour(s)
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	15,000	15,000 hour(s)
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	50,000	15,000 hour(s)
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	50,000	15,000 hour(s)
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	50,000	15,000 hour(s)
929001266441	6W (50W) GU10 Warm white Dimmable Spot	50,000	25,000 hour(s)
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	50,000	15,000 hour(s)
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	50,000	15,000 hour(s)
929002466781	Corepro LEDspot 670lm GU10 830 60D	50,000	25,000 hour(s)
929002466981	Corepro LEDspot 730lm GU10 865 60D	50,000	25,000 hour(s)

Light Technical

Essential LEDspot GU10

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Color rendering		Luminous Intensity	
			Temperature (Nom)		index (CRI)	Color Code	Luminous Flux	(Nom)
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	36 degree(s)	2700 K		80	827	350 lm	540 cd
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	36 degree(s)	2700 K		80	827	350 lm	540 cd
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	36 degree(s)	2700 K		80	827	350 lm	540 cd
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	36 degree(s)	2700 K		80	827	350 lm	540 cd
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	36 degree(s)	6500 K		80	865	350 lm	540 cd
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	36 degree(s)	6500 K		80	865	350 lm	540 cd
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	36 degree(s)	6500 K		80	865	350 lm	540 cd
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	36 degree(s)	6500 K		80	865	350 lm	540 cd
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	40 degree(s)	2700 K		80	827	525 lm	540 cd
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	40 degree(s)	6500 K		80	865	525 lm	540 cd
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	35 degree(s)	3000 K		90	930	400 lm	600 cd
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	35 degree(s)	3000 K		90	930	400 lm	600 cd
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	35 degree(s)	5000 K		80	850	400 lm	600 cd
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	35 degree(s)	6500 K		90	965	400 lm	600 cd
929002981071	CorePro LEDspot 4.9-65W GU10 830 36D	36 degree(s)	3000 K		80	830	520 lm	800 cd
929003739971	CorePro LEDspot 4.9-65W GU10 865 36D	36 degree(s)	6500 K		80	865	550 lm	1,000 cd
929001218182	Corepro LEDspot 4.6-50W GU10 830 36D	36 degree(s)	3000 K		80	830	410 lm	740 cd
929001218382	Corepro LEDspot 4.6-50W GU10 865 36D	36 degree(s)	6500 K		80	865	430 lm	770 cd
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	36 degree(s)	4000 K		80	840	430 lm	750 cd
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	36 degree(s)	6500 K		80	865	430 lm	750 cd
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	36 degree(s)	3000 K		80	830	400 lm	700 cd
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	36 degree(s)	2700 K		80	827	250 lm	450 cd
929001912141	LED MR11 GU10 25W 36D 6500K ND	36 degree(s)	6500 K		80	865	250 lm	450 cd
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	30 degree(s)	2700 K		80	827	1,000 lm	3,500 cd
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	30 degree(s)	6500 K		80	865	1,100 lm	3,500 cd
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	36 degree(s)	2700 K		80	827	400 lm	700 cd
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	36 degree(s)	2700 K		80	827	350 lm	600 cd
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	36 degree(s)	6500 K		80	865	350 lm	600 cd
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	36 degree(s)	6500 K		80	865	350 lm	600 cd
929001266441	6W (50W) GU10 Warm white Dimmable Spot	35 degree(s)	3000 K		90	930	400 lm	600 cd
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	36 degree(s)	6500 K		80	865	350 lm	600 cd
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	36 degree(s)	2700 K		80	827	350 lm	600 cd
929002466781	Corepro LEDspot 670lm GU10 830 60D	60 degree(s)	3000 K		80	830	840 lm	750 cd
929002466981	Corepro LEDspot 730lm GU10 865 60D	60 degree(s)	6500 K		80	865	900 lm	750 cd

Operating and Electrical

Order Code	Full Product	Input	Line	Power	Wattage	Order Code	Full Product	Input	Line	Power	Wattage
	Name	Frequency	Frequency	Consumption	Equivalent		Name	Frequency	Frequency	Consumption	Equivalent
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	4 W	35 W	929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	4 W	50 W
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	50 to 60 Hz	50 to 60 Hz	4 W	50 W	929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	4 W	35 W
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	50 to 60 Hz	50 to 60 Hz	4 W	50 W	929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	50 to 60 Hz	50 to 60 Hz	4 W	50 W

Essential LEDspot GU10

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	50 to 60 Hz	50 to 60 Hz	4 W	50 W
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	4 W	50 W
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	50 to 60 Hz	50 to 60 Hz	4.8 W	50 W
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	50 to 60 Hz	50 to 60 Hz	4.8 W	50 W
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	60 Hz	60 Hz	6 W	50 W
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	60 Hz	60 Hz	6 W	50 W
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	60 Hz	60 Hz	6 W	50 W
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	50 to 60 Hz	50 to 60 Hz	6 W	50 W
929002981071	CorePro LEDspot 4.9-65W GU10 830 36D	50 to 60 Hz	-	4.9 W	65 W
929003739971	CorePro LEDspot 4.9-65W GU10 865 36D	50 to 60 Hz	-	4.9 W	65 W
929001218182	Corepro LEDspot 4.6-50W GU10 830 36D	50 to 60 Hz	-	4.6 W	50 W
929001218382	Corepro LEDspot 4.6-50W GU10 865 36D	50 to 60 Hz	-	4.6 W	50 W
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	50 to 60 Hz	50 to 60 Hz	4.7 W	50 W
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	50 to 60 Hz	50 to 60 Hz	4.7 W	50 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	50 to 60 Hz	50 to 60 Hz	4.7 W	50 W
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	50 to 60 Hz	50 to 60 Hz	3.5 W	25 W
929001912141	LED MR11 GU10 25W 36D 6500K ND	50 to 60 Hz	50 to 60 Hz	3.5 W	25 W
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	50 to 60 Hz	50 to 60 Hz	12 W	70 W
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	50 to 60 Hz	50 to 60 Hz	12 W	70 W
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	50 to 60 Hz	50 to 60 Hz	4.7 W	50 W
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001266441	6W (50W) GU10 Warm white Dimmable Spot	60 Hz	60 Hz	6 W	50 W
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929002466781	Corepro LEDspot 670lm GU10 830 60D	50 to 60 Hz	-	6.7 W	90 W
929002466981	Corepro LEDspot 730lm GU10 865 60D	50 to 60 Hz	-	6.7 W	100 W

Essential LEDspot GU10

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	70 °C
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	70 °C
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	70 °C
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	70 °C
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	70 °C
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	70 °C
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	70 °C
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	70 °C
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	70 °C
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	70 °C
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	72 °C
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	72 °C
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	85 °C
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	72 °C
929002981071	CorePro LEDspot 4.9-65W GU10 830 36D	75 °C
929003739971	CorePro LEDspot 4.9-65W GU10 865 36D	75 °C
929001218182	Corepro LEDspot 4.6-50W GU10 830 36D	75 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001218382	Corepro LEDspot 4.6-50W GU10 865 36D	75 °C
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	75 °C
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	75 °C
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	75 °C
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	70 °C
929001912141	LED MR11 GU10 25W 36D 6500K ND	70 °C
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	70 °C
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	70 °C
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	75 °C
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	75 °C
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	75 °C
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	75 °C
929001266441	6W (50W) GU10 Warm white Dimmable Spot	72 °C
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	75 °C
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	75 °C
929002466781	Corepro LEDspot 670lm GU10 830 60D	75 °C
929002466981	Corepro LEDspot 730lm GU10 865 60D	75 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	No
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	No
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	No
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	No
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	No
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	No
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	No
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	No
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	No
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	No
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	Only with specific dimmers
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	Only with specific dimmers
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	Only with specific dimmers
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	Only with specific dimmers
929002981071	CorePro LEDspot 4.9-65W GU10 830 36D	No
929003739971	CorePro LEDspot 4.9-65W GU10 865 36D	No

Order Code	Full Product Name	Dimmable
929001218182	Corepro LEDspot 4.6-50W GU10 830 36D	No
929001218382	Corepro LEDspot 4.6-50W GU10 865 36D	No
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	No
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	No
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	No
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	No
929001912141	LED MR11 GU10 25W 36D 6500K ND	No
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	No
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	No
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	No
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	No
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	No
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	No
929001266441	6W (50W) GU10 Warm white Dimmable Spot	Only with specific dimmers
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	No
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	No
929002466781	Corepro LEDspot 670lm GU10 830 60D	No
929002466981	Corepro LEDspot 730lm GU10 865 60D	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	-	PAR16
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	-	PAR16

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	-	PAR16
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	-	PAR16

Essential LEDspot GU10

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	-	PAR16
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	-	PAR16
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	-	PAR16
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	-	PAR16
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	-	PAR16
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	-	PAR16
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	Clear	PAR16
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	Clear	PAR16
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	-	PAR16
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	Clear	PAR16
929002981071	CorePro LEDspot 4.9-65W GU10 830 36D	Clear	PAR16
929003739971	CorePro LEDspot 4.9-65W GU10 865 36D	Clear	PAR16
929001218182	Corepro LEDspot 4.6-50W GU10 830 36D	Clear	PAR16
929001218382	Corepro LEDspot 4.6-50W GU10 865 36D	Clear	PAR16
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	-	PAR16
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	-	PAR16
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	-	PAR16

Approval and Application



Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	-	-
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	-	-
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	-	-
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	-	-
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	-	-
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	-	-
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	-	-
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	-	-
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	-	-
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	-	-
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	-20 to +45 °C	-
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	-20 to +45 °C	-
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	-	-

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	-	MR11
929001912141	LED MR11 GU10 25W 36D 6500K ND	-	MR11
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	-	AR111
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	-	AR111
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	-	PAR16
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	-	PAR16
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	-	PAR16
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	-	PAR16
929001266441	6W (50W) GU10 Warm white Dimmable Spot	Clear	PAR16
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	-	PAR16
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	-	PAR16
929002466781	Corepro LEDspot 670lm GU10 830 60D	Clear	PAR16
929002466981	Corepro LEDspot 730lm GU10 865 60D	Clear	PAR16



Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	-20 to +45 °C	-
929002981071	CorePro LEDspot 4.9-65W GU10 830 36D	-20 to +45 °C	-
929003739971	CorePro LEDspot 4.9-65W GU10 865 36D	-20 to +45 °C	-
929001218182	Corepro LEDspot 4.6-50W GU10 830 36D	-20 to +45 °C	-
929001218382	Corepro LEDspot 4.6-50W GU10 865 36D	-20 to +45 °C	-
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	-20 °C to 40 °C	5 kWh
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	-	5 kWh
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	-	5 kWh
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	-	-
929001912141	LED MR11 GU10 25W 36D 6500K ND	-	-
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	-	-
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	-	-
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	-20 °C to 40 °C	5 kWh

Essential LEDspot GU10


Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	-	-
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	-	-
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	-	-
929001266441	6W (50W) GU10 Warm white Dimmable Spot	-20 to +45 °C	-
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	-	-
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	-	-
929002466781	Corepro LEDspot 670lm GU10 830 60D	-20 to +45 °C	-
929002466981	Corepro LEDspot 730lm GU10 865 60D	-20 to +45 °C	-




Essential LEDspot GU10




Accent Diagrams




Accent Diagram - CorePro LEDspot 4.9-65W GU10 830 36D




Accent Diagram - LEDspot 70W AR111GU10 827 220-240V 30DND




Accent Diagram - Corepro LEDspot 4.6-50W GU10 830 36D




Accent Diagram - CorePro LEDspot 4.9-65W GU10 865 36D




Accent Diagram - LEDspot GU10 6-50W D 865 35D 120V 1PF/6




Accent Diagram - LEDspot GU10 6-50W D 830 35D 120V 1PF/6



Accent Diagram - LEDClassic 50W GU10 827 100-240V 40D ND




Accent Diagram - LEDspot GU10 6-50W D 850 35D 120V 3CT/6




Accent Diagram - ESS LEDspots 50W GU10 827 36D ND TR


Accent Diagrams




Accent Diagram - LEDspot 70W AR111GU10 865 220-240V 30DND




Accent Diagram - LED MR11 GU10 25W 36D 6500K ND




Accent Diagram - Corepro LEDspot 730lm GU10 865 60D




Accent Diagram - LEDspot50W GU10Kit_R 827 100-240V 36D




Accent Diagram - Corepro LEDspot 670lm GU10 830 60D




Accent Diagram - ESS LEDspots 50W GU10 865 36D ND TR



Accent Diagram - ESS LEDspots 50W GU10 830 36D ND TR




Accent Diagram - MR11 3.5W-25W 250lm 36D 2700K GU10 ND




Accent Diagram - LEDClassic 35W GU10 865 100-240V 36D ND

Essential LEDspot GU10


Beam Diagrams




Beam diagram - LEDClassic 35W GU10 865
100-240V 36D ND




Beam diagram - CorePro LEDspot 4.9-65W
GU10 865 36D




Beam diagram - ESS LEDspots 50W GU10 865
36D ND TR




Beam diagram - Corepro LEDspot 4.6-50W
GU10 830 36D




Beam diagram - LEDClassic 50W GU10 827
100-240V 40D ND




Beam diagram - MR11 3.5W-25W 250lm 36D
2700K GU10 ND



Beam diagram - LEDspot GU10 6-50W D 850
35D 120V 3CT/6




Beam diagram - Corepro LEDspot 730lm GU10
865 60D




Beam diagram - ESS LEDspots 50W GU10 827
36D ND TR


Beam Diagrams




Beam diagram - ESS LEDspots 50W GU10 830 36D ND TR




Beam diagram - LEDspot50W GU10Kit_R 827 100-240V 36D




Beam diagram - LEDspot 70W AR111GU10 827 220-240V 30DND




Beam diagram - LEDspot GU10 6-50W D 865 35D 120V 1PF/6




Beam diagram - CorePro LEDspot 4.9-65W GU10 830 36D




Beam diagram - Corepro LEDspot 670lm GU10 830 60D



Beam diagram - LED MR11 GU10 25W 36D 6500K ND



Beam diagram - LEDspot 70W AR111GU10 865 220-240V 30DND



Beam diagram - LEDspot GU10 6-50W D 830 35D 120V 1PF/6

Essential LEDspot GU10

