



The affordable LEDTube T8 solution

Ecofit LED tubes T8

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Benefits

- Up to 50% energy saving compared with conventional fluorescent systems
- Easy installation: retrofit replacement of existing T8 lamps improving the quality of light
- Low initial investment

Features

- Retrofit solution with Long lifetime of 15.000hs
- Up to 50% of energy saving
- Instant on, no flicker or buzz

Application

- Domestic applications
- Small offices and retailers

Ecofit LED tubes T8


Versions




LEDtube Ecofit 16W G13 840 24D ND

LEDtube DE GMGC 9,5W G13

Dimensional drawing



Product	D1	D2	A1	A2	A3
Ecofit LEDtube 1500mm 20W 865 T8 I	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm



Product	D1	D2	A1	A2	A3
Ledtube DE 1200mm 19W 865 T8 G13 EG	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Ecofit LED tubes T8

General Information	
Cap-Base	G13
Switching Cycle	50,000
Light Technical	
Beam Angle (Nom)	240 degree(s)
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	80
Color Code	865
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	T8

General Information

Order Code	Full Product Name	Nominal lifetime
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	15,000 hour(s)
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	20,000 hour(s)

Light Technical

Order Code	Full Product Name	Luminous Flux
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	2,000 lm

Order Code	Full Product Name	Luminous Flux
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	2,350 lm

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	50 to 60 Hz	20 W

Order Code	Full Product Name	Line Frequency	Power Consumption
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	-	19 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	60 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	50 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	-

Order Code	Full Product Name	Bulb Finish
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	Frosted

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929001338222	Ecofit LEDtube 1500mm 20W 865 T8 I	-20 °C to 45 °C	20 kWh

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002468038	Ledtube DE 1200mm 19W 865 T8 G13 EG	-20 to +45 °C	-

Ecofit LED tubes T8

