



The new generation of Mains T5 LEDtube lighting

MASTER LED tube Mains T5

The new Philips Master LEDtube Mains T5 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips MASTER LEDtube Mains T5 installs in luminaires operating on mains power connection. So simple to operate! . Perfectly safe, reliable & easy to install, the Philips MASTER LEDtube Mains T5 is the ideal alternative to standard fluorescent tubes to maximise value over lifetime with high energy savings and lower maintenance costs.

Benefits

- Reduced operational cost thanks to lower energy consumption
- Lower maintenance cost thanks to a longer lifetime than conventional lamps
- The fastest and easiest way to upgrade existing luminaires to LED technology; completely safe product and installation process

Features


- Replacement of existing T5 lamps: operates with mains power connection
- Energy savings compared with fluorescent tubes
- Long lifetime
- Enable implementation of HACCP, supported by product level NSF certificate
- No mercury

Application

- Offices, shops, classrooms
- Industrial facilities and warehouses

MASTER LED tube Mains T5

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm HE 16.5W 840 T5	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1200mm HE 16.5W 865 T5	15.8 mm	19 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube 1500mm HE 20W 840 T5 EU	15.7 mm	19 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 1500mm HE 20W 865 T5 EU	15.7 mm	19 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 1500mm HO 26W 840 T5	15.5 mm	17.1 mm	1,449 mm	1,456 mm	1,463 mm
MAS LEDtube 1500mm UO 36W 830 T5	15.5 mm	18.8 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 1500mm UO 36W 840 T5	15.5 mm	18.8 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube 600mm HE 8W 840 T5	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 600mm HE 8W 865 T5	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube 600mm HO 10.5W 830 T5		19 mm	549 mm	556.1 mm	563.2 mm

General Information	
Cap-Base	G5
Switching Cycle	200,000
Nominal lifetime	50,000 hour(s)
Light Technical	
Beam Angle (Nom)	200 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T5

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929002474802	MAS LEDtube 1500mm UO 36W 830 T5	3000 K	830	5,200 lm
929002474902	MAS LEDtube 1500mm UO 36W 840 T5	4000 K	840	5,600 lm
929001908902	MAS LEDtube 1500mm HO 26W 840 T5	4000 K	840	3,900 lm
929002420708	MAS LEDtube 600mm HE 8W 840 T5	4000 K	840	1,050 lm
929002420808	MAS LEDtube 600mm HE 8W 865 T5	6500 K	865	1,050 lm
929002421008	MAS LEDtube 1200mm HE 16.5W 840 T5	4000 K	840	2,500 lm
929002421108	MAS LEDtube 1200mm HE 16.5W 865 T5	6500 K	865	2,500 lm
929002421302	MAS LEDtube 1500mm HE 20W 840 T5 EU	4000 K	840	3,000 lm
929002421402	MAS LEDtube 1500mm HE 20W 865 T5 EU	6500 K	865	3,000 lm
929003734302	MAS LEDtube 600mm HO 10.5W 830 T5	3000 K	830	1,500 lm

Operating and Electrical

MASTER LED tube Mains T5

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002474802	MAS LEDtube 1500mm UO 36W 830 T5	50 to 60 Hz	36 W
929002474902	MAS LEDtube 1500mm UO 36W 840 T5	50 to 60 Hz	36 W
929001908902	MAS LEDtube 1500mm HO 26W 840 T5	50 to 60 Hz	26 W
929002420708	MAS LEDtube 600mm HE 8W 840 T5	50 to 60 Hz	8 W
929002420808	MAS LEDtube 600mm HE 8W 865 T5	50 to 60 Hz	8 W

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002421008	MAS LEDtube 1200mm HE 16.5W 840 T5	50 to 60 Hz	16.5 W
929002421108	MAS LEDtube 1200mm HE 16.5W 865 T5	50 to 60 Hz	16.5 W
929002421302	MAS LEDtube 1500mm HE 20W 840 T5 EU	50 to 60 Hz	20 W
929002421402	MAS LEDtube 1500mm HE 20W 865 T5 EU	50 to 60 Hz	20 W
929003734302	MAS LEDtube 600mm HO 10.5W 830 T5	-	10.5 W


Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002474802	MAS LEDtube 1500mm UO 36W 830 T5	75 °C
929002474902	MAS LEDtube 1500mm UO 36W 840 T5	75 °C
929001908902	MAS LEDtube 1500mm HO 26W 840 T5	65 °C
929002420708	MAS LEDtube 600mm HE 8W 840 T5	60 °C
929002420808	MAS LEDtube 600mm HE 8W 865 T5	60 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002421008	MAS LEDtube 1200mm HE 16.5W 840 T5	70 °C
929002421108	MAS LEDtube 1200mm HE 16.5W 865 T5	70 °C
929002421302	MAS LEDtube 1500mm HE 20W 840 T5 EU	55 °C
929002421402	MAS LEDtube 1500mm HE 20W 865 T5 EU	55 °C
929003734302	MAS LEDtube 600mm HO 10.5W 830 T5	60 °C

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002474802	MAS LEDtube 1500mm UO 36W 830 T5	-20 °C to 45 °C	36 kWh
929002474902	MAS LEDtube 1500mm UO 36W 840 T5	-20 °C to 45 °C	36 kWh
929001908902	MAS LEDtube 1500mm HO 26W 840 T5	-20 to +45 °C	26 kWh
929002420708	MAS LEDtube 600mm HE 8W 840 T5	-20 °C to 45 °C	8 kWh
929002420808	MAS LEDtube 600mm HE 8W 865 T5	-20 °C to 45 °C	8 kWh
929002421008	MAS LEDtube 1200mm HE 16.5W 840 T5	-20 °C to 45 °C	17 kWh
929002421108	MAS LEDtube 1200mm HE 16.5W 865 T5	-20 °C to 45 °C	17 kWh
929002421302	MAS LEDtube 1500mm HE 20W 840 T5 EU	-20 to +45 °C	20 kWh
929002421402	MAS LEDtube 1500mm HE 20W 865 T5 EU	-20 to +45 °C	20 kWh
929003734302	MAS LEDtube 600mm HO 10.5W 830 T5	-20 to +45 °C	11 kWh



MASTER LED tube Mains T5

