



Classic LED filament lamps for decorative lighting

Classic filament LED candles and lusters

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI above 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LED candles and lusters

Versions



LED classic E27 WW A60 FR ND



LEDbulb CLA A15 E27 CL



LEDclassic 40W B35 E14 CL
WGD90 SRT4 1



LED classic 40W P45 B15 CL
WGD90 SRT4 1



CLA LEDcandle 25W E14 827 FR
P45



LEDbulb CLA T25L E14 CL



LED classic 40W B35 E14
WWFRNDRF2SRT6 UK



LEDbulb CLA G16,5 E27 CL

Classic filament LED candles and lusters

Versions



LEDclassic 40W B35 B15 CL
WGD90 SRT4 1



LED classic T25L E14 CL POS2



LEDcandle Classic 35W E14 P45
Mirror Crown 827 CL ND



LEDbulb CLA B35 E14 TA



LEDclassic 40W P45 E27 CL
WGD90 SRT4 1



LEDbulb 6,6BA11 PER UD CL G E12
E26 WGD 3PF T20



LEDbulb Classic 40W E27 P45 827
CL ND



LED classic 40W P45 B22 CL
WGD90 SRT4 1

Classic filament LED candles and lusters

Versions



LED classic 25W E27 WWA60 CL
ND



LEDclassic 40W B35 B22 CL
WGD90 SRT4 1





LEDclassic 40W B35 E27 CL
WGD90 SRT4 1



LEDclassic 40W P45 E14 WGD90
CL SRT4 1

Dimensional drawing







Product	D	C
LEDclassic 40W B35 2700K E14 D CL AU	35 mm	97 mm

Product	D	C
LED classic 40W P45 E14 WW FR ND RFSRT4	45 mm	80 mm
LEDClassic CM P45 35W WW E14 CL ND SRT4	45 mm	82 mm
LEDclassic 40W P45 2700K E14 D CL AU	45 mm	80 mm

Classic filament LED candles and lusters

Dimensional drawing



Product	D	C
CorePro LEDLusterND4.3-40W E27 827P45CLG	45 mm	82 mm
LEDclassic 40W P45 2700K E27 D CL AU	45 mm	78 mm





Product	D	C
LEDclassic 40W P45 2700K B22 D CL AU	45 mm	77 mm

Product	D	C
LED classic 25W E27 WWA60 CL ND 1PF/6	60 mm	104 mm

Product	D	C
LEDclassic 40W B35 2700K B22 D CL AU	35 mm	94 mm

Classic filament LED candles and lusters

Dimensional drawing



Product	D	C
6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	35 mm	107 mm





Product	D	C
LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	52 mm	87 mm

Product	D	C
LEDClassic 40W P45 2700K B15 D CL AU	45 mm	79 mm

Product	D	C
LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	35 mm	99 mm
LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	35 mm	99 mm
LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	35 mm	99 mm
LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	35 mm	99 mm

Classic filament LED candles and lusters

Dimensional drawing



Product	D	C
LEDclassic 40W B35 2700K E14 ND FR AU	35 mm	97 mm





Product	D	C
LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	35 mm	95 mm
LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	35 mm	95 mm
LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	35 mm	95 mm

Product	D	C
LEDclassic 40W B35 2700K E27 D CL AU	35 mm	95 mm

Product	D	C
LED classic 25W E27 WWA60 FR ND 1PF/6	60 mm	104 mm

Classic filament LED candles and lusters

Dimensional drawing



Product	D	C
LEDCLa 25W B35 E14 825 WV ND+E27 BR/MX	35 mm	114 mm


Product	D	C
LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	48 mm	89 mm

Product	D	C
LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	35 mm	99 mm
LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	35 mm	99 mm
LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	35 mm	99 mm
LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	35 mm	99 mm

Product	D	C
LEDclassic 40W B35 2700K B15 D CL AU	35 mm	96 mm

Classic filament LED candles and lusters

Dimensional drawing



Product	D	C
LED classic 25W T25L E14 CL ND RF SRT4	25 mm	90 mm
LED classic 40W T25L E14 CL ND RF SRT4	25 mm	90 mm

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Switching Cycle	Nominal lifetime
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	E27	- hour(s)	20,000	15,000 hour(s)
929003012279	LEDclassic 40W B35 2700K E14 D CL AU	E14	15,000 hour(s)	20,000	15,000 hour(s)
929003013479	LEDclassic 40W P45 2700K B15 D CL AU	B15	15,000 hour(s)	20,000	15,000 hour(s)
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	E14	15,000 hour(s)	20,000	15,000 hour(s)
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	E14	- hour(s)	20,000	15,000 hour(s)
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	E14	15,000 hour(s)	15,000	15,000 hour(s)
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	E27	- hour(s)	20,000	15,000 hour(s)
929003012579	LEDclassic 40W B35 2700K B15 D CL AU	B15	15,000 hour(s)	20,000	15,000 hour(s)
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	E27	- hour(s)	20,000	15,000 hour(s)
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	E27	- hour(s)	20,000	15,000 hour(s)
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	E27	- hour(s)	20,000	15,000 hour(s)
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	E14	- hour(s)	20,000	15,000 hour(s)
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	E12	- hour(s)	20,000	15,000 hour(s)
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	E12	- hour(s)	20,000	15,000 hour(s)
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	E12	- hour(s)	20,000	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Switching Cycle	Nominal lifetime
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	E12	- hour(s)	20,000	15,000 hour(s)
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	E14	15,000 hour(s)	20,000	15,000 hour(s)
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	E14	- hour(s)	20,000	15,000 hour(s)
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	E14	- hour(s)	20,000	15,000 hour(s)
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	E14	- hour(s)	20,000	15,000 hour(s)
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	E14	- hour(s)	20,000	15,000 hour(s)
929002000616	LEDCla 25W B35 E14 825 WV ND+E27 BR/MX	E14	- hour(s)	20,000	15,000 hour(s)
929003013279	LEDclassic 40W P45 2700K E27 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002986603	6.6BA11/PER/UD/CL/G/ E12+E26/WGD 3PF T20	Universal	15,000 hour(s)	20,000	15,000 hour(s)
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	E27	- hour(s)	20,000	10,000 hour(s)
929003013379	LEDclassic 40W P45 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003012479	LEDclassic 40W B35 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929003012379	LEDclassic 40W B35 2700K E27 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003013179	LEDclassic 40W P45 2700K E14 D CL AU	E14	15,000 hour(s)	20,000	15,000 hour(s)

Classic filament LED candles and lusters

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	LLMF At End Of Nominal Lifetime	
						(Nom)	Luminous Flux
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	-	2700 K	80	827	70 %	250 lm
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	-	5000 K	80	850	70 %	500 lm
929003012279	LEDclassic 40W B35 2700K E14 D CL AU	-	2700 K	90	927	70 %	470 lm
929003013479	LEDclassic 40W P45 2700K B15 D CL AU	-	2700 K	90	927	70 %	470 lm
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	-	2700 K	80	827	70 %	470 lm
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	-	2700 K	80	827	70 %	250 lm
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	-	2700 K	80	827	70 %	470 lm
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	-	2700 K	80	827	70 %	500 lm
929003012579	LEDclassic 40W B35 2700K B15 D CL AU	-	2700 K	90	927	70 %	470 lm
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	-	2700 K	80	827	70 %	500 lm
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	-	2700 K	80	827	70 %	500 lm
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	-	5000 K	80	850	70 %	500 lm
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	-	2700 K	80	827	70 %	470 lm
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	-	2700 K	80	827	70 %	500 lm
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	-	2700 K	80	827	70 %	500 lm
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	-	5000 K	80	850	70 %	500 lm
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	-	5000 K	80	850	70 %	500 lm
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	-	2700 K	80	827	70 %	397 lm
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	-	2700 K	80	827	70 %	500 lm
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	-	2700 K	80	827	70 %	500 lm
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	-	5000 K	80	850	70 %	500 lm
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	-	5000 K	80	850	70 %	500 lm
929002000616	LEDCLa 25W B35 E14 825 WV ND+E27 BR/MX	280 degree(s)	2500 K	80	825	70 %	300 lm
929003013279	LEDclassic 40W P45 2700K E27 D CL AU	-	2700 K	90	927	70 %	470 lm
929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	300 degree(s)	2200 K	95	922-927	0.7 %	700 lm
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	270 degree(s)	2700 K	80	827	70 %	470 lm
929003013379	LEDclassic 40W P45 2700K B22 D CL AU	-	2700 K	90	927	70 %	470 lm
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	-	2700 K	80	827	70 %	250 lm
929003012479	LEDclassic 40W B35 2700K B22 D CL AU	-	2700 K	90	927	70 %	470 lm
929003012379	LEDclassic 40W B35 2700K E27 D CL AU	-	2700 K	90	927	70 %	470 lm
929003013179	LEDclassic 40W P45 2700K E14 D CL AU	-	2700 K	90	927	70 %	470 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	50 to 60 Hz	50 to 60 Hz	2.2 W	0.5 s	25 W
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003012279	LEDclassic 40W B35 2700K E14 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929003013479	LEDclassic 40W P45 2700K B15 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	50 to 60 Hz	50 to 60 Hz	4.3 W	0.5 s	40 W
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	50 to 60 Hz	-	2.1 W	0.5 s	25 W
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	50 to 60 Hz	-	3.5 W	0.4 s	40 W
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003012579	LEDclassic 40W B35 2700K B15 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	50 to 60 Hz	-	4.5 W	0.5 s	40 W

Classic filament LED candles and lusters

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	50 to 60 Hz	50 to 60 Hz	4 W	0.5 s	35 W
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	60 Hz	60 Hz	4.5 W	0.5 s	40 W
929002000616	LEDCla 25W B35 E14 825 WV ND+E27 BR/MX	50 to 60 Hz	50 to 60 Hz	2.7 W	0.5 s	30 W
929003013279	LEDclassic 40W P45 2700K E27 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	60 Hz	60 Hz	6.6 W	0.5 s	75 W
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	50 to 60 Hz	50 to 60 Hz	4.3 W	0.5 s	40 W
929003013379	LEDclassic 40W P45 2700K B22 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	50 to 60 Hz	50 to 60 Hz	2.2 W	0.5 s	25 W
929003012479	LEDclassic 40W B35 2700K B22 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929003012379	LEDclassic 40W B35 2700K E27 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W
929003013179	LEDclassic 40W P45 2700K E14 D CL AU	50 to 60 Hz	-	3.5 W	0.5 s	40 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	30 °C
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	50 °C
929003012279	LEDclassic 40W B35 2700K E14 D CL AU	70 °C
929003013479	LEDclassic 40W P45 2700K B15 D CL AU	70 °C
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	55 °C
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	38 °C
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	55 °C
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	50 °C
929003012579	LEDclassic 40W B35 2700K B15 D CL AU	70 °C
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	55 °C
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	55 °C
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	55 °C
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	57 °C
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	55 °C
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	55 °C
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	55 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	55 °C
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	45 °C
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	55 °C
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	55 °C
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	55 °C
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	55 °C
929002000616	LEDCla 25W B35 E14 825 WV ND+E27 BR/MX	50 °C
929003013279	LEDclassic 40W P45 2700K E27 D CL AU	70 °C
929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	-
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	45 °C
929003013379	LEDclassic 40W P45 2700K B22 D CL AU	70 °C
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	30 °C
929003012479	LEDclassic 40W B35 2700K B22 D CL AU	70 °C
929003012379	LEDclassic 40W B35 2700K E27 D CL AU	70 °C
929003013179	LEDclassic 40W P45 2700K E14 D CL AU	70 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	No
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	No
929003012279	LEDclassic 40W B35 2700K E14 D CL AU	Only with specific dimmers
929003013479	LEDclassic 40W P45 2700K B15 D CL AU	Only with specific dimmers
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	No
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	No

Order Code	Full Product Name	Dimmable
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	No
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	No
929003012579	LEDclassic 40W B35 2700K B15 D CL AU	Only with specific dimmers
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	No
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	No
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	No
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	No

Classic filament LED candles and lusters

Order Code	Full Product Name	Dimmable
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	No
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	No
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	No
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	No
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	No
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	No
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	No
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	No
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	No
929002000616	LEDClas 25W B35 E14 825 WV ND+E27 BR/MX	No
929003013279	LEDclassic 40W P45 2700K E27 D CL AU	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	Only with specific dimmers
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	No
929003013379	LEDclassic 40W P45 2700K B22 D CL AU	Only with specific dimmers
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	No
929003012479	LEDclassic 40W B35 2700K B22 D CL AU	Only with specific dimmers
929003012379	LEDclassic 40W B35 2700K E27 D CL AU	Only with specific dimmers
929003013179	LEDclassic 40W P45 2700K E14 D CL AU	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	Frosted	A60
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	Clear	A15
929003012279	LEDclassic 40W B35 2700K E14 D CL AU	Clear	B35
929003013479	LEDclassic 40W P45 2700K B15 D CL AU	Clear	P45
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	Frosted	P45
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	Clear	T25
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	Frosted	B35
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	Clear	G16.5
929003012579	LEDclassic 40W B35 2700K B15 D CL AU	Clear	B35
929002355242	LEDClassic 4.5W B11 E27 827 CL ND 1PF/10	Clear	B11
929002355272	LEDClassic 4.5W B11 E27 827 CL ND 3CT/10	Clear	B12
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	Clear	B11
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	Clear	T25
929002355142	LEDClassic 4.5W B11 E12 827 CL ND 1PF/10	Clear	B11
929002355172	LEDClassic 4.5W B11 E12 827 CL ND 3CT/10	Clear	B12
929003068442	LEDClassic 4.5W B11 E12 850 CL ND 1PF/10	Clear	B11
929003068448	LEDClassic 4.5W B11 E12 850 CL ND 3CT/10	Clear	B11

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	Mirror Crown	P45
929002355442	LEDClassic 4.5W B11 E14 827 CL ND 1PF/10	Clear	B11
929002355472	LEDClassic 4.5W B11 E14 827 CL ND 3CT/10	Clear	B12
929003068342	LEDClassic 4.5W B11 E14 850 CL ND 1PF/10	Clear	B11
929003068348	LEDClassic 4.5W B11 E14 850 CL ND 3CT/10	Clear	B11
929002000616	LEDClas 25W B35 E14 825 WV ND+E27 BR/MX	Transparent amber	B35
929003013279	LEDclassic 40W P45 2700K E27 D CL AU	Clear	P45
929002986603	6.6BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	Clear	BA11
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	Clear	P45
929003013379	LEDclassic 40W P45 2700K B22 D CL AU	Clear	P45
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	Clear	A60
929003012479	LEDclassic 40W B35 2700K B22 D CL AU	Clear	B35
929003012379	LEDclassic 40W B35 2700K E27 D CL AU	Clear	B35
929003013179	LEDclassic 40W P45 2700K E14 D CL AU	Clear	P45






Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	-	3 kWh
929003068042	LEDClassic 4.5W A15 E27 850 CL ND 1PF/10	-	-
929003012279	LEDclassic 40W B35 2700K E14 D CL AU	-20 to +45 °C	4 kWh
929003013479	LEDclassic 40W P45 2700K B15 D CL AU	-20 to +45 °C	4 kWh











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929001345555	LED classic 40W P45 E14 WW FR ND RFSRT4	-20 °C to 45 °C	5 kWh
929001949028	LED classic 25W T25L E14 CL ND RF SRT4	-20 to +45 °C	3 kWh
929001345380	LEDclassic 40W B35 2700K E14 ND FR AU	-20 to +45 °C	5 kWh
929002355572	LEDClassic4.5W G16.5 E27 827 CLND 3CT/10	-	-

Classic filament LED candles and lusters

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003012579	LEDclassic 40W B35 2700K B15 D CL AU	-20 to +45 °C	4 kWh
929002355242	LEDClassic 4.5W B11 E27 827 CL ND - 1PF/10	-	-
929002355272	LEDClassic 4.5W B11 E27 827 CL ND - 3CT/10	-	-
929003068248	LEDClassic 4.5W B11 E27 850 CL ND 3CT/10	-	-
929001956728	LED classic 40W T25L E14 CL ND RF SRT4	-20 to +45 °C	5 kWh
929002355142	LEDClassic 4.5W B11 E12 827 CL ND - 1PF/10	-	-
929002355172	LEDClassic 4.5W B11 E12 827 CL ND - 3CT/10	-	-
929003068442	LEDClassic 4.5W B11 E12 850 CL ND - 1PF/10	-	-
929003068448	LEDClassic 4.5W B11 E12 850 CL ND - 3CT/10	-	-
929001395155	LEDClassic CM P45 35W WW E14 CL ND SRT4	-	4 kWh
929002355442	LEDClassic 4.5W B11 E14 827 CL ND - 1PF/10	-	-
929002355472	LEDClassic 4.5W B11 E14 827 CL ND - 3CT/10	-	-
929003068342	LEDClassic 4.5W B11 E14 850 CL ND - 1PF/10	-	-
929003068348	LEDClassic 4.5W B11 E14 850 CL ND - 3CT/10	-	-
929002000616	LEDcla 25W B35 E14 825 WV ND +E27 BR/MX	-	-
929003013279	LEDclassic 40W P45 2700K E27 D CL AU	-20 to +45 °C	4 kWh
929002986603	6.6BA11/PER/UD/CL/G/ E12+E26/WGD 3PF T20	-20 °C to 40 °C	-
929001890542	CorePro LEDLusterND4.3-40W E27 827P45CLG	-	5 kWh
929003013379	LEDclassic 40W P45 2700K B22 D CL AU	-20 to +45 °C	4 kWh
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	-	3 kWh
929003012479	LEDclassic 40W B35 2700K B22 D CL AU	-20 to +45 °C	4 kWh
929003012379	LEDclassic 40W B35 2700K E27 D CL AU	-20 to +45 °C	4 kWh
929003013179	LEDclassic 40W P45 2700K E14 D CL AU	-20 to +45 °C	4 kWh



Classic filament LED candles and lusters



Classic filament LED candles and lusters

