



亮度更强、高性能照明让商业表现更为出色

高光通 MASTER LEDspot PAR

飞利浦高亮度 LED PAR30L，相较于传统 CDM PAR30L 相同外形，但光源中集成了业界先进的 COB LED 光源和紧凑高效的驱动器。使该产品可提供具有更高亮度的照明，让商业表现更为出色。此外，该灯具还配备了过温保护 (OTP) 功能，可确保长时间工作和长使用寿命。

优点

- 只需低初始投资，即可实现用 LED CDM 替代 PAR30
- 与标准 CDM 灯相比，节能率高达 43%
- 高效的解决方案 >100 lm/W

特点


- 通过轻松移除传统镇流器即可兼容配备 E27 灯座的 CDM PAR30L 灯具
- 无散热问题且不会褪色
- 25,000 小时的使用寿命
- 无 UV 和 IR 的光
- 不含汞和有害材料 – 符合 RoHS

应用

- 商店、酒店、餐厅、博物馆

高光通 MASTER LEDspot PAR

二维绘图



Product	D	C
Master LED PAR30L 20W 15D 830 CN	95.5 mm	129 mm
Master LED PAR30L 20W 15D 840 CN	95.5 mm	129 mm
Master LED PAR30L 20W 30D 830 CN	95.5 mm	129 mm
Master LED PAR30L 20W 30D 840 CN	95.5 mm	129 mm
Master LED PAR30L 32W 15D 830 CN	95.5 mm	129 mm
Master LED PAR30L 32W 15D 840 CN	95.5 mm	129 mm
Master LED PAR30L 32W 15D 860 CN	95.5 mm	129 mm
Master LED PAR30L 32W 30D 830 CN	95.5 mm	129 mm
Master LED PAR30L 32W 30D 840 CN	95.5 mm	129 mm
Master LED PAR30L 32W 30D 860 CN	95.5 mm	129 mm
Master LED PAR30L 40W 30D 830 CN	95.5 mm	129 mm
Master LED PAR30L 40W 30D 840 CN	95.5 mm	129 mm

一般信息	
底盖	E27
切换循环	50,000
标称使用寿命	25,000 小时
灯技术	
显色指数 (CRI)	82
标称使用寿命结束时灯的光通维持率 (标称)	70 %
操作和电气	
输入频率	50 至 60 Hz
线频率	50 to 60 Hz
启动时间 (标称)	0.5 s
控制和调光	
可调光	否
机械和外壳	
灯泡外形	PAR30L

灯技术 (1/2)

Order Code	Full Product Name	光束角度 (标称)	相关色温 (标称)	颜色代码	光通量
929001353810	Master LED PAR30L 20W 15D 830 CN	15 °	3000 K	830	1,800 lm
929001353910	Master LED PAR30L 20W 15D 840 CN	15 °	4000 K	840	1,850 lm
929001354010	Master LED PAR30L 20W 30D 830 CN	30 °	3000 K	830	1,800 lm
929001354110	Master LED PAR30L 20W 30D 840 CN	30 °	4000 K	840	1,850 lm
929001354310	Master LED PAR30L 32W 15D 830 CN	15 °	3000 K	830	3,000 lm
929001354410	Master LED PAR30L 32W 15D 840 CN	15 °	4000 K	840	3,000 lm
929001354510	Master LED PAR30L 32W 15D 860 CN	15 °	6000 K	860	3,000 lm
929001354710	Master LED PAR30L 32W 30D 830 CN	30 °	3000 K	830	3,000 lm
929001354810	Master LED PAR30L 32W 30D 840 CN	30 °	4000 K	840	3,000 lm
929001354910	Master LED PAR30L 32W 30D 860 CN	30 °	6000 K	860	3,000 lm
929001374810	Master LED PAR30L 40W 30D 830 CN	30 °	3000 K	830	4,500 lm
929001374910	Master LED PAR30L 40W 30D 840 CN	30 °	4000 K	840	4,600 lm

灯技术 (2/2)

Order Code	Full Product Name	发光强度 (标称)
929001353810	Master LED PAR30L 20W 15D 830 CN	18,000 cd
929001353910	Master LED PAR30L 20W 15D 840 CN	-
929001354010	Master LED PAR30L 20W 30D 830 CN	5,400 cd
929001354110	Master LED PAR30L 20W 30D 840 CN	-
929001354310	Master LED PAR30L 32W 15D 830 CN	-
929001354410	Master LED PAR30L 32W 15D 840 CN	-

Order Code	Full Product Name	发光强度 (标称)
929001354510	Master LED PAR30L 32W 15D 860 CN	-
929001354710	Master LED PAR30L 32W 30D 830 CN	-
929001354810	Master LED PAR30L 32W 30D 840 CN	-
929001354910	Master LED PAR30L 32W 30D 860 CN	-
929001374810	Master LED PAR30L 40W 30D 830 CN	13,500 cd
929001374910	Master LED PAR30L 40W 30D 840 CN	14,000 cd

操作和电气

Order Code	Full Product Name	功耗	瓦数相当
929001353810	Master LED PAR30L 20W 15D 830 CN	20 W	35 W

Order Code	Full Product Name	功耗	瓦数相当
929001353910	Master LED PAR30L 20W 15D 840 CN	20 W	35 W

高光通 MASTER LEDspot PAR

Order Code	Full Product Name	功耗	瓦数相当
929001354010	Master LED PAR30L 20W 30D 830 CN	20 W	35 W
929001354110	Master LED PAR30L 20W 30D 840 CN	20 W	35 W
929001354310	Master LED PAR30L 32W 15D 830 CN	32 W	50 W
929001354410	Master LED PAR30L 32W 15D 840 CN	32 W	50 W
929001354510	Master LED PAR30L 32W 15D 860 CN	32 W	50 W

Order Code	Full Product Name	功耗	瓦数相当
929001354710	Master LED PAR30L 32W 30D 830 CN	32 W	50 W
929001354810	Master LED PAR30L 32W 30D 840 CN	32 W	50 W
929001354910	Master LED PAR30L 32W 30D 860 CN	32 W	50 W
929001374810	Master LED PAR30L 40W 30D 830 CN	40 W	70 W
929001374910	Master LED PAR30L 40W 30D 840 CN	40 W	70 W



温度








Order Code	Full Product Name	最大外壳温度 (标称)
929001353810	Master LED PAR30L 20W 15D 830 CN	67 °C
929001353910	Master LED PAR30L 20W 15D 840 CN	67 °C
929001354010	Master LED PAR30L 20W 30D 830 CN	67 °C
929001354110	Master LED PAR30L 20W 30D 840 CN	67 °C
929001354310	Master LED PAR30L 32W 15D 830 CN	79 °C
929001354410	Master LED PAR30L 32W 15D 840 CN	79 °C

Order Code	Full Product Name	最大外壳温度 (标称)
929001354510	Master LED PAR30L 32W 15D 860 CN	79 °C
929001354710	Master LED PAR30L 32W 30D 830 CN	79 °C
929001354810	Master LED PAR30L 32W 30D 840 CN	79 °C
929001354910	Master LED PAR30L 32W 30D 860 CN	79 °C
929001374810	Master LED PAR30L 40W 30D 830 CN	90 °C
929001374910	Master LED PAR30L 40W 30D 840 CN	90 °C


审批和申请

Order Code	Full Product Name	能耗 kWh/1000 h
929001353810	Master LED PAR30L 20W 15D 830 CN	20 kWh
929001353910	Master LED PAR30L 20W 15D 840 CN	20 kWh
929001354010	Master LED PAR30L 20W 30D 830 CN	20 kWh
929001354110	Master LED PAR30L 20W 30D 840 CN	20 kWh
929001354310	Master LED PAR30L 32W 15D 830 CN	32 kWh
929001354410	Master LED PAR30L 32W 15D 840 CN	32 kWh
929001354510	Master LED PAR30L 32W 15D 860 CN	32 kWh
929001354710	Master LED PAR30L 32W 30D 830 CN	32 kWh
929001354810	Master LED PAR30L 32W 30D 840 CN	32 kWh
929001354910	Master LED PAR30L 32W 30D 860 CN	32 kWh
929001374810	Master LED PAR30L 40W 30D 830 CN	40 kWh
929001374910	Master LED PAR30L 40W 30D 840 CN	40 kWh







Accent Diagrams




Accent Diagram - Master LED PAR30L 40W 30D 840 CN




Accent Diagram - Master LED PAR30L 40W 30D 830 CN




Accent Diagram - Master LED PAR30L 32W 30D 840 CN




Accent Diagram - Master LED PAR30L 32W 15D 830 CN




Accent Diagram - Master LED PAR30L 32W 15D 840 CN




Accent Diagram - Master LED PAR30L 32W 15D 860 CN



Accent Diagram - Master LED PAR30L 32W 30D 830 CN




Accent Diagram - Master LED PAR30L 32W 30D 860 CN




Accent Diagram - Master LED PAR30L 20W 30D 840 CN


Accent Diagrams



Accent Diagram - Master LED PAR30L 20W 15D 840 CN




Accent Diagram - Master LED PAR30L 20W 15D 830 CN




Accent Diagram - Master LED PAR30L 20W 30D 830 CN

Beam Diagrams




Beam diagram - Master LED PAR30L 32W 15D 830 CN


Beam diagram - Master LED PAR30L 32W 30D 860 CN



Beam diagram - Master LED PAR30L 32W 15D 840 CN




Beam diagram - Master LED PAR30L 40W 30D 830 CN




Beam diagram - Master LED PAR30L 40W 30D 840 CN

Beam diagram - Master LED PAR30L 20W 15D 840 CN


Beam Diagrams




Beam diagram - Master LED PAR30L 20W 30D 840 CN




Beam diagram - Master LED PAR30L 20W 30D 830 CN




Beam diagram - Master LED PAR30L 32W 30D 840 CN



Beam diagram - Master LED PAR30L 32W 15D 860 CN



Beam diagram - Master LED PAR30L 20W 15D 830 CN



Beam diagram - Master LED PAR30L 32W 30D 830 CN

