



# For an optimum combination of value and performance

## MASTER Value LEDtube T8

A high-performance LED solution, the professional MASTER Value LED tube is ideal for replacing T8 fluorescent lamps using EM ballast or installing directly on the mains. This product provides an optimal combination of value and performance – for use in all general lighting, office, industry, retail, and hospitality applications. The unique design of this LED T8 tube light offers wide compatibility, safety and fast installation, as well as instant energy savings.

### Benefits

- An easy retrofit that is easy to install
- Trusted performance and excellent value
- One for all solution: fits a wide range of applications

### Features

- Retrofit for existing T8 lamps on EM ballast or mains
- > 50% energy savings compared to fluorescent tubes with up to 160lm/W
- Extra-long lifetime up to 60,000 hours
- Enable implementation of HACCP, supported by product level NSF certificate
- No mercury

### Application

- Office
- Retail
- Industrial Buildings & Warehouses
- Parking


# MASTER Value LEDtube T8

## Versions



LEDtube 220–240V G13 5ft

## Dimensional drawing



| Product                                | D1      | D2    | A1         | A2         | A3         |
|----------------------------------------|---------|-------|------------|------------|------------|
| MAS LEDtube VLE 1200mm HO 14W 840 T8   | 25.8 mm | 28 mm | 1,198.2 mm | 1,205.3 mm | 1,212.4 mm |
| MAS LEDtube VLE 1200mm HO 14W 865 T8   | 25.8 mm | 28 mm | 1,198.2 mm | 1,205.3 mm | 1,212.4 mm |
| MAS LEDtube VLE 1500mm HO 20.5W 840 T8 | 25.8 mm | 28 mm | 1,498.8 mm | 1,505.9 mm | 1,513 mm   |
| MAS LEDtube VLE 1500mm HO 20.5W 865 T8 | 25.8 mm | 28 mm | 1,498.7 mm | 1,505.8 mm | 1,512.9 mm |
| MAS LEDtube VLE 1500mm UO 23W 840 T8   | 25.8 mm | 28 mm | 1,498.8 mm | 1,505.9 mm | 1,513 mm   |
| MAS LEDtube VLE 600mm HO 8W 840 T8     | 25.8 mm | 28 mm | 588.6 mm   | 595.7 mm   | 602.8 mm   |
| MAS LEDtube VLE 600mm HO 8W 865 T8     | 25.8 mm | 28 mm | 588.5 mm   | 595.5 mm   | 602.5 mm   |

MASTER Value LEDtube T8

| General Information                   |                 |
|---------------------------------------|-----------------|
| Cap-Base                              | G13             |
| Switching Cycle                       | 200,000         |
| Nominal lifetime                      | 60,000 hour(s)  |
| Light Technical                       |                 |
| Beam Angle (Nom)                      | 190 degree(s)   |
| Color rendering index (CRI)           | 80              |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %            |
| Operating and Electrical              |                 |
| Input Frequency                       | 50 to 60 Hz     |
| Line Frequency                        | 50 to 60 Hz     |
| Starting Time (Nom)                   | 0.5 s           |
| Controls and Dimming                  |                 |
| Dimmable                              | No              |
| Mechanical and Housing                |                 |
| Bulb Finish                           | Frosted         |
| Bulb Shape                            | T8              |
| Approval and Application              |                 |
| Ambient temperature range             | -20 °C to 45 °C |

Light Technical

| Order Code   | Full Product Name                      | Correlated Color Temperature (Nom) | Color Code | Luminous Flux |
|--------------|----------------------------------------|------------------------------------|------------|---------------|
| 929002021202 | MAS LEDtube VLE 600mm HO 8W 840 T8     | 4000 K                             | 840        | 1,050 lm      |
| 929002021302 | MAS LEDtube VLE 600mm HO 8W 865 T8     | 6500 K                             | 865        | 1,050 lm      |
| 929002021802 | MAS LEDtube VLE 1500mm HO 20.5W 840 T8 | 4000 K                             | 840        | 3,100 lm      |
| 929002021902 | MAS LEDtube VLE 1500mm HO 20.5W 865 T8 | 6500 K                             | 865        | 3,100 lm      |
| 929002021502 | MAS LEDtube VLE 1200mm HO 14W 840 T8   | 4000 K                             | 840        | 2,100 lm      |
| 929002021602 | MAS LEDtube VLE 1200mm HO 14W 865 T8   | 6500 K                             | 865        | 2,100 lm      |
| 929002998002 | MAS LEDtube VLE 1500mm UO 23W 840 T8   | 4000 K                             | 840        | 3,700 lm      |

Operating and Electrical

| Order Code   | Full Product Name                      | Power Consumption |
|--------------|----------------------------------------|-------------------|
| 929002021202 | MAS LEDtube VLE 600mm HO 8W 840 T8     | 8 W               |
| 929002021302 | MAS LEDtube VLE 600mm HO 8W 865 T8     | 8 W               |
| 929002021802 | MAS LEDtube VLE 1500mm HO 20.5W 840 T8 | 20.5 W            |
| 929002021902 | MAS LEDtube VLE 1500mm HO 20.5W 865 T8 | 20.5 W            |

| Order Code   | Full Product Name                    | Power Consumption |
|--------------|--------------------------------------|-------------------|
| 929002021502 | MAS LEDtube VLE 1200mm HO 14W 840 T8 | 14 W              |
| 929002021602 | MAS LEDtube VLE 1200mm HO 14W 865 T8 | 14 W              |
| 929002998002 | MAS LEDtube VLE 1500mm UO 23W 840 T8 | 23 W              |

Temperature

| Order Code   | Full Product Name                      | T-Case Maximum (Nom) |
|--------------|----------------------------------------|----------------------|
| 929002021202 | MAS LEDtube VLE 600mm HO 8W 840 T8     | 55 °C                |
| 929002021302 | MAS LEDtube VLE 600mm HO 8W 865 T8     | 55 °C                |
| 929002021802 | MAS LEDtube VLE 1500mm HO 20.5W 840 T8 | 65 °C                |
| 929002021902 | MAS LEDtube VLE 1500mm HO 20.5W 865 T8 | 65 °C                |

| Order Code   | Full Product Name                    | T-Case Maximum (Nom) |
|--------------|--------------------------------------|----------------------|
| 929002021502 | MAS LEDtube VLE 1200mm HO 14W 840 T8 | 60 °C                |
| 929002021602 | MAS LEDtube VLE 1200mm HO 14W 865 T8 | 60 °C                |
| 929002998002 | MAS LEDtube VLE 1500mm UO 23W 840 T8 | 65 °C                |

Approval and Application

| Order Code   | Full Product Name                      | Energy Consumption kWh/1000 h |
|--------------|----------------------------------------|-------------------------------|
| 929002021202 | MAS LEDtube VLE 600mm HO 8W 840 T8     | 8 kWh                         |
| 929002021302 | MAS LEDtube VLE 600mm HO 8W 865 T8     | 8 kWh                         |
| 929002021802 | MAS LEDtube VLE 1500mm HO 20.5W 840 T8 | 21 kWh                        |

| Order Code   | Full Product Name                      | Energy Consumption kWh/1000 h |
|--------------|----------------------------------------|-------------------------------|
| 929002021902 | MAS LEDtube VLE 1500mm HO 20.5W 865 T8 | 21 kWh                        |
| 929002021502 | MAS LEDtube VLE 1200mm HO 14W 840 T8   | 14 kWh                        |
| 929002021602 | MAS LEDtube VLE 1200mm HO 14W 865 T8   | 14 kWh                        |
| 929002998002 | MAS LEDtube VLE 1500mm UO 23W 840 T8   | 23 kWh                        |

MASTER Value LEDtube T8

