



Everything you value in a Halogen PAR38 with the benefits of LED. Accent your merchandise or space without distraction.

LED PAR38

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

Features

- Lifetime of upto 40,000 hours
- Emit virtually no UV/IR light in the beam
- Upto CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

LED PAR38

Application

- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

Versions




Product standard image



PAR38 120V 17-90W 1150lm 8D
2700K E26 D



LEDspot MAS 120W E27 PAR38
830 25D ND



Product standard image



LEDspots PAR38 E26 1



LEDspots EXP NAM PAR38 E26 1



LEDspots GM 1 PAR38 E27



LEDspots BH PAR38 E26

LED PAR38

Versions






LED 10PAR38 90W DipS 5CCT
40D D P E26 T20



LEDspots MAS LATAM PAR38 E27

Dimensional drawing







Product	D	C
17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	120.7 mm	134.6 mm

Product	D	C
LEDspot 120W PAR38 830 100-277V 25D ND	120 mm	133 mm
LEDspot 90W PAR38 827 100-277V 25D ND	120 mm	133 mm

Product	D	C
PAR38 13-120W 930 25D 120V G ULW Dim E27	122 mm	131 mm
PAR38 13-120W 950 25D 120V G ULW Dim E27	122 mm	131 mm

LED PAR38

Dimensional drawing



Product	D	C
13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	123 mm	129 mm


Product	D	C
10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	123 mm	129 mm
10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	123 mm	129 mm
13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	123 mm	129 mm

Product	D	C
6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	121 mm	131 mm

Product	D	C
13PAR38/S/120W/927 40D E27 ND/G/110-277V	122 mm	137 mm

LED PAR38

Dimensional drawing



Product	D	C
14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	121 mm	132.5 mm
14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	121 mm	132.5 mm
14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	121 mm	132.5 mm
14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	121 mm	132.5 mm
14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	121 mm	132.5 mm

Product	D	C
10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	122 mm	129 mm

Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Mechanical and Housing	
Bulb Shape	PAR38

General Information

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	E26	-	50,000	50,000 hour(s)
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	E26	-	50,000	25,000 hour(s)
929001343812	LEDspot 120W PAR38 830 100-277V 25D ND	E27	-	25,000	25,000 hour(s)
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	E27	-	25,000	25,000 hour(s)
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	E26	-	50,000	11,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929003736904	13PAR38/COR/927/F25/D IM/P/ULW/T20 6/1FB	E26	-	50,000	25,000 hour(s)
929003737004	13PAR38/COR/927/F40/D IM/P/ULW/T20 6/1FB	E26	-	50,000	25,000 hour(s)
929003737104	13PAR38/COR/930/F25/D IM/P/ULW/T20 6/1FB	E26	-	50,000	25,000 hour(s)
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	E26	-	50,000	25,000 hour(s)
929003737304	13PAR38/COR/940/F25/D IM/P/ULW/T20 6/1FB	E26	-	50,000	25,000 hour(s)

LED PAR38

Order Code	Full Product Name	Cap-Base	Rated			Nominal lifetime
			Lifetime (Hours)	Switching Cycle		
929003737404	13PAR38/COR/940/F40/ DIM/P/ULW/T20 6/1FB	E26	-	50,000		25,000 hour(s)
929003737504	13PAR38/COR/950/F25/D IM/P/ULW/T20 6/1FB	E26	-	50,000		25,000 hour(s)
929003737604	13PAR38/COR/950/F40/ DIM/P/ULW/T20 6/1FB	E26	-	50,000		25,000 hour(s)
929003737804	13PAR38/COR/935/F25/D IM/P/ULW/T20 6/1FB	E26	-	50,000		25,000 hour(s)
929003737904	10PAR38/COR/927/F25/D IM/P/ULW/T20 6/1FB	E26	-	50,000		25,000 hour(s)
929003738004	10PAR38/COR/927/F40/D IM/P/ULW/T20 6/1FB	E26	-	50,000		25,000 hour(s)
929003738104	10PAR38/COR/930/F25/ DIM/P/ULW/T20 6/1FB	E26	-	50,000		25,000 hour(s)
929003738204	10PAR38/COR/930/F40/ DIM/P/ULW/T20 6/1FB	E26	-	50,000		25,000 hour(s)
929003738304	10PAR38/COR/940/F40/ DIM/P/ULW/T20 6/1FB	E26	-	50,000		25,000 hour(s)
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	E26	-	50,000		25,000 hour(s)
929003134407	13PAR38/S/120W/927 40D E27 ND/G/110-277V	E27	15,000 hour(s)	50,000		15,000 hour(s)
929003737704	13PAR38/COR/930/F25/D /P/ULW/B/T20 6/1FB	E26	-	50,000		25,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated			Nominal lifetime
			Lifetime (Hours)	Switching Cycle		
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	E26	-	50,000		25,000 hour(s)
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	E26	-	50,000		25,000 hour(s)
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	E26	-	50,000		25,000 hour(s)
929003754204	14PAR38/EXPERTCOLOR/ S8/927/P/D/T20/JA8	E26	-	50,000		40,000 hour(s)
929003754304	14PAR38/EXPERTCOLOR/ F25/927/P/D/T20/JA8	E26	-	50,000		40,000 hour(s)
929003754404	14PAR38/EXPERTCOLOR/ F40/927/P/D/T20/JA8	E26	-	50,000		40,000 hour(s)
929003754504	14PAR38/EXPERTCOLOR/ S8/940/P/D/T20/JA8	E26	-	50,000		40,000 hour(s)
929003754604	14PAR38/EXPERTCOLOR/ F25/940/P/D/T20/JA8	E26	-	50,000		40,000 hour(s)
929003754704	14PAR38/EXPERTCOLOR/ F40/940/P/D/T20/JA8	E26	-	50,000		40,000 hour(s)
929003741003	10PAR38/90W/DipS/ 5CCT/40D/D/P/E26/T20	E26	-	50,000		25,000 hour(s)
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	E27	-	25,000		25,000 hour(s)
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	E27	-	25,000		25,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering		Luminous	
				index (CRI)	Color Code	Luminous Flux	Intensity (Nom)
929003740805	6PAR38/90W/UE/ 930/40D/D/G/ULW/E26/T20	40 degree(s)	3000 K	90	930	950 lm	1,600 cd
929001285304	17PAR38/EXPERTCOLOR RETAIL/ F25/930/DIM	25 degree(s)	3000 K	90	930	1,200 lm	6,000 cd
929001343812	LEDspot 120W PAR38 830 100-277V 25D ND	25 degree(s)	3000 K	80	830	1,300 lm	5,000 cd
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	25 degree(s)	2700 K	80	827	1,250 lm	5,000 cd
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	40 degree(s)	3000 K	90	930	900 lm	1,533 cd
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	25 degree(s)	2700 K	90	927	1,300 lm	5,700 cd
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	40 degree(s)	2700 K	90	927	1,300 lm	2,450 cd
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	25 degree(s)	3000 K	90	930	1,300 lm	6,000 cd
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	40 degree(s)	3000 K	90	930	1,300 lm	2,500 cd
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	25 degree(s)	4000 K	90	940	1,300 lm	6,000 cd

LED PAR38

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux	Luminous Intensity (Nom)
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	40 degree(s)	4000 K	90	940	1,300 lm	2,500 cd
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	25 degree(s)	5000 K	90	950	1,300 lm	6,000 cd
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	40 degree(s)	5000 K	90	950	1,300 lm	2,500 cd
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	25 degree(s)	3500 K	90	935	1,300 lm	6,000 cd
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	25 degree(s)	2700 K	90	927	1,000 lm	4,100 cd
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	40 degree(s)	2700 K	90	927	1,000 lm	1,800 cd
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	25 degree(s)	3000 K	90	930	1,000 lm	4,100 cd
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	40 degree(s)	3000 K	90	930	1,000 lm	1,900 cd
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	40 degree(s)	4000 K	90	940	1,000 lm	1,900 cd
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	25 degree(s)	3000 K	90	930	1,350 lm	7,000 cd
929003134407	13PAR38/S/120W/927 40D E27 ND/G/110-277V	40 degree(s)	2700 K	90	927	1,200 lm	2,231 cd
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	25 degree(s)	3000 K	90	930	1,300 lm	6,000 cd
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	8 degree(s)	3000 K	90	930	1,350 lm	26,000 cd
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	25 degree(s)	3000 K	90	930	1,350 lm	7,000 cd
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	40 degree(s)	3000 K	90	930	1,350 lm	3,400 cd
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	8 degree(s)	2700 K	95	927	1,250 lm	24,000 cd
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	25 degree(s)	2700 K	95	927	1,250 lm	6,500 cd
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	40 degree(s)	2700 K	95	927	1,250 lm	3,000 cd
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	8 degree(s)	4000 K	95	940	1,350 lm	26,000 cd
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	25 degree(s)	4000 K	95	940	1,350 lm	7,000 cd
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	40 degree(s)	4000 K	95	940	1,350 lm	3,400 cd
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	40 degree(s)	2700 K	90	2700/3000/3500/4000/5000	900 lm	1,533 cd
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	25 degree(s)	3000 K	90	930	1,200 lm	6,000 cd
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	25 degree(s)	5000 K	90	950	1,200 lm	6,000 cd

Operating and Electrical

LED PAR38

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003740805	6PAR38/90W/UE / 930/40D/D/G/U LW/E26/T20	50 to 60 Hz	-	6 W	90 W
929001285304	17PAR38/ EXPERTCOLOR RETAIL/ F25/930/DIM	60 Hz	60 Hz	17 W	120 W
929001343812	LEDspot 120W PAR38 830 100-277V 25D ND	50 to 60 Hz	50 to 60 Hz	14 W	90 W
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	50 to 60 Hz	50 to 60 Hz	14 W	90 W
929001949593	10PAR38/930/G/ E26/F40/ND/UL W T20 4/2CT	50 to 60 Hz	-	10 W	90 W
929003736904	13PAR38/COR/92 7/F25/DIM/P/UL W/T20 6/1FB	60 Hz	-	13 W	120 W
929003737004	13PAR38/COR/92 7/F40/DIM/P/UL W/T20 6/1FB	60 Hz	-	13 W	120 W
929003737104	13PAR38/COR/93 0/F25/DIM/P/UL W/T20 6/1FB	60 Hz	-	13 W	120 W
929003737204	13PAR38/COR/93 0/F40/DIM/P/UL W/T20 6/1FB	60 Hz	-	13 W	120 W
929003737304	13PAR38/COR/94 0/F25/DIM/P/UL W/T20 6/1FB	60 Hz	-	13 W	120 W
929003737404	13PAR38/COR/94 0/F40/DIM/P/UL W/T20 6/1FB	60 Hz	-	13 W	120 W
929003737504	13PAR38/COR/95 0/F25/DIM/P/UL W/T20 6/1FB	60 Hz	-	13 W	120 W
929003737604	13PAR38/COR/95 0/F40/DIM/P/UL W/T20 6/1FB	60 Hz	-	13 W	120 W
929003737804	13PAR38/COR/93 5/F25/DIM/P/UL W/T20 6/1FB	60 Hz	-	13 W	120 W
929003737904	10PAR38/COR/9 27/F25/DIM/P/U LW/T20 6/1FB	60 Hz	-	10 W	90 W
929003738004	10PAR38/COR/9 27/F40/DIM/P/U LW/T20 6/1FB	60 Hz	-	10 W	90 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003738104	10PAR38/COR/9 30/F25/DIM/P/U LW/T20 6/1FB	60 Hz	-	10 W	90 W
929003738204	10PAR38/COR/9 30/F40/DIM/P/U LW/T20 6/1FB	60 Hz	-	10 W	90 W
929003738304	10PAR38/COR/9 40/F40/DIM/P/U LW/T20 6/1FB	60 Hz	-	10 W	90 W
929003754104	14PAR38/ EXPERTCOLOR RETAIL/ F25/930/P/D/B	60 Hz	-	14 W	120 W
929003134407	13PAR38/S/ 120W/927 40D E27 ND/G/ 110-277V	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929003737704	13PAR38/COR/93 0/F25/D/P/ULW/ B/T20 6/1FB	60 Hz	-	13 W	120 W
929003753804	14PAR38/ EXPERTCOLOR RETAIL/ S8/930/P/D	60 Hz	-	14 W	120 W
929003753904	14PAR38/ EXPERTCOLOR RETAIL/ F25/930/P/D	60 Hz	-	14 W	120 W
929003754004	14PAR38/ EXPERTCOLOR RETAIL/ F40/930/P/D	60 Hz	-	14 W	120 W
929003754204	14PAR38/ EXPERTCOLOR/ S8/927/P/D/T20 /JA8	60 Hz	-	14 W	120 W
929003754304	14PAR38/ EXPERTCOLOR/ F25/927/P/D/T2 0/JA8	60 Hz	-	14 W	120 W
929003754404	14PAR38/ EXPERTCOLOR/ F40/927/P/D/T2 0/JA8	60 Hz	-	14 W	120 W
929003754504	14PAR38/ EXPERTCOLOR/ S8/940/P/D/T20 /JA8	60 Hz	-	14 W	120 W
929003754604	14PAR38/ EXPERTCOLOR/	60 Hz	-	14 W	120 W

LED PAR38

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003754704	F25/940/P/D/T2 O/JA8	60 Hz	-	14 W	120 W
	14PAR38/ EXPERTCOLOR/ F40/940/P/D/T2 O/JA8				
929003741003	10PAR38/90W/ DipS/	60 Hz	-	10 W	90 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003516512	5CCT/40D/D/P/E 26/T20	50 to 60 Hz	50 to 60 Hz	13 W	120 W
	PAR38 13-120W 930 25D 120V G ULW Dim E27				
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	50 to 60 Hz	50 to 60 Hz	13 W	120 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	60 °C
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	90 °C
929001343812	LEDspot 120W PAR38 830 100-277V 25D ND	80 °C
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	80 °C
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	70 °C
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	85 °C
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	85 °C
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	85 °C
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	85 °C
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	85 °C
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	80 °C
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	80 °C
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	80 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	80 °C
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	80 °C
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	73 °C
929003134407	13PAR38/S/120W/927 40D E27 ND/G/110-277V	65 °C
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	85 °C
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	73 °C
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	73 °C
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	73 °C
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	73 °C
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	73 °C
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	73 °C
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	73 °C
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	73 °C
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	73 °C
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	75 °C
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	75 °C
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	75 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929003740805	6PAR38/90W/UE/ 930/40D/D/G/ULW/E26/T20	Only with specific dimmers
929001285304	17PAR38/EXPERTCOLOR RETAIL/ F25/930/DIM	Yes
929001343812	LEDspot 120W PAR38 830 100-277V 25D ND	No
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	No
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	No
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	Only with specific dimmers

LED PAR38

Order Code	Full Product Name	Dimmable
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	Only with specific dimmers
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	Only with specific dimmers
929003134407	13PAR38/S/120W/927 40D E27 ND/G/110-277V	No
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	Only with specific dimmers
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	Only with specific dimmers
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	Only with specific dimmers
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	Only with specific dimmers
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	Only with specific dimmers
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	Only with specific dimmers
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	Only with specific dimmers
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	Only with specific dimmers
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	Only with specific dimmers
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	Only with specific dimmers
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	Only with specific dimmers
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	Frosted
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	Clear
929001343812	LEDspot 120W PAR38 830 100-277V 25D ND	-
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	-
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	Clear
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	Clear
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	Clear
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	Clear
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	Clear
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	Clear
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	Clear
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	Clear
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	Clear

Order Code	Full Product Name	Bulb Finish
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	Clear
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	Clear
929003754104	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D/B	Clear
929003134407	13PAR38/S/120W/927 40D E27 ND/G/110-277V	Frosted
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	Clear
929003753804	14PAR38/EXPERTCOLOR RETAIL/S8/930/P/D	Clear
929003753904	14PAR38/EXPERTCOLOR RETAIL/F25/930/P/D	Clear
929003754004	14PAR38/EXPERTCOLOR RETAIL/F40/930/P/D	Clear
929003754204	14PAR38/EXPERTCOLOR/S8/927/P/D/T20/JA8	Clear
929003754304	14PAR38/EXPERTCOLOR/F25/927/P/D/T20/JA8	Clear
929003754404	14PAR38/EXPERTCOLOR/F40/927/P/D/T20/JA8	Clear
929003754504	14PAR38/EXPERTCOLOR/S8/940/P/D/T20/JA8	Clear
929003754604	14PAR38/EXPERTCOLOR/F25/940/P/D/T20/JA8	Clear
929003754704	14PAR38/EXPERTCOLOR/F40/940/P/D/T20/JA8	Clear
929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	Clear
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	Clear
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	Clear

Approval and Application


Order Code	Full Product Name	Ambient temperature range
929003740805	6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	-40 to +45 °C
929001285304	17PAR38/EXPERTCOLOR RETAIL/F25/930/DIM	-
929001343812	LEDspot 120W PAR38 830 100-277V 25D ND	-
929001389512	LEDspot 90W PAR38 827 100-277V 25D ND	-

Order Code	Full Product Name	Ambient temperature range
929001949593	10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT	-20 to +45 °C
929003736904	13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737004	13PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C








LED PAR38


Order Code	Full Product Name	Ambient temperature range
929003737104	13PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737204	13PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737304	13PAR38/COR/940/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737404	13PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737504	13PAR38/COR/950/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737604	13PAR38/COR/950/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737804	13PAR38/COR/935/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003737904	10PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003738004	10PAR38/COR/927/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003738104	10PAR38/COR/930/F25/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003738204	10PAR38/COR/930/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003738304	10PAR38/COR/940/F40/DIM/P/ULW/T20 6/1FB	-40 to +45 °C
929003754104	14PAR38/EXPERTCOLOR RETAIL/ F25/930/P/D/B	-20 to +45 °C
929003134407	13PAR38/S/120W/927 40D E27 ND/G/ 110-277V	-
929003737704	13PAR38/COR/930/F25/D/P/ULW/B/T20 6/1FB	-40 to +45 °C
929003753804	14PAR38/EXPERTCOLOR RETAIL/ S8/930/P/D	-20 to +45 °C
929003753904	14PAR38/EXPERTCOLOR RETAIL/ F25/930/P/D	-20 to +45 °C
929003754004	14PAR38/EXPERTCOLOR RETAIL/ F40/930/P/D	-20 to +45 °C
929003754204	14PAR38/EXPERTCOLOR/ S8/927/P/D/T20/JA8	-20 to +45 °C
929003754304	14PAR38/EXPERTCOLOR/ F25/927/P/D/T20/JA8	-20 to +45 °C
929003754404	14PAR38/EXPERTCOLOR/ F40/927/P/D/T20/JA8	-20 to +45 °C
929003754504	14PAR38/EXPERTCOLOR/ S8/940/P/D/T20/JA8	-20 to +45 °C
929003754604	14PAR38/EXPERTCOLOR/ F25/940/P/D/T20/JA8	-20 to +45 °C
929003754704	14PAR38/EXPERTCOLOR/ F40/940/P/D/T20/JA8	-20 to +45 °C
929003741003	10PAR38/90W/DipS/ 5CCT/40D/D/P/E26/T20	-40 to +45 °C

Order Code	Full Product Name	Ambient temperature range
929003516512	PAR38 13-120W 930 25D 120V G ULW Dim E27	-40 °C to 45 °C
929003516612	PAR38 13-120W 950 25D 120V G ULW Dim E27	-40 °C to 45 °C













LED PAR38








LED PAR38




LED PAR38




Accent Diagrams




Accent Diagram - 14PAR38/EXPERTCOLOR/
F25/940/P/D/T20/JA8




Accent Diagram -
13PAR38/COR/927/F40/DIM/P/ULW/T20
6/1FB




Accent Diagram - 14PAR38/EXPERTCOLOR/
S8/940/P/D/T20/JA8



Accent Diagram - 17PAR38/EXPERTCOLOR
RETAIL/F25/930/DIM



Accent Diagram -
10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT




Accent Diagram -
13PAR38/COR/950/F25/DIM/P/ULW/T20
6/1FB


Accent Diagram -
10PAR38/COR/930/F25/DIM/P/ULW/T20
6/1FB

LED PAR38


Accent Diagrams




Accent Diagram - 14PAR38/EXPERTCOLOR/
F40/927/P/D/T20/JA8




Accent Diagram -
10PAR38/COR/930/F40/DIM/P/ULW/T20
6/1FB




Accent Diagram -
13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB




Accent Diagram - 14PAR38/EXPERTCOLOR/
F25/927/P/D/T20/JA8



Accent Diagram - 10PAR38/90W/DipS/
5CCT/40D/D/P/E26/T20




Accent Diagram - 14PAR38/EXPERTCOLOR
RETAIL/F25/930/P/D/B




Accent Diagram -
10PAR38/COR/927/F25/DIM/P/ULW/T20
6/1FB


Accent Diagrams




Accent Diagram - 14PAR38/EXPERTCOLOR/
F40/940/P/D/T20/JA8




Accent Diagram - 14PAR38/EXPERTCOLOR
RETAIL/S8/930/P/D




Accent Diagram -
13PAR38/COR/940/F40/DIM/P/ULW/T20
6/1FB




Accent Diagram - 14PAR38/EXPERTCOLOR
RETAIL/F40/930/P/D




Accent Diagram -
13PAR38/COR/930/F25/DIM/P/ULW/T20
6/1FB




Accent Diagram -
13PAR38/COR/950/F40/DIM/P/ULW/T20
6/1FB



Accent Diagram -
10PAR38/COR/927/F40/DIM/P/ULW/T20
6/1FB




Accent Diagram - 6PAR38/90W/UE/
930/40D/D/G/ULW/E26/T20




Accent Diagram - PAR38 13-120W 950 25D
120V G ULW Dim E27


Accent Diagrams




Accent Diagram -
10PAR38/COR/940/F40/DIM/P/ULW/T20
6/1FB




Accent Diagram - 13PAR38/S/120W/927 40D
E27 ND/G/110-277V




Accent Diagram -
13PAR38/COR/930/F40/DIM/P/ULW/T20
6/1FB




Accent Diagram - 14PAR38/EXPERTCOLOR/
S8/927/P/D/T20/JA8




Accent Diagram - LEDspot 90W PAR38 827
100-277V 25D ND



Accent Diagram -
13PAR38/COR/940/F25/DIM/P/ULW/T20
6/1FB




Accent Diagram - PAR38 13-120W 930 25D
120V G ULW Dim E27




Accent Diagram -
13PAR38/COR/935/F25/DIM/P/ULW/T20
6/1FB


Beam Diagrams




Beam diagram -
10PAR38/COR/940/F40/DIM/P/ULW/T20
6/1FB




Beam diagram -
10PAR38/COR/930/F25/DIM/P/ULW/T20
6/1FB




Beam diagram -
13PAR38/COR/930/F25/DIM/P/ULW/T20
6/1FB




Beam diagram -
10PAR38/COR/927/F40/DIM/P/ULW/T20
6/1FB




Beam diagram - 17PAR38/EXPERTCOLOR
RETAIL/F25/930/DIM




Beam diagram -
13PAR38/COR/950/F25/DIM/P/ULW/T20
6/1FB



Beam diagram -
13PAR38/COR/935/F25/DIM/P/ULW/T20
6/1FB




Beam diagram -
13PAR38/COR/927/F25/DIM/P/ULW/T20 6/1FB




Beam diagram - 14PAR38/EXPERTCOLOR
RETAIL/S8/930/P/D


Beam Diagrams




Beam diagram -
13PAR38/COR/930/F40/DIM/P/ULW/T20
6/1FB




Beam diagram - 14PAR38/EXPERTCOLOR
RETAIL/F25/930/P/D/B




Beam diagram -
13PAR38/COR/950/F40/DIM/P/ULW/T20
6/1FB




Beam diagram - 14PAR38/EXPERTCOLOR/
F25/940/P/D/T20/JA8



Beam diagram -
10PAR38/COR/927/F25/DIM/P/ULW/T20
6/1FB




Beam diagram - 13PAR38/S/120W/927 40D E27
ND/G/110-277V



Beam diagram - 14PAR38/EXPERTCOLOR
RETAIL/F40/930/P/D

LED PAR38


Beam Diagrams




Beam diagram -
10PAR38/COR/930/F40/DIM/P/ULW/T20
6/1FB




Beam diagram - LEDspot 90W PAR38 827
100-277V 25D ND




Beam diagram - 14PAR38/EXPERTCOLOR/
S8/927/P/D/T20/JA8




Beam diagram - PAR38 13-120W 930 25D 120V
G ULW Dim E27




Beam diagram - 14PAR38/EXPERTCOLOR/
F40/940/P/D/T20/JA8



Beam diagram - 14PAR38/EXPERTCOLOR/
F40/927/P/D/T20/JA8




Beam diagram - PAR38 13-120W 950 25D 120V
G ULW Dim E27




Beam diagram -
13PAR38/COR/940/F25/DIM/P/ULW/T20
6/1FB

LED PAR38

Beam Diagrams




Beam diagram -
13PAR38/COR/940/F40/DIM/P/ULW/T20
6/1FB




Beam diagram - 14PAR38/EXPERTCOLOR/
S8/940/P/D/T20/JA8


Beam diagram -
10PAR38/930/G/E26/F40/ND/ULW T20 4/2CT




Beam diagram - 10PAR38/90W/DipS/
5CCT/40D/D/P/E26/T20



Beam diagram -
13PAR38/COR/927/F40/DIM/P/ULW/T20
6/1FB



Beam diagram - 6PAR38/90W/UE/
930/40D/D/G/ULW/E26/T20



Beam diagram - 14PAR38/EXPERTCOLOR/
F25/927/P/D/T20/JA8

LED PAR38

