



# Everything you value in a Halogen PAR38 with the benefits of LED. Accent your merchandise or space without distraction.

## LED PAR38

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

### Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

### Features

- Lifetime of upto 40,000 hours
- Emit virtually no UV/IR light in the beam
- Upto CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

# LED PAR38

## Application


- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

## Versions




LEDspots GM 1 PAR38 E27

## Dimensional drawing




Product	D	C
13PAR38/S/120W/927 40D E27 ND/G/110-277V	122 mm	137 mm




LED PAR38

Accent Diagrams



Accent Diagram - 13PAR38/S/120W/927 40D  
E27 ND/G/110-277V

Beam Diagrams



Beam diagram - 13PAR38/S/120W/927 40D E27  
ND/G/110-277V

