



Everything you value in a Halogen PAR30 with the benefits of LED. Accent your merchandise or space without distraction.

LED PAR30 S/L

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

Features

- Lifetime of upto 40,000 hours
- Emit virtually no UV/IR light in the beam
- Upto CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

LED PAR30 S/L

Application

- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

Versions



LEDspots EXP NAM PAR30S E26



LEDspots PAR30L E26 1





LEDspots N DIM PAR30L E26



LEDspots PL PAR30S E27

Dimensional drawing







Product	D	C
8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	95 mm	117 mm
8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	95 mm	117 mm

Product	D	C
10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	94 mm	91.5 mm

LED PAR30 S/L

Dimensional drawing



Product	D	C
8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	94 mm	116 mm

Product	D	C
8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	95 mm	92 mm
8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	95 mm	92 mm

Product	D	C
10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	94 mm	114.5 mm

Product	D	C
LEDspot 70W PAR30S 827 100-240V 25D ND	97 mm	97 mm

LED PAR30 S/L

General Information	
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime	Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003754804	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	E26	25,000 hour(s)	929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	E26	25,000 hour(s)	929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	E26	25,000 hour(s)	929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	E26	40,000 hour(s)	929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	E26	40,000 hour(s)	929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755804	10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	E26	40,000 hour(s)	929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755104	10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	E26	25,000 hour(s)	929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	E26	25,000 hour(s)	929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	E26	25,000 hour(s)	929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755404	10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	E26	40,000 hour(s)	929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929003755504	10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	E26	40,000 hour(s)	929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)
929004579004	10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	E26	40,000 hour(s)	929003027304	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	E26	25,000 hour(s)
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)	929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	E27	25,000 hour(s)
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	E26	25,000 hour(s)				

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Color rendering		Luminous Intensity	
			Temperature (Nom)		index (CRI)	Code	Luminous Flux (Nom)	
929003754804	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	10 degree(s)	3000 K		90	930	1,000 lm	10,000 cd
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	25 degree(s)	3000 K		90	930	1,000 lm	5,000 cd
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	40 degree(s)	3000 K		90	930	1,000 lm	2,500 cd
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	40 degree(s)	2700 K		95	927	950 lm	2,000 cd
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	25 degree(s)	4000 K		95	940	1,000 lm	5,000 cd

LED PAR30 S/L

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color	Color rendering	Color	Luminous Intensity	
			Temperature (Nom)	index (CRI)	Code	Luminous Flux	(Nom)
929003755804	10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	40 degree(s)	4000 K	95	940	1,000 lm	2,500 cd
929003755104	10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	10 degree(s)	3000 K	90	930	1,000 lm	10,000 cd
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	25 degree(s)	3000 K	90	930	1,000 lm	5,000 cd
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	40 degree(s)	3000 K	90	930	1,000 lm	2,500 cd
929003755404	10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	25 degree(s)	2700 K	95	927	950 lm	4,500 cd
929003755504	10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	40 degree(s)	2700 K	95	927	950 lm	2,000 cd
929004579004	10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	40 degree(s)	4000 K	95	940	1,000 lm	2,500 cd
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	25 degree(s)	2700 K	90	927	850 lm	3,300 cd
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	40 degree(s)	2700 K	90	927	850 lm	1,600 cd
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	25 degree(s)	3000 K	90	930	900 lm	3,300 cd
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	40 degree(s)	3000 K	90	930	900 lm	1,600 cd
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	25 degree(s)	4000 K	90	940	900 lm	3,300 cd
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	40 degree(s)	4000 K	90	940	900 lm	1,600 cd
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	25 degree(s)	2700 K	90	927	850 lm	3,300 cd
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	40 degree(s)	2700 K	90	927	850 lm	1,600 cd
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	25 degree(s)	3000 K	90	930	900 lm	3,300 cd
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	40 degree(s)	3000 K	90	930	900 lm	1,600 cd
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	25 degree(s)	3500 K	90	935	900 lm	3,300 cd
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	25 degree(s)	4000 K	90	940	900 lm	3,300 cd
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	40 degree(s)	4000 K	90	940	900 lm	1,600 cd
929003027304	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	40 degree(s)	3000 K	90	930	850 lm	1,600 cd
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	25 degree(s)	2700 K	80	827	900 lm	3,500 cd

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003754804	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	60 Hz	-	10 W	75 W
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	60 Hz	-	10 W	75 W
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	60 Hz	-	10 W	75 W
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	60 Hz	-	10 W	75 W
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	60 Hz	-	10 W	75 W
929003755804	10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	60 Hz	-	10 W	75 W
929003755104	10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	60 Hz	-	10 W	75 W
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	60 Hz	-	10 W	75 W
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	60 Hz	-	10 W	75 W
929003755404	10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	60 Hz	-	10 W	75 W
929003755504	10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	60 Hz	-	10 W	75 W
929004579004	10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	60 Hz	-	10 W	75 W

LED PAR30 S/L

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	60 Hz	-	8.5 W	75 W
929003027304	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	50 to 60 Hz	50 to 60 Hz	8.5 W	75 W
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	50 to 60 Hz	50 to 60 Hz	9.5 W	70 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003754804	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	73 °C
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	73 °C
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	73 °C
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	73 °C
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	73 °C
929003755804	10PAR30L/EXPERTCOLOR/F40/940/P/D/T/JA8	73 °C
929003755104	10PAR30S/EXPERTCOLOR RETAIL/S10/930/D	73 °C
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	73 °C
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	73 °C
929003755404	10PAR30S/EXPERTCOLOR/F25/927/P/D/T/JA8	73 °C
929003755504	10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	73 °C
929004579004	10PAR30S/EXPERTCOLOR/F40/940/P/D/T/JA8	73 °C
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	85 °C
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	85 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	85 °C
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	85 °C
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	85 °C
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	85 °C
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	85 °C
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	85 °C
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	85 °C
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	85 °C
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	85 °C
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	85 °C
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	85 °C
929003027304	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	70 °C
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	70 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929003754804	10PAR30L/EXPERTCOLOR RETAIL/S10/930/D	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	Only with specific dimmers

LED PAR30 S/L

Order Code	Full Product Name	Dimmable
929003755004	10PAR30L/EXPERTCOLOR RETAIL/ F40/930/D	Only with specific dimmers
929003755604	10PAR30L/EXPERTCOLOR/ F40/927/P/D/T/JA8	Only with specific dimmers
929003755704	10PAR30L/EXPERTCOLOR/ F25/940/P/D/T/JA8	Only with specific dimmers
929003755804	10PAR30L/EXPERTCOLOR/ F40/940/P/D/T/JA8	Only with specific dimmers
929003755104	10PAR30S/EXPERTCOLOR RETAIL/ S10/930/D	Only with specific dimmers
929003755204	10PAR30S/EXPERTCOLOR RETAIL/ F25/930/D	Only with specific dimmers
929003755304	10PAR30S/EXPERTCOLOR RETAIL/ F40/930/D	Only with specific dimmers
929003755404	10PAR30S/EXPERTCOLOR/ F25/927/P/D/T/JA8	Only with specific dimmers
929003755504	10PAR30S/EXPERTCOLOR/ F40/927/P/D/T/JA8	Only with specific dimmers
929004579004	10PAR30S/EXPERTCOLOR/ F40/940/P/D/T/JA8	Only with specific dimmers
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb	
		Finish	Bulb Shape
929003754804	10PAR30L/EXPERTCOLOR RETAIL/ S10/930/D	Clear	PAR30L
929003754904	10PAR30L/EXPERTCOLOR RETAIL/ F25/930/D	Clear	PAR30L
929003755004	10PAR30L/EXPERTCOLOR RETAIL/ F40/930/D	Clear	PAR30L
929003755604	10PAR30L/EXPERTCOLOR/ F40/927/P/D/T/JA8	Clear	PAR30L
929003755704	10PAR30L/EXPERTCOLOR/ F25/940/P/D/T/JA8	Clear	PAR30L
929003755804	10PAR30L/EXPERTCOLOR/ F40/940/P/D/T/JA8	Clear	PAR30L
929003755104	10PAR30S/EXPERTCOLOR RETAIL/ S10/930/D	Clear	PAR30S
929003755204	10PAR30S/EXPERTCOLOR RETAIL/ F25/930/D	Clear	PAR30S
929003755304	10PAR30S/EXPERTCOLOR RETAIL/ F40/930/D	Clear	PAR30S
929003755404	10PAR30S/EXPERTCOLOR/ F25/927/P/D/T/JA8	Clear	PAR30S

Order Code	Full Product Name	Dimmable
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	Only with specific dimmers
929003027304	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	Only with specific dimmers
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	No

LED PAR30 S/L


Order Code	Full Product Name	Bulb	
		Finish	Bulb Shape
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	Clear	PAR30S

Approval and Application











Order Code	Full Product Name	Ambient temperature range
929003754804	10PAR30L/EXPERTCOLOR RETAIL/ S10/930/D	-20 to +45 °C
929003754904	10PAR30L/EXPERTCOLOR RETAIL/ F25/930/D	-20 to +45 °C
929003755004	10PAR30L/EXPERTCOLOR RETAIL/ F40/930/D	-20 to +45 °C
929003755604	10PAR30L/EXPERTCOLOR/ F40/927/P/D/T/JA8	-20 to +45 °C
929003755704	10PAR30L/EXPERTCOLOR/ F25/940/P/D/T/JA8	-20 to +45 °C
929003755804	10PAR30L/EXPERTCOLOR/ F40/940/P/D/T/JA8	-20 to +45 °C
929003755104	10PAR30S/EXPERTCOLOR RETAIL/ S10/930/D	-20 to +45 °C
929003755204	10PAR30S/EXPERTCOLOR RETAIL/ F25/930/D	-20 to +45 °C
929003755304	10PAR30S/EXPERTCOLOR RETAIL/ F40/930/D	-20 to +45 °C
929003755404	10PAR30S/EXPERTCOLOR/ F25/927/P/D/T/JA8	-20 to +45 °C
929003755504	10PAR30S/EXPERTCOLOR/ F40/927/P/D/T/JA8	-20 to +45 °C
929004579004	10PAR30S/EXPERTCOLOR/ F40/940/P/D/T/JA8	-20 to +45 °C
929003738404	8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003738504	8.5PAR30L/COR/927/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003738604	8.5PAR30L/COR/930/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003738704	8.5PAR30L/COR/930/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003753404	8.5PAR30L/COR/940/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003753504	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003738804	8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C

Order Code	Full Product Name	Bulb	
		Finish	Bulb Shape
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	Clear	PAR30S
929003027304	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	Clear	PAR30L
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	-	PAR30S











Order Code	Full Product Name	Ambient temperature range
929003738904	8.5PAR30S/COR/927/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003739004	8.5PAR30S/COR/930/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003739104	8.5PAR30S/COR/930/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003739204	8.5PAR30S/COR/935/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003753604	8.5PAR30S/COR/940/F25/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003753704	8.5PAR30S/COR/940/F40/D/P/ULW/T20 6/1FB	-40 to +45 °C
929003027304	8.5PAR30L/LED/930/F40/DIM/ GULW/T20 6/1FB	-
929002403212	LEDspot 70W PAR30S 827 100-240V 25D ND	-





LED PAR30 S/L




LED PAR30 S/L




LED PAR30 S/L




Accent Diagrams




Accent Diagram -
8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB




Accent Diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F25/930/D




Accent Diagram -
8.5PAR30S/COR/930/F40/D/P/ULW/T20
6/1FB



Accent Diagram -
8.5PAR30S/COR/930/F25/D/P/ULW/T20
6/1FB




Accent Diagram -
8.5PAR30L/COR/927/F40/D/P/ULW/T20
6/1FB




Accent Diagram - 10PAR30S/EXPERTCOLOR/
F40/940/P/D/T/JA8


Accent Diagrams




Accent Diagram -
8.5PAR30L/COR/930/F25/D/P/ULW/T20
6/1FB




Accent Diagram - 10PAR30L/EXPERTCOLOR/
F40/940/P/D/T/JA8




Accent Diagram -
8.5PAR30L/COR/940/F25/D/P/ULW/T20
6/1FB




Accent Diagram -
8.5PAR30S/COR/927/F40/D/P/ULW/T20
6/1FB



Accent Diagram -
8.5PAR30L/COR/930/F40/D/P/ULW/T20
6/1FB




Accent Diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F25/930/D




Accent Diagram - 10PAR30S/EXPERTCOLOR/
F25/927/P/D/T/JA8


Accent Diagrams




Accent Diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F40/930/D




Accent Diagram -
8.5PAR30S/COR/940/F25/D/P/ULW/T20
6/1FB




Accent Diagram - 10PAR30L/EXPERTCOLOR
RETAIL/S10/930/D




Accent Diagram -
8.5PAR30L/LED/930/F40/DIM/GULW/T20
6/1FB



Accent Diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F40/930/D




Accent Diagram -
8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB




Accent Diagram -
8.5PAR30S/COR/935/F25/D/P/ULW/T20
6/1FB

LED PAR30 S/L


Accent Diagrams




Accent Diagram - 10PAR30S/EXPERTCOLOR/
F40/927/P/D/T/JA8




Accent Diagram - 10PAR30S/EXPERTCOLOR
RETAIL/S10/930/D




Accent Diagram -
8.5PAR30L/COR/940/F40/D/P/ULW/T20
6/1FB



Accent Diagram -
8.5PAR30S/COR/940/F40/D/P/ULW/T20
6/1FB




Accent Diagram - LEDspot 70W PAR30S 827
100-240V 25D ND




Accent Diagram - 10PAR30L/EXPERTCOLOR/
F25/940/P/D/T/JA8


Beam Diagrams



Beam diagram - 10PAR30L/EXPERTCOLOR/
F25/940/P/D/T/JA8




Beam diagram -
8.5PAR30S/COR/935/F25/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F25/930/D

LED PAR30 S/L


Beam Diagrams




Beam diagram -
8.5PAR30S/COR/930/F25/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30L/EXPERTCOLOR/
F40/940/P/D/T/JA8




Beam diagram -
8.5PAR30S/COR/927/F25/D/P/ULW/T20 6/1FB



Beam diagram -
8.5PAR30S/COR/930/F40/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30S/EXPERTCOLOR/
F25/927/P/D/T/JA8




Beam diagram -
8.5PAR30S/COR/927/F40/D/P/ULW/T20
6/1FB


Beam Diagrams




Beam diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F40/930/D




Beam diagram -
8.5PAR30L/COR/930/F25/D/P/ULW/T20
6/1FB




Beam diagram -
8.5PAR30L/COR/940/F40/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30S/EXPERTCOLOR/
F40/927/P/D/T/JA8



Beam diagram -
8.5PAR30L/COR/940/F25/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F25/930/D




Beam diagram -
8.5PAR30L/LED/930/F40/DIM/GULW/T20
6/1FB

LED PAR30 S/L


Beam Diagrams




Beam diagram -
8.5PAR30L/COR/927/F25/D/P/ULW/T20 6/1FB




Beam diagram - 10PAR30L/EXPERTCOLOR
RETAIL/S10/930/D




Beam diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F40/930/D




Beam diagram - LEDspot 70W PAR30S 827
100-240V 25D ND



Beam diagram -
8.5PAR30L/COR/930/F40/D/P/ULW/T20
6/1FB




Beam diagram - 10PAR30S/EXPERTCOLOR/
F40/940/P/D/T/JA8




Beam diagram - 10PAR30S/EXPERTCOLOR
RETAIL/S10/930/D

LED PAR30 S/L


Beam Diagrams



Beam diagram -
8.5PAR30S/COR/940/F25/D/P/ULW/T20
6/1FB



Beam diagram -
8.5PAR30S/COR/940/F40/D/P/ULW/T20
6/1FB



Beam diagram -
8.5PAR30L/COR/927/F40/D/P/ULW/T20
6/1FB

