



Everything you value in a Halogen PAR30 with the benefits of LED. Accent your merchandise or space without distraction.

LED PAR30 S/L

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

Features

- Lifetime of upto 40,000 hours
- Emit virtually no UV/IR light in the beam
- Upto CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

LED PAR30 S/L

Application


- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

Versions




LEDspots PL PAR30S E27

Dimensional drawing




Product	D	C
LEDspot 70W PAR30S 827 100-240V 25D ND	97 mm	97 mm




LED PAR30 S/L

Accent Diagrams



Accent Diagram - LEDspot 70W PAR30S 827
100-240V 25D ND

Beam Diagrams



Beam diagram - LEDspot 70W PAR30S 827
100-240V 25D ND

