



**Todo lo que le gusta
de un PAR30
halógeno con las
ventajas de los LED.
Haga que su
mercancía o espacio
se destaque sin
ninguna distracción.**

LED PAR30 S/L

Los focos Philips LED con un haz de óptica única brindan un haz libre de sombras con ángulos de haz de 15 y 45 grados para adaptarse a cualquier aplicación de iluminación.

Beneficios

- Hasta un 80 % de ahorro de energía en comparación con las lámparas halógenas
- Costos de mantenimiento más bajos
- No causa decoloración o daños

LED PAR30 S/L



Características

- Vida útil prolongada de hasta 40 000 horas
- Prácticamente no emite luz UV/IR en el haz
- Hasta CRI95
- De 3 a 5 años de garantía limitada
- No contiene mercurio

Aplicaciones

- Hoteles, restaurantes, bares, cafés, recepciones
- Museos, exhibiciones
- Comercio

Plano de dimensiones



Product	D	C
10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	94 mm	91.5 mm
10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	94 mm	91.5 mm

Product	D	C
10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	94 mm	114.5 mm
10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	94 mm	114.5 mm

LED PAR30 S/L

Información general	
Tapa-base	E26
Ciclo del interruptor	50,000
Información técnica sobre la luz	
LLMF al final de la vida útil nominal (nominal)	70 %
Operación y aspectos eléctricos	
Frecuencia de entrada	60 Hz
Consumo de energía	10 W
Tiempo de inicio (nominal)	0.5 s
Equivalente en potencia en vatios	75 W
Temperatura	
T° estuche máxima (nominal)	73 °C
Controles y atenuación	
Regulable	Solo con reguladores de intensidad específicos
Mecánica y carcasa	
Acabado de la luz	Transpar.
Aprobación y aplicación	
Rango de temperatura ambiente	-20 a +45 °C

Información general

Order Code	Full Product Name	Vida útil nominal
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	25,000 hora(s)
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	25,000 hora(s)
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	40,000 hora(s)
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	40,000 hora(s)
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	25,000 hora(s)
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	25,000 hora(s)

Información técnica sobre la luz (1/2)

Order Code	Full Product Name	Ángulo de haz (nominal)	Temperatura de color correlacionada (nominal)	Índice de producción de color (IRC)	Código de color
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	25 °	3000 K	90	930
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	40 °	3000 K	90	930
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	40 °	2700 K	95	927
929003755704	10PAR30L/EXPERTCOLOR/	25 °	4000 K	95	940

Order Code	Full Product Name	Ángulo de haz (nominal)	Temperatura de color correlacionada (nominal)	Índice de producción de color (IRC)	Código de color
	F25/940/P/D/T/JA8				
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	25 °	3000 K	90	930
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	40 °	3000 K	90	930

Información técnica sobre la luz (2/2)







LED PAR30 S/L

Order Code	Full Product Name	Flujo luminoso	Intensidad luminica (nominal)
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	1,000 lm	5,000 cd
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	1,000 lm	2,500 cd
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	950 lm	2,000 cd

Order Code	Full Product Name	Flujo luminoso	Intensidad luminica (nominal)
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	1,000 lm	5,000 cd
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	1,000 lm	5,000 cd
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	1,000 lm	2,500 cd


Mecánica y carcasa

Order Code	Full Product Name	Forma del foco
929003754904	10PAR30L/EXPERTCOLOR RETAIL/F25/930/D	PAR30L
929003755004	10PAR30L/EXPERTCOLOR RETAIL/F40/930/D	PAR30L
929003755604	10PAR30L/EXPERTCOLOR/F40/927/P/D/T/JA8	PAR30L
929003755704	10PAR30L/EXPERTCOLOR/F25/940/P/D/T/JA8	PAR30L
929003755204	10PAR30S/EXPERTCOLOR RETAIL/F25/930/D	PAR30S
929003755304	10PAR30S/EXPERTCOLOR RETAIL/F40/930/D	PAR30S




LED PAR30 S/L


Accent Diagrams




Accent Diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F25/930/D




Accent Diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F25/930/D




Accent Diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F40/930/D



Accent Diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F40/930/D




Accent Diagram - 10PAR30L/EXPERTCOLOR/
F40/927/P/D/T/JA8




Accent Diagram - 10PAR30L/EXPERTCOLOR/
F25/940/P/D/T/JA8


Beam Diagrams



Beam diagram - 10PAR30L/EXPERTCOLOR/
F25/940/P/D/T/JA8




Beam diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F25/930/D




Beam diagram - 10PAR30S/EXPERTCOLOR
RETAIL/F40/930/D

LED PAR30 S/L


Beam Diagrams



Beam diagram - 10PAR30L/EXPERTCOLOR/
F40/927/P/D/T/JA8



Beam diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F25/930/D



Beam diagram - 10PAR30L/EXPERTCOLOR
RETAIL/F40/930/D

