



Provides soft, warm light and 3 wattage settings

LED 3-Way

Philips LED A-shape light bulb provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Benefits

- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with high 80+ color rendering (CRI)
- 3-Way switching to get exactly the right amount of light when you need it

Features

- Light equivalent to 3 standard incandescent bulb outputs when used with a standard 3-way socket or luminaire
- 25,000-hour rated average life
- Instant on
- Emits virtually no UV/IR light in the beam

Application

- Hotels/Motels
- Residential & Assisted Living


LED 3-Way

Versions



LEDbulb A21 E26 FR

Dimensional drawing



Product	D	C
14A21/LED/927/P/E26/3WAY ND 4/1FB T20	70.6 mm	133.1 mm
18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	70.6 mm	133.1 mm

General Information	
Cap-Base	E26
Switching Cycle	50,000
Light Technical	
Beam Angle (Nom)	250 degree(s)
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	90
Color Code	927
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Line Frequency	60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A21

General Information

Order Code	Full Product Name	Rated Lifetime (Hours)	Nominal lifetime
929002285005	14A21/LED/927/P/E26/3WAY ND 4/1FB T20	25,000 hour(s)	25,000 hour(s)
929002285105	18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	15,000 hour(s)	15,000 hour(s)

LED 3-Way

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929002285005	14A21/LED/927/P/E26/3WAY ND 4/1FB T20	14 W

Order Code	Full Product Name	Power Consumption
929002285105	18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	18.5 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002285005	14A21/LED/927/P/E26/3WAY ND 4/1FB T20	80 °C
929002285105	18.5A21/LED/927/P/E26/3WAY ND 4/1FB T20	95 °C

