



Create a vintage or modern look while saving money with LED technology

LED Designer Deco

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Benefits

- Light distribution and color which replicates the effect of standard, vintage-style incandescent lamps, or a modern sophisticated tint
- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with high color rendering (CRI)

Features

- Integrated compact driver design to achieve a decorative look and feel
- Smooth Dimming
- Instant on
- 15,000 hours rated average life
- Wet location

Application

- Restaurants/Bars
- Lobbies/Reception areas

Versions




LEDbulb CLAF NAM T10 E26
Amber



LEDbulb UFO Others E27 FR




LEDbulb NAM S14 E26 CL



LEDbulb 5,5ST19 VIN 930 E26 CL
G SP D 1PF T20




LEDbulb UFO 75W E26 Others 865
Frosted






LEDbulb 6,5ST19 VIN 820 E26
Amber G SP D 1PFT20

Dimensional drawing



Product	D	C
5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	64 mm	137 mm
6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	64 mm	137 mm

Dimensional drawing



Product	D	C
16UFO/PER/830/FR/P/E26/ND 4/1PF	150 mm	77 mm
26UFO/PER/830/FR/P/E26/ND 4/1PF	200 mm	77 mm
26UFO/PER/865/FR/P/E26/ND 4/1PF	200 mm	77 mm
UFO LEDBulb 15W E27 6500K 230V 1CT/6	150 mm	82 mm
UFO LEDBulb 24W E27 3000K 230V 1CT/6	200 mm	82 mm
UFO LEDBulb 24W E27 6500K 230V 1CT/6	200 mm	82 mm

Product	D	C
3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	32 mm	103 mm

Product	D	C
1S14/VIN/827/CL/G/E26/ND 1CT	45 mm	86 mm

General Information	
Nominal lifetime	15,000 hour(s)
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s

General Information

LED Designer Deco

Order Code	Full Product Name	Cap-Base	Rated	
			Lifetime (Hours)	Switching Cycle
929002987403	3.5T10/VIN/820/E26/ Amber/G/SP D 4/1PFT20	E26	-	20,000
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	E27	-	50,000
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	E26	-	20,000
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	E26	-	20,000
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	E26	15,000 hour(s)	50,000
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	E27	-	50,000

Order Code	Full Product Name	Cap-Base	Rated	
			Lifetime (Hours)	Switching Cycle
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	E27	-	50,000
929002986903	6.5ST19/VIN/820/E26/ Amber/G/SP/D 1PFT20	E26	-	20,000
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	E26	15,000 hour(s)	50,000
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	E26	15,000 hour(s)	50,000

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	330 degree(s)	2000 K	80	820	225 lm
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	120 degree(s)	6500 K	80	865	1,700 lm
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	-	2700 K	80	827	60 lm
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	330 degree(s)	5000 K	90	950	500 lm
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	120 degree(s)	3000 K	80	830	1,150 lm
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	120 degree(s)	3000 K	80	830	2,715 lm
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	120 degree(s)	6500 K	80	865	2,715 lm
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	330 degree(s)	2000 K	80	820	400 lm
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	120 degree(s)	3000 K	80	830	1,950 lm
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	120 degree(s)	6500 K	80	865	2,050 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002987403	3.5T10/VIN/820/E26/ Amber/G/SP D 4/1PFT20	60 Hz	60 Hz	3.5 W	25 W
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	15 W	100 W
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	50 to 60 Hz	50 to 60 Hz	1 W	10 W
929002988803	5.5ST19/VIN/950/E26/CL/ G/SP D 4/1PF T20	60 Hz	60 Hz	5.5 W	60 W
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	16 W	75 W
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	24 W	150 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002987403	3.5T10/VIN/820/E26/ Amber/G/SP D 4/1PFT20	60 Hz	60 Hz	3.5 W	25 W
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	50 to 60 Hz	50 to 60 Hz	15 W	100 W
929002986903	6.5ST19/VIN/820/E26/ Amber/G/SP/D 1PFT20	60 Hz	60 Hz	6.5 W	60 W
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	26 W	125 W
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	50 to 60 Hz	50 to 60 Hz	26 W	125 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	-
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	72 °C
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	26 °C
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	-
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	75 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	68 °C
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	68 °C
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	-
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	72 °C
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	72 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	Only with specific dimmers
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	No
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	No
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	Only with specific dimmers
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	No

Order Code	Full Product Name	Dimmable
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	No
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	No
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	Only with specific dimmers
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	No
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	Amber	T-10
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	Frosted	Others
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	Clear	S-14
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	Clear	ST19
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	Frosted	Others

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	Frosted	Others
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	Frosted	Others
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	Amber	ST19
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	Frosted	Others
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	Frosted	Others

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002987403	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	-20 °C to 45 °C	-
929001971571	UFO LEDBulb 15W E27 6500K 230V 1CT/6	-	15 kWh
929003082704	1S14/VIN/827/CL/G/E26/ND 1CT	-	-
929002988803	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	-20 °C to 45 °C	-
929002010553	16UFO/PER/830/FR/P/E26/ND 4/1PF	-20 °C to 45 °C	-
929001971871	UFO LEDBulb 24W E27 3000K 230V 1CT/6	-	24 kWh
929001971971	UFO LEDBulb 24W E27 6500K 230V 1CT/6	-	24 kWh
929002986903	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	-20 °C to 45 °C	-

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002010753	26UFO/PER/830/FR/P/E26/ND 4/1PF	-20 °C to 45 °C	-
929002010825	26UFO/PER/865/FR/P/E26/ND 4/1PF	-20 °C to 45 °C	-

