



Instant retrofit, instant savings

LED Corn Cobs

Philips Corn Cob LED replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Benefits

- Energy savings of >50%
- omni-directional lighting enabling use in a variety of applications

Features

- Standard EX39 base to replace metal halide lamps and E39 options
- Available in 3000K, 4000K and 5000K CCTs
- Available in ranges between 70W and 400W replacements options and upto 16,800 lumens
- 3-year limited warranty
- Surge 4&6 KV

Application

- Wall packs, Shoeboxes, Post-Top fixtures
- Parking lots, public areas and office outdoor fixtures


LED Corn Cobs

Versions



LEDTForce Corncob E26 2

Dimensional drawing



Product	D	C
27CC/LED/850/ND E26 G2 BB 6/1	60 mm	170 mm

