



SunStay - All In One solar street light

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

Benefits

- Brings light to areas without access to electric grid
- Saves energy
- Preserves landscape as no trenching for cabling required
- Environment friendly
- Sturdy construction for long life

Applications

- Class A & B roads
- Rural areas
- Parks, pedestrian path lighting
- Industries, office, schools
- Shopping centers, corporate campuses, plazas


Features

- High luminous efficacy of 175 lm/Watt to maximize battery performance
- Replaceable Lithium Ferro Phosphate battery for long life and hassle free operations.
- MPPT charge controller for maximum efficiency
- Pressure die-cast aluminum housing for sturdiness and excellent heat dissipation.
- Specially designed pole mounting bracket with adjustable tilt angles of 0 to 15 degrees, which can also be used in post top & lateral mounting positions
- Factory set dimming profile along with PIR sensor for run time maximization.
- Self diagnostic feature along with battery charging, discharging & cut-off LED Indicators

Versions

	sunstay without pir		SunStay Hybrid
	SunStay Hybrid		SunStay Hybrid
	standard shot sunstay		SunStay Hybrid
	BRP710		SunStay 4500 Lumen
	BRP710		Lithium Ferro Phosphate batery


Dimensional drawing



Dimension drawing Sunstay 4500

PHILIPS

Dimensions




SunStay Dimension drawing

Dimensions





Description	12NC	Product Dimension LxWxH (cm)
SPARE BT LFP 12.8V 30Ah SOLAR EQUIP	919415811056	30x17.5x6
SPARE BT LFP 12.8V 20Ah SOLAR EQUIP	919415811055	30x17.5x6
SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP	919415811054	22x17.5x5

Dimensional Drawing



BRP710 LED30 WW 60MO PDIM30 BLE Solar

Dimensions



SunStay Hybrid

Sunstay dimensions

Light Technical

Color rendering index (CRI) >70

Operating and Electrical

Battery type Lithium Ferro Phosphate
 Battery voltage 12.8 V
 Battery charging & discharging cycles 2000
 Charge controller type MPPT
 Cable connection kit Included

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Ingress protection code IP65 [Dust penetration-protected, jet-proof]

Approval and Application

Ambient temperature range 0 to +35 °C

Application Conditions

Ambient temperature range for charging 0 °C to +45 °C

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)
919515812627	BRP710 LED20 CW MR S1 12V 35MO FDIM50 So	5700 K
919515812628	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	5700 K
919515812631	BRP710 LED20 CW MR S1 12V 35MO FDIM50 So	5700 K
919515812632	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	5700 K
919515812969	BRP710 LED20 WW MR 12V 35MO FDIM50 Solar	3000 K
919515812981	BRP710 LED20 NW MR 12V 35MO FDIM50 Solar	4000 K
919515813174	BRP710 LED30 CW MR HY SOLAR IN	5700 K
919515813614	BRP710 LED20 CW MR HY SOLAR IN	5700 K
919515813615	BRP710 LED20 CW MR HY FDIM50 SOLAR IN	5700 K
919515813616	BRP710 LED30 CW MR HY FDIM50 SOLAR IN	5700 K
919515813168	BRP710 LED45 CW MR HY SOLAR IN	5700 K
919515813617	BRP710 LED45 CW MR HY FDIM50 SOLAR IN	5700 K
919515813754	BRP710 LED60 CW MR HY FDIM20 SOLAR IN	5700 K
919515813978	BRP710 LED45 CW MR HY FDIM50 SOLAR	5700 K
919515813979	BRP710 LED60 CW MR HY FDIM20 SOLAR	5700 K
919515813982	BRP710 LED45 CW MR HY SOLAR	5700 K
919515813985	BRP710 LED45 NW MR HY FDIM50 SOLAR	4000 K
919515813986	BRP710 LED60 NW MR HY FDIM20 SOLAR	4000 K
919515813989	BRP710 LED45 NW MR HY SOLAR	4000 K
919515813992	BRP710 LED45 WW MR HY FDIM50 SOLAR	3000 K
919515813993	BRP710 LED60 WW MR HY FDIM20 SOLAR	3000 K
919515813996	BRP710 LED45 WW MR HY SOLAR	3000 K
919515812387	BRP710 LED20 CW MR S1 12V LFP AIO Solar	5700 K
919515812388	BRP710 LED30 CW MR S1 12V LFP AIO Solar	5700 K
919515812389	BRP710 LED20 CW MR S1 12V LFP AIO Solar	5700 K
919515812390	BRP710 LED30 CW MR S1 12V LFP AIO Solar	5700 K
919515812625	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	5700 K
919515812626	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	5700 K
919515812629	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	5700 K
919515812630	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	5700 K
919515812966	BRP710 LED20 WW MR 12V LFP Solar	3000 K
919515812967	BRP710 LED20 WW MR 12V 28PO PDIM50 Solar	3000 K
919515812968	BRP710 LED20 WW MR 12V 35MO PDIM50 Solar	3000 K
919515812970	BRP710 LED20 WW MR 12V 35MO Solar	3000 K
919515812971	BRP710 LED30 WW MR 12V LFP AIO Solar	3000 K
919515812978	BRP710 LED20 NW MR 12V LFP Solar	4000 K
919515812979	BRP710 LED20 NW MR 12V 28PO PDIM50 Solar	4000 K
919515812980	BRP710 LED20 NW MR 12V 35MO PDIM50 Solar	4000 K
919515812982	BRP710 LED20 NW MR 12V 35MO Solar	4000 K
919515812983	BRP710 LED30 NW MR 12V LFP AIO Solar	4000 K
919515814301	BRP710 LED30 WW 35MO PDIM30 BLE Solar	3000 K

Order Code	Full Product Name	Correlated Color Temperature (Nom)
919515814303	BRP710 LED30 2700K 60MO PDM30 BLE Solar	2700 K
919515814406	BRP710 LED20 WW 28PO PDIM50 BLE Solar	3000 K
919515898025	BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX	4000 K
919515898026	BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX	5700 K
919515898027	BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX	4000 K
919515898028	BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX	5700 K
919515898032	BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX	5700 K
919515898033	BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX	3000 K
919515898034	BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX	4000 K
919515898035	BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX	5700 K
919615811178	BRP710 LED20 CW Housing KIT Solar	5700 K
919615811179	BRP710 LED30 CW Housing KIT Solar	5700 K
919515813976	BRP710 LED20 CW MR HY FDM50 SOLAR	5700 K
919515813977	BRP710 LED30 CW MR HY FDM50 SOLAR	5700 K
919515813980	BRP710 LED20 CW MR HY SOLAR	5700 K
919515813981	BRP710 LED30 CW MR HY SOLAR	5700 K
919515813983	BRP710 LED20 NW MR HY FDM50 SOLAR	4000 K
919515813984	BRP710 LED30 NW MR HY FDM50 SOLAR	4000 K
919515813987	BRP710 LED20 NW MR HY SOLAR	4000 K
919515813988	BRP710 LED30 NW MR HY SOLAR	4000 K
919515813990	BRP710 LED20 WW MR HY FDM50 SOLAR	3000 K
919515813991	BRP710 LED30 WW MR HY FDM50 SOLAR	3000 K
919515813994	BRP710 LED20 WW MR HY SOLAR	3000 K
919515813995	BRP710 LED30 WW MR HY SOLAR	3000 K
919515898031	BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX	4000 K
919515812830	BRP710 LED45 CW MR S1 12V LFP Solar IN	5700 K
919515812831	BRP710 LED45 CW MR S1 12V FD30 Solar IN	5700 K
919515813566	BRP710 LED45 CW MR S1 12V LFP Solar	5700 K
919515813567	BRP710 LED45 CW MR S1 12V FD30 Solar	5700 K
919515813568	BRP710 LED45 WW MR S1 12V LFP Solar	3000 K
919515813569	BRP710 LED45 NW MR S1 12V LFP Solar	4000 K
919515813570	BRP710 LED45 WW MR S1 12V FD30 Solar	3000 K
919515813571	BRP710 LED45 NW MR S1 12V FD30 Solar	4000 K
919515814302	BRP710 LED45 WW 60MO PDIM30 BLE Solar	3000 K
919515898029	BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX	4000 K
919515898030	BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX	5700 K
919615811180	BRP710 LED45 CW Housing KIT Solar	5700 K
919615811265	BRP710 P LED45 CW MR 12V LFP Solar P4125	5700 K
919515814304	BRP710 LED30 WW 60MO PDIM30 BLE Solar	3000 K
919415811054	SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP	-
919415811055	SPARE BT LFP 12.8V 20Ah SOLAR EQUIP	-
919415811056	SPARE BT LFP 12.8V 30Ah SOLAR EQUIP	-

Operating and Electrical

Order Code	Full Product Name	Battery ampere hour	Panel type	Panel voltage	Panel peak wattage	Charge controller wattage	Grid connection type
919515812627	BRP710 LED20 CW MR S1 12V 35MO FDIM50 So	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812628	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812631	BRP710 LED20 CW MR S1 12V 35MO FDIM50 So	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812632	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812969	BRP710 LED20 WW MR 12V 35MO FDIM50 Solar	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812981	BRP710 LED20 NW MR 12V 35MO FDIM50 Solar	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515813174	BRP710 LED30 CW MR HY SOLAR IN	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	17 W	Hybrid
919515813614	BRP710 LED20 CW MR HY SOLAR IN	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	11 W	Hybrid
919515813615	BRP710 LED20 CW MR HY FDIM50 SOLAR IN	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	11 W	Hybrid
919515813616	BRP710 LED30 CW MR HY FDIM50 SOLAR IN	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	17 W	Hybrid
919515813168	BRP710 LED45 CW MR HY SOLAR IN	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	25 W	Hybrid
919515813617	BRP710 LED45 CW MR HY FDIM50 SOLAR IN	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	25 W	Hybrid
919515813754	BRP710 LED60 CW MR HY FDIM20 SOLAR IN	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	35 W	Hybrid
919515813978	BRP710 LED45 CW MR HY FDIM50 SOLAR	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	25 W	Hybrid
919515813979	BRP710 LED60 CW MR HY FDIM20 SOLAR	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	35 W	Hybrid
919515813982	BRP710 LED45 CW MR HY SOLAR	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	25 W	Hybrid
919515813985	BRP710 LED45 NW MR HY FDIM50 SOLAR	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	25 W	Hybrid
919515813986	BRP710 LED60 NW MR HY FDIM20 SOLAR	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	35 W	Hybrid
919515813989	BRP710 LED45 NW MR HY SOLAR	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	25 W	Hybrid
919515813992	BRP710 LED45 WW MR HY FDIM50 SOLAR	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	25 W	Hybrid
919515813993	BRP710 LED60 WW MR HY FDIM20 SOLAR	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	35 W	Hybrid
919515813996	BRP710 LED45 WW MR HY SOLAR	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	25 W	Hybrid
919515812387	BRP710 LED20 CW MR S1 12V LFP AIO Solar	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	-	Off grid
919515812388	BRP710 LED30 CW MR S1 12V LFP AIO Solar	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812389	BRP710 LED20 CW MR S1 12V LFP AIO Solar	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	-	Off grid
919515812390	BRP710 LED30 CW MR S1 12V LFP AIO Solar	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812625	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	-	Off grid
919515812626	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812629	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	-	Off grid

Order Code	Full Product Name	Battery ampere hour	Panel type	Panel voltage	Panel peak wat- tage	Charge controller wattage	Grid con- nection type
919515812630	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812966	BRP710 LED20 WW MR 12V LFP Solar	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	-	Off grid
919515812967	BRP710 LED20 WW MR 12V 28PO PDIM50 Solar	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	-	Off grid
919515812968	BRP710 LED20 WW MR 12V 35MO PDIM50 Solar	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812970	BRP710 LED20 WW MR 12V 35MO Solar	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812971	BRP710 LED30 WW MR 12V LFP AIO Solar	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812978	BRP710 LED20 NW MR 12V LFP Solar	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	-	Off grid
919515812979	BRP710 LED20 NW MR 12V 28PO PDIM50 Solar	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	-	Off grid
919515812980	BRP710 LED20 NW MR 12V 35MO PDIM50 Solar	13.6 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812982	BRP710 LED20 NW MR 12V 35MO Solar	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515812983	BRP710 LED30 NW MR 12V LFP AIO Solar	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515814301	BRP710 LED30 WW 35MO PDIM30 BLE Solar	20 Ah	Mono crystalline	17 V	35 W	-	Off grid
919515814303	BRP710 LED30 2700K 60MO PDM30 BLE Solar	30 Ah	Mono crystalline	17 V	60 W	-	Off grid
919515814406	BRP710 LED20 WW 28PO PDIM50 BLE Solar	13.6 Ah	Poly crystalline	17 V	28 W	-	Off grid
919515898025	BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX	13.6 Ah	Poly crystalline	17 V	28 W	-	Off grid
919515898026	BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX	13.6 Ah	Poly crystalline	17 V	28 W	-	Off grid
919515898027	BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX	20 Ah	Mono crystalline	17 V	35 W	-	Off grid
919515898028	BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX	20 Ah	Mono crystalline	17 V	35 W	-	Off grid
919515898032	BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX	30 Ah	Mono crystalline	17 V	60 W	-	Off grid
919515898033	BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX	20 Ah	Mono crystalline	17 V	35 W	-	Off grid
919515898034	BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX	20 Ah	Mono crystalline	17 V	35 W	-	Off grid
919515898035	BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX	20 Ah	Mono crystalline	17 V	35 W	-	Off grid
919615811178	BRP710 LED20 CW Housing KIT Solar	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	-	Off grid
919615811179	BRP710 LED30 CW Housing KIT Solar	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	-	Off grid
919515813976	BRP710 LED20 CW MR HY FDIM50 SOLAR	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	11 W	Hybrid
919515813977	BRP710 LED30 CW MR HY FDIM50 SOLAR	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	17 W	Hybrid
919515813980	BRP710 LED20 CW MR HY SOLAR	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	11 W	Hybrid
919515813981	BRP710 LED30 CW MR HY SOLAR	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	17 W	Hybrid
919515813983	BRP710 LED20 NW MR HY FDIM50 SOLAR	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	11 W	Hybrid
919515813984	BRP710 LED30 NW MR HY FDIM50 SOLAR	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	17 W	Hybrid
919515813987	BRP710 LED20 NW MR HY SOLAR	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	11 W	Hybrid
919515813988	BRP710 LED30 NW MR HY SOLAR	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	17 W	Hybrid

Order Code	Full Product Name	Battery ampere hour	Panel type	Panel voltage	Panel peak wat- tage	Charge controller wattage	Grid con- nection type
919515813990	BRP710 LED20 WW MR HY FDIM50 SOLAR	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	11 W	Hybrid
919515813991	BRP710 LED30 WW MR HY FDIM50 SOLAR	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	17 W	Hybrid
919515813994	BRP710 LED20 WW MR HY SOLAR	13.6 Ah	Poly crystalline	17 Vmp, 21 Voc V	28 W	11 W	Hybrid
919515813995	BRP710 LED30 WW MR HY SOLAR	20 Ah	Mono crystalline	17 Vmp, 21 Voc V	35 W	17 W	Hybrid
919515898031	BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX	30 Ah	Mono crystalline	17 V	60 W	-	Off grid
919515812830	BRP710 LED45 CW MR S1 12V LFP Solar IN	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919515812831	BRP710 LED45 CW MR S1 12V FD30 Solar IN	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919515813566	BRP710 LED45 CW MR S1 12V LFP Solar	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919515813567	BRP710 LED45 CW MR S1 12V FD30 Solar	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919515813568	BRP710 LED45 WW MR S1 12V LFP Solar	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919515813569	BRP710 LED45 NW MR S1 12V LFP Solar	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919515813570	BRP710 LED45 WW MR S1 12V FD30 Solar	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919515813571	BRP710 LED45 NW MR S1 12V FD30 Solar	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919515814302	BRP710 LED45 WW 60MO PDIM30 BLE Solar	30 Ah	Mono crystalline	17 V	60 W	-	Off grid
919515898029	BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX	30 Ah	Mono crystalline	17 V	60 W	-	Off grid
919515898030	BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX	30 Ah	Mono crystalline	17 V	60 W	-	Off grid
919615811180	BRP710 LED45 CW Housing KIT Solar	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919615811265	BRP710 P LED45 CW MR 12V LFP Solar P4125	30 Ah	Mono crystalline	17 Vmp, 21 Voc V	60 W	-	Off grid
919515814304	BRP710 LED30 WW 60MO PDIM30 BLE Solar	30 Ah	Mono crystalline	17 V	60 W	-	Off grid
919415811054	SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP	13.6 Ah	-	-	-	-	-
919415811055	SPARE BT LFP 12.8V 20Ah SOLAR EQUIP	20 Ah	-	-	-	-	-
919415811056	SPARE BT LFP 12.8V 30Ah SOLAR EQUIP	30 Ah	-	-	-	-	-

Controls and Dimming

Order Code	Full Product Name	Configurability	Solar dimming profile
919515812627	BRP710 LED20 CW MR S1 12V 35MO FDIM50 So	Factory Configurable	5hrs 100% + 7 hrs 50%
919515812628	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	Factory Configurable	No Dimming
919515812631	BRP710 LED20 CW MR S1 12V 35MO FDIM50 So	Factory Configurable	5hrs 100% + 7 hrs 50%
919515812632	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	Factory Configurable	No Dimming
919515812969	BRP710 LED20 WW MR 12V 35MO FDIM50 Solar	Factory Configurable	5hrs 100% + 7 hrs 50%
919515812981	BRP710 LED20 NW MR 12V 35MO FDIM50 Solar	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813174	BRP710 LED30 CW MR HY SOLAR IN	Factory Configurable	100% Dusk to dawn
919515813614	BRP710 LED20 CW MR HY SOLAR IN	Factory Configurable	100% Dusk to dawn
919515813615	BRP710 LED20 CW MR HY FDIM50 SOLAR IN	Factory Configurable	5hrs 100% + 7 hrs 50%

Order Code	Full Product Name	Configurability	Solar dimming profile
919515813616	BRP710 LED30 CW MR HY FDIM50 SOLAR IN	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813168	BRP710 LED45 CW MR HY SOLAR IN	Factory Configurable	100% Dusk to dawn
919515813617	BRP710 LED45 CW MR HY FDIM50 SOLAR IN	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813754	BRP710 LED60 CW MR HY FDIM20 SOLAR IN	Factory Configurable	4hrs 100% + 8 hrs 20%
919515813978	BRP710 LED45 CW MR HY FDIM50 SOLAR	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813979	BRP710 LED60 CW MR HY FDIM20 SOLAR	Factory Configurable	4hrs 100% + 8 hrs 20%
919515813982	BRP710 LED45 CW MR HY SOLAR	Factory Configurable	100% Dusk to dawn
919515813985	BRP710 LED45 NW MR HY FDIM50 SOLAR	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813986	BRP710 LED60 NW MR HY FDIM20 SOLAR	Factory Configurable	4hrs 100% + 8 hrs 20%
919515813989	BRP710 LED45 NW MR HY SOLAR	Factory Configurable	100% Dusk to dawn
919515813992	BRP710 LED45 WW MR HY FDIM50 SOLAR	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813993	BRP710 LED60 WW MR HY FDIM20 SOLAR	Factory Configurable	4hrs 100% + 8 hrs 20%
919515813996	BRP710 LED45 WW MR HY SOLAR	Factory Configurable	100% Dusk to dawn
919515812387	BRP710 LED20 CW MR S1 12V LFP AIO Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812388	BRP710 LED30 CW MR S1 12V LFP AIO Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812389	BRP710 LED20 CW MR S1 12V LFP AIO Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812390	BRP710 LED30 CW MR S1 12V LFP AIO Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812625	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	Factory Configurable	50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812626	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	Factory Configurable	50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812629	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	Factory Configurable	50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812630	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	Factory Configurable	50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812966	BRP710 LED20 WW MR 12V LFP Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812967	BRP710 LED20 WW MR 12V 28PO PDIM50 Solar	Factory Configurable	50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812968	BRP710 LED20 WW MR 12V 35MO PDIM50 Solar	Factory Configurable	50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812970	BRP710 LED20 WW MR 12V 35MO Solar	Factory Configurable	No dimming
919515812971	BRP710 LED30 WW MR 12V LFP AIO Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812978	BRP710 LED20 NW MR 12V LFP Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812979	BRP710 LED20 NW MR 12V 28PO PDIM50 Solar	Factory Configurable	50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812980	BRP710 LED20 NW MR 12V 35MO PDIM50 Solar	Factory Configurable	50% Dusk to dawn, 100% on Motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812982	BRP710 LED20 NW MR 12V 35MO Solar	Factory Configurable	No dimming
919515812983	BRP710 LED30 NW MR 12V LFP AIO Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515814301	BRP710 LED30 WW 35MO PDIM30 BLE Solar	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)

Order Code	Full Product Name	Configurability	Solar dimming profile
919515814303	BRP710 LED30 2700K 60MO PDM30 BLE Solar	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515814406	BRP710 LED20 WW 28PO PDIM50 BLE Solar	Configurable	50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898025	BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX	Configurable	50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898026	BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX	Configurable	50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898027	BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898028	BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898032	BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898033	BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX	Configurable	50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898034	BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX	Configurable	50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898035	BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX	Configurable	50% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919615811178	BRP710 LED20 CW Housing KIT Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919615811179	BRP710 LED30 CW Housing KIT Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515813976	BRP710 LED20 CW MR HY FDIM50 SOLAR	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813977	BRP710 LED30 CW MR HY FDIM50 SOLAR	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813980	BRP710 LED20 CW MR HY SOLAR	Factory Configurable	100% Dusk to dawn
919515813981	BRP710 LED30 CW MR HY SOLAR	Factory Configurable	100% Dusk to dawn
919515813983	BRP710 LED20 NW MR HY FDIM50 SOLAR	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813984	BRP710 LED30 NW MR HY FDIM50 SOLAR	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813987	BRP710 LED20 NW MR HY SOLAR	Factory Configurable	100% Dusk to dawn
919515813988	BRP710 LED30 NW MR HY SOLAR	Factory Configurable	100% Dusk to dawn
919515813990	BRP710 LED20 WW MR HY FDIM50 SOLAR	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813991	BRP710 LED30 WW MR HY FDIM50 SOLAR	Factory Configurable	5hrs 100% + 7 hrs 50%
919515813994	BRP710 LED20 WW MR HY SOLAR	Factory Configurable	100% Dusk to dawn
919515813995	BRP710 LED30 WW MR HY SOLAR	Factory Configurable	100% Dusk to dawn
919515898031	BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812830	BRP710 LED45 CW MR S1 12V LFP Solar IN	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515812831	BRP710 LED45 CW MR S1 12V FD30 Solar IN	Factory Configurable	5hrs 100% + 7 hrs 30%
919515813566	BRP710 LED45 CW MR S1 12V LFP Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515813567	BRP710 LED45 CW MR S1 12V FD30 Solar	Factory Configurable	5hrs 100% + 7 hrs 30%
919515813568	BRP710 LED45 WW MR S1 12V LFP Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515813569	BRP710 LED45 NW MR S1 12V LFP Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515813570	BRP710 LED45 WW MR S1 12V FD30 Solar	Factory Configurable	5hrs 100% + 7 hrs 30%

Order Code	Full Product Name	Configurability	Solar dimming profile
919515813571	BRP710 LED45 NW MR S1 12V FD30 Solar	Factory Configurable	5hrs 100% + 7 hrs 30%
919515814302	BRP710 LED45 WW 60MO PDIM30 BLE Solar	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898029	BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515898030	BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919615811180	BRP710 LED45 CW Housing KIT Solar	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919615811265	BRP710 P LED45 CW MR 12V LFP Solar P4125	Factory Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919515814304	BRP710 LED30 WW 60MO PDIM30 BLE Solar	Configurable	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)
919415811054	SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP	-	-
919415811055	SPARE BT LFP 12.8V 20Ah SOLAR EQUIP	-	-
919415811056	SPARE BT LFP 12.8V 30Ah SOLAR EQUIP	-	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Overall length	Overall width	Overall height	Battery location
919515812627	BRP710 LED20 CW MR S1 12V 35MO FDIM50 So	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812628	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812631	BRP710 LED20 CW MR S1 12V 35MO FDIM50 So	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812632	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812969	BRP710 LED20 WW MR 12V 35MO FDIM50 Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812981	BRP710 LED20 NW MR 12V 35MO FDIM50 Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515813174	BRP710 LED30 CW MR HY SOLAR IN	RAL 7011	684 mm	369 mm	156 mm	Integrated
919515813614	BRP710 LED20 CW MR HY SOLAR IN	RAL 7011	684 mm	369 mm	156 mm	Integrated
919515813615	BRP710 LED20 CW MR HY FDIM50 SOLAR IN	RAL 7011	684 mm	369 mm	156 mm	Integrated
919515813616	BRP710 LED30 CW MR HY FDIM50 SOLAR IN	RAL 7011	684 mm	369 mm	156 mm	Integrated
919515813168	BRP710 LED45 CW MR HY SOLAR IN	RAL 7011	757 mm	511 mm	188 mm	Integrated
919515813617	BRP710 LED45 CW MR HY FDIM50 SOLAR IN	RAL 7011	757 mm	511 mm	188 mm	Integrated
919515813754	BRP710 LED60 CW MR HY FDIM20 SOLAR IN	RAL 7011	757 mm	511 mm	188 mm	Integrated
919515813978	BRP710 LED45 CW MR HY FDIM50 SOLAR	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515813979	BRP710 LED60 CW MR HY FDIM20 SOLAR	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515813982	BRP710 LED45 CW MR HY SOLAR	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515813985	BRP710 LED45 NW MR HY FDIM50 SOLAR	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515813986	BRP710 LED60 NW MR HY FDIM20 SOLAR	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515813989	BRP710 LED45 NW MR HY SOLAR	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515813992	BRP710 LED45 WW MR HY FDIM50 SOLAR	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515813993	BRP710 LED60 WW MR HY FDIM20 SOLAR	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515813996	BRP710 LED45 WW MR HY SOLAR	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515812387	BRP710 LED20 CW MR S1 12V LFP AIO Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812388	BRP710 LED30 CW MR S1 12V LFP AIO Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812389	BRP710 LED20 CW MR S1 12V LFP AIO Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire

Order Code	Full Product Name	Housing Color	Overall length	Overall width	Overall height	Battery location
919515812390	BRP710 LED30 CW MR S1 12V LFP AIO Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812625	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812626	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812629	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812630	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812966	BRP710 LED20 WW MR 12V LFP Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812967	BRP710 LED20 WW MR 12V 28PO PDIM50 Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812968	BRP710 LED20 WW MR 12V 35MO PDIM50 Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812970	BRP710 LED20 WW MR 12V 35MO Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812971	BRP710 LED30 WW MR 12V LFP AIO Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812978	BRP710 LED20 NW MR 12V LFP Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812979	BRP710 LED20 NW MR 12V 28PO PDIM50 Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812980	BRP710 LED20 NW MR 12V 35MO PDIM50 Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812982	BRP710 LED20 NW MR 12V 35MO Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515812983	BRP710 LED30 NW MR 12V LFP AIO Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515814301	BRP710 LED30 WW 35MO PDIM30 BLE Solar	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515814303	BRP710 LED30 2700K 60MO PDM30 BLE Solar	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515814406	BRP710 LED20 WW 28PO PDIM50 BLE Solar	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515898025	BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515898026	BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515898027	BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515898028	BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515898032	BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515898033	BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515898034	BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515898035	BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919615811178	BRP710 LED20 CW Housing KIT Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919615811179	BRP710 LED30 CW Housing KIT Solar	Gray	684 mm	369 mm	156 mm	Inside Luminaire
919515813976	BRP710 LED20 CW MR HY FDIM50 SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813977	BRP710 LED30 CW MR HY FDIM50 SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813980	BRP710 LED20 CW MR HY SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813981	BRP710 LED30 CW MR HY SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813983	BRP710 LED20 NW MR HY FDIM50 SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813984	BRP710 LED30 NW MR HY FDIM50 SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813987	BRP710 LED20 NW MR HY SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813988	BRP710 LED30 NW MR HY SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813990	BRP710 LED20 WW MR HY FDIM50 SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813991	BRP710 LED30 WW MR HY FDIM50 SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813994	BRP710 LED20 WW MR HY SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515813995	BRP710 LED30 WW MR HY SOLAR	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515898031	BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919515812830	BRP710 LED45 CW MR S1 12V LFP Solar IN	Gray	757 mm	511 mm	188 mm	Inside Luminaire

Order Code	Full Product Name	Housing Color	Overall length	Overall width	Overall height	Battery location
919515812831	BRP710 LED45 CW MR S1 12V FD30 Solar IN	Gray	757 mm	511 mm	188 mm	Inside Luminaire
919515813566	BRP710 LED45 CW MR S1 12V LFP Solar	Gray	757 mm	511 mm	188 mm	Inside Luminaire
919515813567	BRP710 LED45 CW MR S1 12V FD30 Solar	Gray	757 mm	511 mm	188 mm	Inside Luminaire
919515813568	BRP710 LED45 WW MR S1 12V LFP Solar	Gray	757 mm	511 mm	188 mm	Inside Luminaire
919515813569	BRP710 LED45 NW MR S1 12V LFP Solar	Gray	757 mm	511 mm	188 mm	Inside Luminaire
919515813570	BRP710 LED45 WW MR S1 12V FD30 Solar	Gray	757 mm	511 mm	188 mm	Inside Luminaire
919515813571	BRP710 LED45 NW MR S1 12V FD30 Solar	Gray	757 mm	511 mm	188 mm	Inside Luminaire
919515814302	BRP710 LED45 WW 60MO PDIM30 BLE Solar	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515898029	BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919515898030	BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX	RAL 7011	757 mm	511 mm	188 mm	Inside Luminaire
919615811180	BRP710 LED45 CW Housing KIT Solar	Gray	757 mm	511 mm	188 mm	Inside Luminaire
919615811265	BRP710 P LED45 CW MR 12V LFP Solar P4125	Gray	757 mm	511 mm	188 mm	Inside Luminaire
919515814304	BRP710 LED30 WW 60MO PDIM30 BLE Solar	RAL 7011	684 mm	369 mm	156 mm	Inside Luminaire
919415811054	SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP	-	175 mm	50 mm	220 mm	-
919415811055	SPARE BT LFP 12.8V 20Ah SOLAR EQUIP	-	175 mm	60 mm	300 mm	-
919415811056	SPARE BT LFP 12.8V 30Ah SOLAR EQUIP	-	175 mm	60 mm	300 mm	-

Application Conditions

Order Code	Full Product Name	Ambient temperature range for discharging (when light is on)
919515812627	BRP710 LED20 CW MR S1 12V 35MO FDM50 So	-20 °C to +35 °C
919515812628	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	-20 °C to +35 °C
919515812631	BRP710 LED20 CW MR S1 12V 35MO FDM50 So	-20 °C to +35 °C
919515812632	BRP710 LED20 CW MR S1 12V 35MO Solar Equ	-20 °C to +35 °C
919515812969	BRP710 LED20 WW MR 12V 35MO FDM50 Solar	-20 °C to +35 °C
919515812981	BRP710 LED20 NW MR 12V 35MO FDM50 Solar	-20 °C to +35 °C
919515813174	BRP710 LED30 CW MR HY SOLAR IN	-20 °C to +35 °C
919515813614	BRP710 LED20 CW MR HY SOLAR IN	-20 °C to +35 °C
919515813615	BRP710 LED20 CW MR HY FDM50 SOLAR IN	-20 °C to +35 °C
919515813616	BRP710 LED30 CW MR HY FDM50 SOLAR IN	-20 °C to +35 °C
919515813168	BRP710 LED45 CW MR HY SOLAR IN	-20 °C to +35 °C
919515813617	BRP710 LED45 CW MR HY FDM50 SOLAR IN	-20 °C to +35 °C
919515813754	BRP710 LED60 CW MR HY FDM20 SOLAR IN	-20 °C to +35 °C
919515813978	BRP710 LED45 CW MR HY FDM50 SOLAR	-20 °C to +35 °C
919515813979	BRP710 LED60 CW MR HY FDM20 SOLAR	-20 °C to +35 °C
919515813982	BRP710 LED45 CW MR HY SOLAR	-20 °C to +35 °C
919515813985	BRP710 LED45 NW MR HY FDM50 SOLAR	-20 °C to +35 °C
919515813986	BRP710 LED60 NW MR HY FDM20 SOLAR	-20 °C to +35 °C
919515813989	BRP710 LED45 NW MR HY SOLAR	-20 °C to +35 °C
919515813992	BRP710 LED45 WW MR HY FDM50 SOLAR	-20 °C to +35 °C
919515813993	BRP710 LED60 WW MR HY FDM20 SOLAR	-20 °C to +35 °C
919515813996	BRP710 LED45 WW MR HY SOLAR	-20 °C to +35 °C
919515812387	BRP710 LED20 CW MR S1 12V LFP AIO Solar	-20 °C to +35 °C

Order Code	Full Product Name	Ambient temperature range for discharging (when light is on)
919515812388	BRP710 LED30 CW MR S1 12V LFP AIO Solar	-20 °C to +35 °C
919515812389	BRP710 LED20 CW MR S1 12V LFP AIO Solar	-20 °C to +35 °C
919515812390	BRP710 LED30 CW MR S1 12V LFP AIO Solar	-20 °C to +35 °C
919515812625	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	-20 °C to +35 °C
919515812626	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	-20 °C to +35 °C
919515812629	BRP710 LED20 CW MR S1 12V 28PO PDIM50 So	-20 °C to +35 °C
919515812630	BRP710 LED20 CW MR S1 12V 35MO PDIM50 So	-20 °C to +35 °C
919515812966	BRP710 LED20 WW MR 12V LFP Solar	-20 °C to +35 °C
919515812967	BRP710 LED20 WW MR 12V 28PO PDIM50 Solar	-20 °C to +35 °C
919515812968	BRP710 LED20 WW MR 12V 35MO PDIM50 Solar	-20 °C to +35 °C
919515812970	BRP710 LED20 WW MR 12V 35MO Solar	-20 °C to +35 °C
919515812971	BRP710 LED30 WW MR 12V LFP AIO Solar	-20 °C to +35 °C
919515812978	BRP710 LED20 NW MR 12V LFP Solar	-20 °C to +35 °C
919515812979	BRP710 LED20 NW MR 12V 28PO PDIM50 Solar	-20 °C to +35 °C
919515812980	BRP710 LED20 NW MR 12V 35MO PDIM50 Solar	-20 °C to +35 °C
919515812982	BRP710 LED20 NW MR 12V 35MO Solar	-20 °C to +35 °C
919515812983	BRP710 LED30 NW MR 12V LFP AIO Solar	-20 °C to +35 °C
919515814301	BRP710 LED30 WW 35MO PDIM30 BLE Solar	-20 °C to +35 °C
919515814303	BRP710 LED30 2700K 60MO PDM30 BLE Solar	-20 °C to +35 °C
919515814406	BRP710 LED20 WW 28PO PDIM50 BLE Solar	-20 °C to +35 °C
919515898025	BRP710 LED20 NW 28PO PDIM50 BLE SOLAR EX	-20 °C to +35 °C
919515898026	BRP710 LED20 CW 28PO PDIM50 BLE SOLAR EX	-20 °C to +35 °C
919515898027	BRP710 LED30 NW 35MO PDIM30 BLE SOLAR EX	-20 °C to +35 °C
919515898028	BRP710 LED30 CW 35MO PDIM30 BLE SOLAR EX	-20 °C to +35 °C
919515898032	BRP710 LED30 CW 60MO PDIM30 BLE SOLAR EX	-20 °C to +35 °C
919515898033	BRP710 LED20 WW 35MO PDIM50 BLE SOLAR EX	-20 °C to +35 °C
919515898034	BRP710 LED20 NW 35MO PDIM50 BLE SOLAR EX	-20 °C to +35 °C
919515898035	BRP710 LED20 CW 35MO PDIM50 BLE SOLAR EX	-20 °C to +35 °C
919615811178	BRP710 LED20 CW Housing KIT Solar	-20 °C to +35 °C
919615811179	BRP710 LED30 CW Housing KIT Solar	-20 °C to +35 °C
919515813976	BRP710 LED20 CW MR HY FDIM50 SOLAR	-20 °C to +35 °C
919515813977	BRP710 LED30 CW MR HY FDIM50 SOLAR	-20 °C to +35 °C
919515813980	BRP710 LED20 CW MR HY SOLAR	-20 °C to +35 °C
919515813981	BRP710 LED30 CW MR HY SOLAR	-20 °C to +35 °C
919515813983	BRP710 LED20 NW MR HY FDIM50 SOLAR	-20 °C to +35 °C
919515813984	BRP710 LED30 NW MR HY FDIM50 SOLAR	-20 °C to +35 °C
919515813987	BRP710 LED20 NW MR HY SOLAR	-20 °C to +35 °C
919515813988	BRP710 LED30 NW MR HY SOLAR	-20 °C to +35 °C
919515813990	BRP710 LED20 WW MR HY FDIM50 SOLAR	-20 °C to +35 °C
919515813991	BRP710 LED30 WW MR HY FDIM50 SOLAR	-20 °C to +35 °C
919515813994	BRP710 LED20 WW MR HY SOLAR	-20 °C to +35 °C
919515813995	BRP710 LED30 WW MR HY SOLAR	-20 °C to +35 °C

Order Code	Full Product Name	Ambient temperature range for discharging (when light is on)
919515898031	BRP710 LED30 NW 60MO PDIM30 BLE SOLAR EX	-20 °C to +35 °C
919515812830	BRP710 LED45 CW MR S1 12V LFP Solar IN	-20 °C to +35 °C
919515812831	BRP710 LED45 CW MR S1 12V FD30 Solar IN	-20 °C to +35 °C
919515813566	BRP710 LED45 CW MR S1 12V LFP Solar	-20 °C to +35 °C
919515813567	BRP710 LED45 CW MR S1 12V FD30 Solar	-20 °C to +35 °C
919515813568	BRP710 LED45 WW MR S1 12V LFP Solar	-20 °C to +35 °C
919515813569	BRP710 LED45 NW MR S1 12V LFP Solar	-20 °C to +35 °C
919515813570	BRP710 LED45 WW MR S1 12V FD30 Solar	-20 °C to +35 °C
919515813571	BRP710 LED45 NW MR S1 12V FD30 Solar	-20 °C to +35 °C
919515814302	BRP710 LED45 WW 60MO PDIM30 BLE Solar	-20 °C to +35 °C
919515898029	BRP710 LED45 NW 60MO PDIM30 BLE SOLAR EX	-20 °C to +35 °C
919515898030	BRP710 LED45 CW 60MO PDIM30 BLE SOLAR EX	-20 °C to +35 °C
919615811180	BRP710 LED45 CW Housing KIT Solar	-20 °C to +35 °C
919615811265	BRP710 P LED45 CW MR 12V LFP Solar P4125	-20 °C to +35 °C
919515814304	BRP710 LED30 WW 60MO PDIM30 BLE Solar	-20 °C to +35 °C
919415811054	SPARE BT LFP 12.8V 13.6Ah SOLAR EQUIP	-20 °C to +60 °C
919415811055	SPARE BT LFP 12.8V 20Ah SOLAR EQUIP	-20 °C to +60 °C
919415811056	SPARE BT LFP 12.8V 30Ah SOLAR EQUIP	-20 °C to +60 °C