



Urban style that last. All-purpose lighting solution.

VistaGlow

VistaGlow bulkhead is an IP65, all-purpose lighting solution meant for indoor and semi outdoor application. This luminaire is designed to offer general lighting for applications such as staircases, circulation areas in the buildings and lift wells etc. VistaGlow bulkhead has robust all-weather design with a pressure die casting housing and polycarbonate cover which are sealed for life to offer a dustproof and waterproof solution. The product is available in three color temperatures to meet the requirements of different applications.

Benefits

- Aesthetical design that combines well with the interiors
- Suitable for use on dusty and semi outdoor environment
- Best-in-class efficacy, low connected load
- Creates a diffused natural light, ensuring visual comfort
- Long useful life with low maintenance
- Multiple options in CCT make it suitable for different applications in indoor
- Easy to install

Features

- High ingress protection-IP65
- Impact resistant-IK08
- Compact integral design
- Light color : 4000K, 6500K
- Pressure diecast housing and polycarbonate cover
- External mounting through simple tools

Application

- Lift wells
- Staircases
- Indoor circulation areas
- Wall mounted application in semi outdoor area
- Balconies and terraces
- Government buildings

Warnings and Safety

- Meant for use in Indoor Industrial environment only


Versions



WT140W LED7S

Dimensional drawing

Product : Bulkhead
Type : WT140W
Application : Outdoor



Product details



WT140W LED7S



WT140W LED7S

Product details



WT140W LED7S

General Information	
Driver included	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	107 lm/W
Luminous Flux	700 lm
Optic type	Beam angle 120°
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	140-270 V
Power Consumption	6.5 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate
Housing Color	Gray
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	0 to +45 °C
Flammability mark	For mounting on normally flammable surfaces
Initial Performance (IEC Compliant)	
Initial chromaticity	<5

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)
919515812243	WT140W LED7S CW PSU S1 PC	6500 K
919515812244	WT140W LED7S NW PSU S1 PC	4000 K

