



Robust Design, superior performance, Unparallel strength and Durability with Superior aesthetics suitable for versatile road applications

SmartBright Street BRP042

Smartbright LED is a sleek elegant & finless design innovative streetlight with best in class energy efficiency. Ease of maintenance with dual optics makes it unique and differentiated from others. Smartbright uses High efficacy driver and LED platform to ensure higher energy saving and reliable operation over committed lifetime.

Smartbright LED Luminaire is a high pressure die-cast IK 07 rated housing, ensuring high strength and safety on the pole. The solid die-cast aluminum also has excellent heat dissipation, extending the life of the components inside. The multiple lumen packs and optics makes it optimum for the B2 category of Roads.

Benefits

- Use with peace of mind
- Long-lasting performance
- High-quality materials and design
- Uniform lighting

SmartBright Street BRP042

Features

- 4KV Surge Protection
- IK07 classification
- IP65 certified
- Designed for energy savings of up to 70% compared with conventional lighting
- Life class of 50k hrs@L70B50
- Designed for operations under diverse environment from -10°C to 45°C
- Finless design with superior aesthetic looks
- Toughened and shatter-proof quality built-in lens enhances safety
- Pressure die-cast housing offers excellent corrosion-resistance and robustness
- Streetlight distribution with uniform lighting on the street

Application

- Road and Street
- Residential
- Security Lighting
- Parks
- Gated Communities

Warnings and Safety

- Meant for use in Outdoor applications


Versions



BRP042

Dimensional drawing

Product: SmartBright Street BRP042
Type: BRP042
Application: Street Lighting Solution



SmartBright Street BRP042

General Information	
Driver included	Yes
Light Technical	
Luminaire light beam spread	60°
Light source color	857 daylight
Correlated Color Temperature (Nom)	5700 K
Color rendering index (CRI)	>70
Luminous Flux	95 lm
Optic type outdoor	Asymmetrical axis angle 60° wide beam
Operating and Electrical	
Surge Protection (Common/ Differential)	Surge protection level until 4 kV
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate
Housing Color	Gray
Mech. impact protection code	IK07
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	0 to +35 °C
Flammability mark	For mounting on normally flammable surfaces

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)
919515811468	BRP042 LED 14 CW MR S1 PSU GR	1,400 lm/W
919515811469	BRP042 LED 19 CW MR S1 PSU GR	1,900 lm/W

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
919515811468	BRP042 LED 14 CW MR S1 PSU GR	15 W	919515811469	BRP042 LED 19 CW MR S1 PSU GR	20 W

