



The new Coreline slim batten is slim design and come in 3 sizes and 2 CCT choices based on specific customer needs.

Coreline Slim Batten

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Benefits

- Slim and Robust design
- 50K Hours Life L70B50
- 5 Years warranty

Features

- Energy efficient with long service life. (50 000 hours - L70)
- 5 Years Warranty
- IP20, IK04
- CRI80
- 3 Different sizes L600/L1200/L1500 and 2 Different CCT (4000K/6500K) choices

Coreline Slim Batten

Application

- Offices
- Residential
- Parking Garages




Versions



BN126C LED41S L1200

BN126C LED22S L600

Dimensional drawing



Coreline Slim Batten

General Information	
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	105 lm/W
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Optical cover type	Polycarbonate Diffuser
Housing Color	White RAL 9003
Mech. impact protection code	IK04
Ingress protection code	IP20/40
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Flux
911401898980	BN126C LED41S/840 PSU L1200	4000 K	4,100 lm
911401899080	BN126C LED41S/865 PSU L1200	6500 K	4,100 lm
911401899180	BN126C LED60S/840 PSU L1500	4000 K	6,000 lm
911401899280	BN126C LED60S/865 PSU L1500	6500 K	6,000 lm
911401898780	BN126C LED22S/840 PSU L600	4000 K	2,200 lm
911401898880	BN126C LED22S/865 PSU L600	6500 K	2,200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401898980	BN126C LED41S/840 PSU L1200	31 W
911401899080	BN126C LED41S/865 PSU L1200	31 W
911401899180	BN126C LED60S/840 PSU L1500	46 W

Order Code	Full Product Name	Power Consumption
911401899280	BN126C LED60S/865 PSU L1500	46 W
911401898780	BN126C LED22S/840 PSU L600	17 W
911401898880	BN126C LED22S/865 PSU L600	17 W

