



New Trunklinea Plus Batten provide flexibility to customer to choose from 3 CCT and 4 different size and lumen packages, based on their specific need

Trunklinea Plus

The new Philips Trunklinea Plus offers exceptional value. It is Perfect for your everyday lighting installations. Available in 4 standard sizes and 3 CCTs to provide flexibility to customer. It provide quality light and substantial energy and maintenance savings. This new batten range can be used to replace traditional battens with T5 fluorescent lamps.

Benefits

- Slim and trunkable, integrated design
- Polycarbonate housing with one pc extrusion process
- Slim profile: Ideal for task lighting / cove lighting applications

Trunklinea Plus





Features

- 15,000 hrs life, L70/B50
- 1 year warranty
- 4 lengths, 3 colors Increased number of options for easy application
- CRI 70, SDCM < 7, 80lm/W
- Mounting accessories included

Application

- Hospitality
- Offices
- Residential

Dimensional drawing



Trunklinea Plus

| | |
|-------------------------------------|--------------------------------------|
| Light Technical | |
| Color rendering index (CRI) | >70 |
| Luminous Efficacy (rated) (Nom) | 80 lm/W |
| Operating and Electrical | |
| Protection class IEC | Safety class II |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Optical cover type | Opal diffuser in polycarbonate cover |
| Housing Color | White |
| Mech. impact protection code | IK02 |
| Ingress protection code | IP20 |
| Approval and Application | |
| Ambient temperature range | -20 to +40 °C |
| CE mark | No |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |

Light Technical

| Order Code | Full Product Name | Correlated Color Temperature | |
|--------------|---|------------------------------|---------------|
| | | (Nom) | Luminous Flux |
| 911401868080 | 31600 Trunklinea Plus LED3/WW L300 GM | 6500 K | 300 lm |
| 911401868180 | 31600 Trunklinea Plus LED3/NW L300 GM | 4000 K | 300 lm |
| 911401868280 | 31600 Trunklinea Plus LED3/CW L300 GM | 3000 K | 300 lm |
| 911401868680 | 31600 Trunklinea Plus LED9/WW L900 GM | 6500 K | 900 lm |
| 911401868780 | 31600 Trunklinea Plus LED9/NW L900 GM | 4000 K | 900 lm |
| 911401868880 | 31600 Trunklinea Plus LED9/CW L900 GM | 3000 K | 900 lm |
| 911401868980 | 31600 Trunklinea Plus LED12/WW L1200 GM | 6500 K | 1,100 lm |
| 911401869080 | 31600 Trunklinea Plus LED12/NW L1200 GM | 4000 K | 1,100 lm |
| 911401869180 | 31600 Trunklinea Plus LED12/CW L1200 GM | 3000 K | 1,100 lm |
| 911401868380 | 31600 Trunklinea Plus LED6/WW L600 GM | 6500 K | 500 lm |
| 911401868480 | 31600 Trunklinea Plus LED6/NW L600 GM | 4000 K | 500 lm |
| 911401868580 | 31600 Trunklinea Plus LED6/CW L600 GM | 3000 K | 500 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption |
|--------------|---------------------------------------|-------------------|
| 911401868080 | 31600 Trunklinea Plus LED3/WW L300 GM | 4 W |
| 911401868180 | 31600 Trunklinea Plus LED3/NW L300 GM | 4 W |
| 911401868280 | 31600 Trunklinea Plus LED3/CW L300 GM | 4 W |
| 911401868680 | 31600 Trunklinea Plus LED9/WW L900 GM | 10 W |
| 911401868780 | 31600 Trunklinea Plus LED9/NW L900 GM | 10 W |
| 911401868880 | 31600 Trunklinea Plus LED9/CW L900 GM | 10 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|---|-------------------|
| 911401868980 | 31600 Trunklinea Plus LED12/WW L1200 GM | 13 W |
| 911401869080 | 31600 Trunklinea Plus LED12/NW L1200 GM | 13 W |
| 911401869180 | 31600 Trunklinea Plus LED12/CW L1200 GM | 13 W |
| 911401868380 | 31600 Trunklinea Plus LED6/WW L600 GM | 7 W |
| 911401868480 | 31600 Trunklinea Plus LED6/NW L600 GM | 7 W |
| 911401868580 | 31600 Trunklinea Plus LED6/CW L600 GM | 7 W |

