



# The new generation of energy-saving LED PLC 2P tube lighting

## CorePro LED PLC 2P

CorePro LED PLC 2P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

### Benefits

- Reduced operational cost thanks to lower energy consumption
- Lower maintenance cost thanks to 2-3 times longer lifetime than conventional lamps
- Fastest and easiest way to upgrade existing luminaires to LED technology
- Completely safe product and installation process

### Features




- Highly energy-efficient
- Easy installation
- Conventional form factor to fit into existing luminaires
- No mercury

### Application

- Hospitality, retail, office, industrial and home applications

CorePro LED PLC 2P

Dimensional drawing



| Product                  | D1    | D     | A1    | A2    | A3     |
|--------------------------|-------|-------|-------|-------|--------|
| LED PLC 7.5W 830 2P G24d | 38 mm | 38 mm | 40 mm | 93 mm | 115 mm |
| LED PLC 7.5W 840 2P G24d | 38 mm | 38 mm | 40 mm | 93 mm | 115 mm |
| LED PLC 7.5W 865 2P G24d | 38 mm | 38 mm | 40 mm | 93 mm | 115 mm |
| LED PLC 9W 830 2P G24d   | 38 mm | 38 mm | 40 mm | 93 mm | 115 mm |
| LED PLC 9W 840 2P G24d   | 38 mm | 38 mm | 40 mm | 93 mm | 115 mm |
| LED PLC 9W 865 2P G24d   | 38 mm | 38 mm | 40 mm | 93 mm | 115 mm |

| Product                            | D1    | D2    | A1     | A2     | A3     |
|------------------------------------|-------|-------|--------|--------|--------|
| CorePro LED PLC 5.9W 830 2P G24d-1 | 34 mm |       | 95 mm  | 115 mm | 138 mm |
| CorePro LED PLC 5.9W 840 2P G24d-1 | 34 mm |       | 95 mm  | 115 mm | 138 mm |
| CorePro LED PLC 6.9W 830 2P G24d-2 | 34 mm |       | 106 mm | 125 mm | 148 mm |
| CorePro LED PLC 6.9W 840 2P G24d-2 | 34 mm | 34 mm | 106 mm | 125 mm | 148 mm |
| CorePro LED PLC 8.9W 830 2P G24d-3 | 34 mm |       | 129 mm | 148 mm | 171 mm |
| CorePro LED PLC 8.9W 840 2P G24d-3 | 34 mm | 34 mm | 129 mm | 148 mm | 171 mm |
| LED PLC 6.9W 840 2P G24d-2         | 34 mm | 34 mm | 106 mm | 125 mm | 148 mm |
| LED PLC 8.9W 830 2P G24d-3         | 34 mm | 34 mm | 129 mm | 148 mm | 171 mm |
| LED PLC 8.9W 840 2P G24d-3         | 34 mm | 34 mm | 129 mm | 148 mm | 171 mm |

| Product                            | D1    | D     | A1     | A2     | A3     |
|------------------------------------|-------|-------|--------|--------|--------|
| CorePro LED PLC 4.5W 840 2P G24d-1 | 34 mm | 34 mm | 95 mm  | 115 mm | 138 mm |
| CorePro LED PLC 6.5W 830 2P G24d-2 | 34 mm | 34 mm | 106 mm | 125 mm | 148 mm |
| CorePro LED PLC 6.5W 840 2P G24d-2 | 34 mm | 34 mm | 106 mm | 125 mm | 148 mm |
| CorePro LED PLC 8.5W 830 2P G24d-3 | 34 mm | 34 mm | 129 mm | 148 mm | 171 mm |
| CorePro LED PLC 8.5W 840 2P G24d-3 | 34 mm | 34 mm | 129 mm | 148 mm | 171 mm |
| LED PLC 6.5W 830 2P G24d-2         | 34 mm | 34 mm | 106 mm | 125 mm | 148 mm |
| LED PLC 6.5W 840 2P G24d-2         | 34 mm | 34 mm | 106 mm | 125 mm | 148 mm |
| LED PLC 6.5W 865 2P G24d-2         | 34 mm | 34 mm | 106 mm | 125 mm | 148 mm |
| LED PLC 8.5W 830 2P G24d-3         | 34 mm | 34 mm | 129 mm | 148 mm | 171 mm |
| LED PLC 8.5W 865 2P G24d-3         | 34 mm | 34 mm | 129 mm | 148 mm | 171 mm |

CorePro LED PLC 2P

|                                       |             |
|---------------------------------------|-------------|
| General Information                   |             |
| Switching Cycle                       | 50,000      |
| Light Technical                       |             |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %        |
| Operating and Electrical              |             |
| Input Frequency                       | 50 to 60 Hz |
| Starting Time (Nom)                   | 0.5 s       |
| Controls and Dimming                  |             |
| Dimmable                              | No          |
| Mechanical and Housing                |             |
| Bulb Shape                            | PL-C        |

General Information

| Order Code   | Full Product Name                  | Cap-Base | Nominal lifetime | Order Code   | Full Product Name                  | Cap-Base | Nominal lifetime |
|--------------|------------------------------------|----------|------------------|--------------|------------------------------------|----------|------------------|
| 929001878908 | LED PLC 7.5W 830 2P G24d           | G24d     | 15,000 hour(s)   | 929001280208 | LED PLC 6.5W 865 2P G24d-2         | G24d-2   | 30,000 hour(s)   |
| 929001879008 | LED PLC 7.5W 840 2P G24d           | G24d     | 15,000 hour(s)   | 929003757202 | CorePro LED PLC 6.9W 830 2P G24d-2 | G24d-2   | 30,000 hour(s)   |
| 929001879108 | LED PLC 7.5W 865 2P G24d           | G24d     | 15,000 hour(s)   | 929003757302 | CorePro LED PLC 6.9W 840 2P G24d-2 | G24d-2   | 30,000 hour(s)   |
| 929001879208 | LED PLC 9W 830 2P G24d             | G24d     | 15,000 hour(s)   | 929003757308 | LED PLC 6.9W 840 2P G24d-2         | G24d-2   | 30,000 hour(s)   |
| 929001879308 | LED PLC 9W 840 2P G24d             | G24d     | 15,000 hour(s)   | 929001201202 | CorePro LED PLC 8.5W 830 2P G24d-3 | G24d-3   | 30,000 hour(s)   |
| 929001879408 | LED PLC 9W 865 2P G24d             | G24d     | 15,000 hour(s)   | 929001201208 | LED PLC 8.5W 830 2P G24d-3         | G24d-3   | 30,000 hour(s)   |
| 929001350802 | CorePro LED PLC 4.5W 840 2P G24d-1 | G24d-1   | 30,000 hour(s)   | 929001201302 | CorePro LED PLC 8.5W 840 2P G24d-3 | G24d-3   | 30,000 hour(s)   |
| 929003757002 | CorePro LED PLC 5.9W 830 2P G24d-1 | G24d-1   | 30,000 hour(s)   | 929001280108 | LED PLC 8.5W 865 2P G24d-3         | G24d-3   | 30,000 hour(s)   |
| 929003757102 | CorePro LED PLC 5.9W 840 2P G24d-1 | G24d-1   | 30,000 hour(s)   | 929003757402 | CorePro LED PLC 8.9W 830 2P G24d-3 | G24d-3   | 30,000 hour(s)   |
| 929001201402 | CorePro LED PLC 6.5W 830 2P G24d-2 | G24d-2   | 30,000 hour(s)   | 929003757408 | LED PLC 8.9W 830 2P G24d-3         | G24d-3   | 30,000 hour(s)   |
| 929001201408 | LED PLC 6.5W 830 2P G24d-2         | G24d-2   | 30,000 hour(s)   | 929003757502 | CorePro LED PLC 8.9W 840 2P G24d-3 | G24d-3   | 30,000 hour(s)   |
| 929001201502 | CorePro LED PLC 6.5W 840 2P G24d-2 | G24d-2   | 30,000 hour(s)   | 929003757508 | LED PLC 8.9W 840 2P G24d-3         | G24d-3   | 30,000 hour(s)   |
| 929001201508 | LED PLC 6.5W 840 2P G24d-2         | G24d-2   | 30,000 hour(s)   |              |                                    |          |                  |

Light Technical

| Order Code   | Full Product Name                  | Beam Angle (Nom) | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Color Code | Luminous Flux |
|--------------|------------------------------------|------------------|------------------------------------|-----------------------------|------------|---------------|
| 929001878908 | LED PLC 7.5W 830 2P G24d           | 240 degree(s)    | 3000 K                             | 80                          | 830        | 750 lm        |
| 929001879008 | LED PLC 7.5W 840 2P G24d           | 240 degree(s)    | 4000 K                             | 80                          | 840        | 806 lm        |
| 929001879108 | LED PLC 7.5W 865 2P G24d           | 240 degree(s)    | 6500 K                             | 80                          | 865        | 806 lm        |
| 929001879208 | LED PLC 9W 830 2P G24d             | 240 degree(s)    | 3000 K                             | 80                          | 830        | 950 lm        |
| 929001879308 | LED PLC 9W 840 2P G24d             | 240 degree(s)    | 4000 K                             | 80                          | 840        | 1,050 lm      |
| 929001879408 | LED PLC 9W 865 2P G24d             | 240 degree(s)    | 6500 K                             | 80                          | 865        | 1,050 lm      |
| 929001350802 | CorePro LED PLC 4.5W 840 2P G24d-1 | 120 degree(s)    | 4000 K                             | 83                          | 840        | 500 lm        |
| 929003757002 | CorePro LED PLC 5.9W 830 2P G24d-1 | 120 degree(s)    | 3000 K                             | 82                          | 830        | 600 lm        |
| 929003757102 | CorePro LED PLC 5.9W 840 2P G24d-1 | 120 degree(s)    | 4000 K                             | 82                          | 840        | 660 lm        |
| 929001201402 | CorePro LED PLC 6.5W 830 2P G24d-2 | 120 degree(s)    | 3000 K                             | 83                          | 830        | 650 lm        |
| 929001201408 | LED PLC 6.5W 830 2P G24d-2         | 120 degree(s)    | 3000 K                             | 83                          | 830        | 650 lm        |
| 929001201502 | CorePro LED PLC 6.5W 840 2P G24d-2 | 120 degree(s)    | 4000 K                             | 83                          | 840        | 700 lm        |
| 929001201508 | LED PLC 6.5W 840 2P G24d-2         | 120 degree(s)    | 4000 K                             | 83                          | 840        | 700 lm        |
| 929001280208 | LED PLC 6.5W 865 2P G24d-2         | 120 degree(s)    | 6500 K                             | 83                          | 865        | 700 lm        |
| 929003757202 | CorePro LED PLC 6.9W 830 2P G24d-2 | 120 degree(s)    | 3000 K                             | 82                          | 830        | 700 lm        |

## CorePro LED PLC 2P

| Order Code   | Full Product Name                  | Beam Angle (Nom) | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Color Code | Luminous Flux |
|--------------|------------------------------------|------------------|------------------------------------|-----------------------------|------------|---------------|
| 929003757302 | CorePro LED PLC 6.9W 840 2P G24d-2 | 120 degree(s)    | 4000 K                             | 82                          | 840        | 770 lm        |
| 929003757308 | LED PLC 6.9W 840 2P G24d-2         | 120 degree(s)    | 4000 K                             | 82                          | 840        | 770 lm        |
| 929001201202 | CorePro LED PLC 8.5W 830 2P G24d-3 | 120 degree(s)    | 3000 K                             | 83                          | 830        | 950 lm        |
| 929001201208 | LED PLC 8.5W 830 2P G24d-3         | 120 degree(s)    | 3000 K                             | 83                          | 830        | 950 lm        |
| 929001201302 | CorePro LED PLC 8.5W 840 2P G24d-3 | 120 degree(s)    | 4000 K                             | 83                          | 840        | 1,000 lm      |
| 929001280108 | LED PLC 8.5W 865 2P G24d-3         | 120 degree(s)    | 6500 K                             | 83                          | 865        | 1,000 lm      |
| 929003757402 | CorePro LED PLC 8.9W 830 2P G24d-3 | 120 degree(s)    | 3000 K                             | 82                          | 830        | 990 lm        |
| 929003757408 | LED PLC 8.9W 830 2P G24d-3         | 120 degree(s)    | 3000 K                             | 82                          | 830        | 990 lm        |
| 929003757502 | CorePro LED PLC 8.9W 840 2P G24d-3 | 120 degree(s)    | 4000 K                             | 82                          | 840        | 1,100 lm      |
| 929003757508 | LED PLC 8.9W 840 2P G24d-3         | 120 degree(s)    | 4000 K                             | 82                          | 840        | 1,100 lm      |

### Operating and Electrical

| Order Code   | Full Product Name                  | Line Frequency | Power       | Wattage    |
|--------------|------------------------------------|----------------|-------------|------------|
|              |                                    |                | Consumption | Equivalent |
| 929001878908 | LED PLC 7.5W 830 2P G24d           | 50 to 60 Hz    | 7.5 W       | -          |
| 929001879008 | LED PLC 7.5W 840 2P G24d           | 50 to 60 Hz    | 7.5 W       | -          |
| 929001879108 | LED PLC 7.5W 865 2P G24d           | 50 to 60 Hz    | 7.5 W       | -          |
| 929001879208 | LED PLC 9W 830 2P G24d             | 50 to 60 Hz    | 9 W         | -          |
| 929001879308 | LED PLC 9W 840 2P G24d             | 50 to 60 Hz    | 9 W         | -          |
| 929001879408 | LED PLC 9W 865 2P G24d             | 50 to 60 Hz    | 9 W         | -          |
| 929001350802 | CorePro LED PLC 4.5W 840 2P G24d-1 | 50 to 60 Hz    | 4.5 W       | -          |
| 929003757002 | CorePro LED PLC 5.9W 830 2P G24d-1 | -              | 5.9 W       | -          |
| 929003757102 | CorePro LED PLC 5.9W 840 2P G24d-1 | -              | 5.9 W       | -          |
| 929001201402 | CorePro LED PLC 6.5W 830 2P G24d-2 | 50 to 60 Hz    | 6.5 W       | -          |
| 929001201408 | LED PLC 6.5W 830 2P G24d-2         | 50 to 60 Hz    | 6.5 W       | -          |
| 929001201502 | CorePro LED PLC 6.5W 840 2P G24d-2 | 50 to 60 Hz    | 6.5 W       | -          |
| 929001201508 | LED PLC 6.5W 840 2P G24d-2         | 50 to 60 Hz    | 6.5 W       | -          |
| 929001280208 | LED PLC 6.5W 865 2P G24d-2         | 50 to 60 Hz    | 6.5 W       | -          |

| Order Code   | Full Product Name                  | Line Frequency | Power       | Wattage    |
|--------------|------------------------------------|----------------|-------------|------------|
|              |                                    |                | Consumption | Equivalent |
| 929003757202 | CorePro LED PLC 6.9W 830 2P G24d-2 | -              | 6.9 W       | -          |
| 929003757302 | CorePro LED PLC 6.9W 840 2P G24d-2 | -              | 6.9 W       | -          |
| 929003757308 | LED PLC 6.9W 840 2P G24d-2         | -              | 6.9 W       | 18 W       |
| 929001201202 | CorePro LED PLC 8.5W 830 2P G24d-3 | 50 to 60 Hz    | 8.5 W       | -          |
| 929001201208 | LED PLC 8.5W 830 2P G24d-3         | 50 to 60 Hz    | 8.5 W       | -          |
| 929001201302 | CorePro LED PLC 8.5W 840 2P G24d-3 | 50 to 60 Hz    | 8.5 W       | -          |
| 929001280108 | LED PLC 8.5W 865 2P G24d-3         | 50 to 60 Hz    | 8.5 W       | -          |
| 929003757402 | CorePro LED PLC 8.9W 830 2P G24d-3 | -              | 8.9 W       | -          |
| 929003757408 | LED PLC 8.9W 830 2P G24d-3         | -              | 8.9 W       | 26 W       |
| 929003757502 | CorePro LED PLC 8.9W 840 2P G24d-3 | -              | 8.9 W       | -          |
| 929003757508 | LED PLC 8.9W 840 2P G24d-3         | -              | 8.9 W       | 26 W       |

### Temperature

| Order Code   | Full Product Name        | T-Case Maximum (Nom) |
|--------------|--------------------------|----------------------|
| 929001878908 | LED PLC 7.5W 830 2P G24d | 64 °C                |
| 929001879008 | LED PLC 7.5W 840 2P G24d | 64 °C                |

| Order Code   | Full Product Name        | T-Case Maximum (Nom) |
|--------------|--------------------------|----------------------|
| 929001879108 | LED PLC 7.5W 865 2P G24d | 64 °C                |
| 929001879208 | LED PLC 9W 830 2P G24d   | 72 °C                |

CorePro LED PLC 2P

| Order Code   | Full Product Name                  | T-Case Maximum (Nom) |
|--------------|------------------------------------|----------------------|
| 929001879308 | LED PLC 9W 840 2P G24d             | 72 °C                |
| 929001879408 | LED PLC 9W 865 2P G24d             | 72 °C                |
| 929001350802 | CorePro LED PLC 4.5W 840 2P G24d-1 | 60 °C                |
| 929003757002 | CorePro LED PLC 5.9W 830 2P G24d-1 | 75 °C                |
| 929003757102 | CorePro LED PLC 5.9W 840 2P G24d-1 | 75 °C                |
| 929001201402 | CorePro LED PLC 6.5W 830 2P G24d-2 | 65 °C                |
| 929001201408 | LED PLC 6.5W 830 2P G24d-2         | 65 °C                |
| 929001201502 | CorePro LED PLC 6.5W 840 2P G24d-2 | 65 °C                |
| 929001201508 | LED PLC 6.5W 840 2P G24d-2         | 65 °C                |
| 929001280208 | LED PLC 6.5W 865 2P G24d-2         | 65 °C                |
| 929003757202 | CorePro LED PLC 6.9W 830 2P G24d-2 | 75 °C                |

| Order Code   | Full Product Name                  | T-Case Maximum (Nom) |
|--------------|------------------------------------|----------------------|
| 929003757302 | CorePro LED PLC 6.9W 840 2P G24d-2 | 75 °C                |
| 929003757308 | LED PLC 6.9W 840 2P G24d-2         | 75 °C                |
| 929001201202 | CorePro LED PLC 8.5W 830 2P G24d-3 | 75 °C                |
| 929001201208 | LED PLC 8.5W 830 2P G24d-3         | 75 °C                |
| 929001201302 | CorePro LED PLC 8.5W 840 2P G24d-3 | 75 °C                |
| 929001280108 | LED PLC 8.5W 865 2P G24d-3         | 75 °C                |
| 929003757402 | CorePro LED PLC 8.9W 830 2P G24d-3 | 75 °C                |
| 929003757408 | LED PLC 8.9W 830 2P G24d-3         | 75 °C                |
| 929003757502 | CorePro LED PLC 8.9W 840 2P G24d-3 | 75 °C                |
| 929003757508 | LED PLC 8.9W 840 2P G24d-3         | 75 °C                |

Mechanical and Housing

| Order Code   | Full Product Name                  | Bulb Finish |
|--------------|------------------------------------|-------------|
| 929001878908 | LED PLC 7.5W 830 2P G24d           | -           |
| 929001879008 | LED PLC 7.5W 840 2P G24d           | -           |
| 929001879108 | LED PLC 7.5W 865 2P G24d           | -           |
| 929001879208 | LED PLC 9W 830 2P G24d             | -           |
| 929001879308 | LED PLC 9W 840 2P G24d             | -           |
| 929001879408 | LED PLC 9W 865 2P G24d             | -           |
| 929001350802 | CorePro LED PLC 4.5W 840 2P G24d-1 | -           |
| 929003757002 | CorePro LED PLC 5.9W 830 2P G24d-1 | Frosted     |
| 929003757102 | CorePro LED PLC 5.9W 840 2P G24d-1 | Frosted     |
| 929001201402 | CorePro LED PLC 6.5W 830 2P G24d-2 | -           |
| 929001201408 | LED PLC 6.5W 830 2P G24d-2         | -           |
| 929001201502 | CorePro LED PLC 6.5W 840 2P G24d-2 | -           |
| 929001201508 | LED PLC 6.5W 840 2P G24d-2         | -           |

| Order Code   | Full Product Name                  | Bulb Finish |
|--------------|------------------------------------|-------------|
| 929001280208 | LED PLC 6.5W 865 2P G24d-2         | -           |
| 929003757202 | CorePro LED PLC 6.9W 830 2P G24d-2 | Frosted     |
| 929003757302 | CorePro LED PLC 6.9W 840 2P G24d-2 | Frosted     |
| 929003757308 | LED PLC 6.9W 840 2P G24d-2         | Frosted     |
| 929001201202 | CorePro LED PLC 8.5W 830 2P G24d-3 | -           |
| 929001201208 | LED PLC 8.5W 830 2P G24d-3         | -           |
| 929001201302 | CorePro LED PLC 8.5W 840 2P G24d-3 | -           |
| 929001280108 | LED PLC 8.5W 865 2P G24d-3         | -           |
| 929003757402 | CorePro LED PLC 8.9W 830 2P G24d-3 | Frosted     |
| 929003757408 | LED PLC 8.9W 830 2P G24d-3         | Frosted     |
| 929003757502 | CorePro LED PLC 8.9W 840 2P G24d-3 | Frosted     |
| 929003757508 | LED PLC 8.9W 840 2P G24d-3         | Frosted     |



Approval and Application

| Order Code   | Full Product Name                  | Ambient temperature range | Energy Consumption kWh/1000 h |
|--------------|------------------------------------|---------------------------|-------------------------------|
| 929001878908 | LED PLC 7.5W 830 2P G24d           | -20 °C to 45 °C           | -                             |
| 929001879008 | LED PLC 7.5W 840 2P G24d           | -20 °C to 45 °C           | -                             |
| 929001879108 | LED PLC 7.5W 865 2P G24d           | -20 °C to 45 °C           | -                             |
| 929001879208 | LED PLC 9W 830 2P G24d             | -20 °C to 45 °C           | -                             |
| 929001879308 | LED PLC 9W 840 2P G24d             | -20 °C to 45 °C           | -                             |
| 929001879408 | LED PLC 9W 865 2P G24d             | -20 °C to 45 °C           | -                             |
| 929001350802 | CorePro LED PLC 4.5W 840 2P G24d-1 | -20 °C to 35 °C           | 5 kWh                         |
| 929003757002 | CorePro LED PLC 5.9W 830 2P G24d-1 | -20 to +35 °C             | 6 kWh                         |

| Order Code   | Full Product Name                  | Ambient temperature range | Energy Consumption kWh/1000 h |
|--------------|------------------------------------|---------------------------|-------------------------------|
| 929003757102 | CorePro LED PLC 5.9W 840 2P G24d-1 | -20 to +35 °C             | 6 kWh                         |
| 929001201402 | CorePro LED PLC 6.5W 830 2P G24d-2 | -20 °C to 35 °C           | 7 kWh                         |
| 929001201408 | LED PLC 6.5W 830 2P G24d-2         | -20 °C to 35 °C           | 9 kWh                         |
| 929001201502 | CorePro LED PLC 6.5W 840 2P G24d-2 | -20 °C to 35 °C           | 7 kWh                         |
| 929001201508 | LED PLC 6.5W 840 2P G24d-2         | -20 °C to 35 °C           | 9 kWh                         |
| 929001280208 | LED PLC 6.5W 865 2P G24d-2         | -20 °C to 35 °C           | 9 kWh                         |
| 929003757202 | CorePro LED PLC 6.9W 830 2P G24d-2 | -20 to +35 °C             | 7 kWh                         |
| 929003757302 | CorePro LED PLC 6.9W 840 2P G24d-2 | -20 to +35 °C             | 7 kWh                         |

CorePro LED PLC 2P

| Order Code   | Full Product Name                     | Ambient temperature range | Energy Consumption kWh/1000 h |
|--------------|---------------------------------------|---------------------------|-------------------------------|
| 929003757308 | LED PLC 6.9W 840 2P<br>G24d-2         | -20 to +35 °C             | -                             |
| 929001201202 | CorePro LED PLC 8.5W<br>830 2P G24d-3 | -20 °C to 35 °C           | 9 kWh                         |
| 929001201208 | LED PLC 8.5W 830 2P<br>G24d-3         | -20 °C to 35 °C           | 11 kWh                        |
| 929001201302 | CorePro LED PLC 8.5W<br>840 2P G24d-3 | -20 °C to 35 °C           | 9 kWh                         |
| 929001280108 | LED PLC 8.5W 865 2P<br>G24d-3         | -20 °C to 35 °C           | 11 kWh                        |
| 929003757402 | CorePro LED PLC 8.9W<br>830 2P G24d-3 | -20 to +35 °C             | 9 kWh                         |
| 929003757408 | LED PLC 8.9W 830 2P<br>G24d-3         | -20 to +35 °C             | -                             |
| 929003757502 | CorePro LED PLC 8.9W<br>840 2P G24d-3 | -20 to +35 °C             | 9 kWh                         |
| 929003757508 | LED PLC 8.9W 840 2P<br>G24d-3         | -20 to +35 °C             | -                             |



CorePro LED PLC 2P

