



# Bright, stylish and slim interior module

## MyCare LED Circular

MyCare LED Ceiling Module integrates a LED light source into a module. It is specially designed to replace fluorescent circular tubes working on a G10q fitting. The module offers significant energy savings and a long lifetime.

### Benefits

- Simple, fast, installation method
- Significant energy saving
- Long lifetime

### Features

- Highly energy-efficient
- Long lifetime
- Easy installation
- High Brightness

### Application

- Home application
- Corridors & stairways
- Parking

Versions



LEDtube MOD GMGC 20W Circular




LEDtube MOD GMGC 14W Circular




LEDtube MOD GMGC 10W Circular


Dimensional drawing



Product	D1	D2	A1	A2	A3
LED MOD 20W G3 865	139 mm	139 mm	18 mm	126 mm	139 mm



Product	D1	D2	A1	A2	A3
LED MOD 14W G3 865	139 mm	139 mm	18 mm	126 mm	139 mm



Product	D1	D2	A1	A2	A3
LED MOD 25W G3 865	178.5 mm	178.5 mm	21 mm	160 mm	178.5 mm

MyCare LED Circular

General Information	
Cap-Base	-
Switching Cycle	15,000
Nominal lifetime	20,000 hour(s)
Light Technical	
Beam Angle (Nom)	150 degree(s)
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	83
Color Code	865
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	Others
Approval and Application	
Ambient temperature range	-20 to +45 °C

Light Technical

Order Code	Full Product Name	Luminous Flux
929003765909	LED MOD 25W G3 865	2,400 lm
929003765809	LED MOD 20W G3 865	1,900 lm
929003765709	LED MOD 14W G3 865	1,300 lm



Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003765909	LED MOD 25W G3 865	25 W	40 W
929003765809	LED MOD 20W G3 865	20 W	32 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003765709	LED MOD 14W G3 865	14 W	22 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003765909	LED MOD 25W G3 865	85 °C
929003765809	LED MOD 20W G3 865	85 °C
929003765709	LED MOD 14W G3 865	80 °C



# MyCare LED Circular

