



# Bright, stylish and slim interior module

## MyCare LED Circular

MyCare LED Ceiling Module integrates a LED light source into a module. It is specially designed to replace fluorescent circular tubes working on a G10q fitting. The module offers significant energy savings and a long lifetime.

### Benefits

- Simple, fast, installation method
- Significant energy saving
- Long lifetime

### Features

- Highly energy-efficient
- Long lifetime
- Easy installation
- High Brightness

### Application

- Home application
- Corridors & stairways
- Parking

Versions



LEDtube MOD GMGC 20W Circular





LEDtube MOD GMGC 10W Circular



LED Circular 840 G10q AP

Dimensional drawing



Product

LED Circular 20W 840 G10q AP

Product	D1	D2	A1	A2	A3
LED MOD 14W G3 865 APR	139 mm	139 mm	18 mm	126 mm	139 mm

Product	A1	A2	A3
LED MOD 20W 830 APR	21.5 mm	195 mm	217.5 mm

MyCare LED Circular

Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No

General Information

Order Code	Full Product Name	Cap-Base	Rated	Switching Cycle	Nominal lifetime
			Lifetime (Hours)		
929003620707	LED MOD 20W 830 APR	-	20,000 hour(s)	15,000	20,000 hour(s)
929003765707	LED MOD 14W G3 865 APR	-	-	15,000	20,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated	Switching Cycle	Nominal lifetime
			Lifetime (Hours)		
929002010907	LED Circular 20W 840 G10q AP	G10q	-	50,000	30,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003620707	LED MOD 20W 830 APR	120 degree(s)	3000 K	80	830	2,200 lm
929003765707	LED MOD 14W G3 865 APR	150 degree(s)	6500 K	83	865	1,300 lm
929002010907	LED Circular 20W 840 G10q AP	120 degree(s)	4000 K	80	840	2,000 lm

Operating and Electrical

Order Code	Full Product Name	Line	Power	Wattage
		Frequency	Consumption	Equivalent
929003620707	LED MOD 20W 830 APR	50 to 60 Hz	20 W	-
929003765707	LED MOD 14W G3 865 APR	-	14 W	22 W

Order Code	Full Product Name	Line	Power	Wattage
		Frequency	Consumption	Equivalent
929002010907	LED Circular 20W 840 G10q AP	-	20 W	32 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003620707	LED MOD 20W 830 APR	70 °C
929003765707	LED MOD 14W G3 865 APR	80 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002010907	LED Circular 20W 840 G10q AP	60 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003620707	LED MOD 20W 830 APR	Frosted	Others
929003765707	LED MOD 14W G3 865 APR	Frosted	Others

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002010907	LED Circular 20W 840 G10q AP	-	C-T9

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy
			Consumption kWh/1000 h
929003620707	LED MOD 20W 830 APR	-20 °C to 45 °C	-
929003765707	LED MOD 14W G3 865 APR	-20 to +45 °C	-
929002010907	LED Circular 20W 840 G10q AP	-20 to +45 °C	20 kWh

