



The perfect energy efficient LED Oyster solution

SmartBright LED Oyster

The new Philips tri-colour Splashproof Oyster offers exceptional value. It is perfect for your everyday lighting installations. It comes with a 3 CCT selection switch to provide flexibility to the customer.

Benefits

- Tri-color selectable with a slide of the dial
- Trailing/leading edge dimmable
- 30,000 hours life

Features





- Reliable LED Oyster for residential and general lighting applications
- Splashproof design with IP54 rating 3 years warranty
- 3 years warranty

Application

- Residential
- Office
- Hospitality

SmartBright LED Oyster

Dimensional drawing



General Information	
Light source replaceable	No
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	80
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP54
Approval and Application	
Ambient temperature range	-20 to +40 °C

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
929002562219	CL261 DS Oyster 15.5W 30-40-65K IP54 ANZ	87.00 lm/W	1,400 lm
929002562319	CL261 DS Oyster 22W 30-40-65K IP54 ANZ	95.00 lm/W	2,100 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929002562219	CL261 DS Oyster 15.5W 30-40-65K IP54 ANZ	15.5 W

Order Code	Full Product Name	Power Consumption
929002562319	CL261 DS Oyster 22W 30-40-65K IP54 ANZ	22 W

SmartBright LED Oyster

