



**Philips T8 LED  
Battens offers  
exceptional value.  
They provide quality  
light and substantial  
energy and  
maintenance savings  
compared to  
conventional  
luminaires.**

### **Smartbright T8 Batten**

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. New T8 LED batten range is perfect replacement for traditional battens with fluorescent lamps. The process of selecting, installing, and maintaining is so easy – it's a simple switch. The range offer customer to choose from various options, standalone batten, Batten with individual switch and connectable Battens in addition to 3 CCTs and 2 Wattages.

# Smartbright T8 Batten

## Benefits

- Slim Design: one piece PC extrusion housing
- Different options: Standalone batten with on/off switch and additional BN013 Trunkable version
- Ease of installation: Central and side cable entry

## Features

- 30,000 Hours lifetime (L70) with 3 Years warranty
- CRI 80, SDCM <6, 100lm/W, Superior light quality combined with good energy savings
- Central and side cable entry Ready solution for both new point and replacement
- 3 CCT (3000/4000/6500k) option for different customer needs
- On/Off switch version: Easy to use

## Application


- Retail
- Hospitality
- Offices

## Versions



Smartbright T8 Batten

## Dimensional drawing



## Smartbright T8 Batten

