



The greatest variety in LED Modules, suitable for every application

Fortimo LED strip

Fortimo LED strip allows you to design high-performance, slim linear LED luminaires without having to compromise on design freedom, quality of light, or total cost of ownership. The systems are ideal for use in luminaires for direct lighting in offices, banks, schools, public buildings, supermarkets and anywhere where a small, slim, flexible form factor is appreciated.

Beneficios

- Cover all needs in luminaire designs; different module lengths from 0.5ft to 5ft, high voltage or low voltage, a wide range of CCTs in CRI80 and CRI90, connectors on the front or back, different lumen output versions and wide temperature range -40 °C up to +90 °C
- Easy upgrade to high efficiency solutions; FlexTune (tunable white), high flux and HCL solutions
- Slim module width of only 20 mm

Fortimo LED strip

Características

- Excellent color consistency of 3 SDCM
- Two lumen packages per length available (650 lm per ft and 1100 lm per ft)
- Typical module efficacy of 184 lm/W (at 4000K CRI80)
- High performance for CRI90 of 175 lm/W (at 4000K CRI90)
- Wide range of CCT's: 2700K / 3000K / 4000K / 5000K / 6500K
- Choose from high voltage or low voltage designs
- Five-year system warranty and over 50,000 hours lifetime
- Available from 0.5ft up till 5ft versions with front or back connector
- Easily upgradeable with CES human centric lighting technology of FlexTune tunable white

Aplicaciones

- Office
- Retail
- Industry

Versions



Fortimo LED Strip 2ft LF 840 FC HV6

Fortimo LED Strip 2ft 2200lm FC HV5

Fortimo LED Strip 2ft MF 840 FC HV6

