



# A well-known footprint covering the needs for general lighting purposes

## Fortimo LED line

A well-known footprint covering the needs for general lighting purposes

### Benefits

- Cover all needs in luminaire designs; choice of color temperatures (3000, 4000 and 5000K), two module lengths (1 ft/280 mm or 2 ft/560 mm), three lumen packages (650, 1100, and 2000 lm per foot/280 mm) and wide temperature (Tc) range from -40 °C up to +90 °C
- Available in 1R systems and 3R systems
- Push-in connectors enabling automated wiring

### Features

- Excellent color consistency of 3 SDCM
- State-of-the-art LED module efficiency of up to 186 lm/W
- High color rendering CRI >80 and >90
- Tunable lumen output, efficacy and lifetime
- Five-year system warranty and over 50,000 hours lifetime

### Application

- Office
- Retail
- Industry

## Fortimo LED line

### Versions



Fortimo LED Line 2ft HF 1R HV5

