



Ahead in flexibility and connectivity

Xitanium LED linear drivers – non-isolated

Xitanium linear non-isolated drivers are ideal for high voltage (HV) professional general lighting applications. The range includes DALI dimmable and programmable, 1-10V dimmable, non-dimmable and single current versions. They offer high efficiency, good quality of light and full flexibility. The new generation of 16mm DALI drivers offer ultimate performance. They comply with the latest DiiA standards, including implementation of the new DALI parts related to data. Configuring the drivers can be done quickly and wirelessly with SimpleSet. The new 21mm DALI drivers offer the best value for money.

Benefits

- Non-isolated drivers to support HV and LV linear office systems
- Flexible operating windows to simplify dynamic generation and complexity management
- Complete range of Sensor Ready (SR) drivers for connected systems

Features

- Non-isolated DALI and Fixed Output drivers with 11 mm and 16 mm height
- Flexible programming of DALI drivers via MultiOne software or wireless via SimpleSet
- Low ripple output current for camera- and scanner-friendly performance
- Unique AM dimming in DALI drivers for flicker and noise-free dimming
- Five-year system warranty and 100,000 hour lifetime

Application

- Office
- Retail
- Industry

Xitanium LED linear drivers – non-isolated

Versions

| | | | |
|---|---|--|---|
|  | Xitanium LED linear drivers - Non - Isolated family |  | Xitanium non-isolated DALI driver |
|  | Xitanium non-iso 100W+150W iXt TD |  | CertaDrive 44W 0.35A 125V 230V EL Image |
|  | Xitanium non-isolated DALI driver |  | CertaDrive 60W 350mA |
|  | CertaDrive 65W 0.35A 185V 230V EL Image |  | Xitanium 90W 0.25-0.7A 220V TD21 |
| | |  | Xitanium 90W 21 |

Xitanium LED linear drivers – non-isolated

Versions

CertaDrive 30W 0.35A 85V 230V
EL Image



Xitanium non-isolated DALI driver




Xitanium 90W non-isolated non-dimmable driver LEDset



CertaDrive 21W 0.35A 60V 230V
EL Image



Dimensional drawing



| Product | A1 | A2 | B1 | C1 | D1 |
|---------------------------------------|--------|--------|-------|-------|--------|
| Xitanium 100W 0.15–0.5A 300V iXt 230V | 360 mm | 350 mm | 30 mm | 21 mm | 4.1 mm |

| Product | A1 | B1 | C1 | D1 | A2 |
|-------------------------------------|--------|-------|-------|--------|--------|
| Xitanium 75W 0.12–0.4A 215V TD 230V | 360 mm | 30 mm | 22 mm | 4.1 mm | 350 mm |

Xtanium LED linear drivers – non-isolated

