



# Comfortable LED ceiling light that's easy on your eyes

## Apex Ceiling light

With its EyeComfort design, Apex provides comfortable high quality LED light for home and residential project. Its long lifetime and high lumen maintenance ensures bright light level over time. With various shapes, sizes, it enables to serve from bedroom to big living room, and dining to kitchen space. Installation becomes easier with easy connector and installation bracket.

### Benefits

- Ensure comfortable LED light all around home, residential application
- Hassle free easy installation saves time and effort
- Stay bright along the long life time

### Features

- high quality LED light with EyeComfort feature, safe from Blue light hazard risk
- Easy to install with easy connector and bracket
- various models and size to fit for all rooms in residential application
- long lifetime of 20,000 hours with high lumen maintenance
- uniform light distribution

### Application

- Residential, home: living room, bedroom, dining room, kitchen

# Apex Ceiling light



## Versions



Ceiling APEX S LED 25W



Ceiling APEX L LED 45W

## Dimensional drawing




Product

Apex SQ LED 55W 4000K



Apex Ceiling light

Dimensional drawing



| Product              |
|----------------------|
| Apex S LED 25W 4000K |

| Product               |
|-----------------------|
| Apex RT LED 40W 4000K |

Product details



Ceiling APEX RT LED 40W ON 1-DPP




Ceiling APEX L LED 45W ON 1-DPP



Ceiling APEX S LED 25W ON 2-DPP

# Apex Ceiling light

## Product details



Ceiling APEX S LED 25W ON 1-DPP



Ceiling APEX SQ LED 55W ON 1-DPP



Ceiling APEX RT LED 40W ON 2-DPP



Ceiling APEX L LED 45W ON 2-DPP



Ceiling APEX SQ LED 55W ON 2-DPP

| General Information         |   |
|-----------------------------|---|
| Light source replaceable    | No  |
| Light Technical             |   |
| Color rendering index (CRI) | 80  |
| Operating and Electrical    |   |
| Protection class IEC        | Safety class I                              |
| Input Voltage               | 220 to 240 V                                |
| Line Frequency              | 50 or 60 Hz                                 |
| Controls and Dimming        |   |
| Dimmable                    | No  |
| Mechanical and Housing      |   |
| Housing Color               | White                                       |
| Ingress protection code     | IP20  |
| Approval and Application    |   |
| Ambient temperature range   | -20 to +40 °C                               |
| Flammability mark           | For mounting on normally flammable surfaces |

## Light Technical

| Order Code   | Full Product Name     | Correlated Color  | Luminous Efficacy (rated) |               |
|--------------|-----------------------|-------------------|---------------------------|---------------|
|              |                       | Temperature (Nom) | (Nom)                     | Luminous Flux |
| 929002612381 | Apex S LED 25W 4000K  | 4000 K            | 88.00 lm/W                | 2,200 lm      |
| 929002612481 | Apex S LED 25W 5700K  | 5700 K            | 88.00 lm/W                | 2,200 lm      |
| 929002612581 | Apex RT LED 40W 4000K | 4000 K            | 85.00 lm/W                | 3,400 lm      |
| 929002612681 | Apex RT LED 40W 5700K | 5700 K            | 85.00 lm/W                | 3,400 lm      |
| 929002612881 | Apex L LED 45W 5700K  | 5700 K            | 88.00 lm/W                | 4,000 lm      |
| 929002613181 | Apex SQ LED 55W 4000K | 4000 K            | 84.00 lm/W                | 4,200 lm      |
| 929002613281 | Apex SQ LED 55W 5700K | 5700 K            | 84.00 lm/W                | 4,200 lm      |

## Operating and Electrical

# Apex Ceiling light

| Order Code   | Full Product Name     | Power Consumption |
|--------------|-----------------------|-------------------|
| 929002612381 | Apex S LED 25W 4000K  | 25 W              |
| 929002612481 | Apex S LED 25W 5700K  | 25 W              |
| 929002612581 | Apex RT LED 40W 4000K | 40 W              |
| 929002612681 | Apex RT LED 40W 5700K | 40 W              |

| Order Code   | Full Product Name     | Power Consumption |
|--------------|-----------------------|-------------------|
| 929002612881 | Apex L LED 45W 5700K  | 45 W              |
| 929002613181 | Apex SQ LED 55W 4000K | 55 W              |
| 929002613281 | Apex SQ LED 55W 5700K | 55 W              |

## Initial Performance (IEC Compliant)

| Order Code   | Full Product Name     | Initial chromaticity          |
|--------------|-----------------------|-------------------------------|
| 929002612381 | Apex S LED 25W 4000K  | (ANSI4000K, 0.3818, 0.3797) 6 |
| 929002612481 | Apex S LED 25W 5700K  | (0.3287, 0.3425) 6            |
| 929002612581 | Apex RT LED 40W 4000K | (ANSI4000K, 0.3818, 0.3797) 6 |
| 929002612681 | Apex RT LED 40W 5700K | (0.3287, 0.3425) 6            |

| Order Code   | Full Product Name     | Initial chromaticity          |
|--------------|-----------------------|-------------------------------|
| 929002612881 | Apex L LED 45W 5700K  | (0.3287, 0.3425) 6            |
| 929002613181 | Apex SQ LED 55W 4000K | (ANSI4000K, 0.3818, 0.3797) 6 |
| 929002613281 | Apex SQ LED 55W 5700K | (0.3287, 0.3425) 6            |

