



Robust, connectable luminaire with outstanding performance.

Pacific LED Gen5

Pacific LED gen5 is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact and reliable luminaire with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED gen5 can perfectly withstand the harsh conditions of the automotive, food and heavy industries. But it also performs well in parking garages and warehouses. Pacific LED gen5 luminaires provide superior, artefact-free light quality and homogeneous light, offered with multiple optics and broad range of light outputs (up to 15,000 lm). This ensures more flexibility in optimized light scheme planning. They are also designed with a circular approach, which means these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. The luminaires stand out because of their quick and easy installation that facilitates through wiring and various connection and mounting options. But also, because of their attractive TCO, energy efficiency, and ease of maintenance – with minimum of disruption to operations in demanding applications. To make the Pacific LED gen5 even more complete, system integration with Interact Industry opens up additional opportunities for optimized efficiency, energy savings, improved light management, productivity, and safety. Making it future proof in every aspect. Discover Pacific LED gen5. Optimal performance for demanding environments.

Pacific LED Gen5

Benefits

- Long service life offering peace of mind on your lighting installation.
- Suitable for your industrial application due to wide coverage including food production, heavy and chemical industries, automotive, parking garages and warehousing.
- Lowers your maintenance investments due to easy servicing and parts replacements with a modular approach.
- Can be integrated into an Interact connected lighting installation to optimize your operations and maximize energy saving and insights.

Features

- Highly energy efficient and long lifetime: up to 160 lm/W and lifetime up to 100,000 hrs L80.
- Wide application coverage with extensive lumen output (up to 15000 lumen) and optics choice, combined with high quality chemical-resistant materials.
- Robust and compact product architecture, with high water and dust protection (IP66), combined with a high degree of mechanical protection (IK08).
- High uniformity, glare control and artefact-free light distributions.
- Hassle-free installation and maintenance.

Application

- Food Processing
- Parking Garages
- Manufacturing
- Warehouses/distribution centers

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Versions




Pacific LED gen5, L700




Pacific LED gen5, Wieland connector

Dimensional drawing



Pacific LED Gen5

Dimensional drawing



Product details



Pacific LED gen5, looping connection, 2 entry on one side



Pacific LED gen5 with push in 7-pole (PI7) connector



Pacific LED gen5 with WAGO connector



Pacific LED gen5 connection through WAGO connector side view



Pacific LED gen5 with Wiegand connector



Pacific LED gen5 with push in 5-pole (PI5) connecto

Pacific LED Gen5

Product details



Pacific LED gen5 connection
through WAGO connector

General Information	
Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK08
Ingress protection code	IP66
Approval and Application	
CE mark	Yes
ENEC mark	ENEC plus mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925867731	WT490C 80S/840 PSU NB-HRO PI5L1800	4000 K	165 lm/W	8,000 lm	Narrow beam - High-rack optic
910925867732	WT490C 80S/840 PSD NB-HRO PI5L1800	4000 K	165 lm/W	8,000 lm	Narrow beam - High-rack optic
910925867733	WT490C 80S/840 PSU WB TW3 PI5L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	4000 K	154 lm/W	8,000 lm	Wide beam
910925867735	WT490C 80S/840 PSD WB PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925867736	WT490C 80S/840 PSD WB TW3 PI7L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	4000 K	154 lm/W	8,000 lm	Wide beam
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	4000 K	165 lm/W	8,000 lm	Very wide beam
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	4000 K	165 lm/W	8,000 lm	Very wide beam
910925867740	WT490C 100S/840 PSD WB PI5 L1800	4000 K	161 lm/W	10,000 lm	Wide beam
910925867741	WT490C 120S/840 PSD WB PI5 L1800	4000 K	158 lm/W	12,000 lm	Wide beam
910925868292	WT490C 80S/840 PSU WB PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925868293	WT490C 100S/840 PSU WB PI5 L1800	4000 K	161 lm/W	10,000 lm	Wide beam
910925868294	WT490C 120S/840 PSU WB PI5 L1800	4000 K	158 lm/W	12,000 lm	Wide beam
910925868516	WT490C 80S/840 SIA WB IA9 PI5L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925868697	WT490C 80S/840 PSU O PI5 L1800	4000 K	157 lm/W	7,600 lm	Opal

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925868698	WT490C 80S/840 PSU PCO PI5 L1800	4000 K	136 lm/W	6,600 lm	Opal
910925868701	WT495C 80S/840 PSU WB PI5 L1800	4000 K	157 lm/W	8,000 lm	Wide beam
910925868703	WT495C 80S/840 PSD WB PI5 L1800	4000 K	157 lm/W	8,000 lm	Wide beam
910925868709	WT490C 80S/840 PSU WB WA7 CLII L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925869405	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925869406	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925869607	WT490C 150S/840 PSD WB PI5 L1800	4000 K	155 lm/W	15,000 lm	Very wide beam
910925869611	WT490C 150S/840 PSU WB PI5 L1800	4000 K	155 lm/W	15,000 lm	Very wide beam
910925868704	WT492C 64S/840 PSU WB W5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868705	WT492C 80S/840 PSU WB W5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910925868706	WT492C 64S/840 PSD WB W5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925868707	WT492C 80S/840 PSD WB W5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
910770229590	WT490C 42S/830 PSU WB PI5 L1200	3000 K	157 lm/W	4,200 lm	Wide beam
910925867704	WT490C 42S/840 PSD WB PI5 L1200	4000 K	162 lm/W	4,200 lm	Wide beam
910925867705	WT490C 64S/840 PSU NB-HRO PI5L1200	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
910925867706	WT490C 64S/840 PSD NB-HRO PI5L1200	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
910925867707	WT490C 64S/840 PSU WB TW1 PI5L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925867708	WT490C 64S/840 PSU WB TW3 PI5L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925867709	WT490C 64S/840 PSU WB TC5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
910925867711	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
910925867712	WT490C 64S/840 PSD WB PI5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925867713	WT490C 64S/840 PSD WB TW1 PI5L1200	4000 K	162 lm/W	6,400 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925867714	WT490C 64S/840 PSD WB TW3 PI7L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925867715	WT490C 64S/840 PSD WB ELD3 PI7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
910925867716	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
910925867717	WT490C 64S/840 PSU VWB PI5 L1200	4000 K	160 lm/W	6,400 lm	Very wide beam
910925867718	WT490C 64S/840 PSD VWB PI5 L1200	4000 K	162 lm/W	6,400 lm	Very wide beam
910925867719	WT490C 80S/840 PSU NB-HRO PI5L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925867720	WT490C 80S/840 PSD NB-HRO PI5L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925867721	WT490C 80S/840 PSU WB TW1 PI5L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867722	WT490C 80S/840 PSU WB TW3 PI5L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
910925867724	WT490C 80S/840 PSD WB PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867725	WT490C 80S/840 PSD WB TW1 PI5L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867726	WT490C 80S/840 PSD WB TW3 PI7L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
910925867743	WT490C 64S/840 PSU NB-HRO WA7L1200	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
910925867744	WT490C 64S/840 PSD NB-HRO WA7L1200	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
910925868247	WT490C 64S/840 PSU WB WA7 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868249	WT490C 64S/840 PSU WB TW3 WA7L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	4000 K	146 lm/W	6,400 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925868252	WT490C 64S/840 PSD WB WA7 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925868253	WT490C 64S/840 PSD WB TW3 WA7L1200	4000 K	162 lm/W	6,400 lm	Wide beam
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	4000 K	160 lm/W	6,400 lm	Very wide beam
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	4000 K	162 lm/W	6,400 lm	Very wide beam
910925868257	WT490C 80S/840 PSU NB-HRO WA7L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925868258	WT490C 80S/840 PSD NB-HRO WA7L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925868259	WT490C 80S/840 PSU WB WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868260	WT490C 80S/840 PSU WB TW3 WA7L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
910925868262	WT490C 80S/840 PSD WB WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868263	WT490C 80S/840 PSD WB TW3 WA7L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
910925868265	WT490C 80S/840 PSU VWB WA7 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
910925868266	WT490C 80S/840 PSD VWB WA7 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
910925868288	WT490C 42S/840 PSU WB PI5 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
910925868289	WT490C 64S/840 PSU WB PI5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868290	WT490C 80S/840 PSU WB PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	4000 K	162 lm/W	4,200 lm	Very wide beam
910925868611	WT490C 42S/840 PSU WB WA7 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	4000 K	165 lm/W	4,200 lm	Very wide beam
910925868613	WT490C 42S/840 PSU WB TW3 WA7L1200	4000 K	165 lm/W	4,200 lm	Wide beam
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	4000 K	162 lm/W	4,200 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925868615	WT490C 42S/840 PSD WB WA7 L1200	4000 K	162 lm/W	4,200 lm	Wide beam
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	4000 K	162 lm/W	4,200 lm	Very wide beam
910925868617	WT490C 42S/840 PSD WB TW3 WA7L1200	4000 K	162 lm/W	4,200 lm	Wide beam
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	4000 K	162 lm/W	4,200 lm	Very wide beam
910925868619	WT490C 64S/840 PSU NB-HRO TW3WA7 L1200	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
910925868620	WT490C 64S/840 PSD NB-HRO TW3WA7 L1200	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
910925868621	WT490C 80S/840 PSU NB-HRO TW3WA7 L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925868622	WT490C 80S/840 PSD NB-HRO TW3WA7 L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
910925868691	WT490C 35S/840 PSU WB PI5 L1200	4000 K	159 lm/W	3,500 lm	Wide beam
910925868693	WT490C 35S/840 PSU WB WA7 L1200	4000 K	159 lm/W	3,500 lm	Wide beam
910925868695	WT490C 64S/840 PSU O PI5 L1200	4000 K	155 lm/W	6,200 lm	Opal
910925868696	WT490C 64S/840 PSU PCO PI5 L1200	4000 K	133 lm/W	5,300 lm	Opal
910925868699		4000 K	158 lm/W	6,400 lm	Wide beam
910925868702	WT495C 64S/840 PSD WB PI5 L1200	4000 K	158 lm/W	6,400 lm	Wide beam
910925868708	WT490C 64S/840 PSU WB WA7 CLII L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925869401	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	4000 K	146 lm/W	6,400 lm	Wide beam
910925869403	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925869404	WT490C 80S/840 PSD WB TW3x2.5PI7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925869410	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
91092586960	WT490C 100S/840 PSD WB PI5 L1200	4000 K	152 lm/W	10,000 lm	Very wide beam
6					

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910925869608	WT490C 100S/840 PSU WB WA7 L1200	4000 K	154 lm/W	10,000 lm	Very wide beam
910925869609	WT490C 100S/840 PSD WB WA7 L1200	4000 K	152 lm/W	10,000 lm	Very wide beam
910925869610	WT490C 100S/840 PSU WB PI5 L1200	4000 K	154 lm/W	10,000 lm	Very wide beam
910925868412	WT490C 64S/840 PSD WB PI5 L1600	4000 K	162 lm/W	6,400 lm	Wide beam
910925868413	WT490C 64S/840 PSU WB TW3 PI5L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925868414	WT490C 64S/840 PSU WB PI5 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925868415	WT490C 80S/840 PSU WB PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868416	WT490C 80S/840 PSD WB PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868417	WT490C 80S/840 PSU WB TW3 PI5L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868418	WT490C 64S/840 PSD WB WA7 L1600	4000 K	162 lm/W	6,400 lm	Wide beam
910925868419	WT490C 64S/840 PSU WB TW3 WA7L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925868420	WT490C 64S/840 PSU WB WA7 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925868421	WT490C 80S/840 PSU WB WA7 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868422	WT490C 80S/840 PSD WB WA7 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868423	WT490C 80S/840 PSU WB TW3 WA7L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925868692	WT490C 35S/840 PSU WB PI5 L1600	4000 K	159 lm/W	3,500 lm	Wide beam
910925868694	WT490C 35S/840 PSU WB WA7 L1600	4000 K	159 lm/W	3,500 lm	Wide beam
910925869407	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
910925869408	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
910925867703	WT490C 23S/840 PSD WB PI5 L700	4000 K	160 lm/W	2,300 lm	Wide beam
910925868287	WT490C 23S/840 PSU WB PI5 L700	4000 K	151 lm/W	2,300 lm	Wide beam
910925868250	WT490C 64S/840 PSU WB TCW5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868510	WT490C 64S/840 PSU WB W5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
910925868511	WT490C 80S/840 PSU WB W5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
910925868512	WT490C 64S/840 PSD WB W5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous	Optic type
		Temperature	Efficacy (rated)		
		(Nom)	(Nom)	Flux	
910925868513	WT490C 80S/840 PSD WB	4000 K	157 lm/W	8,000 lm	Wide beam
	W5 L1200				

Operating and Electrical

		Protection class	Power			Protection class	Power
Order Code	Full Product Name	IEC	Consumption	Order Code	Full Product Name	IEC	Consumption
910925867731	WT490C 80S/840 PSU NB-HRO PI5L1800	Safety class I	48.5 W	910925869406	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	Safety class I	48.5 W
910925867732	WT490C 80S/840 PSD NB-HRO PI5L1800	Safety class I	48.5 W	910925869607	WT490C 150S/840 PSD WB PI5 L1800	Safety class I	97 W
910925867733	WT490C 80S/840 PSU WB TW3 PI5L1800	Safety class I	48.5 W	910925869611	WT490C 150S/840 PSU WB PI5 L1800	Safety class I	97 W
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	Safety class I	52 W	910925868704	WT492C 64S/840 PSU WB W5 L1200	Safety class I	40 W
910925867735	WT490C 80S/840 PSD WB PI5 L1800	Safety class I	48.5 W	910925868705	WT492C 80S/840 PSU WB W5 L1800	Safety class I	49 W
910925867736	WT490C 80S/840 PSD WB TW3 PI7L1800	Safety class I	48.5 W	910925868706	WT492C 64S/840 PSD WB W5 L1200	Safety class I	39.5 W
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	Safety class I	52 W	910925868707	WT492C 80S/840 PSD WB W5 L1800	Safety class I	48.5 W
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	Safety class I	48.5 W	910770229590	WT490C 42S/830 PSU WB PI5 L1200	Safety class I	25.5 W
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	Safety class I	48.5 W	910925867704	WT490C 42S/840 PSD WB PI5 L1200	Safety class I	26 W
910925867740	WT490C 100S/840 PSD WB PI5 L1800	Safety class I	62 W	910925867705	WT490C 64S/840 PSU NB-HRO PI5L1200	Safety class I	40 W
910925867741	WT490C 120S/840 PSD WB PI5 L1800	Safety class I	76 W	910925867706	WT490C 64S/840 PSD NB-HRO PI5L1200	Safety class I	39.5 W
910925868292	WT490C 80S/840 PSU WB PI5 L1800	Safety class I	48.5 W	910925867707	WT490C 64S/840 PSU WB TW1 PI5L1200	Safety class I	40 W
910925868293	WT490C 100S/840 PSU WB PI5 L1800	Safety class I	62 W	910925867708	WT490C 64S/840 PSU WB TW3 PI5L1200	Safety class I	40 W
910925868294	WT490C 120S/840 PSU WB PI5 L1800	Safety class I	76 W	910925867709	WT490C 64S/840 PSU WB TC5 L1200	Safety class I	40 W
910925868516	WT490C 80S/840 SIA WB IA9 PI5L1800	Safety class I	48.5 W	910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	Safety class I	44 W
910925868697	WT490C 80S/840 PSU O PI5 L1800	Safety class I	51 W	910925867711	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	Safety class I	44 W
910925868698	WT490C 80S/840 PSU PCO PI5 L1800	Safety class I	48.5 W	910925867712	WT490C 64S/840 PSD WB PI5 L1200	Safety class I	39.5 W
910925868701	WT495C 80S/840 PSU WB PI5 L1800	Safety class I	49 W	910925867713	WT490C 64S/840 PSD WB TW1 PI5L1200	Safety class I	39.5 W
910925868703	WT495C 80S/840 PSD WB PI5 L1800	Safety class I	48.5 W	910925867714	WT490C 64S/840 PSD WB TW3 PI7L1200	Safety class I	39.5 W
910925868709	WT490C 80S/840 PSU WB WA7 CLII L1800	Safety class II	51 W	910925867715	WT490C 64S/840 PSD WB ELD3 PI7 L1200	Safety class I	43.5 W
910925869405	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	Safety class I	48.5 W	910925867716	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	Safety class I	43.5 W

Pacific LED Gen5

Order Code	Full Product Name	Protection class IEC	Power Consumption
910925867717	WT490C 64S/840 PSU VWB PI5 L1200	Safety class I	40 W
910925867718	WT490C 64S/840 PSD VWB PI5 L1200	Safety class I	39.5 W
910925867719	WT490C 80S/840 PSU NB- HRO PI5L1200	Safety class I	51 W
910925867720	WT490C 80S/840 PSD NB- HRO PI5L1200	Safety class I	51 W
910925867721	WT490C 80S/840 PSU WB TW1 PI5L1200	Safety class I	51 W
910925867722	WT490C 80S/840 PSU WB TW3 PI5L1200	Safety class I	51 W
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	Safety class I	55 W
910925867724	WT490C 80S/840 PSD WB PI5 L1200	Safety class I	51 W
910925867725	WT490C 80S/840 PSD WB TW1 PI5L1200	Safety class I	51 W
910925867726	WT490C 80S/840 PSD WB TW3 PI7L1200	Safety class I	51 W
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	Safety class I	55 W
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	Safety class I	51 W
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	Safety class I	51 W
910925867743	WT490C 64S/840 PSU NB- HRO WA7L1200	Safety class I	40 W
910925867744	WT490C 64S/840 PSD NB- HRO WA7L1200	Safety class I	39.5 W
910925868247	WT490C 64S/840 PSU WB WA7 L1200	Safety class I	40 W
910925868249	WT490C 64S/840 PSU WB TW3 WA7L1200	Safety class I	40 W
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	Safety class I	44 W
910925868252	WT490C 64S/840 PSD WB WA7 L1200	Safety class I	39.5 W
910925868253	WT490C 64S/840 PSD WB TW3 WA7L1200	Safety class I	39.5 W
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	Safety class I	43.5 W
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	Safety class I	40 W
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	Safety class I	39.5 W
910925868257	WT490C 80S/840 PSU NB- HRO WA7L1200	Safety class I	51 W
910925868258	WT490C 80S/840 PSD NB- HRO WA7L1200	Safety class I	51 W

Order Code	Full Product Name	Protection class IEC	Power Consumption
910925868259	WT490C 80S/840 PSU WB WA7 L1200	Safety class I	51 W
910925868260	WT490C 80S/840 PSU WB TW3 WA7L1200	Safety class I	51 W
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	Safety class I	55 W
910925868262	WT490C 80S/840 PSD WB WA7 L1200	Safety class I	51 W
910925868263	WT490C 80S/840 PSD WB TW3 WA7L1200	Safety class I	51 W
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	Safety class I	55 W
910925868265	WT490C 80S/840 PSU VWB WA7 L1200	Safety class I	51 W
910925868266	WT490C 80S/840 PSD VWB WA7 L1200	Safety class I	51 W
910925868288	WT490C 42S/840 PSU WB PI5 L1200	Safety class I	25.5 W
910925868289	WT490C 64S/840 PSU WB PI5 L1200	Safety class I	40 W
910925868290	WT490C 80S/840 PSU WB PI5 L1200	Safety class I	51 W
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	Safety class I	26 W
910925868611	WT490C 42S/840 PSU WB WA7 L1200	Safety class I	25.5 W
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	Safety class I	25.5 W
910925868613	WT490C 42S/840 PSU WB TW3 WA7L1200	Safety class I	25.5 W
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	Safety class I	26 W
910925868615	WT490C 42S/840 PSD WB WA7 L1200	Safety class I	26 W
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	Safety class I	26 W
910925868617	WT490C 42S/840 PSD WB TW3 WA7L1200	Safety class I	26 W
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	Safety class I	26 W
910925868619	WT490C 64S/840 PSU NB- HRO TW3WA7 L1200	Safety class I	40 W
910925868620	WT490C 64S/840 PSD NB- HRO TW3WA7 L1200	Safety class I	39.5 W
910925868621	WT490C 80S/840 PSU NB- HRO TW3WA7 L1200	Safety class I	51 W
910925868622	WT490C 80S/840 PSD NB- HRO TW3WA7 L1200	Safety class I	51 W
910925868691	WT490C 35S/840 PSU WB PI5 L1200	Safety class I	22 W

Pacific LED Gen5

Order Code	Full Product Name	Protection class	Power
		IEC	Consumption
910925868693	WT490C 35S/840 PSU WB WA7 L1200	Safety class I	22 W
910925868695	WT490C 64S/840 PSU O PI5 L1200	Safety class I	40 W
910925868696	WT490C 64S/840 PSU PCO PI5 L1200	Safety class I	40 W
910925868699		Safety class I	40.5 W
910925868702	WT495C 64S/840 PSD WB PI5 L1200	Safety class I	40.5 W
910925868708	WT490C 64S/840 PSU WB WA7 CLII L1200	Safety class II	40 W
910925869401	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	Safety class I	40 W
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	Safety class I	44 W
910925869403	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	Safety class I	51 W
910925869404	WT490C 80S/840 PSD WB TW3x2.5PI7 L1200	Safety class I	51 W
910925869410	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	Safety class I	25.5 W
91092586960 6	WT490C 100S/840 PSD WB PI5 L1200	Safety class I	66 W
91092586960 8	WT490C 100S/840 PSU WB WA7 L1200	Safety class I	65 W
91092586960 9	WT490C 100S/840 PSD WB WA7 L1200	Safety class I	66 W
910925869610	WT490C 100S/840 PSU WB PI5 L1200	Safety class I	65 W
910925868412	WT490C 64S/840 PSD WB PI5 L1600	Safety class I	39.5 W
910925868413	WT490C 64S/840 PSU WB TW3 PI5L1600	Safety class I	40 W
910925868414	WT490C 64S/840 PSU WB PI5 L1600	Safety class I	40 W
910925868415	WT490C 80S/840 PSU WB PI5 L1600	Safety class I	51 W
910925868416	WT490C 80S/840 PSD WB PI5 L1600	Safety class I	51 W

Controls and Dimming

Order Code	Full Product Name	Embedded	
		Dimmable	control
910925867731	WT490C 80S/840 PSU NB-HRO PI5L1800	No	-
910925867732	WT490C 80S/840 PSD NB-HRO PI5L1800	Yes	-
910925867733	WT490C 80S/840 PSU WB TW3 PI5L1800	No	-
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	No	-
910925867735	WT490C 80S/840 PSD WB PI5 L1800	Yes	-
910925867736	WT490C 80S/840 PSD WB TW3 PI7L1800	Yes	-

Order Code	Full Product Name	Protection class	Power
		IEC	Consumption
910925868417	WT490C 80S/840 PSU WB TW3 PI5L1600	Safety class I	51 W
910925868418	WT490C 64S/840 PSD WB WA7 L1600	Safety class I	39.5 W
910925868419	WT490C 64S/840 PSU WB TW3 WA7L1600	Safety class I	40 W
910925868420	WT490C 64S/840 PSU WB WA7 L1600	Safety class I	40 W
910925868421	WT490C 80S/840 PSU WB WA7 L1600	Safety class I	51 W
910925868422	WT490C 80S/840 PSD WB WA7 L1600	Safety class I	51 W
910925868423	WT490C 80S/840 PSU WB TW3 WA7L1600	Safety class I	51 W
910925868692	WT490C 35S/840 PSU WB PI5 L1600	Safety class I	22 W
910925868694	WT490C 35S/840 PSU WB WA7 L1600	Safety class I	22 W
910925869407	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	Safety class I	40 W
910925869408	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	Safety class I	51 W
910925867703	WT490C 23S/840 PSD WB PI5 L700	Safety class I	14.4 W
910925868287	WT490C 23S/840 PSU WB PI5 L700	Safety class I	15.2 W
910925868250	WT490C 64S/840 PSU WB TCW5 L1200	Safety class I	40 W
910925868510	WT490C 64S/840 PSU WB W5 L1200	Safety class I	40 W
910925868511	WT490C 80S/840 PSU WB W5 L1200	Safety class I	51 W
910925868512	WT490C 64S/840 PSD WB W5 L1200	Safety class I	39.5 W
910925868513	WT490C 80S/840 PSD WB W5 L1200	Safety class I	51 W

Order Code	Full Product Name	Embedded	
		Dimmable	control
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	Yes	-
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	No	-
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	Yes	-
910925867740	WT490C 100S/840 PSD WB PI5 L1800	Yes	-
910925867741	WT490C 120S/840 PSD WB PI5 L1800	Yes	-
910925868292	WT490C 80S/840 PSU WB PI5 L1800	No	-

Pacific LED Gen5

Order Code	Full Product Name	Embedded	
		Dimmable	control
910925868293	WT490C 100S/840 PSU WB PI5 L1800	No	-
910925868294	WT490C 120S/840 PSU WB PI5 L1800	No	-
910925868516	WT490C 80S/840 SIA WB IA9 PI5L1800	Yes	InterAct SNS410 antenna
910925868697	WT490C 80S/840 PSU O PI5 L1800	No	-
910925868698	WT490C 80S/840 PSU PCO PI5 L1800	No	-
910925868701	WT495C 80S/840 PSU WB PI5 L1800	No	-
910925868703	WT495C 80S/840 PSD WB PI5 L1800	Yes	-
910925868709	WT490C 80S/840 PSU WB WA7 CLII L1800	No	-
910925869405	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	No	-
910925869406	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	Yes	-
910925869607	WT490C 150S/840 PSD WB PI5 L1800	Yes	-
910925869611	WT490C 150S/840 PSU WB PI5 L1800	No	-
910925868704	WT492C 64S/840 PSU WB W5 L1200	No	-
910925868705	WT492C 80S/840 PSU WB W5 L1800	No	-
910925868706	WT492C 64S/840 PSD WB W5 L1200	Yes	-
910925868707	WT492C 80S/840 PSD WB W5 L1800	Yes	-
910770229590	WT490C 42S/830 PSU WB PI5 L1200	No	-
910925867704	WT490C 42S/840 PSD WB PI5 L1200	Yes	-
910925867705	WT490C 64S/840 PSU NB-HRO PI5L1200	No	-
910925867706	WT490C 64S/840 PSD NB-HRO PI5L1200	Yes	-
910925867707	WT490C 64S/840 PSU WB TW1 PI5L1200	No	-
910925867708	WT490C 64S/840 PSU WB TW3 PI5L1200	No	-
910925867709	WT490C 64S/840 PSU WB TC5 L1200	No	-
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	No	-
910925867711	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	No	-
910925867712	WT490C 64S/840 PSD WB PI5 L1200	Yes	-
910925867713	WT490C 64S/840 PSD WB TW1 PI5L1200	Yes	-
910925867714	WT490C 64S/840 PSD WB TW3 PI7L1200	Yes	-
910925867715	WT490C 64S/840 PSD WB ELD3 PI7 L1200	Yes	-
910925867716	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	Yes	-
910925867717	WT490C 64S/840 PSU VWB PI5 L1200	No	-
910925867718	WT490C 64S/840 PSD VWB PI5 L1200	Yes	-
910925867719	WT490C 80S/840 PSU NB-HRO PI5L1200	No	-
910925867720	WT490C 80S/840 PSD NB-HRO PI5L1200	Yes	-
910925867721	WT490C 80S/840 PSU WB TW1 PI5L1200	No	-
910925867722	WT490C 80S/840 PSU WB TW3 PI5L1200	No	-
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	No	-
910925867724	WT490C 80S/840 PSD WB PI5 L1200	Yes	-
910925867725	WT490C 80S/840 PSD WB TW1 PI5L1200	Yes	-
910925867726	WT490C 80S/840 PSD WB TW3 PI7L1200	Yes	-
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	Yes	-

Order Code	Full Product Name	Embedded	
		Dimmable	control
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	No	-
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	Yes	-
910925867743	WT490C 64S/840 PSU NB-HRO WA7L1200	No	-
910925867744	WT490C 64S/840 PSD NB-HRO WA7L1200	Yes	-
910925868247	WT490C 64S/840 PSU WB WA7 L1200	No	-
910925868249	WT490C 64S/840 PSU WB TW3 WA7L1200	No	-
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	No	-
910925868252	WT490C 64S/840 PSD WB WA7 L1200	Yes	-
910925868253	WT490C 64S/840 PSD WB TW3 WA7L1200	Yes	-
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	Yes	-
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	No	-
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	Yes	-
910925868257	WT490C 80S/840 PSU NB-HRO WA7L1200	No	-
910925868258	WT490C 80S/840 PSD NB-HRO WA7L1200	Yes	-
910925868259	WT490C 80S/840 PSU WB WA7 L1200	No	-
910925868260	WT490C 80S/840 PSU WB TW3 WA7L1200	No	-
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	No	-
910925868262	WT490C 80S/840 PSD WB WA7 L1200	Yes	-
910925868263	WT490C 80S/840 PSD WB TW3 WA7L1200	Yes	-
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	Yes	-
910925868265	WT490C 80S/840 PSU VWB WA7 L1200	No	-
910925868266	WT490C 80S/840 PSD VWB WA7 L1200	Yes	-
910925868288	WT490C 42S/840 PSU WB PI5 L1200	No	-
910925868289	WT490C 64S/840 PSU WB PI5 L1200	No	-
910925868290	WT490C 80S/840 PSU WB PI5 L1200	No	-
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	Yes	-
910925868611	WT490C 42S/840 PSU WB WA7 L1200	No	-
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	No	-
910925868613	WT490C 42S/840 PSU WB TW3 WA7L1200	No	-
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	No	-
910925868615	WT490C 42S/840 PSD WB WA7 L1200	Yes	-
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	Yes	-
910925868617	WT490C 42S/840 PSD WB TW3 WA7L1200	Yes	-
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	Yes	-

Pacific LED Gen5

Order Code	Full Product Name	Embedded	
		Dimmable	control
910925868619	WT490C 64S/840 PSU NB-HRO TW3WA7 L1200	No	-
910925868620	WT490C 64S/840 PSD NB-HRO TW3WA7 L1200	Yes	-
910925868621	WT490C 80S/840 PSU NB-HRO TW3WA7 L1200	No	-
910925868622	WT490C 80S/840 PSD NB-HRO TW3WA7 L1200	Yes	-
910925868691	WT490C 35S/840 PSU WB PI5 L1200	No	-
910925868693	WT490C 35S/840 PSU WB WA7 L1200	No	-
910925868695	WT490C 64S/840 PSU O PI5 L1200	No	-
910925868696	WT490C 64S/840 PSU PCO PI5 L1200	No	-
910925868699		No	-
910925868702	WT495C 64S/840 PSD WB PI5 L1200	Yes	-
910925868708	WT490C 64S/840 PSU WB WA7 CLII L1200	No	-
910925869401	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	No	-
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	No	-
910925869403	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	No	-
910925869404	WT490C 80S/840 PSD WB TW3x2.5PI7 L1200	Yes	-
910925869410	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	No	-
91092586960	WT490C 100S/840 PSD WB PI5 L1200	Yes	-
6			
91092586960	WT490C 100S/840 PSU WB WA7 L1200	No	-
8			

Order Code	Full Product Name	Embedded	
		Dimmable	control
91092586960	WT490C 100S/840 PSD WB WA7 L1200	Yes	-
9			
910925869610	WT490C 100S/840 PSU WB PI5 L1200	No	-
910925868412	WT490C 64S/840 PSD WB PI5 L1600	Yes	-
910925868413	WT490C 64S/840 PSU WB TW3 PI5L1600	No	-
910925868414	WT490C 64S/840 PSU WB PI5 L1600	No	-
910925868415	WT490C 80S/840 PSU WB PI5 L1600	No	-
910925868416	WT490C 80S/840 PSD WB PI5 L1600	Yes	-
910925868417	WT490C 80S/840 PSU WB TW3 PI5L1600	No	-
910925868418	WT490C 64S/840 PSD WB WA7 L1600	Yes	-
910925868419	WT490C 64S/840 PSU WB TW3 WA7L1600	No	-
910925868420	WT490C 64S/840 PSU WB WA7 L1600	No	-
910925868421	WT490C 80S/840 PSU WB WA7 L1600	No	-
910925868422	WT490C 80S/840 PSD WB WA7 L1600	Yes	-
910925868423	WT490C 80S/840 PSU WB TW3 WA7L1600	No	-
910925868692	WT490C 35S/840 PSU WB PI5 L1600	No	-
910925868694	WT490C 35S/840 PSU WB WA7 L1600	No	-
910925869407	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	No	-
910925869408	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	No	-
910925867703	WT490C 23S/840 PSD WB PI5 L700	Yes	-
910925868287	WT490C 23S/840 PSU WB PI5 L700	No	-
910925868250	WT490C 64S/840 PSU WB TCW5 L1200	No	-
910925868510	WT490C 64S/840 PSU WB W5 L1200	No	-
910925868511	WT490C 80S/840 PSU WB W5 L1200	No	-
910925868512	WT490C 64S/840 PSD WB W5 L1200	Yes	-
910925868513	WT490C 80S/840 PSD WB W5 L1200	Yes	-

Mechanical and Housing

Order Code	Full Product Name	Explosion hazard	
		class	
910925867731	WT490C 80S/840 PSU NB-HRO PI5L1800	-	
910925867732	WT490C 80S/840 PSD NB-HRO PI5L1800	-	
910925867733	WT490C 80S/840 PSU WB TW3 PI5L1800	-	
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	-	
910925867735	WT490C 80S/840 PSD WB PI5 L1800	-	
910925867736	WT490C 80S/840 PSD WB TW3 PI7L1800	-	
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	-	
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	-	
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	-	
910925867740	WT490C 100S/840 PSD WB PI5 L1800	-	
910925867741	WT490C 120S/840 PSD WB PI5 L1800	-	
910925868292	WT490C 80S/840 PSU WB PI5 L1800	-	
910925868293	WT490C 100S/840 PSU WB PI5 L1800	-	
910925868294	WT490C 120S/840 PSU WB PI5 L1800	-	
910925868516	WT490C 80S/840 SIA WB IA9 PI5L1800	-	
910925868697	WT490C 80S/840 PSU O PI5 L1800	-	

Order Code	Full Product Name	Explosion hazard	
		class	
910925868698	WT490C 80S/840 PSU PCO PI5 L1800	-	
910925868701	WT495C 80S/840 PSU WB PI5 L1800	-	
910925868703	WT495C 80S/840 PSD WB PI5 L1800	-	
910925868709	WT490C 80S/840 PSU WB WA7 CLII L1800	-	
910925869405	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	-	
910925869406	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	-	
910925869607	WT490C 150S/840 PSD WB PI5 L1800	-	
910925869611	WT490C 150S/840 PSU WB PI5 L1800	-	
910925868704	WT492C 64S/840 PSU WB W5 L1200	Zone 2 and 22	
910925868705	WT492C 80S/840 PSU WB W5 L1800	Zone 2 and 22	
910925868706	WT492C 64S/840 PSD WB W5 L1200	Zone 2 and 22	
910925868707	WT492C 80S/840 PSD WB W5 L1800	Zone 2 and 22	
910770229590	WT490C 42S/830 PSU WB PI5 L1200	-	
910925867704	WT490C 42S/840 PSD WB PI5 L1200	-	
910925867705	WT490C 64S/840 PSU NB-HRO PI5L1200	-	
910925867706	WT490C 64S/840 PSD NB-HRO PI5L1200	-	

Order Code	Full Product Name	Explosion hazard class
910925867707	WT490C 64S/840 PSU WB TW1 PI5L1200	-
910925867708	WT490C 64S/840 PSU WB TW3 PI5L1200	-
910925867709	WT490C 64S/840 PSU WB TC5 L1200	-
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	-
910925867711	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	-
910925867712	WT490C 64S/840 PSD WB PI5 L1200	-
910925867713	WT490C 64S/840 PSD WB TW1 PI5L1200	-
910925867714	WT490C 64S/840 PSD WB TW3 PI7L1200	-
910925867715	WT490C 64S/840 PSD WB ELD3 PI7 L1200	-
910925867716	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	-
910925867717	WT490C 64S/840 PSU VWB PI5 L1200	-
910925867718	WT490C 64S/840 PSD VWB PI5 L1200	-
910925867719	WT490C 80S/840 PSU NB-HRO PI5L1200	-
910925867720	WT490C 80S/840 PSD NB-HRO PI5L1200	-
910925867721	WT490C 80S/840 PSU WB TW1 PI5L1200	-
910925867722	WT490C 80S/840 PSU WB TW3 PI5L1200	-
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	-
910925867724	WT490C 80S/840 PSD WB PI5 L1200	-
910925867725	WT490C 80S/840 PSD WB TW1 PI5L1200	-
910925867726	WT490C 80S/840 PSD WB TW3 PI7L1200	-
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	-
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	-
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	-
910925867743	WT490C 64S/840 PSU NB-HRO WA7L1200	-
910925867744	WT490C 64S/840 PSD NB-HRO WA7L1200	-
910925868247	WT490C 64S/840 PSU WB WA7 L1200	-
910925868249	WT490C 64S/840 PSU WB TW3 WA7L1200	-
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	-
910925868252	WT490C 64S/840 PSD WB WA7 L1200	-
910925868253	WT490C 64S/840 PSD WB TW3 WA7L1200	-
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	-
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	-
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	-
910925868257	WT490C 80S/840 PSU NB-HRO WA7L1200	-
910925868258	WT490C 80S/840 PSD NB-HRO WA7L1200	-
910925868259	WT490C 80S/840 PSU WB WA7 L1200	-
910925868260	WT490C 80S/840 PSU WB TW3 WA7L1200	-
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	-
910925868262	WT490C 80S/840 PSD WB WA7 L1200	-
910925868263	WT490C 80S/840 PSD WB TW3 WA7L1200	-
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	-
910925868265	WT490C 80S/840 PSU VWB WA7 L1200	-
910925868266	WT490C 80S/840 PSD VWB WA7 L1200	-
910925868288	WT490C 42S/840 PSU WB PI5 L1200	-
910925868289	WT490C 64S/840 PSU WB PI5 L1200	-
910925868290	WT490C 80S/840 PSU WB PI5 L1200	-
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	-
910925868611	WT490C 42S/840 PSU WB WA7 L1200	-
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	-
910925868613	WT490C 42S/840 PSU WB TW3 WA7L1200	-
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	-

Order Code	Full Product Name	Explosion hazard class
910925868615	WT490C 42S/840 PSD WB WA7 L1200	-
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	-
910925868617	WT490C 42S/840 PSD WB TW3 WA7L1200	-
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	-
910925868619	WT490C 64S/840 PSU NB-HRO TW3WA7 L1200	-
910925868620	WT490C 64S/840 PSD NB-HRO TW3WA7 L1200	-
910925868621	WT490C 80S/840 PSU NB-HRO TW3WA7 L1200	-
910925868622	WT490C 80S/840 PSD NB-HRO TW3WA7 L1200	-
910925868691	WT490C 35S/840 PSU WB PI5 L1200	-
910925868693	WT490C 35S/840 PSU WB WA7 L1200	-
910925868695	WT490C 64S/840 PSU O PI5 L1200	-
910925868696	WT490C 64S/840 PSU PCO PI5 L1200	-
910925868699		-
910925868702	WT495C 64S/840 PSD WB PI5 L1200	-
910925868708	WT490C 64S/840 PSU WB WA7 CLII L1200	-
910925869401	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	-
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	-
910925869403	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	-
910925869404	WT490C 80S/840 PSD WB TW3x2.5PI7 L1200	-
910925869410	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	-
91092586960	WT490C 100S/840 PSD WB PI5 L1200	-
6		
91092586960	WT490C 100S/840 PSU WB WA7 L1200	-
8		
91092586960	WT490C 100S/840 PSD WB WA7 L1200	-
9		
910925869610	WT490C 100S/840 PSU WB PI5 L1200	-
910925868412	WT490C 64S/840 PSD WB PI5 L1600	-
910925868413	WT490C 64S/840 PSU WB TW3 PI5L1600	-
910925868414	WT490C 64S/840 PSU WB PI5 L1600	-
910925868415	WT490C 80S/840 PSU WB PI5 L1600	-
910925868416	WT490C 80S/840 PSD WB PI5 L1600	-
910925868417	WT490C 80S/840 PSU WB TW3 PI5L1600	-
910925868418	WT490C 64S/840 PSD WB WA7 L1600	-
910925868419	WT490C 64S/840 PSU WB TW3 WA7L1600	-
910925868420	WT490C 64S/840 PSU WB WA7 L1600	-
910925868421	WT490C 80S/840 PSU WB WA7 L1600	-
910925868422	WT490C 80S/840 PSD WB WA7 L1600	-
910925868423	WT490C 80S/840 PSU WB TW3 WA7L1600	-
910925868692	WT490C 35S/840 PSU WB PI5 L1600	-
910925868694	WT490C 35S/840 PSU WB WA7 L1600	-
910925869407	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	-
910925869408	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	-
910925867703	WT490C 23S/840 PSD WB PI5 L700	-
910925868287	WT490C 23S/840 PSU WB PI5 L700	-
910925868250	WT490C 64S/840 PSU WB TCW5 L1200	-
910925868510	WT490C 64S/840 PSU WB W5 L1200	-
910925868511	WT490C 80S/840 PSU WB W5 L1200	-
910925868512	WT490C 64S/840 PSD WB W5 L1200	-
910925868513	WT490C 80S/840 PSD WB W5 L1200	-

Emergency Operation

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867731	WT490C 80S/840 PSU NB-HRO PI5L1800	-	-
910925867732	WT490C 80S/840 PSD NB-HRO PI5L1800	-	-
910925867733	WT490C 80S/840 PSU WB TW3 PI5L1800	-	-
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867735	WT490C 80S/840 PSD WB PI5 L1800	-	-
910925867736	WT490C 80S/840 PSD WB TW3 PI7L1800	-	-
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	-	-
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	-	-
910925867740	WT490C 100S/840 PSD WB PI5 L1800	-	-
910925867741	WT490C 120S/840 PSD WB PI5 L1800	-	-
910925868292	WT490C 80S/840 PSU WB PI5 L1800	-	-
910925868293	WT490C 100S/840 PSU WB PI5 L1800	-	-
910925868294	WT490C 120S/840 PSU WB PI5 L1800	-	-
910925868516	WT490C 80S/840 SIA WB IA9 PI5L1800	-	-
910925868697	WT490C 80S/840 PSU O PI5 L1800	-	-
910925868698	WT490C 80S/840 PSU PCO PI5 L1800	-	-
910925868701	WT495C 80S/840 PSU WB PI5 L1800	-	-
910925868703	WT495C 80S/840 PSD WB PI5 L1800	-	-
910925868709	WT490C 80S/840 PSU WB WA7 CLII L1800	-	-
910925869405	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	-	-
910925869406	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925869607	WT490C 150S/840 PSD WB PI5 L1800	-	-
910925869611	WT490C 150S/840 PSU WB PI5 L1800	-	-
910925868704	WT492C 64S/840 PSU WB W5 L1200	-	-
910925868705	WT492C 80S/840 PSU WB W5 L1800	-	-
910925868706	WT492C 64S/840 PSD WB W5 L1200	-	-
910925868707	WT492C 80S/840 PSD WB W5 L1800	-	-
910770229590	WT490C 42S/830 PSU WB PI5 L1200	-	-
910925867704	WT490C 42S/840 PSD WB PI5 L1200	-	-
910925867705	WT490C 64S/840 PSU NB-HRO PI5L1200	-	-
910925867706	WT490C 64S/840 PSD NB-HRO PI5L1200	-	-
910925867707	WT490C 64S/840 PSU WB TW1 PI5L1200	-	-
910925867708	WT490C 64S/840 PSU WB TW3 PI5L1200	-	-
910925867709	WT490C 64S/840 PSU WB TC5 L1200	-	-
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867711	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867712	WT490C 64S/840 PSD WB PI5 L1200	-	-
910925867713	WT490C 64S/840 PSD WB TW1 PI5L1200	-	-
910925867714	WT490C 64S/840 PSD WB TW3 PI7L1200	-	-
910925867715	WT490C 64S/840 PSD WB ELD3 PI7 L1200	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867716	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	Emergency lighting 3 hours	3 hour(s)

Pacific LED Gen5

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
		duration with DALI interface	
910925867717	WT490C 64S/840 PSU VWB PI5 L1200	-	-
910925867718	WT490C 64S/840 PSD VWB PI5 L1200	-	-
910925867719	WT490C 80S/840 PSU NB-HRO PI5L1200	-	-
910925867720	WT490C 80S/840 PSD NB-HRO PI5L1200	-	-
910925867721	WT490C 80S/840 PSU WB TW1 PI5L1200	-	-
910925867722	WT490C 80S/840 PSU WB TW3 PI5L1200	-	-
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867724	WT490C 80S/840 PSD WB PI5 L1200	-	-
910925867725	WT490C 80S/840 PSD WB TW1 PI5L1200	-	-
910925867726	WT490C 80S/840 PSD WB TW3 PI7L1200	-	-
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	-	-
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	-	-
910925867743	WT490C 64S/840 PSU NB-HRO WA7L1200	-	-
910925867744	WT490C 64S/840 PSD NB-HRO WA7L1200	-	-
910925868247	WT490C 64S/840 PSU WB WA7 L1200	-	-
910925868249	WT490C 64S/840 PSU WB TW3 WA7L1200	-	-
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925868252	WT490C 64S/840 PSD WB WA7 L1200	-	-
910925868253	WT490C 64S/840 PSD WB TW3 WA7L1200	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	-	-
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	-	-
910925868257	WT490C 80S/840 PSU NB-HRO WA7L1200	-	-
910925868258	WT490C 80S/840 PSD NB-HRO WA7L1200	-	-
910925868259	WT490C 80S/840 PSU WB WA7 L1200	-	-
910925868260	WT490C 80S/840 PSU WB TW3 WA7L1200	-	-
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925868262	WT490C 80S/840 PSD WB WA7 L1200	-	-
910925868263	WT490C 80S/840 PSD WB TW3 WA7L1200	-	-
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925868265	WT490C 80S/840 PSU VWB WA7 L1200	-	-
910925868266	WT490C 80S/840 PSD VWB WA7 L1200	-	-
910925868288	WT490C 42S/840 PSU WB PI5 L1200	-	-
910925868289	WT490C 64S/840 PSU WB PI5 L1200	-	-
910925868290	WT490C 80S/840 PSU WB PI5 L1200	-	-
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	-	-
910925868611	WT490C 42S/840 PSU WB WA7 L1200	-	-
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	-	-
910925868613	WT490C 42S/840 PSU WB TW3 WA7L1200	-	-
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	-	-

Pacific LED Gen5

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925868615	WT490C 42S/840 PSD WB WA7 L1200	-	-
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	-	-
910925868617	WT490C 42S/840 PSD WB TW3 WA7L1200	-	-
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	-	-
910925868619	WT490C 64S/840 PSU NB-HRO TW3WA7 L1200	-	-
910925868620	WT490C 64S/840 PSD NB-HRO TW3WA7 L1200	-	-
910925868621	WT490C 80S/840 PSU NB-HRO TW3WA7 L1200	-	-
910925868622	WT490C 80S/840 PSD NB-HRO TW3WA7 L1200	-	-
910925868691	WT490C 35S/840 PSU WB PI5 L1200	-	-
910925868693	WT490C 35S/840 PSU WB WA7 L1200	-	-
910925868695	WT490C 64S/840 PSU O PI5 L1200	-	-
910925868696	WT490C 64S/840 PSU PCO PI5 L1200	-	-
910925868699		-	-
910925868702	WT495C 64S/840 PSD WB PI5 L1200	-	-
910925868708	WT490C 64S/840 PSU WB WA7 CLII L1200	-	-
910925869401	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	-	-
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925869403	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	-	-
910925869404	WT490C 80S/840 PSD WB TW3x2.5PI7 L1200	-	-
910925869410	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	-	-
91092586960	WT490C 100S/840 PSD WB PI5 L1200	-	-
6			
91092586960	WT490C 100S/840 PSU WB WA7 L1200	-	-
8			
91092586960	WT490C 100S/840 PSD WB WA7 L1200	-	-
9			
910925869610	WT490C 100S/840 PSU WB PI5 L1200	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925868412	WT490C 64S/840 PSD WB PI5 L1600	-	-
910925868413	WT490C 64S/840 PSU WB TW3 PI5L1600	-	-
910925868414	WT490C 64S/840 PSU WB PI5 L1600	-	-
910925868415	WT490C 80S/840 PSU WB PI5 L1600	-	-
910925868416	WT490C 80S/840 PSD WB PI5 L1600	-	-
910925868417	WT490C 80S/840 PSU WB TW3 PI5L1600	-	-
910925868418	WT490C 64S/840 PSD WB WA7 L1600	-	-
910925868419	WT490C 64S/840 PSU WB TW3 WA7L1600	-	-
910925868420	WT490C 64S/840 PSU WB WA7 L1600	-	-
910925868421	WT490C 80S/840 PSU WB WA7 L1600	-	-
910925868422	WT490C 80S/840 PSD WB WA7 L1600	-	-
910925868423	WT490C 80S/840 PSU WB TW3 WA7L1600	-	-
910925868692	WT490C 35S/840 PSU WB PI5 L1600	-	-
910925868694	WT490C 35S/840 PSU WB WA7 L1600	-	-
910925869407	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	-	-
910925869408	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	-	-
910925867703	WT490C 23S/840 PSD WB PI5 L700	-	-
910925868287	WT490C 23S/840 PSU WB PI5 L700	-	-
910925868250	WT490C 64S/840 PSU WB TCW5 L1200	-	-
910925868510	WT490C 64S/840 PSU WB W5 L1200	-	-
910925868511	WT490C 80S/840 PSU WB W5 L1200	-	-
910925868512	WT490C 64S/840 PSD WB W5 L1200	-	-
910925868513	WT490C 80S/840 PSD WB W5 L1200	-	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925867731	WT490C 80S/840 PSU NB-HRO PI5L1800	-25 to +45 °C	1	0.4
910925867732	WT490C 80S/840 PSD NB-HRO PI5L1800	-25 to +45 °C	1	0.4
910925867733	WT490C 80S/840 PSU WB TW3 PI5L1800	-25 to +45 °C	1	0.4
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	0 to +30 °C	1	0.4
910925867735	WT490C 80S/840 PSD WB PI5 L1800	-25 to +45 °C	1	0.4
910925867736	WT490C 80S/840 PSD WB TW3 PI7L1800	-25 to +45 °C	1	0.4
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	0 to +30 °C	1	0.4
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	-25 to +45 °C	1	0.4
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	-25 to +45 °C	1	0.4
910925867740	WT490C 100S/840 PSD WB PI5 L1800	-25 to +45 °C	1	0.4
910925867741	WT490C 120S/840 PSD WB PI5 L1800	-25 to +45 °C	1	0.4
910925868292	WT490C 80S/840 PSU WB PI5 L1800	-25 to +45 °C	1	0.4
910925868293	WT490C 100S/840 PSU WB PI5 L1800	-25 to +45 °C	1	0.4
910925868294	WT490C 120S/840 PSU WB PI5 L1800	-25 to +45 °C	1	0.4
910925868516	WT490C 80S/840 SIA WB IA9 PI5L1800	-25 to +45 °C	1	0.4
910925868697	WT490C 80S/840 PSU O PI5 L1800	-25 to +45 °C	1	0.4
910925868698	WT490C 80S/840 PSU PCO PI5 L1800	-25 to +45 °C	1	0.4
910925868701	WT495C 80S/840 PSU WB PI5 L1800	-35 to +60 °C	1	0.4
910925868703	WT495C 80S/840 PSD WB PI5 L1800	-35 to +60 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925868709	WT490C 80S/840 PSU WB WA7 CLII L1800	-25 to +45 °C	1	0.4
910925869405	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	-25 to +45 °C	1	0.4
910925869406	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	-25 to +45 °C	1	0.4
910925869607	WT490C 150S/840 PSD WB PI5 L1800	-25 to +25 °C	-	-
910925869611	WT490C 150S/840 PSU WB PI5 L1800	-25 to +25 °C	-	-
910925868704	WT492C 64S/840 PSU WB W5 L1200	-25 to +45 °C	1	0.4
910925868705	WT492C 80S/840 PSU WB W5 L1800	-25 to +45 °C	1	0.4
910925868706	WT492C 64S/840 PSD WB W5 L1200	-25 to +45 °C	1	0.4
910925868707	WT492C 80S/840 PSD WB W5 L1800	-25 to +45 °C	1	0.4
910770229590	WT490C 42S/830 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
910925867704	WT490C 42S/840 PSD WB PI5 L1200	-25 to +45 °C	1	0.4
910925867705	WT490C 64S/840 PSU NB-HRO PI5L1200	-25 to +45 °C	1	0.4
910925867706	WT490C 64S/840 PSD NB-HRO PI5L1200	-25 to +45 °C	1	0.4
910925867707	WT490C 64S/840 PSU WB TW1 PI5L1200	-25 to +45 °C	1	0.4
910925867708	WT490C 64S/840 PSU WB TW3 PI5L1200	-25 to +45 °C	1	0.4
910925867709	WT490C 64S/840 PSU WB TC5 L1200	-25 to +45 °C	1	0.4
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	0 to +40 °C	1	0.4
910925867711	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	0 to +40 °C	1	0.4

Pacific LED Gen5

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925867712	WT490C 64S/840 PSD WB PI5 L1200	-25 to +45 °C	1	0.4
910925867713	WT490C 64S/840 PSD WB TW1 PI5L1200	-25 to +45 °C	1	0.4
910925867714	WT490C 64S/840 PSD WB TW3 PI7L1200	-25 to +45 °C	1	0.4
910925867715	WT490C 64S/840 PSD WB ELD3 PI7 L1200	0 to +40 °C	1	0.4
910925867716	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	0 to +40 °C	1	0.4
910925867717	WT490C 64S/840 PSU VWB PI5 L1200	-25 to +45 °C	1	0.4
910925867718	WT490C 64S/840 PSD VWB PI5 L1200	-25 to +45 °C	1	0.4
910925867719	WT490C 80S/840 PSU NB-HRO PI5L1200	-25 to +45 °C	1	0.4
910925867720	WT490C 80S/840 PSD NB-HRO PI5L1200	-25 to +45 °C	1	0.4
910925867721	WT490C 80S/840 PSU WB TW1 PI5L1200	-25 to +45 °C	1	0.4
910925867722	WT490C 80S/840 PSU WB TW3 PI5L1200	-25 to +45 °C	1	0.4
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	0 to +30 °C	1	0.4
910925867724	WT490C 80S/840 PSD WB PI5 L1200	-25 to +45 °C	1	0.4
910925867725	WT490C 80S/840 PSD WB TW1 PI5L1200	-25 to +45 °C	1	0.4
910925867726	WT490C 80S/840 PSD WB TW3 PI7L1200	-25 to +45 °C	1	0.4
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	0 to +30 °C	1	0.4
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	-25 to +45 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	-25 to +45 °C	1	0.4
910925867743	WT490C 64S/840 PSU NB-HRO WA7L1200	-25 to +45 °C	1	0.4
910925867744	WT490C 64S/840 PSD NB-HRO WA7L1200	-25 to +45 °C	1	0.4
910925868247	WT490C 64S/840 PSU WB WA7 L1200	-25 to +45 °C	1	0.4
910925868249	WT490C 64S/840 PSU WB TW3 WA7L1200	-25 to +45 °C	1	0.4
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	0 to +40 °C	1	0.4
910925868252	WT490C 64S/840 PSD WB WA7 L1200	-25 to +45 °C	1	0.4
910925868253	WT490C 64S/840 PSD WB TW3 WA7L1200	-25 to +45 °C	1	0.4
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	0 to +40 °C	1	0.4
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	-25 to +45 °C	1	0.4
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	-25 to +45 °C	1	0.4
910925868257	WT490C 80S/840 PSU NB-HRO WA7L1200	-25 to +45 °C	1	0.4
910925868258	WT490C 80S/840 PSD NB-HRO WA7L1200	-25 to +45 °C	1	0.4
910925868259	WT490C 80S/840 PSU WB WA7 L1200	-25 to +45 °C	1	0.4
910925868260	WT490C 80S/840 PSU WB TW3 WA7L1200	-25 to +45 °C	1	0.4
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	0 to +30 °C	1	0.4
910925868262	WT490C 80S/840 PSD WB WA7 L1200	-25 to +45 °C	1	0.4

Pacific LED Gen5

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925868263	WT490C 80S/840 PSD WB TW3 WA7L1200	-25 to +45 °C	1	0.4
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	0 to +30 °C	1	0.4
910925868265	WT490C 80S/840 PSU VWB WA7 L1200	-25 to +45 °C	1	0.4
910925868266	WT490C 80S/840 PSD VWB WA7 L1200	-25 to +45 °C	1	0.4
910925868288	WT490C 42S/840 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
910925868289	WT490C 64S/840 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
910925868290	WT490C 80S/840 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	-25 to +45 °C	1	0.4
910925868611	WT490C 42S/840 PSU WB WA7 L1200	-25 to +45 °C	1	0.4
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	-25 to +45 °C	1	0.4
910925868613	WT490C 42S/840 PSU WB TW3 WA7L1200	-25 to +45 °C	1	0.4
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	-25 to +45 °C	1	0.4
910925868615	WT490C 42S/840 PSD WB WA7 L1200	-25 to +45 °C	1	0.4
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	-25 to +45 °C	1	0.4
910925868617	WT490C 42S/840 PSD WB TW3 WA7L1200	-25 to +45 °C	1	0.4
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	-25 to +45 °C	1	0.4
910925868619	WT490C 64S/840 PSU NB-HRO TW3WA7 L1200	-25 to +45 °C	1	0.4
910925868620	WT490C 64S/840 PSD NB-HRO TW3WA7 L1200	-25 to +45 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925868621	WT490C 80S/840 PSU NB-HRO TW3WA7 L1200	-25 to +45 °C	1	0.4
910925868622	WT490C 80S/840 PSD NB-HRO TW3WA7 L1200	-25 to +45 °C	1	0.4
910925868691	WT490C 35S/840 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
910925868693	WT490C 35S/840 PSU WB WA7 L1200	-25 to +45 °C	1	0.4
910925868695	WT490C 64S/840 PSU O PI5 L1200	-25 to +45 °C	1	0.4
910925868696	WT490C 64S/840 PSU PCO PI5 L1200	-25 to +45 °C	1	0.4
910925868699		-35 to +60 °C	1	0.4
910925868702	WT495C 64S/840 PSD WB PI5 L1200	-35 to +60 °C	1	0.4
910925868708	WT490C 64S/840 PSU WB WA7 CLII L1200	-25 to +45 °C	1	0.4
910925869401	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	-25 to +45 °C	1	0.4
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	0 to +40 °C	1	0.4
910925869403	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	-25 to +45 °C	1	0.4
910925869404	WT490C 80S/840 PSD WB TW3x2.5PI7 L1200	-25 to +45 °C	1	0.4
910925869410	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	-25 to +45 °C	1	0.4
91092586960	WT490C 100S/840 PSD WB PI5 L1200	-25 to +25 °C	-	-
91092586960	WT490C 100S/840 PSU WB WA7 L1200	-25 to +25 °C	-	-
91092586960	WT490C 100S/840 PSD WB WA7 L1200	-25 to +25 °C	-	-
91092586960	WT490C 100S/840 PSU WB PI5 L1200	-25 to +25 °C	-	-
910925868412	WT490C 64S/840 PSD WB PI5 L1600	-25 to +45 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925868413	WT490C 64S/840 PSU WB TW3 PI5L1600	-25 to +45 °C	1	0.4
910925868414	WT490C 64S/840 PSU WB PI5 L1600	-25 to +45 °C	1	0.4
910925868415	WT490C 80S/840 PSU WB PI5 L1600	-25 to +45 °C	1	0.4
910925868416	WT490C 80S/840 PSD WB PI5 L1600	-25 to +45 °C	1	0.4
910925868417	WT490C 80S/840 PSU WB TW3 PI5L1600	-25 to +45 °C	1	0.4
910925868418	WT490C 64S/840 PSD WB WA7 L1600	-25 to +45 °C	1	0.4
910925868419	WT490C 64S/840 PSU WB TW3 WA7L1600	-25 to +45 °C	1	0.4
910925868420	WT490C 64S/840 PSU WB WA7 L1600	-25 to +45 °C	1	0.4
910925868421	WT490C 80S/840 PSU WB WA7 L1600	-25 to +45 °C	1	0.4
910925868422	WT490C 80S/840 PSD WB WA7 L1600	-25 to +45 °C	1	0.4
910925868423	WT490C 80S/840 PSU WB TW3 WA7L1600	-25 to +45 °C	1	0.4

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925867731	WT490C 80S/840 PSU NB-HRO PI5L1800	(0.38, 0.38) SDCM <3
910925867732	WT490C 80S/840 PSD NB-HRO PI5L1800	(0.38, 0.38) SDCM <3
910925867733	WT490C 80S/840 PSU WB TW3 PI5L1800	(0.38, 0.38) SDCM <3
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	(0.38, 0.38) SDCM <3
910925867735	WT490C 80S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925867736	WT490C 80S/840 PSD WB TW3 PI7L1800	(0.38, 0.38) SDCM <3
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	(0.38, 0.38) SDCM <3
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	(0.38, 0.38) SDCM <3
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	(0.38, 0.38) SDCM <3
910925867740	WT490C 100S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925867741	WT490C 120S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868292	WT490C 80S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868293	WT490C 100S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868294	WT490C 120S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868516	WT490C 80S/840 SIA WB IA9 PI5L1800	(0.38, 0.38) SDCM <3
910925868697	WT490C 80S/840 PSU O PI5 L1800	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925868692	WT490C 35S/840 PSU WB PI5 L1600	-25 to +45 °C	1	0.4
910925868694	WT490C 35S/840 PSU WB WA7 L1600	-25 to +45 °C	1	0.4
910925869407	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	-25 to +45 °C	1	0.4
910925869408	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	-25 to +45 °C	1	0.4
910925867703	WT490C 23S/840 PSD WB PI5 L700	-25 to +45 °C	1	0.4
910925868287	WT490C 23S/840 PSU WB PI5 L700	-25 to +45 °C	1	0.4
910925868250	WT490C 64S/840 PSU WB TCW5 L1200	-25 to +45 °C	1	0.4
910925868510	WT490C 64S/840 PSU WB W5 L1200	-25 to +45 °C	1	0.4
910925868511	WT490C 80S/840 PSU WB W5 L1200	-25 to +45 °C	1	0.4
910925868512	WT490C 64S/840 PSD WB W5 L1200	-25 to +45 °C	1	0.4
910925868513	WT490C 80S/840 PSD WB W5 L1200	-25 to +45 °C	1	0.4

Order Code	Full Product Name	Initial chromaticity
910925868698	WT490C 80S/840 PSU PCO PI5 L1800	(0.38, 0.38) SDCM <3
910925868701	WT495C 80S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868703	WT495C 80S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868709	WT490C 80S/840 PSU WB WA7 CLII L1800	(0.38, 0.38) SDCM <3
910925869405	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	(0.38, 0.38) SDCM <3
910925869406	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	(0.38, 0.38) SDCM <3
910925869607	WT490C 150S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
910925869611	WT490C 150S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
910925868704	WT492C 64S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
910925868705	WT492C 80S/840 PSU WB W5 L1800	(0.38, 0.38) SDCM <3
910925868706	WT492C 64S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3
910925868707	WT492C 80S/840 PSD WB W5 L1800	(0.38, 0.38) SDCM <3
910770229590	WT490C 42S/830 PSU WB PI5 L1200	(0.43, 0.40) SDCM <3
910925867704	WT490C 42S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
910925867705	WT490C 64S/840 PSU NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
910925867706	WT490C 64S/840 PSD NB-HRO PI5L1200	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925867707	WT490C 64S/840 PSU WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
910925867708	WT490C 64S/840 PSU WB TW3 PI5L1200	(0.38, 0.38) SDCM <3
910925867709	WT490C 64S/840 PSU WB TC5 L1200	(0.38, 0.38) SDCM <3
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3
910925867711	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	(0.38, 0.38) SDCM <3
910925867712	WT490C 64S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
910925867713	WT490C 64S/840 PSD WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
910925867714	WT490C 64S/840 PSD WB TW3 PI7L1200	(0.38, 0.38) SDCM <3
910925867715	WT490C 64S/840 PSD WB ELD3 PI7 L1200	(0.38, 0.38) SDCM <3
910925867716	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	(0.38, 0.38) SDCM <3
910925867717	WT490C 64S/840 PSU VWB PI5 L1200	(0.38, 0.38) SDCM <3
910925867718	WT490C 64S/840 PSD VWB PI5 L1200	(0.38, 0.38) SDCM <3
910925867719	WT490C 80S/840 PSU NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
910925867720	WT490C 80S/840 PSD NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
910925867721	WT490C 80S/840 PSU WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
910925867722	WT490C 80S/840 PSU WB TW3 PI5L1200	(0.38, 0.38) SDCM <3
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3
910925867724	WT490C 80S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
910925867725	WT490C 80S/840 PSD WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
910925867726	WT490C 80S/840 PSD WB TW3 PI7L1200	(0.38, 0.38) SDCM <3
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	(0.38, 0.38) SDCM <3
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	(0.38, 0.38) SDCM <3
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	(0.38, 0.38) SDCM <3
910925867743	WT490C 64S/840 PSU NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
910925867744	WT490C 64S/840 PSD NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
910925868247	WT490C 64S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868249	WT490C 64S/840 PSU WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868252	WT490C 64S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868253	WT490C 64S/840 PSD WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	(0.38, 0.38) SDCM <3
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	(0.38, 0.38) SDCM <3
910925868257	WT490C 80S/840 PSU NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
910925868258	WT490C 80S/840 PSD NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
910925868259	WT490C 80S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868260	WT490C 80S/840 PSU WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868262	WT490C 80S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868263	WT490C 80S/840 PSD WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868265	WT490C 80S/840 PSU VWB WA7 L1200	(0.38, 0.38) SDCM <3
910925868266	WT490C 80S/840 PSD VWB WA7 L1200	(0.38, 0.38) SDCM <3
910925868288	WT490C 42S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868289	WT490C 64S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868290	WT490C 80S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	(0.38, 0.38) SDCM <3
910925868611	WT490C 42S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	(0.38, 0.38) SDCM <3
910925868613	WT490C 42S/840 PSU WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925868615	WT490C 42S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	(0.38, 0.38) SDCM <3
910925868617	WT490C 42S/840 PSD WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	(0.38, 0.38) SDCM <3
910925868619	WT490C 64S/840 PSU NB-HRO TW3WA7 L1200	(0.38, 0.38) SDCM <3
910925868620	WT490C 64S/840 PSD NB-HRO TW3WA7 L1200	(0.38, 0.38) SDCM <3
910925868621	WT490C 80S/840 PSU NB-HRO TW3WA7 L1200	(0.38, 0.38) SDCM <3
910925868622	WT490C 80S/840 PSD NB-HRO TW3WA7 L1200	(0.38, 0.38) SDCM <3
910925868691	WT490C 35S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868693	WT490C 35S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
910925868695	WT490C 64S/840 PSU O PI5 L1200	(0.38, 0.38) SDCM <3
910925868696	WT490C 64S/840 PSU PCO PI5 L1200	(0.38, 0.38) SDCM <3
910925868699		(0.38, 0.38) SDCM <3
910925868702	WT495C 64S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868708	WT490C 64S/840 PSU WB WA7 CLII L1200	(0.38, 0.38) SDCM <3
910925869401	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	(0.38, 0.38) SDCM <3
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	(0.38, 0.38) SDCM <3
910925869403	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	(0.38, 0.38) SDCM <3
910925869404	WT490C 80S/840 PSD WB TW3x2.5PI7 L1200	(0.38, 0.38) SDCM <3
910925869410	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	(0.38, 0.38) SDCM <3
91092586960	WT490C 100S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
6		
91092586960	WT490C 100S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
8		
91092586960	WT490C 100S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
9		
910925869610	WT490C 100S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
910925868412	WT490C 64S/840 PSD WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868413	WT490C 64S/840 PSU WB TW3 PI5L1600	(0.38, 0.38) SDCM <3
910925868414	WT490C 64S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868415	WT490C 80S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868416	WT490C 80S/840 PSD WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868417	WT490C 80S/840 PSU WB TW3 PI5L1600	(0.38, 0.38) SDCM <3
910925868418	WT490C 64S/840 PSD WB WA7 L1600	(0.38, 0.38) SDCM <3
910925868419	WT490C 64S/840 PSU WB TW3 WA7L1600	(0.38, 0.38) SDCM <3
910925868420	WT490C 64S/840 PSU WB WA7 L1600	(0.38, 0.38) SDCM <3
910925868421	WT490C 80S/840 PSU WB WA7 L1600	(0.38, 0.38) SDCM <3
910925868422	WT490C 80S/840 PSD WB WA7 L1600	(0.38, 0.38) SDCM <3
910925868423	WT490C 80S/840 PSU WB TW3 WA7L1600	(0.38, 0.38) SDCM <3
910925868692	WT490C 35S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
910925868694	WT490C 35S/840 PSU WB WA7 L1600	(0.38, 0.38) SDCM <3
910925869407	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	(0.38, 0.38) SDCM <3
910925869408	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	(0.38, 0.38) SDCM <3
910925867703	WT490C 23S/840 PSD WB PI5 L700	(0.38, 0.38) SDCM <3
910925868287	WT490C 23S/840 PSU WB PI5 L700	(0.38, 0.38) SDCM <3
910925868250	WT490C 64S/840 PSU WB TCW5 L1200	(0.38, 0.38) SDCM <3
910925868510	WT490C 64S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
910925868511	WT490C 80S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
910925868512	WT490C 64S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3
910925868513	WT490C 80S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3

Product Data

Pacific LED Gen5




Order Code	Full Product Name	Product family code
910925867731	WT490C 80S/840 PSU NB-HRO PI5L1800	WT490C
910925867732	WT490C 80S/840 PSD NB-HRO PI5L1800	WT490C
910925867733	WT490C 80S/840 PSU WB TW3 PI5L1800	WT490C
910925867734	WT490C 80S/840 PSU WB ELP3 PI5 L1800	WT490C
910925867735	WT490C 80S/840 PSD WB PI5 L1800	WT490C
910925867736	WT490C 80S/840 PSD WB TW3 PI7L1800	WT490C
910925867737	WT490C 80S/840 PSD WB ELD3 PI7 L1800	WT490C
910925867738	WT490C 80S/840 PSU VWB PI5 L1800	WT490C
910925867739	WT490C 80S/840 PSD VWB PI5 L1800	WT490C
910925867740	WT490C 100S/840 PSD WB PI5 L1800	WT490C
910925867741	WT490C 120S/840 PSD WB PI5 L1800	WT490C
910925868292	WT490C 80S/840 PSU WB PI5 L1800	WT490C
910925868293	WT490C 100S/840 PSU WB PI5 L1800	WT490C
910925868294	WT490C 120S/840 PSU WB PI5 L1800	WT490C
910925868516	WT490C 80S/840 SIA WB IA9 PI5L1800	WT490C
910925868697	WT490C 80S/840 PSU O PI5 L1800	WT490C
910925868698	WT490C 80S/840 PSU PCO PI5 L1800	WT490C
910925868701	WT495C 80S/840 PSU WB PI5 L1800	WT495C
910925868703	WT495C 80S/840 PSD WB PI5 L1800	WT495C
910925868709	WT490C 80S/840 PSU WB WA7 CLII L1800	WT490C
910925869405	WT490C 80S/840 PSU WB TW3x2.5PI5 L1800	WT490C
910925869406	WT490C 80S/840 PSD WB TW3x2.5PI7 L1800	WT490C
910925869607	WT490C 150S/840 PSD WB PI5 L1800	WT490C
910925869611	WT490C 150S/840 PSU WB PI5 L1800	WT490C
910925868704	WT492C 64S/840 PSU WB W5 L1200	WT492C
910925868705	WT492C 80S/840 PSU WB W5 L1800	WT492C
910925868706	WT492C 64S/840 PSD WB W5 L1200	WT492C
910925868707	WT492C 80S/840 PSD WB W5 L1800	WT492C
910770229590	WT490C 42S/830 PSU WB PI5 L1200	WT490C
910925867704	WT490C 42S/840 PSD WB PI5 L1200	WT490C
910925867705	WT490C 64S/840 PSU NB-HRO PI5L1200	WT490C
910925867706	WT490C 64S/840 PSD NB-HRO PI5L1200	WT490C
910925867707	WT490C 64S/840 PSU WB TW1 PI5L1200	WT490C
910925867708	WT490C 64S/840 PSU WB TW3 PI5L1200	WT490C
910925867709	WT490C 64S/840 PSU WB TC5 L1200	WT490C
910925867710	WT490C 64S/840 PSU WB ELP3 PI5 L1200	WT490C
910925867711	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	WT490C
910925867712	WT490C 64S/840 PSD WB PI5 L1200	WT490C
910925867713	WT490C 64S/840 PSD WB TW1 PI5L1200	WT490C
910925867714	WT490C 64S/840 PSD WB TW3 PI7L1200	WT490C
910925867715	WT490C 64S/840 PSD WB ELD3 PI7 L1200	WT490C
910925867716	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	WT490C
910925867717	WT490C 64S/840 PSU VWB PI5 L1200	WT490C
910925867718	WT490C 64S/840 PSD VWB PI5 L1200	WT490C
910925867719	WT490C 80S/840 PSU NB-HRO PI5L1200	WT490C
910925867720	WT490C 80S/840 PSD NB-HRO PI5L1200	WT490C
910925867721	WT490C 80S/840 PSU WB TW1 PI5L1200	WT490C
910925867722	WT490C 80S/840 PSU WB TW3 PI5L1200	WT490C
910925867723	WT490C 80S/840 PSU WB ELP3 PI5 L1200	WT490C
910925867724	WT490C 80S/840 PSD WB PI5 L1200	WT490C
910925867725	WT490C 80S/840 PSD WB TW1 PI5L1200	WT490C
910925867726	WT490C 80S/840 PSD WB TW3 PI7L1200	WT490C

Order Code	Full Product Name	Product family code
910925867727	WT490C 80S/840 PSD WB ELD3 PI7 L1200	WT490C
910925867728	WT490C 80S/840 PSU VWB PI5 L1200	WT490C
910925867729	WT490C 80S/840 PSD VWB PI5 L1200	WT490C
910925867743	WT490C 64S/840 PSU NB-HRO WA7L1200	WT490C
910925867744	WT490C 64S/840 PSD NB-HRO WA7L1200	WT490C
910925868247	WT490C 64S/840 PSU WB WA7 L1200	WT490C
910925868249	WT490C 64S/840 PSU WB TW3 WA7L1200	WT490C
910925868251	WT490C 64S/840 PSU WB ELP3 WA7 L1200	WT490C
910925868252	WT490C 64S/840 PSD WB WA7 L1200	WT490C
910925868253	WT490C 64S/840 PSD WB TW3 WA7L1200	WT490C
910925868254	WT490C 64S/840 PSD WB ELD3 WA7 L1200	WT490C
910925868255	WT490C 64S/840 PSU VWB WA7 L1200	WT490C
910925868256	WT490C 64S/840 PSD VWB WA7 L1200	WT490C
910925868257	WT490C 80S/840 PSU NB-HRO WA7L1200	WT490C
910925868258	WT490C 80S/840 PSD NB-HRO WA7L1200	WT490C
910925868259	WT490C 80S/840 PSU WB WA7 L1200	WT490C
910925868260	WT490C 80S/840 PSU WB TW3 WA7L1200	WT490C
910925868261	WT490C 80S/840 PSU WB ELP3 WA7 L1200	WT490C
910925868262	WT490C 80S/840 PSD WB WA7 L1200	WT490C
910925868263	WT490C 80S/840 PSD WB TW3 WA7L1200	WT490C
910925868264	WT490C 80S/840 PSD WB ELD3 WA7 L1200	WT490C
910925868265	WT490C 80S/840 PSU VWB WA7 L1200	WT490C
910925868266	WT490C 80S/840 PSD VWB WA7 L1200	WT490C
910925868288	WT490C 42S/840 PSU WB PI5 L1200	WT490C
910925868289	WT490C 64S/840 PSU WB PI5 L1200	WT490C
910925868290	WT490C 80S/840 PSU WB PI5 L1200	WT490C
910925868509	WT490C 42S/840 PSD VWB PI5 L1200	WT490C
910925868611	WT490C 42S/840 PSU WB WA7 L1200	WT490C
910925868612	WT490C 42S/840 PSU VWB WA7 L1200	WT490C
910925868613	WT490C 42S/840 PSU WB TW3 WA7L1200	WT490C
910925868614	WT490C 42S/840 PSU VWB TW3 WA7 L1200	WT490C
910925868615	WT490C 42S/840 PSD WB WA7 L1200	WT490C
910925868616	WT490C 42S/840 PSD VWB WA7 L1200	WT490C
910925868617	WT490C 42S/840 PSD WB TW3 WA7L1200	WT490C
910925868618	WT490C 42S/840 PSD VWB TW3 WA7 L1200	WT490C
910925868619	WT490C 64S/840 PSU NB-HRO TW3WA7 L1200	WT490C
910925868620	WT490C 64S/840 PSD NB-HRO TW3WA7 L1200	WT490C
910925868621	WT490C 80S/840 PSU NB-HRO TW3WA7 L1200	WT490C
910925868622	WT490C 80S/840 PSD NB-HRO TW3WA7 L1200	WT490C
910925868691	WT490C 35S/840 PSU WB PI5 L1200	WT490C
910925868693	WT490C 35S/840 PSU WB WA7 L1200	WT490C
910925868695	WT490C 64S/840 PSU O PI5 L1200	WT490C
910925868696	WT490C 64S/840 PSU PCO PI5 L1200	WT490C
910925868699		WT495C
910925868702	WT495C 64S/840 PSD WB PI5 L1200	WT495C
910925868708	WT490C 64S/840 PSU WB WA7 CLII L1200	WT490C
910925869401	WT490C 64S/840 PSU WB TW3x2.5PI5 L1200	WT490C
910925869402	WT490C 64S/840 PSU WB ELP3 TW1x2.5 PI5 L	WT490C
910925869403	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	WT490C
910925869404	WT490C 80S/840 PSD WB TW3x2.5PI7 L1200	WT490C
910925869410	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	WT490C
910925869606	WT490C 100S/840 PSD WB PI5 L1200	WT490C

Order Code	Full Product Name	Product family code
910925869608	WT490C 100S/840 PSU WB WA7 L1200	WT490C
910925869609	WT490C 100S/840 PSD WB WA7 L1200	WT490C
910925869610	WT490C 100S/840 PSU WB PI5 L1200	WT490C
910925868412	WT490C 64S/840 PSD WB PI5 L1600	WT490C
910925868413	WT490C 64S/840 PSU WB TW3 PI5L1600	WT490C
910925868414	WT490C 64S/840 PSU WB PI5 L1600	WT490C
910925868415	WT490C 80S/840 PSU WB PI5 L1600	WT490C
910925868416	WT490C 80S/840 PSD WB PI5 L1600	WT490C
910925868417	WT490C 80S/840 PSU WB TW3 PI5L1600	WT490C
910925868418	WT490C 64S/840 PSD WB WA7 L1600	WT490C
910925868419	WT490C 64S/840 PSU WB TW3 WA7L1600	WT490C
910925868420	WT490C 64S/840 PSU WB WA7 L1600	WT490C
910925868421	WT490C 80S/840 PSU WB WA7 L1600	WT490C

Order Code	Full Product Name	Product family code
910925868422	WT490C 80S/840 PSD WB WA7 L1600	WT490C
910925868423	WT490C 80S/840 PSU WB TW3 WA7L1600	WT490C
910925868692	WT490C 35S/840 PSU WB PI5 L1600	WT490C
910925868694	WT490C 35S/840 PSU WB WA7 L1600	WT490C
910925869407	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	WT490C
910925869408	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	WT490C
910925867703	WT490C 23S/840 PSD WB PI5 L700	WT490C
910925868287	WT490C 23S/840 PSU WB PI5 L700	WT490C
910925868250	WT490C 64S/840 PSU WB TCW5 L1200	WT490C
910925868510	WT490C 64S/840 PSU WB W5 L1200	WT490C
910925868511	WT490C 80S/840 PSU WB W5 L1200	WT490C
910925868512	WT490C 64S/840 PSD WB W5 L1200	WT490C
910925868513	WT490C 80S/840 PSD WB W5 L1200	WT490C




Polar Wide Diagrams



Polar Normal (separate) - WT490CI - 910770229590

Polar Normal (separate) - WT490CI - 910925868249

Polar Normal (separate) - WT490CI - 910925868292




Polar Normal (separate) - WT490CI - 910925868698


Polar Normal (separate) - WT490CI - 910925868708

Polar Normal (separate) - WT490CI - 910925868259


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868423




Polar Normal (separate) - WT490CI - 910925868702




Polar Normal (separate) - WT490CI - 910925868261




Polar Normal (separate) - WT490CI - 910925868413




Polar Normal (separate) - WT490CI - 910925868697




Polar Normal (separate) - WT490CI - 910925868699



Polar Normal (separate) - WT490CI - 910925868692






Polar Normal (separate) - WT490CI - 910925868694



Polar Normal (separate) - WT490CI - 910925868693




Polar Wide Diagrams



Polar Normal (separate) - WT490CI - 910925868706

Polar Normal (separate) - WT490CI - 910925868709




Polar Normal (separate) - WT490CI - 910925868288



Polar Normal (separate) - WT490CI - 910925868414

Polar Normal (separate) - WT490CI - 910925868513

Polar Normal (separate) - WT490CI - 910925868705




Polar Normal (separate) - WT490CI - 910925868419


Polar Normal (separate) - WT490CI - 910925868511

Polar Normal (separate) - WT490CI - 910925868613


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868516




Polar Normal (separate) - WT490CI - 910925868701




Polar Normal (separate) - WT490CI - 910925868703




Polar Normal (separate) - WT490CI - 910925868422




Polar Normal (separate) - WT490CI - 910925868509




Polar Normal (separate) - WT490CI - 910925867704



Polar Normal (separate) - WT490CI - 910925867723




Polar Normal (separate) - WT490CI - 910925867732




Polar Normal (separate) - WT490CI - 910925867735


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867706




Polar Normal (separate) - WT490CI - 910925867712




Polar Normal (separate) - WT490CI - 910925867711




Polar Normal (separate) - WT490CI - 910925867724




Polar Normal (separate) - WT490CI - 910925867726




Polar Normal (separate) - WT490CI - 910925867727



Polar Normal (separate) - WT490CI - 910925867720




Polar Normal (separate) - WT490CI - 910925867738




Polar Normal (separate) - WT490CI - 910925867713


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867717




Polar Normal (separate) - WT490CI - 910925867714




Polar Normal (separate) - WT490CI - 910925867715




Polar Normal (separate) - WT490CI - 910925867716




Polar Normal (separate) - WT490CI - 910925867739




Polar Normal (separate) - WT490CI - 910925867708



Polar Normal (separate) - WT490CI - 910925867719




Polar Normal (separate) - WT490CI - 910925867725




Polar Normal (separate) - WT490CI - 910925867737


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867718




Polar Normal (separate) - WT490CI - 910925867734




Polar Normal (separate) - WT490CI - 910925867721




Polar Normal (separate) - WT490CI - 910925867729




Polar Normal (separate) - WT490CI - 910925868253




Polar Normal (separate) - WT490CI - 910925868266



Polar Normal (separate) - WT490CI - 910925868287




Polar Normal (separate) - WT490CI - 910925868289




Polar Normal (separate) - WT490CI - 910925868290


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868256




Polar Normal (separate) - WT490CI - 910925868264




Polar Normal (separate) - WT490CI - 910925868412




Polar Normal (separate) - WT490CI - 910925868611




Polar Normal (separate) - WT490CI - 910925868252




Polar Normal (separate) - WT490CI - 910925868262



Polar Normal (separate) - WT490CI - 910925868265




Polar Normal (separate) - WT490CI - 910925868416




Polar Normal (separate) - WT490CI - 910925868510


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867703




Polar Normal (separate) - WT490CI - 910925867705




Polar Normal (separate) - WT490CI - 910925867707




Polar Normal (separate) - WT490CI - 910925867709




Polar Normal (separate) - WT490CI - 910925867710




Polar Normal (separate) - WT490CI - 910925867722



Polar Normal (separate) - WT490CI - 910925867728




Polar Normal (separate) - WT490CI - 910925867731




Polar Normal (separate) - WT490CI - 910925867733


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867736




Polar Normal (separate) - WT490CI - 910925867743




Polar Normal (separate) - WT490CI - 910925867741




Polar Normal (separate) - WT490CI - 910925867740




Polar Normal (separate) - WT490CI - 910925867744




Polar Normal (separate) - WT490CI - 910925868247



Polar Normal (separate) - WT490CI - 910925868251




Polar Normal (separate) - WT490CI - 910925868255




Polar Normal (separate) - WT490CI - 910925868254


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868258




Polar Normal (separate) - WT490CI - 910925868263




Polar Normal (separate) - WT490CI - 910925868260




Polar Normal (separate) - WT490CI - 910925868257




Polar Normal (separate) - WT490CI - 910925868294




Polar Normal (separate) - WT490CI - 910925868293



Polar Normal (separate) - WT490CI - 910925868415




Polar Normal (separate) - WT490CI - 910925868417




Polar Normal (separate) - WT490CI - 910925868418


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868420




Polar Normal (separate) - WT490CI - 910925868421




Polar Normal (separate) - WT490CI - 910925868512




Polar Normal (separate) - WT490CI - 910925868691




Polar Normal (separate) - WT490CI - 910925868695




Polar Normal (separate) - WT490CI - 910925868696



Polar Normal (separate) - WT490CI - 910925868704




Polar Normal (separate) - WT490CI - 910925868707




Polar Normal (separate) - WT490CI - 910925869401


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925869402




Polar Normal (separate) - WT490CI - 910925869403




Polar Normal (separate) - WT490CI - 910925869405




Polar Normal (separate) - WT490CI - 910925869406




Polar Normal (separate) - WT490CI - 910925869404




Polar Normal (separate) - WT490CI - 910925869407



Polar Normal (separate) - WT490CI - 910925869408




Polar Normal (separate) - WT490CI - 910925869410




Polar Normal (separate) - WT490CI - 910925868250


Polar Wide Diagrams




**Polar Normal (separate) - WT490CI -
910925868614**




**Polar Normal (separate) - WT490CI -
910925868612**




**Polar Normal (separate) - WT490CI -
910925868615**




**Polar Normal (separate) - WT490CI -
910925868619**




**Polar Normal (separate) - WT490CI -
910925868616**




**Polar Normal (separate) - WT490CI -
910925868617**



Polar Normal (separate) - WT490CI - 910925868618




**Polar Normal (separate) - WT490CI -
910925868620**




**Polar Normal (separate) - WT490CI -
910925868621**


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868622




Polar Normal (separate) - WT490CI - 910925869609




Polar Normal (separate) - WT490CI - 910925869610




Polar Normal (separate) - WT490CI - 910925869608



Polar Normal (separate) - WT490CI - 910925869611



Polar Normal (separate) - WT490CI - 910925869606



Polar Normal (separate) - WT490CI - 910925869607

