



Robust, connectable luminaire with outstanding performance.

Pacific LED Gen5

Pacific LED gen5 is an innovative and best-in-class LED waterproof luminaire that is praised for its optimal performance. It meets the demanding requirements of contemporary and harsh industries. It is a very robust, compact and reliable luminaire with excellent quality of light. With a high degree of mechanical (IK08), water and dust protection (IP66), combined with proven chemical resistance, the Pacific LED gen5 can perfectly withstand the harsh conditions of the automotive, food and heavy industries. But it also performs well in parking garages and warehouses. Pacific LED gen5 luminaires provide superior, artefact-free light quality and homogeneous light, offered with multiple optics and broad range of light outputs (up to 15,000 lm). This ensures more flexibility in optimized light scheme planning. They are also designed with a circular approach, which means these fully-serviceable luminaires can be upgraded to extend their overall lifecycle. The luminaires stand out because of their quick and easy installation that facilitates through wiring and various connection and mounting options. But also, because of their attractive TCO, energy efficiency, and ease of maintenance – with minimum of disruption to operations in demanding applications. To make the Pacific LED gen5 even more complete, system integration with Interact Industry opens up additional opportunities for optimized efficiency, energy savings, improved light management, productivity, and safety. Making it future proof in every aspect. Discover Pacific LED gen5. Optimal performance for demanding environments.

Pacific LED Gen5

Benefits

- Long service life offering peace of mind on your lighting installation.
- Suitable for your industrial application due to wide coverage including food production, heavy and chemical industries, automotive, parking garages and warehousing.
- Lowers your maintenance investments due to easy servicing and parts replacements with a modular approach.
- Can be integrated into an Interact connected lighting installation to optimize your operations and maximize energy saving and insights.

Features

- Highly energy efficient and long lifetime: up to 160 lm/W and lifetime up to 100,000 hrs L80.
- Wide application coverage with extensive lumen output (up to 15000 lumen) and optics choice, combined with high quality chemical-resistant materials.
- Robust and compact product architecture, with high water and dust protection (IP66), combined with a high degree of mechanical protection (IK08).
- High uniformity, glare control and artefact-free light distributions.
- Hassle-free installation and maintenance.

Application

- Food Processing
- Parking Garages
- Manufacturing
- Warehouses/distribution centers

Warnings and Safety


- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Versions




Pacific LED gen5, L700

Dimensional drawing



Pacific LED Gen5

Dimensional drawing



Product details



Pacific LED gen5, looping connection, 2 entry on one side



Pacific LED gen5 with push in 7-pole (PI7) connector



Pacific LED gen5, Wieland connector



Pacific LED gen5 with WAGO connector



Pacific LED gen5 connection through WAGO connector side view



Pacific LED gen5 with push in 5-pole (PI5) connecto



Pacific LED gen5 with Wieland connector

Pacific LED Gen5

Product details



Pacific LED gen5 connection
through WAGO connector

General Information

Driver included	Yes
Light source replaceable	Yes
Number of gear units	1 unit
Service tag	Yes

Light Technical

Color rendering index (CRI)	>80
-----------------------------	-----

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Mechanical and Housing

Housing Color	White
Mech. impact protection code	IK08
Ingress protection code	IP66

Approval and Application

CE mark	Yes
ENEC mark	ENEC plus mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
-------------------------	-------

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	4000 K	165 lm/W	8,000 lm	Narrow beam - High-rack optic
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	4000 K	165 lm/W	8,000 lm	Narrow beam - High-rack optic
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	4000 K	165 lm/W	8,000 lm	Wide beam
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	4000 K	154 lm/W	8,000 lm	Wide beam
10990200	WT490C 80S/840 PSD WB PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	4000 K	165 lm/W	8,000 lm	Wide beam
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	4000 K	154 lm/W	8,000 lm	Wide beam
10993300	WT490C 80S/840 PSU VWB PI5 L1800	4000 K	165 lm/W	8,000 lm	Very wide beam
10994000	WT490C 80S/840 PSD VWB PI5 L1800	4000 K	165 lm/W	8,000 lm	Very wide beam
10995700	WT490C 100S/840 PSD WB PI5 L1800	4000 K	161 lm/W	10,000 lm	Wide beam
10996400	WT490C 120S/840 PSD WB PI5 L1800	4000 K	158 lm/W	12,000 lm	Wide beam
62357600	WT490C 80S/840 PSU WB PI5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
62358300	WT490C 100S/840 PSU WB PI5 L1800	4000 K	161 lm/W	10,000 lm	Wide beam
62359000	WT490C 120S/840 PSU WB PI5 L1800	4000 K	158 lm/W	12,000 lm	Wide beam
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	4000 K	165 lm/W	8,000 lm	Wide beam
62758100	WT490C 80S/840 PSU O PI5 L1800	4000 K	157 lm/W	7,600 lm	Opal

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
62759800	WT490C 80S/840 PSU PCO PI5 L1800	4000 K	136 lm/W	6,600 lm	Opal
62761100	WT495C 80S/840 PSU WB PI5 L1800	4000 K	157 lm/W	8,000 lm	Wide beam
62763500	WT495C 80S/840 PSD WB PI5 L1800	4000 K	157 lm/W	8,000 lm	Wide beam
77399800	WT490C 150S/840 PSU WB PI5 L1800	4000 K	155 lm/W	15,000 lm	Very wide beam
62764200	WT492C 64S/840 PSU WB W5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62765900	WT492C 80S/840 PSU WB W5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
62766600	WT492C 64S/840 PSD WB W5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
62767300	WT492C 80S/840 PSD WB W5 L1800	4000 K	165 lm/W	8,000 lm	Wide beam
73290200	WT490C 42S/830 PSU WB PI5 L1200	3000 K	157 lm/W	4,200 lm	Wide beam
10959900	WT490C 42S/840 PSD WB PI5 L1200	4000 K	162 lm/W	4,200 lm	Wide beam
10960500	WT490C 64S/840 PSU NB- HRO PI5L1200	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
10961200	WT490C 64S/840 PSD NB- HRO PI5L1200	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	4000 K	160 lm/W	6,400 lm	Wide beam
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	4000 K	160 lm/W	6,400 lm	Wide beam
10964300	WT490C 64S/840 PSU WB TC5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
10967400	WT490C 64S/840 PSD WB PI5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	4000 K	162 lm/W	6,400 lm	Wide beam
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	4000 K	162 lm/W	6,400 lm	Wide beam
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
10972800	WT490C 64S/840 PSU VWB PI5 L1200	4000 K	160 lm/W	6,400 lm	Very wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
10973500	WT490C 64S/840 PSD VWB PI5 L1200	4000 K	162 lm/W	6,400 lm	Very wide beam
10974200	WT490C 80S/840 PSU NB- HRO PI5L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
10975900	WT490C 80S/840 PSD NB- HRO PI5L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
10979700	WT490C 80S/840 PSD WB PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	4000 K	157 lm/W	8,000 lm	Wide beam
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
10983400	WT490C 80S/840 PSU VWB PI5 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
10984100	WT490C 80S/840 PSD VWB PI5 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
10998800	WT490C 64S/840 PSU NB- HRO WA7L1200	4000 K	160 lm/W	6,400 lm	Narrow beam - High-rack optic
10999500	WT490C 64S/840 PSD NB- HRO WA7L1200	4000 K	162 lm/W	6,400 lm	Narrow beam - High-rack optic
62312500	WT490C 64S/840 PSU WB WA7 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	4000 K	146 lm/W	6,400 lm	Wide beam
62317000	WT490C 64S/840 PSD WB WA7 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	4000 K	162 lm/W	6,400 lm	Wide beam
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	4000 K	147 lm/W	6,400 lm	Wide beam
62320000	WT490C 64S/840 PSU VWB WA7 L1200	4000 K	160 lm/W	6,400 lm	Very wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
62321700	WT490C 64S/840 PSD VWB WA7 L1200	4000 K	162 lm/W	6,400 lm	Very wide beam
62322400	WT490C 80S/840 PSU NB- HRO WA7L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
62323100	WT490C 80S/840 PSD NB- HRO WA7L1200	4000 K	157 lm/W	8,000 lm	Narrow beam - High-rack optic
62324800	WT490C 80S/840 PSU WB WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
62327900	WT490C 80S/840 PSD WB WA7 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	4000 K	146 lm/W	8,000 lm	Wide beam
62330900	WT490C 80S/840 PSU VWB WA7 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
62331600	WT490C 80S/840 PSD VWB WA7 L1200	4000 K	157 lm/W	8,000 lm	Very wide beam
62353800	WT490C 42S/840 PSU WB PI5 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
62354500	WT490C 64S/840 PSU WB PI5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62355200	WT490C 80S/840 PSU WB PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62571600	WT490C 42S/840 PSD VWB PI5 L1200	4000 K	162 lm/W	4,200 lm	Very wide beam
62752900	WT490C 35S/840 PSU WB PI5 L1200	4000 K	159 lm/W	3,500 lm	Wide beam
62757400	WT490C 64S/840 PSU PCO PI5 L1200	4000 K	133 lm/W	5,300 lm	Opal
62760400		4000 K	158 lm/W	6,400 lm	Wide beam
62762800	WT495C 64S/840 PSD WB PI5 L1200	4000 K	158 lm/W	6,400 lm	Wide beam
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	4000 K	165 lm/W	4,200 lm	Wide beam
77394300	WT490C 100S/840 PSD WB PI5 L1200	4000 K	152 lm/W	10,000 lm	Very wide beam
62475700	WT490C 64S/840 PSD WB PI5 L1600	4000 K	162 lm/W	6,400 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	4000 K	160 lm/W	6,400 lm	Wide beam
62477100	WT490C 64S/840 PSU WB PI5 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
62478800	WT490C 80S/840 PSU WB PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
62479500	WT490C 80S/840 PSD WB PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
62480100	WT490C 80S/840 PSU WB TW3 PI5L1600	4000 K	157 lm/W	8,000 lm	Wide beam
62481800	WT490C 64S/840 PSD WB WA7 L1600	4000 K	162 lm/W	6,400 lm	Wide beam
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	4000 K	160 lm/W	6,400 lm	Wide beam
62483200	WT490C 64S/840 PSU WB WA7 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
62484900	WT490C 80S/840 PSU WB WA7 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
62485600	WT490C 80S/840 PSD WB WA7 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
62486300	WT490C 80S/840 PSU WB TW3 WA7L1600	4000 K	157 lm/W	8,000 lm	Wide beam
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	4000 K	160 lm/W	6,400 lm	Wide beam
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	4000 K	157 lm/W	8,000 lm	Wide beam
10958200	WT490C 23S/840 PSD WB PI5 L700	4000 K	160 lm/W	2,300 lm	Wide beam
62352100	WT490C 23S/840 PSU WB PI5 L700	4000 K	151 lm/W	2,300 lm	Wide beam
62572300	WT490C 64S/840 PSU WB W5 L1200	4000 K	160 lm/W	6,400 lm	Wide beam
62573000	WT490C 80S/840 PSU WB W5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam
62574700	WT490C 64S/840 PSD WB W5 L1200	4000 K	162 lm/W	6,400 lm	Wide beam
62575400	WT490C 80S/840 PSD WB W5 L1200	4000 K	157 lm/W	8,000 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	48.5 W	10994000	WT490C 80S/840 PSD VWB PI5 L1800	48.5 W
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	48.5 W	10995700	WT490C 100S/840 PSD WB PI5 L1800	62 W
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	48.5 W	10996400	WT490C 120S/840 PSD WB PI5 L1800	76 W
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	52 W	62357600	WT490C 80S/840 PSU WB PI5 L1800	48.5 W
10990200	WT490C 80S/840 PSD WB PI5 L1800	48.5 W	62358300	WT490C 100S/840 PSU WB PI5 L1800	62 W
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	48.5 W	62359000	WT490C 120S/840 PSU WB PI5 L1800	76 W
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	52 W	62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	48.5 W
10993300	WT490C 80S/840 PSU VWB PI5 L1800	48.5 W	62758100	WT490C 80S/840 PSU O PI5 L1800	51 W

Pacific LED Gen5

Order Code	Full Product Name	Power Consumption
62759800	WT490C 80S/840 PSU PCO PI5 L1800	48.5 W
62761100	WT495C 80S/840 PSU WB PI5 L1800	49 W
62763500	WT495C 80S/840 PSD WB PI5 L1800	48.5 W
77399800	WT490C 150S/840 PSU WB PI5 L1800	97 W
62764200	WT492C 64S/840 PSU WB W5 L1200	40 W
62765900	WT492C 80S/840 PSU WB W5 L1800	49 W
62766600	WT492C 64S/840 PSD WB W5 L1200	39.5 W
62767300	WT492C 80S/840 PSD WB W5 L1800	48.5 W
73290200	WT490C 42S/830 PSU WB PI5 L1200	25.5 W
10959900	WT490C 42S/840 PSD WB PI5 L1200	26 W
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	40 W
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	39.5 W
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	40 W
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	40 W
10964300	WT490C 64S/840 PSU WB TC5 L1200	40 W
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	44 W
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	44 W
10967400	WT490C 64S/840 PSD WB PI5 L1200	39.5 W
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	39.5 W
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	39.5 W
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	43.5 W
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	43.5 W
10972800	WT490C 64S/840 PSU VWB PI5 L1200	40 W
10973500	WT490C 64S/840 PSD VWB PI5 L1200	39.5 W
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	51 W
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	51 W
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	51 W
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	51 W
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	55 W
10979700	WT490C 80S/840 PSD WB PI5 L1200	51 W
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	51 W
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	51 W
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	55 W
10983400	WT490C 80S/840 PSU VWB PI5 L1200	51 W
10984100	WT490C 80S/840 PSD VWB PI5 L1200	51 W
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	40 W
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	39.5 W
62312500	WT490C 64S/840 PSU WB WA7 L1200	40 W
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	40 W
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	44 W
62317000	WT490C 64S/840 PSD WB WA7 L1200	39.5 W
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	39.5 W
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	43.5 W

Order Code	Full Product Name	Power Consumption
62320000	WT490C 64S/840 PSU VWB WA7 L1200	40 W
62321700	WT490C 64S/840 PSD VWB WA7 L1200	39.5 W
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	51 W
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	51 W
62324800	WT490C 80S/840 PSU WB WA7 L1200	51 W
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	51 W
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	55 W
62327900	WT490C 80S/840 PSD WB WA7 L1200	51 W
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	51 W
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	55 W
62330900	WT490C 80S/840 PSU VWB WA7 L1200	51 W
62331600	WT490C 80S/840 PSD VWB WA7 L1200	51 W
62353800	WT490C 42S/840 PSU WB PI5 L1200	25.5 W
62354500	WT490C 64S/840 PSU WB PI5 L1200	40 W
62355200	WT490C 80S/840 PSU WB PI5 L1200	51 W
62571600	WT490C 42S/840 PSD VWB PI5 L1200	26 W
62752900	WT490C 35S/840 PSU WB PI5 L1200	22 W
62757400	WT490C 64S/840 PSU PCO PI5 L1200	40 W
62760400		40.5 W
62762800	WT495C 64S/840 PSD WB PI5 L1200	40.5 W
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	51 W
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	25.5 W
77394300	WT490C 100S/840 PSD WB PI5 L1200	66 W
62475700	WT490C 64S/840 PSD WB PI5 L1600	39.5 W
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	40 W
62477100	WT490C 64S/840 PSU WB PI5 L1600	40 W
62478800	WT490C 80S/840 PSU WB PI5 L1600	51 W
62479500	WT490C 80S/840 PSD WB PI5 L1600	51 W
62480100	WT490C 80S/840 PSU WB TW3 PI5L1600	51 W
62481800	WT490C 64S/840 PSD WB WA7 L1600	39.5 W
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	40 W
62483200	WT490C 64S/840 PSU WB WA7 L1600	40 W
62484900	WT490C 80S/840 PSU WB WA7 L1600	51 W
62485600	WT490C 80S/840 PSD WB WA7 L1600	51 W
62486300	WT490C 80S/840 PSU WB TW3 WA7L1600	51 W
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	40 W
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	51 W
10958200	WT490C 23S/840 PSD WB PI5 L700	14.4 W
62352100	WT490C 23S/840 PSU WB PI5 L700	15.2 W
62572300	WT490C 64S/840 PSU WB W5 L1200	40 W
62573000	WT490C 80S/840 PSU WB W5 L1200	51 W
62574700	WT490C 64S/840 PSD WB W5 L1200	39.5 W
62575400	WT490C 80S/840 PSD WB W5 L1200	51 W

Controls and Dimming

Order Code	Full Product Name	Embedded	
		Dimmable	control
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	No	-
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	Yes	-
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	No	-
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	No	-

Order Code	Full Product Name	Embedded	
		Dimmable	control
10990200	WT490C 80S/840 PSD WB PI5 L1800	Yes	-
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	Yes	-
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	Yes	-
10993300	WT490C 80S/840 PSU VWB PI5 L1800	No	-

Pacific LED Gen5

Order Code	Full Product Name	Embedded	
		Dimmable	control
10994000	WT490C 80S/840 PSD VWB PI5 L1800	Yes	-
10995700	WT490C 100S/840 PSD WB PI5 L1800	Yes	-
10996400	WT490C 120S/840 PSD WB PI5 L1800	Yes	-
62357600	WT490C 80S/840 PSU WB PI5 L1800	No	-
62358300	WT490C 100S/840 PSU WB PI5 L1800	No	-
62359000	WT490C 120S/840 PSU WB PI5 L1800	No	-
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	Yes	InterAct SNS410 antenna
62758100	WT490C 80S/840 PSU O PI5 L1800	No	-
62759800	WT490C 80S/840 PSU PCO PI5 L1800	No	-
62761100	WT495C 80S/840 PSU WB PI5 L1800	No	-
62763500	WT495C 80S/840 PSD WB PI5 L1800	Yes	-
77399800	WT490C 150S/840 PSU WB PI5 L1800	No	-
62764200	WT492C 64S/840 PSU WB W5 L1200	No	-
62765900	WT492C 80S/840 PSU WB W5 L1800	No	-
62766600	WT492C 64S/840 PSD WB W5 L1200	Yes	-
62767300	WT492C 80S/840 PSD WB W5 L1800	Yes	-
73290200	WT490C 42S/830 PSU WB PI5 L1200	No	-
10959900	WT490C 42S/840 PSD WB PI5 L1200	Yes	-
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	No	-
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	Yes	-
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	No	-
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	No	-
10964300	WT490C 64S/840 PSU WB TC5 L1200	No	-
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	No	-
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	No	-
10967400	WT490C 64S/840 PSD WB PI5 L1200	Yes	-
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	Yes	-
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	Yes	-
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	Yes	-
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	Yes	-
10972800	WT490C 64S/840 PSU VWB PI5 L1200	No	-
10973500	WT490C 64S/840 PSD VWB PI5 L1200	Yes	-
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	No	-
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	Yes	-
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	No	-
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	No	-
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	No	-
10979700	WT490C 80S/840 PSD WB PI5 L1200	Yes	-
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	Yes	-
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	Yes	-
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	Yes	-
10983400	WT490C 80S/840 PSU VWB PI5 L1200	No	-
10984100	WT490C 80S/840 PSD VWB PI5 L1200	Yes	-
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	No	-
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	Yes	-
62312500	WT490C 64S/840 PSU WB WA7 L1200	No	-
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	No	-

Order Code	Full Product Name	Embedded	
		Dimmable	control
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	No	-
62317000	WT490C 64S/840 PSD WB WA7 L1200	Yes	-
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	Yes	-
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	Yes	-
62320000	WT490C 64S/840 PSU VWB WA7 L1200	No	-
62321700	WT490C 64S/840 PSD VWB WA7 L1200	Yes	-
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	No	-
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	Yes	-
62324800	WT490C 80S/840 PSU WB WA7 L1200	No	-
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	No	-
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	No	-
62327900	WT490C 80S/840 PSD WB WA7 L1200	Yes	-
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	Yes	-
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	Yes	-
62330900	WT490C 80S/840 PSU VWB WA7 L1200	No	-
62331600	WT490C 80S/840 PSD VWB WA7 L1200	Yes	-
62353800	WT490C 42S/840 PSU WB PI5 L1200	No	-
62354500	WT490C 64S/840 PSU WB PI5 L1200	No	-
62355200	WT490C 80S/840 PSU WB PI5 L1200	No	-
62571600	WT490C 42S/840 PSD VWB PI5 L1200	Yes	-
62752900	WT490C 35S/840 PSU WB PI5 L1200	No	-
62757400	WT490C 64S/840 PSU PCO PI5 L1200	No	-
62760400		No	-
62762800	WT495C 64S/840 PSD WB PI5 L1200	Yes	-
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	No	-
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	No	-
77394300	WT490C 100S/840 PSD WB PI5 L1200	Yes	-
62475700	WT490C 64S/840 PSD WB PI5 L1600	Yes	-
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	No	-
62477100	WT490C 64S/840 PSU WB PI5 L1600	No	-
62478800	WT490C 80S/840 PSU WB PI5 L1600	No	-
62479500	WT490C 80S/840 PSD WB PI5 L1600	Yes	-
62480100	WT490C 80S/840 PSU WB TW3 PI5L1600	No	-
62481800	WT490C 64S/840 PSD WB WA7 L1600	Yes	-
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	No	-
62483200	WT490C 64S/840 PSU WB WA7 L1600	No	-
62484900	WT490C 80S/840 PSU WB WA7 L1600	No	-
62485600	WT490C 80S/840 PSD WB WA7 L1600	Yes	-
62486300	WT490C 80S/840 PSU WB TW3 WA7L1600	No	-
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	No	-
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	No	-
10958200	WT490C 23S/840 PSD WB PI5 L700	Yes	-
62352100	WT490C 23S/840 PSU WB PI5 L700	No	-
62572300	WT490C 64S/840 PSU WB W5 L1200	No	-
62573000	WT490C 80S/840 PSU WB W5 L1200	No	-
62574700	WT490C 64S/840 PSD WB W5 L1200	Yes	-
62575400	WT490C 80S/840 PSD WB W5 L1200	Yes	-

Mechanical and Housing

Pacific LED Gen5

Order Code	Full Product Name	Explosion hazard class
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	-
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	-
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	-
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	-
10990200	WT490C 80S/840 PSD WB PI5 L1800	-
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	-
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	-
10993300	WT490C 80S/840 PSU VWB PI5 L1800	-
10994000	WT490C 80S/840 PSD VWB PI5 L1800	-
10995700	WT490C 100S/840 PSD WB PI5 L1800	-
10996400	WT490C 120S/840 PSD WB PI5 L1800	-
62357600	WT490C 80S/840 PSU WB PI5 L1800	-
62358300	WT490C 100S/840 PSU WB PI5 L1800	-
62359000	WT490C 120S/840 PSU WB PI5 L1800	-
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	-
62758100	WT490C 80S/840 PSU O PI5 L1800	-
62759800	WT490C 80S/840 PSU PCO PI5 L1800	-
62761100	WT495C 80S/840 PSU WB PI5 L1800	-
62763500	WT495C 80S/840 PSD WB PI5 L1800	-
77399800	WT490C 150S/840 PSU WB PI5 L1800	-
62764200	WT492C 64S/840 PSU WB W5 L1200	Zone 2 and 22
62765900	WT492C 80S/840 PSU WB W5 L1800	Zone 2 and 22
62766600	WT492C 64S/840 PSD WB W5 L1200	Zone 2 and 22
62767300	WT492C 80S/840 PSD WB W5 L1800	Zone 2 and 22
73290200	WT490C 42S/830 PSU WB PI5 L1200	-
10959900	WT490C 42S/840 PSD WB PI5 L1200	-
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	-
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	-
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	-
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	-
10964300	WT490C 64S/840 PSU WB TC5 L1200	-
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	-
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	-
10967400	WT490C 64S/840 PSD WB PI5 L1200	-
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	-
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	-
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	-
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	-
10972800	WT490C 64S/840 PSU VWB PI5 L1200	-
10973500	WT490C 64S/840 PSD VWB PI5 L1200	-
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	-
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	-
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	-
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	-
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	-
10979700	WT490C 80S/840 PSD WB PI5 L1200	-
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	-
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	-
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	-
10983400	WT490C 80S/840 PSU VWB PI5 L1200	-
10984100	WT490C 80S/840 PSD VWB PI5 L1200	-

Order Code	Full Product Name	Explosion hazard class
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	-
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	-
62312500	WT490C 64S/840 PSU WB WA7 L1200	-
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	-
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	-
62317000	WT490C 64S/840 PSD WB WA7 L1200	-
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	-
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	-
62320000	WT490C 64S/840 PSU VWB WA7 L1200	-
62321700	WT490C 64S/840 PSD VWB WA7 L1200	-
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	-
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	-
62324800	WT490C 80S/840 PSU WB WA7 L1200	-
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	-
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	-
62327900	WT490C 80S/840 PSD WB WA7 L1200	-
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	-
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	-
62330900	WT490C 80S/840 PSU VWB WA7 L1200	-
62331600	WT490C 80S/840 PSD VWB WA7 L1200	-
62353800	WT490C 42S/840 PSU WB PI5 L1200	-
62354500	WT490C 64S/840 PSU WB PI5 L1200	-
62355200	WT490C 80S/840 PSU WB PI5 L1200	-
62571600	WT490C 42S/840 PSD VWB PI5 L1200	-
62752900	WT490C 35S/840 PSU WB PI5 L1200	-
62757400	WT490C 64S/840 PSU PCO PI5 L1200	-
62760400		-
62762800	WT495C 64S/840 PSD WB PI5 L1200	-
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	-
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	-
77394300	WT490C 100S/840 PSD WB PI5 L1200	-
62475700	WT490C 64S/840 PSD WB PI5 L1600	-
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	-
62477100	WT490C 64S/840 PSU WB PI5 L1600	-
62478800	WT490C 80S/840 PSU WB PI5 L1600	-
62479500	WT490C 80S/840 PSD WB PI5 L1600	-
62480100	WT490C 80S/840 PSU WB TW3 PI5L1600	-
62481800	WT490C 64S/840 PSD WB WA7 L1600	-
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	-
62483200	WT490C 64S/840 PSU WB WA7 L1600	-
62484900	WT490C 80S/840 PSU WB WA7 L1600	-
62485600	WT490C 80S/840 PSD WB WA7 L1600	-
62486300	WT490C 80S/840 PSU WB TW3 WA7L1600	-
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	-
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	-
10958200	WT490C 23S/840 PSD WB PI5 L700	-
62352100	WT490C 23S/840 PSU WB PI5 L700	-
62572300	WT490C 64S/840 PSU WB W5 L1200	-
62573000	WT490C 80S/840 PSU WB W5 L1200	-
62574700	WT490C 64S/840 PSD WB W5 L1200	-
62575400	WT490C 80S/840 PSD WB W5 L1200	-

Emergency Operation

Pacific LED Gen5

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	-	-
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	-	-
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	-	-
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	Emergency lighting 3 hours duration Pro version	3 hour(s)
10990200	WT490C 80S/840 PSD WB PI5 L1800	-	-
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	-	-
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10993300	WT490C 80S/840 PSU VWB PI5 L1800	-	-
10994000	WT490C 80S/840 PSD VWB PI5 L1800	-	-
10995700	WT490C 100S/840 PSD WB PI5 L1800	-	-
10996400	WT490C 120S/840 PSD WB PI5 L1800	-	-
62357600	WT490C 80S/840 PSU WB PI5 L1800	-	-
62358300	WT490C 100S/840 PSU WB PI5 L1800	-	-
62359000	WT490C 120S/840 PSU WB PI5 L1800	-	-
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	-	-
62758100	WT490C 80S/840 PSU O PI5 L1800	-	-
62759800	WT490C 80S/840 PSU PCO PI5 L1800	-	-
62761100	WT495C 80S/840 PSU WB PI5 L1800	-	-
62763500	WT495C 80S/840 PSD WB PI5 L1800	-	-
77399800	WT490C 150S/840 PSU WB PI5 L1800	-	-
62764200	WT492C 64S/840 PSU WB W5 L1200	-	-
62765900	WT492C 80S/840 PSU WB W5 L1800	-	-
62766600	WT492C 64S/840 PSD WB W5 L1200	-	-
62767300	WT492C 80S/840 PSD WB W5 L1800	-	-
73290200	WT490C 42S/830 PSU WB PI5 L1200	-	-
10959900	WT490C 42S/840 PSD WB PI5 L1200	-	-
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	-	-
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	-	-
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	-	-
10964300	WT490C 64S/840 PSU WB TC5 L1200	-	-
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
10967400	WT490C 64S/840 PSD WB PI5 L1200	-	-
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	-	-
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	-	-
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10972800	WT490C 64S/840 PSU VWB PI5 L1200	-	-
10973500	WT490C 64S/840 PSD VWB PI5 L1200	-	-
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	-	-
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	-	-
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	-	-
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	-	-
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
10979700	WT490C 80S/840 PSD WB PI5 L1200	-	-
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	-	-
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	-	-
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	Emergency lighting 3 hours	3 hour(s)

Pacific LED Gen5

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
		duration with DALI interface	
10983400	WT490C 80S/840 PSU VWB PI5 L1200	-	-
10984100	WT490C 80S/840 PSD VWB PI5 L1200	-	-
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	-	-
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	-	-
62312500	WT490C 64S/840 PSU WB WA7 L1200	-	-
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	-	-
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
62317000	WT490C 64S/840 PSD WB WA7 L1200	-	-
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	-	-
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
62320000	WT490C 64S/840 PSU VWB WA7 L1200	-	-
62321700	WT490C 64S/840 PSD VWB WA7 L1200	-	-
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	-	-
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	-	-
62324800	WT490C 80S/840 PSU WB WA7 L1200	-	-
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	-	-
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	Emergency lighting 3 hours duration Pro version	3 hour(s)
62327900	WT490C 80S/840 PSD WB WA7 L1200	-	-
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	-	-
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	Emergency lighting 3 hours	3 hour(s)

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
		duration with DALI interface	
62330900	WT490C 80S/840 PSU VWB WA7 L1200	-	-
62331600	WT490C 80S/840 PSD VWB WA7 L1200	-	-
62353800	WT490C 42S/840 PSU WB PI5 L1200	-	-
62354500	WT490C 64S/840 PSU WB PI5 L1200	-	-
62355200	WT490C 80S/840 PSU WB PI5 L1200	-	-
62571600	WT490C 42S/840 PSD VWB PI5 L1200	-	-
62752900	WT490C 35S/840 PSU WB PI5 L1200	-	-
62757400	WT490C 64S/840 PSU PCO PI5 L1200	-	-
62760400		-	-
62762800	WT495C 64S/840 PSD WB PI5 L1200	-	-
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	-	-
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	-	-
77394300	WT490C 100S/840 PSD WB PI5 L1200	-	-
62475700	WT490C 64S/840 PSD WB PI5 L1600	-	-
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	-	-
62477100	WT490C 64S/840 PSU WB PI5 L1600	-	-
62478800	WT490C 80S/840 PSU WB PI5 L1600	-	-
62479500	WT490C 80S/840 PSD WB PI5 L1600	-	-
62480100	WT490C 80S/840 PSU WB TW3 PI5L1600	-	-
62481800	WT490C 64S/840 PSD WB WA7 L1600	-	-
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	-	-
62483200	WT490C 64S/840 PSU WB WA7 L1600	-	-
62484900	WT490C 80S/840 PSU WB WA7 L1600	-	-
62485600	WT490C 80S/840 PSD WB WA7 L1600	-	-
62486300	WT490C 80S/840 PSU WB TW3 WA7L1600	-	-
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	-	-
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	-	-
10958200	WT490C 23S/840 PSD WB PI5 L700	-	-
62352100	WT490C 23S/840 PSU WB PI5 L700	-	-

Pacific LED Gen5

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
62572300	WT490C 64S/840 PSU WB W5 L1200	-	-
62573000	WT490C 80S/840 PSU WB W5 L1200	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
62574700	WT490C 64S/840 PSD WB W5 L1200	-	-
62575400	WT490C 80S/840 PSD WB W5 L1200	-	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	-25 to +45 °C	1	0.4
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	-25 to +45 °C	1	0.4
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	-25 to +45 °C	1	0.4
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	0 to +30 °C	1	0.4
10990200	WT490C 80S/840 PSD WB PI5 L1800	-25 to +45 °C	1	0.4
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	-25 to +45 °C	1	0.4
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	0 to +30 °C	1	0.4
10993300	WT490C 80S/840 PSU VWB PI5 L1800	-25 to +45 °C	1	0.4
10994000	WT490C 80S/840 PSD VWB PI5 L1800	-25 to +45 °C	1	0.4
10995700	WT490C 100S/840 PSD WB PI5 L1800	-25 to +45 °C	1	0.4
10996400	WT490C 120S/840 PSD WB PI5 L1800	-25 to +45 °C	1	0.4
62357600	WT490C 80S/840 PSU WB PI5 L1800	-25 to +45 °C	1	0.4
62358300	WT490C 100S/840 PSU WB PI5 L1800	-25 to +45 °C	1	0.4
62359000	WT490C 120S/840 PSU WB PI5 L1800	-25 to +45 °C	1	0.4
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	-25 to +45 °C	1	0.4
62758100	WT490C 80S/840 PSU O PI5 L1800	-25 to +45 °C	1	0.4
62759800	WT490C 80S/840 PSU PCO PI5 L1800	-25 to +45 °C	1	0.4
62761100	WT495C 80S/840 PSU WB PI5 L1800	-35 to +60 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
62763500	WT495C 80S/840 PSD WB PI5 L1800	-35 to +60 °C	1	0.4
77399800	WT490C 150S/840 PSU WB PI5 L1800	-25 to +25 °C	-	-
62764200	WT492C 64S/840 PSU WB W5 L1200	-25 to +45 °C	1	0.4
62765900	WT492C 80S/840 PSU WB W5 L1800	-25 to +45 °C	1	0.4
62766600	WT492C 64S/840 PSD WB W5 L1200	-25 to +45 °C	1	0.4
62767300	WT492C 80S/840 PSD WB W5 L1800	-25 to +45 °C	1	0.4
73290200	WT490C 42S/830 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
10959900	WT490C 42S/840 PSD WB PI5 L1200	-25 to +45 °C	1	0.4
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	-25 to +45 °C	1	0.4
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	-25 to +45 °C	1	0.4
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	-25 to +45 °C	1	0.4
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	-25 to +45 °C	1	0.4
10964300	WT490C 64S/840 PSU WB TC5 L1200	-25 to +45 °C	1	0.4
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	0 to +40 °C	1	0.4
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	0 to +40 °C	1	0.4
10967400	WT490C 64S/840 PSD WB PI5 L1200	-25 to +45 °C	1	0.4
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	-25 to +45 °C	1	0.4

Pacific LED Gen5

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	-25 to +45 °C	1	0.4
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	0 to +40 °C	1	0.4
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	0 to +40 °C	1	0.4
10972800	WT490C 64S/840 PSU VWB PI5 L1200	-25 to +45 °C	1	0.4
10973500	WT490C 64S/840 PSD VWB PI5 L1200	-25 to +45 °C	1	0.4
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	-25 to +45 °C	1	0.4
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	-25 to +45 °C	1	0.4
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	-25 to +45 °C	1	0.4
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	-25 to +45 °C	1	0.4
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	0 to +30 °C	1	0.4
10979700	WT490C 80S/840 PSD WB PI5 L1200	-25 to +45 °C	1	0.4
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	-25 to +45 °C	1	0.4
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	-25 to +45 °C	1	0.4
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	0 to +30 °C	1	0.4
10983400	WT490C 80S/840 PSU VWB PI5 L1200	-25 to +45 °C	1	0.4
10984100	WT490C 80S/840 PSD VWB PI5 L1200	-25 to +45 °C	1	0.4
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	-25 to +45 °C	1	0.4
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	-25 to +45 °C	1	0.4
62312500	WT490C 64S/840 PSU WB WA7 L1200	-25 to +45 °C	1	0.4
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	-25 to +45 °C	1	0.4
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	0 to +40 °C	1	0.4
62317000	WT490C 64S/840 PSD WB WA7 L1200	-25 to +45 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	-25 to +45 °C	1	0.4
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	0 to +40 °C	1	0.4
62320000	WT490C 64S/840 PSU VWB WA7 L1200	-25 to +45 °C	1	0.4
62321700	WT490C 64S/840 PSD VWB WA7 L1200	-25 to +45 °C	1	0.4
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	-25 to +45 °C	1	0.4
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	-25 to +45 °C	1	0.4
62324800	WT490C 80S/840 PSU WB WA7 L1200	-25 to +45 °C	1	0.4
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	-25 to +45 °C	1	0.4
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	0 to +30 °C	1	0.4
62327900	WT490C 80S/840 PSD WB WA7 L1200	-25 to +45 °C	1	0.4
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	-25 to +45 °C	1	0.4
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	0 to +30 °C	1	0.4
62330900	WT490C 80S/840 PSU VWB WA7 L1200	-25 to +45 °C	1	0.4
62331600	WT490C 80S/840 PSD VWB WA7 L1200	-25 to +45 °C	1	0.4
62353800	WT490C 42S/840 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
62354500	WT490C 64S/840 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
62355200	WT490C 80S/840 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
62571600	WT490C 42S/840 PSD VWB PI5 L1200	-25 to +45 °C	1	0.4
62752900	WT490C 35S/840 PSU WB PI5 L1200	-25 to +45 °C	1	0.4
62757400	WT490C 64S/840 PSU PCO PI5 L1200	-25 to +45 °C	1	0.4
62760400		-35 to +60 °C	1	0.4
62762800	WT495C 64S/840 PSD WB PI5 L1200	-35 to +60 °C	1	0.4
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	-25 to +45 °C	1	0.4

Pacific LED Gen5

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	-25 to +45 °C	1	0.4
77394300	WT490C 100S/840 PSD WB PI5 L1200	-25 to +25 °C	-	-
62475700	WT490C 64S/840 PSD WB PI5 L1600	-25 to +45 °C	1	0.4
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	-25 to +45 °C	1	0.4
62477100	WT490C 64S/840 PSU WB PI5 L1600	-25 to +45 °C	1	0.4
62478800	WT490C 80S/840 PSU WB PI5 L1600	-25 to +45 °C	1	0.4
62479500	WT490C 80S/840 PSD WB PI5 L1600	-25 to +45 °C	1	0.4
62480100	WT490C 80S/840 PSU WB TW3 PI5L1600	-25 to +45 °C	1	0.4
62481800	WT490C 64S/840 PSD WB WA7 L1600	-25 to +45 °C	1	0.4
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	-25 to +45 °C	1	0.4
62483200	WT490C 64S/840 PSU WB WA7 L1600	-25 to +45 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
62484900	WT490C 80S/840 PSU WB WA7 L1600	-25 to +45 °C	1	0.4
62485600	WT490C 80S/840 PSD WB WA7 L1600	-25 to +45 °C	1	0.4
62486300	WT490C 80S/840 PSU WB TW3 WA7L1600	-25 to +45 °C	1	0.4
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	-25 to +45 °C	1	0.4
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	-25 to +45 °C	1	0.4
10958200	WT490C 23S/840 PSD WB PI5 L700	-25 to +45 °C	1	0.4
62352100	WT490C 23S/840 PSU WB PI5 L700	-25 to +45 °C	1	0.4
62572300	WT490C 64S/840 PSU WB W5 L1200	-25 to +45 °C	1	0.4
62573000	WT490C 80S/840 PSU WB W5 L1200	-25 to +45 °C	1	0.4
62574700	WT490C 64S/840 PSD WB W5 L1200	-25 to +45 °C	1	0.4
62575400	WT490C 80S/840 PSD WB W5 L1200	-25 to +45 °C	1	0.4

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	(0.38, 0.38) SDCM <3
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	(0.38, 0.38) SDCM <3
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	(0.38, 0.38) SDCM <3
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	(0.38, 0.38) SDCM <3
10990200	WT490C 80S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	(0.38, 0.38) SDCM <3
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	(0.38, 0.38) SDCM <3
10993300	WT490C 80S/840 PSU VWB PI5 L1800	(0.38, 0.38) SDCM <3
10994000	WT490C 80S/840 PSD VWB PI5 L1800	(0.38, 0.38) SDCM <3
10995700	WT490C 100S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
10996400	WT490C 120S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
62357600	WT490C 80S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
62358300	WT490C 100S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
62359000	WT490C 120S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	(0.38, 0.38) SDCM <3
62758100	WT490C 80S/840 PSU O PI5 L1800	(0.38, 0.38) SDCM <3
62759800	WT490C 80S/840 PSU PCO PI5 L1800	(0.38, 0.38) SDCM <3
62761100	WT495C 80S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3
62763500	WT495C 80S/840 PSD WB PI5 L1800	(0.38, 0.38) SDCM <3
77399800	WT490C 150S/840 PSU WB PI5 L1800	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
62764200	WT492C 64S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
62765900	WT492C 80S/840 PSU WB W5 L1800	(0.38, 0.38) SDCM <3
62766600	WT492C 64S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3
62767300	WT492C 80S/840 PSD WB W5 L1800	(0.38, 0.38) SDCM <3
73290200	WT490C 42S/830 PSU WB PI5 L1200	(0.43, 0.40) SDCM <3
10959900	WT490C 42S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	(0.38, 0.38) SDCM <3
10964300	WT490C 64S/840 PSU WB TC5 L1200	(0.38, 0.38) SDCM <3
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	(0.38, 0.38) SDCM <3
10967400	WT490C 64S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	(0.38, 0.38) SDCM <3
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	(0.38, 0.38) SDCM <3
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	(0.38, 0.38) SDCM <3
10972800	WT490C 64S/840 PSU VWB PI5 L1200	(0.38, 0.38) SDCM <3
10973500	WT490C 64S/840 PSD VWB PI5 L1200	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	(0.38, 0.38) SDCM <3
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	(0.38, 0.38) SDCM <3
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	(0.38, 0.38) SDCM <3
10979700	WT490C 80S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	(0.38, 0.38) SDCM <3
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	(0.38, 0.38) SDCM <3
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	(0.38, 0.38) SDCM <3
10983400	WT490C 80S/840 PSU VWB PI5 L1200	(0.38, 0.38) SDCM <3
10984100	WT490C 80S/840 PSD VWB PI5 L1200	(0.38, 0.38) SDCM <3
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
62312500	WT490C 64S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
62317000	WT490C 64S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
62320000	WT490C 64S/840 PSU VWB WA7 L1200	(0.38, 0.38) SDCM <3
62321700	WT490C 64S/840 PSD VWB WA7 L1200	(0.38, 0.38) SDCM <3
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	(0.38, 0.38) SDCM <3
62324800	WT490C 80S/840 PSU WB WA7 L1200	(0.38, 0.38) SDCM <3
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	(0.38, 0.38) SDCM <3
62327900	WT490C 80S/840 PSD WB WA7 L1200	(0.38, 0.38) SDCM <3
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	(0.38, 0.38) SDCM <3
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	(0.38, 0.38) SDCM <3
62330900	WT490C 80S/840 PSU VWB WA7 L1200	(0.38, 0.38) SDCM <3
62331600	WT490C 80S/840 PSD VWB WA7 L1200	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
62353800	WT490C 42S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62354500	WT490C 64S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62355200	WT490C 80S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62571600	WT490C 42S/840 PSD VWB PI5 L1200	(0.38, 0.38) SDCM <3
62752900	WT490C 35S/840 PSU WB PI5 L1200	(0.38, 0.38) SDCM <3
62757400	WT490C 64S/840 PSU PCO PI5 L1200	(0.38, 0.38) SDCM <3
62760400		(0.38, 0.38) SDCM <3
62762800	WT495C 64S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	(0.38, 0.38) SDCM <3
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	(0.38, 0.38) SDCM <3
77394300	WT490C 100S/840 PSD WB PI5 L1200	(0.38, 0.38) SDCM <3
62475700	WT490C 64S/840 PSD WB PI5 L1600	(0.38, 0.38) SDCM <3
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	(0.38, 0.38) SDCM <3
62477100	WT490C 64S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
62478800	WT490C 80S/840 PSU WB PI5 L1600	(0.38, 0.38) SDCM <3
62479500	WT490C 80S/840 PSD WB PI5 L1600	(0.38, 0.38) SDCM <3
62480100	WT490C 80S/840 PSU WB TW3 PI5L1600	(0.38, 0.38) SDCM <3
62481800	WT490C 64S/840 PSD WB WA7 L1600	(0.38, 0.38) SDCM <3
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	(0.38, 0.38) SDCM <3
62483200	WT490C 64S/840 PSU WB WA7 L1600	(0.38, 0.38) SDCM <3
62484900	WT490C 80S/840 PSU WB WA7 L1600	(0.38, 0.38) SDCM <3
62485600	WT490C 80S/840 PSD WB WA7 L1600	(0.38, 0.38) SDCM <3
62486300	WT490C 80S/840 PSU WB TW3 WA7L1600	(0.38, 0.38) SDCM <3
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	(0.38, 0.38) SDCM <3
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	(0.38, 0.38) SDCM <3
10958200	WT490C 23S/840 PSD WB PI5 L700	(0.38, 0.38) SDCM <3
62352100	WT490C 23S/840 PSU WB PI5 L700	(0.38, 0.38) SDCM <3
62572300	WT490C 64S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
62573000	WT490C 80S/840 PSU WB W5 L1200	(0.38, 0.38) SDCM <3
62574700	WT490C 64S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3
62575400	WT490C 80S/840 PSD WB W5 L1200	(0.38, 0.38) SDCM <3

Product Data


Order Code	Full Product Name	Product family code
10986500	WT490C 80S/840 PSU NB-HRO PI5L1800	WT490C
10987200	WT490C 80S/840 PSD NB-HRO PI5L1800	WT490C
10988900	WT490C 80S/840 PSU WB TW3 PI5L1800	WT490C
10989600	WT490C 80S/840 PSU WB ELP3 PI5 L1800	WT490C
10990200	WT490C 80S/840 PSD WB PI5 L1800	WT490C
10991900	WT490C 80S/840 PSD WB TW3 PI7L1800	WT490C
10992600	WT490C 80S/840 PSD WB ELD3 PI7 L1800	WT490C
10993300	WT490C 80S/840 PSU VWB PI5 L1800	WT490C
10994000	WT490C 80S/840 PSD VWB PI5 L1800	WT490C
10995700	WT490C 100S/840 PSD WB PI5 L1800	WT490C
10996400	WT490C 120S/840 PSD WB PI5 L1800	WT490C
62357600	WT490C 80S/840 PSU WB PI5 L1800	WT490C
62358300	WT490C 100S/840 PSU WB PI5 L1800	WT490C
62359000	WT490C 120S/840 PSU WB PI5 L1800	WT490C
62578500	WT490C 80S/840 SIA WB IA9 PI5L1800	WT490C
62758100	WT490C 80S/840 PSU O PI5 L1800	WT490C
62759800	WT490C 80S/840 PSU PCO PI5 L1800	WT490C

Order Code	Full Product Name	Product family code
62761100	WT495C 80S/840 PSU WB PI5 L1800	WT495C
62763500	WT495C 80S/840 PSD WB PI5 L1800	WT495C
77399800	WT490C 150S/840 PSU WB PI5 L1800	WT490C
62764200	WT492C 64S/840 PSU WB W5 L1200	WT492C
62765900	WT492C 80S/840 PSU WB W5 L1800	WT492C
62766600	WT492C 64S/840 PSD WB W5 L1200	WT492C
62767300	WT492C 80S/840 PSD WB W5 L1800	WT492C
73290200	WT490C 42S/830 PSU WB PI5 L1200	WT490C
10959900	WT490C 42S/840 PSD WB PI5 L1200	WT490C
10960500	WT490C 64S/840 PSU NB-HRO PI5L1200	WT490C
10961200	WT490C 64S/840 PSD NB-HRO PI5L1200	WT490C
10962900	WT490C 64S/840 PSU WB TW1 PI5L1200	WT490C
10963600	WT490C 64S/840 PSU WB TW3 PI5L1200	WT490C
10964300	WT490C 64S/840 PSU WB TC5 L1200	WT490C
10965000	WT490C 64S/840 PSU WB ELP3 PI5 L1200	WT490C
10966700	WT490C 64S/840 PSU WB ELP3 TW1 PI5 L1200	WT490C
10967400	WT490C 64S/840 PSD WB PI5 L1200	WT490C


Order Code	Full Product Name	Product family code
10968100	WT490C 64S/840 PSD WB TW1 PI5L1200	WT490C
10969800	WT490C 64S/840 PSD WB TW3 PI7L1200	WT490C
10970400	WT490C 64S/840 PSD WB ELD3 PI7 L1200	WT490C
10971100	WT490C 64S/840 PSD WB ELD3 TW1 PI7 L1200	WT490C
10972800	WT490C 64S/840 PSU VWB PI5 L1200	WT490C
10973500	WT490C 64S/840 PSD VWB PI5 L1200	WT490C
10974200	WT490C 80S/840 PSU NB-HRO PI5L1200	WT490C
10975900	WT490C 80S/840 PSD NB-HRO PI5L1200	WT490C
10976600	WT490C 80S/840 PSU WB TW1 PI5L1200	WT490C
10977300	WT490C 80S/840 PSU WB TW3 PI5L1200	WT490C
10978000	WT490C 80S/840 PSU WB ELP3 PI5 L1200	WT490C
10979700	WT490C 80S/840 PSD WB PI5 L1200	WT490C
10980300	WT490C 80S/840 PSD WB TW1 PI5L1200	WT490C
10981000	WT490C 80S/840 PSD WB TW3 PI7L1200	WT490C
10982700	WT490C 80S/840 PSD WB ELD3 PI7 L1200	WT490C
10983400	WT490C 80S/840 PSU VWB PI5 L1200	WT490C
10984100	WT490C 80S/840 PSD VWB PI5 L1200	WT490C
10998800	WT490C 64S/840 PSU NB-HRO WA7L1200	WT490C
10999500	WT490C 64S/840 PSD NB-HRO WA7L1200	WT490C
62312500	WT490C 64S/840 PSU WB WA7 L1200	WT490C
62314900	WT490C 64S/840 PSU WB TW3 WA7L1200	WT490C
62316300	WT490C 64S/840 PSU WB ELP3 WA7 L1200	WT490C
62317000	WT490C 64S/840 PSD WB WA7 L1200	WT490C
62318700	WT490C 64S/840 PSD WB TW3 WA7L1200	WT490C
62319400	WT490C 64S/840 PSD WB ELD3 WA7 L1200	WT490C
62320000	WT490C 64S/840 PSU VWB WA7 L1200	WT490C
62321700	WT490C 64S/840 PSD VWB WA7 L1200	WT490C
62322400	WT490C 80S/840 PSU NB-HRO WA7L1200	WT490C
62323100	WT490C 80S/840 PSD NB-HRO WA7L1200	WT490C
62324800	WT490C 80S/840 PSU WB WA7 L1200	WT490C
62325500	WT490C 80S/840 PSU WB TW3 WA7L1200	WT490C
62326200	WT490C 80S/840 PSU WB ELP3 WA7 L1200	WT490C
62327900	WT490C 80S/840 PSD WB WA7 L1200	WT490C
62328600	WT490C 80S/840 PSD WB TW3 WA7L1200	WT490C

Order Code	Full Product Name	Product family code
62329300	WT490C 80S/840 PSD WB ELD3 WA7 L1200	WT490C
62330900	WT490C 80S/840 PSU VWB WA7 L1200	WT490C
62331600	WT490C 80S/840 PSD VWB WA7 L1200	WT490C
62353800	WT490C 42S/840 PSU WB PI5 L1200	WT490C
62354500	WT490C 64S/840 PSU WB PI5 L1200	WT490C
62355200	WT490C 80S/840 PSU WB PI5 L1200	WT490C
62571600	WT490C 42S/840 PSD VWB PI5 L1200	WT490C
62752900	WT490C 35S/840 PSU WB PI5 L1200	WT490C
62757400	WT490C 64S/840 PSU PCO PI5 L1200	WT490C
62760400		WT495C
62762800	WT495C 64S/840 PSD WB PI5 L1200	WT495C
77193200	WT490C 80S/840 PSU WB TW3x2.5PI5 L1200	WT490C
77200700	WT490C 42S/840 PSU WB TW3x2.5PI5 L1200	WT490C
77394300	WT490C 100S/840 PSD WB PI5 L1200	WT490C
62475700	WT490C 64S/840 PSD WB PI5 L1600	WT490C
62476400	WT490C 64S/840 PSU WB TW3 PI5L1600	WT490C
62477100	WT490C 64S/840 PSU WB PI5 L1600	WT490C
62478800	WT490C 80S/840 PSU WB PI5 L1600	WT490C
62479500	WT490C 80S/840 PSD WB PI5 L1600	WT490C
62480100	WT490C 80S/840 PSU WB TW3 PI5L1600	WT490C
62481800	WT490C 64S/840 PSD WB WA7 L1600	WT490C
62482500	WT490C 64S/840 PSU WB TW3 WA7L1600	WT490C
62483200	WT490C 64S/840 PSU WB WA7 L1600	WT490C
62484900	WT490C 80S/840 PSU WB WA7 L1600	WT490C
62485600	WT490C 80S/840 PSD WB WA7 L1600	WT490C
62486300	WT490C 80S/840 PSU WB TW3 WA7L1600	WT490C
77197000	WT490C 64S/840 PSU WB TW3x2.5PI5 L1600	WT490C
77198700	WT490C 80S/840 PSU WB TW3x2.5PI5 L1600	WT490C
10958200	WT490C 23S/840 PSD WB PI5 L700	WT490C
62352100	WT490C 23S/840 PSU WB PI5 L700	WT490C
62572300	WT490C 64S/840 PSU WB W5 L1200	WT490C
62573000	WT490C 80S/840 PSU WB W5 L1200	WT490C
62574700	WT490C 64S/840 PSD WB W5 L1200	WT490C
62575400	WT490C 80S/840 PSD WB W5 L1200	WT490C


Polar Wide Diagrams



Polar Normal (separate) - WT490CI - 910770229590




Polar Normal (separate) - WT490CI - 910925868249




Polar Normal (separate) - WT490CI - 910925868292


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868698




Polar Normal (separate) - WT490CI - 910925868259




Polar Normal (separate) - WT490CI - 910925868423




Polar Normal (separate) - WT490CI - 910925868702




Polar Normal (separate) - WT490CI - 910925868261




Polar Normal (separate) - WT490CI - 910925868413



Polar Normal (separate) - WT490CI - 910925868697




Polar Normal (separate) - WT490CI - 910925868699




Polar Normal (separate) - WT490CI - 910925868706


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868288




**Polar Normal (separate) - WT490CI -
910925868414**




**Polar Normal (separate) - WT490CI -
910925868513**




Polar Normal (separate) - WT490CI - 910925868705




**Polar Normal (separate) - WT490CI -
910925868419**




**Polar Normal (separate) - WT490CI -
910925868511**



Polar Normal (separate) - WT490CI - 910925868516




Polar Normal (separate) - WT490CI - 910925868701




Polar Normal (separate) - WT490CI - 910925868703


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868422




Polar Normal (separate) - WT490CI - 910925868509




Polar Normal (separate) - WT490CI - 910925867704




Polar Normal (separate) - WT490CI - 910925867723




Polar Normal (separate) - WT490CI - 910925867732




Polar Normal (separate) - WT490CI - 910925867735



Polar Normal (separate) - WT490CI - 910925867706




Polar Normal (separate) - WT490CI - 910925867712




Polar Normal (separate) - WT490CI - 910925867711


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867724




Polar Normal (separate) - WT490CI - 910925867726




Polar Normal (separate) - WT490CI - 910925867727




Polar Normal (separate) - WT490CI - 910925867720




Polar Normal (separate) - WT490CI - 910925867738




Polar Normal (separate) - WT490CI - 910925867713



Polar Normal (separate) - WT490CI - 910925867717




Polar Normal (separate) - WT490CI - 910925867714




Polar Normal (separate) - WT490CI - 910925867715


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867716




Polar Normal (separate) - WT490CI - 910925867739




Polar Normal (separate) - WT490CI - 910925867708




Polar Normal (separate) - WT490CI - 910925867719




Polar Normal (separate) - WT490CI - 910925867725




Polar Normal (separate) - WT490CI - 910925867737



Polar Normal (separate) - WT490CI - 910925867718




Polar Normal (separate) - WT490CI - 910925867734




Polar Normal (separate) - WT490CI - 910925867721


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867729




Polar Normal (separate) - WT490CI - 910925868253




Polar Normal (separate) - WT490CI - 910925868266




Polar Normal (separate) - WT490CI - 910925868287




Polar Normal (separate) - WT490CI - 910925868289




Polar Normal (separate) - WT490CI - 910925868290



Polar Normal (separate) - WT490CI - 910925868256




Polar Normal (separate) - WT490CI - 910925868264




Polar Normal (separate) - WT490CI - 910925868412


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868252




**Polar Normal (separate) - WT490CI -
910925868262**




**Polar Normal (separate) - WT490CI -
910925868265**




**Polar Normal (separate) - WT490CI -
910925868416**




**Polar Normal (separate) - WT490CI -
910925868510**




**Polar Normal (separate) - WT490CI -
910925867703**



Polar Normal (separate) - WT490CI - 910925867705




**Polar Normal (separate) - WT490CI -
910925867707**




Polar Normal (separate) - WT490CI - 910925867709


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925867710




Polar Normal (separate) - WT490CI - 910925867722




Polar Normal (separate) - WT490CI - 910925867728




Polar Normal (separate) - WT490CI - 910925867731




Polar Normal (separate) - WT490CI - 910925867733




Polar Normal (separate) - WT490CI - 910925867736



Polar Normal (separate) - WT490CI - 910925867743




Polar Normal (separate) - WT490CI - 910925867741




Polar Normal (separate) - WT490CI - 910925867740


Polar Wide Diagrams




**Polar Normal (separate) - WT490CI -
910925867744**




**Polar Normal (separate) - WT490CI -
910925868247**




**Polar Normal (separate) - WT490CI -
910925868251**




Polar Normal (separate) - WT490CI - 910925868255




Polar Normal (separate) - WT490CI - 910925868254




Polar Normal (separate) - WT490CI - 910925868258



Polar Normal (separate) - WT490CI - 910925868263




**Polar Normal (separate) - WT490CI -
910925868260**




Polar Normal (separate) - WT490CI - 910925868257


Polar Wide Diagrams




Polar Normal (separate) - WT490CI - 910925868294




Polar Normal (separate) - WT490CI - 910925868293




Polar Normal (separate) - WT490CI - 910925868415




Polar Normal (separate) - WT490CI - 910925868417




Polar Normal (separate) - WT490CI - 910925868418




Polar Normal (separate) - WT490CI - 910925868420



Polar Normal (separate) - WT490CI - 910925868421




Polar Normal (separate) - WT490CI - 910925868512




Polar Normal (separate) - WT490CI - 910925868691


Polar Wide Diagrams




**Polar Normal (separate) - WT490CI -
910925868696**




**Polar Normal (separate) - WT490CI -
910925868704**




Polar Normal (separate) - WT490CI - 910925868707




Polar Normal (separate) - WT490CI - 910925869403




Polar Normal (separate) - WT490CI - 910925869407




Polar Normal (separate) - WT490CI - 910925869408



Polar Normal (separate) - WT490CI - 910925869410



Polar Normal (separate) - WT490CI - 910925869611



**Polar Normal (separate) - WT490CI -
910925869606**

Pacific LED Gen5

