



Safe & Reliable

Essential Smartbright Projector Gen 2

Essential SmartBright Projector ST033T is a value for money product designed for Mass market trade. It is designed to replace halogen and CDM-standard-based projectors for retail and hospitality applications. This track based luminaire supports retailers to let their products stand out, or highlight certain objects. The clean and contemporary design with integrated driver, and choice in 24 or 36 degree beam angle makes the Essential SmartBright Projector relevant to many applications. The choice of 2 colors in White and Black helps the Retailer to choose products best suited to blend into the Store Environment. Compared to its predecessor, it is not only cost effective, but also a more sleek and lighter product design. The product family includes 1M and 2M Track in Black and white color with I and L connector to support various applications.

Benefits

- Reduced operating costs thanks to energy savings and longer lifetime, compared to conventional CDM-standard-based projectors
- Value for Money product for Mass market retail applications
- Clean, simple finish ensures Essential SmartBright Projector blends into many interior designs.

Features

- Unobtrusive design in white or black finish
- 24 and 36 degree beam angle with Lumen output ranging from 800-2500 Lm.
- Energy-efficient: 80 lm/W
- Integrated driver and uniform track adaptor
- color temperature 3000 or 4000 K

Application

- Fashion
- Retail
- Hospitality

Essential Smartbright Projector Gen 2

Versions



Essential SmartBright Projector Gen 2




Essential SmartBright Projector Gen 2






Essential SmartBright Projector 30W




Dimensional drawing



ST033T 30W









ST033T 10W



ST033T 7W

Essential Smartbright Projector Gen 2

Dimensional drawing



Product details



Essential SmartBright Projector Gen 2

Essential Smartbright Projector Gen 2

Operating and Electrical	
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
CE mark	No
ENEC mark	-

General Information

Order Code	Full Product Name	Driver included	Gear	Number of gear units
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	-	-	-
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	-	-	-
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	-	-	-
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	-	-	-
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	-	-	-
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	-	-	-
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	-	-	-
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	-	-	-
911401832287	ST033T G2 LED8/930 10W I MB BK GM	Yes	EB	1 unit
911401832387	ST033T G2 LED8/930 10W I WB BK GM	Yes	EB	1 unit
911401832487	ST033T G2 LED8/940 10W I MB BK GM	Yes	EB	1 unit
911401832587	ST033T G2 LED8/940 10W I WB BK GM	Yes	EB	1 unit
911401834787	ST033T G2 LED8/930 10W I MB BK CN	Yes	EB	1 unit
911401834987	ST033T G2 LED8/940 10W I MB BK CN	Yes	EB	1 unit
911401835187	ST033T G2 LED8/930 10W I WB BK CN	Yes	EB	1 unit
911401835387	ST033T G2 LED8/940 10W I WB BK CN	Yes	EB	1 unit
911401833087	ST033T G2 LED17/930 20W I MB BK GM	Yes	EB	1 unit
911401833187	ST033T G2 LED17/930 20W I WB BK GM	Yes	EB	1 unit
911401833287	ST033T G2 LED17/940 20W I MB BK GM	Yes	EB	1 unit

Order Code	Full Product Name	Driver included	Gear	Number of gear units
911401833387	ST033T G2 LED17/940 20W I WB BK GM	Yes	EB	1 unit
911401835587	ST033T G2 LED17/930 20W I MB BK CN	Yes	EB	1 unit
911401835787	ST033T G2 LED17/940 20W I MB BK CN	Yes	EB	1 unit
911401835987	ST033T G2 LED17/930 20W I WB BK CN	Yes	EB	1 unit
911401836187	ST033T G2 LED17/940 20W I WB BK CN	Yes	EB	1 unit
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	-	-	-
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	-	-	-
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	-	-	-
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	-	-	-
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	-	-	-
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	-	-	-
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	-	-	-
911401832687	ST033T G2 LED17/930 20W I MB WH GM	Yes	EB	1 unit
911401832787	ST033T G2 LED17/930 20W I WB WH GM	Yes	EB	1 unit
911401832887	ST033T G2 LED17/940 20W I MB WH GM	Yes	EB	1 unit
911401832987	ST033T G2 LED17/940 20W I WB WH GM	Yes	EB	1 unit
911401835487	ST033T G2 LED17/930 20W I MB WH CN	Yes	EB	1 unit
911401835687	ST033T G2 LED17/940 20W I MB WH CN	Yes	EB	1 unit
911401835887	ST033T G2 LED17/930 20W I WB WH CN	Yes	EB	1 unit

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Driver included	Number of	
			Gear	gear units
911401836087	ST033T G2 LED17/940 20W I WB WH CN	Yes	EB	1 unit
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	-	-	-
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	-	-	-
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	-	-	-
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	-	-	-
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	-	-	-
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	-	-	-
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	-	-	-
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	-	-	-
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	-	-	-
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	-	-	-
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	-	-	-
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	-	-	-
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	-	-	-
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	-	-	-
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	-	-	-
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	-	-	-
911401831887	ST033T G2 LED8/930 10W I MB WH GM	Yes	EB	1 unit
911401831987	ST033T G2 LED8/930 10W I WB WH GM	Yes	EB	1 unit
911401832087	ST033T G2 LED8/940 10W I MB WH GM	Yes	EB	1 unit
911401832187	ST033T G2 LED8/940 10W I WB WH GM	Yes	EB	1 unit
911401834687	ST033T G2 LED8/930 10W I MB WH CN	Yes	EB	1 unit
911401834887	ST033T G2 LED8/940 10W I MB WH CN	Yes	EB	1 unit
911401835087	ST033T G2 LED8/930 10W I WB WH CN	Yes	EB	1 unit
911401835287	ST033T G2 LED8/940 10W I WB WH CN	Yes	EB	1 unit

Order Code	Full Product Name	Driver included	Number of	
			Gear	gear units
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	-	-	-
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	-	-	-
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	-	-	-
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	-	-	-
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	-	-	-
911401833887	ST033T G2 LED25/930 33W I MB BK GM	Yes	EB	1 unit
911401833987	ST033T G2 LED25/930 33W I WB BK GM	Yes	EB	1 unit
911401834087	ST033T G2 LED25/940 33W I MB BK GM	Yes	EB	1 unit
911401834187	ST033T G2 LED25/940 33W I WB BK GM	Yes	EB	1 unit
911401836387	ST033T G2 LED25/930 33W I MB BK CN	Yes	EB	1 unit
911401836587	ST033T G2 LED25/940 33W I MB BK CN	Yes	EB	1 unit
911401836787	ST033T G2 LED25/930 33W I WB BK CN	Yes	EB	1 unit
911401836987	ST033T G2 LED25/940 33W I WB BK CN	Yes	EB	1 unit
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	-	-	-
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	-	-	-
911401831687	ST033T G2 LED5/930 7W I WB BK GM	Yes	EB	1 unit
911401831787	ST033T G2 LED5/940 7W I WB BK GM	Yes	EB	1 unit
911401834287	ST033T G2 LED5/940 7W I WB BK CN	Yes	EB	1 unit
911401834387	ST033T G2 LED5/930 7W I WB BK CN	Yes	EB	1 unit
911401833487	ST033T G2 LED25/930 33W I MB WH GM	Yes	EB	1 unit
911401833587	ST033T G2 LED25/930 33W I WB WH GM	Yes	EB	1 unit
911401833687	ST033T G2 LED25/940 33W I MB WH GM	Yes	EB	1 unit
911401833787	ST033T G2 LED25/940 33W I WB WH GM	Yes	EB	1 unit
911401836287	ST033T G2 LED25/930 33W I MB WH CN	Yes	EB	1 unit
911401836487	ST033T G2 LED25/940 33W I MB WH CN	Yes	EB	1 unit
911401836687	ST033T G2 LED25/930 33W I WB WH CN	Yes	EB	1 unit

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Driver included	Number of	
			Gear	gear units
911401836887	ST033T G2 LED25/940 33W I WB WH CN	Yes	EB	1 unit
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	-	-	-
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	-	-	-
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	-	-	-
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	-	-	-
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	-	-	-
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	-	-	-
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	-	-	-

Order Code	Full Product Name	Driver included	Number of	
			Gear	gear units
911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	-	-	-
911401831487	ST033T G2 LED5/930 7W I WB WH GM	Yes	EB	1 unit
911401831587	ST033T G2 LED5/940 7W I WB WH GM	Yes	EB	1 unit
911401834487	ST033T G2 LED5/940 7W I WB WH CN	Yes	EB	1 unit
911401834587	ST033T G2 LED5/930 7W I WB WH CN	Yes	EB	1 unit
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	-	-	-
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	-	-	-

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	
								Optic type
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	-	3000 K	>80	85 lm/W	850 lm	-	-
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	-	4000 K	>80	90 lm/W	900 lm	-	-
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	-	3000 K	>80	80 lm/W	1,600 lm	-	-
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	-	4000 K	>80	85 lm/W	1,700 lm	-	-
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	-	3000 K	>80	80 lm/W	2,400 lm	-	-
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	-	4000 K	>80	85 lm/W	2,500 lm	-	-
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	-	3000 K	>80	80 lm/W	2,400 lm	-	-
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	-	4000 K	>80	85 lm/W	2,500 lm	-	-
911401832287	ST033T G2 LED8/930 10W I MB BK GM	24 degree(s)	3000 K	90	80 lm/W	800 lm	1	Beam angle 24°
911401832387	ST033T G2 LED8/930 10W I WB BK GM	36 degree(s)	3000 K	90	80 lm/W	800 lm	1	Beam angle 36°
911401832487	ST033T G2 LED8/940 10W I MB BK GM	24 degree(s)	4000 K	90	85 lm/W	850 lm	1	Beam angle 24°
911401832587	ST033T G2 LED8/940 10W I WB BK GM	36 degree(s)	4000 K	90	85 lm/W	850 lm	1	Beam angle 36°
911401834787	ST033T G2 LED8/930 10W I MB BK CN	24 degree(s)	3000 K	90	80 lm/W	800 lm	1	Beam angle 24°
911401834987	ST033T G2 LED8/940 10W I MB BK CN	24 degree(s)	4000 K	90	85 lm/W	850 lm	1	Beam angle 24°

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
911401835187	ST033T G2 LED8/930 10W I WB BK CN	36 degree(s)	3000 K	90	80 lm/W	800 lm	1	Beam angle 36°
911401835387	ST033T G2 LED8/940 10W I WB BK CN	36 degree(s)	4000 K	90	85 lm/W	850 lm	1	Beam angle 36°
911401833087	ST033T G2 LED17/930 20W I MB BK GM	24 degree(s)	3000 K	90	80 lm/W	1,600 lm	1	Beam angle 24°
911401833187	ST033T G2 LED17/930 20W I WB BK GM	36 degree(s)	3000 K	90	80 lm/W	1,600 lm	1	Beam angle 36°
911401833287	ST033T G2 LED17/940 20W I MB BK GM	24 degree(s)	4000 K	90	85 lm/W	1,700 lm	1	Beam angle 24°
911401833387	ST033T G2 LED17/940 20W I WB BK GM	36 degree(s)	4000 K	90	85 lm/W	1,700 lm	1	Beam angle 36°
911401835587	ST033T G2 LED17/930 20W I MB BK CN	24 degree(s)	3000 K	90	80 lm/W	1,600 lm	1	Beam angle 24°
911401835787	ST033T G2 LED17/940 20W I MB BK CN	24 degree(s)	4000 K	90	85 lm/W	1,700 lm	1	Beam angle 24°
911401835987	ST033T G2 LED17/930 20W I WB BK CN	36 degree(s)	3000 K	90	80 lm/W	1,600 lm	1	Beam angle 36°
911401836187	ST033T G2 LED17/940 20W I WB BK CN	36 degree(s)	4000 K	90	85 lm/W	1,700 lm	1	Beam angle 36°
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	-	6000 K	>80	85 lm/W	1,700 lm	-	-
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	-	3000 K	>80	80 lm/W	1,600 lm	-	-
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	-	4000 K	>80	85 lm/W	1,700 lm	-	-
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	-	3000 K	>80	80 lm/W	1,600 lm	-	-
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	-	4000 K	>80	85 lm/W	1,700 lm	-	-
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	-	3000 K	>80	85 lm/W	600 lm	-	-
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	-	4000 K	>80	85 lm/W	600 lm	-	-
911401832687	ST033T G2 LED17/930 20W I MB WH GM	24 degree(s)	3000 K	90	80 lm/W	1,600 lm	1	Beam angle 24°
911401832787	ST033T G2 LED17/930 20W I WB WH GM	36 degree(s)	3000 K	90	80 lm/W	1,600 lm	1	Beam angle 36°
911401832887	ST033T G2 LED17/940 20W I MB WH GM	24 degree(s)	4000 K	90	85 lm/W	850 lm	1	Beam angle 24°
911401832987	ST033T G2 LED17/940 20W I WB WH GM	36 degree(s)	4000 K	90	85 lm/W	1,700 lm	1	Beam angle 36°
911401835487	ST033T G2 LED17/930 20W I MB WH CN	24 degree(s)	3000 K	90	80 lm/W	1,600 lm	1	Beam angle 24°
911401835687	ST033T G2 LED17/940 20W I MB WH CN	24 degree(s)	4000 K	90	85 lm/W	1,700 lm	1	Beam angle 24°
911401835887	ST033T G2 LED17/930 20W I WB WH CN	36 degree(s)	3000 K	90	80 lm/W	1,600 lm	1	Beam angle 36°
911401836087	ST033T G2 LED17/940 20W I WB WH CN	36 degree(s)	4000 K	90	85 lm/W	1,700 lm	1	Beam angle 36°

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	-	6000 K	>80	85 lm/W	2,500 lm	-	-
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	-	3000 K	>80	80 lm/W	2,400 lm	-	-
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	-	4000 K	>80	83 lm/W	2,500 lm	-	-
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	-	3000 K	>80	80 lm/W	2,400 lm	-	-
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	-	4000 K	>80	83 lm/W	2,500 lm	-	-
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	-	3000 K	>80	85 lm/W	850 lm	-	-
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	-	4000 K	>80	90 lm/W	900 lm	-	-
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	-	3000 K	>80	80 lm/W	1,600 lm	-	-
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	-	4000 K	>80	85 lm/W	1,700 lm	-	-
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	-	3000 K	>80	80 lm/W	560 lm	-	-
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	-	4000 K	>80	80 lm/W	560 lm	-	-
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	-	6000 K	>80	85 lm/W	2,500 lm	-	-
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	-	3000 K	>80	80 lm/W	2,400 lm	-	-
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	-	4000 K	>80	83 lm/W	2,500 lm	-	-
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	-	3000 K	>80	80 lm/W	2,400 lm	-	-
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	-	4000 K	>80	83 lm/W	2,500 lm	-	-
911401831887	ST033T G2 LED8/930 10W I MB WH GM	24 degree(s)	3000 K	90	80 lm/W	800 lm	1	Beam angle 24°
911401831987	ST033T G2 LED8/930 10W I WB WH GM	36 degree(s)	3000 K	90	80 lm/W	800 lm	1	Beam angle 36°
911401832087	ST033T G2 LED8/940 10W I MB WH GM	24 degree(s)	4000 K	90	80 lm/W	800 lm	1	Beam angle 24°
911401832187	ST033T G2 LED8/940 10W I WB WH GM	36 degree(s)	4000 K	90	85 lm/W	850 lm	1	Beam angle 36°
911401834687	ST033T G2 LED8/930 10W I MB WH CN	24 degree(s)	3000 K	90	80 lm/W	800 lm	1	Beam angle 24°
911401834887	ST033T G2 LED8/940 10W I MB WH CN	24 degree(s)	4000 K	90	85 lm/W	850 lm	1	Beam angle 24°
911401835087	ST033T G2 LED8/930 10W I WB WH CN	36 degree(s)	3000 K	90	80 lm/W	800 lm	1	Beam angle 36°
911401835287	ST033T G2 LED8/940 10W I WB WH CN	36 degree(s)	4000 K	90	85 lm/W	850 lm	1	Beam angle 36°
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	-	6000 K	>80	85 lm/W	1,700 lm	-	-

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	-	3000 K	>80	80 lm/W	1,600 lm	-	-
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	-	4000 K	>80	85 lm/W	1,700 lm	-	-
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	-	3000 K	>80	80 lm/W	1,600 lm	-	-
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	-	4000 K	>80	85 lm/W	1,700 lm	-	-
911401833887	ST033T G2 LED25/930 33W I MB BK GM	24 degree(s)	3000 K	90	80 lm/W	2,640 lm	1	Beam angle 24°
911401833987	ST033T G2 LED25/930 33W I WB BK GM	36 degree(s)	3000 K	90	80 lm/W	2,640 lm	1	Beam angle 36°
911401834087	ST033T G2 LED25/940 33W I MB BK GM	24 degree(s)	4000 K	90	85 lm/W	2,805 lm	1	Beam angle 24°
911401834187	ST033T G2 LED25/940 33W I WB BK GM	36 degree(s)	4000 K	90	85 lm/W	2,805 lm	1	Beam angle 36°
911401836387	ST033T G2 LED25/930 33W I MB BK CN	24 degree(s)	3000 K	90	80 lm/W	2,640 lm	1	Beam angle 24°
911401836587	ST033T G2 LED25/940 33W I MB BK CN	24 degree(s)	4000 K	90	85 lm/W	2,805 lm	1	Beam angle 24°
911401836787	ST033T G2 LED25/930 33W I WB BK CN	36 degree(s)	3000 K	90	80 lm/W	2,640 lm	1	Beam angle 36°
911401836987	ST033T G2 LED25/940 33W I WB BK CN	36 degree(s)	4000 K	90	85 lm/W	2,805 lm	1	Beam angle 36°
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	-	3000 K	>80	80 lm/W	2,400 lm	-	-
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	-	4000 K	>80	85 lm/W	2,500 lm	-	-
911401831687	ST033T G2 LED5/930 7W I WB BK GM	36 degree(s)	3000 K	90	85 lm/W	595 lm	1	Beam angle 36°
911401831787	ST033T G2 LED5/940 7W I WB BK GM	36 degree(s)	4000 K	90	90 lm/W	640 lm	1	Beam angle 36°
911401834287	ST033T G2 LED5/940 7W I WB BK CN	36 degree(s)	4000 K	90	90 lm/W	640 lm	1	Beam angle 36°
911401834387	ST033T G2 LED5/930 7W I WB BK CN	36 degree(s)	3000 K	90	85 lm/W	595 lm	1	Beam angle 36°
911401833487	ST033T G2 LED25/930 33W I MB WH GM	24 degree(s)	3000 K	90	80 lm/W	2,640 lm	1	Beam angle 24°
911401833587	ST033T G2 LED25/930 33W I WB WH GM	36 degree(s)	3000 K	90	80 lm/W	2,640 lm	1	Beam angle 36°
911401833687	ST033T G2 LED25/940 33W I MB WH GM	24 degree(s)	4000 K	90	85 lm/W	2,805 lm	1	Beam angle 24°
911401833787	ST033T G2 LED25/940 33W I WB WH GM	36 degree(s)	4000 K	90	85 lm/W	2,805 lm	1	Beam angle 36°
911401836287	ST033T G2 LED25/930 33W I MB WH CN	24 degree(s)	3000 K	90	80 lm/W	2,640 lm	1	Beam angle 24°
911401836487	ST033T G2 LED25/940 33W I MB WH CN	24 degree(s)	4000 K	90	85 lm/W	2,805 lm	1	Beam angle 24°
911401836687	ST033T G2 LED25/930 33W I WB WH CN	36 degree(s)	3000 K	90	80 lm/W	2,640 lm	1	Beam angle 36°

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources	Optic type
911401836887	STO33T G2 LED25/940 33W I WB WH CN	36 degree(s)	4000 K	90	85 lm/W	2,805 lm	1	Beam angle 36°
911401857182	STO33T LED8/830 10W 220-240V I MB WH CN	-	3000 K	>80	80 lm/W	800 lm	-	-
911401857382	STO33T LED8/840 10W 220-240V I MB WH CN	-	4000 K	>80	85 lm/W	850 lm	-	-
911401857582	STO33T LED8/830 10W 220-240V I WB WH CN	-	3000 K	>80	80 lm/W	800 lm	-	-
911401857782	STO33T LED8/840 10W 220-240V I WB WH CN	-	4000 K	>80	85 lm/W	850 lm	-	-
911401857282	STO33T LED8/830 10W 220-240V I MB BK CN	-	3000 K	>80	80 lm/W	800 lm	-	-
911401857482	STO33T LED8/840 10W 220-240V I MB BK CN	-	4000 K	>80	85 lm/W	850 lm	-	-
911401857682	STO33T LED8/830 10W 220-240V I WB BK CN	-	3000 K	>80	80 lm/W	800 lm	-	-
911401857882	STO33T LED8/840 10W 220-240V I WB BK CN	-	4000 K	>80	85 lm/W	850 lm	-	-
911401831487	STO33T G2 LED5/930 7W I WB WH GM	36 degree(s)	3000 K	90	85 lm/W	595 lm	1	Beam angle 36°
911401831587	STO33T G2 LED5/940 7W I WB WH GM	36 degree(s)	4000 K	90	90 lm/W	640 lm	1	Beam angle 36°
911401834487	STO33T G2 LED5/940 7W I WB WH CN	36 degree(s)	4000 K	90	90 lm/W	640 lm	1	Beam angle 36°
911401834587	STO33T G2 LED5/930 7W I WB WH CN	36 degree(s)	3000 K	90	85 lm/W	595 lm	1	Beam angle 36°
911401826984	STO33T LED25/830 30W 110-240V I WB BK KC	-	3000 K	>80	80 lm/W	2,400 lm	-	-
911401827084	STO33T LED25/840 30W 110-240V I WB BK KC	-	4000 K	>80	85 lm/W	2,500 lm	-	-

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401882084	STO33T LED9/830 10W 110-240V I MB BK HK	Safety class II	110 to 240 V	10 W	-
911401882184	STO33T LED9/840 10W 110-240V I MB BK HK	Safety class II	110 to 240 V	10 W	-
911401882484	STO33T LED17/830 20W 110-240V I MB BK HK	Safety class II	110 to 240 V	20 W	-

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401882584	STO33T LED17/840 20W 110-240V I MB BK HK	Safety class II	110 to 240 V	20 W	-
911401882684	STO33T LED25/830 30W 110-240V I MB WH HK	Safety class II	110 to 240 V	30 W	-
911401882784	STO33T LED25/840 30W 110-240V I MB WH HK	Safety class II	110 to 240 V	30 W	-

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	Safety class II	110 to 240 V	30 W	-
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	Safety class II	110 to 240 V	30 W	-
911401832287	ST033T G2 LED8/930 10W I MB BK GM	Safety class I	220-240 V	10 W	No
911401832387	ST033T G2 LED8/930 10W I WB BK GM	Safety class I	220-240 V	10 W	No
911401832487	ST033T G2 LED8/940 10W I MB BK GM	Safety class I	220-240 V	10 W	No
911401832587	ST033T G2 LED8/940 10W I WB BK GM	Safety class I	220-240 V	10 W	No
911401834787	ST033T G2 LED8/930 10W I MB BK CN	Safety class I	220-240 V	10 W	No
911401834987	ST033T G2 LED8/940 10W I MB BK CN	Safety class I	220-240 V	10 W	No
911401835187	ST033T G2 LED8/930 10W I WB BK CN	Safety class I	220-240 V	10 W	No
911401835387	ST033T G2 LED8/940 10W I WB BK CN	Safety class I	220-240 V	10 W	No
911401833087	ST033T G2 LED17/930 20W I MB BK GM	Safety class I	220-240 V	20 W	No
911401833187	ST033T G2 LED17/930 20W I WB BK GM	Safety class I	220-240 V	20 W	No
911401833287	ST033T G2 LED17/940 20W I MB BK GM	Safety class I	220-240 V	20 W	No
911401833387	ST033T G2 LED17/940 20W I WB BK GM	Safety class I	220-240 V	20 W	No
911401835587	ST033T G2 LED17/930 20W I MB BK CN	Safety class I	220-240 V	20 W	No

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401835787	ST033T G2 LED17/940 20W I MB BK CN	Safety class I	220-240 V	20 W	No
911401835987	ST033T G2 LED17/930 20W I WB BK CN	Safety class I	220-240 V	20 W	No
911401836187	ST033T G2 LED17/940 20W I WB BK CN	Safety class I	220-240 V	20 W	No
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	Safety class I	220 to 240 V	20 W	-
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	Safety class I	220 to 240 V	20 W	-
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	Safety class I	220 to 240 V	20 W	-
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	Safety class I	220 to 240 V	20 W	-
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	Safety class I	220 to 240 V	20 W	-
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	Safety class II	110 to 240 V	7 W	-
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	Safety class II	110 to 240 V	7 W	-
911401832687	ST033T G2 LED17/930 20W I MB WH GM	Safety class I	220-240 V	20 W	No
911401832787	ST033T G2 LED17/930 20W I WB WH GM	Safety class I	220-240 V	20 W	No
911401832887	ST033T G2 LED17/940 20W I MB WH GM	Safety class I	220-240 V	20 W	No
911401832987	ST033T G2 LED17/940 20W I WB WH GM	Safety class I	220-240 V	20 W	No

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401835487	ST033T G2 LED17/930 20W I I MB WH CN	Safety class	220-240 V	20 W	No
911401835687	ST033T G2 LED17/940 20W I I MB WH CN	Safety class	220-240 V	20 W	No
911401835887	ST033T G2 LED17/930 20W I I WB WH CN	Safety class	220-240 V	20 W	No
911401836087	ST033T G2 LED17/940 20W I I WB WH CN	Safety class	220-240 V	20 W	No
911401805184	ST033T LED25/860 30W I 220-240V I MB BK CN	Safety class	220 to 240 V	30 W	-
911401858882	ST033T LED25/830 30W I 220-240V I MB BK CN	Safety class	220 to 240 V	30 W	-
911401859082	ST033T LED25/840 30W I 220-240V I MB BK CN	Safety class	220 to 240 V	30 W	-
911401859282	ST033T LED25/830 30W I 220-240V I WB BK CN	Safety class	220 to 240 V	30 W	-
911401859482	ST033T LED25/840 30W I 220-240V I WB BK CN	Safety class	220 to 240 V	30 W	-
911401881884	ST033T LED9/830 10W II 110-240V I MB WH HK	Safety class	110 to 240 V	10 W	-
911401881984	ST033T LED9/840 10W II 110-240V I MB WH HK	Safety class	110 to 240 V	10 W	-
911401882284	ST033T LED17/830 20W II 110-240V I MB WH HK	Safety class	110 to 240 V	20 W	-
911401882384	ST033T LED17/840 20W II 110-240V I MB WH HK	Safety class	110 to 240 V	20 W	-

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	Safety class II	110 to 240 V	7 W	-
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	Safety class II	110 to 240 V	7 W	-
911401805284	ST033T LED25/860 30W I 220-240V I MB WH CN	Safety class	220 to 240 V	30 W	-
911401858782	ST033T LED25/830 30W I 220-240V I MB WH CN	Safety class	220 to 240 V	30 W	-
911401858982	ST033T LED25/840 30W I 220-240V I MB WH CN	Safety class	220 to 240 V	30 W	-
911401859182	ST033T LED25/830 30W I 220-240V I WB WH CN	Safety class	220 to 240 V	30 W	-
911401859382	ST033T LED25/840 30W I 220-240V I WB WH CN	Safety class	220 to 240 V	30 W	-
911401831887	ST033T G2 LED8/930 10W I I MB WH GM	Safety class	220-240 V	10 W	No
911401831987	ST033T G2 LED8/930 10W I I WB WH GM	Safety class	220-240 V	10 W	No
911401832087	ST033T G2 LED8/940 10W I I MB WH GM	Safety class	220-240 V	10 W	No
911401832187	ST033T G2 LED8/940 10W I I WB WH GM	Safety class	220-240 V	10 W	No
911401834687	ST033T G2 LED8/930 10W I I MB WH CN	Safety class	220-240 V	10 W	No
911401834887	ST033T G2 LED8/940 10W I I MB WH CN	Safety class	220-240 V	10 W	No
911401835087	ST033T G2 LED8/930 10W I I WB WH CN	Safety class	220-240 V	10 W	No

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401835287	ST033T G2 LED8/940 10W I WB WH CN	Safety class I	220-240 V	10 W	No
911401805484	ST033T LED17/860 20W I 220-240V I MB WH CN	Safety class I	220 to 240 V	20 W	-
911401857982	ST033T LED17/830 20W I 220-240V I MB WH CN	Safety class I	220 to 240 V	20 W	-
911401858182	ST033T LED17/840 20W I 220-240V I MB WH CN	Safety class I	220 to 240 V	20 W	-
911401858382	ST033T LED17/830 20W I 220-240V I WB WH CN	Safety class I	220 to 240 V	20 W	-
911401858582	ST033T LED17/840 20W I 220-240V I WB WH CN	Safety class I	220 to 240 V	20 W	-
911401833887	ST033T G2 LED25/930 33W I I MB BK GM	Safety class I	220-240 V	33 W	No
911401833987	ST033T G2 LED25/930 33W I I WB BK GM	Safety class I	220-240 V	33 W	No
911401834087	ST033T G2 LED25/940 33W I I MB BK GM	Safety class I	220-240 V	33 W	No
911401834187	ST033T G2 LED25/940 33W I I WB BK GM	Safety class I	220-240 V	33 W	No
911401836387	ST033T G2 LED25/930 33W I I MB BK CN	Safety class I	220-240 V	33 W	No
911401836587	ST033T G2 LED25/940 33W I I MB BK CN	Safety class I	220-240 V	33 W	No
911401836787	ST033T G2 LED25/930 33W I I WB BK CN	Safety class I	220-240 V	33 W	No
911401836987	ST033T G2 LED25/940 33W I I WB BK CN	Safety class I	220-240 V	33 W	No
911401826784	ST033T LED25/830 30W II	Safety class II	110 to 240 V	30 W	-

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401826884	ST033T LED25/840 30W II 110-240V I WB WH KC	Safety class II	110 to 240 V	30 W	-
911401831687	ST033T G2 LED5/930 7W I WB BK GM	Safety class I	220-240 V	7 W	No
911401831787	ST033T G2 LED5/940 7W I WB BK GM	Safety class I	220-240 V	7 W	No
911401834287	ST033T G2 LED5/940 7W I WB BK CN	Safety class I	220-240 V	7 W	No
911401834387	ST033T G2 LED5/930 7W I WB BK CN	Safety class I	220-240 V	7 W	No
911401833487	ST033T G2 LED25/930 33W I I MB WH GM	Safety class I	220-240 V	33 W	No
911401833587	ST033T G2 LED25/930 33W I I WB WH GM	Safety class I	220-240 V	33 W	No
911401833687	ST033T G2 LED25/940 33W I I MB WH GM	Safety class I	220-240 V	33 W	No
911401833787	ST033T G2 LED25/940 33W I I WB WH GM	Safety class I	220-240 V	33 W	No
911401836287	ST033T G2 LED25/930 33W I I MB WH CN	Safety class I	220-240 V	33 W	No
911401836487	ST033T G2 LED25/940 33W I I MB WH CN	Safety class I	220-240 V	33 W	No
911401836687	ST033T G2 LED25/930 33W I I WB WH CN	Safety class I	220-240 V	33 W	No
911401836887	ST033T G2 LED25/940 33W I I WB WH CN	Safety class I	220-240 V	33 W	No
911401857182	ST033T LED8/830 10W I 220-240V I MB WH CN	Safety class I	220 to 240 V	10 W	-
911401857382	ST033T LED8/840 10W I	Safety class I	220 to 240 V	10 W	-

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401857582	220-240V I MB WH CN				
	ST033T	Safety class	220 to 240 V	10 W	-
	LED8/830 10W	I	V		
911401857782	220-240V I WB WH CN				
	ST033T	Safety class	220 to 240 V	10 W	-
	LED8/840 10W	I	V		
911401857282	220-240V I MB BK CN				
	ST033T	Safety class	220 to 240 V	10 W	-
	LED8/830 10W	I	V		
911401857482	220-240V I MB BK CN				
	ST033T	Safety class	220 to 240 V	10 W	-
	LED8/840 10W	I	V		
911401857682	220-240V I WB BK CN				
	ST033T	Safety class	220 to 240 V	10 W	-
	LED8/830 10W	I	V		
911401857882	220-240V I WB BK CN				
	ST033T	Safety class	220 to 240 V	10 W	-
	LED8/840 10W	I	V		

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	No	-
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	No	-
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	No	-
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	No	-
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	No	-
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	No	-
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	No	-
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	No	-
911401832287	ST033T G2 LED8/930 10W I MB BK GM	-	Not applicable
911401832387	ST033T G2 LED8/930 10W I WB BK GM	-	Not applicable

Order Code	Full Product Name	Protection class IEC	Input Voltage	Power Consumption	Suitable for random switching
911401831487	ST033T G2 LED5/930 7W I WB WH GM	Safety class I	220-240 V	7 W	No
911401831587	ST033T G2 LED5/940 7W I WB WH GM	Safety class I	220-240 V	7 W	No
911401834487	ST033T G2 LED5/940 7W I WB WH CN	Safety class I	220-240 V	7 W	No
911401834587	ST033T G2 LED5/930 7W I WB WH CN	Safety class I	220-240 V	7 W	No
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	Safety class II	110 to 240 V	30 W	-
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	Safety class II	110 to 240 V	30 W	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401832487	ST033T G2 LED8/940 10W I MB BK GM	-	Not applicable
911401832587	ST033T G2 LED8/940 10W I WB BK GM	-	Not applicable
911401834787	ST033T G2 LED8/930 10W I MB BK CN	-	Not applicable
911401834987	ST033T G2 LED8/940 10W I MB BK CN	-	Not applicable
911401835187	ST033T G2 LED8/930 10W I WB BK CN	-	Not applicable
911401835387	ST033T G2 LED8/940 10W I WB BK CN	-	Not applicable
911401833087	ST033T G2 LED17/930 20W I MB BK GM	-	Not applicable
911401833187	ST033T G2 LED17/930 20W I WB BK GM	-	Not applicable
911401833287	ST033T G2 LED17/940 20W I MB BK GM	-	Not applicable
911401833387	ST033T G2 LED17/940 20W I WB BK GM	-	Not applicable
911401835587	ST033T G2 LED17/930 20W I MB BK CN	-	Not applicable
911401835787	ST033T G2 LED17/940 20W I MB BK CN	-	Not applicable
911401835987	ST033T G2 LED17/930 20W I WB BK CN	-	Not applicable
911401836187	ST033T G2 LED17/940 20W I WB BK CN	-	Not applicable
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	No	-
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	No	-

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	No	-
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	No	-
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	No	-
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	No	-
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	No	-
911401832687	ST033T G2 LED17/930 20W I MB WH GM	-	Not applicable
911401832787	ST033T G2 LED17/930 20W I WB WH GM	-	Not applicable
911401832887	ST033T G2 LED17/940 20W I MB WH GM	-	Not applicable
911401832987	ST033T G2 LED17/940 20W I WB WH GM	-	Not applicable
911401835487	ST033T G2 LED17/930 20W I MB WH CN	-	Not applicable
911401835687	ST033T G2 LED17/940 20W I MB WH CN	-	Not applicable
911401835887	ST033T G2 LED17/930 20W I WB WH CN	-	Not applicable
911401836087	ST033T G2 LED17/940 20W I WB WH CN	-	Not applicable
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	No	-
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	No	-
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	No	-
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	No	-
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	No	-
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	No	-
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	No	-
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	No	-
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	No	-
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	No	-
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	No	-
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	No	-
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	No	-
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	No	-
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	No	-
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	No	-
911401831887	ST033T G2 LED8/930 10W I MB WH GM	-	Not applicable

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401831987	ST033T G2 LED8/930 10W I WB WH GM	-	Not applicable
911401832087	ST033T G2 LED8/940 10W I MB WH GM	-	Not applicable
911401832187	ST033T G2 LED8/940 10W I WB WH GM	-	Not applicable
911401834687	ST033T G2 LED8/930 10W I MB WH CN	-	Not applicable
911401834887	ST033T G2 LED8/940 10W I MB WH CN	-	Not applicable
911401835087	ST033T G2 LED8/930 10W I WB WH CN	-	Not applicable
911401835287	ST033T G2 LED8/940 10W I WB WH CN	-	Not applicable
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	No	-
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	No	-
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	No	-
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	No	-
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	No	-
911401833887	ST033T G2 LED25/930 33W I MB BK GM	-	Not applicable
911401833987	ST033T G2 LED25/930 33W I WB BK GM	-	Not applicable
911401834087	ST033T G2 LED25/940 33W I MB BK GM	-	Not applicable
911401834187	ST033T G2 LED25/940 33W I WB BK GM	-	Not applicable
911401836387	ST033T G2 LED25/930 33W I MB BK CN	-	Not applicable
911401836587	ST033T G2 LED25/940 33W I MB BK CN	-	Not applicable
911401836787	ST033T G2 LED25/930 33W I WB BK CN	-	Not applicable
911401836987	ST033T G2 LED25/940 33W I WB BK CN	-	Not applicable
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	No	-
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	No	-
911401831687	ST033T G2 LED5/930 7W I WB BK GM	-	Not applicable
911401831787	ST033T G2 LED5/940 7W I WB BK GM	-	Not applicable
911401834287	ST033T G2 LED5/940 7W I WB BK CN	-	Not applicable
911401834387	ST033T G2 LED5/930 7W I WB BK CN	-	Not applicable
911401833487	ST033T G2 LED25/930 33W I MB WH GM	-	Not applicable
911401833587	ST033T G2 LED25/930 33W I WB WH GM	-	Not applicable
911401833687	ST033T G2 LED25/940 33W I MB WH GM	-	Not applicable
911401833787	ST033T G2 LED25/940 33W I WB WH GM	-	Not applicable
911401836287	ST033T G2 LED25/930 33W I MB WH CN	-	Not applicable
911401836487	ST033T G2 LED25/940 33W I MB WH CN	-	Not applicable
911401836687	ST033T G2 LED25/930 33W I WB WH CN	-	Not applicable
911401836887	ST033T G2 LED25/940 33W I WB WH CN	-	Not applicable
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	No	-
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	No	-
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	No	-
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	No	-
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	No	-

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	No	-
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	No	-
911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	No	-
911401831487	ST033T G2 LED5/930 7W I WB WH GM	-	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing Color
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	Collimator with focus angle 24°	Black
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	Collimator with focus angle 24°	Black
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	Collimator with focus angle 24°	Black
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	Collimator with focus angle 24°	Black
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	Collimator with focus angle 24°	White
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	Collimator with focus angle 24°	White
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	Collimator with focus angle 24°	Black
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	Collimator with focus angle 24°	Black
911401832287	ST033T G2 LED8/930 10W I MB BK GM	Polycarbonate	Black
911401832387	ST033T G2 LED8/930 10W I WB BK GM	Polycarbonate	Black
911401832487	ST033T G2 LED8/940 10W I MB BK GM	Polycarbonate	Black
911401832587	ST033T G2 LED8/940 10W I WB BK GM	Polycarbonate	Black
911401834787	ST033T G2 LED8/930 10W I MB BK CN	Polycarbonate	Black
911401834987	ST033T G2 LED8/940 10W I MB BK CN	Polycarbonate	Black
911401835187	ST033T G2 LED8/930 10W I WB BK CN	Polycarbonate	Black
911401835387	ST033T G2 LED8/940 10W I WB BK CN	Polycarbonate	Black
911401833087	ST033T G2 LED17/930 20W I MB BK GM	Polycarbonate	Black
911401833187	ST033T G2 LED17/930 20W I WB BK GM	Polycarbonate	Black
911401833287	ST033T G2 LED17/940 20W I MB BK GM	Polycarbonate	Black
911401833387	ST033T G2 LED17/940 20W I WB BK GM	Polycarbonate	Black

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
911401831587	ST033T G2 LED5/940 7W I WB WH GM	-	Not applicable
911401834487	ST033T G2 LED5/940 7W I WB WH CN	-	Not applicable
911401834587	ST033T G2 LED5/930 7W I WB WH CN	-	Not applicable
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	No	-
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	No	-

Order Code	Full Product Name	Optical cover type	Housing Color
911401835587	ST033T G2 LED17/930 20W I MB BK CN	Polycarbonate	Black
911401835787	ST033T G2 LED17/940 20W I MB BK CN	Polycarbonate	Black
911401835987	ST033T G2 LED17/930 20W I WB BK CN	Polycarbonate	Black
911401836187	ST033T G2 LED17/940 20W I WB BK CN	Polycarbonate	Black
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	Fashion proof optic beam angle 24°	Aluminum and black
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	Fashion proof optic beam angle 24°	Aluminum and black
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	Fashion proof optic beam angle 24°	Aluminum and black
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	Fashion proof optic beam angle 36°	Aluminum and black
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	Fashion proof optic beam angle 36°	Aluminum and black
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	Collimator with focus angle 30°	White
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	Collimator with focus angle 30°	White
911401832687	ST033T G2 LED17/930 20W I MB WH GM	Polycarbonate	White RAL 9003
911401832787	ST033T G2 LED17/930 20W I WB WH GM	Polycarbonate	White RAL 9003
911401832887	ST033T G2 LED17/940 20W I MB WH GM	Polycarbonate	White RAL 9003
911401832987	ST033T G2 LED17/940 20W I WB WH GM	Polycarbonate	White RAL 9003
911401835487	ST033T G2 LED17/930 20W I MB WH CN	Polycarbonate	White RAL 9003
911401835687	ST033T G2 LED17/940 20W I MB WH CN	Polycarbonate	White RAL 9003
911401835887	ST033T G2 LED17/930 20W I WB WH CN	Polycarbonate	White RAL 9003
911401836087	ST033T G2 LED17/940 20W I WB WH CN	Polycarbonate	White RAL 9003
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	Fashion proof optic beam angle 24°	Aluminum and black

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Optical cover type	Housing Color
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	Fashion proof optic beam angle 24°	Aluminum and black
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	Fashion proof optic beam angle 24°	Aluminum and black
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	Fashion proof optic beam angle 36°	Aluminum and black
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	Fashion proof optic beam angle 36°	Aluminum and black
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	Collimator with focus angle 24°	White
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	Collimator with focus angle 24°	White
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	Collimator with focus angle 24°	White
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	Collimator with focus angle 24°	White
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	Collimator with focus angle 30°	Black
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	Collimator with focus angle 30°	Black
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	Fashion proof optic beam angle 24°	Aluminum and white
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	Fashion proof optic beam angle 24°	Aluminum and white
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	Fashion proof optic beam angle 24°	Aluminum and white
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	Fashion proof optic beam angle 36°	Aluminum and white
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	Fashion proof optic beam angle 36°	Aluminum and white
911401831887	ST033T G2 LED8/930 10W I MB WH GM	Polycarbonate	White RAL 9003
911401831987	ST033T G2 LED8/930 10W I WB WH GM	Polycarbonate	White RAL 9003
911401832087	ST033T G2 LED8/940 10W I MB WH GM	Polycarbonate	White RAL 9003
911401832187	ST033T G2 LED8/940 10W I WB WH GM	Polycarbonate	White RAL 9003
911401834687	ST033T G2 LED8/930 10W I MB WH CN	Polycarbonate	White RAL 9003
911401834887	ST033T G2 LED8/940 10W I MB WH CN	Polycarbonate	White RAL 9003
911401835087	ST033T G2 LED8/930 10W I WB WH CN	Polycarbonate	White RAL 9003
911401835287	ST033T G2 LED8/940 10W I WB WH CN	Polycarbonate	White RAL 9003
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	Fashion proof optic beam angle 24°	Aluminum and white
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	Fashion proof optic beam angle 24°	Aluminum and white
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	Fashion proof optic beam angle 24°	Aluminum and white

Order Code	Full Product Name	Optical cover type	Housing Color
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	Fashion proof optic beam angle 36°	Aluminum and white
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	Fashion proof optic beam angle 36°	Aluminum and white
911401833887	ST033T G2 LED25/930 33W I MB BK GM	Polycarbonate	Black
911401833987	ST033T G2 LED25/930 33W I WB BK GM	Polycarbonate	Black
911401834087	ST033T G2 LED25/940 33W I MB BK GM	Polycarbonate	Black
911401834187	ST033T G2 LED25/940 33W I WB BK GM	Polycarbonate	Black
911401836387	ST033T G2 LED25/930 33W I MB BK CN	Polycarbonate	Black
911401836587	ST033T G2 LED25/940 33W I MB BK CN	Polycarbonate	Black
911401836787	ST033T G2 LED25/930 33W I WB BK CN	Polycarbonate	Black
911401836987	ST033T G2 LED25/940 33W I WB BK CN	Polycarbonate	Black
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	Polycarbonate micro lens optic	White
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	Polycarbonate micro lens optic	White
911401831687	ST033T G2 LED5/930 7W I WB BK GM	Polycarbonate	Black
911401831787	ST033T G2 LED5/940 7W I WB BK GM	Polycarbonate	Black
911401834287	ST033T G2 LED5/940 7W I WB BK CN	Polycarbonate	Black
911401834387	ST033T G2 LED5/930 7W I WB BK CN	Polycarbonate	Black
911401833487	ST033T G2 LED25/930 33W I MB WH GM	Polycarbonate	White RAL 9003
911401833587	ST033T G2 LED25/930 33W I WB WH GM	Polycarbonate	White RAL 9003
911401833687	ST033T G2 LED25/940 33W I MB WH GM	Polycarbonate	White RAL 9003
911401833787	ST033T G2 LED25/940 33W I WB WH GM	Polycarbonate	White RAL 9003
911401836287	ST033T G2 LED25/930 33W I MB WH CN	Polycarbonate	White RAL 9003
911401836487	ST033T G2 LED25/940 33W I MB WH CN	Polycarbonate	White RAL 9003
911401836687	ST033T G2 LED25/930 33W I WB WH CN	Polycarbonate	White RAL 9003
911401836887	ST033T G2 LED25/940 33W I WB WH CN	Polycarbonate	White RAL 9003
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	Fashion proof optic beam angle 24°	Aluminum and white
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	Fashion proof optic beam angle 24°	Aluminum and white

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Optical cover type	Housing Color
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	Fashion proof optic beam angle 36°	Aluminum and white
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	Fashion proof optic beam angle 36°	Aluminum and white
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	Fashion proof optic beam angle 24°	Aluminum and black
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	Fashion proof optic beam angle 24°	Aluminum and black
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	Fashion proof optic beam angle 36°	Aluminum and black
911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	Fashion proof optic beam angle 36°	Aluminum and black

Order Code	Full Product Name	Optical cover type	Housing Color
911401831487	ST033T G2 LED5/930 7W I WB WH GM	Polycarbonate	White RAL 9003
911401831587	ST033T G2 LED5/940 7W I WB WH GM	Polycarbonate	White RAL 9003
911401834487	ST033T G2 LED5/940 7W I WB WH CN	Polycarbonate	White RAL 9003
911401834587	ST033T G2 LED5/930 7W I WB WH CN	Polycarbonate	White RAL 9003
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	Polycarbonate micro lens optic	Black
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	Polycarbonate micro lens optic	Black

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	-20 to +45 °C	For mounting on normally flammable surfaces	-

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
911401832287	ST033T G2 LED8/930 10W I MB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401832387	ST033T G2 LED8/930 10W I WB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401832487	ST033T G2 LED8/940 10W I MB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401832587	ST033T G2 LED8/940 10W I WB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834787	ST033T G2 LED8/930 10W I MB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834987	ST033T G2 LED8/940 10W I MB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835187	ST033T G2 LED8/930 10W I WB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835387	ST033T G2 LED8/940 10W I WB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
911401833087	ST033T G2 LED17/930 20W I MB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401833187	ST033T G2 LED17/930 20W I WB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401833287	ST033T G2 LED17/940 20W I MB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401833387	ST033T G2 LED17/940 20W I WB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835587	ST033T G2 LED17/930 20W I MB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835787	ST033T G2 LED17/940 20W I MB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835987	ST033T G2 LED17/930 20W I WB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836187	ST033T G2 LED17/940 20W I WB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	-20 to +45 °C	-	-
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	-20 to +45 °C	-	-
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	-20 to +45 °C	-	-
911401858682	ST033T LED17/840 20W	-20 to +45 °C	-	-

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
	220-240V I WB BK CN			
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401832687	ST033T G2 LED17/930 20W I MB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401832787	ST033T G2 LED17/930 20W I WB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401832887	ST033T G2 LED17/940 20W I MB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401832987	ST033T G2 LED17/940 20W I WB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835487	ST033T G2 LED17/930 20W I MB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835687	ST033T G2 LED17/940 20W I MB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835887	ST033T G2 LED17/930 20W I WB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836087	ST033T G2 LED17/940 20W I WB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	-20 to +45 °C	-	-

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	-20 to +45 °C	-	-
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	-20 to +45 °C	-	-
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	-20 to +45 °C	-	-
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	-20 to +45 °C	-	-
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	-20 to +45 °C	-	-
911401859182	ST033T LED25/830 30W	-20 to +45 °C	-	-

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
	220-240V I WB WH CN			
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	-20 to +45 °C	-	-
911401831887	ST033T G2 LED8/930 10W I MB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401831987	ST033T G2 LED8/930 10W I WB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401832087	ST033T G2 LED8/940 10W I MB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401832187	ST033T G2 LED8/940 10W I WB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834687	ST033T G2 LED8/930 10W I MB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834887	ST033T G2 LED8/940 10W I MB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835087	ST033T G2 LED8/930 10W I WB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401835287	ST033T G2 LED8/940 10W I WB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	-20 to +45 °C	For mounting on normally flammable surfaces	-
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	-20 to +45 °C	-	-
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	-20 to +45 °C	-	-

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	-20 to +45 °C	-	-
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	-20 to +45 °C	-	-
911401833887	ST033T G2 LED25/930 33W I MB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401833987	ST033T G2 LED25/930 33W I WB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834087	ST033T G2 LED25/940 33W I MB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834187	ST033T G2 LED25/940 33W I WB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836387	ST033T G2 LED25/930 33W I MB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836587	ST033T G2 LED25/940 33W I MB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836787	ST033T G2 LED25/930 33W I WB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836987	ST033T G2 LED25/940 33W I WB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	-20 to +45 °C	-	-
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	-20 to +45 °C	-	-

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
911401831687	ST033T G2 LED5/930 7W I WB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401831787	ST033T G2 LED5/940 7W I WB BK GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834287	ST033T G2 LED5/940 7W I WB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834387	ST033T G2 LED5/930 7W I WB BK CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401833487	ST033T G2 LED25/930 33W I MB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401833587	ST033T G2 LED25/930 33W I WB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401833687	ST033T G2 LED25/940 33W I MB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401833787	ST033T G2 LED25/940 33W I WB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836287	ST033T G2 LED25/930 33W I MB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836487	ST033T G2 LED25/940 33W I MB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836687	ST033T G2 LED25/930 33W I WB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401836887	ST033T G2 LED25/940 33W I WB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401857182	ST033T LED8/830 10W	-20 to +45 °C	-	-

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
	220-240V I MB WH CN			
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	-20 to +45 °C	-	-
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	-20 to +45 °C	-	-
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	-20 to +45 °C	-	-
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	-20 to +45 °C	-	-
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	-20 to +45 °C	-	-
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	-20 to +45 °C	-	-
911401857882	ST033T LED8/840 10W	-20 to +45 °C	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401882084	ST033T LED9/830 10W 110-240V I MB BK HK	(0.4338, 0.4030) SDCM <5	+/-10%
911401882184	ST033T LED9/840 10W 110-240V I MB BK HK	(0.3818, 0.3797) SDCM <5	+/-10%
911401882484	ST033T LED17/830 20W 110-240V I MB BK HK	(0.4338, 0.4030) SDCM <5	+/-10%
911401882584	ST033T LED17/840 20W 110-240V I MB BK HK	(0.3818, 0.3797) SDCM <5	+/-10%
911401882684	ST033T LED25/830 30W 110-240V I MB WH HK	(0.4338, 0.4030) SDCM <5	+/-10%
911401882784	ST033T LED25/840 30W 110-240V I MB WH HK	(0.3818, 0.3797) SDCM <5	+/-10%
911401882884	ST033T LED25/830 30W 110-240V I MB BK HK	(0.4338, 0.4030) SDCM <5	+/-10%
911401882984	ST033T LED25/840 30W 110-240V I MB BK HK	(0.3818, 0.3797) SDCM <5	+/-10%

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
	220-240V I WB BK CN			
911401831487	ST033T G2 LED5/930 7W I WB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401831587	ST033T G2 LED5/940 7W I WB WH GM	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834487	ST033T G2 LED5/940 7W I WB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401834587	ST033T G2 LED5/930 7W I WB WH CN	-20 °C to 45 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	-20 to +45 °C	-	-
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	-20 to +45 °C	-	-

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401832287	ST033T G2 LED8/930 10W I MB BK GM	(0.44,0.40) SDCM<5	-0%,+20%
911401832387	ST033T G2 LED8/930 10W I WB BK GM	(0.44,0.40) SDCM<5	-0%,+20%
911401832487	ST033T G2 LED8/940 10W I MB BK GM	(0.38,0.38) SDCM<5	-0%,+20%
911401832587	ST033T G2 LED8/940 10W I WB BK GM	(0.38,0.38) SDCM<5	-0%,+20%
911401834787	ST033T G2 LED8/930 10W I MB BK CN	(0.44,0.40) SDCM<5	-0%,+20%
911401834987	ST033T G2 LED8/940 10W I MB BK CN	(0.38,0.38) SDCM<5	-0%,+20%
911401835187	ST033T G2 LED8/930 10W I WB BK CN	(0.44,0.40) SDCM<5	-0%,+20%
911401835387	ST033T G2 LED8/940 10W I WB BK CN	(0.38,0.38) SDCM<5	-0%,+20%

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401833087	ST033T G2 LED17/930 20W I MB BK GM	(0.44,0.40) SDCM<5	-0%,+20%
911401833187	ST033T G2 LED17/930 20W I WB BK GM	(0.44,0.40) SDCM<5	-0%,+20%
911401833287	ST033T G2 LED17/940 20W I MB BK GM	(0.38,0.38) SDCM<5	-0%,+20%
911401833387	ST033T G2 LED17/940 20W I WB BK GM	(0.38,0.38) SDCM<5	-0%,+20%
911401835587	ST033T G2 LED17/930 20W I MB BK CN	(0.44,0.40) SDCM<5	-0%,+20%
911401835787	ST033T G2 LED17/940 20W I MB BK CN	(0.38,0.38) SDCM<5	-0%,+20%
911401835987	ST033T G2 LED17/930 20W I WB BK CN	(0.44,0.40) SDCM<5	-0%,+20%
911401836187	ST033T G2 LED17/940 20W I WB BK CN	(0.38,0.38) SDCM<5	-0%,+20%
911401805384	ST033T LED17/860 20W 220-240V I MB BK CN	(0.318, 0.333) SDCM≤5	+/-10%
911401858082	ST033T LED17/830 20W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401858282	ST033T LED17/840 20W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401858482	ST033T LED17/830 20W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401858682	ST033T LED17/840 20W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401881484	ST033T LED6/830 7W 110-240V I WB WH HK	(0.4338, 0.4030) SDCM <5	+/-10%
911401881584	ST033T LED6/840 7W 110-240V I WB WH HK	(0.3818, 0.3797) SDCM <5	+/-10%
911401832687	ST033T G2 LED17/930 20W I MB WH GM	(0.44,0.40) SDCM<5	-0%,+20%
911401832787	ST033T G2 LED17/930 20W I WB WH GM	(0.44,0.40) SDCM<5	-0%,+20%
911401832887	ST033T G2 LED17/940 20W I MB WH GM	(0.38,0.38) SDCM<5	-0%,+20%
911401832987	ST033T G2 LED17/940 20W I WB WH GM	(0.38,0.38) SDCM<5	-0%,+20%
911401835487	ST033T G2 LED17/930 20W I MB WH CN	(0.44,0.40) SDCM<5	-0%,+20%
911401835687	ST033T G2 LED17/940 20W I MB WH CN	(0.38,0.38) SDCM<5	-0%,+20%
911401835887	ST033T G2 LED17/930 20W I WB WH CN	(0.44,0.40) SDCM<5	-0%,+20%
911401836087	ST033T G2 LED17/940 20W I WB WH CN	(0.38,0.38) SDCM<5	-0%,+20%
911401805184	ST033T LED25/860 30W 220-240V I MB BK CN	(0.318, 0.333) SDCM≤5	+/-10%
911401858882	ST033T LED25/830 30W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401859082	ST033T LED25/840 30W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401859282	ST033T LED25/830 30W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401859482	ST033T LED25/840 30W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401881884	ST033T LED9/830 10W 110-240V I MB WH HK	(0.4338, 0.4030) SDCM <5	+/-10%
911401881984	ST033T LED9/840 10W 110-240V I MB WH HK	(0.3818, 0.3797) SDCM <5	+/-10%
911401882284	ST033T LED17/830 20W 110-240V I MB WH HK	(0.4338, 0.4030) SDCM <5	+/-10%
911401882384	ST033T LED17/840 20W 110-240V I MB WH HK	(0.3818, 0.3797) SDCM <5	+/-10%
911401881684	ST033T LED6/830 7W 110-240V I WB BK HK	(0.4338, 0.4030) SDCM <5	+/-10%
911401881784	ST033T LED6/840 7W 110-240V I WB BK HK	(0.3818, 0.3797) SDCM <5	+/-10%
911401805284	ST033T LED25/860 30W 220-240V I MB WH CN	(0.318, 0.333) SDCM≤5	+/-10%
911401858782	ST033T LED25/830 30W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401858982	ST033T LED25/840 30W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401859182	ST033T LED25/830 30W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401859382	ST033T LED25/840 30W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401831887	ST033T G2 LED8/930 10W I MB WH GM	(0.44,0.40) SDCM<5	-0%,+20%
911401831987	ST033T G2 LED8/930 10W I WB WH GM	(0.44,0.40) SDCM<5	-0%,+20%
911401832087	ST033T G2 LED8/940 10W I MB WH GM	(0.38,0.38) SDCM<5	-0%,+20%
911401832187	ST033T G2 LED8/940 10W I WB WH GM	(0.38,0.38) SDCM<5	-0%,+20%
911401834687	ST033T G2 LED8/930 10W I MB WH CN	(0.44,0.40) SDCM<5	-0%,+20%
911401834887	ST033T G2 LED8/940 10W I MB WH CN	(0.38,0.38) SDCM<5	-0%,+20%
911401835087	ST033T G2 LED8/930 10W I WB WH CN	(0.44,0.40) SDCM<5	-0%,+20%
911401835287	ST033T G2 LED8/940 10W I WB WH CN	(0.38,0.38) SDCM<5	-0%,+20%
911401805484	ST033T LED17/860 20W 220-240V I MB WH CN	(0.318, 0.333) SDCM≤5	+/-10%
911401857982	ST033T LED17/830 20W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401858182	ST033T LED17/840 20W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%

Essential Smartbright Projector Gen 2

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401858382	ST033T LED17/830 20W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401858582	ST033T LED17/840 20W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401833887	ST033T G2 LED25/930 33W I MB BK GM	(0.44,0.40) SDCM<5	-0%,+20%
911401833987	ST033T G2 LED25/930 33W I WB BK GM	(0.44,0.40) SDCM<5	-0%,+20%
911401834087	ST033T G2 LED25/940 33W I MB BK GM	(0.38,0.38) SDCM<5	-0%,+20%
911401834187	ST033T G2 LED25/940 33W I WB BK GM	(0.38,0.38) SDCM<5	-0%,+20%
911401836387	ST033T G2 LED25/930 33W I MB BK CN	(0.44,0.40) SDCM<5	-0%,+20%
911401836587	ST033T G2 LED25/940 33W I MB BK CN	(0.38,0.38) SDCM<5	-0%,+20%
911401836787	ST033T G2 LED25/930 33W I WB BK CN	(0.44,0.40) SDCM<5	-0%,+20%
911401836987	ST033T G2 LED25/940 33W I WB BK CN	(0.38,0.38) SDCM<5	-0%,+20%
911401826784	ST033T LED25/830 30W 110-240V I WB WH KC	(0.43, 0.40) SDCM <5	+/-10%
911401826884	ST033T LED25/840 30W 110-240V I WB WH KC	(0.38, 0.38) SDCM <5	+/-10%
911401831687	ST033T G2 LED5/930 7W I WB BK GM	(0.44,0.40) SDCM<5	-0%,+20%
911401831787	ST033T G2 LED5/940 7W I WB BK GM	(0.38,0.38) SDCM<5	-0%,+20%
911401834287	ST033T G2 LED5/940 7W I WB BK CN	(0.38,0.38) SDCM<5	-0%,+20%
911401834387	ST033T G2 LED5/930 7W I WB BK CN	(0.44,0.40) SDCM<5	-0%,+20%
911401833487	ST033T G2 LED25/930 33W I MB WH GM	(0.44,0.40) SDCM<5	-0%,+20%
911401833587	ST033T G2 LED25/930 33W I WB WH GM	(0.44,0.40) SDCM<5	-0%,+20%
911401833687	ST033T G2 LED25/940 33W I MB WH GM	(0.38,0.38) SDCM<5	-0%,+20%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401833787	ST033T G2 LED25/940 33W I WB WH GM	(0.38,0.38) SDCM<5	-0%,+20%
911401836287	ST033T G2 LED25/930 33W I MB WH CN	(0.44,0.40) SDCM<5	-0%,+20%
911401836487	ST033T G2 LED25/940 33W I MB WH CN	(0.38,0.38) SDCM<5	-0%,+20%
911401836687	ST033T G2 LED25/930 33W I WB WH CN	(0.44,0.40) SDCM<5	-0%,+20%
911401836887	ST033T G2 LED25/940 33W I WB WH CN	(0.38,0.38) SDCM<5	-0%,+20%
911401857182	ST033T LED8/830 10W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401857382	ST033T LED8/840 10W 220-240V I MB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401857582	ST033T LED8/830 10W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401857782	ST033T LED8/840 10W 220-240V I WB WH CN	(0.4316, 0.3984) SDCM <5	+/-10%
911401857282	ST033T LED8/830 10W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401857482	ST033T LED8/840 10W 220-240V I MB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401857682	ST033T LED8/830 10W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401857882	ST033T LED8/840 10W 220-240V I WB BK CN	(0.3811, 0.3772) SDCM <5	+/-10%
911401831487	ST033T G2 LED5/930 7W I WB WH GM	(0.44,0.40) SDCM<5	-0%,+20%
911401831587	ST033T G2 LED5/940 7W I WB WH GM	(0.38,0.38) SDCM<5	-0%,+20%
911401834487	ST033T G2 LED5/940 7W I WB WH CN	(0.38,0.38) SDCM<5	-0%,+20%
911401834587	ST033T G2 LED5/930 7W I WB WH CN	(0.44,0.40) SDCM<5	-0%,+20%
911401826984	ST033T LED25/830 30W 110-240V I WB BK KC	(0.43, 0.40) SDCM <5	+/-10%
911401827084	ST033T LED25/840 30W 110-240V I WB BK KC	(0.38, 0.38) SDCM <5	+/-10%

