



The most reliable and complete lighting solution for retail and industry of today and tomorrow.

SlimPerform Batten

Lighting plays a different role in every application. Some require latest-generation solutions with high light quality and connectivity; others just simple functionality. But whether for retail or industrial applications, you always need a combination of quality, performance, and flexibility. Get to know SlimPerform. The Batten LED luminaire where all these benefits come together. Putting the new lighting trend in your company.

Benefits

- High efficiency and longer service life to reduce operating costs
- Superior optical performance
- Easy installation
- Ready for the future

Features

- Efficacy up to 169lm/W
- Quality and reliability with a lifetime > 50k hours
- Four optics options - DA (double asymmetric), WB (open), MB (medium) and HRO (corridor)
- Version with integrated emergency module with 3-hour autonomy
- Ready for Interact Indoor Navigation system

SlimPerform Batten

Application

- Hypermarkets
- Supermarkets
- Wholesalers
- Department Stores
- Pet Centers
- Home Centers
- Industries
- Logistic Warehouses

Warnings and Safety

- 5-year warranty

Versions



SlimPerform Batten




SlimPerform Black



SlimPerform Batten




SlimPerform Batten



SlimPerform Batten

SlimPerform Batten

Dimensional drawing



Product details



SlimPerform Batten



SlimPerform Batten



SlimPerform Batten

General Information	
Light source replaceable	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Driver included
919406021901	BN310P LED92/840 SRD H4 WB L1150 WH	Yes
919406021911	BN310P LED92/840 SRD H4 MB L1150 WH	Yes
919406021921	BN310P LED92/840 SRD H4 HRO L1150 WH	Yes
919406021931	BN310P LED92/840 SRD H4 DA L1150 WH	Yes
919406021941	BN310P LED92/865 SRD H4 WB L1150 WH	Yes
919406021951	BN310P LED92/865 SRD H4 MB L1150 WH	Yes
919406021961	BN310P LED92/865 SRD H4 HRO L1150 WH	Yes
919406021971	BN310P LED92/865 SRD H4 DA L1150 WH	Yes
919406021981	BN310P LED160/840 SRD H4 WB L1700 WH	Yes
919406021991	BN310P LED160/840 SRD H4 MB L1700 WH	Yes
919406022001	BN310P LED160/840 SRD H4 HRO L1700 WH	Yes
919406022011	BN310P LED160/865 SRD H4 WB L1700 WH	Yes
919406022021	BN310P LED160/865 SRD H4 MB L1700 WH	Yes
919406022031	BN310P LED160/865 SRD H4 HRO L1700 WH	Yes
919406022041	BN310P LED200/840 SRD H4 WB L1700 WH	Yes

Order Code	Full Product Name	Driver included
919406022051	BN310P LED200/840 SRD H4 MB L1700 WH	Yes
919406022061	BN310P LED200/840 SRD H4 HRO L1700 WH	Yes
919406022071	BN310P LED200/865 SRD H4 WB L1700 WH	Yes
919406022081	BN310P LED200/865 SRD H4 MB L1700 WH	Yes
919406022091	BN310P LED200/865 SRD H4 HRO L1700 WH	Yes
919506310581	BN310P Xitanium 60W Driver Spare Part	Yes
820619284351	BN310P LED92/840 PSU HRO L1150 WH	Yes
820619284711	BN310P LED160/850 PSU WB L1700 WH	Yes
820619284721	BN310P LED160/850 PSU HRO L1700 WH	Yes
820619284731	BN310P LED160/850 PSU MB L1700 WH	Yes
820619284761	BN310P LED92/850 PSU MB L1150 WH	Yes
820619284771	BN310P LED70/850 PSU WB L1150 WH	Yes
820619284781	BN310P LED130/850 PSU HRO L1700 WH	Yes
820619284791	BN310P LED130/850 PSU MB L1700 WH	Yes
820619284801	BN310P LED130/850 PSU WB L1700 WH	Yes

Order Code	Full Product Name	Driver included
919406020741	BN310P LED70/840 PSU WB L1150 WH	Yes
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	Yes
919406020761	BN310P LED92/840 PSU WB L1150 WH	Yes
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	Yes
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	Yes
919406020791	BN310P LED160/840 PSU WB L1700 WH	Yes
919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	Yes
919406020811	BN310P LED160/840PSD- VLC WB EL L1700 WH	Yes
919406020821	BN310P LED70/865 PSU MB L1150 WH	Yes
919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	Yes
919406020841	BN310P LED92/830 PSU DA L1150 WH	Yes
919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	Yes
919406020881	BN310P LED160/865 PSU HRO L1700 WH	Yes
919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	Yes
919406020901	BN310P LED92/865 PSU DA L1150 WH	Yes
919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	Yes
919406020921	BN310P LED70/840 PSU MB L1150 WH	Yes
919406020931	BN310P LED160/840 PSU HRO L1700 WH	Yes
919406020951	BN310P LED70/865 PSU WB L1150 WH	Yes
919406020961	BN310P LED70/865 PSD-VLC WB L1150 WH	Yes
919406020971	BN310P LED70/840 PSD-VLC MB L1150 WH	Yes
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	Yes
919406020991	BN310P LED70/840 PSD-VLC WB EL L1150 WH	Yes
919406021001	BN310P LED70/830 PSU MB L1150 WH	Yes
919406021011	BN310P LED70/830 PSD-VLC MB L1150 WH	Yes
919406021021	BN310P LED70/830 PSU WB L1150 WH	Yes
919406021031	BN310P LED70/830 PSD-VLC WB L1150 WH	Yes
919406021041	BN310P LED92/865 PSU MB L1150 WH	Yes
919406021051	BN310P LED92/865 PSD-VLC MB L1150 WH	Yes
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	Yes
919406021071	BN310P LED92/865 PSD-VLC MB EL L1150 WH	Yes
919406021081	BN310P LED92/865 PSU WB L1150 WH	Yes
919406021091	BN310P LED92/865 PSD-VLC WB L1150 WH	Yes
919406021101	BN310P LED92/865 PSU WB EL L1150 WH	Yes
919406021111	BN310P LED92/865 PSD WB EL L1150 WH	Yes
919406021121	BN310P LED92/865 PSU DA EL L1150 WH	Yes
919406021131	BN310P LED92/865 PSD-VLC DA EL L1150 WH	Yes
919406021141	BN310P LED92/840 PSU MB L1150 WH	Yes
919406021151	BN310P LED92/840 PSD-VLC MB L1150 WH	Yes
919406021161	BN310P LED92/840 PSU MB EL L1150 WH	Yes
919406021171	BN310P LED92/840 PSD-VLC MB EL L1150 WH	Yes
919406021181	BN310P LED92/840 PSU WB EL L1150 WH	Yes
919406021191	BN310P LED92/840 PSU DA EL L1150 WH	Yes
919406021201	BN310P LED92/840 PSD-VLC DA EL L1150 WH	Yes
919406021211	BN310P LED92/830 PSU MB L1150 WH	Yes
919406021221	BN310P LED92/830 PSD-VLC MB L1150 WH	Yes
919406021231	BN310P LED92/830 PSU MB EL L1150 WH	Yes
919406021241	BN310P LED92/830 PSD-VLC MB EL L1150 WH	Yes
919406021251	BN310P LED92/830 PSU WB L1150 WH	Yes
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	Yes
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	Yes
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	Yes

Order Code	Full Product Name	Driver included
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	Yes
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	Yes
919406021341	BN310P LED160/865 PSU MB L1700 WH	Yes
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	Yes
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	Yes
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	Yes
919406021381	BN310P LED160/865 PSU WB L1700 WH	Yes
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	Yes
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	Yes
919406021411	BN310P LED160/865 PSD-VLC WB EL L1700 WH	Yes
919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	Yes
919406021431	BN310P LED160/865PSD-VLC HRO EL L1700 WH	Yes
919406021441	BN310P LED160/840 PSU MB L1700 WH	Yes
919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	Yes
919406021461	BN310P LED160/840 PSU MB EL L1700 WH	Yes
919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	Yes
919406021481	BN310P LED160/840 PSU WB EL L1700 WH	Yes
919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	Yes
919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	Yes
919406021511	BN310P LED160/840PSD-VLC HRO EL L1700 WH	Yes
919406021521	BN310P LED92/840 PSU DA L1150 WH	Yes
919406021531	BN310P LED92/840 PSD- VLC DA L1150 WH	Yes
919406021621	BN310P LED200/840 PSD- VLC WB L1700 WH	Yes
919406021631	BN310P LED200/840 PSD-VLC HRO L1700 WH	Yes
919406021641	BN310P LED200/840 PSD-VLC MB EL L1700 WH	Yes
919406021651	BN310P LED200/840 PSD-VLC MB L1700 WH	Yes
919406021661	BN310P LED200/840 PSU HRO EL L1700 WH	Yes
919406021671	BN310P LED200/840 PSU HRO L1700 WH	Yes
919406021681	BN310P LED200/840 PSU MB EL L1700 WH	Yes
919406021691	BN310P LED200/840 PSU MB L1700 WH	Yes
919406021701	BN310P LED200/840 PSU WB EL L1700 WH	Yes
919406021711	BN310P LED200/840 PSU WB L1700 WH	Yes
919406021721	BN310P LED200/840PSD-VLC WB EL L1700 WH	Yes
919406021731	BN310P LED200/840PSD-VLC HRO EL L1700WH	Yes
919406021741	BN310P LED200/865 PSD-V LC HRO L1700 WH	Yes
919406021751	BN310P LED200/865 PSD-VLC MB EL L1700 WH	Yes
919406021761	BN310P LED200/865 PSD-VLC MB L1700 WH	Yes
919406021771	BN310P LED200/865 PSD-VLC WB EL L1700 WH	Yes
919406021781	BN310P LED200/865 PSD-VLC WB L1700 WH	Yes
919406021791	BN310P LED200/865 PSU HRO EL L1700 WH	Yes
919406021801	BN310P LED200/865 PSU HRO L1700 WH	Yes
919406021811	BN310P LED200/865 PSU MB EL L1700 WH	Yes
919406021821	BN310P LED200/865 PSU MB L1700 WH	Yes
919406021831	BN310P LED200/865 PSU WB EL L1700 WH	Yes
919406021841	BN310P LED200/865 PSU WB L1700 WH	Yes
919406021851	BN310P LED200/865PSD-VLC HRO EL L1700 WH	Yes
919406021861	BN310P LED70/840 WIA WB L1150 WH	Yes
919406021871	BN310P LED70/840 WIA MB L1150 WH	Yes
919406021881	BN310P LED70/865 WIA WB L1150 WH	Yes
919406021891	BN310P LED70/865 WIA MB L1150 WH	Yes
919406022101	BN310P LED230/840 PSD- VLC WB L1700 WH	Yes
919406022111	BN310P LED230/840 PSD-VLC HRO L1700 WH	Yes

SlimPerform Batten

Order Code	Full Product Name	Driver included
919406022121	BN310P LED230/840 PSD-VLC MB L1700 WH	Yes
919406022131	BN310P LED230/840 PSU HRO L1700 WH	Yes
919406022141	BN310P LED230/840 PSU MB L1700 WH	Yes
919406022151	BN310P LED230/840 PSU WB L1700 WH	Yes
820619283931	BN310P LED92/840 PSU MB L1150 BK	Yes
820619284281	BN310P LED92/865 PSU MB L1150 BK	Yes
820619284431	BN310P LED92/830 PSU MB L1150 BK	Yes
820619284681	BN310P LED70/840 PSU WB L1150 BK	Yes
820619284691	BN310P LED70/840 PSU WB EL L1150 BK	Yes
820619284701	BN310P LED70/830 PSU MB L1150 BK	Yes

Order Code	Full Product Name	Driver included
919406020861	BN310P LED92/840 PSU DA L1150 BK	Yes
919406020871	BN310P LED92/840 PSD- VLC DA L1150 BK	Yes
919406021311	BN310P LED92/840 PSD-VLC WB L1150 BK	Yes
919406021321	BN310P LED92/840 PSU WB EL L1150 BK	Yes
919406021331	BN310P LED92/840 PSD-VLC WB EL L1150 BK	Yes
919506310591	BN310P Xitanium 100W Driver Spare Part	Yes
919506310621	BN310P Bracket White Spare Part	No
919506310631	BN310P Bracket Black Spare Part	No
919506310601	BN310P CertaDrive 44W Driver Spare Part	Yes
919506310611	BN310P CertaDrive 65W Driver Spare Part	Yes

Light Technical

Correlated Color Temperature index Luminous Efficacy (Nom)						Correlated Color Temperature index Luminous Efficacy (Nom)					
Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
919406021901	BN310P LED92/840 SRD H4 WB L1150 WH	4000 K	>80	163.8 lm/W	9,500 lm	919406022011	H4 HRO L1700 WH	6500 K	>80	161.77 lm/W	16,500 lm
919406021911	BN310P LED92/840 SRD H4 MB L1150 WH	4000 K	>80	163.8 lm/W	9,500 lm	919406022021	BN310P LED160/865 SRD H4 WB L1700 WH	6500 K	>80	161.77 lm/W	16,500 lm
919406021921	BN310P LED92/840 SRD H4 HRO L1150 WH	4000 K	>80	163.8 lm/W	9,500 lm	919406022031	BN310P LED160/865 SRD H4 MB L1700 WH	6500 K	>80	161.77 lm/W	16,500 lm
919406021931	BN310P LED92/840 SRD H4 DA L1150 WH	4000 K	>80	163.8 lm/W	9,500 lm	919406022041	BN310P LED200/840 SRD H4 WB L1700 WH	4000 K	>80	155.04 lm/W	20,000 lm
919406021941	BN310P LED92/865 SRD H4 WB L1150 WH	6500 K	>80	163.8 lm/W	9,500 lm	919406022051	BN310P LED200/840 SRD H4 MB L1700 WH	4000 K	>80	155.04 lm/W	20,000 lm
919406021951	BN310P LED92/865 SRD H4 MB L1150 WH	6500 K	>80	163.8 lm/W	9,500 lm	919406022061	BN310P LED200/840 SRD H4 HRO L1700 WH	4000 K	>80	155.04 lm/W	20,000 lm
919406021961	BN310P LED92/865 SRD H4 HRO L1150 WH	6500 K	>80	163.8 lm/W	9,500 lm	919406022071	BN310P LED200/865 SRD H4 WB L1700 WH	6500 K	>80	155.04 lm/W	20,000 lm
919406021971	BN310P LED92/865 SRD H4 DA L1150 WH	6500 K	>80	163.8 lm/W	9,500 lm	919406022081	BN310P LED200/865 SRD H4 MB L1700 WH	6500 K	>80	155.04 lm/W	20,000 lm
919406021981	BN310P LED160/840 SRD H4 WB L1700 WH	4000 K	>80	161.77 lm/W	16,500 lm	919406022091	BN310P LED200/865 SRD H4 HRO L1700 WH	6500 K	>80	155.04 lm/W	20,000 lm
919406021991	BN310P LED160/840 SRD H4 MB L1700 WH	4000 K	>80	161.77 lm/W	16,500 lm						
919406022001	BN310P LED160/840 SRD	4000 K	>80	161.77 lm/W	16,500 lm						

Correlated Color Temperature index Luminous Efficacy Luminous Flux						Correlated Color Temperature index Luminous Efficacy Luminous Flux					
Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
919506310581	BN310P Xitanium 60W Driver Spare Part	-	-	0 lm/W	0 lm	919406020791	BN310P LED160/840 PSU WB L1700 WH	4000 K	>80	163.36633663366337 lm/W	16,500 lm
820619284351	BN310P LED92/840 PSU HRO L1150 WH	4000 K	>80	169.65 lm/W	9,500 lm	919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	4000 K	>80	161.76470588235293 lm/W	16,500 lm
820619284711	BN310P LED160/850 PSU WB L1700 WH	5000 K	>80	163.37 lm/W	16,500 lm	919406020811	BN310P LED160/840PSD- VLC WB EL L1700 WH	4000 K	>80	161.76470588235293 lm/W	16,500 lm
820619284721	BN310P LED160/850 PSU HRO L1700 WH	5000 K	>80	163.37 lm/W	16,500 lm	919406020821	BN310P LED70/865 PSU MB L1150 WH	6500 K	>80	165.11627906976744 lm/W	7,100 lm
820619284731	BN310P LED160/850 PSU MB L1700 WH	5000 K	>80	163.37 lm/W	16,500 lm	919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	6500 K	>80	161.36363636363637 lm/W	7,100 lm
820619284761	BN310P LED92/850 PSU MB L1150 WH	5000 K	>80	169.65 lm/W	9,500 lm	919406020841	BN310P LED92/830 PSU DA L1150 WH	3000 K	>80	164.28571428571428 lm/W	9,200 lm
820619284771	BN310P LED70/850 PSU WB L1150 WH	5000 K	>80	165.12 lm/W	7,100 lm	919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	3000 K	>80	158.6206896551724 lm/W	9,200 lm
820619284781	BN310P LED130/850 PSU HRO L1700 WH	5000 K	>80	162.69 lm/W	14,154 lm	919406020881	BN310P LED160/865 PSU HRO L1700 WH	6500 K	>80	163.36633663366337 lm/W	16,500 lm
820619284791	BN310P LED130/850 PSU MB L1700 WH	5000 K	>80	162.69 lm/W	14,154 lm	919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	6500 K	>80	161.76470588235293 lm/W	16,500 lm
820619284801	BN310P LED130/850 PSU WB L1700 WH	5000 K	>80	162.69 lm/W	14,154 lm	919406020901	BN310P LED92/865 PSU DA L1150 WH	6500 K	>80	169.64285714285714 lm/W	9,500 lm
919406020741	BN310P LED70/840 PSU WB L1150 WH	4000 K	>80	165.11627906976744 lm/W	7,100 lm	919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	6500 K	>80	163.79310344827587 lm/W	9,500 lm
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	4000 K	>80	161.36363636363637 lm/W	7,100 lm	919406020921	BN310P LED70/840 PSU MB L1150 WH	4000 K	>80	165.11627906976744 lm/W	7,100 lm
919406020761	BN310P LED92/840 PSU WB L1150 WH	4000 K	>80	169.64285714285714 lm/W	9,500 lm	919406020931	BN310P LED160/840 PSU HRO L1700 WH	4000 K	>80	163.36633663366337 lm/W	16,500 lm
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	4000 K	>80	163.79310344827587 lm/W	9,500 lm	919406020951	BN310P LED70/865 PSU WB L1150 WH	6500 K	>80	165.11627906976744 lm/W	7,100 lm
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	4000 K	>80	163.79310344827587 lm/W	9,500 lm	919406020961	BN310P LED70/865 PSD-	6500 K	>80	161.36363636363637 lm/W	7,100 lm

Correlated Color Temperature index Luminous Efficacy Luminous Flux						Correlated Color Temperature index Luminous Efficacy Luminous Flux					
Order Code	Full Product Name	(Nom)	(CRI)	(rated) (Nom)	Flux	Order Code	Full Product Name	(Nom)	(CRI)	(rated) (Nom)	Flux
919406020971	VLC WB L1150 WH	4000 K	>80	161.36363636363637 lm/W	7,100 lm	919406021101	BN310P LED92/865 PSU WB EL L1150 WH	6500 K	>80	169.64285714285714 lm/W	9,500 lm
	BN310P LED70/840 PSD-VLC MB L1150 WH					919406021111	BN310P LED92/865 PSD WB EL L1150 WH				
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	4000 K	>80	161.36363636363637 lm/W	7,100 lm	919406021121	BN310P LED92/865 PSU DA EL L1150 WH	6500 K	>80	169.64285714285714 lm/W	9,500 lm
	BN310P LED70/840 PSD-VLC WB EL L1150 WH					919406021131	BN310P LED92/865 PSD-VLC DA EL L1150 WH				
919406021001	BN310P LED70/830 PSU MB L1150 WH	3000 K	>80	162.7906976744486 lm/W	7,000 lm	919406021141	BN310P LED92/840 PSU MB L1150 WH	4000 K	>80	169.64285714285714 lm/W	9,500 lm
	BN310P LED70/830 PSD-VLC MB L1150 WH					919406021151	BN310P LED92/840 PSD-VLC MB L1150 WH				
919406021021	BN310P LED70/830 PSU WB L1150 WH	3000 K	>80	162.7906976744486 lm/W	7,000 lm	919406021161	BN310P LED92/840 PSU MB EL L1150 WH	4000 K	>80	169.64285714285714 lm/W	9,500 lm
	BN310P LED70/830 PSD-VLC WB L1150 WH					919406021171	BN310P LED92/840 PSD-VLC MB EL L1150 WH				
919406021041	BN310P LED92/865 PSU MB L1150 WH	6500 K	>80	169.64285714285714 lm/W	9,500 lm	919406021181	BN310P LED92/840 PSU WB EL L1150 WH	4000 K	>80	169.64285714285714 lm/W	9,500 lm
	BN310P LED92/865 PSD-VLC MB L1150 WH					919406021191	BN310P LED92/840 PSU DA EL L1150 WH				
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	6500 K	>80	169.64285714285714 lm/W	9,500 lm	919406021201	BN310P LED92/840 PSD-VLC DA EL L1150 WH	4000 K	>80	163.79310344827587 lm/W	9,200 lm
	BN310P LED92/865 PSD-VLC MB EL L1150 WH					919406021211	BN310P LED92/830 PSU MB L1150 WH				
919406021081	BN310P LED92/865 PSU WB L1150 WH	6500 K	>80	169.64285714285714 lm/W	9,500 lm	919406021221	BN310P LED92/830 PSD-VLC MB L1150 WH	3000 K	>80	158.6206896551724 lm/W	9,200 lm
	BN310P LED92/865 PSD-VLC WB L1150 WH					919406021231	BN310P LED92/830 PSU MB EL L1150 WH				
919406021091	BN310P LED92/865 PSD-VLC WB L1150 WH	6500 K	>80	163.79310344827587 lm/W	9,500 lm	919406021241	BN310P LED92/830 PSD-VLC WB L1150 WH	3000 K	>80	158.6206896551724 lm/W	9,200 lm
	BN310P LED92/865 PSD-VLC WB L1150 WH										

SlimPerform Batten

SlimPerform Batten						SlimPerform Batten					
Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	VLC MB EL L1150 WH						PSD-VLC WB EL L1700 WH				
919406021251	BN310P LED92/830 PSU WB L1150 WH	3000 K	>80	164.28571428571428 lm/W	9,200 lm	919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	6500 K	>80	163.36633663366337 lm/W	16,500 lm
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	3000 K	>80	158.6206896551724 lm/W	9,200 lm	919406021431	BN310P LED160/865PSD-VLC HRO EL L1700 WH	6500 K	>80	161.76470588235293 lm/W	16,500 lm
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	3000 K	>80	164.28571428571428 lm/W	9,200 lm	919406021441	BN310P LED160/840 PSU MB L1700 WH	4000 K	>80	163.36633663366337 lm/W	16,500 lm
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	3000 K	>80	158.6206896551724 lm/W	9,200 lm	919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	4000 K	>80	161.76470588235293 lm/W	16,500 lm
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	3000 K	>80	164.28571428571428 lm/W	9,200 lm	919406021461	BN310P LED160/840 PSU MB EL L1700 WH	4000 K	>80	163.36633663366337 lm/W	16,500 lm
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	3000 K	>80	158.6206896551724 lm/W	9,200 lm	919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	4000 K	>80	161.76470588235293 lm/W	16,500 lm
919406021341	BN310P LED160/865 PSU MB L1700 WH	6500 K	>80	163.36633663366337 lm/W	16,500 lm	919406021481	BN310P LED160/840 PSU WB EL L1700 WH	4000 K	>80	163.36633663366337 lm/W	16,500 lm
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	6500 K	>80	161.76470588235293 lm/W	16,500 lm	919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	4000 K	>80	161.76470588235293 lm/W	16,500 lm
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	6500 K	>80	163.36633663366337 lm/W	16,500 lm	919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	4000 K	>80	163.36633663366337 lm/W	16,500 lm
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	6500 K	>80	161.76470588235293 lm/W	16,500 lm	919406021511	BN310P LED160/840PSD-VLC HRO EL L1700 WH	4000 K	>80	161.76470588235293 lm/W	16,500 lm
919406021381	BN310P LED160/865 PSU WB L1700 WH	6500 K	>80	163.36633663366337 lm/W	16,500 lm	919406021521	BN310P LED92/840 PSU DA L1150 WH	4000 K	>80	169.64285714285714 lm/W	9,500 lm
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	6500 K	>80	161.76470588235293 lm/W	16,500 lm	919406021531	BN310P LED92/840 PSD-VLC DA L1150 WH	4000 K	>80	163.79310344827587 lm/W	9,500 lm
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	6500 K	>80	163.36633663366337 lm/W	16,500 lm	919406021621	BN310P LED200/840 PSD- VLC WB L1700 WH	4000 K	>80	155.04 lm/W	20,000 lm
919406021411	BN310P LED160/865	6500 K	>80	161.76470588235293 lm/W	16,500 lm						

		Correlated Color						Correlated Color			
		Temperature	index	Luminous Efficacy	Luminous			Temperature	index	Luminous Efficacy	Luminous
Order Code	Full Product Name	(Nom)	(CRI)	(rated) (Nom)	Flux	Order Code	Full Product Name	(Nom)	(CRI)	(rated) (Nom)	Flux
919406021631	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021771	PSD-VLC MB	6500 K	>80	155.04 lm/W	20,000 lm
	LED200/840						L1700 WH				
	PSD-VLC HRO						LED200/865				
	L1700 WH						PSD-VLC WB EL				
919406021641	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021781	L1700 WH	6500 K	>80	155.04 lm/W	20,000 lm
	LED200/840						PSD-VLC WB				
	PSD-VLC MB EL						LED200/865				
	L1700 WH						L1700 WH				
919406021651	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021791	PSD-VLC WB	6500 K	>80	155.04 lm/W	20,000 lm
	LED200/840						L1700 WH				
	PSD-VLC MB						LED200/865 PSU				
	L1700 WH						HRO EL L1700				
919406021661	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021801	WH	6500 K	>80	155.04 lm/W	20,000 lm
	LED200/840 PSU						LED200/865 PSU				
	HRO EL L1700						HRO L1700 WH				
	WH						LED200/865 PSU				
919406021671	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021811	LED200/865 PSU	6500 K	>80	155.04 lm/W	20,000 lm
	LED200/840 PSU						MB EL L1700 WH				
	HRO L1700 WH						LED200/865 PSU				
							MB L1700 WH				
919406021681	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021821	LED200/865 PSU	6500 K	>80	155.04 lm/W	20,000 lm
	LED200/840 PSU						WB EL L1700 WH				
	MB EL L1700 WH						LED200/865 PSD				
							-VLC HRO EL				
919406021691	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021831	L1700 WH	4000 K	>80	155.04 lm/W	20,000 lm
	LED200/840 PSU						LED70/840 WIA				
	MB L1700 WH						WB L1150 WH				
							LED70/840 WIA				
919406021701	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021841	MB L1150 WH	4000 K	>80	155.04 lm/W	20,000 lm
	LED200/840 PSU						LED70/865 WIA				
	WB EL L1700 WH						WB L1150 WH				
							LED230/840				
919406021711	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021851	PSD-VLC WB	6500 K	>80	155.04 lm/W	20,000 lm
	LED200/840 PSU						L1700 WH				
	WB L1700 WH										
919406021721	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021861	LED200/865PSD	4000 K	>80	161.37 lm/W	7,100 lm
	LED200/840PSD						LED70/840 WIA				
	-VLC WB EL						WB L1150 WH				
	L1700 WH						LED70/840 WIA				
919406021731	BN310P	4000 K	>80	155.04 lm/W	20,000 lm	919406021871	MB L1150 WH	4000 K	>80	161.37 lm/W	7,100 lm
	LED200/840PSD						LED70/865 WIA				
	-VLC HRO EL						WB L1150 WH				
	L1700WH						LED70/840 WIA				
919406021741	BN310P	6500 K	>80	155.04 lm/W	20,000 lm	919406021881	MB L1150 WH	6500 K	>80	161.37 lm/W	7,100 lm
	LED200/865						LED70/865 WIA				
	PSD-V LC HRO						WB L1150 WH				
	L1700 WH						LED70/865 WIA				
919406021751	BN310P	6500 K	>80	155.04 lm/W	20,000 lm	919406021891	MB L1150 WH	6500 K	>80	161.37 lm/W	7,100 lm
	LED200/865						LED70/865 WIA				
	PSD-VLC MB EL						MB L1150 WH				
	L1700 WH						LED230/840				
919406021761	BN310P	6500 K	>80	155.04 lm/W	20,000 lm	919406022101	PSD-VLC WB	4000 K	>80	150.33 lm/W	23,000 lm
	LED200/865						L1700 WH				

SlimPerform Batten

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
919406022111	BN310P	4000 K	>80	150.33 lm/W	23,000 lm	820619284701	BN310P	3000 K	>80	162.8 lm/W	7,000 lm
	LED230/840						LED70/830 PSU				
	PSD-VLC HRO						MB L1150 BK				
	L1700 WH										
919406022121	BN310P	4000 K	>80	150.33 lm/W	23,000 lm	919406020861	BN310P	4000 K	>80	169.64285714285714 lm/W	9,500 lm
	LED230/840						LED92/840 PSU				
	PSD-VLC MB						DA L1150 BK				
	L1700 WH										
919406022131	BN310P	4000 K	>80	150.33 lm/W	23,000 lm	919406020871	BN310P	4000 K	>80	163.79310344827587 lm/W	9,500 lm
	LED230/840 PSU						LED92/840 PSD-				
	HRO L1700 WH						VLC DA L1150 BK				
919406022141	BN310P	4000 K	>80	150.33 lm/W	23,000 lm	919406021311	BN310P	4000 K	>80	163.79310344827587 lm/W	9,500 lm
	LED230/840 PSU						LED92/840 PSD-				
	MB L1700 WH						VLC WB L1150 BK				
919406022151	BN310P	4000 K	>80	150.33 lm/W	23,000 lm	919406021321	BN310P	4000 K	>80	169.64285714285714 lm/W	9,500 lm
	LED230/840 PSU						LED92/840 PSU				
	WB L1700 WH						WB EL L1150 BK				
820619283931	BN310P	4000 K	>80	169.65 lm/W	9,500 lm	919406021331	BN310P	4000 K	>80	163.79310344827587 lm/W	9,500 lm
	LED92/840 PSU						LED92/840 PSD-				
	MB L1150 BK						VLC WB EL L1150 BK				
820619284281	BN310P	6500 K	>80	169.65 lm/W	9,500 lm	919506310591	BN310P Xitanium	-	-	0 lm/W	0 lm
	LED92/865 PSU						100W Driver				
	MB L1150 BK						Spare Part				
820619284431	BN310P	3000 K	>80	164.29 lm/W	9,200 lm	919506310621	BN310P Bracket	-	-	0 lm/W	0 lm
	LED92/830 PSU						White Spare Part				
	MB L1150 BK										
820619284681	BN310P	4000 K	>80	165.12 lm/W	7,100 lm	919506310631	BN310P Bracket	-	-	0 lm/W	0 lm
	LED70/840 PSU						Black Spare Part				
	WB L1150 BK										
820619284691	BN310P	4000 K	>80	165.12 lm/W	7,100 lm	919506310601	BN310P	-	-	0 lm/W	0 lm
	LED70/840 PSU						CertaDrive 44W				
	WB EL L1150 BK						Driver Spare Part				
820619284691	BN310P	4000 K	>80	165.12 lm/W	7,100 lm	919506310611	BN310P	-	-	0 lm/W	0 lm
	LED70/840 PSU						CertaDrive 65W				
	WB EL L1150 BK						Driver Spare Part				

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption	Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406021901	BN310P	Safety	220 to	50 or 60	58 W	919406021941	BN310P	Safety	220 to	50 or 60	58 W
	LED92/840 SRD	class I	240 V	Hz			LED92/865 SRD	class I	240 V	Hz	
	H4 WB L1150 WH						H4 WB L1150 WH				
919406021911	BN310P	Safety	220 to	50 or 60	58 W	919406021951	BN310P	Safety	220 to	50 or 60	58 W
	LED92/840 SRD	class I	240 V	Hz			LED92/865 SRD	class I	240 V	Hz	
	H4 MB L1150 WH						H4 MB L1150 WH				
919406021921	BN310P	Safety	220 to	50 or 60	58 W	919406021961	BN310P	Safety	220 to	50 or 60	58 W
	LED92/840 SRD	class I	240 V	Hz			LED92/865 SRD	class I	240 V	Hz	
	H4 HRO L1150 WH						H4 HRO L1150 WH				
919406021931	BN310P	Safety	220 to	50 or 60	58 W	919406021971	BN310P	Safety	220 to	50 or 60	58 W
	LED92/840 SRD	class I	240 V	Hz			LED92/865 SRD	class I	240 V	Hz	
	H4 DA L1150 WH						H4 DA L1150 WH				

SlimPerform Batten

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406021981	BN310P LED160/840 SRD H4 WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406021991	BN310P LED160/840 SRD H4 MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406022001	BN310P LED160/840 SRD H4 HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406022011	BN310P LED160/865 SRD H4 WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406022021	BN310P LED160/865 SRD H4 MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406022031	BN310P LED160/865 SRD H4 HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406022041	BN310P LED200/840 SRD H4 WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406022051	BN310P LED200/840 SRD H4 MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406022061	BN310P LED200/840 SRD H4 HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406022071	BN310P LED200/865 SRD H4 WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406022081	BN310P LED200/865 SRD H4 MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406022091	BN310P LED200/865 SRD H4 HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919506310581	BN310P Xitanium 60W Driver Spare Part	Safety class I	220 to 240 V	- Hz	60 W
820619284351	BN310P LED92/840 PSU HRO L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
820619284711	BN310P LED160/850 PSU WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
820619284721	BN310P LED160/850 PSU HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
820619284731	BN310P LED160/850 PSU MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
820619284761	BN310P LED92/850 PSU MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
820619284771	BN310P LED70/850 PSU WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	43 W
820619284781	BN310P LED130/850 PSU HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	87 W
820619284791	BN310P LED130/850 PSU MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	87 W
820619284801	BN310P LED130/850 PSU WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	87 W
919406020741	BN310P LED70/840 PSU WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	43 W
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406020761	BN310P LED92/840 PSU WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406020791	BN310P LED160/840 PSU WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406020811	BN310P LED160/840PSD- VLC WB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406020821	BN310P LED70/865 PSU MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	43 W
919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406020841	BN310P LED92/830 PSU DA L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W

SlimPerform Batten

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406020881	BN310P LED160/865 PSU HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406020901	BN310P LED92/865 PSU DA L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406020921	BN310P LED70/840 PSU MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	43 W
919406020931	BN310P LED160/840 PSU HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406020951	BN310P LED70/865 PSU WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	43 W
919406020961	BN310P LED70/865 PSD- VLC WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406020971	BN310P LED70/840 PSD- VLC MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406020991	BN310P LED70/840 PSD- VLC WB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406021001	BN310P LED70/830 PSU MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	43 W
919406021011	BN310P LED70/830 PSD- VLC MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406021021	BN310P LED70/830 PSU WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	43 W
919406021031	BN310P LED70/830 PSD- VLC WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406021041	BN310P LED92/865 PSU MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021051	BN310P LED92/865 PSD- VLC MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021071	BN310P LED92/865 PSD- VLC MB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021081	BN310P LED92/865 PSU WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021091	BN310P LED92/865 PSD- VLC WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021101	BN310P LED92/865 PSU WB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021111	BN310P LED92/865 PSD WB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021121	BN310P LED92/865 PSU DA EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021131	BN310P LED92/865 PSD- VLC DA EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021141	BN310P LED92/840 PSU MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021151	BN310P LED92/840 PSD- VLC MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021161	BN310P LED92/840 PSU MB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021171	BN310P LED92/840 PSD- VLC MB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021181	BN310P LED92/840 PSU WB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021191	BN310P LED92/840 PSU DA EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W

SlimPerform Batten

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406021201	BN310P LED92/840 PSD- VLC DA EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021211	BN310P LED92/830 PSU MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021221	BN310P LED92/830 PSD- VLC MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021231	BN310P LED92/830 PSU MB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021241	BN310P LED92/830 PSD- VLC MB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021251	BN310P LED92/830 PSU WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021261	BN310P LED92/830 PSD- VLC WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021281	BN310P LED92/830 PSD- VLC WB EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W
919406021301	BN310P LED92/830 PSD- VLC DA EL L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021341	BN310P LED160/865 PSU MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406021351	BN310P LED160/865 PSD- VLC MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406021371	BN310P LED160/865 PSD- VLC MB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406021381	BN310P LED160/865 PSU WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406021391	BN310P LED160/865 PSD- VLC WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406021411	BN310P LED160/865 PSD- VLC WB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406021431	BN310P LED160/865PSD- VLC HRO EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406021441	BN310P LED160/840 PSU MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406021451	BN310P LED160/840 PSD- VLC MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406021461	BN310P LED160/840 PSU MB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406021471	BN310P LED160/840 PSD- VLC MB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406021481	BN310P LED160/840 PSU WB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406021491	BN310P LED160/840 PSD- VLC HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	101 W
919406021511	BN310P LED160/840PSD- VLC HRO EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	102 W
919406021521	BN310P LED92/840 PSU DA L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	56 W

SlimPerform Batten

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406021531	BN310P LED92/840 PSD- VLC DA L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	58 W
919406021621	BN310P LED200/840 PSD- VLC WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021631	BN310P LED200/840 PSD- VLC HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021641	BN310P LED200/840 PSD- VLC MB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021651	BN310P LED200/840 PSD- VLC MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021661	BN310P LED200/840 PSU HRO EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021671	BN310P LED200/840 PSU HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021681	BN310P LED200/840 PSU MB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021691	BN310P LED200/840 PSU MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021701	BN310P LED200/840 PSU WB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021711	BN310P LED200/840 PSU WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021721	BN310P LED200/840PSD- VLC WB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021731	BN310P LED200/840PSD- VLC HRO EL L1700WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021741	BN310P LED200/865 PSD- V LC HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021751	BN310P LED200/865 PSD- VLC MB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406021761	BN310P LED200/865 PSD- VLC MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021771	BN310P LED200/865 PSD- VLC WB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021781	BN310P LED200/865 PSD- VLC WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021791	BN310P LED200/865 PSU HRO EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021801	BN310P LED200/865 PSU HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021811	BN310P LED200/865 PSU MB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021821	BN310P LED200/865 PSU MB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021831	BN310P LED200/865 PSU WB EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021841	BN310P LED200/865 PSU WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021851	BN310P LED200/865PSD- VLC HRO EL L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	129 W
919406021861	BN310P LED70/840 WIA WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406021871	BN310P LED70/840 WIA MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406021881	BN310P LED70/865 WIA WB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406021891	BN310P LED70/865 WIA MB L1150 WH	Safety class I	220 to 240 V	50 or 60 Hz	44 W
919406022101	BN310P LED230/840 PSD- VLC WB L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	153 W
919406022111	BN310P LED230/840 PSD- VLC HRO L1700 WH	Safety class I	220 to 240 V	50 or 60 Hz	153 W

SlimPerform Batten

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406022121	BN310P	Safety	220 to	50 or 60	153 W
	LED230/840 PSD-	class I	240 V	Hz	
	VLC MB L1700 WH				
919406022131	BN310P	Safety	220 to	50 or 60	153 W
	LED230/840 PSU	class I	240 V	Hz	
	HRO L1700 WH				
919406022141	BN310P	Safety	220 to	50 or 60	153 W
	LED230/840 PSU	class I	240 V	Hz	
	MB L1700 WH				
919406022151	BN310P	Safety	220 to	50 or 60	153 W
	LED230/840 PSU	class I	240 V	Hz	
	WB L1700 WH				
820619283931	BN310P	Safety	220 to	50 or 60	56 W
	LED92/840 PSU	class I	240 V	Hz	
	MB L1150 BK				
820619284281	BN310P	Safety	220 to	50 or 60	56 W
	LED92/865 PSU	class I	240 V	Hz	
	MB L1150 BK				
820619284431	BN310P	Safety	220 to	50 or 60	56 W
	LED92/830 PSU	class I	240 V	Hz	
	MB L1150 BK				
820619284681	BN310P	Safety	220 to	50 or 60	43 W
	LED70/840 PSU	class I	240 V	Hz	
	WB L1150 BK				
820619284691	BN310P	Safety	220 to	50 or 60	43 W
	LED70/840 PSU	class I	240 V	Hz	
	WB EL L1150 BK				
820619284701	BN310P	Safety	220 to	50 or 60	43 W
	LED70/830 PSU	class I	240 V	Hz	
	MB L1150 BK				

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
919406021901	BN310P LED92/840 SRD H4 WB L1150 WH	Wireless Dim	Programmable
919406021911	BN310P LED92/840 SRD H4 MB L1150 WH	Wireless Dim	Programmable
919406021921	BN310P LED92/840 SRD H4 HRO L1150 WH	Wireless Dim	Programmable
919406021931	BN310P LED92/840 SRD H4 DA L1150 WH	Wireless Dim	Programmable
919406021941	BN310P LED92/865 SRD H4 WB L1150 WH	Wireless Dim	Programmable
919406021951	BN310P LED92/865 SRD H4 MB L1150 WH	Wireless Dim	Programmable
919406021961	BN310P LED92/865 SRD H4 HRO L1150 WH	Wireless Dim	Programmable
919406021971	BN310P LED92/865 SRD H4 DA L1150 WH	Wireless Dim	Programmable

Order Code	Full Product Name	Protection class IEC	Input Voltage	Line Frequency	Power Consumption
919406020861	BN310P	Safety	220 to	50 or 60	56 W
	LED92/840 PSU	class I	240 V	Hz	
	DA L1150 BK				
919406020871	BN310P	Safety	220 to	50 or 60	58 W
	LED92/840 PSD-	class I	240 V	Hz	
	VLC DA L1150 BK				
919406021311	BN310P	Safety	220 to	50 or 60	58 W
	LED92/840 PSD-	class I	240 V	Hz	
	VLC WB L1150 BK				
919406021321	BN310P	Safety	220 to	50 or 60	56 W
	LED92/840 PSU	class I	240 V	Hz	
	WB EL L1150 BK				
919406021331	BN310P	Safety	220 to	50 or 60	58 W
	LED92/840 PSD-	class I	240 V	Hz	
	VLC WB EL L1150 BK				
919506310591	BN310P Xitanium 100W Driver Spare Part	Safety class I	220 to 240 V	- Hz	100 W
919506310621	BN310P Bracket White Spare Part	-	- V	- Hz	0 W
919506310631	BN310P Bracket Black Spare Part	-	- V	- Hz	0 W
919506310601	BN310P CertaDrive 44W Driver Spare Part	Safety class I	220 to 240 V	- Hz	44 W
919506310611	BN310P CertaDrive 65W Driver Spare Part	Safety class I	220 to 240 V	- Hz	65 W

Order Code	Full Product Name	Dimmable	Maximum dim level
919406021981	BN310P LED160/840 SRD H4 WB L1700 WH	Wireless Dim	Programmable
919406021991	BN310P LED160/840 SRD H4 MB L1700 WH	Wireless Dim	Programmable
919406022001	BN310P LED160/840 SRD H4 HRO L1700 WH	Wireless Dim	Programmable
919406022011	BN310P LED160/865 SRD H4 WB L1700 WH	Wireless Dim	Programmable
919406022021	BN310P LED160/865 SRD H4 MB L1700 WH	Wireless Dim	Programmable
919406022031	BN310P LED160/865 SRD H4 HRO L1700 WH	Wireless Dim	Programmable
919406022041	BN310P LED200/840 SRD H4 WB L1700 WH	Wireless Dim	Programmable
919406022051	BN310P LED200/840 SRD H4 MB L1700 WH	Wireless Dim	Programmable

SlimPerform Batten

Order Code	Full Product Name	Dimmable	Maximum dim level
919406022061	BN310P LED200/840 SRD H4 HRO L1700 WH	Wireless Dim	Programmable
919406022071	BN310P LED200/865 SRD H4 WB L1700 WH	Wireless Dim	Programmable
919406022081	BN310P LED200/865 SRD H4 MB L1700 WH	Wireless Dim	Programmable
919406022091	BN310P LED200/865 SRD H4 HRO L1700 WH	Wireless Dim	Programmable
919506310581	BN310P Xitanium 60W Driver Spare Part	Yes	-
820619284351	BN310P LED92/840 PSU HRO L1150 WH	No	Not applicable
820619284711	BN310P LED160/850 PSU WB L1700 WH	No	Not applicable
820619284721	BN310P LED160/850 PSU HRO L1700 WH	No	Not applicable
820619284731	BN310P LED160/850 PSU MB L1700 WH	No	Not applicable
820619284761	BN310P LED92/850 PSU MB L1150 WH	No	Not applicable
820619284771	BN310P LED70/850 PSU WB L1150 WH	No	Not applicable
820619284781	BN310P LED130/850 PSU HRO L1700 WH	No	Not applicable
820619284791	BN310P LED130/850 PSU MB L1700 WH	No	Not applicable
820619284801	BN310P LED130/850 PSU WB L1700 WH	No	Not applicable
919406020741	BN310P LED70/840 PSU WB L1150 WH	No	Not applicable
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	Yes	1%
919406020761	BN310P LED92/840 PSU WB L1150 WH	No	Not applicable
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	Yes	1%
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	Yes	1%
919406020791	BN310P LED160/840 PSU WB L1700 WH	No	Not applicable
919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	Yes	1%
919406020811	BN310P LED160/840PSD- VLC WB EL L1700 WH	Yes	1%
919406020821	BN310P LED70/865 PSU MB L1150 WH	No	Not applicable
919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	Yes	1%
919406020841	BN310P LED92/830 PSU DA L1150 WH	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	Yes	1%
919406020881	BN310P LED160/865 PSU HRO L1700 WH	No	Not applicable
919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	Yes	1%
919406020901	BN310P LED92/865 PSU DA L1150 WH	No	Not applicable
919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	Yes	1%
919406020921	BN310P LED70/840 PSU MB L1150 WH	No	Not applicable
919406020931	BN310P LED160/840 PSU HRO L1700 WH	No	Not applicable
919406020951	BN310P LED70/865 PSU WB L1150 WH	No	Not applicable
919406020961	BN310P LED70/865 PSD-VLC WB L1150 WH	Yes	1%
919406020971	BN310P LED70/840 PSD-VLC MB L1150 WH	Yes	1%
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	No	Not applicable
919406020991	BN310P LED70/840 PSD-VLC WB EL L1150 WH	Yes	1%
919406021001	BN310P LED70/830 PSU MB L1150 WH	No	Not applicable
919406021011	BN310P LED70/830 PSD-VLC MB L1150 WH	Yes	1%
919406021021	BN310P LED70/830 PSU WB L1150 WH	No	Not applicable
919406021031	BN310P LED70/830 PSD-VLC WB L1150 WH	Yes	1%
919406021041	BN310P LED92/865 PSU MB L1150 WH	No	Not applicable
919406021051	BN310P LED92/865 PSD-VLC MB L1150 WH	Yes	1%
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	No	Not applicable
919406021071	BN310P LED92/865 PSD-VLC MB EL L1150 WH	Yes	1%
919406021081	BN310P LED92/865 PSU WB L1150 WH	No	Not applicable
919406021091	BN310P LED92/865 PSD-VLC WB L1150 WH	Yes	1%
919406021101	BN310P LED92/865 PSU WB EL L1150 WH	No	Not applicable
919406021111	BN310P LED92/865 PSD WB EL L1150 WH	Yes	1%
919406021121	BN310P LED92/865 PSU DA EL L1150 WH	No	Not applicable

SlimPerform Batten

Order Code	Full Product Name	Dimmable	Maximum dim level
919406021131	BN310P LED92/865 PSD-VLC DA EL L1150 WH	Yes	1%
919406021141	BN310P LED92/840 PSU MB L1150 WH	No	Not applicable
919406021151	BN310P LED92/840 PSD-VLC MB L1150 WH	Yes	1%
919406021161	BN310P LED92/840 PSU MB EL L1150 WH	No	Not applicable
919406021171	BN310P LED92/840 PSD-VLC MB EL L1150 WH	Yes	1%
919406021181	BN310P LED92/840 PSU WB EL L1150 WH	No	Not applicable
919406021191	BN310P LED92/840 PSU DA EL L1150 WH	No	Not applicable
919406021201	BN310P LED92/840 PSD-VLC DA EL L1150 WH	Yes	1%
919406021211	BN310P LED92/830 PSU MB L1150 WH	No	Not applicable
919406021221	BN310P LED92/830 PSD-VLC MB L1150 WH	Yes	1%
919406021231	BN310P LED92/830 PSU MB EL L1150 WH	No	Not applicable
919406021241	BN310P LED92/830 PSD-VLC MB EL L1150 WH	Yes	1%
919406021251	BN310P LED92/830 PSU WB L1150 WH	No	Not applicable
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	Yes	1%
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	No	Not applicable
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	Yes	1%
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	No	Not applicable
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	Yes	1%
919406021341	BN310P LED160/865 PSU MB L1700 WH	No	Not applicable
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	Yes	1%
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	No	Not applicable
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	Yes	1%
919406021381	BN310P LED160/865 PSU WB L1700 WH	No	Not applicable
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	Yes	1%
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
919406021411	BN310P LED160/865 PSD-VLC WB EL L1700 WH	Yes	1%
919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	No	Not applicable
919406021431	BN310P LED160/865PSD-VLC HRO EL L1700 WH	Yes	1%
919406021441	BN310P LED160/840 PSU MB L1700 WH	No	Not applicable
919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	Yes	1%
919406021461	BN310P LED160/840 PSU MB EL L1700 WH	No	Not applicable
919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	Yes	1%
919406021481	BN310P LED160/840 PSU WB EL L1700 WH	No	Not applicable
919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	Yes	1%
919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	No	Not applicable
919406021511	BN310P LED160/840PSD-VLC HRO EL L1700 WH	Yes	1%
919406021521	BN310P LED92/840 PSU DA L1150 WH	No	Not applicable
919406021531	BN310P LED92/840 PSD- VLC DA L1150 WH	Yes	1%
919406021621	BN310P LED200/840 PSD- VLC WB L1700 WH	Yes	1%
919406021631	BN310P LED200/840 PSD-VLC HRO L1700 WH	Yes	1%
919406021641	BN310P LED200/840 PSD-VLC MB EL L1700 WH	Yes	1%
919406021651	BN310P LED200/840 PSD-VLC MB L1700 WH	Yes	1%
919406021661	BN310P LED200/840 PSU HRO EL L1700 WH	No	Not applicable
919406021671	BN310P LED200/840 PSU HRO L1700 WH	No	Not applicable
919406021681	BN310P LED200/840 PSU MB EL L1700 WH	No	Not applicable
919406021691	BN310P LED200/840 PSU MB L1700 WH	No	Not applicable
919406021701	BN310P LED200/840 PSU WB EL L1700 WH	No	Not applicable
919406021711	BN310P LED200/840 PSU WB L1700 WH	No	Not applicable
919406021721	BN310P LED200/840PSD-VLC WB EL L1700 WH	Yes	1%
919406021731	BN310P LED200/840PSD-VLC HRO EL L1700WH	Yes	1%

SlimPerform Batten

Order Code	Full Product Name	Dimmable	Maximum dim level
919406021741	BN310P LED200/865 PSD-V LC HRO L1700 WH	Yes	1%
919406021751	BN310P LED200/865 PSD-VLC MB EL L1700 WH	Yes	1%
919406021761	BN310P LED200/865 PSD-VLC MB L1700 WH	Yes	1%
919406021771	BN310P LED200/865 PSD-VLC WB EL L1700 WH	Yes	1%
919406021781	BN310P LED200/865 PSD-VLC WB L1700 WH	Yes	1%
919406021791	BN310P LED200/865 PSU HRO EL L1700 WH	No	Not applicable
919406021801	BN310P LED200/865 PSU HRO L1700 WH	No	Not applicable
919406021811	BN310P LED200/865 PSU MB EL L1700 WH	No	Not applicable
919406021821	BN310P LED200/865 PSU MB L1700 WH	No	Not applicable
919406021831	BN310P LED200/865 PSU WB EL L1700 WH	No	Not applicable
919406021841	BN310P LED200/865 PSU WB L1700 WH	No	Not applicable
919406021851	BN310P LED200/865PSD-VLC HRO EL L1700 WH	Yes	1%
919406021861	BN310P LED70/840 WIA WB L1150 WH	Wireless Dim	Programmable
919406021871	BN310P LED70/840 WIA MB L1150 WH	Wireless Dim	Programmable
919406021881	BN310P LED70/865 WIA WB L1150 WH	Wireless Dim	Programmable
919406021891	BN310P LED70/865 WIA MB L1150 WH	Wireless Dim	Programmable
919406022101	BN310P LED230/840 PSD- VLC WB L1700 WH	Yes	1%
919406022111	BN310P LED230/840 PSD-VLC HRO L1700 WH	Yes	1%
919406022121	BN310P LED230/840 PSD-VLC MB L1700 WH	Yes	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
919406022131	BN310P LED230/840 PSU HRO L1700 WH	No	Not applicable
919406022141	BN310P LED230/840 PSU MB L1700 WH	No	Not applicable
919406022151	BN310P LED230/840 PSU WB L1700 WH	No	Not applicable
820619283931	BN310P LED92/840 PSU MB L1150 BK	No	Not applicable
820619284281	BN310P LED92/865 PSU MB L1150 BK	No	Not applicable
820619284431	BN310P LED92/830 PSU MB L1150 BK	No	Not applicable
820619284681	BN310P LED70/840 PSU WB L1150 BK	No	Not applicable
820619284691	BN310P LED70/840 PSU WB EL L1150 BK	No	Not applicable
820619284701	BN310P LED70/830 PSU MB L1150 BK	No	Not applicable
919406020861	BN310P LED92/840 PSU DA L1150 BK	No	Not applicable
919406020871	BN310P LED92/840 PSD- VLC DA L1150 BK	Yes	1%
919406021311	BN310P LED92/840 PSD-VLC WB L1150 BK	Yes	1%
919406021321	BN310P LED92/840 PSU WB EL L1150 BK	No	Not applicable
919406021331	BN310P LED92/840 PSD-VLC WB EL L1150 BK	Yes	1%
919506310591	BN310P Xitanium 100W Driver Spare Part	Yes	-
919506310621	BN310P Bracket White Spare Part	No	-
919506310631	BN310P Bracket Black Spare Part	No	-
919506310601	BN310P CertaDrive 44W Driver Spare Part	No	-
919506310611	BN310P CertaDrive 65W Driver Spare Part	No	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Ingress protection code
919406021901	BN310P LED92/840 SRD H4 WB L1150 WH	White	IP20
919406021911	BN310P LED92/840 SRD H4 MB L1150 WH	White	IP20
919406021921	BN310P LED92/840 SRD H4 HRO L1150 WH	White	IP20
919406021931	BN310P LED92/840 SRD H4 DA L1150 WH	White	IP20
919406021941	BN310P LED92/865 SRD H4 WB L1150 WH	White	IP20
919406021951	BN310P LED92/865 SRD H4 MB L1150 WH	White	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
919406021961	BN310P LED92/865 SRD H4 HRO L1150 WH	White	IP20
919406021971	BN310P LED92/865 SRD H4 DA L1150 WH	White	IP20
919406021981	BN310P LED160/840 SRD H4 WB L1700 WH	White	IP20
919406021991	BN310P LED160/840 SRD H4 MB L1700 WH	White	IP20

SlimPerform Batten

Order Code	Full Product Name	Housing Color	Ingress protection code
919406022001	BN310P LED160/840 SRD H4 HRO L1700 WH	White	IP20
919406022011	BN310P LED160/865 SRD H4 WB L1700 WH	White	IP20
919406022021	BN310P LED160/865 SRD H4 MB L1700 WH	White	IP20
919406022031	BN310P LED160/865 SRD H4 HRO L1700 WH	White	IP20
919406022041	BN310P LED200/840 SRD H4 WB L1700 WH	White	IP20
919406022051	BN310P LED200/840 SRD H4 MB L1700 WH	White	IP20
919406022061	BN310P LED200/840 SRD H4 HRO L1700 WH	White	IP20
919406022071	BN310P LED200/865 SRD H4 WB L1700 WH	White	IP20
919406022081	BN310P LED200/865 SRD H4 MB L1700 WH	White	IP20
919406022091	BN310P LED200/865 SRD H4 HRO L1700 WH	White	IP20
919506310581	BN310P Xitanium 60W Driver Spare Part	White	IP20
820619284351	BN310P LED92/840 PSU HRO L1150 WH	White	IP20
820619284711	BN310P LED160/850 PSU WB L1700 WH	White	IP20
820619284721	BN310P LED160/850 PSU HRO L1700 WH	White	IP20
820619284731	BN310P LED160/850 PSU MB L1700 WH	White	IP20
820619284761	BN310P LED92/850 PSU MB L1150 WH	White	IP20
820619284771	BN310P LED70/850 PSU WB L1150 WH	White	IP20
820619284781	BN310P LED130/850 PSU HRO L1700 WH	White	IP20
820619284791	BN310P LED130/850 PSU MB L1700 WH	White	IP20
820619284801	BN310P LED130/850 PSU WB L1700 WH	White	IP20
919406020741	BN310P LED70/840 PSU WB L1150 WH	White	IP20
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	White	IP20
919406020761	BN310P LED92/840 PSU WB L1150 WH	White	IP20
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	White	IP20
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	White	IP23
919406020791	BN310P LED160/840 PSU WB L1700 WH	White	IP20
919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	White	IP20
919406020811	BN310P LED160/840PSD- VLC WB EL L1700 WH	White	IP20
919406020821	BN310P LED70/865 PSU MB L1150 WH	White	IP20
919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	White	IP20
919406020841	BN310P LED92/830 PSU DA L1150 WH	White	IP20
919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	White	IP20
919406020881	BN310P LED160/865 PSU HRO L1700 WH	White	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	White	IP20
919406020901	BN310P LED92/865 PSU DA L1150 WH	White	IP20
919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	White	IP20
919406020921	BN310P LED70/840 PSU MB L1150 WH	White	IP20
919406020931	BN310P LED160/840 PSU HRO L1700 WH	White	IP20
919406020951	BN310P LED70/865 PSU WB L1150 WH	White	IP20
919406020961	BN310P LED70/865 PSD-VLC WB L1150 WH	White	IP20
919406020971	BN310P LED70/840 PSD-VLC MB L1150 WH	White	IP20
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	White	IP23
919406020991	BN310P LED70/840 PSD-VLC WB EL L1150 WH	White	IP23
919406021001	BN310P LED70/830 PSU MB L1150 WH	White	IP20
919406021011	BN310P LED70/830 PSD-VLC MB L1150 WH	White	IP20
919406021021	BN310P LED70/830 PSU WB L1150 WH	White	IP20
919406021031	BN310P LED70/830 PSD-VLC WB L1150 WH	White	IP20
919406021041	BN310P LED92/865 PSU MB L1150 WH	White	IP20
919406021051	BN310P LED92/865 PSD-VLC MB L1150 WH	White	IP20
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	White	IP23
919406021071	BN310P LED92/865 PSD-VLC MB EL L1150 WH	White	IP23
919406021081	BN310P LED92/865 PSU WB L1150 WH	White	IP20
919406021091	BN310P LED92/865 PSD-VLC WB L1150 WH	White	IP20
919406021101	BN310P LED92/865 PSU WB EL L1150 WH	White	IP23
919406021111	BN310P LED92/865 PSD WB EL L1150 WH	White	IP23
919406021121	BN310P LED92/865 PSU DA EL L1150 WH	White	IP23
919406021131	BN310P LED92/865 PSD-VLC DA EL L1150 WH	White	IP23
919406021141	BN310P LED92/840 PSU MB L1150 WH	White	IP20
919406021151	BN310P LED92/840 PSD-VLC MB L1150 WH	White	IP20
919406021161	BN310P LED92/840 PSU MB EL L1150 WH	White	IP23
919406021171	BN310P LED92/840 PSD-VLC MB EL L1150 WH	White	IP23
919406021181	BN310P LED92/840 PSU WB EL L1150 WH	White	IP23
919406021191	BN310P LED92/840 PSU DA EL L1150 WH	White	IP23
919406021201	BN310P LED92/840 PSD-VLC DA EL L1150 WH	White	IP23
919406021211	BN310P LED92/830 PSU MB L1150 WH	White	IP20
919406021221	BN310P LED92/830 PSD-VLC MB L1150 WH	White	IP20
919406021231	BN310P LED92/830 PSU MB EL L1150 WH	White	IP23

SlimPerform Batten

Order Code	Full Product Name	Housing Color	Ingress protection code
919406021241	BN310P LED92/830 PSD-VLC MB EL L1150 WH	White	IP23
919406021251	BN310P LED92/830 PSU WB L1150 WH	White	IP20
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	White	IP20
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	White	IP23
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	White	IP23
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	White	IP23
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	White	IP23
919406021341	BN310P LED160/865 PSU MB L1700 WH	White	IP20
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	White	IP20
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	White	IP23
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	White	IP23
919406021381	BN310P LED160/865 PSU WB L1700 WH	White	IP20
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	White	IP20
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	White	IP23
919406021411	BN310P LED160/865 PSD-VLC WB EL L1700 WH	White	IP23
919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	White	IP23
919406021431	BN310P LED160/865PSD-VLC HRO EL L1700 WH	White	IP23
919406021441	BN310P LED160/840 PSU MB L1700 WH	White	IP20
919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	White	IP20
919406021461	BN310P LED160/840 PSU MB EL L1700 WH	White	IP23
919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	White	IP23
919406021481	BN310P LED160/840 PSU WB EL L1700 WH	White	IP23
919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	White	IP20
919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	White	IP23
919406021511	BN310P LED160/840PSD-VLC HRO EL L1700 WH	White	IP23
919406021521	BN310P LED92/840 PSU DA L1150 WH	White	IP20
919406021531	BN310P LED92/840 PSD- VLC DA L1150 WH	White	IP20
919406021621	BN310P LED200/840 PSD- VLC WB L1700 WH	White	IP20

Order Code	Full Product Name	Housing Color	Ingress protection code
919406021631	BN310P LED200/840 PSD-VLC HRO L1700 WH	White	IP20
919406021641	BN310P LED200/840 PSD-VLC MB EL L1700 WH	White	IP23
919406021651	BN310P LED200/840 PSD-VLC MB L1700 WH	White	IP20
919406021661	BN310P LED200/840 PSU HRO EL L1700 WH	White	IP23
919406021671	BN310P LED200/840 PSU HRO L1700 WH	White	IP20
919406021681	BN310P LED200/840 PSU MB EL L1700 WH	White	IP23
919406021691	BN310P LED200/840 PSU MB L1700 WH	White	IP20
919406021701	BN310P LED200/840 PSU WB EL L1700 WH	White	IP23
919406021711	BN310P LED200/840 PSU WB L1700 WH	White	IP20
919406021721	BN310P LED200/840PSD-VLC WB EL L1700 WH	White	IP23
919406021731	BN310P LED200/840PSD-VLC HRO EL L1700WH	White	IP23
919406021741	BN310P LED200/865 PSD-V LC HRO L1700 WH	White	IP20
919406021751	BN310P LED200/865 PSD-VLC MB EL L1700 WH	White	IP23
919406021761	BN310P LED200/865 PSD-VLC MB L1700 WH	White	IP20
919406021771	BN310P LED200/865 PSD-VLC WB EL L1700 WH	White	IP23
919406021781	BN310P LED200/865 PSD-VLC WB L1700 WH	White	IP20
919406021791	BN310P LED200/865 PSU HRO EL L1700 WH	White	IP23
919406021801	BN310P LED200/865 PSU HRO L1700 WH	White	IP20
919406021811	BN310P LED200/865 PSU MB EL L1700 WH	White	IP23
919406021821	BN310P LED200/865 PSU MB L1700 WH	White	IP20
919406021831	BN310P LED200/865 PSU WB EL L1700 WH	White	IP23
919406021841	BN310P LED200/865 PSU WB L1700 WH	White	IP20
919406021851	BN310P LED200/865PSD-VLC HRO EL L1700 WH	White	IP23
919406021861	BN310P LED70/840 WIA WB L1150 WH	White	IP20
919406021871	BN310P LED70/840 WIA MB L1150 WH	White	IP20
919406021881	BN310P LED70/865 WIA WB L1150 WH	White	IP20
919406021891	BN310P LED70/865 WIA MB L1150 WH	White	IP20
919406022101	BN310P LED230/840 PSD- VLC WB L1700 WH	White	IP20
919406022111	BN310P LED230/840 PSD-VLC HRO L1700 WH	White	IP20
919406022121	BN310P LED230/840 PSD-VLC MB L1700 WH	White	IP20

SlimPerform Batten

Order Code	Full Product Name	Housing	Ingress
		Color	protection code
919406022131	BN310P LED230/840 PSU HRO L1700 WH	White	IP20
919406022141	BN310P LED230/840 PSU MB L1700 WH	White	IP20
919406022151	BN310P LED230/840 PSU WB L1700 WH	White	IP20
820619283931	BN310P LED92/840 PSU MB L1150 BK	Black	IP20
820619284281	BN310P LED92/865 PSU MB L1150 BK	Black	IP20
820619284431	BN310P LED92/830 PSU MB L1150 BK	Black	IP20
820619284681	BN310P LED70/840 PSU WB L1150 BK	Black	IP20
820619284691	BN310P LED70/840 PSU WB EL L1150 BK	Black	IP23
820619284701	BN310P LED70/830 PSU MB L1150 BK	Black	IP20
919406020861	BN310P LED92/840 PSU DA L1150 BK	Black	IP20
919406020871	BN310P LED92/840 PSD- VLC DA L1150 BK	Black	IP20

Approval and Application

Order Code	Full Product Name	Ambient temperature
		range
919406021901	BN310P LED92/840 SRD H4 WB L1150 WH	-20 to +45 °C
919406021911	BN310P LED92/840 SRD H4 MB L1150 WH	-20 to +45 °C
919406021921	BN310P LED92/840 SRD H4 HRO L1150 WH	-20 to +45 °C
919406021931	BN310P LED92/840 SRD H4 DA L1150 WH	-20 to +45 °C
919406021941	BN310P LED92/865 SRD H4 WB L1150 WH	-20 to +45 °C
919406021951	BN310P LED92/865 SRD H4 MB L1150 WH	-20 to +45 °C
919406021961	BN310P LED92/865 SRD H4 HRO L1150 WH	-20 to +45 °C
919406021971	BN310P LED92/865 SRD H4 DA L1150 WH	-20 to +45 °C
919406021981	BN310P LED160/840 SRD H4 WB L1700 WH	-20 to +45 °C
919406021991	BN310P LED160/840 SRD H4 MB L1700 WH	-20 to +45 °C
919406022001	BN310P LED160/840 SRD H4 HRO L1700 WH	-20 to +45 °C
919406022011	BN310P LED160/865 SRD H4 WB L1700 WH	-20 to +45 °C
919406022021	BN310P LED160/865 SRD H4 MB L1700 WH	-20 to +45 °C
919406022031	BN310P LED160/865 SRD H4 HRO L1700 WH	-20 to +45 °C
919406022041	BN310P LED200/840 SRD H4 WB L1700 WH	-20 to +45 °C
919406022051	BN310P LED200/840 SRD H4 MB L1700 WH	-20 to +45 °C
919406022061	BN310P LED200/840 SRD H4 HRO L1700 WH	-20 to +45 °C
919406022071	BN310P LED200/865 SRD H4 WB L1700 WH	-20 to +45 °C
919406022081	BN310P LED200/865 SRD H4 MB L1700 WH	-20 to +45 °C

Order Code	Full Product Name	Housing	Ingress
		Color	protection code
919406021311	BN310P LED92/840 PSD-VLC WB L1150 BK	Black	IP20
919406021321	BN310P LED92/840 PSU WB EL L1150 BK	Black	IP23
919406021331	BN310P LED92/840 PSD-VLC WB EL L1150 BK	Black	IP23
919506310591	BN310P Xitanium 100W Driver Spare Part	White	IP20
919506310621	BN310P Bracket White Spare Part	White	-
919506310631	BN310P Bracket Black Spare Part	Black	-
919506310601	BN310P CertaDrive 44W Driver Spare Part	White	IP20
919506310611	BN310P CertaDrive 65W Driver Spare Part	White	IP20

Order Code	Full Product Name	Ambient temperature
		range
919406022091	BN310P LED200/865 SRD H4 HRO L1700 WH	-20 to +45 °C
919506310581	BN310P Xitanium 60W Driver Spare Part	-20 to +45 °C
820619284351	BN310P LED92/840 PSU HRO L1150 WH	-20 to +45 °C
820619284711	BN310P LED160/850 PSU WB L1700 WH	-20 to +45 °C
820619284721	BN310P LED160/850 PSU HRO L1700 WH	-20 to +45 °C
820619284731	BN310P LED160/850 PSU MB L1700 WH	-20 to +45 °C
820619284761	BN310P LED92/850 PSU MB L1150 WH	-20 to +45 °C
820619284771	BN310P LED70/850 PSU WB L1150 WH	-20 to +45 °C
820619284781	BN310P LED130/850 PSU HRO L1700 WH	-20 to +45 °C
820619284791	BN310P LED130/850 PSU MB L1700 WH	-20 to +45 °C
820619284801	BN310P LED130/850 PSU WB L1700 WH	-20 to +45 °C
919406020741	BN310P LED70/840 PSU WB L1150 WH	-20 to +35 °C
919406020751	BN310P LED70/840 PSD- VLC WB L1150 WH	-20 to +35 °C
919406020761	BN310P LED92/840 PSU WB L1150 WH	-20 to +35 °C
919406020771	BN310P LED92/840 PSD- VLC WB L1150 WH	-20 to +35 °C
919406020781	BN310P LED92/840 PSD- VLC WB EL L1150 WH	-20 to +35 °C
919406020791	BN310P LED160/840 PSU WB L1700 WH	-20 to +35 °C
919406020801	BN310P LED160/840 PSD- VLC WB L1700 WH	-20 to +35 °C
919406020811	BN310P LED160/840PSD- VLC WB EL L1700 WH	-20 to +35 °C
919406020821	BN310P LED70/865 PSU MB L1150 WH	-20 to +35 °C
919406020831	BN310P LED70 /865 PSD- VLC MB L1150 WH	-20 to +35 °C
919406020841	BN310P LED92/830 PSU DA L1150 WH	-20 to +35 °C
919406020851	BN310P LED92/830 PSD- VLC DA L1150 WH	-20 to +35 °C
919406020881	BN310P LED160/865 PSU HRO L1700 WH	-20 to +35 °C

SlimPerform Batten

Order Code	Full Product Name	Ambient temperature range
919406020891	BN310P LED160/865 PSD- VLC HRO L1700 WH	-20 to +35 °C
919406020901	BN310P LED92/865 PSU DA L1150 WH	-20 to +35 °C
919406020911	BN310P LED92/865 PSD- VLC DA L1150 WH	-20 to +35 °C
919406020921	BN310P LED70/840 PSU MB L1150 WH	-20 to +35 °C
919406020931	BN310P LED160/840 PSU HRO L1700 WH	-20 to +35 °C
919406020951	BN310P LED70/865 PSU WB L1150 WH	-20 to +35 °C
919406020961	BN310P LED70/865 PSD-VLC WB L1150 WH	-20 to +35 °C
919406020971	BN310P LED70/840 PSD-VLC MB L1150 WH	-20 to +35 °C
919406020981	BN310P LED70/840 PSU WB EL L1150 WH	-20 to +35 °C
919406020991	BN310P LED70/840 PSD-VLC WB EL L1150 WH	-20 to +35 °C
919406021001	BN310P LED70/830 PSU MB L1150 WH	-20 to +35 °C
919406021011	BN310P LED70/830 PSD-VLC MB L1150 WH	-20 to +35 °C
919406021021	BN310P LED70/830 PSU WB L1150 WH	-20 to +35 °C
919406021031	BN310P LED70/830 PSD-VLC WB L1150 WH	-20 to +35 °C
919406021041	BN310P LED92/865 PSU MB L1150 WH	-20 to +35 °C
919406021051	BN310P LED92/865 PSD-VLC MB L1150 WH	-20 to +35 °C
919406021061	BN310P LED92/865 PSU MB EL L1150 WH	-20 to +35 °C
919406021071	BN310P LED92/865 PSD-VLC MB EL L1150 WH	-20 to +35 °C
919406021081	BN310P LED92/865 PSU WB L1150 WH	-20 to +35 °C
919406021091	BN310P LED92/865 PSD-VLC WB L1150 WH	-20 to +35 °C
919406021101	BN310P LED92/865 PSU WB EL L1150 WH	-20 to +35 °C
919406021111	BN310P LED92/865 PSD WB EL L1150 WH	-20 to +35 °C
919406021121	BN310P LED92/865 PSU DA EL L1150 WH	-20 to +35 °C
919406021131	BN310P LED92/865 PSD-VLC DA EL L1150 WH	-20 to +35 °C
919406021141	BN310P LED92/840 PSU MB L1150 WH	-20 to +35 °C
919406021151	BN310P LED92/840 PSD-VLC MB L1150 WH	-20 to +35 °C
919406021161	BN310P LED92/840 PSU MB EL L1150 WH	-20 to +35 °C
919406021171	BN310P LED92/840 PSD-VLC MB EL L1150 WH	-20 to +35 °C
919406021181	BN310P LED92/840 PSU WB EL L1150 WH	-20 to +35 °C
919406021191	BN310P LED92/840 PSU DA EL L1150 WH	-20 to +35 °C
919406021201	BN310P LED92/840 PSD-VLC DA EL L1150 WH	-20 to +35 °C
919406021211	BN310P LED92/830 PSU MB L1150 WH	-20 to +35 °C
919406021221	BN310P LED92/830 PSD-VLC MB L1150 WH	-20 to +35 °C
919406021231	BN310P LED92/830 PSU MB EL L1150 WH	-20 to +35 °C
919406021241	BN310P LED92/830 PSD-VLC MB EL L1150 WH	-20 to +35 °C

Order Code	Full Product Name	Ambient temperature range
919406021251	BN310P LED92/830 PSU WB L1150 WH	-20 to +35 °C
919406021261	BN310P LED92/830 PSD-VLC WB L1150 WH	-20 to +35 °C
919406021271	BN310P LED92/830 PSU WB EL L1150 WH	-20 to +35 °C
919406021281	BN310P LED92/830 PSD-VLC WB EL L1150 WH	-20 to +35 °C
919406021291	BN310P LED92/830 PSU DA EL L1150 WH	-20 to +35 °C
919406021301	BN310P LED92/830 PSD-VLC DA EL L1150 WH	-20 to +35 °C
919406021341	BN310P LED160/865 PSU MB L1700 WH	-20 to +35 °C
919406021351	BN310P LED160/865 PSD-VLC MB L1700 WH	-20 to +35 °C
919406021361	BN310P LED160/865 PSU MB EL L1700 WH	-20 to +35 °C
919406021371	BN310P LED160/865 PSD-VLC MB EL L1700 WH	-20 to +35 °C
919406021381	BN310P LED160/865 PSU WB L1700 WH	-20 to +35 °C
919406021391	BN310P LED160/865 PSD-VLC WB L1700 WH	-20 to +35 °C
919406021401	BN310P LED160/865 PSU WB EL L1700 WH	-20 to +35 °C
919406021411	BN310P LED160/865 PSD-VLC WB EL L1700 WH	-20 to +35 °C
919406021421	BN310P LED160/865 PSU HRO EL L1700 WH	-20 to +35 °C
919406021431	BN310P LED160/865PSD-VLC HRO EL L1700 WH	-20 to +35 °C
919406021441	BN310P LED160/840 PSU MB L1700 WH	-20 to +35 °C
919406021451	BN310P LED160/840 PSD-VLC MB L1700 WH	-20 to +35 °C
919406021461	BN310P LED160/840 PSU MB EL L1700 WH	-20 to +35 °C
919406021471	BN310P LED160/840 PSD-VLC MB EL L1700 WH	-20 to +35 °C
919406021481	BN310P LED160/840 PSU WB EL L1700 WH	-20 to +35 °C
919406021491	BN310P LED160/840 PSD-VLC HRO L1700 WH	-20 to +35 °C
919406021501	BN310P LED160/840 PSU HRO EL L1700 WH	-20 to +35 °C
919406021511	BN310P LED160/840PSD-VLC HRO EL L1700 WH	-20 to +35 °C
919406021521	BN310P LED92/840 PSU DA L1150 WH	-20 to +35 °C
919406021531	BN310P LED92/840 PSD- VLC DA L1150 WH	-20 to +35 °C
919406021621	BN310P LED200/840 PSD- VLC WB L1700 WH	-20 to +45 °C
919406021631	BN310P LED200/840 PSD-VLC HRO L1700 WH	-20 to +45 °C
919406021641	BN310P LED200/840 PSD-VLC MB EL L1700 WH	-20 to +45 °C

SlimPerform Batten

Order Code	Full Product Name	Ambient temperature range
919406021651	BN310P LED200/840 PSD-VLC MB L1700 WH	-20 to +45 °C
919406021661	BN310P LED200/840 PSU HRO EL L1700 WH	-20 to +45 °C
919406021671	BN310P LED200/840 PSU HRO L1700 WH	-20 to +45 °C
919406021681	BN310P LED200/840 PSU MB EL L1700 WH	-20 to +45 °C
919406021691	BN310P LED200/840 PSU MB L1700 WH	-20 to +45 °C
919406021701	BN310P LED200/840 PSU WB EL L1700 WH	-20 to +45 °C
919406021711	BN310P LED200/840 PSU WB L1700 WH	-20 to +45 °C
919406021721	BN310P LED200/840PSD-VLC WB EL L1700 WH	-20 to +45 °C
919406021731	BN310P LED200/840PSD-VLC HRO EL L1700WH	-20 to +45 °C
919406021741	BN310P LED200/865 PSD-V LC HRO L1700 WH	-20 to +45 °C
919406021751	BN310P LED200/865 PSD-VLC MB EL L1700 WH	-20 to +45 °C
919406021761	BN310P LED200/865 PSD-VLC MB L1700 WH	-20 to +45 °C
919406021771	BN310P LED200/865 PSD-VLC WB EL L1700 WH	-20 to +45 °C
919406021781	BN310P LED200/865 PSD-VLC WB L1700 WH	-20 to +45 °C
919406021791	BN310P LED200/865 PSU HRO EL L1700 WH	-20 to +45 °C
919406021801	BN310P LED200/865 PSU HRO L1700 WH	-20 to +45 °C
919406021811	BN310P LED200/865 PSU MB EL L1700 WH	-20 to +45 °C
919406021821	BN310P LED200/865 PSU MB L1700 WH	-20 to +45 °C
919406021831	BN310P LED200/865 PSU WB EL L1700 WH	-20 to +45 °C
919406021841	BN310P LED200/865 PSU WB L1700 WH	-20 to +45 °C

Order Code	Full Product Name	Ambient temperature range
919406021851	BN310P LED200/865PSD-VLC HRO EL L1700 WH	-20 to +45 °C
919406021861	BN310P LED70/840 WIA WB L1150 WH	-20 to +45 °C
919406021871	BN310P LED70/840 WIA MB L1150 WH	-20 to +45 °C
919406021881	BN310P LED70/865 WIA WB L1150 WH	-20 to +45 °C
919406021891	BN310P LED70/865 WIA MB L1150 WH	-20 to +45 °C
919406022101	BN310P LED230/840 PSD- VLC WB L1700 WH	-20 to +45 °C
919406022111	BN310P LED230/840 PSD-VLC HRO L1700 WH	-20 to +45 °C
919406022121	BN310P LED230/840 PSD-VLC MB L1700 WH	-20 to +45 °C
919406022131	BN310P LED230/840 PSU HRO L1700 WH	-20 to +45 °C
919406022141	BN310P LED230/840 PSU MB L1700 WH	-20 to +45 °C
919406022151	BN310P LED230/840 PSU WB L1700 WH	-20 to +45 °C
820619283931	BN310P LED92/840 PSU MB L1150 BK	-20 to +45 °C
820619284281	BN310P LED92/865 PSU MB L1150 BK	-20 to +45 °C
820619284431	BN310P LED92/830 PSU MB L1150 BK	-20 to +45 °C
820619284681	BN310P LED70/840 PSU WB L1150 BK	-20 to +45 °C
820619284691	BN310P LED70/840 PSU WB EL L1150 BK	-20 to +45 °C
820619284701	BN310P LED70/830 PSU MB L1150 BK	-20 to +45 °C
919406020861	BN310P LED92/840 PSU DA L1150 BK	-20 to +35 °C
919406020871	BN310P LED92/840 PSD- VLC DA L1150 BK	-20 to +35 °C
919406021311	BN310P LED92/840 PSD-VLC WB L1150 BK	-20 to +35 °C
919406021321	BN310P LED92/840 PSU WB EL L1150 BK	-20 to +35 °C
919406021331	BN310P LED92/840 PSD-VLC WB EL L1150 BK	-20 to +35 °C
919506310591	BN310P Xitanium 100W Driver Spare Part	-20 to +45 °C
919506310621	BN310P Bracket White Spare Part	-20 to +45 °C
919506310631	BN310P Bracket Black Spare Part	-20 to +45 °C
919506310601	BN310P CertaDrive 44W Driver Spare Part	-20 to +45 °C
919506310611	BN310P CertaDrive 65W Driver Spare Part	-20 to +45 °C

