



Ledinaire Clear Accent: reliable and superior lighting performance with precise design, suitable for diverse applications.

Ledinaire Clear Accent

A complete family of LED recessed spots that deliver superior lighting performance. Choose the best fit for every project from fixed/adjustable head with various color temperatures or All-in versions with 3 CCTs combined in one product. Enjoy great reliable performance free of maintenance.

Benefits

- IC Compliant: can be covered by insulation material.
- Easy installation: Through wiring (loop in/loop out) via connection box is optionally available.
- Long useful lifetime up to 35,000 hours.

Ledinaire Clear Accent

Features

- 3 variants available: fixed recessed RS060, adjustable recessed RS061 and adjustable recessed RS071B (All-in).
- Full product range with RS060B/RS061B: 6W, 500lm, 2700K/3000K/4000K options, available in white color.
- 3 CCT in one product with RS071B: 6W, 550lm, 2700K-3000K-4000K selectable, white and black color options.
- Extra color options available with trim accessories for RS071B: Gold and Silver.
- 36 deg beam angle for RS060B/RS061B, 40 deg & 60 deg beam angle options for RS071B for different application needs.

Application


- Retail
- Offices
- Hospitality

Versions



Downlight RS061B LDNR WH TW

Dimensional drawing



Cut-out hole diameter - Ø68mm

Ledinaire Clear Accent

Product details

ClearAccent-RS060B-DP02.tif

