



All-in-one Solar pathway light range up-to 4000 Lumen

Essential SmartBright All-in-one Solar Pathway Light

Integrated solar pathway light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Optional wall mounting arm bracket. Microwave based motion sensor for optimizing battery autonomy.

Benefits

- Saves energy
- Environment friendly
- Easy configurability with remote
- No trenching for cabling required

Features

- Remote control for selecting lighting profile
- Wall mounting arm Kit option available
- High Lumen efficacy of upto 160lm/W
- Microwave sensor for run time maximization

Application


- Walkways
- Pathways
- Amenities
- Gardens

Essential SmartBright All-in-one Solar Pathway Light

Warnings and Safety

- Not recommended to install this luminaire higher than 4 meters height.
- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- It works 100% on solar energy. This luminaire does not need any external electrical connection.

Dimensional drawing



Light Technical	
Color rendering index (CRI)	70
Operating and Electrical	
Battery type	LiFePO4
Battery voltage	3.2 V
Charge controller type	PWM
Grid connection type	Off grid
Panel type	Mono crystalline
Controls and Dimming	
Dimmable	Preset Dimming
Configurability	Not configurable
Solar dimming profile	Preset Dimming
Mechanical and Housing	
Battery location	Inbuilt luminaire
Housing Color	Grey
Ingress protection code	IP65
Overall height	44.5 mm
Approval and Application	
Ambient temperature range	0 to +45 °C

Order Code	Full Product Name	Correlated Color Temperature (Nom)
911401894102	BRC010 LED40/765 G2	6500 K
911401894702	BRC010 LED40/765 Pro G2	6500 K
911401896502	BRC010 LED40/740 G2	4000 K
911401897102	BRC010 LED40/730 G2	3000 K
911401897702	BRC010 LED40/740 Pro G2	4000 K
911401898302	BRC010 LED40/730 Pro G2	3000 K
911401893902	BRC010 LED10/765 G2	6500 K
911401894502	BRC010 LED10/765 Pro G2	6500 K
911401896302	BRC010 LED10/740 G2	4000 K
911401896902	BRC010 LED10/730 G2	3000 K
911401897502	BRC010 LED10/740 Pro G2	4000 K
911401898102	BRC010 LED10/730 Pro G2	3000 K
911401894302	BRC010 LED20/765 kit G2	6500 K
911401894902	BRC010 LED20/765 kit Pro G2	6500 K
911401896702	BRC010 LED20/740 kit G2	4000 K
911401897302	BRC010 LED20/730 kit G2	3000 K
911401897902	BRC010 LED20/740 kit Pro G2	4000 K
911401898502	BRC010 LED20/730 kit Pro G2	3000 K
911401894202	BRC010 LED10/765 kit G2	6500 K
911401894802	BRC010 LED10/765 kit Pro G2	6500 K
911401896602	BRC010 LED10/740 kit G2	4000 K
911401897202	BRC010 LED10/730 kit G2	3000 K
911401897802	BRC010 LED10/740 kit Pro G2	4000 K
911401898402	BRC010 LED10/730 kit Pro G2	3000 K
911401894002	BRC010 LED20/765 G2	6500 K
911401894602	BRC010 LED20/765 Pro G2	6500 K
911401896402	BRC010 LED20/740 G2	4000 K
911401897002	BRC010 LED20/730 G2	3000 K
911401897602	BRC010 LED20/740 Pro G2	4000 K

Essential SmartBright All-in-one Solar Pathway Light

Order Code	Full Product Name	Correlated Color Temperature (Nom)
911401898202	BRC010 LED20/730 Pro G2	3000 K
911401894402	BRC010 LED40/765 kit G2	6500 K
911401895002	BRC010 LED40/765 kit Pro G2	6500 K
911401896802	BRC010 LED40/740 kit G2	4000 K
911401897402	BRC010 LED40/730 kit G2	3000 K
911401898002	BRC010 LED40/740 kit Pro G2	4000 K
911401898602	BRC010 LED40/730 kit Pro G2	3000 K

Operating and Electrical

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401894102	BRC010 LED40/765 G2	15 Ah	500	14 W	4.5 V
911401894702	BRC010 LED40/765 Pro G2	15 Ah	1000	14 W	4.5 V
911401896502	BRC010 LED40/740 G2	15 Ah	500	14 W	4.5 V
911401897102	BRC010 LED40/730 G2	15 Ah	500	14 W	4.5 V
911401897702	BRC010 LED40/740 Pro G2	15 Ah	1000	14 W	4.5 V
911401898302	BRC010 LED40/730 Pro G2	15 Ah	1000	14 W	4.5 V
911401893902	BRC010 LED10/765 G2	5 Ah	500	6 W	5 V
911401894502	BRC010 LED10/765 Pro G2	5 Ah	1000	6 W	5 V
911401896302	BRC010 LED10/740 G2	5 Ah	500	6 W	5 V
911401896902	BRC010 LED10/730 G2	5 Ah	500	6 W	5 V
911401897502	BRC010 LED10/740 Pro G2	5 Ah	1000	6 W	5 V
911401898102	BRC010 LED10/730 Pro G2	5 Ah	1000	6 W	5 V
911401894302	BRC010 LED20/765 kit G2	8 Ah	500	8 W	4.5 V
911401894902	BRC010 LED20/765 kit Pro G2	8 Ah	1000	8 W	4.5 V
911401896702	BRC010 LED20/740 kit G2	8 Ah	500	8 W	4.5 V
911401897302	BRC010 LED20/730 kit G2	8 Ah	500	8 W	4.5 V

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401897902	BRC010 LED20/740 kit Pro G2	8 Ah	1000	8 W	4.5 V
911401898502	BRC010 LED20/730 kit Pro G2	8 Ah	1000	8 W	4.5 V
911401894202	BRC010 LED10/765 kit G2	5 Ah	500	6 W	5 V
911401894802	BRC010 LED10/765 kit Pro G2	5 Ah	1000	6 W	5 V
911401896602	BRC010 LED10/740 kit G2	5 Ah	500	6 W	5 V
911401897202	BRC010 LED10/730 kit G2	5 Ah	500	6 W	5 V
911401897802	BRC010 LED10/740 kit Pro G2	5 Ah	1000	6 W	5 V
911401898402	BRC010 LED10/730 kit Pro G2	5 Ah	1000	6 W	5 V
911401894002	BRC010 LED20/765 G2	8 Ah	500	8 W	4.5 V
911401894602	BRC010 LED20/765 Pro G2	8 Ah	1000	8 W	4.5 V
911401896402	BRC010 LED20/740 G2	8 Ah	500	8 W	4.5 V
911401897002	BRC010 LED20/730 G2	8 Ah	500	8 W	4.5 V
911401897602	BRC010 LED20/740 Pro G2	8 Ah	1000	8 W	4.5 V
911401898202	BRC010 LED20/730 Pro G2	8 Ah	1000	8 W	4.5 V
911401894402	BRC010 LED40/765 kit G2	15 Ah	500	14 W	4.5 V

Essential SmartBright All-in-one Solar Pathway Light

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401895002	BRC010 LED40/765 kit Pro G2	15 Ah	1000	14 W	4.5 V
911401896802	BRC010 LED40/740 kit G2	15 Ah	500	14 W	4.5 V
911401897402	BRC010 LED40/730 kit G2	15 Ah	500	14 W	4.5 V

Order Code	Full Product Name	Battery ampere hour	Battery charging & discharging cycles	Panel peak wattage	Panel voltage
911401898002	BRC010 LED40/740 kit Pro G2	15 Ah	1000	14 W	4.5 V
911401898602	BRC010 LED40/730 kit Pro G2	15 Ah	1000	14 W	4.5 V

Mechanical and Housing

Order Code	Full Product Name	Overall length	Overall width
911401894102	BRC010 LED40/765 G2	508 mm	228 mm
911401894702	BRC010 LED40/765 Pro G2	508 mm	228 mm
911401896502	BRC010 LED40/740 G2	508 mm	228 mm
911401897102	BRC010 LED40/730 G2	508 mm	228 mm
911401897702	BRC010 LED40/740 Pro G2	508 mm	228 mm
911401898302	BRC010 LED40/730 Pro G2	508 mm	228 mm
911401893902	BRC010 LED10/765 G2	371 mm	171 mm
911401894502	BRC010 LED10/765 Pro G2	371 mm	171 mm
911401896302	BRC010 LED10/740 G2	371 mm	171 mm
911401896902	BRC010 LED10/730 G2	371 mm	171 mm
911401897502	BRC010 LED10/740 Pro G2	371 mm	171 mm
911401898102	BRC010 LED10/730 Pro G2	371 mm	171 mm
911401894302	BRC010 LED20/765 kit G2	412 mm	203 mm
911401894902	BRC010 LED20/765 kit Pro G2	412 mm	203 mm
911401896702	BRC010 LED20/740 kit G2	412 mm	203 mm
911401897302	BRC010 LED20/730 kit G2	412 mm	203 mm
911401897902	BRC010 LED20/740 kit Pro G2	412 mm	203 mm
911401898502	BRC010 LED20/730 kit Pro G2	412 mm	203 mm

Order Code	Full Product Name	Overall length	Overall width
911401894202	BRC010 LED10/765 kit G2	371 mm	171 mm
911401894802	BRC010 LED10/765 kit Pro G2	371 mm	171 mm
911401896602	BRC010 LED10/740 kit G2	371 mm	171 mm
911401897202	BRC010 LED10/730 kit G2	371 mm	171 mm
911401897802	BRC010 LED10/740 kit Pro G2	371 mm	171 mm
911401898402	BRC010 LED10/730 kit Pro G2	371 mm	171 mm
911401894002	BRC010 LED20/765 G2	412 mm	203 mm
911401894602	BRC010 LED20/765 Pro G2	412 mm	203 mm
911401896402	BRC010 LED20/740 G2	412 mm	203 mm
911401897002	BRC010 LED20/730 G2	412 mm	203 mm
911401897602	BRC010 LED20/740 Pro G2	412 mm	203 mm
911401898202	BRC010 LED20/730 Pro G2	412 mm	203 mm
911401894402	BRC010 LED40/765 kit G2	508 mm	228 mm
911401895002	BRC010 LED40/765 kit Pro G2	508 mm	228 mm
911401896802	BRC010 LED40/740 kit G2	508 mm	228 mm
911401897402	BRC010 LED40/730 kit G2	508 mm	228 mm
911401898002	BRC010 LED40/740 kit Pro G2	508 mm	228 mm
911401898602	BRC010 LED40/730 kit Pro G2	508 mm	228 mm

