



Slim LED strip offering high quality light with diversified options in terms of brightness and light color

MASTER LED Strip

A complete family delivering superior light with great uniformity and safety. Choose the best fit for every projects, from 5 lumen packs/wattages, and 4 CCTs, and enjoy great reliable performance free of maintenance

Benefits

- Superior light quality: Great color rendering and extremely good color consistency
- Wide range of products: Variety in lumen/wattage and CCT combinations to cater to different applications.
- Easy installation: Slim design ensures fit in tight spaces.

Features

- Superior light quality: CRI 90, SDCM 3
- Full product range: 500lm,1000lm,1500lm,2000lm,2500/m, 2700K, 3000K, 4000K & 6500K options
- High efficiency for energy saving: 120lm/W
- DC 24V low voltage offers superior safety
- 60,000 Life hours

MASTER LED Strip

Application

- Retail
- Hospitality
- Offices

Dimensional drawing



Light Technical	
Color rendering index (CRI)	90
Operating and Electrical	
Input Voltage	24 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C

Light Technical

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
929002697002	MAS LEDstrip 8.3W965 950LM/M 5M	6500 K	950 lm
929002697602	MAS LEDstrip 16.6W930 1830LM/M 5M	3000 K	1,830 lm

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
929002697702	MAS LEDstrip 16.6W940 2000LM/M 5M	4000 K	2,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929002697002	MAS LEDstrip 8.3W965 950LM/M 5M	37 W
929002697602	MAS LEDstrip 16.6W930 1830LM/M 5M	67 W
929002697702	MAS LEDstrip 16.6W940 2000LM/M 5M	67 W

MASTER LED Strip

